

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332370-940

Luminaire Tested: **S123RDIP-S1165D585U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332370-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D585U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5700.2 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63	59
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	56	53	50
3	86	76	69	63	81	72	66	60	65	60	55	58	54	51	52	49	46	43
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	37
5	72	61	53	46	68	58	50	45	52	46	42	47	42	38	42	38	35	32
6	67	55	47	41	63	52	45	39	47	41	37	43	38	34	38	34	31	29
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	35	31	28	26
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.8
10°-20°	451.6	7.9
20°-30°	650.2	11.4
30°-40°	732.4	12.8
40°-50°	700.7	12.3
50°-60°	573.8	10.1
60°-70°	387.1	6.8
70°-80°	194.8	3.4
80°-90°	53.5	0.9
90°-100°	42.2	0.7
100°-110°	126.2	2.2
110°-120°	214.7	3.8
120°-130°	282.4	5.0
130°-140°	317.5	5.6
140°-150°	312.1	5.5
150°-160°	262.7	4.6
160°-170°	174.9	3.1
170°-180°	61.2	1.1
0°-30°	1264.1	22.2
0°-40°	1996.5	35.0
0°-60°	3270.9	57.4
0°-90°	3906.3	68.5
90°-120°	383.2	6.7
90°-150°	1295.1	22.7
90°-180°	1794.0	31.5
0°-180°	5700.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	0	6	12	14	15	6
95°	30	34	38	40	40	34
105°	114	116	120	120	121	123
115°	216	218	217	217	217	214
125°	316	318	317	315	313	282
135°	410	413	413	411	410	316
145°	498	499	500	500	498	311
155°	570	570	571	572	569	262
165°	621	620	620	622	619	175
175°	646	644	644	647	643	61
180°	648	648	648	648	648	



TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.0	24.5	22.0	19.4	16.9	15.9	16.1	16.4	16.8	17.0	16.9
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	12.3	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9
95°	30.1	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1
97.5°	53.3	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4
100°	69.2	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1
102.5°	87.5	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0
105°	114.4	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0
107.5°	145.8	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6
110°	165.3	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8



TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	185.7	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0
115°	216.2	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8
117.5°	246.9	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6
120°	266.0	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4
122.5°	286.0	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6
125°	316.4	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4
127.5°	344.5	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0
130°	363.2	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2
132.5°	381.8	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2
135°	410.5	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6
137.5°	436.9	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3
140°	455.2	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	471.9	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3
145°	497.9	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3
147.5°	520.8	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0
150°	536.6	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6
152.5°	549.7	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8
155°	570.2	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1
157.5°	587.6	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9
160°	598.6	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2
162.5°	608.4	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0
165°	621.0	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2
167.5°	631.1	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2
170°	636.8	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5
172.5°	641.2	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0
175°	646.0	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6
177.5°	647.9	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	16.7	16.6	16.4	16.2	16.0	15.8	15.6	15.4
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.2	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	38.5	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	59.9	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.4	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.4	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	148.9	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.3	168.7	169.2	169.2	169.1	168.8	168.6	168.4



TEST NUMBER: P332370-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	187.5	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.6	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.3	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.2	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.9	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	345.3	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.8	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.7	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	412.1	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.8	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	458.1	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.1	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.1	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	571.6	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.4	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	598.8	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	608.5	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	620.9	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	640.6	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	645.2	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.4	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)