

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332279-935

Luminaire Tested: **S123RDIP-S560D585U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332279-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3854.7 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112



TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.0
10°-20°	212.5	5.5
20°-30°	305.9	7.9
30°-40°	344.6	8.9
40°-50°	329.7	8.6
50°-60°	270.0	7.0
60°-70°	182.2	4.7
70°-80°	91.6	2.4
80°-90°	26.1	0.7
90°-100°	24.0	0.6
100°-110°	114.5	3.0
110°-120°	275.1	7.1
120°-130°	350.3	9.1
130°-140°	374.3	9.7
140°-150°	350.0	9.1
150°-160°	282.3	7.3
160°-170°	182.2	4.7
170°-180°	62.8	1.6
0°-30°	594.8	15.4
0°-40°	939.4	24.4
0°-60°	1539.1	39.9
0°-90°	1839.0	47.7
90°-120°	413.7	10.7
90°-150°	1488.3	38.6
90°-180°	2016.0	52.3
0°-180°	3854.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	0	5	12	14	15	3
95°	30	11	15	18	19	37
105°	146	149	108	26	22	155
115°	274	278	282	287	289	271
125°	387	391	393	394	395	345
135°	482	485	487	488	487	371
145°	556	559	560	561	561	348
155°	612	612	612	614	611	282
165°	646	644	644	647	644	182
175°	661	659	659	662	658	63
180°	661	661	661	661	661	



TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	12.7	11.7	10.6	9.6	8.4	8.1	8.4	8.6	9.0	9.2	9.2
90°	0.5	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2
92.5°	9.1	8.9	8.5	8.2	7.9	8.3	9.4	10.4	11.5	12.6	13.3
95°	30.0	25.5	21.0	16.5	12.1	10.4	11.6	12.8	14.0	15.2	16.0
97.5°	60.2	58.2	56.2	54.2	52.2	47.3	39.3	31.5	23.7	15.8	16.7
100°	83.0	85.2	87.4	89.5	91.7	84.3	67.2	50.3	33.2	16.2	17.0
102.5°	108.9	110.5	112.1	113.7	115.2	106.7	88.1	69.5	50.9	32.3	29.6
105°	146.4	147.6	148.8	149.9	151.1	146.8	137.0	127.2	117.4	107.5	88.3
107.5°	185.8	186.8	187.8	188.7	189.7	190.9	192.4	194.0	195.5	197.1	183.0
110°	212.2	213.0	213.9	214.7	215.6	216.7	217.8	219.0	220.2	221.4	217.8



TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.3	238.1	238.8	239.6	240.4	241.4	242.6	243.8	245.0	246.2	246.3
115°	274.5	275.2	275.8	276.5	277.2	277.9	279.0	279.9	280.9	281.9	283.0
117.5°	310.6	311.3	312.2	313.0	313.7	314.4	315.0	315.5	316.0	316.4	317.4
120°	332.9	333.9	334.9	335.9	336.9	337.5	337.9	338.2	338.5	338.8	339.8
122.5°	355.8	356.5	357.3	358.2	359.0	359.6	360.0	360.4	360.8	361.3	361.9
125°	386.9	387.9	388.7	389.6	390.5	391.2	391.6	392.0	392.4	392.9	393.0
127.5°	417.2	418.1	419.0	419.8	420.7	421.4	421.9	422.5	423.0	423.5	423.9
130°	436.1	437.0	437.8	438.7	439.5	440.2	440.7	441.1	441.5	442.0	442.4
132.5°	454.2	455.0	455.9	456.8	457.6	458.2	458.6	458.9	459.3	459.7	460.1
135°	481.7	482.4	483.0	483.7	484.4	484.9	485.3	485.8	486.2	486.6	487.0
137.5°	505.3	506.2	507.0	507.8	508.6	509.2	509.4	509.6	509.9	510.1	510.7
140°	521.0	521.7	522.4	523.0	523.7	524.2	524.4	524.8	525.1	525.5	525.9
142.5°	535.5	536.2	536.9	537.5	538.2	538.6	539.0	539.3	539.7	540.0	540.4
145°	555.9	556.6	557.4	558.2	559.0	559.5	559.6	559.9	560.1	560.3	560.5
147.5°	575.1	575.6	576.1	576.5	577.0	577.4	577.6	577.8	578.1	578.3	578.5
150°	586.9	587.2	587.5	587.8	588.1	588.4	588.7	588.8	589.1	589.3	589.5
152.5°	597.4	597.6	597.7	597.9	598.1	598.2	598.3	598.5	598.6	598.7	599.1
155°	612.3	612.2	611.9	611.7	611.5	611.5	611.6	611.7	611.7	611.9	612.4
157.5°	624.0	624.0	623.9	623.9	623.9	623.8	623.7	623.6	623.5	623.4	624.1
160°	631.0	630.9	630.9	630.7	630.6	630.5	630.3	630.3	630.2	630.1	630.7
162.5°	637.7	637.4	637.1	636.9	636.5	636.4	636.3	636.2	636.0	635.9	636.7
165°	645.8	645.4	645.1	644.8	644.5	644.2	644.1	644.0	643.9	643.8	644.7
167.5°	652.0	651.6	651.2	650.7	650.3	650.1	650.1	650.1	650.1	650.1	651.0
170°	655.6	655.1	654.7	654.3	653.8	653.6	653.6	653.6	653.6	653.6	654.5
172.5°	658.0	657.5	656.9	656.3	655.8	655.7	655.7	655.8	655.9	656.0	656.9
175°	661.0	660.5	659.9	659.4	658.8	658.6	658.7	658.8	658.9	659.0	659.8
177.5°	661.8	661.3	660.9	660.5	660.0	659.9	660.0	660.0	660.1	660.2	660.9
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	9.1	9.1	9.1	9.0	9.0	8.9	8.8	8.8
90°	12.7	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	13.9	14.6	15.3	15.8	15.9	16.0	16.2	16.3
95°	16.8	17.5	18.3	18.7	18.7	18.7	18.7	18.7
97.5°	17.6	18.4	19.3	19.8	19.9	20.0	20.1	20.2
100°	17.9	18.9	19.7	20.1	20.3	20.4	20.5	20.7
102.5°	26.9	24.2	21.5	20.2	20.4	20.7	20.8	21.0
105°	68.9	49.6	30.3	20.8	20.9	21.2	21.4	21.6
107.5°	168.8	154.6	140.4	126.1	111.5	96.9	82.4	67.8
110°	214.3	210.7	207.1	197.4	181.8	166.3	150.7	135.0



TEST NUMBER: P332279-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.3	246.4	246.5	244.9	241.6	238.2	235.0	231.7
115°	284.0	285.2	286.3	287.0	287.4	287.9	288.3	288.8
117.5°	318.2	319.1	319.9	320.5	320.6	320.6	320.7	320.8
120°	340.6	341.5	342.3	342.8	342.8	342.8	342.8	342.8
122.5°	362.5	363.1	363.7	364.0	364.1	364.2	364.3	364.4
125°	393.3	393.5	393.7	394.0	394.2	394.4	394.6	394.9
127.5°	424.2	424.6	424.9	425.0	424.7	424.6	424.3	424.1
130°	442.8	443.2	443.7	443.8	443.6	443.4	443.2	443.0
132.5°	460.5	461.0	461.4	461.5	461.2	460.8	460.5	460.2
135°	487.3	487.7	487.9	487.9	487.7	487.3	487.0	486.6
137.5°	511.2	511.7	512.2	512.4	512.1	512.0	511.7	511.5
140°	526.3	526.8	527.2	527.3	527.1	526.8	526.7	526.4
142.5°	540.7	541.1	541.4	541.4	541.1	540.8	540.4	540.2
145°	560.8	560.9	561.2	561.3	561.3	561.3	561.3	561.3
147.5°	578.8	578.9	579.2	579.0	578.5	578.0	577.6	577.0
150°	589.7	590.0	590.1	590.1	589.8	589.4	589.1	588.8
152.5°	599.5	599.9	600.3	600.2	599.8	599.3	598.7	598.2
155°	612.9	613.5	614.1	614.0	613.4	612.7	612.1	611.4
157.5°	624.7	625.3	626.0	625.9	625.0	624.2	623.4	622.5
160°	631.4	632.0	632.7	632.6	631.9	631.1	630.3	629.6
162.5°	637.4	638.2	638.9	638.9	638.3	637.6	636.9	636.3
165°	645.6	646.4	647.3	647.4	646.6	645.8	645.1	644.3
167.5°	651.9	652.7	653.6	653.6	652.7	651.9	651.0	650.1
170°	655.4	656.3	657.1	657.1	656.3	655.4	654.5	653.6
172.5°	657.7	658.6	659.4	659.4	658.5	657.5	656.5	655.6
175°	660.6	661.3	662.1	662.0	661.2	660.3	659.4	658.5
177.5°	661.6	662.3	663.0	662.9	662.0	661.2	660.3	659.4
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0

(END OF REPORT)