

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832029

Luminaire Tested: S123RDIP-S1165D805U940-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832029
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U940-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7293.3 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	94	90	95	91	88	85	80	78	75	69	68	66	60	59	58	58	58	58	53	
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	50	50	50	46	
3	86	77	70	64	80	72	66	61	64	59	55	56	52	50	49	46	44	44	44	44	40	
4	79	69	61	56	74	65	58	53	58	52	48	51	47	44	44	41	39	39	39	39	36	
5	73	62	54	49	68	59	52	47	52	47	43	46	42	39	41	37	35	35	35	35	32	
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	37	34	31	31	31	31	29	
7	63	51	44	38	59	49	42	37	44	38	34	39	35	31	35	31	28	28	28	28	26	
8	59	47	40	35	55	45	38	33	40	35	31	36	32	28	32	29	26	26	26	26	24	
9	55	43	36	31	52	41	35	30	37	32	28	34	29	26	30	27	24	24	24	24	22	
10	52	40	33	29	49	38	32	28	35	29	26	31	27	24	28	25	22	22	22	22	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	35972	35972	35972	35972	35972
5°	42712	41351	36199	29262	27167
10°	38699	42001	36018	23446	20113
15°	26644	36012	35638	19163	15911
20°	18536	27726	34922	16158	13985
25°	14125	21131	33882	14361	12889
30°	12296	16894	32579	13335	11938
35°	11289	14251	30734	12469	11073
40°	10301	12726	28322	11619	10281
45°	9302	11639	25718	10816	9490
50°	8443	10739	22647	10027	8512
55°	7638	9862	19697	9257	7302
60°	6844	8966	17108	8407	6902
65°	6316	7957	14727	7554	6525
70°	5133	6877	12850	6836	5303
75°	4500	5469	10884	5669	4675
80°	4079	4630	8920	4754	4420
85°	3717	4063	6768	4310	4063

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 27136 cd/sqm



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.6	4.2
10°-20°	704.9	9.7
20°-30°	808.7	11.1
30°-40°	797.1	10.9
40°-50°	703.0	9.6
50°-60°	540.8	7.4
60°-70°	355.6	4.9
70°-80°	172.7	2.4
80°-90°	45.4	0.6
90°-100°	33.1	0.5
100°-110°	159.9	2.2
110°-120°	392.0	5.4
120°-130°	497.7	6.8
130°-140°	531.7	7.3
140°-150°	497.2	6.8
150°-160°	401.0	5.5
160°-170°	258.8	3.5
170°-180°	89.2	1.2
0°-30°	1818.2	24.9
0°-40°	2615.4	35.9
0°-60°	3859.1	52.9
0°-90°	4432.8	60.8
90°-120°	585.0	8.0
90°-150°	2111.5	29.0
90°-180°	2860.0	39.2
0°-180°	7293.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3342	3342	3342	3342	3342	
5°	3953	3827	3350	2708	2514	361
15°	2391	3232	3198	1720	1428	675
25°	1189	1779	2853	1209	1085	562
35°	859	1084	2339	949	843	536
45°	611	765	1690	710	623	474
55°	407	526	1050	493	389	365
65°	248	312	578	297	256	243
75°	108	132	262	136	112	116
85°	30	33	55	35	33	32
90°	21	17	1	17	21	11
95°	26	22	42	22	26	22
105°	31	153	208	153	31	64
115°	410	400	390	400	410	386
125°	560	558	549	558	560	501
135°	691	691	684	691	691	533
145°	797	795	789	795	797	498
155°	868	869	869	869	868	400
165°	915	914	917	914	915	258
175°	935	936	938	936	935	89
180°	938	938	938	938	938	



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3703.7	3692.0	3680.4	3676.9	3673.5	3662.6	3651.6	3626.9	3602.3	3576.9	3551.6
5°	3953.0	3954.4	3955.8	3952.4	3948.9	3934.5	3920.2	3890.0	3859.9	3827.0	3794.1
7.5°	3876.3	3898.2	3920.2	3924.3	3928.4	3939.3	3950.3	3943.5	3936.6	3924.3	3911.9
10°	3540.6	3539.2	3537.9	3562.5	3587.2	3660.5	3733.8	3771.5	3809.2	3842.7	3876.3
12.5°	2992.5	2994.6	2996.6	3077.5	3158.3	3227.5	3296.7	3392.6	3488.5	3592.0	3695.4
15°	2391.0	2424.6	2458.1	2530.1	2602.0	2706.2	2810.3	2939.1	3067.9	3231.6	3395.4
17.5°	1963.5	1977.9	1992.3	2061.5	2130.7	2229.3	2328.0	2473.9	2619.8	2830.8	3041.9
20°	1618.2	1631.2	1644.2	1694.3	1744.3	1838.8	1933.4	2072.4	2211.5	2420.5	2629.4
22.5°	1351.0	1376.4	1401.7	1435.3	1468.9	1537.4	1605.9	1747.7	1889.5	2080.0	2270.4
25°	1189.3	1201.0	1212.6	1241.4	1270.2	1336.0	1401.7	1495.6	1589.4	1779.2	1969.0
27.5°	1079.7	1083.1	1086.6	1107.8	1129.0	1171.5	1214.0	1301.0	1388.0	1544.2	1700.4
30°	989.3	995.5	1001.6	1018.1	1034.5	1065.3	1096.2	1157.8	1219.5	1359.2	1499.0
32.5°	919.4	922.8	926.3	940.0	953.7	976.3	998.9	1047.5	1096.2	1203.0	1309.9
35°	859.1	859.8	860.5	870.8	881.0	903.0	924.9	965.3	1005.7	1084.5	1163.3
37.5°	790.6	795.4	800.2	807.7	815.3	834.5	853.6	886.5	919.4	984.5	1049.6
40°	733.1	737.2	741.3	750.2	759.1	774.2	789.2	819.4	849.5	905.7	961.9
42.5°	675.5	678.3	681.0	689.9	698.8	717.3	735.8	759.8	783.8	830.3	876.9
45°	611.1	618.0	624.8	634.4	644.0	659.8	675.5	700.2	724.8	764.6	804.3
47.5°	557.7	561.1	564.5	572.7	581.0	600.2	619.3	641.3	663.2	700.2	737.2
50°	504.2	505.6	507.0	514.5	522.0	539.2	556.3	581.7	607.0	641.3	675.5
52.5°	453.5	457.0	460.4	467.9	475.5	487.1	498.8	524.8	550.8	584.4	618.0
55°	407.0	409.0	411.1	416.5	422.0	435.7	449.4	472.0	494.6	525.5	556.3
57.5°	363.1	365.8	368.6	372.7	376.8	389.1	401.5	421.3	441.2	472.0	502.9
60°	317.9	321.3	324.7	329.5	334.3	343.9	353.5	371.3	389.1	416.5	443.9
62.5°	285.0	285.7	286.4	290.5	294.6	301.4	308.3	322.7	337.1	364.5	391.9
65°	248.0	250.1	252.1	254.2	256.2	261.7	267.2	279.5	291.9	312.4	333.0
67.5°	209.6	211.7	213.8	217.2	220.6	225.4	230.2	238.4	246.6	265.8	285.0
70°	163.1	163.1	163.1	168.5	174.0	182.2	190.5	196.6	202.8	218.5	234.3
72.5°	132.9	133.6	134.3	135.0	135.7	140.4	145.2	155.5	165.8	175.4	185.0
75°	108.2	108.9	109.6	110.3	111.0	112.4	113.7	117.2	120.6	131.5	142.5
77.5°	86.3	87.0	87.7	88.4	89.1	90.4	91.8	93.2	94.5	98.7	102.8
80°	65.8	66.5	67.1	67.8	68.5	69.2	69.9	71.3	72.6	74.7	76.7
82.5°	48.0	48.0	48.0	48.0	48.0	49.3	50.7	50.7	50.7	52.1	53.4
85°	30.1	30.1	30.1	30.8	31.5	31.5	31.5	32.2	32.9	32.9	32.9
87.5°	13.7	13.0	12.3	13.0	13.7	13.7	13.7	14.4	15.1	15.1	15.1
90°	20.9	20.6	20.3	20.0	19.7	19.2	18.6	18.0	17.4	16.7	14.7
92.5°	23.7	23.5	23.4	23.2	23.1	22.5	21.4	20.3	19.2	18.1	16.7
95°	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8	22.7	21.6	19.9
97.5°	28.6	28.4	28.3	28.1	28.0	27.3	26.0	24.8	23.5	22.3	30.2
100°	29.3	29.1	29.0	28.8	28.7	28.0	26.7	25.5	24.2	23.0	47.2
102.5°	30.0	29.7	29.4	29.0	28.7	31.1	36.3	41.4	46.5	51.6	78.5
105°	30.7	30.4	30.1	29.7	29.4	43.0	70.4	97.8	125.3	152.7	166.6
107.5°	72.5	92.8	113.1	133.4	153.7	175.8	199.6	223.5	247.3	271.2	268.9
110°	191.7	213.9	236.0	258.2	280.3	294.0	299.1	304.2	309.3	314.4	312.7



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.2	363.5	363.8	364.1	364.4	363.9	362.5	361.1	359.7	358.3	356.6
115°	409.9	409.3	408.7	408.1	407.4	406.4	404.8	403.3	401.7	400.2	398.8
117.5°	447.6	447.4	447.3	447.1	446.9	446.2	445.0	443.8	442.5	441.3	440.5
120°	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5	482.3	481.0	480.6
122.5°	524.9	524.8	524.6	524.5	524.3	523.9	523.1	522.3	521.5	520.8	520.1
125°	560.5	560.2	559.9	559.6	559.3	558.9	558.6	558.3	558.0	557.7	557.1
127.5°	595.4	595.7	596.0	596.3	596.6	596.5	596.0	595.6	595.1	594.7	593.9
130°	628.8	629.1	629.4	629.7	630.1	629.9	629.3	628.7	628.0	627.4	626.8
132.5°	659.5	660.0	660.4	660.9	661.3	661.3	660.7	660.0	659.4	658.8	658.3
135°	690.9	691.3	691.8	692.3	692.7	692.7	692.3	691.8	691.3	690.9	690.2
137.5°	720.8	721.1	721.5	721.8	722.1	721.8	721.1	720.3	719.5	718.7	718.4
140°	747.3	747.6	747.9	748.3	748.6	748.4	747.8	747.2	746.6	745.9	745.5
142.5°	771.7	772.2	772.7	773.1	773.6	773.6	773.1	772.7	772.2	771.7	771.3
145°	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0	795.7	795.4	795.1
147.5°	814.9	815.7	816.5	817.3	818.0	818.3	818.0	817.7	817.4	817.0	816.7
150°	835.9	836.3	836.8	837.3	837.7	837.8	837.5	837.2	836.9	836.6	836.3
152.5°	852.6	853.4	854.1	854.9	855.7	855.8	855.2	854.5	853.9	853.3	853.1
155°	867.9	868.9	869.8	870.7	871.7	871.7	871.0	870.2	869.4	868.6	868.5
157.5°	881.2	882.4	883.7	884.9	886.1	886.3	885.4	884.4	883.5	882.6	882.7
160°	893.7	894.8	895.9	897.0	898.1	898.1	897.2	896.3	895.4	894.4	894.6
162.5°	905.6	906.5	907.4	908.4	909.3	909.2	908.1	907.0	906.0	904.9	905.0
165°	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4	915.2	913.9	914.1
167.5°	921.6	922.9	924.1	925.3	926.6	926.6	925.3	924.1	922.9	921.6	921.6
170°	927.9	929.1	930.4	931.6	932.8	932.8	931.6	930.4	929.1	927.9	927.9
172.5°	931.4	932.8	934.2	935.6	936.9	937.0	935.8	934.5	933.3	932.1	931.9
175°	934.9	936.1	937.3	938.6	939.8	939.9	938.8	937.7	936.6	935.6	935.4
177.5°	935.6	937.1	938.7	940.2	941.8	941.9	940.7	939.4	938.2	936.9	936.8
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3548.1	3544.7	3511.8	3479.0	3446.8	3414.6	3390.6	3366.6	3326.2	3285.8	3260.4
5°	3768.1	3742.0	3690.0	3637.9	3559.8	3481.7	3415.9	3350.2	3266.6	3183.0	3113.1
7.5°	3890.7	3869.5	3806.4	3743.4	3640.0	3536.5	3433.7	3331.0	3207.7	3084.3	2978.8
10°	3894.1	3911.9	3859.9	3807.8	3691.3	3574.9	3435.1	3295.3	3129.6	2963.8	2827.4
12.5°	3772.2	3848.9	3837.9	3827.0	3708.5	3589.9	3420.0	3250.1	3046.7	2843.2	2672.6
15°	3544.0	3692.7	3736.6	3780.4	3682.4	3584.5	3391.3	3198.1	2959.0	2719.9	2523.9
17.5°	3250.1	3458.4	3574.2	3690.0	3618.7	3547.5	3335.8	3124.1	2854.8	2585.6	2372.5
20°	2902.1	3174.8	3356.3	3537.9	3511.8	3485.8	3267.3	3048.7	2758.2	2467.7	2236.9
22.5°	2558.2	2845.9	3096.7	3347.4	3374.1	3400.9	3180.2	2959.6	2641.8	2323.9	2088.9
25°	2261.5	2554.1	2852.8	3151.5	3211.8	3272.1	3062.4	2852.8	2523.2	2193.7	1960.1
27.5°	1978.6	2256.7	2585.6	2914.4	3024.0	3133.7	2941.8	2750.0	2406.8	2063.5	1830.6
30°	1747.7	1996.4	2332.1	2667.8	2820.6	2973.3	2797.3	2621.2	2280.7	1940.2	1712.1
32.5°	1532.6	1755.2	2092.3	2429.4	2606.8	2784.3	2632.2	2480.1	2152.6	1825.1	1599.7
35°	1362.7	1562.0	1876.5	2191.0	2389.6	2588.3	2463.6	2338.9	2019.0	1699.1	1486.0
37.5°	1216.7	1383.9	1679.2	1974.5	2185.5	2396.5	2292.4	2188.2	1887.5	1586.7	1385.3
40°	1096.2	1230.4	1505.2	1779.9	1986.8	2193.7	2104.6	2015.6	1746.3	1477.1	1288.7
42.5°	992.7	1108.5	1355.1	1601.8	1791.5	1981.3	1922.4	1863.5	1619.6	1375.7	1201.0
45°	901.6	998.9	1216.1	1433.2	1607.9	1782.6	1736.1	1689.5	1479.1	1268.8	1108.5
47.5°	820.8	904.3	1098.2	1292.1	1449.0	1605.9	1562.7	1519.6	1345.5	1171.5	1025.6
50°	746.8	818.0	979.7	1141.4	1282.5	1423.6	1388.0	1352.4	1208.5	1064.7	938.6
52.5°	676.9	735.8	881.0	1026.3	1140.0	1253.7	1226.3	1198.9	1087.9	977.0	862.5
55°	610.4	664.5	787.2	909.8	1007.1	1104.4	1077.0	1049.6	963.3	876.9	776.2
57.5°	550.1	597.4	696.7	796.1	873.5	950.9	937.9	924.9	853.0	781.0	698.1
60°	486.4	528.9	614.5	700.2	762.5	824.9	809.8	794.7	743.3	692.0	620.7
62.5°	429.6	467.2	535.8	604.3	655.0	705.7	694.7	683.7	644.7	605.6	546.7
65°	370.0	407.0	462.4	517.9	557.7	597.4	587.8	578.2	548.8	519.3	472.0
67.5°	315.8	346.7	394.6	442.6	469.3	496.0	490.5	485.1	462.4	439.8	402.8
70°	261.0	287.7	327.5	367.2	385.7	404.2	406.3	408.3	387.8	367.2	339.8
72.5°	206.2	227.5	264.4	301.4	315.8	330.2	329.5	328.8	316.5	304.2	279.5
75°	158.3	174.0	202.8	231.6	243.9	256.2	259.0	261.7	250.1	238.4	224.7
77.5°	113.7	124.7	146.6	168.5	182.2	195.9	197.3	198.7	193.2	187.7	174.7
80°	80.2	83.6	97.3	111.0	125.4	139.8	141.8	143.9	138.4	132.9	124.7
82.5°	55.5	57.5	62.3	67.1	78.8	90.4	93.2	95.9	93.2	90.4	81.5
85°	33.6	34.3	36.3	38.4	43.8	49.3	52.1	54.8	53.4	52.1	47.3
87.5°	15.1	15.1	15.8	16.4	17.8	19.2	22.6	26.0	24.0	21.9	19.9
90°	12.7	10.7	8.7	6.9	5.3	3.8	2.2	0.7	2.2	3.8	5.3
92.5°	15.3	13.9	12.5	12.3	13.2	14.2	15.1	16.0	15.1	14.2	13.2
95°	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5	36.2	29.8	23.5
97.5°	38.1	46.0	53.9	60.0	64.4	68.7	73.0	77.4	73.0	68.7	64.4
100°	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8	120.9	124.0	127.1
102.5°	105.5	132.5	159.4	171.9	169.9	167.9	165.8	163.8	165.8	167.9	169.9
105°	180.6	194.5	208.4	214.6	212.9	211.2	209.5	207.7	209.5	211.2	212.9
107.5°	266.5	264.2	261.9	260.0	258.6	257.2	255.8	254.5	255.8	257.2	258.6
110°	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.2	302.4	303.6	304.9



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.9	353.2	351.5	350.1	349.0	347.9	346.9	345.8	346.9	347.9	349.0
115°	397.4	396.0	394.6	393.4	392.5	391.6	390.6	389.7	390.6	391.6	392.5
117.5°	439.7	439.0	438.2	437.3	436.2	435.1	434.0	432.9	434.0	435.1	436.2
120°	480.1	479.6	479.2	478.2	476.8	475.4	474.1	472.7	474.1	475.4	476.8
122.5°	519.5	518.9	518.3	517.4	516.3	515.3	514.2	513.1	514.2	515.3	516.3
125°	556.5	555.8	555.2	554.3	553.1	551.8	550.6	549.3	550.6	551.8	553.1
127.5°	593.1	592.3	591.6	590.6	589.3	588.1	586.8	585.6	586.8	588.1	589.3
130°	626.2	625.6	624.9	624.0	622.8	621.5	620.3	619.1	620.3	621.5	622.8
132.5°	657.9	657.4	656.9	656.1	654.8	653.6	652.4	651.1	652.4	653.6	654.8
135°	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9	684.8	685.7	686.7
137.5°	718.1	717.8	717.5	716.7	715.5	714.3	713.0	711.8	713.0	714.3	715.5
140°	745.0	744.5	744.1	743.4	742.4	741.5	740.6	739.7	740.6	741.5	742.4
142.5°	770.8	770.3	769.9	769.2	768.2	767.3	766.4	765.5	766.4	767.3	768.2
145°	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2	790.2	791.3	792.4
147.5°	816.4	816.1	815.8	815.3	814.5	813.7	812.9	812.2	812.9	813.7	814.5
150°	835.9	835.6	835.3	834.9	834.5	834.0	833.5	833.1	833.5	834.0	834.5
152.5°	853.0	852.8	852.7	852.5	852.4	852.2	852.1	851.9	852.1	852.2	852.4
155°	868.3	868.2	868.0	868.1	868.4	868.7	869.0	869.3	869.0	868.7	868.4
157.5°	882.9	883.0	883.2	883.3	883.3	883.3	883.3	883.3	883.3	883.3	883.3
160°	894.7	894.9	895.0	895.2	895.4	895.5	895.7	895.8	895.7	895.5	895.4
162.5°	905.2	905.3	905.5	905.8	906.3	906.7	907.2	907.7	907.2	906.7	906.3
165°	914.3	914.4	914.6	914.9	915.3	915.8	916.3	916.7	916.3	915.8	915.3
167.5°	921.6	921.6	921.6	921.9	922.5	923.2	923.8	924.4	923.8	923.2	922.5
170°	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7	930.1	929.4	928.8
172.5°	931.8	931.6	931.4	931.8	932.5	933.3	934.1	934.9	934.1	933.3	932.5
175°	935.2	935.1	934.9	935.2	936.0	936.8	937.6	938.3	937.6	936.8	936.0
177.5°	936.6	936.5	936.3	936.6	937.4	938.2	939.0	939.7	939.0	938.2	937.4
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3235.1	3196.0	3157.0	3128.9	3100.8	3065.8	3030.9	3029.5	3028.2	3002.1	2976.1
5°	3043.2	2975.4	2907.6	2841.1	2774.7	2708.2	2641.8	2626.7	2611.6	2589.0	2566.4
7.5°	2873.3	2765.1	2656.8	2571.9	2486.9	2420.5	2354.0	2308.8	2263.6	2228.6	2193.7
10°	2691.1	2556.8	2422.5	2319.8	2217.0	2145.1	2073.1	2021.1	1969.0	1944.3	1919.7
12.5°	2502.0	2356.1	2210.1	2109.4	2008.7	1922.4	1836.1	1788.8	1741.5	1707.3	1673.0
15°	2328.0	2171.1	2014.2	1907.3	1800.5	1719.6	1638.8	1591.5	1544.2	1510.0	1475.7
17.5°	2159.4	2001.2	1842.9	1734.7	1626.4	1553.1	1479.8	1433.9	1388.0	1366.8	1345.5
20°	2006.0	1846.4	1686.7	1584.6	1482.6	1410.6	1338.7	1314.0	1289.4	1269.5	1249.6
22.5°	1853.9	1700.4	1547.0	1449.0	1351.0	1299.0	1246.9	1227.0	1207.2	1192.1	1177.0
25°	1726.5	1573.7	1420.9	1335.3	1249.6	1209.2	1168.8	1155.8	1142.8	1127.7	1112.6
27.5°	1597.7	1452.4	1307.2	1238.7	1170.2	1137.3	1104.4	1087.9	1071.5	1059.2	1046.8
30°	1483.9	1349.7	1215.4	1158.5	1101.6	1072.9	1044.1	1026.3	1008.5	996.8	985.2
32.5°	1374.3	1255.1	1135.9	1087.3	1038.6	1010.5	982.4	965.3	948.2	934.5	920.8
35°	1272.9	1169.5	1066.0	1021.5	977.0	948.9	920.8	903.7	886.5	872.8	859.1
37.5°	1183.9	1090.0	996.1	954.3	912.6	887.9	863.2	845.4	827.6	813.2	798.8
40°	1100.3	1017.4	934.5	894.1	853.6	826.9	800.2	784.4	768.7	755.7	742.7
42.5°	1026.3	950.2	874.2	834.5	794.7	769.4	744.0	725.5	707.0	699.5	692.0
45°	948.2	881.0	813.9	775.5	737.2	710.5	683.7	668.0	652.2	645.4	638.5
47.5°	879.7	817.3	755.0	717.3	679.6	655.6	631.7	619.3	607.0	597.4	587.8
50°	812.5	752.2	692.0	655.6	619.3	598.8	578.2	563.2	548.1	541.2	534.4
52.5°	748.1	693.3	638.5	601.5	564.5	544.7	524.8	511.8	498.8	484.4	470.0
55°	675.5	627.6	579.6	546.7	513.8	493.3	472.7	457.6	442.6	427.5	412.4
57.5°	615.2	568.0	520.7	491.2	461.8	441.9	422.0	405.6	389.1	376.8	364.5
60°	549.5	508.3	467.2	438.5	409.7	390.5	371.3	355.6	339.8	333.6	327.5
62.5°	487.8	449.4	411.1	385.7	360.4	341.9	323.4	313.1	302.8	298.7	294.6
65°	424.8	391.9	359.0	335.7	312.4	296.6	280.9	276.1	271.3	267.9	264.4
67.5°	365.8	337.8	309.7	289.1	268.6	257.6	246.6	241.2	235.7	231.6	227.5
70°	312.4	287.7	263.1	245.3	227.5	217.2	206.9	202.1	197.3	189.8	182.2
72.5°	254.9	235.7	216.5	202.8	189.1	180.2	171.3	161.7	152.1	145.2	138.4
75°	211.0	191.8	172.6	159.6	146.6	136.3	126.1	122.6	119.2	117.2	115.1
77.5°	161.7	145.2	128.8	118.5	108.2	103.5	98.7	96.6	94.5	93.9	93.2
80°	116.5	102.8	89.1	83.6	78.1	76.7	75.4	74.0	72.6	71.9	71.3
82.5°	72.6	65.8	58.9	57.5	56.2	55.5	54.8	54.1	53.4	52.8	52.1
85°	42.5	39.7	37.0	36.3	35.6	34.9	34.3	34.3	34.3	34.3	34.3
87.5°	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.1	16.4
90°	6.9	8.7	10.7	12.7	14.7	16.7	17.4	18.0	18.6	19.2	19.7
92.5°	12.3	12.5	13.9	15.3	16.7	18.1	19.2	20.3	21.4	22.5	23.1
95°	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8	24.9	25.9	26.5
97.5°	60.0	53.9	46.0	38.1	30.2	22.3	23.5	24.8	26.0	27.3	28.0
100°	130.2	119.7	95.5	71.3	47.2	23.0	24.2	25.5	26.7	28.0	28.7
102.5°	171.9	159.4	132.5	105.5	78.5	51.6	46.5	41.4	36.3	31.1	28.7
105°	214.6	208.4	194.5	180.6	166.6	152.7	125.3	97.8	70.4	43.0	29.4
107.5°	260.0	261.9	264.2	266.5	268.9	271.2	247.3	223.5	199.6	175.8	153.7
110°	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2	299.1	294.0	280.3



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	350.1	351.5	353.2	354.9	356.6	358.3	359.7	361.1	362.5	363.9	364.4
115°	393.4	394.6	396.0	397.4	398.8	400.2	401.7	403.3	404.8	406.4	407.4
117.5°	437.3	438.2	439.0	439.7	440.5	441.3	442.5	443.8	445.0	446.2	446.9
120°	478.2	479.2	479.6	480.1	480.6	481.0	482.3	483.5	484.7	486.0	486.6
122.5°	517.4	518.3	518.9	519.5	520.1	520.8	521.5	522.3	523.1	523.9	524.3
125°	554.3	555.2	555.8	556.5	557.1	557.7	558.0	558.3	558.6	558.9	559.3
127.5°	590.6	591.6	592.3	593.1	593.9	594.7	595.1	595.6	596.0	596.5	596.6
130°	624.0	624.9	625.6	626.2	626.8	627.4	628.0	628.7	629.3	629.9	630.1
132.5°	656.1	656.9	657.4	657.9	658.3	658.8	659.4	660.0	660.7	661.3	661.3
135°	687.6	688.4	689.0	689.6	690.2	690.9	691.3	691.8	692.3	692.7	692.7
137.5°	716.7	717.5	717.8	718.1	718.4	718.7	719.5	720.3	721.1	721.8	722.1
140°	743.4	744.1	744.5	745.0	745.5	745.9	746.6	747.2	747.8	748.4	748.6
142.5°	769.2	769.9	770.3	770.8	771.3	771.7	772.2	772.7	773.1	773.6	773.6
145°	793.5	794.2	794.5	794.8	795.1	795.4	795.7	796.0	796.4	796.7	796.8
147.5°	815.3	815.8	816.1	816.4	816.7	817.0	817.4	817.7	818.0	818.3	818.0
150°	834.9	835.3	835.6	835.9	836.3	836.6	836.9	837.2	837.5	837.8	837.7
152.5°	852.5	852.7	852.8	853.0	853.1	853.3	853.9	854.5	855.2	855.8	855.7
155°	868.1	868.0	868.2	868.3	868.5	868.6	869.4	870.2	871.0	871.7	871.7
157.5°	883.3	883.2	883.0	882.9	882.7	882.6	883.5	884.4	885.4	886.3	886.1
160°	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3	897.2	898.1	898.1
162.5°	905.8	905.5	905.3	905.2	905.0	904.9	906.0	907.0	908.1	909.2	909.3
165°	914.9	914.6	914.4	914.3	914.1	913.9	915.2	916.4	917.7	918.9	919.0
167.5°	921.9	921.6	921.6	921.6	921.6	921.6	922.9	924.1	925.3	926.6	926.6
170°	928.2	927.9	927.9	927.9	927.9	927.9	929.1	930.4	931.6	932.8	932.8
172.5°	931.8	931.4	931.6	931.8	931.9	932.1	933.3	934.5	935.8	937.0	936.9
175°	935.2	934.9	935.1	935.2	935.4	935.6	936.6	937.7	938.8	939.9	939.8
177.5°	936.6	936.3	936.5	936.6	936.8	936.9	938.2	939.4	940.7	941.9	941.8
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3341.9	3341.9	3341.9	3341.9
2.5°	2969.2	2962.4	2959.6	2956.9
5°	2545.2	2523.9	2519.1	2514.3
7.5°	2184.8	2175.9	2146.4	2117.0
10°	1892.3	1864.9	1852.5	1840.2
12.5°	1647.7	1622.3	1618.2	1614.1
15°	1457.9	1440.1	1433.9	1427.8
17.5°	1333.2	1320.9	1313.3	1305.8
20°	1240.7	1231.8	1226.3	1220.9
22.5°	1170.2	1163.3	1159.2	1155.1
25°	1102.3	1092.1	1088.6	1085.2
27.5°	1037.9	1029.0	1025.6	1022.2
30°	977.6	970.1	965.3	960.5
32.5°	911.9	903.0	900.2	897.5
35°	853.6	848.2	845.4	842.7
37.5°	792.0	785.1	781.0	776.9
40°	739.2	735.8	733.7	731.7
42.5°	685.8	679.6	678.9	678.3
45°	632.4	626.2	624.8	623.4
47.5°	582.3	576.9	576.2	575.5
50°	526.8	519.3	513.8	508.3
52.5°	463.1	456.3	451.5	446.7
55°	404.9	397.4	393.2	389.1
57.5°	361.0	357.6	355.6	353.5
60°	325.4	323.4	322.0	320.6
62.5°	292.5	290.5	290.5	290.5
65°	262.4	260.3	258.3	256.2
67.5°	223.3	219.2	218.5	217.9
70°	176.1	169.9	169.2	168.5
72.5°	137.7	137.0	135.7	134.3
75°	113.7	112.4	112.4	112.4
77.5°	91.8	90.4	90.4	90.4
80°	70.6	69.9	70.6	71.3
82.5°	52.1	52.1	51.4	50.7
85°	33.6	32.9	32.9	32.9
87.5°	16.4	16.4	16.4	16.4
90°	20.0	20.3	20.6	20.9
92.5°	23.2	23.4	23.5	23.7
95°	26.5	26.5	26.5	26.5
97.5°	28.1	28.3	28.4	28.6
100°	28.8	29.0	29.1	29.3
102.5°	29.0	29.4	29.7	30.0
105°	29.7	30.1	30.4	30.7
107.5°	133.4	113.1	92.8	72.5
110°	258.2	236.0	213.9	191.7



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	364.1	363.8	363.5	363.2
115°	408.1	408.7	409.3	409.9
117.5°	447.1	447.3	447.4	447.6
120°	486.6	486.6	486.6	486.6
122.5°	524.5	524.6	524.8	524.9
125°	559.6	559.9	560.2	560.5
127.5°	596.3	596.0	595.7	595.4
130°	629.7	629.4	629.1	628.8
132.5°	660.9	660.4	660.0	659.5
135°	692.3	691.8	691.3	690.9
137.5°	721.8	721.5	721.1	720.8
140°	748.3	747.9	747.6	747.3
142.5°	773.1	772.7	772.2	771.7
145°	796.8	796.8	796.8	796.8
147.5°	817.3	816.5	815.7	814.9
150°	837.3	836.8	836.3	835.9
152.5°	854.9	854.1	853.4	852.6
155°	870.7	869.8	868.9	867.9
157.5°	884.9	883.7	882.4	881.2
160°	897.0	895.9	894.8	893.7
162.5°	908.4	907.4	906.5	905.6
165°	917.9	916.8	915.7	914.6
167.5°	925.3	924.1	922.9	921.6
170°	931.6	930.4	929.1	927.9
172.5°	935.6	934.2	932.8	931.4
175°	938.6	937.3	936.1	934.9
177.5°	940.2	938.7	937.1	935.6
180°	938.3	938.3	938.3	938.3



TEST NUMBER: P832029

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.15	15.05	15.02	15.93	17.05	18.82	19.71	19.69	20.60	21.71
	3H	15.38	16.18	16.26	17.07	18.21	20.32	21.12	21.21	22.02	23.16
	4H	15.76	16.52	16.66	17.42	18.57	20.81	21.57	21.71	22.47	23.62
	6H	16.05	16.74	16.96	17.65	18.81	21.13	21.82	22.04	22.73	23.89
	8H	16.14	16.80	17.06	17.72	18.88	21.21	21.87	22.13	22.79	23.96
	12H	16.19	16.82	17.11	17.74	18.92	21.24	21.87	22.17	22.79	23.97
4H	2H	14.88	15.64	15.79	16.54	17.69	18.82	19.58	19.72	20.47	21.63
	3H	16.26	16.89	17.17	17.82	18.98	20.48	21.11	21.40	22.04	23.21
	4H	16.72	17.29	17.64	18.21	19.40	21.09	21.66	22.02	22.59	23.78
	6H	17.09	17.58	18.03	18.53	19.72	21.53	22.03	22.47	22.97	24.17
	8H	17.21	17.67	18.15	18.62	19.82	21.67	22.12	22.61	23.07	24.27
	12H	17.29	17.70	18.25	18.67	19.87	21.73	22.14	22.69	23.10	24.31
8H	4H	17.04	17.49	17.98	18.44	19.64	21.06	21.52	22.01	22.47	23.67
	6H	17.50	17.88	18.47	18.86	20.07	21.56	21.94	22.53	22.93	24.13
	8H	17.69	18.03	18.67	19.00	20.22	21.75	22.08	22.73	23.06	24.28
	12H	17.84	18.13	18.81	19.10	20.37	21.87	22.16	22.85	23.13	24.40
12H	4H	17.05	17.46	18.01	18.42	19.63	21.02	21.43	21.98	22.39	23.60
	6H	17.56	17.89	18.54	18.87	20.09	21.54	21.87	22.51	22.85	24.07
	8H	17.78	18.07	18.76	19.04	20.31	21.73	22.03	22.71	22.99	24.27