

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332281-935

Luminaire Tested: **S123RDIP-S560D585U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332281-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3664.2 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	36
3	82	73	66	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	34	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112



TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.1
10°-20°	212.5	5.8
20°-30°	305.9	8.3
30°-40°	344.6	9.4
40°-50°	329.7	9.0
50°-60°	270.0	7.4
60°-70°	182.2	5.0
70°-80°	91.6	2.5
80°-90°	26.1	0.7
90°-100°	135.0	3.7
100°-110°	382.3	10.4
110°-120°	376.1	10.3
120°-130°	300.0	8.2
130°-140°	236.5	6.5
140°-150°	176.5	4.8
150°-160°	123.0	3.4
160°-170°	72.3	2.0
170°-180°	23.5	0.6
0°-30°	594.8	16.2
0°-40°	939.4	25.6
0°-60°	1539.1	42.0
0°-90°	1839.0	50.2
90°-120°	893.4	24.4
90°-150°	1606.4	43.8
90°-180°	1825.0	49.8
0°-180°	3664.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	1	6	12	14	14	3
95°	17	54	291	85	57	18
105°	57	84	395	690	625	61
115°	101	125	302	662	760	100
125°	140	165	282	511	599	124
135°	164	196	278	421	486	127
145°	187	214	274	345	380	117
155°	213	229	266	302	315	98
165°	232	239	254	270	274	65
175°	242	242	244	248	247	23
180°	243	243	243	243	243	



TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	12.8	11.8	10.7	9.6	8.6	8.1	8.4	8.7	9.0	9.3	9.1
90°	0.9	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8
92.5°	6.1	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0
95°	16.7	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2
97.5°	28.5	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8
100°	36.3	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8
102.5°	44.6	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8
105°	57.0	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8
107.5°	70.1	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4
110°	79.6	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3



TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.2	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6
115°	100.7	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0
117.5°	113.1	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1
120°	121.8	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1
122.5°	129.2	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0
125°	140.0	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4
127.5°	148.1	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3
130°	153.3	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7
132.5°	157.1	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6
135°	164.0	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9
137.5°	170.5	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2
140°	174.9	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6
142.5°	179.5	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5
145°	187.1	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2
147.5°	194.8	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1
150°	199.8	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4
152.5°	205.0	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3
155°	212.7	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5
157.5°	218.7	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2
160°	223.4	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7
162.5°	227.0	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1
165°	232.3	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3
167.5°	236.3	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7
170°	238.7	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0
172.5°	240.2	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2
175°	242.1	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0
177.5°	243.0	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	9.0	9.0	9.0	9.1	8.9	8.9	8.9	8.6
90°	12.3	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	41.3	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	176.8	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	440.7	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	579.0	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	625.0	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	638.4	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	599.7	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	562.7	653.2	715.1	749.4	763.2	767.1	766.1	765.1



TEST NUMBER: P332281-935

CATALOG NUMBER: S123RDIP-S560D585U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	526.2	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	477.9	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	442.7	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	424.3	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	409.7	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	390.4	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	373.5	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	362.9	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	353.1	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	339.8	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	327.8	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	320.7	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	314.0	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	305.9	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	299.4	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	294.6	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	290.3	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	283.9	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	277.0	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	273.0	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	268.4	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	262.3	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	256.9	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	253.4	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	250.3	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.1	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.4	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)