

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332269-940

Luminaire Tested: **S123RDIP-S340D1195U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332269-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U940-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5011.8 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.0
10°-20°	133.9	2.7
20°-30°	192.7	3.8
30°-40°	217.1	4.3
40°-50°	207.7	4.1
50°-60°	170.1	3.4
60°-70°	114.8	2.3
70°-80°	57.7	1.2
80°-90°	19.2	0.4
90°-100°	284.8	5.7
100°-110°	806.5	16.1
110°-120°	793.4	15.8
120°-130°	632.8	12.6
130°-140°	498.9	10.0
140°-150°	372.4	7.4
150°-160°	259.6	5.2
160°-170°	152.5	3.0
170°-180°	49.6	1.0
0°-30°	374.7	7.5
0°-40°	591.8	11.8
0°-60°	969.6	19.3
0°-90°	1161.3	23.2
90°-120°	1884.7	37.6
90°-150°	3388.9	67.6
90°-180°	3851.0	76.8
0°-180°	5011.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	2	12	26	29	30	3
95°	35	114	614	179	120	38
105°	120	178	833	1457	1318	128
115°	212	265	637	1397	1603	210
125°	295	349	595	1077	1264	262
135°	346	413	586	887	1025	267
145°	395	452	579	728	801	247
155°	449	484	560	637	664	206
165°	490	504	537	569	579	138
175°	511	511	515	522	521	48
180°	512	512	512	512	512	



TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.4	8.0	7.6	7.4	7.0	7.0	7.7	8.3	8.9	9.5	9.2
90°	2.1	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9
92.5°	12.8	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2
95°	35.2	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3
97.5°	60.1	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6
100°	76.7	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3
102.5°	94.1	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5
105°	120.2	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3
107.5°	147.9	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7
110°	167.8	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0



TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.1	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6
115°	212.4	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4
117.5°	238.7	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2
120°	256.9	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0
122.5°	272.7	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0
125°	295.2	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5
127.5°	312.5	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0
130°	323.2	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3
132.5°	331.5	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6
135°	346.1	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6
137.5°	359.7	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3
140°	368.8	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9
142.5°	378.8	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2
145°	394.8	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3
147.5°	410.9	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6
150°	421.7	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8
152.5°	432.5	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2
155°	448.6	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2
157.5°	461.5	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0
160°	471.4	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6
162.5°	478.8	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1
165°	490.1	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9
167.5°	498.6	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2
170°	503.5	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4
172.5°	506.8	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6
175°	510.8	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0
177.5°	512.6	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	9.4	9.5	9.6	10.0	9.7	9.8	10.0	9.6
90°	25.9	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	87.2	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	373.0	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	929.7	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1221.5	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1318.5	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1346.8	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1265.2	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1187.3	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2





TEST NUMBER: P332269-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1110.2	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1008.1	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	934.1	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	895.1	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	864.4	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	823.7	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	788.0	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	765.6	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	744.9	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	716.9	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	691.4	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	676.5	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	662.5	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	645.4	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	631.6	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	621.6	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	612.5	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	598.8	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	584.3	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	576.0	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	566.1	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	553.2	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	542.1	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	534.6	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	528.0	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	519.1	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	513.4	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)