

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332282-935

Luminaire Tested: **S123RDIP-S560D805U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332282-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4683.6 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																												
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35																												
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	36	30																												
3	81	72	65	59	73	66	60	55	54	50	47	44	41	39	34	32	31	26																												
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23																												
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	28	26	24	20																												
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	18																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16																												
8	54	42	35	29	49	39	32	28	33	28	24	27	23	20	22	19	17	15																												
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	13																												
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14	12																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8291	8291	8291	8291
5°	9884	8327	7333	8327
10°	12342	8279	6625	8279
15°	14487	8195	6042	8195
20°	16167	8069	5545	8069
25°	15909	7935	5241	7935
30°	11436	7812	4927	7812
35°	7636	7653	4724	7653
40°	5626	7461	4513	7461
45°	4719	7124	4306	7124
50°	4165	6683	4019	6683
55°	3652	6178	3626	6178
60°	3251	5694	3324	5694
65°	2855	5173	3092	5173
70°	2241	4711	2823	4711
75°	1975	4113	2578	4113
80°	1717	3496	2535	3496
85°	1383	2803	2692	2803



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	1.6
10°-20°	236.7	5.1
20°-30°	371.8	7.9
30°-40°	387.9	8.3
40°-50°	332.0	7.1
50°-60°	253.0	5.4
60°-70°	162.2	3.5
70°-80°	78.0	1.7
80°-90°	23.2	0.5
90°-100°	32.9	0.7
100°-110°	157.0	3.4
110°-120°	377.1	8.1
120°-130°	480.2	10.3
130°-140°	513.1	11.0
140°-150°	479.8	10.2
150°-160°	387.0	8.3
160°-170°	249.8	5.3
170°-180°	86.1	1.8
0°-30°	684.3	14.6
0°-40°	1072.2	22.9
0°-60°	1657.2	35.4
0°-90°	1920.6	41.0
90°-120°	567.0	12.1
90°-150°	2040.1	43.6
90°-180°	2763.0	59.0
0°-180°	4683.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	915	771	679	771	915	94
15°	1300	735	542	735	1300	369
25°	1340	668	441	668	1340	576
35°	581	582	360	582	581	381
45°	310	468	283	468	310	244
55°	195	329	193	329	195	176
65°	112	203	121	203	112	110
75°	48	99	62	99	48	51
85°	11	23	22	23	11	13
90°	20	1	20	1	20	10
95°	26	41	26	41	26	21
105°	30	201	30	201	30	68
115°	396	376	396	376	396	366
125°	541	530	541	530	541	483
135°	667	660	667	660	667	514
145°	769	762	769	762	769	480
155°	838	839	838	839	838	386
165°	883	885	883	885	883	249
175°	903	906	903	906	903	86
180°	906	906	906	906	906	



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	820.4	821.6	818.1	817.6	813.6	812.6	812.6	807.0	803.6	799.1	796.5
5°	914.8	920.1	917.5	911.5	901.6	899.3	893.0	883.1	871.9	858.1	851.5
7.5°	1032.6	1039.8	1037.0	1027.9	1017.5	1009.1	991.4	975.0	952.0	931.9	914.6
10°	1129.2	1121.5	1115.7	1106.7	1097.2	1081.7	1063.2	1037.8	1008.5	985.4	959.7
12.5°	1201.4	1200.2	1192.7	1183.5	1170.0	1155.3	1132.6	1101.6	1067.6	1034.1	1004.8
15°	1300.0	1302.0	1297.0	1287.5	1268.3	1242.3	1208.0	1195.2	1146.3	1110.0	1073.8
17.5°	1368.2	1367.8	1367.1	1353.8	1334.4	1315.8	1284.0	1250.2	1206.0	1154.9	1106.0
20°	1411.4	1408.2	1408.9	1394.0	1379.5	1358.1	1327.1	1277.9	1241.6	1182.6	1132.1
22.5°	1410.4	1409.7	1412.2	1407.1	1396.6	1380.2	1355.8	1314.3	1268.0	1208.4	1151.7
25°	1339.5	1337.0	1352.5	1356.7	1373.6	1376.5	1369.2	1346.5	1302.6	1241.3	1171.0
27.5°	1121.1	1119.6	1148.4	1184.4	1230.1	1265.6	1299.9	1316.4	1302.6	1258.7	1188.4
30°	920.1	951.1	965.6	1017.7	1075.7	1145.0	1205.7	1263.3	1277.6	1258.4	1200.8
32.5°	763.9	790.9	803.1	847.8	901.9	983.0	1074.0	1155.7	1213.5	1228.1	1193.3
35°	581.1	581.4	609.1	628.9	679.0	762.4	850.8	960.3	1069.1	1151.6	1160.2
37.5°	463.6	465.3	482.1	501.8	539.4	583.5	661.3	752.3	878.0	1004.6	1078.8
40°	400.4	403.3	415.9	435.3	462.4	495.7	556.4	642.0	746.9	887.8	1002.9
42.5°	359.7	364.5	371.0	386.0	402.7	433.9	483.0	549.2	644.5	777.7	910.5
45°	310.0	312.6	317.5	324.5	339.7	361.4	394.4	438.9	518.1	625.3	758.2
47.5°	273.5	272.1	277.2	282.9	293.0	307.8	329.9	366.3	422.8	508.7	621.5
50°	248.7	248.3	251.9	256.2	265.8	276.7	294.8	322.2	367.0	438.2	541.5
52.5°	225.4	226.7	229.3	234.6	241.5	250.3	266.6	286.3	324.9	386.3	472.3
55°	194.6	195.5	199.1	202.2	207.1	216.0	226.3	242.7	269.1	311.9	382.9
57.5°	168.4	168.0	171.5	172.2	177.8	185.0	193.0	205.8	224.9	256.8	304.5
60°	151.0	150.1	153.0	155.3	158.3	164.2	170.8	183.4	198.5	222.0	262.9
62.5°	135.2	134.7	136.9	139.2	141.6	147.1	152.7	162.2	174.3	194.0	226.4
65°	112.1	113.1	114.1	115.1	116.4	119.7	125.0	131.6	139.8	153.7	177.1
67.5°	88.1	89.1	89.5	91.4	94.3	96.3	99.6	105.5	111.2	122.9	136.2
70°	71.2	70.9	71.2	72.2	75.9	79.5	83.8	88.1	91.7	100.0	111.2
72.5°	61.2	60.6	61.5	61.6	63.5	64.4	67.2	71.2	75.9	81.5	89.5
75°	47.5	47.5	47.5	47.5	48.8	49.5	50.5	51.5	53.1	55.7	61.6
77.5°	35.1	35.1	35.6	35.9	36.2	36.6	37.2	38.2	38.7	40.2	42.7
80°	27.7	28.1	27.7	28.1	28.1	28.7	29.0	30.0	30.3	32.0	33.0
82.5°	20.8	20.7	20.8	21.2	21.2	21.9	21.9	22.6	22.7	23.5	24.5
85°	11.2	10.6	11.2	10.8	11.5	10.8	11.2	11.9	11.9	12.2	13.5
87.5°	6.7	7.1	6.5	6.8	6.7	6.9	6.7	6.6	7.1	6.6	6.5
90°	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4	16.8	16.2	14.2
92.5°	22.4	22.1	22.0	21.8	21.6	21.1	20.1	19.1	18.2	17.2	15.8
95°	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0	22.0	20.8	19.2
97.5°	27.7	27.6	27.5	27.3	27.1	26.4	25.2	24.1	22.9	21.7	32.5
100°	28.2	28.2	28.0	27.8	27.6	27.0	25.8	24.6	23.4	22.2	45.5
102.5°	28.8	28.5	28.2	28.0	27.7	29.4	33.1	36.9	40.6	44.3	69.7
105°	29.6	29.4	29.0	28.8	28.4	41.5	68.0	94.5	121.0	147.4	160.8
107.5°	93.0	113.0	132.9	152.9	172.8	192.5	212.0	231.4	250.8	270.2	268.0
110°	185.1	206.5	227.9	249.3	270.7	283.9	288.8	293.7	298.7	303.6	302.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.6	322.1	326.6	331.1	335.6	337.9	337.8	337.7	337.6	337.5	335.9
115°	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.3	387.9	386.4	385.0
117.5°	439.7	439.5	439.5	439.4	439.2	438.5	437.4	436.2	435.0	433.8	433.1
120°	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8	465.6	464.4	464.0
122.5°	499.5	499.4	499.2	499.1	498.9	498.5	497.7	496.8	496.0	495.2	494.6
125°	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1	538.8	538.5	537.9
127.5°	581.3	581.6	581.9	582.2	582.5	582.4	581.9	581.4	581.0	580.5	579.8
130°	607.2	607.4	607.8	608.0	608.4	608.2	607.6	607.0	606.4	605.8	605.2
132.5°	630.9	631.3	631.7	632.1	632.5	632.4	631.8	631.2	630.7	630.1	629.6
135°	667.1	667.5	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1	666.5
137.5°	701.1	701.5	701.7	702.1	702.3	702.1	701.4	700.7	700.0	699.2	698.9
140°	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4	720.8	720.2	719.8
142.5°	740.5	740.9	741.2	741.7	742.1	742.1	741.6	741.1	740.6	740.2	739.7
145°	769.4	769.4	769.4	769.4	769.4	769.2	769.0	768.6	768.4	768.0	767.8
147.5°	790.9	791.6	792.3	793.0	793.7	793.8	793.6	793.2	793.0	792.6	792.4
150°	807.1	807.5	808.0	808.4	808.9	808.9	808.7	808.3	808.0	807.8	807.4
152.5°	820.0	820.7	821.4	822.1	822.8	822.9	822.3	821.7	821.2	820.7	820.5
155°	838.0	839.0	839.8	840.8	841.6	841.7	840.9	840.2	839.5	838.7	838.5
157.5°	853.3	854.5	855.6	856.8	857.9	858.1	857.1	856.3	855.4	854.5	854.6
160°	863.0	864.0	865.0	866.1	867.1	867.2	866.3	865.4	864.5	863.6	863.8
162.5°	872.1	873.1	873.9	874.9	875.8	875.7	874.8	873.7	872.7	871.7	871.8
165°	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.8	883.6	882.4	882.6
167.5°	891.0	892.3	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0	891.0
170°	896.0	897.2	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0	896.0
172.5°	898.6	899.9	901.3	902.6	903.9	904.0	902.8	901.6	900.3	899.1	899.1
175°	902.7	903.9	905.1	906.3	907.4	907.5	906.5	905.4	904.4	903.4	903.2
177.5°	903.9	905.1	906.3	907.5	908.7	908.8	907.8	906.9	905.9	904.9	904.8
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	795.4	794.6	790.9	786.7	781.2	777.5	774.6	773.0	768.3	762.4	758.5
5°	844.6	834.7	824.1	811.2	799.4	787.2	779.6	770.7	759.8	747.6	739.0
7.5°	897.2	877.8	856.9	835.3	814.0	794.9	778.0	763.5	746.2	728.8	716.4
10°	937.5	909.2	879.9	849.8	822.4	796.8	777.0	757.5	736.8	716.6	701.5
12.5°	974.2	936.9	903.1	866.2	831.2	800.5	772.0	749.1	724.1	702.7	685.4
15°	1020.6	982.4	941.5	885.5	839.0	800.0	765.4	735.4	705.1	678.7	661.9
17.5°	1064.0	1006.5	951.6	904.7	844.4	795.7	753.5	717.6	684.3	656.3	635.6
20°	1082.0	1026.3	966.6	906.9	847.6	793.2	744.0	704.4	669.8	638.1	619.0
22.5°	1092.8	1029.7	966.8	902.7	839.6	783.1	734.5	691.0	653.4	623.4	599.8
25°	1105.4	1030.2	961.0	897.7	833.4	772.0	714.3	668.1	627.6	595.6	570.5
27.5°	1113.7	1025.3	943.4	873.1	807.8	746.7	693.9	644.9	603.7	569.9	543.0
30°	1115.3	1021.3	930.0	853.8	787.5	731.4	675.4	628.5	585.0	549.1	524.0
32.5°	1117.4	1011.6	911.8	830.9	763.0	707.5	656.7	611.9	567.3	531.9	506.4
35°	1108.7	1006.2	884.2	791.2	723.2	669.4	623.6	582.4	538.6	504.2	478.2
37.5°	1071.3	984.7	855.5	746.4	675.4	625.6	588.2	552.3	512.1	475.1	450.6
40°	1033.5	963.6	833.4	719.3	645.1	593.9	560.3	531.0	492.1	457.4	431.0
42.5°	977.3	934.9	812.3	690.8	610.7	561.5	533.1	505.6	471.5	436.3	411.5
45°	874.3	879.9	769.0	645.4	563.3	513.8	487.1	468.0	437.6	408.6	383.2
47.5°	744.9	797.4	718.3	597.0	513.2	466.7	443.4	426.7	406.3	377.8	354.6
50°	660.6	735.4	677.7	564.6	481.8	435.7	412.6	399.1	381.3	358.8	336.7
52.5°	582.7	663.1	628.6	528.4	447.8	405.5	383.0	371.9	357.7	336.7	316.7
55°	475.2	556.6	548.7	473.9	396.7	358.8	341.6	329.2	319.5	303.8	287.9
57.5°	384.4	461.6	465.7	413.2	351.7	314.3	299.5	290.1	283.8	271.9	257.3
60°	327.2	398.0	411.9	372.3	319.5	286.5	272.1	264.5	259.5	249.9	238.8
62.5°	279.7	340.0	355.7	327.2	288.7	257.8	246.5	239.2	235.8	227.6	217.7
65°	214.0	264.2	279.3	263.5	243.4	218.6	209.4	203.1	200.2	195.5	188.3
67.5°	160.9	197.5	214.1	202.9	195.7	180.0	174.2	170.8	168.2	165.1	158.9
70°	129.2	156.4	173.5	170.5	164.5	156.4	152.1	149.7	147.1	144.5	139.1
72.5°	103.9	122.5	138.6	140.2	135.3	133.6	129.8	128.9	127.3	124.2	121.2
75°	69.0	81.8	93.0	97.3	99.3	100.9	99.3	98.9	98.6	96.0	94.3
77.5°	45.2	52.1	59.2	66.5	69.6	71.8	72.3	73.5	72.7	71.3	70.5
80°	34.6	36.2	41.2	47.5	52.4	54.4	55.7	56.4	56.1	55.7	54.4
82.5°	25.1	26.5	28.8	33.2	37.4	40.7	41.5	41.3	42.1	42.3	41.2
85°	13.5	13.9	14.6	15.2	17.5	21.1	22.1	22.7	23.4	23.4	21.4
87.5°	6.7	6.0	6.2	5.9	6.3	6.3	7.6	8.6	9.1	8.4	8.7
90°	12.2	10.3	8.4	6.6	5.2	3.7	2.2	0.7	2.2	3.7	5.2
92.5°	14.3	12.8	11.4	10.8	11.3	11.7	12.1	12.5	12.1	11.7	11.3
95°	17.6	15.9	14.3	16.5	22.6	28.8	35.0	41.1	35.0	28.8	22.6
97.5°	43.2	54.0	64.7	71.5	74.3	77.1	79.8	82.5	79.8	77.1	74.3
100°	68.9	92.2	115.5	125.7	122.7	119.8	116.8	113.7	116.8	119.8	122.7
102.5°	95.2	120.8	146.3	157.9	155.8	153.6	151.4	149.3	151.4	153.6	155.8
105°	174.4	187.8	201.3	207.2	205.5	203.9	202.2	200.6	202.2	203.9	205.5
107.5°	266.0	263.8	261.7	259.9	258.6	257.4	256.1	254.7	256.1	257.4	258.6
110°	300.3	298.7	297.0	295.6	294.4	293.2	292.0	290.8	292.0	293.2	294.4



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.2	332.6	330.9	329.6	328.5	327.4	326.3	325.3	326.3	327.4	328.5
115°	383.7	382.4	381.0	379.9	379.0	378.1	377.2	376.3	377.2	378.1	379.0
117.5°	432.4	431.7	431.0	430.1	429.0	427.9	426.8	425.7	426.8	427.9	429.0
120°	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4	457.7	459.1	460.4
122.5°	494.0	493.4	492.8	492.1	490.9	489.8	488.7	487.6	488.7	489.8	490.9
125°	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.5	531.6	532.8	534.0
127.5°	579.1	578.3	577.6	576.7	575.5	574.3	573.1	571.9	573.1	574.3	575.5
130°	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7	598.9	600.1	601.3
132.5°	629.0	628.6	628.1	627.3	626.1	624.9	623.7	622.5	623.7	624.9	626.1
135°	665.9	665.3	664.7	663.9	663.1	662.1	661.2	660.3	661.2	662.1	663.1
137.5°	698.6	698.3	697.9	697.2	696.0	694.9	693.8	692.7	693.8	694.9	696.0
140°	719.4	718.9	718.4	717.8	716.9	716.0	715.1	714.2	715.1	716.0	716.9
142.5°	739.3	738.8	738.4	737.7	736.8	735.9	735.0	734.1	735.0	735.9	736.8
145°	767.4	767.2	766.8	766.2	765.1	764.1	763.0	762.0	763.0	764.1	765.1
147.5°	792.0	791.8	791.5	791.0	790.3	789.6	788.9	788.2	788.9	789.6	790.3
150°	807.2	806.8	806.6	806.2	805.7	805.3	804.9	804.3	804.9	805.3	805.7
152.5°	820.3	820.1	819.9	819.8	819.6	819.3	819.2	818.9	819.2	819.3	819.6
155°	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4	839.1	838.8	838.5
157.5°	854.8	854.9	855.1	855.1	855.1	855.2	855.2	855.2	855.2	855.2	855.1
160°	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0	864.8	864.7	864.5
162.5°	872.0	872.1	872.3	872.5	873.0	873.3	873.7	874.1	873.7	873.3	873.0
165°	882.8	883.0	883.0	883.4	883.8	884.2	884.7	885.2	884.7	884.2	883.8
167.5°	891.0	891.0	891.0	891.4	892.0	892.6	893.2	893.8	893.2	892.6	892.0
170°	896.0	896.0	896.0	896.2	896.8	897.4	898.0	898.6	898.0	897.4	896.8
172.5°	898.9	898.8	898.7	899.0	899.7	900.4	901.1	901.8	901.1	900.4	899.7
175°	903.0	902.8	902.8	903.0	903.8	904.6	905.3	906.0	905.3	904.6	903.8
177.5°	904.7	904.6	904.5	904.7	905.3	905.9	906.5	907.1	906.5	905.9	905.3
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	757.2	753.7	751.4	746.1	742.7	739.0	735.3	737.6	737.4	737.1	737.1
5°	731.8	724.2	717.3	708.3	702.7	695.9	690.5	689.9	691.2	686.6	684.0
7.5°	706.6	696.2	686.4	676.6	666.2	657.8	652.6	650.2	646.9	644.0	641.0
10°	688.9	676.7	667.1	655.0	643.8	633.9	627.6	623.3	621.0	618.6	614.4
12.5°	670.7	658.8	646.5	632.7	622.1	610.6	606.0	601.2	596.7	594.1	588.2
15°	644.0	628.5	615.7	601.2	589.4	578.1	571.5	562.0	560.6	557.3	551.4
17.5°	617.3	600.5	582.8	572.0	558.6	547.0	536.9	533.7	524.3	520.7	515.6
20°	596.2	580.7	567.2	553.0	533.6	522.7	514.8	510.5	502.9	498.3	495.0
22.5°	578.1	562.2	546.6	530.1	514.0	501.9	496.0	489.4	485.3	478.8	475.2
25°	552.1	534.9	516.1	498.3	486.7	477.5	468.3	462.4	456.4	453.4	446.9
27.5°	521.9	503.9	486.4	472.9	458.7	449.5	441.2	435.9	428.8	423.8	420.2
30°	505.2	484.1	469.0	456.8	438.6	430.1	423.8	417.2	411.9	406.7	402.9
32.5°	485.9	466.7	452.3	437.2	423.3	414.0	405.8	400.0	395.5	390.5	386.9
35°	455.7	439.6	424.7	409.6	399.3	389.8	380.2	375.3	371.0	366.4	363.1
37.5°	428.4	413.4	399.2	384.9	372.2	364.4	356.7	352.9	347.2	344.1	340.7
40°	411.6	396.7	381.6	367.7	354.5	348.6	341.6	336.0	330.8	328.5	324.9
42.5°	393.1	378.2	365.5	350.5	339.8	331.7	325.3	319.2	315.2	311.9	309.8
45°	365.8	352.5	340.0	325.2	315.0	308.0	300.7	295.2	291.5	289.2	285.6
47.5°	339.1	326.0	313.2	300.3	290.4	282.5	275.3	271.3	266.6	263.7	261.2
50°	319.9	308.0	294.5	282.6	272.8	264.8	258.9	253.9	249.6	246.0	244.4
52.5°	302.2	289.6	277.8	266.8	256.4	247.4	242.0	236.8	233.6	229.4	227.5
55°	273.0	260.9	251.0	240.0	229.9	222.3	215.7	211.0	207.8	203.1	200.5
57.5°	245.6	234.7	222.9	213.5	202.9	196.6	191.1	184.8	180.8	177.2	174.6
60°	227.2	214.6	204.5	195.5	186.3	178.1	173.1	168.2	163.9	160.2	158.0
62.5°	207.9	197.0	187.4	177.6	169.2	162.0	156.3	152.1	148.4	146.0	143.7
65°	178.4	169.9	160.0	152.1	144.1	138.9	134.2	130.6	127.9	126.3	124.3
67.5°	151.3	142.9	134.3	126.5	121.2	117.2	114.2	111.1	109.8	107.6	106.3
70°	133.5	125.0	117.4	111.5	106.2	103.2	101.3	98.9	97.6	95.0	93.7
72.5°	114.3	108.1	102.6	97.7	93.5	90.8	88.3	85.5	83.3	80.5	79.1
75°	90.1	84.5	80.2	76.8	74.2	70.6	67.0	64.0	63.0	62.0	61.6
77.5°	66.6	63.1	60.0	57.3	54.0	51.3	50.5	49.9	49.7	49.2	49.2
80°	52.4	49.2	46.8	43.6	41.6	41.6	41.6	40.9	41.2	41.2	41.2
82.5°	39.0	35.9	34.7	33.5	33.1	33.4	33.4	33.5	33.3	33.8	33.6
85°	20.1	20.4	21.1	20.8	21.1	21.1	21.8	21.4	21.8	21.1	21.8
87.5°	8.7	9.8	10.5	11.2	11.8	12.0	12.3	12.4	12.8	12.9	13.0
90°	6.6	8.4	10.3	12.2	14.2	16.2	16.8	17.4	17.9	18.5	19.0
92.5°	10.8	11.4	12.8	14.3	15.8	17.2	18.2	19.1	20.1	21.1	21.6
95°	16.5	14.3	15.9	17.6	19.2	20.8	22.0	23.0	24.0	25.1	25.6
97.5°	71.5	64.7	54.0	43.2	32.5	21.7	22.9	24.1	25.2	26.4	27.1
100°	125.7	115.5	92.2	68.9	45.5	22.2	23.4	24.6	25.8	27.0	27.6
102.5°	157.9	146.3	120.8	95.2	69.7	44.3	40.6	36.9	33.1	29.4	27.7
105°	207.2	201.3	187.8	174.4	160.8	147.4	121.0	94.5	68.0	41.5	28.4
107.5°	259.9	261.7	263.8	266.0	268.0	270.2	250.8	231.4	212.0	192.5	172.8
110°	295.6	297.0	298.7	300.3	302.0	303.6	298.7	293.7	288.8	283.9	270.7



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	329.6	330.9	332.6	334.2	335.9	337.5	337.6	337.7	337.8	337.9	335.6
115°	379.9	381.0	382.4	383.7	385.0	386.4	387.9	389.3	390.9	392.4	393.4
117.5°	430.1	431.0	431.7	432.4	433.1	433.8	435.0	436.2	437.4	438.5	439.2
120°	461.8	462.7	463.1	463.6	464.0	464.4	465.6	466.8	468.0	469.2	469.8
122.5°	492.1	492.8	493.4	494.0	494.6	495.2	496.0	496.8	497.7	498.5	498.9
125°	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1	539.4	539.7	540.0
127.5°	576.7	577.6	578.3	579.1	579.8	580.5	581.0	581.4	581.9	582.4	582.5
130°	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0	607.6	608.2	608.4
132.5°	627.3	628.1	628.6	629.0	629.6	630.1	630.7	631.2	631.8	632.4	632.5
135°	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0	668.4	668.8	668.8
137.5°	697.2	697.9	698.3	698.6	698.9	699.2	700.0	700.7	701.4	702.1	702.3
140°	717.8	718.4	718.9	719.4	719.8	720.2	720.8	721.4	722.0	722.6	722.8
142.5°	737.7	738.4	738.8	739.3	739.7	740.2	740.6	741.1	741.6	742.1	742.1
145°	766.2	766.8	767.2	767.4	767.8	768.0	768.4	768.6	769.0	769.2	769.4
147.5°	791.0	791.5	791.8	792.0	792.4	792.6	793.0	793.2	793.6	793.8	793.7
150°	806.2	806.6	806.8	807.2	807.4	807.8	808.0	808.3	808.7	808.9	808.9
152.5°	819.8	819.9	820.1	820.3	820.5	820.7	821.2	821.7	822.3	822.9	822.8
155°	838.2	838.1	838.3	838.4	838.5	838.7	839.5	840.2	840.9	841.7	841.6
157.5°	855.1	855.1	854.9	854.8	854.6	854.5	855.4	856.3	857.1	858.1	857.9
160°	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4	866.3	867.2	867.1
162.5°	872.5	872.3	872.1	872.0	871.8	871.7	872.7	873.7	874.8	875.7	875.8
165°	883.4	883.0	883.0	882.8	882.6	882.4	883.6	884.8	886.1	887.3	887.3
167.5°	891.4	891.0	891.0	891.0	891.0	891.0	892.3	893.5	894.7	895.9	895.9
170°	896.2	896.0	896.0	896.0	896.0	896.0	897.2	898.3	899.5	900.7	900.7
172.5°	899.0	898.7	898.8	898.9	899.1	899.1	900.3	901.6	902.8	904.0	903.9
175°	903.0	902.8	902.8	903.0	903.2	903.4	904.4	905.4	906.5	907.5	907.4
177.5°	904.7	904.5	904.6	904.7	904.8	904.9	905.9	906.9	907.8	908.8	908.7
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	733.9	733.7	733.9	732.9	733.9	733.7	733.9	737.1	737.1	737.4	737.6
5°	682.9	682.6	681.7	678.7	681.7	682.6	682.9	684.0	686.6	691.2	689.9
7.5°	638.4	638.0	635.1	635.2	635.1	638.0	638.4	641.0	644.0	646.9	650.2
10°	612.1	612.4	608.5	606.1	608.5	612.4	612.1	614.4	618.6	621.0	623.3
12.5°	586.5	585.0	581.8	579.2	581.8	585.0	586.5	588.2	594.1	596.7	601.2
15°	552.7	549.4	541.5	542.2	541.5	549.4	552.7	551.4	557.3	560.6	562.0
17.5°	512.9	510.5	510.4	505.8	510.4	510.5	512.9	515.6	520.7	524.3	533.7
20°	489.7	488.1	488.7	484.1	488.7	488.1	489.7	495.0	498.3	502.9	510.5
22.5°	471.5	469.8	467.1	465.6	467.1	469.8	471.5	475.2	478.8	485.3	489.4
25°	444.9	442.2	439.6	441.3	439.6	442.2	444.9	446.9	453.4	456.4	462.4
27.5°	418.2	416.2	413.6	413.3	413.6	416.2	418.2	420.2	423.8	428.8	435.9
30°	401.3	399.3	398.0	396.4	398.0	399.3	401.3	402.9	406.7	411.9	417.2
32.5°	384.2	383.8	381.4	381.1	381.4	383.8	384.2	386.9	390.5	395.5	400.0
35°	361.8	359.8	359.1	359.5	359.1	359.8	361.8	363.1	366.4	371.0	375.3
37.5°	340.4	337.9	336.7	335.4	336.7	337.9	340.4	340.7	344.1	347.2	352.9
40°	325.2	322.5	321.8	321.2	321.8	322.5	325.2	324.9	328.5	330.8	336.0
42.5°	308.0	306.9	306.6	305.4	306.6	306.9	308.0	309.8	311.9	315.2	319.2
45°	284.6	284.3	282.3	282.9	282.3	284.3	284.6	285.6	289.2	291.5	295.2
47.5°	259.9	258.5	257.1	258.0	257.1	258.5	259.9	261.2	263.7	266.6	271.3
50°	243.1	242.4	239.4	240.0	239.4	242.4	243.1	244.4	246.0	249.6	253.9
52.5°	226.2	223.7	222.6	222.1	222.6	223.7	226.2	227.5	229.4	233.6	236.8
55°	198.2	195.2	193.9	193.2	193.9	195.2	198.2	200.5	203.1	207.8	211.0
57.5°	170.7	170.0	168.9	169.6	168.9	170.0	170.7	174.6	177.2	180.8	184.8
60°	154.6	154.6	154.6	154.4	154.6	154.6	154.6	158.0	160.2	163.9	168.2
62.5°	142.2	141.5	141.2	141.6	141.2	141.5	142.2	143.7	146.0	148.4	152.1
65°	123.3	123.0	121.7	121.4	121.7	123.0	123.3	124.3	126.3	127.9	130.6
67.5°	105.5	104.3	103.9	103.4	103.9	104.3	105.5	106.3	107.6	109.8	111.1
70°	92.0	91.4	89.4	89.7	89.4	91.4	92.0	93.7	95.0	97.6	98.9
72.5°	77.5	76.8	76.5	75.9	76.5	76.8	77.5	79.1	80.5	83.3	85.5
75°	61.3	61.0	60.7	62.0	60.7	61.0	61.3	61.6	62.0	63.0	64.0
77.5°	49.2	49.2	49.3	48.8	49.3	49.2	49.2	49.2	49.2	49.7	49.9
80°	41.2	41.2	40.9	40.9	40.9	41.2	41.2	41.2	41.2	41.2	40.9
82.5°	33.1	33.3	33.5	33.0	33.5	33.3	33.1	33.6	33.8	33.3	33.5
85°	21.8	21.4	22.1	21.8	22.1	21.4	21.8	21.8	21.1	21.8	21.4
87.5°	13.6	13.2	13.2	13.5	13.2	13.2	13.6	13.0	12.9	12.8	12.4
90°	19.3	19.6	19.9	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4
92.5°	21.8	22.0	22.1	22.4	22.1	22.0	21.8	21.6	21.1	20.1	19.1
95°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0
97.5°	27.3	27.5	27.6	27.7	27.6	27.5	27.3	27.1	26.4	25.2	24.1
100°	27.8	28.0	28.2	28.2	28.2	28.0	27.8	27.6	27.0	25.8	24.6
102.5°	28.0	28.2	28.5	28.8	28.5	28.2	28.0	27.7	29.4	33.1	36.9
105°	28.8	29.0	29.4	29.6	29.4	29.0	28.8	28.4	41.5	68.0	94.5
107.5°	152.9	132.9	113.0	93.0	113.0	132.9	152.9	172.8	192.5	212.0	231.4
110°	249.3	227.9	206.5	185.1	206.5	227.9	249.3	270.7	283.9	288.8	293.7



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	331.1	326.6	322.1	317.6	322.1	326.6	331.1	335.6	337.9	337.8	337.7
115°	394.0	394.6	395.2	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.3
117.5°	439.4	439.5	439.5	439.7	439.5	439.5	439.4	439.2	438.5	437.4	436.2
120°	469.8	469.8	469.8	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8
122.5°	499.1	499.2	499.4	499.5	499.4	499.2	499.1	498.9	498.5	497.7	496.8
125°	540.3	540.6	540.9	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1
127.5°	582.2	581.9	581.6	581.3	581.6	581.9	582.2	582.5	582.4	581.9	581.4
130°	608.0	607.8	607.4	607.2	607.4	607.8	608.0	608.4	608.2	607.6	607.0
132.5°	632.1	631.7	631.3	630.9	631.3	631.7	632.1	632.5	632.4	631.8	631.2
135°	668.4	668.0	667.5	667.1	667.5	668.0	668.4	668.8	668.8	668.4	668.0
137.5°	702.1	701.7	701.5	701.1	701.5	701.7	702.1	702.3	702.1	701.4	700.7
140°	722.5	722.2	721.9	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4
142.5°	741.7	741.2	740.9	740.5	740.9	741.2	741.7	742.1	742.1	741.6	741.1
145°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.2	769.0	768.6
147.5°	793.0	792.3	791.6	790.9	791.6	792.3	793.0	793.7	793.8	793.6	793.2
150°	808.4	808.0	807.5	807.1	807.5	808.0	808.4	808.9	808.9	808.7	808.3
152.5°	822.1	821.4	820.7	820.0	820.7	821.4	822.1	822.8	822.9	822.3	821.7
155°	840.8	839.8	839.0	838.0	839.0	839.8	840.8	841.6	841.7	840.9	840.2
157.5°	856.8	855.6	854.5	853.3	854.5	855.6	856.8	857.9	858.1	857.1	856.3
160°	866.1	865.0	864.0	863.0	864.0	865.0	866.1	867.1	867.2	866.3	865.4
162.5°	874.9	873.9	873.1	872.1	873.1	873.9	874.9	875.8	875.7	874.8	873.7
165°	886.3	885.2	884.2	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.8
167.5°	894.7	893.5	892.3	891.0	892.3	893.5	894.7	895.9	895.9	894.7	893.5
170°	899.5	898.3	897.2	896.0	897.2	898.3	899.5	900.7	900.7	899.5	898.3
172.5°	902.6	901.3	899.9	898.6	899.9	901.3	902.6	903.9	904.0	902.8	901.6
175°	906.3	905.1	903.9	902.7	903.9	905.1	906.3	907.4	907.5	906.5	905.4
177.5°	907.5	906.3	905.1	903.9	905.1	906.3	907.5	908.7	908.8	907.8	906.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	735.3	739.0	742.7	746.1	751.4	753.7	757.2	758.5	762.4	768.3	773.0
5°	690.5	695.9	702.7	708.3	717.3	724.2	731.8	739.0	747.6	759.8	770.7
7.5°	652.6	657.8	666.2	676.6	686.4	696.2	706.6	716.4	728.8	746.2	763.5
10°	627.6	633.9	643.8	655.0	667.1	676.7	688.9	701.5	716.6	736.8	757.5
12.5°	606.0	610.6	622.1	632.7	646.5	658.8	670.7	685.4	702.7	724.1	749.1
15°	571.5	578.1	589.4	601.2	615.7	628.5	644.0	661.9	678.7	705.1	735.4
17.5°	536.9	547.0	558.6	572.0	582.8	600.5	617.3	635.6	656.3	684.3	717.6
20°	514.8	522.7	533.6	553.0	567.2	580.7	596.2	619.0	638.1	669.8	704.4
22.5°	496.0	501.9	514.0	530.1	546.6	562.2	578.1	599.8	623.4	653.4	691.0
25°	468.3	477.5	486.7	498.3	516.1	534.9	552.1	570.5	595.6	627.6	668.1
27.5°	441.2	449.5	458.7	472.9	486.4	503.9	521.9	543.0	569.9	603.7	644.9
30°	423.8	430.1	438.6	456.8	469.0	484.1	505.2	524.0	549.1	585.0	628.5
32.5°	405.8	414.0	423.3	437.2	452.3	466.7	485.9	506.4	531.9	567.3	611.9
35°	380.2	389.8	399.3	409.6	424.7	439.6	455.7	478.2	504.2	538.6	582.4
37.5°	356.7	364.4	372.2	384.9	399.2	413.4	428.4	450.6	475.1	512.1	552.3
40°	341.6	348.6	354.5	367.7	381.6	396.7	411.6	431.0	457.4	492.1	531.0
42.5°	325.3	331.7	339.8	350.5	365.5	378.2	393.1	411.5	436.3	471.5	505.6
45°	300.7	308.0	315.0	325.2	340.0	352.5	365.8	383.2	408.6	437.6	468.0
47.5°	275.3	282.5	290.4	300.3	313.2	326.0	339.1	354.6	377.8	406.3	426.7
50°	258.9	264.8	272.8	282.6	294.5	308.0	319.9	336.7	358.8	381.3	399.1
52.5°	242.0	247.4	256.4	266.8	277.8	289.6	302.2	316.7	336.7	357.7	371.9
55°	215.7	222.3	229.9	240.0	251.0	260.9	273.0	287.9	303.8	319.5	329.2
57.5°	191.1	196.6	202.9	213.5	222.9	234.7	245.6	257.3	271.9	283.8	290.1
60°	173.1	178.1	186.3	195.5	204.5	214.6	227.2	238.8	249.9	259.5	264.5
62.5°	156.3	162.0	169.2	177.6	187.4	197.0	207.9	217.7	227.6	235.8	239.2
65°	134.2	138.9	144.1	152.1	160.0	169.9	178.4	188.3	195.5	200.2	203.1
67.5°	114.2	117.2	121.2	126.5	134.3	142.9	151.3	158.9	165.1	168.2	170.8
70°	101.3	103.2	106.2	111.5	117.4	125.0	133.5	139.1	144.5	147.1	149.7
72.5°	88.3	90.8	93.5	97.7	102.6	108.1	114.3	121.2	124.2	127.3	128.9
75°	67.0	70.6	74.2	76.8	80.2	84.5	90.1	94.3	96.0	98.6	98.9
77.5°	50.5	51.3	54.0	57.3	60.0	63.1	66.6	70.5	71.3	72.7	73.5
80°	41.6	41.6	41.6	43.6	46.8	49.2	52.4	54.4	55.7	56.1	56.4
82.5°	33.4	33.4	33.1	33.5	34.7	35.9	39.0	41.2	42.3	42.1	41.3
85°	21.8	21.1	21.1	20.8	21.1	20.4	20.1	21.4	23.4	23.4	22.7
87.5°	12.3	12.0	11.8	11.2	10.5	9.8	8.7	8.7	8.4	9.1	8.6
90°	16.8	16.2	14.2	12.2	10.3	8.4	6.6	5.2	3.7	2.2	0.7
92.5°	18.2	17.2	15.8	14.3	12.8	11.4	10.8	11.3	11.7	12.1	12.5
95°	22.0	20.8	19.2	17.6	15.9	14.3	16.5	22.6	28.8	35.0	41.1
97.5°	22.9	21.7	32.5	43.2	54.0	64.7	71.5	74.3	77.1	79.8	82.5
100°	23.4	22.2	45.5	68.9	92.2	115.5	125.7	122.7	119.8	116.8	113.7
102.5°	40.6	44.3	69.7	95.2	120.8	146.3	157.9	155.8	153.6	151.4	149.3
105°	121.0	147.4	160.8	174.4	187.8	201.3	207.2	205.5	203.9	202.2	200.6
107.5°	250.8	270.2	268.0	266.0	263.8	261.7	259.9	258.6	257.4	256.1	254.7
110°	298.7	303.6	302.0	300.3	298.7	297.0	295.6	294.4	293.2	292.0	290.8



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	337.6	337.5	335.9	334.2	332.6	330.9	329.6	328.5	327.4	326.3	325.3
115°	387.9	386.4	385.0	383.7	382.4	381.0	379.9	379.0	378.1	377.2	376.3
117.5°	435.0	433.8	433.1	432.4	431.7	431.0	430.1	429.0	427.9	426.8	425.7
120°	465.6	464.4	464.0	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4
122.5°	496.0	495.2	494.6	494.0	493.4	492.8	492.1	490.9	489.8	488.7	487.6
125°	538.8	538.5	537.9	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.5
127.5°	581.0	580.5	579.8	579.1	578.3	577.6	576.7	575.5	574.3	573.1	571.9
130°	606.4	605.8	605.2	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7
132.5°	630.7	630.1	629.6	629.0	628.6	628.1	627.3	626.1	624.9	623.7	622.5
135°	667.5	667.1	666.5	665.9	665.3	664.7	663.9	663.1	662.1	661.2	660.3
137.5°	700.0	699.2	698.9	698.6	698.3	697.9	697.2	696.0	694.9	693.8	692.7
140°	720.8	720.2	719.8	719.4	718.9	718.4	717.8	716.9	716.0	715.1	714.2
142.5°	740.6	740.2	739.7	739.3	738.8	738.4	737.7	736.8	735.9	735.0	734.1
145°	768.4	768.0	767.8	767.4	767.2	766.8	766.2	765.1	764.1	763.0	762.0
147.5°	793.0	792.6	792.4	792.0	791.8	791.5	791.0	790.3	789.6	788.9	788.2
150°	808.0	807.8	807.4	807.2	806.8	806.6	806.2	805.7	805.3	804.9	804.3
152.5°	821.2	820.7	820.5	820.3	820.1	819.9	819.8	819.6	819.3	819.2	818.9
155°	839.5	838.7	838.5	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4
157.5°	855.4	854.5	854.6	854.8	854.9	855.1	855.1	855.1	855.2	855.2	855.2
160°	864.5	863.6	863.8	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0
162.5°	872.7	871.7	871.8	872.0	872.1	872.3	872.5	873.0	873.3	873.7	874.1
165°	883.6	882.4	882.6	882.8	883.0	883.0	883.4	883.8	884.2	884.7	885.2
167.5°	892.3	891.0	891.0	891.0	891.0	891.0	891.4	892.0	892.6	893.2	893.8
170°	897.2	896.0	896.0	896.0	896.0	896.0	896.2	896.8	897.4	898.0	898.6
172.5°	900.3	899.1	899.1	898.9	898.8	898.7	899.0	899.7	900.4	901.1	901.8
175°	904.4	903.4	903.2	903.0	902.8	902.8	903.0	903.8	904.6	905.3	906.0
177.5°	905.9	904.9	904.8	904.7	904.6	904.5	904.7	905.3	905.9	906.5	907.1
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	774.6	777.5	781.2	786.7	790.9	794.6	795.4	796.5	799.1	803.6	807.0
5°	779.6	787.2	799.4	811.2	824.1	834.7	844.6	851.5	858.1	871.9	883.1
7.5°	778.0	794.9	814.0	835.3	856.9	877.8	897.2	914.6	931.9	952.0	975.0
10°	777.0	796.8	822.4	849.8	879.9	909.2	937.5	959.7	985.4	1008.5	1037.8
12.5°	772.0	800.5	831.2	866.2	903.1	936.9	974.2	1004.8	1034.1	1067.6	1101.6
15°	765.4	800.0	839.0	885.5	941.5	982.4	1020.6	1073.8	1110.0	1146.3	1195.2
17.5°	753.5	795.7	844.4	904.7	951.6	1006.5	1064.0	1106.0	1154.9	1206.0	1250.2
20°	744.0	793.2	847.6	906.9	966.6	1026.3	1082.0	1132.1	1182.6	1241.6	1277.9
22.5°	734.5	783.1	839.6	902.7	966.8	1029.7	1092.8	1151.7	1208.4	1268.0	1314.3
25°	714.3	772.0	833.4	897.7	961.0	1030.2	1105.4	1171.0	1241.3	1302.6	1346.5
27.5°	693.9	746.7	807.8	873.1	943.4	1025.3	1113.7	1188.4	1258.7	1302.6	1316.4
30°	675.4	731.4	787.5	853.8	930.0	1021.3	1115.3	1200.8	1258.4	1277.6	1263.3
32.5°	656.7	707.5	763.0	830.9	911.8	1011.6	1117.4	1193.3	1228.1	1213.5	1155.7
35°	623.6	669.4	723.2	791.2	884.2	1006.2	1108.7	1160.2	1151.6	1069.1	960.3
37.5°	588.2	625.6	675.4	746.4	855.5	984.7	1071.3	1078.8	1004.6	878.0	752.3
40°	560.3	593.9	645.1	719.3	833.4	963.6	1033.5	1002.9	887.8	746.9	642.0
42.5°	533.1	561.5	610.7	690.8	812.3	934.9	977.3	910.5	777.7	644.5	549.2
45°	487.1	513.8	563.3	645.4	769.0	879.9	874.3	758.2	625.3	518.1	438.9
47.5°	443.4	466.7	513.2	597.0	718.3	797.4	744.9	621.5	508.7	422.8	366.3
50°	412.6	435.7	481.8	564.6	677.7	735.4	660.6	541.5	438.2	367.0	322.2
52.5°	383.0	405.5	447.8	528.4	628.6	663.1	582.7	472.3	386.3	324.9	286.3
55°	341.6	358.8	396.7	473.9	548.7	556.6	475.2	382.9	311.9	269.1	242.7
57.5°	299.5	314.3	351.7	413.2	465.7	461.6	384.4	304.5	256.8	224.9	205.8
60°	272.1	286.5	319.5	372.3	411.9	398.0	327.2	262.9	222.0	198.5	183.4
62.5°	246.5	257.8	288.7	327.2	355.7	340.0	279.7	226.4	194.0	174.3	162.2
65°	209.4	218.6	243.4	263.5	279.3	264.2	214.0	177.1	153.7	139.8	131.6
67.5°	174.2	180.0	195.7	202.9	214.1	197.5	160.9	136.2	122.9	111.2	105.5
70°	152.1	156.4	164.5	170.5	173.5	156.4	129.2	111.2	100.0	91.7	88.1
72.5°	129.8	133.6	135.3	140.2	138.6	122.5	103.9	89.5	81.5	75.9	71.2
75°	99.3	100.9	99.3	97.3	93.0	81.8	69.0	61.6	55.7	53.1	51.5
77.5°	72.3	71.8	69.6	66.5	59.2	52.1	45.2	42.7	40.2	38.7	38.2
80°	55.7	54.4	52.4	47.5	41.2	36.2	34.6	33.0	32.0	30.3	30.0
82.5°	41.5	40.7	37.4	33.2	28.8	26.5	25.1	24.5	23.5	22.7	22.6
85°	22.1	21.1	17.5	15.2	14.6	13.9	13.5	13.5	12.2	11.9	11.9
87.5°	7.6	6.3	6.3	5.9	6.2	6.0	6.7	6.5	6.6	7.1	6.6
90°	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8	17.4
92.5°	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2	19.1
95°	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0	23.0
97.5°	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9	24.1
100°	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4	24.6
102.5°	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6	36.9
105°	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0	94.5
107.5°	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8	231.4
110°	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7	293.7



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6	337.7
115°	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9	389.3
117.5°	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0	436.2
120°	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6	466.8
122.5°	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0	496.8
125°	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1
127.5°	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0	581.4
130°	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0
132.5°	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7	631.2
135°	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0
137.5°	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0	700.7
140°	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8	721.4
142.5°	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6	741.1
145°	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4	768.6
147.5°	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0	793.2
150°	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0	808.3
152.5°	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2	821.7
155°	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5	840.2
157.5°	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4	856.3
160°	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4
162.5°	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7	873.7
165°	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6	884.8
167.5°	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3	893.5
170°	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2	898.3
172.5°	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3	901.6
175°	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4	905.4
177.5°	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9	906.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	812.6	812.6	813.6	817.6	818.1	821.6	820.4
5°	893.0	899.3	901.6	911.5	917.5	920.1	914.8
7.5°	991.4	1009.1	1017.5	1027.9	1037.0	1039.8	1032.6
10°	1063.2	1081.7	1097.2	1106.7	1115.7	1121.5	1129.2
12.5°	1132.6	1155.3	1170.0	1183.5	1192.7	1200.2	1201.4
15°	1208.0	1242.3	1268.3	1287.5	1297.0	1302.0	1300.0
17.5°	1284.0	1315.8	1334.4	1353.8	1367.1	1367.8	1368.2
20°	1327.1	1358.1	1379.5	1394.0	1408.9	1408.2	1411.4
22.5°	1355.8	1380.2	1396.6	1407.1	1412.2	1409.7	1410.4
25°	1369.2	1376.5	1373.6	1356.7	1352.5	1337.0	1339.5
27.5°	1299.9	1265.6	1230.1	1184.4	1148.4	1119.6	1121.1
30°	1205.7	1145.0	1075.7	1017.7	965.6	951.1	920.1
32.5°	1074.0	983.0	901.9	847.8	803.1	790.9	763.9
35°	850.8	762.4	679.0	628.9	609.1	581.4	581.1
37.5°	661.3	583.5	539.4	501.8	482.1	465.3	463.6
40°	556.4	495.7	462.4	435.3	415.9	403.3	400.4
42.5°	483.0	433.9	402.7	386.0	371.0	364.5	359.7
45°	394.4	361.4	339.7	324.5	317.5	312.6	310.0
47.5°	329.9	307.8	293.0	282.9	277.2	272.1	273.5
50°	294.8	276.7	265.8	256.2	251.9	248.3	248.7
52.5°	266.6	250.3	241.5	234.6	229.3	226.7	225.4
55°	226.3	216.0	207.1	202.2	199.1	195.5	194.6
57.5°	193.0	185.0	177.8	172.2	171.5	168.0	168.4
60°	170.8	164.2	158.3	155.3	153.0	150.1	151.0
62.5°	152.7	147.1	141.6	139.2	136.9	134.7	135.2
65°	125.0	119.7	116.4	115.1	114.1	113.1	112.1
67.5°	99.6	96.3	94.3	91.4	89.5	89.1	88.1
70°	83.8	79.5	75.9	72.2	71.2	70.9	71.2
72.5°	67.2	64.4	63.5	61.6	61.5	60.6	61.2
75°	50.5	49.5	48.8	47.5	47.5	47.5	47.5
77.5°	37.2	36.6	36.2	35.9	35.6	35.1	35.1
80°	29.0	28.7	28.1	28.1	27.7	28.1	27.7
82.5°	21.9	21.9	21.2	21.2	20.8	20.7	20.8
85°	11.2	10.8	11.5	10.8	11.2	10.6	11.2
87.5°	6.7	6.9	6.7	6.8	6.5	7.1	6.7
90°	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P332282-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)