

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332287-935

Luminaire Tested: **S123RDIP-S560D805U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332287-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D805U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4341.5 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	74	63	55	50	67	58	51	46	48	43	40	39	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	23	21	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112



TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.4	1.8
10°-20°	212.5	4.9
20°-30°	305.9	7.0
30°-40°	344.6	7.9
40°-50°	329.7	7.6
50°-60°	270.0	6.2
60°-70°	182.2	4.2
70°-80°	91.6	2.1
80°-90°	26.8	0.6
90°-100°	185.1	4.3
100°-110°	524.0	12.1
110°-120°	515.5	11.9
120°-130°	411.2	9.5
130°-140°	324.2	7.5
140°-150°	242.0	5.6
150°-160°	168.6	3.9
160°-170°	99.1	2.3
170°-180°	32.2	0.7
0°-30°	594.8	13.7
0°-40°	939.4	21.6
0°-60°	1539.1	35.5
0°-90°	1839.7	42.4
90°-120°	1224.6	28.2
90°-150°	2201.9	50.7
90°-180°	2502.0	57.6
0°-180°	4341.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	1	8	17	19	20	3
95°	23	74	399	116	78	25
105°	78	115	541	946	856	83
115°	138	172	414	908	1041	137
125°	192	226	386	700	821	170
135°	225	268	381	576	666	174
145°	256	294	376	473	520	161
155°	291	314	364	414	431	134
165°	318	327	349	370	376	90
175°	332	332	335	339	339	32
180°	332	332	332	332	332	



TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	12.9	11.9	10.8	10.0	9.0	8.6	9.0	9.4	9.8	10.2	10.0
90°	1.4	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2
92.5°	8.4	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1
95°	22.9	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8
97.5°	39.0	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9
100°	49.9	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1
102.5°	61.1	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5
105°	78.1	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4
107.5°	96.1	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5
110°	109.1	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3



TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	120.9	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0
115°	138.0	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5
117.5°	155.1	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8
120°	166.9	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7
122.5°	177.2	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3
125°	191.8	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4
127.5°	203.0	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4
130°	210.0	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9
132.5°	215.4	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9
135°	224.8	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7
137.5°	233.7	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8
140°	239.6	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9
142.5°	246.1	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6
145°	256.5	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9
147.5°	267.0	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2
150°	274.0	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4
152.5°	280.9	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1
155°	291.4	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6
157.5°	299.8	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4
160°	306.3	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5
162.5°	311.2	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7
165°	318.4	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0
167.5°	323.9	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8
170°	327.2	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0
172.5°	329.3	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2
175°	331.8	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9
177.5°	333.0	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	10.0	10.0	10.0	10.2	9.9	9.9	10.0	9.7
90°	16.8	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	56.7	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	242.4	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	604.1	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	793.7	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	856.6	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	875.1	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	822.1	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	771.5	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8





TEST NUMBER: P332287-935

CATALOG NUMBER: S123RDIP-S560D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.3	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	655.0	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	606.9	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	581.6	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	561.7	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	535.1	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	512.0	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	497.5	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	484.0	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	465.8	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	449.3	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	439.5	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	430.4	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	419.4	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	410.4	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	403.9	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	398.0	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	389.1	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	379.6	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	374.3	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	367.8	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	359.5	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	352.1	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	347.3	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	343.0	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.3	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	333.6	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)