

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332249-940

Luminaire Tested: **S123RDIP-S340D585U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332249-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3246.9 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31
2	86	79	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.5
10°-20°	133.9	4.1
20°-30°	192.7	5.9
30°-40°	217.1	6.7
40°-50°	207.7	6.4
50°-60°	170.1	5.2
60°-70°	114.8	3.5
70°-80°	57.7	1.8
80°-90°	17.2	0.5
90°-100°	24.9	0.8
100°-110°	118.6	3.7
110°-120°	284.9	8.8
120°-130°	362.8	11.2
130°-140°	387.7	11.9
140°-150°	362.5	11.2
150°-160°	292.4	9.0
160°-170°	188.7	5.8
170°-180°	65.0	2.0
0°-30°	374.7	11.5
0°-40°	591.8	18.2
0°-60°	969.6	29.9
0°-90°	1159.3	35.7
90°-120°	428.4	13.2
90°-150°	1541.4	47.5
90°-180°	2088.0	64.3
0°-180°	3246.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	0	6	12	14	15	3
95°	31	12	16	19	19	38
105°	152	154	111	26	22	161
115°	284	287	292	297	299	281
125°	401	405	407	408	409	358
135°	499	502	504	505	504	384
145°	576	579	580	581	581	360
155°	634	633	634	636	633	292
165°	669	667	667	670	667	189
175°	685	682	682	686	682	65
180°	685	685	685	685	685	



TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.1	7.5	6.9	6.3	5.7	5.6	5.9	6.2	6.5	6.8	6.8
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	9.5	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7
95°	31.0	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6
97.5°	62.3	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3
100°	86.0	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7
102.5°	112.8	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7
105°	151.6	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4
107.5°	192.4	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5
110°	219.7	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6



TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1
115°	284.3	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1
117.5°	321.6	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7
120°	344.8	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9
122.5°	368.5	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8
125°	400.7	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1
127.5°	432.1	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0
130°	451.7	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2
132.5°	470.4	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5
135°	498.9	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4
137.5°	523.3	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9
140°	539.6	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7
142.5°	554.6	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6
145°	575.7	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5
147.5°	595.6	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1
150°	607.8	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6
152.5°	618.8	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5
155°	634.2	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3
157.5°	646.2	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3
160°	653.5	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2
162.5°	660.5	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4
165°	668.8	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7
167.5°	675.3	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2
170°	678.9	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9
172.5°	681.4	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3
175°	684.6	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3
177.5°	685.4	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	6.8	6.8	6.9	6.9	6.8	6.8	6.8	6.7
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	14.4	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	17.4	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	18.2	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	18.5	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	27.8	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	71.3	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	174.8	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	221.9	218.2	214.5	204.5	188.3	172.2	156.0	139.8



TEST NUMBER: P332249-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.1	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	294.2	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	329.6	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	352.8	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	375.4	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.3	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.3	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	458.6	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.0	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.4	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.1	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.0	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.8	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.4	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	610.7	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	620.9	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	634.8	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	646.9	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	653.9	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.1	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	668.6	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	681.2	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.1	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.2	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)