

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332251-940

Luminaire Tested: **S123RDIP-S340D585U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332251-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3049.6 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.6
10°-20°	133.9	4.4
20°-30°	192.7	6.3
30°-40°	217.1	7.1
40°-50°	207.7	6.8
50°-60°	170.1	5.6
60°-70°	114.8	3.8
70°-80°	57.7	1.9
80°-90°	17.2	0.6
90°-100°	139.8	4.6
100°-110°	395.9	13.0
110°-120°	389.5	12.8
120°-130°	310.7	10.2
130°-140°	244.9	8.0
140°-150°	182.8	6.0
150°-160°	127.4	4.2
160°-170°	74.9	2.5
170°-180°	24.4	0.8
0°-30°	374.7	12.3
0°-40°	591.8	19.4
0°-60°	969.6	31.8
0°-90°	1159.3	38.0
90°-120°	925.2	30.3
90°-150°	1663.7	54.6
90°-180°	1890.0	62.0
0°-180°	3049.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	1	6	13	14	15	2
95°	17	56	302	88	59	19
105°	59	87	409	715	647	63
115°	104	130	313	686	787	103
125°	145	171	292	529	620	129
135°	170	203	288	436	503	131
145°	194	222	284	357	393	121
155°	220	238	275	313	326	101
165°	241	247	264	279	284	68
175°	251	251	253	256	256	24
180°	251	251	251	251	251	



TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.2	7.6	7.0	6.4	5.9	5.6	6.0	6.2	6.6	6.9	6.7
90°	1.0	2.1	3.0	4.5	5.6	6.6	8.1	9.6	11.1	12.8	12.2
92.5°	6.3	9.4	13.6	17.6	21.8	29.4	42.7	64.6	86.1	78.2	59.0
95°	17.3	18.8	24.4	33.1	46.3	66.1	109.3	185.1	268.6	301.6	244.6
97.5°	29.5	30.1	34.4	41.9	54.9	76.4	117.7	203.1	342.1	467.4	500.1
100°	37.6	38.2	41.7	48.9	61.0	80.9	116.5	191.7	325.5	481.6	581.8
102.5°	46.2	47.1	50.3	57.0	67.9	86.1	118.1	182.0	301.1	455.2	585.9
105°	59.0	60.5	63.6	69.6	79.4	95.1	122.6	175.0	271.1	408.9	554.9
107.5°	72.6	74.2	77.1	83.1	92.2	106.8	130.9	174.4	252.0	368.0	500.6
110°	82.4	83.9	86.5	92.0	100.7	114.9	137.9	176.5	244.6	344.8	466.4



TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	91.3	92.9	95.4	101.0	109.7	123.5	144.7	180.6	240.6	329.4	436.7
115°	104.2	106.3	109.3	114.4	123.1	136.8	156.1	187.2	239.1	312.8	400.8
117.5°	117.2	119.5	122.1	126.7	136.4	149.1	168.3	195.9	240.0	303.0	379.2
120°	126.2	127.7	130.2	135.3	145.0	157.7	175.9	202.4	241.6	298.5	367.7
122.5°	133.8	135.4	137.9	143.4	152.7	166.2	184.1	208.6	244.4	295.7	358.4
125°	145.0	146.0	149.0	154.6	164.3	178.0	195.8	218.2	248.7	291.9	346.3
127.5°	153.4	154.9	158.7	164.3	175.0	188.8	206.0	226.1	253.6	290.1	335.8
130°	158.7	160.2	164.8	170.9	181.6	195.3	212.0	231.4	256.8	288.9	330.1
132.5°	162.7	164.7	169.7	177.0	187.7	201.0	217.4	236.3	259.3	288.5	324.8
135°	169.9	171.9	177.5	185.1	195.8	209.6	225.3	242.6	263.0	287.8	317.9
137.5°	176.6	178.7	184.2	192.3	203.0	215.6	230.8	247.3	265.4	286.8	311.9
140°	181.1	183.6	188.7	196.8	207.0	219.7	234.4	249.8	267.0	286.3	308.2
142.5°	185.9	188.1	193.6	200.9	211.1	223.0	237.3	252.2	268.2	285.5	305.0
145°	193.8	195.3	199.9	207.5	216.2	227.8	241.1	254.9	269.0	284.3	300.6
147.5°	201.7	202.6	207.1	213.7	222.0	232.0	244.2	256.5	269.0	282.4	296.3
150°	207.0	207.5	211.6	218.2	225.3	234.4	246.2	256.8	269.0	280.7	293.5
152.5°	212.3	212.4	216.5	222.3	228.5	237.3	247.4	257.7	267.9	278.7	290.3
155°	220.3	220.3	223.3	228.4	234.0	241.1	249.8	257.9	266.5	275.2	285.3
157.5°	226.5	226.9	229.3	233.9	238.6	244.2	251.0	258.4	264.7	272.0	279.8
160°	231.4	231.4	233.4	237.6	241.1	246.2	252.3	258.4	263.9	269.6	276.2
162.5°	235.1	235.1	236.7	240.0	243.1	247.4	252.7	258.0	262.3	267.2	272.5
165°	240.6	240.0	241.1	243.6	245.7	249.2	253.2	256.8	259.9	263.5	267.5
167.5°	244.8	244.2	244.6	246.6	248.0	250.2	253.2	256.0	257.4	259.8	262.8
170°	247.2	246.2	246.6	248.2	249.2	250.2	252.8	254.9	255.8	257.3	259.9
172.5°	248.8	248.2	248.3	249.4	250.0	250.7	252.8	254.4	254.6	255.3	257.1
175°	250.7	250.2	249.8	250.7	250.7	251.3	252.3	253.2	252.8	252.8	253.8
177.5°	251.6	251.3	250.8	251.3	251.3	251.3	251.6	252.4	251.6	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	6.7	6.8	6.8	6.9	6.7	6.8	6.8	6.6
90°	12.8	13.2	13.7	14.7	14.3	14.7	15.2	14.7
92.5°	42.8	34.0	30.1	27.4	26.5	24.9	25.4	24.5
95°	183.1	124.1	97.1	78.8	69.2	64.6	61.0	59.0
97.5°	456.5	365.6	300.0	239.2	201.6	178.7	165.0	160.6
100°	599.7	558.5	498.9	426.7	375.3	338.2	318.4	318.9
102.5°	647.3	646.0	611.3	565.4	525.5	496.1	479.5	467.8
105°	661.2	712.0	721.8	708.5	685.1	665.8	649.5	646.9
107.5°	621.1	703.7	748.2	766.3	766.8	760.3	754.7	750.1
110°	582.8	676.5	740.6	776.1	790.4	794.4	793.4	792.4



TEST NUMBER: P332251-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	545.0	640.6	712.5	758.2	784.3	796.9	800.8	800.9
115°	494.9	583.4	658.2	713.5	751.7	774.1	784.3	786.8
117.5°	458.5	534.9	602.1	658.4	698.1	723.7	738.4	741.8
120°	439.4	508.1	569.1	620.5	660.7	689.2	701.3	704.5
122.5°	424.4	486.5	543.1	590.8	626.5	652.1	665.6	669.4
125°	404.3	459.8	508.6	549.3	581.8	604.2	617.0	620.5
127.5°	386.8	436.3	480.4	517.4	546.4	565.4	576.9	580.2
130°	375.9	421.6	462.8	497.4	524.4	542.7	553.4	557.4
132.5°	365.7	407.8	446.1	479.1	504.4	522.7	532.2	535.0
135°	352.0	388.1	421.2	450.1	475.0	490.3	499.4	503.0
137.5°	339.5	369.1	397.5	422.7	443.6	459.1	466.8	469.1
140°	332.2	358.0	382.5	404.3	423.7	437.9	446.0	445.5
142.5°	325.2	347.5	368.6	387.6	404.1	416.8	424.1	423.6
145°	316.8	333.7	349.9	364.7	377.4	388.1	392.2	393.2
147.5°	310.0	323.3	336.5	347.0	356.6	363.8	367.7	368.1
150°	305.1	316.8	327.5	337.2	344.8	350.4	353.5	353.5
152.5°	300.7	310.8	320.2	328.2	334.2	339.5	341.3	341.3
155°	294.0	302.1	309.8	315.8	320.4	324.5	325.5	326.0
157.5°	286.9	293.6	299.6	304.3	308.4	311.4	312.2	312.1
160°	282.8	288.4	293.5	297.0	300.6	303.6	303.6	303.1
162.5°	277.9	282.7	287.4	290.5	292.8	295.5	295.5	295.0
165°	271.6	274.6	278.2	280.7	282.8	284.8	284.3	284.3
167.5°	266.1	268.4	270.5	272.3	273.2	274.6	274.1	274.1
170°	262.4	263.9	266.0	267.0	267.5	268.6	268.0	268.0
172.5°	259.2	260.3	261.9	262.5	262.6	263.7	262.8	262.3
175°	254.9	255.3	256.4	256.4	256.4	256.8	256.4	255.8
177.5°	252.1	252.4	252.9	252.9	252.4	252.9	252.1	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3

(END OF REPORT)