

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332327-935

Luminaire Tested: **S123RDIP-S775D1195U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332327-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6620.9 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	1.6
10°-20°	290.4	4.4
20°-30°	418.2	6.3
30°-40°	471.1	7.1
40°-50°	450.7	6.8
50°-60°	369.0	5.6
60°-70°	249.0	3.8
70°-80°	125.3	1.9
80°-90°	36.9	0.6
90°-100°	48.9	0.7
100°-110°	233.3	3.5
110°-120°	560.4	8.5
120°-130°	713.6	10.8
130°-140°	762.5	11.5
140°-150°	713.0	10.8
150°-160°	575.1	8.7
160°-170°	371.2	5.6
170°-180°	127.9	1.9
0°-30°	813.0	12.3
0°-40°	1284.1	19.4
0°-60°	2103.8	31.8
0°-90°	2514.9	38.0
90°-120°	842.6	12.7
90°-150°	3031.7	45.8
90°-180°	4106.0	62.0
0°-180°	6620.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	11	24	28	30	5
95°	61	23	31	38	38	75
105°	298	304	219	52	44	316
115°	559	565	574	584	588	552
125°	788	796	800	802	804	704
135°	981	987	991	994	991	755
145°	1132	1139	1141	1143	1143	709
155°	1247	1246	1246	1251	1245	574
165°	1315	1313	1311	1319	1312	371
175°	1346	1342	1342	1349	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.5	16.2	14.9	13.5	12.2	11.9	12.5	13.0	13.6	14.2	14.2
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	18.6	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0
95°	61.0	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5
97.5°	122.6	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0
100°	169.0	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8
102.5°	221.9	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3
105°	298.1	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7
107.5°	378.5	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6
110°	432.1	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8



TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.4	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7
115°	559.2	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4
117.5°	632.6	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4
120°	678.2	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0
122.5°	724.6	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1
125°	788.2	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7
127.5°	849.9	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4
130°	888.3	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2
132.5°	925.1	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2
135°	981.3	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0
137.5°	1029.3	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2
140°	1061.4	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3
142.5°	1091.0	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7
145°	1132.4	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8
147.5°	1171.4	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5
150°	1195.4	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8
152.5°	1217.0	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4
155°	1247.4	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5
157.5°	1271.0	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2
160°	1285.4	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8
162.5°	1299.0	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9
165°	1315.4	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2
167.5°	1328.3	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0
170°	1335.4	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2
172.5°	1340.2	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0
175°	1346.4	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0
177.5°	1348.1	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	14.2	14.2	14.2	14.2	14.1	14.1	14.0	13.9
90°	25.7	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	28.4	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	34.1	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	35.7	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	36.6	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	54.8	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	140.3	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	343.8	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	436.4	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P332327-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	501.8	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	578.6	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	648.2	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	693.8	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	738.3	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.2	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.1	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.1	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	938.1	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1041.3	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1072.1	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1101.4	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.3	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1178.9	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.3	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1221.2	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1248.6	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1272.5	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1286.1	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1298.5	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1315.0	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1339.8	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1345.6	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1347.6	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)