

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832138

Luminaire Tested: S123RDIP-S340D585U940-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832138  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U940-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3108.8 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 27.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42				
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	43	37				
2	89	82	76	71	81	75	70	66	62	59	56	51	48	46	40	38	37	32				
3	81	73	66	60	74	67	61	56	56	51	48	45	43	40	36	34	32	28				
4	75	65	57	52	68	60	53	48	50	45	42	41	38	35	33	31	29	25				
5	69	58	50	45	63	54	47	42	45	40	36	37	34	31	30	28	26	22				
6	64	52	45	39	58	48	42	37	41	36	32	34	30	28	28	25	23	20				
7	59	48	40	35	54	44	38	33	38	32	29	31	28	25	25	23	21	18				
8	55	43	36	31	51	40	34	29	34	29	26	29	25	22	24	21	19	17				
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15				
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	10663	10663	10663	10663	10663
5°	12661	12257	10730	8674	8053
10°	11471	12450	10676	6949	5962
15°	7899	10674	10564	5680	4716
20°	5495	8219	10352	4789	4145
25°	4187	6264	10043	4257	3821
30°	3644	5008	9657	3952	3539
35°	3347	4225	9110	3696	3282
40°	3053	3773	8396	3444	3048
45°	2757	3449	7623	3206	2813
50°	2503	3183	6713	2972	2524
55°	2263	2924	5838	2744	2164
60°	2028	2659	5072	2493	2045
65°	1872	2358	4365	2239	1936
70°	1520	2039	3808	2027	1574
75°	1335	1622	3227	1680	1385
80°	1209	1370	2641	1407	1308
85°	1099	1198	2001	1284	1198

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 8044 cd/sqm



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.3	2.9
10°-20°	208.9	6.7
20°-30°	239.7	7.7
30°-40°	236.3	7.6
40°-50°	208.4	6.7
50°-60°	160.3	5.2
60°-70°	105.4	3.4
70°-80°	51.2	1.6
80°-90°	14.3	0.5
90°-100°	41.7	1.3
100°-110°	126.2	4.1
110°-120°	214.8	6.9
120°-130°	282.5	9.1
130°-140°	317.6	10.2
140°-150°	312.2	10.0
150°-160°	262.9	8.5
160°-170°	175.0	5.6
170°-180°	61.3	2.0
0°-30°	539.0	17.3
0°-40°	775.3	24.9
0°-60°	1143.9	36.8
0°-90°	1314.8	42.3
90°-120°	382.6	12.3
90°-150°	1294.9	41.7
90°-180°	1794.0	57.7
0°-180°	3108.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	991	991	991	991	991	
5°	1172	1134	993	803	745	107
15°	709	958	948	510	423	200
25°	352	527	846	358	322	167
35°	255	322	693	281	250	159
45°	181	227	501	211	185	141
55°	121	156	311	146	115	108
65°	74	93	171	88	76	72
75°	32	39	78	40	33	35
85°	9	10	16	10	10	9
90°	15	12	0	12	15	8
95°	40	38	30	38	40	40
105°	121	120	114	120	121	128
115°	217	217	216	217	217	215
125°	313	317	316	317	313	280
135°	410	413	410	413	410	315
145°	498	500	498	500	498	311
155°	569	571	570	571	569	262
165°	619	620	621	620	619	175
175°	643	644	646	644	643	61
180°	648	648	648	648	648	



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1097.9	1094.4	1090.9	1089.9	1088.9	1085.7	1082.4	1075.1	1067.8	1060.3	1052.8
5°	1171.8	1172.2	1172.6	1171.6	1170.6	1166.3	1162.0	1153.1	1144.2	1134.4	1124.7
7.5°	1149.0	1155.5	1162.0	1163.2	1164.5	1167.7	1171.0	1168.9	1166.9	1163.2	1159.6
10°	1049.5	1049.1	1048.7	1056.0	1063.3	1085.1	1106.8	1118.0	1129.1	1139.1	1149.0
12.5°	887.1	887.7	888.3	912.2	936.2	956.7	977.2	1005.7	1034.1	1064.8	1095.4
15°	708.8	718.7	728.7	750.0	771.3	802.2	833.0	871.2	909.4	957.9	1006.5
17.5°	582.0	586.3	590.6	611.1	631.6	660.8	690.1	733.3	776.6	839.1	901.7
20°	479.7	483.5	487.4	502.2	517.0	545.1	573.1	614.3	655.5	717.5	779.4
22.5°	400.5	408.0	415.5	425.5	435.4	455.7	476.0	518.1	560.1	616.6	673.0
25°	352.5	356.0	359.5	368.0	376.5	396.0	415.5	443.3	471.1	527.4	583.7
27.5°	320.1	321.1	322.1	328.4	334.7	347.3	359.9	385.6	411.4	457.7	504.0
30°	293.2	295.1	296.9	301.8	306.7	315.8	324.9	343.2	361.5	402.9	444.3
32.5°	272.5	273.5	274.6	278.6	282.7	289.4	296.1	310.5	324.9	356.6	388.3
35°	254.7	254.9	255.1	258.1	261.2	267.7	274.2	286.1	298.1	321.5	344.8
37.5°	234.4	235.8	237.2	239.4	241.7	247.4	253.0	262.8	272.5	291.8	311.1
40°	217.3	218.5	219.7	222.4	225.0	229.5	233.9	242.9	251.8	268.5	285.1
42.5°	200.2	201.0	201.9	204.5	207.1	212.6	218.1	225.2	232.3	246.1	259.9
45°	181.1	183.2	185.2	188.1	190.9	195.6	200.2	207.5	214.9	226.6	238.4
47.5°	165.3	166.3	167.3	169.8	172.2	177.9	183.6	190.1	196.6	207.5	218.5
50°	149.5	149.9	150.3	152.5	154.7	159.8	164.9	172.4	179.9	190.1	200.2
52.5°	134.4	135.5	136.5	138.7	140.9	144.4	147.8	155.6	163.3	173.2	183.2
55°	120.6	121.2	121.8	123.5	125.1	129.2	133.2	139.9	146.6	155.8	164.9
57.5°	107.6	108.4	109.3	110.5	111.7	115.3	119.0	124.9	130.8	139.9	149.1
60°	94.2	95.2	96.3	97.7	99.1	101.9	104.8	110.1	115.3	123.5	131.6
62.5°	84.5	84.7	84.9	86.1	87.3	89.4	91.4	95.7	99.9	108.0	116.2
65°	73.5	74.1	74.7	75.3	76.0	77.6	79.2	82.9	86.5	92.6	98.7
67.5°	62.1	62.8	63.4	64.4	65.4	66.8	68.2	70.7	73.1	78.8	84.5
70°	48.3	48.3	48.3	50.0	51.6	54.0	56.5	58.3	60.1	64.8	69.5
72.5°	39.4	39.6	39.8	40.0	40.2	41.6	43.1	46.1	49.1	52.0	54.8
75°	32.1	32.3	32.5	32.7	32.9	33.3	33.7	34.7	35.7	39.0	42.2
77.5°	25.6	25.8	26.0	26.2	26.4	26.8	27.2	27.6	28.0	29.2	30.5
80°	19.5	19.7	19.9	20.1	20.3	20.5	20.7	21.1	21.5	22.1	22.7
82.5°	14.2	14.2	14.2	14.2	14.2	14.6	15.0	15.0	15.0	15.4	15.8
85°	8.9	8.9	8.9	9.1	9.3	9.3	9.3	9.5	9.7	9.7	9.7
87.5°	4.1	3.9	3.7	3.9	4.1	4.1	4.1	4.3	4.5	4.5	4.5
90°	15.3	15.0	14.8	14.6	14.4	14.0	13.6	13.1	12.7	12.2	10.7
92.5°	21.9	22.1	22.3	22.5	22.8	22.7	22.4	22.0	21.7	21.4	20.7
95°	39.7	39.7	39.7	39.7	39.7	39.4	39.0	38.5	38.1	37.6	36.7
97.5°	57.0	57.1	57.2	57.3	57.4	57.2	56.6	56.1	55.5	54.9	54.3
100°	77.3	77.1	76.9	76.6	76.4	76.1	75.8	75.4	75.1	74.8	74.2
102.5°	98.2	98.3	98.4	98.5	98.6	98.5	98.2	97.8	97.5	97.1	96.4
105°	121.1	120.8	120.6	120.4	120.1	120.0	120.0	120.0	120.0	120.0	119.0
107.5°	144.4	144.6	144.7	144.8	144.9	144.8	144.4	144.1	143.8	143.4	143.0
110°	168.4	168.6	168.8	169.0	169.3	169.1	168.7	168.2	167.8	167.3	167.1



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	193.8	193.8	193.8	193.8	193.8	193.5	192.9	192.4	191.8	191.2	191.2
115°	216.7	216.8	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7	216.9
117.5°	240.1	240.4	240.7	241.1	241.4	241.6	241.6	241.6	241.6	241.6	241.8
120°	265.0	265.2	265.4	265.7	265.9	266.1	266.2	266.3	266.4	266.5	267.1
122.5°	288.9	289.2	289.6	289.9	290.3	290.6	290.9	291.3	291.6	291.9	292.2
125°	312.8	313.3	313.7	314.2	314.6	315.1	315.5	316.0	316.4	316.9	317.1
127.5°	336.7	337.2	337.6	338.1	338.5	339.1	339.8	340.4	341.1	341.8	342.0
130°	360.1	360.9	361.7	362.5	363.3	363.9	364.3	364.8	365.2	365.7	366.0
132.5°	384.5	385.1	385.6	386.2	386.8	387.3	387.9	388.5	389.0	389.6	389.8
135°	410.0	410.2	410.4	410.6	410.9	411.2	411.6	412.1	412.6	413.0	413.1
137.5°	432.3	432.7	433.0	433.3	433.7	434.1	434.7	435.3	435.8	436.4	436.1
140°	454.2	455.0	455.8	456.6	457.4	457.8	457.9	458.0	458.2	458.3	458.2
142.5°	476.6	477.1	477.7	478.3	478.8	479.2	479.3	479.4	479.5	479.6	479.4
145°	497.9	498.4	498.8	499.3	499.8	500.0	500.1	500.3	500.4	500.5	500.1
147.5°	517.3	517.9	518.6	519.3	520.0	520.3	520.3	520.3	520.3	520.3	520.0
150°	535.6	536.3	536.9	537.6	538.3	538.6	538.6	538.6	538.6	538.6	538.4
152.5°	553.4	553.9	554.5	555.1	555.6	555.8	555.6	555.4	555.1	554.9	554.8
155°	569.1	569.9	570.7	571.5	572.3	572.5	572.0	571.6	571.1	570.7	570.6
157.5°	583.9	584.6	585.3	585.9	586.6	586.7	586.3	585.8	585.4	584.9	584.8
160°	598.1	598.6	599.0	599.5	599.9	599.9	599.3	598.8	598.2	597.6	597.6
162.5°	608.8	609.6	610.4	611.2	612.0	612.1	611.5	611.0	610.4	609.8	609.7
165°	619.0	619.8	620.6	621.4	622.2	622.2	621.5	620.9	620.2	619.5	619.5
167.5°	628.1	628.8	629.5	630.2	630.9	630.9	630.2	629.5	628.8	628.1	628.0
170°	634.8	635.6	636.3	637.1	637.9	637.9	637.1	636.3	635.6	634.8	634.8
172.5°	639.8	640.6	641.4	642.2	643.0	643.1	642.4	641.7	641.0	640.4	640.4
175°	643.4	644.2	645.0	645.8	646.6	646.6	646.0	645.3	644.6	643.9	643.9
177.5°	645.4	646.2	647.0	647.8	648.6	648.7	648.0	647.3	646.6	646.0	646.0
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1051.8	1050.7	1041.0	1031.2	1021.7	1012.2	1005.0	997.9	986.0	974.0	966.5
5°	1116.9	1109.2	1093.8	1078.4	1055.2	1032.1	1012.6	993.1	968.3	943.5	922.8
7.5°	1153.3	1147.0	1128.3	1109.6	1079.0	1048.3	1017.8	987.4	950.8	914.3	883.0
10°	1154.3	1159.6	1144.2	1128.7	1094.2	1059.7	1018.2	976.8	927.7	878.5	838.1
12.5°	1118.2	1140.9	1137.7	1134.4	1099.3	1064.1	1013.8	963.4	903.1	842.8	792.2
15°	1050.5	1094.6	1107.6	1120.6	1091.6	1062.5	1005.2	948.0	877.1	806.2	748.1
17.5°	963.4	1025.1	1059.5	1093.8	1072.7	1051.6	988.8	926.0	846.2	766.4	703.3
20°	860.2	941.1	994.9	1048.7	1041.0	1033.3	968.5	903.7	817.6	731.5	663.1
22.5°	758.3	843.6	917.9	992.3	1000.2	1008.1	942.7	877.3	783.1	688.8	619.2
25°	670.4	757.1	845.6	934.2	952.0	969.9	907.8	845.6	747.9	650.3	581.0
27.5°	586.5	668.9	766.4	863.9	896.4	928.9	872.0	815.2	713.4	611.7	542.6
30°	518.1	591.8	691.3	790.8	836.1	881.4	829.2	777.0	676.1	575.1	507.5
32.5°	454.3	520.3	620.2	720.1	772.7	825.3	780.2	735.2	638.1	541.0	474.2
35°	403.9	463.0	556.2	649.5	708.3	767.2	730.3	693.3	598.5	503.6	440.5
37.5°	360.7	410.2	497.7	585.3	647.8	710.4	679.5	648.6	559.5	470.3	410.6
40°	324.9	364.7	446.2	527.6	588.9	650.3	623.9	597.5	517.7	437.8	382.0
42.5°	294.3	328.6	401.7	474.8	531.1	587.3	569.8	552.4	480.1	407.8	356.0
45°	267.3	296.1	360.5	424.8	476.6	528.4	514.6	500.8	438.5	376.1	328.6
47.5°	243.3	268.1	325.5	383.0	429.5	476.0	463.2	450.4	398.8	347.3	304.0
50°	221.4	242.5	290.4	338.3	380.2	422.0	411.4	400.9	358.2	315.6	278.2
52.5°	200.6	218.1	261.2	304.2	337.9	371.6	363.5	355.4	322.5	289.6	255.7
55°	180.9	197.0	233.3	269.7	298.5	327.4	319.2	311.1	285.5	259.9	230.1
57.5°	163.1	177.1	206.5	236.0	258.9	281.9	278.0	274.2	252.8	231.5	206.9
60°	144.2	156.8	182.2	207.5	226.0	244.5	240.0	235.6	220.3	205.1	184.0
62.5°	127.3	138.5	158.8	179.1	194.1	209.2	205.9	202.7	191.1	179.5	162.1
65°	109.7	120.6	137.1	153.5	165.3	177.1	174.2	171.4	162.7	153.9	139.9
67.5°	93.6	102.8	117.0	131.2	139.1	147.0	145.4	143.8	137.1	130.4	119.4
70°	77.4	85.3	97.1	108.9	114.3	119.8	120.4	121.0	114.9	108.9	100.7
72.5°	61.1	67.4	78.4	89.4	93.6	97.9	97.7	97.5	93.8	90.2	82.9
75°	46.9	51.6	60.1	68.6	72.3	76.0	76.8	77.6	74.1	70.7	66.6
77.5°	33.7	37.0	43.5	50.0	54.0	58.1	58.5	58.9	57.3	55.6	51.8
80°	23.8	24.8	28.8	32.9	37.2	41.4	42.0	42.6	41.0	39.4	37.0
82.5°	16.4	17.1	18.5	19.9	23.4	26.8	27.6	28.4	27.6	26.8	24.2
85°	10.0	10.2	10.8	11.4	13.0	14.6	15.4	16.2	15.8	15.4	14.0
87.5°	4.5	4.5	4.7	4.9	5.3	5.7	6.7	7.7	7.1	6.5	5.9
90°	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5	1.6	2.8	3.9
92.5°	20.0	19.3	18.6	18.0	17.3	16.6	15.9	15.3	15.9	16.6	17.3
95°	35.8	34.9	34.0	33.2	32.4	31.6	30.8	30.0	30.8	31.6	32.4
97.5°	53.6	52.9	52.2	51.6	51.0	50.5	49.9	49.3	49.9	50.5	51.0
100°	73.6	73.1	72.5	71.9	71.2	70.5	69.9	69.2	69.9	70.5	71.2
102.5°	95.6	94.8	94.0	93.4	93.1	92.7	92.4	92.1	92.4	92.7	93.1
105°	118.0	117.0	116.0	115.3	115.1	114.9	114.7	114.4	114.7	114.9	115.1
107.5°	142.5	142.1	141.6	141.3	141.2	141.1	141.0	140.9	141.0	141.1	141.2
110°	166.9	166.7	166.4	166.2	166.0	165.8	165.5	165.3	165.5	165.8	166.0





TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	191.2	191.2	191.2	191.2	191.1	191.0	190.8	190.7	190.8	191.0	191.1
115°	217.1	217.4	217.6	217.5	217.2	216.8	216.5	216.2	216.5	216.8	217.2
117.5°	242.0	242.3	242.5	242.6	242.4	242.3	242.2	242.1	242.2	242.3	242.4
120°	267.6	268.2	268.8	268.7	268.0	267.4	266.7	266.0	266.7	267.4	268.0
122.5°	292.4	292.6	292.9	292.7	292.3	291.8	291.4	290.9	291.4	291.8	292.3
125°	317.3	317.6	317.8	317.7	317.4	317.0	316.7	316.4	316.7	317.0	317.4
127.5°	342.2	342.5	342.7	342.5	341.8	341.1	340.4	339.8	340.4	341.1	341.8
130°	366.4	366.7	367.1	366.8	365.9	365.0	364.1	363.2	364.1	365.0	365.9
132.5°	390.1	390.3	390.5	390.2	389.3	388.4	387.5	386.6	387.5	388.4	389.3
135°	413.2	413.3	413.5	413.2	412.5	411.8	411.1	410.5	411.1	411.8	412.5
137.5°	435.7	435.4	435.0	434.6	434.0	433.5	432.9	432.3	432.9	433.5	434.0
140°	458.0	457.9	457.8	457.5	456.9	456.3	455.8	455.2	455.8	456.3	456.9
142.5°	479.2	479.0	478.7	478.3	477.8	477.2	476.6	476.1	476.6	477.2	477.8
145°	499.8	499.5	499.1	498.8	498.6	498.4	498.2	497.9	498.2	498.4	498.6
147.5°	519.6	519.3	519.0	518.6	518.1	517.7	517.2	516.8	517.2	517.7	518.1
150°	538.2	538.0	537.7	537.5	537.3	537.0	536.8	536.6	536.8	537.0	537.3
152.5°	554.7	554.6	554.5	554.2	553.9	553.6	553.2	552.9	553.2	553.6	553.9
155°	570.4	570.3	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
157.5°	584.7	584.6	584.5	584.5	584.6	584.7	584.8	584.9	584.8	584.7	584.6
160°	597.6	597.6	597.6	597.7	598.0	598.2	598.4	598.6	598.4	598.2	598.0
162.5°	609.6	609.5	609.4	609.5	609.8	610.2	610.5	610.9	610.5	610.2	609.8
165°	619.5	619.5	619.5	619.7	620.0	620.4	620.7	621.0	620.7	620.4	620.0
167.5°	627.9	627.8	627.7	627.9	628.3	628.8	629.2	629.7	629.2	628.8	628.3
170°	634.8	634.8	634.8	635.0	635.4	635.9	636.3	636.8	636.3	635.9	635.4
172.5°	640.4	640.4	640.4	640.6	641.0	641.5	641.9	642.4	641.9	641.5	641.0
175°	643.9	643.9	643.9	644.1	644.6	645.0	645.5	646.0	645.5	645.0	644.6
177.5°	646.0	646.0	646.0	646.2	646.6	647.1	647.5	648.0	647.5	647.1	646.6
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	958.9	947.4	935.8	927.5	919.1	908.8	898.4	898.0	897.6	889.9	882.2
5°	902.1	882.0	861.9	842.2	822.5	802.8	783.1	778.6	774.1	767.4	760.7
7.5°	851.7	819.6	787.5	762.4	737.2	717.5	697.8	684.4	671.0	660.6	650.3
10°	797.7	757.9	718.1	687.6	657.2	635.8	614.5	599.1	583.7	576.3	569.0
12.5°	741.6	698.4	655.1	625.3	595.4	569.8	544.3	530.2	516.2	506.1	495.9
15°	690.1	643.6	597.1	565.4	533.7	509.7	485.8	471.8	457.7	447.6	437.4
17.5°	640.1	593.2	546.3	514.2	482.1	460.4	438.7	425.0	411.4	405.1	398.8
20°	594.6	547.3	500.0	469.7	439.5	418.1	396.8	389.5	382.2	376.3	370.4
22.5°	549.5	504.0	458.6	429.5	400.5	385.0	369.6	363.7	357.8	353.4	348.9
25°	511.8	466.5	421.2	395.8	370.4	358.4	346.5	342.6	338.7	334.3	329.8
27.5°	473.6	430.5	387.5	367.2	346.9	337.1	327.4	322.5	317.6	314.0	310.3
30°	439.9	400.1	360.3	343.4	326.6	318.0	309.5	304.2	298.9	295.5	292.0
32.5°	407.4	372.0	336.7	322.3	307.9	299.5	291.2	286.1	281.1	277.0	272.9
35°	377.3	346.7	316.0	302.8	289.6	281.3	272.9	267.9	262.8	258.7	254.7
37.5°	350.9	323.1	295.3	282.9	270.5	263.2	255.9	250.6	245.3	241.1	236.8
40°	326.1	301.6	277.0	265.0	253.0	245.1	237.2	232.5	227.9	224.0	220.1
42.5°	304.2	281.7	259.1	247.4	235.6	228.1	220.5	215.1	209.6	207.3	205.1
45°	281.1	261.2	241.3	229.9	218.5	210.6	202.7	198.0	193.3	191.3	189.3
47.5°	260.8	242.3	223.8	212.6	201.5	194.3	187.2	183.6	179.9	177.1	174.2
50°	240.9	223.0	205.1	194.3	183.6	177.5	171.4	166.9	162.5	160.4	158.4
52.5°	221.8	205.5	189.3	178.3	167.3	161.4	155.6	151.7	147.8	143.6	139.3
55°	200.2	186.0	171.8	162.1	152.3	146.2	140.1	135.7	131.2	126.7	122.3
57.5°	182.4	168.4	154.3	145.6	136.9	131.0	125.1	120.2	115.3	111.7	108.0
60°	162.9	150.7	138.5	130.0	121.4	115.8	110.1	105.4	100.7	98.9	97.1
62.5°	144.6	133.2	121.8	114.3	106.8	101.3	95.9	92.8	89.8	88.5	87.3
65°	125.9	116.2	106.4	99.5	92.6	87.9	83.3	81.8	80.4	79.4	78.4
67.5°	108.4	100.1	91.8	85.7	79.6	76.4	73.1	71.5	69.9	68.6	67.4
70°	92.6	85.3	78.0	72.7	67.4	64.4	61.3	59.9	58.5	56.3	54.0
72.5°	75.5	69.9	64.2	60.1	56.1	53.4	50.8	47.9	45.1	43.1	41.0
75°	62.5	56.9	51.2	47.3	43.5	40.4	37.4	36.4	35.3	34.7	34.1
77.5°	47.9	43.1	38.2	35.1	32.1	30.7	29.2	28.6	28.0	27.8	27.6
80°	34.5	30.5	26.4	24.8	23.2	22.7	22.3	21.9	21.5	21.3	21.1
82.5°	21.5	19.5	17.5	17.1	16.7	16.4	16.2	16.0	15.8	15.6	15.4
85°	12.6	11.8	11.0	10.8	10.6	10.4	10.2	10.2	10.2	10.2	10.2
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.1	4.9
90°	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1	13.6	14.0	14.4
92.5°	18.0	18.6	19.3	20.0	20.7	21.4	21.7	22.0	22.4	22.7	22.8
95°	33.2	34.0	34.9	35.8	36.7	37.6	38.1	38.5	39.0	39.4	39.7
97.5°	51.6	52.2	52.9	53.6	54.3	54.9	55.5	56.1	56.6	57.2	57.4
100°	71.9	72.5	73.1	73.6	74.2	74.8	75.1	75.4	75.8	76.1	76.4
102.5°	93.4	94.0	94.8	95.6	96.4	97.1	97.5	97.8	98.2	98.5	98.6
105°	115.3	116.0	117.0	118.0	119.0	120.0	120.0	120.0	120.0	120.0	120.1
107.5°	141.3	141.6	142.1	142.5	143.0	143.4	143.8	144.1	144.4	144.8	144.9
110°	166.2	166.4	166.7	166.9	167.1	167.3	167.8	168.2	168.7	169.1	169.3



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	191.2	191.2	191.2	191.2	191.2	191.2	191.8	192.4	192.9	193.5	193.8
115°	217.5	217.6	217.4	217.1	216.9	216.7	216.8	216.9	217.0	217.1	217.1
117.5°	242.6	242.5	242.3	242.0	241.8	241.6	241.6	241.6	241.6	241.6	241.4
120°	268.7	268.8	268.2	267.6	267.1	266.5	266.4	266.3	266.2	266.1	265.9
122.5°	292.7	292.9	292.6	292.4	292.2	291.9	291.6	291.3	290.9	290.6	290.3
125°	317.7	317.8	317.6	317.3	317.1	316.9	316.4	316.0	315.5	315.1	314.6
127.5°	342.5	342.7	342.5	342.2	342.0	341.8	341.1	340.4	339.8	339.1	338.5
130°	366.8	367.1	366.7	366.4	366.0	365.7	365.2	364.8	364.3	363.9	363.3
132.5°	390.2	390.5	390.3	390.1	389.8	389.6	389.0	388.5	387.9	387.3	386.8
135°	413.2	413.5	413.3	413.2	413.1	413.0	412.6	412.1	411.6	411.2	410.9
137.5°	434.6	435.0	435.4	435.7	436.1	436.4	435.8	435.3	434.7	434.1	433.7
140°	457.5	457.8	457.9	458.0	458.2	458.3	458.2	458.0	457.9	457.8	457.4
142.5°	478.3	478.7	479.0	479.2	479.4	479.6	479.5	479.4	479.3	479.2	478.8
145°	498.8	499.1	499.5	499.8	500.1	500.5	500.4	500.3	500.1	500.0	499.8
147.5°	518.6	519.0	519.3	519.6	520.0	520.3	520.3	520.3	520.3	520.3	520.0
150°	537.5	537.7	538.0	538.2	538.4	538.6	538.6	538.6	538.6	538.6	538.3
152.5°	554.2	554.5	554.6	554.7	554.8	554.9	555.1	555.4	555.6	555.8	555.6
155°	570.2	570.2	570.3	570.4	570.6	570.7	571.1	571.6	572.0	572.5	572.3
157.5°	584.5	584.5	584.6	584.7	584.8	584.9	585.4	585.8	586.3	586.7	586.6
160°	597.7	597.6	597.6	597.6	597.6	597.6	598.2	598.8	599.3	599.9	599.9
162.5°	609.5	609.4	609.5	609.6	609.7	609.8	610.4	611.0	611.5	612.1	612.0
165°	619.7	619.5	619.5	619.5	619.5	619.5	620.2	620.9	621.5	622.2	622.2
167.5°	627.9	627.7	627.8	627.9	628.0	628.1	628.8	629.5	630.2	630.9	630.9
170°	635.0	634.8	634.8	634.8	634.8	634.8	635.6	636.3	637.1	637.9	637.9
172.5°	640.6	640.4	640.4	640.4	640.4	640.4	641.0	641.7	642.4	643.1	643.0
175°	644.1	643.9	643.9	643.9	643.9	643.9	644.6	645.3	646.0	646.6	646.6
177.5°	646.2	646.0	646.0	646.0	646.0	646.0	646.6	647.3	648.0	648.7	648.6
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	990.6	990.6	990.6	990.6
2.5°	880.2	878.1	877.3	876.5
5°	754.4	748.1	746.7	745.3
7.5°	647.6	645.0	636.3	627.5
10°	560.9	552.8	549.1	545.5
12.5°	488.4	480.9	479.7	478.5
15°	432.2	426.9	425.0	423.2
17.5°	395.2	391.5	389.3	387.1
20°	367.8	365.1	363.5	361.9
22.5°	346.9	344.8	343.6	342.4
25°	326.8	323.7	322.7	321.7
27.5°	307.7	305.0	304.0	303.0
30°	289.8	287.6	286.1	284.7
32.5°	270.3	267.7	266.8	266.0
35°	253.0	251.4	250.6	249.8
37.5°	234.8	232.7	231.5	230.3
40°	219.1	218.1	217.5	216.9
42.5°	203.3	201.5	201.3	201.0
45°	187.4	185.6	185.2	184.8
47.5°	172.6	171.0	170.8	170.6
50°	156.2	153.9	152.3	150.7
52.5°	137.3	135.3	133.8	132.4
55°	120.0	117.8	116.6	115.3
57.5°	107.0	106.0	105.4	104.8
60°	96.5	95.9	95.4	95.0
62.5°	86.7	86.1	86.1	86.1
65°	77.8	77.2	76.6	76.0
67.5°	66.2	65.0	64.8	64.6
70°	52.2	50.4	50.2	50.0
72.5°	40.8	40.6	40.2	39.8
75°	33.7	33.3	33.3	33.3
77.5°	27.2	26.8	26.8	26.8
80°	20.9	20.7	20.9	21.1
82.5°	15.4	15.4	15.2	15.0
85°	10.0	9.7	9.7	9.7
87.5°	4.9	4.9	4.9	4.9
90°	14.6	14.8	15.0	15.3
92.5°	22.5	22.3	22.1	21.9
95°	39.7	39.7	39.7	39.7
97.5°	57.3	57.2	57.1	57.0
100°	76.6	76.9	77.1	77.3
102.5°	98.5	98.4	98.3	98.2
105°	120.4	120.6	120.8	121.1
107.5°	144.8	144.7	144.6	144.4
110°	169.0	168.8	168.6	168.4



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	193.8	193.8	193.8	193.8
115°	217.0	216.9	216.8	216.7
117.5°	241.1	240.7	240.4	240.1
120°	265.7	265.4	265.2	265.0
122.5°	289.9	289.6	289.2	288.9
125°	314.2	313.7	313.3	312.8
127.5°	338.1	337.6	337.2	336.7
130°	362.5	361.7	360.9	360.1
132.5°	386.2	385.6	385.1	384.5
135°	410.6	410.4	410.2	410.0
137.5°	433.3	433.0	432.7	432.3
140°	456.6	455.8	455.0	454.2
142.5°	478.3	477.7	477.1	476.6
145°	499.3	498.8	498.4	497.9
147.5°	519.3	518.6	517.9	517.3
150°	537.6	536.9	536.3	535.6
152.5°	555.1	554.5	553.9	553.4
155°	571.5	570.7	569.9	569.1
157.5°	585.9	585.3	584.6	583.9
160°	599.5	599.0	598.6	598.1
162.5°	611.2	610.4	609.6	608.8
165°	621.4	620.6	619.8	619.0
167.5°	630.2	629.5	628.8	628.1
170°	637.1	636.3	635.6	634.8
172.5°	642.2	641.4	640.6	639.8
175°	645.8	645.0	644.2	643.4
177.5°	647.8	647.0	646.2	645.4
180°	647.5	647.5	647.5	647.5



TEST NUMBER: P832138

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.20	8.95	9.23	9.98	11.36	12.86	13.61	13.89	14.65	16.03
	3H	9.41	10.09	10.46	11.13	12.53	14.36	15.03	15.40	16.07	17.47
	4H	9.79	10.43	10.85	11.47	12.88	14.84	15.48	15.89	16.52	17.93
	6H	10.07	10.66	11.13	11.70	13.12	15.15	15.73	16.21	16.78	18.20
	8H	10.16	10.71	11.22	11.77	13.19	15.23	15.78	16.29	16.84	18.26
	12H	10.20	10.73	11.28	11.79	13.23	15.26	15.78	16.33	16.84	18.28
4H	2H	8.91	9.55	9.97	10.59	12.00	12.85	13.48	13.91	14.53	15.94
	3H	10.28	10.80	11.34	11.88	13.30	14.50	15.03	15.57	16.10	17.52
	4H	10.73	11.21	11.80	12.27	13.72	15.10	15.59	16.17	16.65	18.09
	6H	11.09	11.51	12.17	12.59	14.03	15.54	15.95	16.62	17.04	18.47
	8H	11.22	11.60	12.30	12.68	14.13	15.67	16.05	16.75	17.13	18.58
	12H	11.29	11.64	12.39	12.73	14.18	15.72	16.07	16.82	17.17	18.62
8H	4H	11.04	11.42	12.12	12.50	13.95	15.06	15.45	16.15	16.53	17.98
	6H	11.50	11.82	12.60	12.94	14.39	15.56	15.88	16.66	17.00	18.45
	8H	11.69	11.97	12.80	13.07	14.54	15.74	16.02	16.85	17.13	18.59
	12H	11.83	12.07	12.94	13.17	14.68	15.86	16.10	16.97	17.20	18.71
12H	4H	11.04	11.39	12.14	12.48	13.94	15.01	15.36	16.11	16.45	17.91
	6H	11.56	11.84	12.67	12.94	14.41	15.53	15.81	16.64	16.91	18.38
	8H	11.77	12.02	12.88	13.11	14.62	15.72	15.97	16.84	17.07	18.57