

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332303-935

Luminaire Tested: **S123RDIP-S775D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332303-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3761.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	79	77	73	71	69	64	63	61	57
2	93	86	80	75	88	81	76	71	72	68	65	64	61	58	57	54	52	49
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	60	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	46	41	46	41	38	41	37	34	32
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	30	28
7	62	49	41	36	58	47	40	34	43	36	32	38	33	30	34	30	27	25
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	2.8
10°-20°	290.4	7.7
20°-30°	418.2	11.1
30°-40°	471.1	12.5
40°-50°	450.7	12.0
50°-60°	369.0	9.8
60°-70°	249.0	6.6
70°-80°	125.3	3.3
80°-90°	34.3	0.9
90°-100°	14.9	0.4
100°-110°	71.0	1.9
110°-120°	170.4	4.5
120°-130°	217.0	5.8
130°-140°	231.9	6.2
140°-150°	216.9	5.8
150°-160°	174.9	4.7
160°-170°	112.9	3.0
170°-180°	38.9	1.0
0°-30°	813.0	21.6
0°-40°	1284.1	34.1
0°-60°	2103.8	55.9
0°-90°	2512.3	66.8
90°-120°	256.3	6.8
90°-150°	922.1	24.5
90°-180°	1249.0	33.2
0°-180°	3761.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	0	3	7	8	9	3
95°	19	7	10	11	12	23
105°	91	92	67	16	13	96
115°	170	172	175	178	179	168
125°	240	242	243	244	245	214
135°	298	300	302	302	302	230
145°	344	346	347	348	348	216
155°	379	379	379	380	379	175
165°	400	399	399	401	399	113
175°	410	408	408	410	408	39
180°	410	410	410	410	410	



TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.4	15.8	14.1	12.5	10.8	10.2	10.3	10.5	10.7	10.8	10.8
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	5.7	5.5	5.3	5.1	4.9	5.2	5.8	6.5	7.1	7.7	8.2
95°	18.6	15.8	13.0	10.2	7.5	6.5	7.2	7.9	8.7	9.5	9.9
97.5°	37.3	36.1	34.8	33.6	32.3	29.3	24.4	19.5	14.6	9.8	10.3
100°	51.4	52.8	54.2	55.4	56.8	52.3	41.7	31.2	20.6	10.1	10.6
102.5°	67.5	68.4	69.4	70.4	71.4	66.1	54.6	43.0	31.5	20.1	18.3
105°	90.7	91.4	92.1	92.9	93.7	91.0	84.9	78.8	72.8	66.6	54.7
107.5°	115.1	115.7	116.3	116.9	117.5	118.3	119.2	120.2	121.1	122.1	113.3
110°	131.5	132.0	132.5	133.0	133.6	134.2	135.0	135.7	136.5	137.2	135.0



TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	147.5	148.0	148.4	149.0	149.6	150.3	151.1	151.8	152.6	152.6
115°	170.0	170.5	170.9	171.3	171.7	172.2	172.8	173.4	174.0	174.6	175.3
117.5°	192.4	193.0	193.4	193.9	194.4	194.8	195.1	195.4	195.8	196.0	196.6
120°	206.3	206.9	207.5	208.1	208.7	209.1	209.3	209.6	209.7	209.9	210.5
122.5°	220.4	220.9	221.4	221.9	222.4	222.7	223.0	223.3	223.5	223.8	224.2
125°	239.8	240.3	240.8	241.3	241.9	242.3	242.6	242.9	243.1	243.4	243.6
127.5°	258.5	259.1	259.6	260.1	260.6	261.1	261.4	261.7	262.1	262.3	262.6
130°	270.2	270.7	271.2	271.8	272.3	272.8	273.0	273.3	273.5	273.8	274.1
132.5°	281.4	281.9	282.5	283.0	283.5	283.9	284.1	284.4	284.6	284.8	285.1
135°	298.5	298.9	299.3	299.7	300.1	300.4	300.7	301.0	301.3	301.5	301.7
137.5°	313.1	313.6	314.1	314.6	315.1	315.5	315.6	315.7	315.9	316.1	316.4
140°	322.8	323.2	323.6	324.0	324.4	324.8	324.9	325.1	325.4	325.5	325.8
142.5°	331.8	332.3	332.6	333.0	333.5	333.7	334.0	334.2	334.3	334.6	334.8
145°	344.4	344.9	345.3	345.9	346.3	346.6	346.7	346.9	347.0	347.2	347.3
147.5°	356.3	356.6	356.9	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
150°	363.6	363.8	363.9	364.2	364.4	364.5	364.7	364.8	365.0	365.1	365.2
152.5°	370.1	370.2	370.3	370.4	370.5	370.7	370.7	370.7	370.8	370.9	371.2
155°	379.4	379.3	379.1	379.0	378.8	378.8	378.9	378.9	379.0	379.1	379.4
157.5°	386.6	386.6	386.6	386.5	386.5	386.5	386.4	386.3	386.2	386.2	386.6
160°	391.0	390.9	390.8	390.7	390.7	390.6	390.5	390.5	390.5	390.4	390.7
162.5°	395.1	394.9	394.8	394.6	394.4	394.3	394.2	394.2	394.1	394.0	394.4
165°	400.1	399.8	399.7	399.5	399.2	399.2	399.1	399.0	398.9	398.9	399.4
167.5°	404.0	403.7	403.5	403.2	402.9	402.8	402.8	402.8	402.8	402.8	403.3
170°	406.1	405.9	405.6	405.4	405.1	404.9	404.9	404.9	404.9	404.9	405.5
172.5°	407.6	407.3	407.0	406.7	406.3	406.2	406.2	406.3	406.4	406.4	407.0
175°	409.5	409.1	408.8	408.5	408.2	408.0	408.1	408.2	408.2	408.3	408.8
177.5°	410.0	409.7	409.5	409.2	408.9	408.8	408.9	408.9	409.0	409.1	409.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	10.6	10.5	10.4	10.3	10.2	10.0	9.9	9.7
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	8.7	9.1	9.6	9.8	9.8	9.9	10.0	10.1
95°	10.4	10.8	11.4	11.5	11.5	11.5	11.5	11.5
97.5°	10.8	11.5	12.0	12.2	12.3	12.4	12.5	12.6
100°	11.1	11.6	12.2	12.5	12.6	12.7	12.7	12.7
102.5°	16.7	15.0	13.3	12.6	12.7	12.7	12.9	13.0
105°	42.7	30.7	18.8	12.8	13.0	13.1	13.3	13.3
107.5°	104.6	95.8	87.0	78.1	69.1	60.1	51.1	42.0
110°	132.8	130.5	128.3	122.3	112.7	103.0	93.3	83.7



TEST NUMBER: P332303-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.7	152.7	152.7	151.7	149.6	147.7	145.6	143.5
115°	176.0	176.7	177.4	177.8	178.1	178.4	178.7	178.9
117.5°	197.2	197.7	198.2	198.5	198.5	198.6	198.7	198.7
120°	211.0	211.5	212.1	212.4	212.4	212.4	212.4	212.4
122.5°	224.5	225.0	225.3	225.5	225.6	225.7	225.7	225.8
125°	243.7	243.8	243.9	244.1	244.2	244.4	244.5	244.6
127.5°	262.8	263.0	263.3	263.3	263.1	263.0	262.9	262.8
130°	274.4	274.7	274.9	275.0	274.8	274.7	274.6	274.4
132.5°	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.2
135°	302.0	302.1	302.3	302.3	302.1	302.0	301.7	301.5
137.5°	316.7	317.0	317.4	317.5	317.3	317.2	317.0	316.9
140°	326.1	326.3	326.7	326.7	326.6	326.4	326.3	326.1
142.5°	335.0	335.2	335.4	335.4	335.3	335.0	334.8	334.7
145°	347.4	347.6	347.7	347.8	347.8	347.8	347.8	347.8
147.5°	358.5	358.7	358.9	358.8	358.4	358.1	357.8	357.5
150°	365.4	365.5	365.7	365.6	365.4	365.2	365.0	364.8
152.5°	371.4	371.7	372.0	371.9	371.6	371.3	370.9	370.7
155°	379.8	380.1	380.5	380.4	380.0	379.6	379.2	378.8
157.5°	387.0	387.4	387.9	387.8	387.3	386.8	386.2	385.6
160°	391.2	391.6	392.0	391.9	391.5	391.0	390.5	390.0
162.5°	394.9	395.4	395.8	395.9	395.5	395.0	394.6	394.2
165°	399.9	400.5	401.1	401.1	400.6	400.1	399.7	399.2
167.5°	403.8	404.4	404.9	404.9	404.4	403.8	403.3	402.8
170°	406.0	406.6	407.1	407.1	406.6	406.0	405.5	404.9
172.5°	407.5	408.0	408.5	408.5	407.9	407.3	406.7	406.1
175°	409.2	409.7	410.2	410.2	409.7	409.1	408.5	408.0
177.5°	409.9	410.4	410.8	410.7	410.2	409.7	409.1	408.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5

(END OF REPORT)