

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332310-935

Luminaire Tested: **S123RDIP-S775D585U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332310-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4245.1 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		65	65	65	59
1	100	96	92	89	93	90	87	84	78	76	74		68	66	64		58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61		60	57	54		51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52		53	49	46		46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45		48	43	40		41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39		43	38	35		37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34		39	34	31		34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30		36	31	27		31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27		33	28	25		29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24		30	25	22		26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	2.5
10°-20°	290.4	6.8
20°-30°	418.2	9.9
30°-40°	471.1	11.1
40°-50°	450.7	10.6
50°-60°	369.0	8.7
60°-70°	249.0	5.9
70°-80°	125.3	3.0
80°-90°	35.0	0.8
90°-100°	40.7	1.0
100°-110°	121.9	2.9
110°-120°	207.3	4.9
120°-130°	272.7	6.4
130°-140°	306.5	7.2
140°-150°	301.3	7.1
150°-160°	253.7	6.0
160°-170°	168.9	4.0
170°-180°	59.1	1.4
0°-30°	813.0	19.2
0°-40°	1284.1	30.2
0°-60°	2103.8	49.6
0°-90°	2513.0	59.2
90°-120°	370.0	8.7
90°-150°	1250.5	29.5
90°-180°	1732.0	40.8
0°-180°	4245.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	0	5	12	14	15	4
95°	29	32	36	38	38	33
105°	110	112	116	116	117	118
115°	209	210	209	210	209	206
125°	306	307	306	304	302	272
135°	396	399	399	397	396	305
145°	481	482	483	483	481	300
155°	550	551	551	553	550	253
165°	600	598	598	601	598	169
175°	624	622	622	624	621	59
180°	625	625	625	625	625	



TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.4	15.8	14.3	12.7	11.2	10.6	10.8	11.2	11.5	11.7	11.6
90°	0.5	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2
92.5°	11.9	12.7	13.3	14.1	14.9	15.7	16.4	17.2	18.1	18.9	19.2
95°	29.0	29.7	30.5	31.3	32.0	32.9	33.8	34.6	35.5	36.3	36.8
97.5°	51.5	52.0	52.6	53.2	53.7	54.3	54.9	55.6	56.2	56.9	57.3
100°	66.8	67.4	68.1	68.8	69.4	70.0	70.5	71.1	71.6	72.2	72.5
102.5°	84.5	84.9	85.2	85.7	86.0	86.6	87.3	88.1	88.8	89.5	89.8
105°	110.5	110.7	110.9	111.2	111.4	111.9	113.0	113.9	114.9	115.9	115.9
107.5°	140.8	140.9	141.0	141.1	141.3	141.5	141.9	142.3	142.8	143.1	143.4
110°	159.6	159.8	160.1	160.2	160.5	160.7	160.9	161.2	161.4	161.6	162.0



TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	179.3	179.5	179.6	179.8	179.9	179.9	179.9	180.0	180.0	180.6
115°	208.7	209.1	209.4	209.7	210.0	210.1	209.8	209.7	209.4	209.2	209.3
117.5°	238.4	238.6	238.8	239.0	239.3	239.2	238.9	238.7	238.4	238.1	238.1
120°	256.8	257.5	258.1	258.8	259.5	259.5	259.0	258.5	257.9	257.4	257.3
122.5°	276.1	276.6	277.1	277.5	278.0	278.1	277.8	277.6	277.2	277.0	276.7
125°	305.5	305.8	306.1	306.4	306.8	306.9	306.6	306.4	306.2	306.0	305.5
127.5°	332.6	333.3	334.0	334.7	335.4	335.6	335.4	335.1	334.8	334.7	334.1
130°	350.7	351.5	352.4	353.3	354.1	354.4	354.1	353.8	353.4	353.1	352.7
132.5°	368.7	369.6	370.5	371.3	372.2	372.6	372.3	372.0	371.8	371.6	371.0
135°	396.3	397.0	397.6	398.3	398.9	399.2	399.1	399.0	398.9	398.8	398.4
137.5°	421.9	422.4	422.9	423.5	424.0	424.5	424.7	425.0	425.3	425.6	425.2
140°	439.5	440.1	440.7	441.2	441.7	442.0	442.1	442.3	442.4	442.5	442.4
142.5°	455.6	456.2	456.8	457.3	457.8	458.2	458.4	458.6	458.8	459.0	458.9
145°	480.8	481.0	481.2	481.5	481.6	481.9	482.2	482.6	482.9	483.3	483.1
147.5°	502.8	503.2	503.6	503.9	504.4	504.7	505.1	505.3	505.7	505.9	505.9
150°	518.1	518.3	518.6	518.8	519.0	519.2	519.4	519.6	519.9	520.0	520.0
152.5°	530.7	531.0	531.3	531.6	531.9	532.1	532.3	532.4	532.5	532.6	532.8
155°	550.5	550.5	550.5	550.5	550.5	550.6	550.7	550.8	551.0	551.0	551.5
157.5°	567.4	567.3	567.1	567.1	566.9	566.9	567.0	567.1	567.1	567.2	567.7
160°	578.0	577.8	577.6	577.4	577.1	577.0	577.0	577.0	577.0	577.0	577.6
162.5°	587.5	587.1	586.9	586.5	586.3	586.2	586.3	586.3	586.4	586.5	587.0
165°	599.6	599.3	599.0	598.7	598.3	598.1	598.1	598.1	598.1	598.1	598.8
167.5°	609.3	608.9	608.5	608.0	607.6	607.4	607.5	607.6	607.7	607.8	608.5
170°	614.8	614.4	614.0	613.5	613.1	612.9	612.9	612.9	612.9	612.9	613.6
172.5°	619.1	618.7	618.3	617.9	617.4	617.3	617.3	617.3	617.3	617.3	617.9
175°	623.7	623.3	622.8	622.4	622.0	621.7	621.7	621.7	621.7	621.7	622.4
177.5°	625.6	625.3	624.9	624.5	624.1	624.0	624.0	624.0	624.0	624.0	624.5
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2



TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	11.6	11.5	11.5	11.4	11.2	11.1	11.0	10.8
90°	12.7	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	19.5	19.9	20.2	20.4	20.2	20.1	20.0	19.8
95°	37.2	37.6	38.1	38.3	38.3	38.3	38.3	38.3
97.5°	57.9	58.4	58.9	59.1	59.1	59.0	59.0	58.9
100°	72.8	73.2	73.5	73.8	74.0	74.2	74.4	74.6
102.5°	90.1	90.5	90.7	90.9	90.9	90.8	90.8	90.7
105°	115.9	115.9	115.9	116.0	116.2	116.4	116.7	116.9
107.5°	143.8	144.1	144.5	144.6	144.5	144.4	144.2	144.1
110°	162.5	162.9	163.3	163.4	163.2	163.0	162.8	162.6



TEST NUMBER: P332310-935

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	181.1	181.6	182.1	182.4	182.4	182.3	182.3	182.2
115°	209.4	209.6	209.7	209.7	209.6	209.4	209.3	209.2
117.5°	238.1	238.0	238.0	237.8	237.5	237.2	236.9	236.6
120°	257.1	257.0	256.9	256.8	256.5	256.3	256.1	255.9
122.5°	276.4	276.1	275.9	275.5	275.3	274.9	274.7	274.3
125°	305.1	304.6	304.2	303.8	303.3	302.9	302.5	302.0
127.5°	333.4	332.8	332.2	331.7	331.1	330.6	330.1	329.6
130°	352.2	351.8	351.4	350.8	350.0	349.2	348.4	347.7
132.5°	370.5	370.0	369.5	368.9	368.3	367.7	367.1	366.5
135°	397.9	397.4	397.0	396.7	396.5	396.2	396.1	395.8
137.5°	424.6	424.2	423.8	423.4	422.9	422.5	422.1	421.6
140°	442.3	442.1	442.0	441.6	440.8	440.1	439.3	438.6
142.5°	458.7	458.7	458.6	458.2	457.6	457.0	456.4	455.8
145°	483.0	482.9	482.8	482.5	482.1	481.6	481.2	480.8
147.5°	505.9	505.9	505.9	505.6	505.0	504.3	503.7	503.0
150°	520.0	520.0	520.0	519.8	519.1	518.4	517.8	517.1
152.5°	533.0	533.2	533.4	533.1	532.6	532.0	531.5	530.9
155°	551.9	552.3	552.8	552.6	551.8	551.0	550.4	549.6
157.5°	568.2	568.6	569.0	568.9	568.3	567.7	567.1	566.5
160°	578.2	578.7	579.2	579.3	578.9	578.4	578.0	577.6
162.5°	587.5	588.1	588.7	588.6	587.9	587.2	586.5	585.8
165°	599.5	600.1	600.8	600.7	599.9	599.2	598.5	597.7
167.5°	609.2	609.8	610.5	610.5	609.8	609.2	608.5	607.8
170°	614.4	615.2	616.0	616.0	615.2	614.4	613.6	612.9
172.5°	618.5	619.2	619.9	619.9	619.1	618.4	617.6	616.8
175°	623.0	623.7	624.4	624.3	623.5	622.8	622.0	621.2
177.5°	625.1	625.6	626.1	626.0	625.4	624.8	624.2	623.6
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2

(END OF REPORT)