

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332257-940

Luminaire Tested: **S123RDIP-S340D805U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332257-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D805U940-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3751.1 lumens  
Efficiency: N/A  
Efficacy: 120.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.3
10°-20°	133.9	3.6
20°-30°	192.7	5.1
30°-40°	217.1	5.8
40°-50°	207.7	5.5
50°-60°	170.1	4.5
60°-70°	114.8	3.1
70°-80°	57.7	1.5
80°-90°	17.9	0.5
90°-100°	191.7	5.1
100°-110°	542.7	14.5
110°-120°	533.9	14.2
120°-130°	425.8	11.4
130°-140°	335.7	9.0
140°-150°	250.6	6.7
150°-160°	174.7	4.7
160°-170°	102.6	2.7
170°-180°	33.4	0.9
0°-30°	374.7	10.0
0°-40°	591.8	15.8
0°-60°	969.6	25.8
0°-90°	1160.0	30.9
90°-120°	1268.2	33.8
90°-150°	2280.4	60.8
90°-180°	2591.0	69.1
0°-180°	3751.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	1	8	17	20	20	3
95°	24	77	413	121	81	26
105°	81	120	560	980	887	86
115°	143	178	429	940	1078	141
125°	199	235	400	725	850	176
135°	233	278	395	597	690	180
145°	266	304	390	490	539	166
155°	302	326	377	429	447	139
165°	330	339	361	383	390	93
175°	344	344	346	351	351	33
180°	344	344	344	344	344	



TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.3	7.8	7.2	6.8	6.2	6.2	6.5	7.0	7.4	7.8	7.6
90°	1.4	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8
92.5°	8.6	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9
95°	23.7	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4
97.5°	40.4	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5
100°	51.6	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5
102.5°	63.3	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2
105°	80.9	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6
107.5°	99.5	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2
110°	113.0	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3



TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.2	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6
115°	142.9	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4
117.5°	160.6	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7
120°	172.9	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1
122.5°	183.5	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2
125°	198.7	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7
127.5°	210.3	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3
130°	217.5	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5
132.5°	223.1	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2
135°	232.8	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7
137.5°	242.0	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5
140°	248.2	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5
142.5°	254.9	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0
145°	265.6	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1
147.5°	276.5	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2
150°	283.7	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3
152.5°	291.0	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8
155°	301.8	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1
157.5°	310.5	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6
160°	317.2	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5
162.5°	322.3	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5
165°	329.8	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7
167.5°	335.5	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2
170°	338.9	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2
172.5°	341.1	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3
175°	343.7	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9
177.5°	344.9	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	7.7	7.8	7.8	8.0	7.8	7.8	7.9	7.7
90°	17.4	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	58.7	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	251.0	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	625.6	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	822.0	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	887.2	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	906.3	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	851.4	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	799.0	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2





TEST NUMBER: P332257-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	747.1	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	678.3	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	628.6	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	602.4	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	581.8	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	554.2	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	530.3	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	515.2	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	501.2	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	482.4	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	465.3	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	455.2	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	445.8	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	434.4	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	425.0	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	418.3	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	412.1	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	403.0	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	393.2	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	387.6	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	380.9	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	372.3	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	364.7	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	359.7	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	355.3	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	349.3	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	345.5	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)