

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332007-840

Luminaire Tested: **S123DIP-S1000D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332007-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D365U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5419.5 lumens  
Efficiency: N/A  
Efficacy: 124.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	70	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	63	60	57	54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	55	52	49	46
4	79	67	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42	39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32	30
7	62	49	41	35	59	47	39	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	32	26	22	29	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.6	2.8
10°-20°	425.2	7.8
20°-30°	628.0	11.6
30°-40°	733.6	13.5
40°-50°	737.6	13.6
50°-60°	647.9	12.0
60°-70°	482.7	8.9
70°-80°	275.0	5.1
80°-90°	80.3	1.5
90°-100°	29.6	0.5
100°-110°	88.6	1.6
110°-120°	150.7	2.8
120°-130°	198.2	3.7
130°-140°	222.7	4.1
140°-150°	219.0	4.0
150°-160°	184.3	3.4
160°-170°	122.7	2.3
170°-180°	43.0	0.8
0°-30°	1203.8	22.2
0°-40°	1937.4	35.7
0°-60°	3322.8	61.3
0°-90°	4160.8	76.8
90°-120°	268.8	5.0
90°-150°	908.7	16.8
90°-180°	1259.0	23.2
0°-180°	5419.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	0	4	9	10	11	5
95°	21	24	26	28	28	24
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	219	198
135°	288	290	290	288	288	222
145°	349	350	351	351	349	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.7	28.1	27.5	27.0	26.4	26.1	26.1	26.0	26.0	26.0	25.8
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	8.7	9.2	9.7	10.3	10.8	11.3	11.9	12.5	13.1	13.7	13.9
95°	21.1	21.6	22.1	22.7	23.2	23.8	24.5	25.1	25.8	26.5	26.8
97.5°	37.4	37.8	38.3	38.7	39.1	39.5	40.0	40.4	40.9	41.3	41.7
100°	48.6	49.0	49.5	50.0	50.4	50.9	51.3	51.7	52.1	52.4	52.7
102.5°	61.4	61.7	61.9	62.2	62.5	62.9	63.4	64.0	64.5	65.0	65.2
105°	80.3	80.5	80.6	80.8	80.9	81.4	82.1	82.8	83.5	84.2	84.2
107.5°	102.3	102.4	102.5	102.6	102.7	102.8	103.1	103.4	103.7	104.0	104.2
110°	116.0	116.1	116.3	116.4	116.6	116.7	116.9	117.1	117.2	117.4	117.8



TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	130.4	130.5	130.6	130.7	130.7	130.8	130.8	130.8	130.9	131.2
115°	151.7	151.9	152.2	152.4	152.6	152.7	152.5	152.4	152.2	152.0	152.1
117.5°	173.2	173.4	173.6	173.7	173.9	173.8	173.6	173.4	173.2	173.0	173.0
120°	186.6	187.1	187.6	188.0	188.5	188.5	188.2	187.8	187.4	187.0	186.9
122.5°	200.7	201.0	201.4	201.7	202.1	202.1	201.9	201.7	201.5	201.3	201.1
125°	222.0	222.2	222.5	222.7	223.0	223.0	222.8	222.7	222.5	222.4	222.0
127.5°	241.7	242.2	242.7	243.2	243.7	243.9	243.7	243.5	243.4	243.2	242.8
130°	254.8	255.4	256.1	256.7	257.3	257.5	257.3	257.1	256.8	256.6	256.3
132.5°	267.9	268.6	269.2	269.8	270.4	270.7	270.5	270.3	270.1	270.0	269.6
135°	288.0	288.5	288.9	289.4	289.9	290.1	290.0	289.9	289.8	289.8	289.4
137.5°	306.6	307.0	307.3	307.7	308.1	308.4	308.6	308.8	309.0	309.2	308.9
140°	319.4	319.8	320.2	320.6	321.0	321.2	321.3	321.3	321.4	321.5	321.4
142.5°	331.1	331.5	331.9	332.3	332.6	333.0	333.2	333.3	333.4	333.6	333.5
145°	349.4	349.5	349.7	349.8	350.0	350.2	350.4	350.7	350.9	351.1	351.1
147.5°	365.4	365.7	366.0	366.3	366.5	366.8	367.0	367.2	367.4	367.7	367.7
150°	376.5	376.7	376.8	377.0	377.2	377.3	377.5	377.6	377.8	377.9	377.9
152.5°	385.7	385.9	386.1	386.3	386.6	386.7	386.8	386.9	387.0	387.1	387.2
155°	400.1	400.1	400.1	400.1	400.1	400.1	400.2	400.2	400.3	400.4	400.7
157.5°	412.3	412.2	412.1	412.0	411.9	411.9	412.0	412.0	412.1	412.2	412.5
160°	420.0	419.9	419.7	419.6	419.4	419.3	419.3	419.3	419.3	419.3	419.7
162.5°	426.9	426.7	426.5	426.3	426.0	426.0	426.0	426.1	426.2	426.2	426.6
165°	435.8	435.6	435.3	435.0	434.7	434.6	434.6	434.6	434.6	434.6	435.2
167.5°	442.8	442.5	442.2	441.8	441.5	441.4	441.5	441.5	441.6	441.7	442.1
170°	446.8	446.5	446.2	445.9	445.6	445.4	445.4	445.4	445.4	445.4	446.0
172.5°	450.0	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.2	452.9	452.6	452.3	452.0	451.8	451.8	451.8	451.8	451.8	452.3
177.5°	454.5	454.3	454.0	453.8	453.5	453.4	453.4	453.4	453.4	453.4	453.8
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	25.5	25.3	25.1	25.1	25.1	25.1	25.2	25.2
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.2	14.4	14.7	14.8	14.7	14.6	14.5	14.4
95°	27.1	27.4	27.7	27.9	27.9	27.9	27.9	27.9
97.5°	42.0	42.4	42.8	42.9	42.9	42.9	42.8	42.8
100°	52.9	53.2	53.4	53.6	53.7	53.9	54.1	54.2
102.5°	65.5	65.7	65.9	66.0	66.0	66.0	65.9	65.9
105°	84.2	84.2	84.2	84.3	84.4	84.6	84.8	84.9
107.5°	104.5	104.7	105.0	105.1	105.0	104.9	104.8	104.7
110°	118.1	118.4	118.7	118.8	118.6	118.5	118.3	118.2





TEST NUMBER: P332007-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.6	132.0	132.4	132.5	132.5	132.5	132.4	132.4
115°	152.2	152.3	152.4	152.4	152.3	152.2	152.1	152.0
117.5°	173.0	173.0	173.0	172.8	172.6	172.4	172.2	172.0
120°	186.8	186.7	186.7	186.5	186.4	186.2	186.1	185.9
122.5°	200.9	200.7	200.5	200.3	200.1	199.8	199.5	199.3
125°	221.7	221.4	221.1	220.8	220.5	220.2	219.7	219.4
127.5°	242.3	241.9	241.4	241.0	240.7	240.2	239.9	239.5
130°	256.0	255.6	255.3	254.9	254.4	253.8	253.3	252.7
132.5°	269.2	268.8	268.5	268.1	267.6	267.2	266.8	266.4
135°	289.1	288.8	288.5	288.3	288.1	287.9	287.8	287.6
137.5°	308.6	308.3	307.9	307.6	307.3	307.0	306.7	306.4
140°	321.3	321.3	321.2	320.9	320.3	319.8	319.2	318.7
142.5°	333.4	333.3	333.3	333.0	332.5	332.1	331.6	331.2
145°	351.0	350.9	350.8	350.6	350.3	350.0	349.7	349.4
147.5°	367.7	367.7	367.7	367.4	367.0	366.5	366.0	365.5
150°	377.9	377.9	377.9	377.7	377.2	376.8	376.3	375.8
152.5°	387.3	387.5	387.6	387.4	387.0	386.6	386.2	385.8
155°	401.0	401.3	401.7	401.5	401.0	400.4	399.9	399.3
157.5°	412.8	413.2	413.5	413.4	413.0	412.6	412.1	411.7
160°	420.1	420.5	420.9	420.9	420.6	420.3	420.0	419.7
162.5°	427.0	427.4	427.8	427.7	427.2	426.7	426.2	425.7
165°	435.7	436.1	436.6	436.6	436.0	435.5	434.8	434.3
167.5°	442.6	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.5	447.1	447.6	447.6	447.1	446.5	446.0	445.4
172.5°	449.5	450.0	450.5	450.5	449.9	449.4	448.8	448.3
175°	452.7	453.2	453.7	453.6	453.1	452.5	452.0	451.4
177.5°	454.2	454.5	454.9	454.9	454.5	454.0	453.6	453.1
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

(END OF REPORT)