

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332009-840

Luminaire Tested: **S123DIP-S1000D585U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332009-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D585U840-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6647.3 lumens  
Efficiency: N/A  
Efficacy: 136.2 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	50	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	51	46	50	45	42	44	40	38	34
5	71	60	52	45	67	57	49	44	50	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	43	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15268	15268	15268	15268
5°	18208	15333	13588	15333
10°	22789	15255	12273	15255
15°	27952	15133	11426	15133
20°	33298	14940	10879	14940
25°	35357	14707	10757	14707
30°	30305	14537	10813	14537
35°	21077	14294	10926	14294
40°	15874	14011	10893	14011
45°	13181	13589	10753	13589
50°	11807	12727	10655	12727
55°	11038	11798	10524	11798
60°	10355	10828	10415	10828
65°	9732	9872	10083	9872
70°	9127	8781	9602	8781
75°	8172	7690	8804	7690
80°	7153	6304	7581	6304
85°	5595	4582	5088	4582



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.7	2.1
10°-20°	448.0	6.7
20°-30°	751.9	11.3
30°-40°	851.4	12.8
40°-50°	763.5	11.5
50°-60°	616.1	9.3
60°-70°	429.4	6.5
70°-80°	225.7	3.4
80°-90°	57.4	0.9
90°-100°	28.2	0.4
100°-110°	134.3	2.0
110°-120°	322.7	4.9
120°-130°	410.9	6.2
130°-140°	439.0	6.6
140°-150°	410.5	6.2
150°-160°	331.2	5.0
160°-170°	213.7	3.2
170°-180°	73.7	1.1
0°-30°	1339.7	20.2
0°-40°	2191.1	33.0
0°-60°	3570.7	53.7
0°-90°	4283.1	64.4
90°-120°	485.2	7.3
90°-150°	1745.7	26.3
90°-180°	2364.0	35.6
0°-180°	6647.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1685	1419	1258	1419	1685	175
15°	2508	1358	1025	1358	2508	724
25°	2977	1238	906	1238	2977	1306
35°	1604	1088	832	1088	1604	1042
45°	866	893	706	893	866	685
55°	588	629	561	629	588	528
65°	382	388	396	388	382	380
75°	196	185	212	185	196	210
85°	45	37	41	37	45	54
90°	17	1	17	1	17	10
95°	22	35	22	35	22	18
105°	25	172	25	172	25	58
115°	339	322	339	322	339	313
125°	463	454	463	454	463	414
135°	571	565	571	565	571	440
145°	658	652	658	652	658	411
155°	717	718	717	718	717	331
165°	756	757	756	757	756	213
175°	772	775	772	775	772	74
180°	775	775	775	775	775	



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1505.2	1504.2	1501.4	1503.6	1499.2	1493.2	1492.6	1487.1	1471.2	1470.1	1465.7
5°	1685.1	1679.5	1678.8	1678.2	1668.5	1655.5	1630.7	1628.7	1595.7	1579.2	1559.2
7.5°	1917.8	1920.8	1910.7	1901.9	1872.5	1853.1	1826.5	1792.6	1752.1	1711.0	1683.6
10°	2085.0	2107.7	2079.5	2060.2	2042.4	2008.7	1969.5	1920.8	1872.0	1814.9	1771.6
12.5°	2264.2	2275.3	2269.7	2251.6	2223.8	2172.5	2103.1	2049.4	2004.5	1909.5	1871.1
15°	2508.3	2550.2	2523.5	2461.5	2463.0	2414.2	2323.4	2223.8	2170.9	2087.7	1974.4
17.5°	2768.3	2773.6	2762.2	2710.6	2676.2	2609.2	2525.5	2429.9	2322.8	2222.1	2101.9
20°	2906.9	2902.8	2878.7	2851.9	2792.8	2740.6	2649.2	2542.6	2405.2	2306.2	2175.0
22.5°	2983.8	2977.0	2965.6	2943.2	2894.0	2837.9	2755.8	2639.4	2508.6	2372.3	2220.6
25°	2977.0	2985.9	2987.3	2981.1	2964.0	2930.2	2865.6	2772.9	2642.3	2467.1	2309.1
27.5°	2707.5	2720.3	2756.9	2789.6	2825.9	2863.1	2858.1	2812.1	2715.4	2564.0	2370.9
30°	2438.2	2410.7	2478.7	2564.7	2623.0	2726.1	2783.9	2787.3	2733.0	2603.1	2414.8
32.5°	2064.4	2094.6	2124.7	2230.4	2358.0	2473.8	2588.7	2681.2	2691.8	2605.4	2440.6
35°	1604.0	1641.7	1696.7	1751.7	1889.2	2007.3	2209.4	2385.3	2525.5	2544.1	2443.0
37.5°	1292.5	1311.2	1345.9	1401.1	1491.0	1631.1	1787.5	2009.8	2212.9	2364.0	2370.6
40°	1129.7	1135.3	1174.5	1216.4	1289.2	1404.6	1545.5	1742.0	1985.3	2196.4	2284.3
42.5°	1007.7	1019.8	1036.4	1076.7	1134.7	1221.5	1352.5	1515.0	1738.0	1980.7	2152.8
45°	865.9	879.6	889.9	916.8	958.0	1016.3	1107.8	1256.2	1425.9	1676.8	1908.3
47.5°	772.1	773.3	780.9	801.1	829.2	873.0	937.7	1033.0	1188.8	1392.3	1630.0
50°	705.1	716.1	718.8	734.6	756.6	788.9	842.5	923.6	1051.5	1230.1	1448.7
52.5°	657.8	661.1	668.8	680.2	699.4	724.6	771.0	834.6	934.8	1087.1	1288.1
55°	588.2	588.2	595.8	604.7	615.7	638.4	669.3	716.1	792.3	910.6	1076.8
57.5°	523.9	527.4	532.7	535.4	544.8	559.8	585.6	621.1	678.0	769.0	901.2
60°	481.0	487.3	486.6	492.0	500.3	512.0	533.9	562.8	613.7	686.5	797.9
62.5°	443.6	443.2	443.1	449.7	458.0	469.1	483.4	508.4	551.6	616.1	710.9
65°	382.1	380.7	385.6	389.6	392.4	400.6	411.6	433.6	462.5	510.6	584.1
67.5°	327.4	323.4	326.0	327.4	332.0	338.5	348.8	362.4	385.4	424.0	479.4
70°	290.0	286.6	285.9	287.2	291.3	296.2	303.8	316.8	338.1	369.0	409.6
72.5°	251.6	249.1	249.0	252.1	254.0	257.1	262.5	274.5	291.3	314.6	352.4
75°	196.5	196.5	196.5	197.2	199.2	202.1	206.1	212.4	225.4	241.9	267.3
77.5°	147.3	147.2	146.3	146.2	149.3	150.5	151.5	157.2	164.5	175.6	194.2
80°	115.4	112.0	113.4	115.4	116.8	117.5	119.6	121.0	127.1	133.3	146.3
82.5°	85.7	82.9	83.1	86.3	86.5	87.3	89.4	91.3	93.6	99.3	106.2
85°	45.3	45.3	46.0	46.0	46.8	46.0	48.1	48.8	48.8	52.2	56.4
87.5°	20.0	18.8	19.3	19.8	19.2	19.7	20.1	20.6	21.0	21.4	21.7
90°	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8	14.3	13.8	12.1
92.5°	19.1	19.0	18.8	18.7	18.5	18.0	17.2	16.4	15.6	14.7	13.5
95°	21.9	21.9	21.9	21.9	21.9	21.4	20.5	19.7	18.8	17.9	16.5
97.5°	23.7	23.6	23.4	23.3	23.2	22.6	21.6	20.6	19.6	18.6	27.8
100°	24.2	24.0	23.9	23.8	23.6	23.1	22.1	21.0	20.0	19.0	39.0
102.5°	24.6	24.4	24.2	23.9	23.7	25.2	28.4	31.5	34.7	37.9	59.7
105°	25.3	25.0	24.8	24.5	24.3	35.5	58.2	80.8	103.5	126.1	137.6
107.5°	79.6	96.6	113.7	130.8	147.9	164.7	181.4	197.9	214.6	231.2	229.3
110°	158.3	176.7	195.0	213.3	231.6	242.9	247.1	251.4	255.5	259.7	258.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.8	275.6	279.4	283.4	287.2	289.1	289.0	288.9	288.9	288.8	287.4
115°	338.7	338.2	337.7	337.1	336.6	335.8	334.5	333.2	331.9	330.6	329.4
117.5°	376.3	376.2	376.1	376.0	375.9	375.3	374.3	373.2	372.2	371.1	370.6
120°	402.0	402.0	402.0	402.0	402.0	401.5	400.5	399.5	398.5	397.4	397.1
122.5°	427.4	427.3	427.2	427.1	427.0	426.6	425.9	425.2	424.4	423.7	423.2
125°	463.1	462.8	462.6	462.3	462.1	461.8	461.5	461.3	461.0	460.8	460.3
127.5°	497.5	497.7	498.0	498.2	498.5	498.4	498.0	497.6	497.2	496.8	496.1
130°	519.6	519.8	520.1	520.3	520.6	520.4	519.9	519.4	518.9	518.4	517.9
132.5°	539.8	540.2	540.5	540.9	541.3	541.2	540.7	540.2	539.7	539.2	538.7
135°	570.8	571.2	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8	570.3
137.5°	600.0	600.2	600.5	600.7	601.0	600.8	600.2	599.6	599.0	598.3	598.0
140°	617.4	617.7	617.9	618.2	618.4	618.3	617.8	617.3	616.8	616.3	615.9
142.5°	633.6	633.9	634.3	634.7	635.0	635.0	634.6	634.2	633.8	633.4	633.0
145°	658.3	658.3	658.3	658.3	658.3	658.2	657.9	657.7	657.4	657.2	656.9
147.5°	676.8	677.4	677.9	678.5	679.1	679.3	679.0	678.8	678.5	678.3	678.0
150°	690.6	690.9	691.4	691.8	692.2	692.2	692.0	691.7	691.5	691.2	690.9
152.5°	701.7	702.3	702.9	703.5	704.0	704.1	703.6	703.2	702.7	702.3	702.1
155°	717.1	717.9	718.6	719.4	720.1	720.2	719.6	718.9	718.3	717.7	717.5
157.5°	730.1	731.1	732.2	733.1	734.1	734.3	733.5	732.7	732.0	731.1	731.2
160°	738.4	739.3	740.2	741.1	741.9	742.0	741.2	740.5	739.7	739.0	739.1
162.5°	746.3	747.0	747.8	748.6	749.4	749.4	748.5	747.6	746.8	745.9	746.0
165°	755.7	756.6	757.5	758.4	759.3	759.2	758.2	757.2	756.2	755.1	755.3
167.5°	762.4	763.6	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4	762.4
170°	766.6	767.7	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6	766.6
172.5°	768.9	770.0	771.2	772.3	773.5	773.5	772.4	771.4	770.4	769.4	769.3
175°	772.3	773.5	774.5	775.5	776.5	776.6	775.7	774.8	773.9	773.0	772.8
177.5°	773.5	774.5	775.5	776.5	777.5	777.6	776.8	776.0	775.2	774.4	774.3
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1462.4	1457.9	1453.6	1445.9	1439.3	1430.0	1427.1	1423.9	1414.0	1405.2	1398.6
5°	1551.7	1535.2	1511.2	1489.1	1471.3	1447.2	1433.5	1419.1	1398.5	1379.9	1364.8
7.5°	1645.2	1612.8	1575.4	1534.9	1497.3	1461.0	1431.7	1405.6	1376.7	1349.4	1328.1
10°	1719.4	1672.6	1620.4	1564.1	1516.0	1469.3	1430.1	1395.7	1358.6	1326.3	1299.5
12.5°	1804.0	1734.7	1662.7	1594.3	1537.4	1472.6	1425.1	1381.4	1339.4	1300.5	1270.4
15°	1904.2	1816.2	1731.1	1636.9	1550.3	1469.3	1412.9	1358.0	1309.1	1269.3	1230.8
17.5°	1995.5	1895.8	1783.5	1669.1	1564.6	1468.4	1389.6	1327.4	1266.4	1217.6	1179.2
20°	2047.2	1933.8	1806.6	1687.8	1572.4	1465.1	1378.6	1304.3	1238.3	1186.8	1143.5
22.5°	2091.7	1959.0	1827.6	1700.4	1571.8	1456.3	1358.2	1281.8	1210.3	1159.8	1113.8
25°	2137.9	1979.1	1847.2	1698.1	1554.5	1434.9	1324.9	1238.3	1166.9	1107.8	1060.4
27.5°	2177.5	1977.8	1821.2	1660.8	1527.2	1407.3	1290.0	1197.1	1121.3	1057.0	1009.0
30°	2203.8	1980.5	1794.3	1635.6	1500.9	1377.2	1263.0	1169.6	1089.9	1024.6	979.3
32.5°	2220.4	1978.8	1769.6	1600.3	1459.1	1349.7	1234.0	1137.2	1055.3	991.1	947.4
35°	2230.0	1966.8	1727.0	1527.6	1391.6	1285.1	1188.2	1087.8	1002.0	942.2	892.7
37.5°	2210.7	1941.4	1677.5	1457.5	1308.6	1203.7	1122.2	1036.7	954.5	888.7	846.1
40°	2180.5	1924.9	1639.0	1408.1	1251.4	1150.3	1081.0	997.1	916.0	853.5	813.6
42.5°	2122.7	1891.3	1596.7	1353.1	1192.0	1091.0	1027.1	957.0	880.3	821.6	781.7
45°	1981.9	1818.4	1533.2	1270.6	1104.3	999.9	943.5	892.7	823.2	766.2	731.8
47.5°	1786.5	1708.5	1441.4	1183.7	1012.8	912.3	853.7	812.8	762.1	716.1	683.1
50°	1650.6	1618.4	1379.2	1124.3	951.8	853.5	797.2	760.0	723.7	677.6	647.3
52.5°	1494.0	1513.9	1306.7	1062.7	889.7	793.0	740.0	710.5	677.4	639.6	613.3
55°	1273.4	1345.5	1181.3	959.4	797.2	705.1	654.9	628.7	609.6	581.4	558.7
57.5°	1066.8	1158.6	1045.8	852.8	706.3	626.8	578.8	550.3	538.0	523.2	505.3
60°	944.2	1034.9	949.1	781.3	645.3	569.7	527.0	503.0	490.7	480.4	465.2
62.5°	834.9	926.7	854.4	708.8	585.3	515.2	478.2	454.6	445.0	439.7	426.8
65°	684.5	763.5	715.4	595.8	499.6	437.8	404.0	387.6	378.7	376.6	368.3
67.5°	557.0	617.2	582.2	494.2	418.5	365.1	336.5	322.4	315.6	314.9	308.7
70°	473.5	529.9	503.0	423.3	358.0	316.1	291.3	279.0	274.9	274.2	270.7
72.5°	408.6	447.9	426.6	360.1	309.6	271.6	253.5	240.5	235.8	236.8	234.5
75°	302.4	331.9	319.5	273.5	233.0	208.2	193.1	184.9	180.8	182.8	180.1
77.5°	217.5	236.3	225.1	193.3	168.2	150.4	139.3	134.1	130.5	130.3	129.1
80°	164.2	175.2	169.1	149.8	129.2	114.1	105.1	101.7	99.7	99.0	98.3
82.5°	116.9	126.3	119.1	105.8	91.8	82.7	77.7	73.1	71.6	72.0	71.3
85°	59.1	62.5	59.8	51.5	46.0	41.9	39.2	37.1	35.7	36.5	35.0
87.5°	22.4	22.6	20.7	18.2	16.9	14.9	14.6	13.3	12.4	12.7	12.4
90°	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.2	11.0	9.7	9.3	9.6	10.0	10.4	10.7	10.4	10.0	9.6
95°	15.0	13.6	12.2	14.1	19.4	24.6	29.9	35.1	29.9	24.6	19.4
97.5°	37.0	46.2	55.4	61.2	63.5	65.9	68.3	70.6	68.3	65.9	63.5
100°	59.0	78.9	98.9	107.6	105.0	102.5	99.9	97.4	99.9	102.5	105.0
102.5°	81.5	103.3	125.1	135.1	133.3	131.5	129.6	127.7	129.6	131.5	133.3
105°	149.2	160.7	172.2	177.2	175.8	174.5	173.1	171.7	173.1	174.5	175.8
107.5°	227.5	225.7	223.9	222.5	221.4	220.3	219.0	217.9	219.0	220.3	221.4
110°	256.9	255.5	254.2	252.9	251.9	250.9	249.8	248.8	249.8	250.9	251.9





TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	286.0	284.6	283.2	282.0	281.0	280.1	279.2	278.3	279.2	280.1	281.0
115°	328.3	327.2	326.0	325.1	324.3	323.5	322.8	321.9	322.8	323.5	324.3
117.5°	370.0	369.4	368.8	368.0	367.1	366.2	365.2	364.3	365.2	366.2	367.1
120°	396.7	396.3	395.9	395.2	393.9	392.8	391.6	390.5	391.6	392.8	393.9
122.5°	422.7	422.2	421.7	421.0	420.1	419.1	418.2	417.3	418.2	419.1	420.1
125°	459.8	459.3	458.8	458.0	457.0	456.0	454.9	453.8	454.9	456.0	457.0
127.5°	495.5	494.8	494.2	493.4	492.4	491.4	490.4	489.4	490.4	491.4	492.4
130°	517.4	516.8	516.3	515.5	514.5	513.5	512.5	511.5	512.5	513.5	514.5
132.5°	538.3	537.9	537.5	536.7	535.7	534.7	533.7	532.7	533.7	534.7	535.7
135°	569.8	569.3	568.8	568.2	567.3	566.5	565.8	565.0	565.8	566.5	567.3
137.5°	597.7	597.4	597.2	596.5	595.6	594.6	593.7	592.7	593.7	594.6	595.6
140°	615.5	615.1	614.8	614.2	613.4	612.7	611.9	611.1	611.9	612.7	613.4
142.5°	632.6	632.2	631.8	631.3	630.5	629.8	628.9	628.1	628.9	629.8	630.5
145°	656.7	656.4	656.2	655.6	654.7	653.8	652.9	652.0	652.9	653.8	654.7
147.5°	677.7	677.5	677.2	676.8	676.2	675.7	675.1	674.5	675.1	675.7	676.2
150°	690.6	690.4	690.1	689.8	689.4	689.0	688.7	688.3	688.7	689.0	689.4
152.5°	702.0	701.8	701.7	701.5	701.3	701.0	700.9	700.7	700.9	701.0	701.3
155°	717.4	717.3	717.2	717.2	717.5	717.7	718.0	718.2	718.0	717.7	717.5
157.5°	731.4	731.5	731.6	731.7	731.7	731.7	731.8	731.8	731.8	731.7	731.7
160°	739.2	739.3	739.5	739.6	739.7	739.9	740.0	740.1	740.0	739.9	739.7
162.5°	746.2	746.3	746.4	746.6	747.0	747.3	747.6	748.0	747.6	747.3	747.0
165°	755.4	755.5	755.6	755.9	756.3	756.7	757.0	757.4	757.0	756.7	756.3
167.5°	762.4	762.4	762.4	762.8	763.3	763.8	764.3	764.8	764.3	763.8	763.3
170°	766.6	766.6	766.6	766.9	767.4	767.9	768.4	768.9	768.4	767.9	767.4
172.5°	769.2	769.1	769.0	769.2	769.8	770.4	771.1	771.7	771.1	770.4	769.8
175°	772.7	772.5	772.4	772.7	773.4	774.0	774.7	775.3	774.7	774.0	773.4
177.5°	774.2	774.1	774.0	774.2	774.7	775.2	775.7	776.2	775.7	775.2	774.7
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1394.7	1390.9	1385.4	1377.2	1370.6	1360.1	1360.1	1361.8	1361.8	1361.2	1360.1
5°	1352.4	1342.1	1329.8	1315.3	1300.2	1285.1	1282.3	1276.9	1272.7	1269.9	1266.5
7.5°	1307.8	1289.5	1271.4	1251.2	1232.8	1217.6	1207.0	1198.2	1192.5	1186.5	1182.1
10°	1277.5	1254.9	1233.6	1212.2	1188.8	1170.3	1158.6	1150.3	1144.2	1138.7	1136.0
12.5°	1241.7	1215.8	1192.3	1172.0	1146.5	1127.4	1116.3	1112.5	1105.2	1093.6	1087.5
15°	1189.5	1165.5	1137.3	1106.4	1094.0	1070.7	1057.6	1051.5	1047.3	1038.3	1035.6
17.5°	1144.9	1113.4	1081.8	1058.7	1035.7	1016.8	1009.5	1001.8	996.3	989.1	986.8
20°	1109.1	1081.0	1052.1	1027.3	1003.3	982.7	976.5	971.0	965.5	962.1	959.4
22.5°	1072.9	1044.7	1020.8	997.6	972.0	958.5	951.8	945.7	941.9	939.6	936.8
25°	1021.9	997.1	970.4	949.7	929.1	920.2	916.0	912.6	909.9	906.5	905.7
27.5°	976.2	949.3	927.6	908.4	893.5	886.1	882.1	880.4	881.0	882.2	883.0
30°	942.2	917.5	899.6	883.0	869.3	862.4	861.7	861.7	864.5	865.2	866.6
32.5°	910.8	890.5	872.6	856.7	846.3	841.5	844.1	844.1	846.4	848.2	850.6
35°	865.2	847.3	833.5	819.8	810.9	812.9	814.4	815.7	819.1	823.2	826.1
37.5°	821.6	806.1	791.8	781.0	777.0	780.6	784.0	786.9	790.8	794.0	796.8
40°	790.3	778.6	764.9	755.3	756.6	758.7	761.4	764.9	768.3	770.3	773.2
42.5°	761.1	748.9	738.5	730.5	732.5	735.1	736.7	738.5	742.5	746.2	747.8
45°	716.8	707.1	697.5	692.7	694.1	695.5	696.8	698.9	702.4	705.1	705.8
47.5°	666.8	660.1	653.7	649.0	651.2	650.7	652.5	656.8	657.9	659.5	663.4
50°	635.0	628.7	621.3	619.9	619.9	619.9	620.6	626.0	626.0	628.7	631.6
52.5°	599.8	595.8	591.0	588.5	587.4	587.4	590.3	593.1	594.2	598.0	600.8
55°	547.8	543.6	539.5	537.3	536.0	537.3	542.9	544.2	547.8	549.8	551.8
57.5°	493.4	490.3	487.0	485.8	485.5	487.4	490.4	494.5	495.3	501.7	504.8
60°	457.7	452.8	450.1	450.1	448.8	454.9	453.5	460.4	461.8	466.0	470.7
62.5°	420.8	414.3	413.2	413.2	415.3	417.0	418.9	421.9	425.6	430.7	434.4
65°	361.4	358.0	362.8	362.1	360.8	364.9	364.9	368.3	372.4	377.3	384.9
67.5°	305.3	303.5	303.9	303.9	306.0	308.3	310.2	313.3	318.2	323.3	328.2
70°	267.3	269.4	266.0	268.7	270.7	271.5	272.9	276.9	282.5	285.9	291.3
72.5°	230.5	230.4	230.8	231.9	233.9	235.2	236.5	241.3	247.2	250.1	254.6
75°	177.3	176.6	178.6	178.6	182.1	183.5	184.9	186.9	192.4	196.5	200.0
77.5°	129.5	130.3	129.9	132.2	131.3	131.5	135.8	137.8	138.5	146.5	148.3
80°	97.6	99.0	99.7	100.4	101.0	99.7	104.4	106.5	106.5	111.3	114.7
82.5°	70.1	70.9	72.7	73.4	73.5	74.9	75.3	76.9	78.5	80.6	85.0
85°	35.0	37.1	37.8	37.1	37.8	36.5	38.5	39.2	39.9	39.9	39.9
87.5°	12.1	13.0	12.7	13.6	13.4	14.3	14.4	13.4	13.5	15.2	13.1
90°	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8	15.3	15.9	16.3
92.5°	9.3	9.7	11.0	12.2	13.5	14.7	15.6	16.4	17.2	18.0	18.5
95°	14.1	12.2	13.6	15.0	16.5	17.9	18.8	19.7	20.5	21.4	21.9
97.5°	61.2	55.4	46.2	37.0	27.8	18.6	19.6	20.6	21.6	22.6	23.2
100°	107.6	98.9	78.9	59.0	39.0	19.0	20.0	21.0	22.1	23.1	23.6
102.5°	135.1	125.1	103.3	81.5	59.7	37.9	34.7	31.5	28.4	25.2	23.7
105°	177.2	172.2	160.7	149.2	137.6	126.1	103.5	80.8	58.2	35.5	24.3
107.5°	222.5	223.9	225.7	227.5	229.3	231.2	214.6	197.9	181.4	164.7	147.9
110°	252.9	254.2	255.5	256.9	258.3	259.7	255.5	251.4	247.1	242.9	231.6



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	282.0	283.2	284.6	286.0	287.4	288.8	288.9	288.9	289.0	289.1	287.2
115°	325.1	326.0	327.2	328.3	329.4	330.6	331.9	333.2	334.5	335.8	336.6
117.5°	368.0	368.8	369.4	370.0	370.6	371.1	372.2	373.2	374.3	375.3	375.9
120°	395.2	395.9	396.3	396.7	397.1	397.4	398.5	399.5	400.5	401.5	402.0
122.5°	421.0	421.7	422.2	422.7	423.2	423.7	424.4	425.2	425.9	426.6	427.0
125°	458.0	458.8	459.3	459.8	460.3	460.8	461.0	461.3	461.5	461.8	462.1
127.5°	493.4	494.2	494.8	495.5	496.1	496.8	497.2	497.6	498.0	498.4	498.5
130°	515.5	516.3	516.8	517.4	517.9	518.4	518.9	519.4	519.9	520.4	520.6
132.5°	536.7	537.5	537.9	538.3	538.7	539.2	539.7	540.2	540.7	541.2	541.3
135°	568.2	568.8	569.3	569.8	570.3	570.8	571.2	571.6	572.0	572.3	572.3
137.5°	596.5	597.2	597.4	597.7	598.0	598.3	599.0	599.6	600.2	600.8	601.0
140°	614.2	614.8	615.1	615.5	615.9	616.3	616.8	617.3	617.8	618.3	618.4
142.5°	631.3	631.8	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.0
145°	655.6	656.2	656.4	656.7	656.9	657.2	657.4	657.7	657.9	658.2	658.3
147.5°	676.8	677.2	677.5	677.7	678.0	678.3	678.5	678.8	679.0	679.3	679.1
150°	689.8	690.1	690.4	690.6	690.9	691.2	691.5	691.7	692.0	692.2	692.2
152.5°	701.5	701.7	701.8	702.0	702.1	702.3	702.7	703.2	703.6	704.1	704.0
155°	717.2	717.2	717.3	717.4	717.5	717.7	718.3	718.9	719.6	720.2	720.1
157.5°	731.7	731.6	731.5	731.4	731.2	731.1	732.0	732.7	733.5	734.3	734.1
160°	739.6	739.5	739.3	739.2	739.1	739.0	739.7	740.5	741.2	742.0	741.9
162.5°	746.6	746.4	746.3	746.2	746.0	745.9	746.8	747.6	748.5	749.4	749.4
165°	755.9	755.6	755.5	755.4	755.3	755.1	756.2	757.2	758.2	759.2	759.3
167.5°	762.8	762.4	762.4	762.4	762.4	762.4	763.6	764.6	765.6	766.6	766.6
170°	766.9	766.6	766.6	766.6	766.6	766.6	767.7	768.7	769.7	770.7	770.7
172.5°	769.2	769.0	769.1	769.2	769.3	769.4	770.4	771.4	772.4	773.5	773.5
175°	772.7	772.4	772.5	772.7	772.8	773.0	773.9	774.8	775.7	776.6	776.5
177.5°	774.2	774.0	774.1	774.2	774.3	774.4	775.2	776.0	776.8	777.6	777.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1356.2	1355.7	1359.6	1356.9	1359.6	1355.7	1356.2	1360.1	1361.2	1361.8	1361.8
5°	1262.4	1264.5	1257.6	1257.6	1257.6	1264.5	1262.4	1266.5	1269.9	1272.7	1276.9
7.5°	1178.8	1175.8	1176.1	1172.4	1176.1	1175.8	1178.8	1182.1	1186.5	1192.5	1198.2
10°	1127.7	1123.6	1122.2	1122.9	1122.2	1123.6	1127.7	1136.0	1138.7	1144.2	1150.3
12.5°	1085.4	1084.6	1075.5	1075.6	1075.5	1084.6	1085.4	1087.5	1093.6	1105.2	1112.5
15°	1035.6	1022.6	1021.2	1025.3	1021.2	1022.6	1035.6	1035.6	1038.3	1047.3	1051.5
17.5°	985.7	978.9	979.3	977.2	979.3	978.9	985.7	986.8	989.1	996.3	1001.8
20°	959.4	955.2	954.5	949.7	954.5	955.2	959.4	959.4	962.1	965.5	971.0
22.5°	935.1	933.8	934.2	928.9	934.2	933.8	935.1	936.8	939.6	941.9	945.7
25°	905.0	908.5	905.7	905.7	905.7	908.5	905.0	905.7	906.5	909.9	912.6
27.5°	884.7	884.5	883.2	883.2	883.2	884.5	884.7	883.0	882.2	881.0	880.4
30°	869.3	868.6	870.0	870.0	870.0	868.6	869.3	866.6	865.2	864.5	861.7
32.5°	853.9	854.9	855.2	855.7	855.2	854.9	853.9	850.6	848.2	846.4	844.1
35°	830.1	830.8	832.9	831.5	832.9	830.8	830.1	826.1	823.2	819.1	815.7
37.5°	798.0	801.1	800.4	801.5	800.4	801.1	798.0	796.8	794.0	790.8	786.9
40°	773.8	775.9	775.2	775.2	775.2	775.9	773.8	773.2	770.3	768.3	764.9
42.5°	749.0	750.5	748.8	747.7	748.8	750.5	749.0	747.8	746.2	742.5	738.5
45°	708.5	707.1	709.2	706.4	709.2	707.1	708.5	705.8	705.1	702.4	698.9
47.5°	663.2	664.5	665.1	667.1	665.1	664.5	663.2	663.4	659.5	657.9	656.8
50°	632.9	637.0	637.0	636.3	637.0	637.0	632.9	631.6	628.7	626.0	626.0
52.5°	603.2	605.1	607.9	607.7	607.9	605.1	603.2	600.8	598.0	594.2	593.1
55°	557.3	558.7	560.1	560.8	560.1	558.7	557.3	551.8	549.8	547.8	544.2
57.5°	509.8	509.2	512.5	513.5	512.5	509.2	509.8	504.8	501.7	495.3	494.5
60°	476.3	476.3	481.7	483.8	481.7	476.3	476.3	470.7	466.0	461.8	460.4
62.5°	440.5	442.7	448.2	445.4	448.2	442.7	440.5	434.4	430.7	425.6	421.9
65°	388.3	393.7	393.0	395.9	393.0	393.7	388.3	384.9	377.3	372.4	368.3
67.5°	333.7	337.1	342.0	342.5	342.0	337.1	333.7	328.2	323.3	318.2	313.3
70°	296.9	300.3	303.1	305.1	303.1	300.3	296.9	291.3	285.9	282.5	276.9
72.5°	261.2	263.0	269.5	266.6	269.5	263.0	261.2	254.6	250.1	247.2	241.3
75°	204.8	209.5	213.7	211.7	213.7	209.5	204.8	200.0	196.5	192.4	186.9
77.5°	151.5	156.2	158.1	156.4	158.1	156.2	151.5	148.3	146.5	138.5	137.8
80°	119.6	118.9	123.0	122.3	123.0	118.9	119.6	114.7	111.3	106.5	106.5
82.5°	87.7	87.1	89.0	89.4	89.0	87.1	87.7	85.0	80.6	78.5	76.9
85°	42.6	44.6	41.9	41.2	41.9	44.6	42.6	39.9	39.9	39.9	39.2
87.5°	13.2	13.2	12.7	12.2	12.7	13.2	13.2	13.1	15.2	13.5	13.4
90°	16.6	16.8	17.1	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8
92.5°	18.7	18.8	19.0	19.1	19.0	18.8	18.7	18.5	18.0	17.2	16.4
95°	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.4	20.5	19.7
97.5°	23.3	23.4	23.6	23.7	23.6	23.4	23.3	23.2	22.6	21.6	20.6
100°	23.8	23.9	24.0	24.2	24.0	23.9	23.8	23.6	23.1	22.1	21.0
102.5°	23.9	24.2	24.4	24.6	24.4	24.2	23.9	23.7	25.2	28.4	31.5
105°	24.5	24.8	25.0	25.3	25.0	24.8	24.5	24.3	35.5	58.2	80.8
107.5°	130.8	113.7	96.6	79.6	96.6	113.7	130.8	147.9	164.7	181.4	197.9
110°	213.3	195.0	176.7	158.3	176.7	195.0	213.3	231.6	242.9	247.1	251.4



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	283.4	279.4	275.6	271.8	275.6	279.4	283.4	287.2	289.1	289.0	288.9
115°	337.1	337.7	338.2	338.7	338.2	337.7	337.1	336.6	335.8	334.5	333.2
117.5°	376.0	376.1	376.2	376.3	376.2	376.1	376.0	375.9	375.3	374.3	373.2
120°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	401.5	400.5	399.5
122.5°	427.1	427.2	427.3	427.4	427.3	427.2	427.1	427.0	426.6	425.9	425.2
125°	462.3	462.6	462.8	463.1	462.8	462.6	462.3	462.1	461.8	461.5	461.3
127.5°	498.2	498.0	497.7	497.5	497.7	498.0	498.2	498.5	498.4	498.0	497.6
130°	520.3	520.1	519.8	519.6	519.8	520.1	520.3	520.6	520.4	519.9	519.4
132.5°	540.9	540.5	540.2	539.8	540.2	540.5	540.9	541.3	541.2	540.7	540.2
135°	572.0	571.6	571.2	570.8	571.2	571.6	572.0	572.3	572.3	572.0	571.6
137.5°	600.7	600.5	600.2	600.0	600.2	600.5	600.7	601.0	600.8	600.2	599.6
140°	618.2	617.9	617.7	617.4	617.7	617.9	618.2	618.4	618.3	617.8	617.3
142.5°	634.7	634.3	633.9	633.6	633.9	634.3	634.7	635.0	635.0	634.6	634.2
145°	658.3	658.3	658.3	658.3	658.3	658.3	658.3	658.3	658.2	657.9	657.7
147.5°	678.5	677.9	677.4	676.8	677.4	677.9	678.5	679.1	679.3	679.0	678.8
150°	691.8	691.4	690.9	690.6	690.9	691.4	691.8	692.2	692.2	692.0	691.7
152.5°	703.5	702.9	702.3	701.7	702.3	702.9	703.5	704.0	704.1	703.6	703.2
155°	719.4	718.6	717.9	717.1	717.9	718.6	719.4	720.1	720.2	719.6	718.9
157.5°	733.1	732.2	731.1	730.1	731.1	732.2	733.1	734.1	734.3	733.5	732.7
160°	741.1	740.2	739.3	738.4	739.3	740.2	741.1	741.9	742.0	741.2	740.5
162.5°	748.6	747.8	747.0	746.3	747.0	747.8	748.6	749.4	749.4	748.5	747.6
165°	758.4	757.5	756.6	755.7	756.6	757.5	758.4	759.3	759.2	758.2	757.2
167.5°	765.6	764.6	763.6	762.4	763.6	764.6	765.6	766.6	766.6	765.6	764.6
170°	769.7	768.7	767.7	766.6	767.7	768.7	769.7	770.7	770.7	769.7	768.7
172.5°	772.3	771.2	770.0	768.9	770.0	771.2	772.3	773.5	773.5	772.4	771.4
175°	775.5	774.5	773.5	772.3	773.5	774.5	775.5	776.5	776.6	775.7	774.8
177.5°	776.5	775.5	774.5	773.5	774.5	775.5	776.5	777.5	777.6	776.8	776.0
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1360.1	1360.1	1370.6	1377.2	1385.4	1390.9	1394.7	1398.6	1405.2	1414.0	1423.9
5°	1282.3	1285.1	1300.2	1315.3	1329.8	1342.1	1352.4	1364.8	1379.9	1398.5	1419.1
7.5°	1207.0	1217.6	1232.8	1251.2	1271.4	1289.5	1307.8	1328.1	1349.4	1376.7	1405.6
10°	1158.6	1170.3	1188.8	1212.2	1233.6	1254.9	1277.5	1299.5	1326.3	1358.6	1395.7
12.5°	1116.3	1127.4	1146.5	1172.0	1192.3	1215.8	1241.7	1270.4	1300.5	1339.4	1381.4
15°	1057.6	1070.7	1094.0	1106.4	1137.3	1165.5	1189.5	1230.8	1269.3	1309.1	1358.0
17.5°	1009.5	1016.8	1035.7	1058.7	1081.8	1113.4	1144.9	1179.2	1217.6	1266.4	1327.4
20°	976.5	982.7	1003.3	1027.3	1052.1	1081.0	1109.1	1143.5	1186.8	1238.3	1304.3
22.5°	951.8	958.5	972.0	997.6	1020.8	1044.7	1072.9	1113.8	1159.8	1210.3	1281.8
25°	916.0	920.2	929.1	949.7	970.4	997.1	1021.9	1060.4	1107.8	1166.9	1238.3
27.5°	882.1	886.1	893.5	908.4	927.6	949.3	976.2	1009.0	1057.0	1121.3	1197.1
30°	861.7	862.4	869.3	883.0	899.6	917.5	942.2	979.3	1024.6	1089.9	1169.6
32.5°	844.1	841.5	846.3	856.7	872.6	890.5	910.8	947.4	991.1	1055.3	1137.2
35°	814.4	812.9	810.9	819.8	833.5	847.3	865.2	892.7	942.2	1002.0	1087.8
37.5°	784.0	780.6	777.0	781.0	791.8	806.1	821.6	846.1	888.7	954.5	1036.7
40°	761.4	758.7	756.6	755.3	764.9	778.6	790.3	813.6	853.5	916.0	997.1
42.5°	736.7	735.1	732.5	730.5	738.5	748.9	761.1	781.7	821.6	880.3	957.0
45°	696.8	695.5	694.1	692.7	697.5	707.1	716.8	731.8	766.2	823.2	892.7
47.5°	652.5	650.7	651.2	649.0	653.7	660.1	666.8	683.1	716.1	762.1	812.8
50°	620.6	619.9	619.9	619.9	621.3	628.7	635.0	647.3	677.6	723.7	760.0
52.5°	590.3	587.4	587.4	588.5	591.0	595.8	599.8	613.3	639.6	677.4	710.5
55°	542.9	537.3	536.0	537.3	539.5	543.6	547.8	558.7	581.4	609.6	628.7
57.5°	490.4	487.4	485.5	485.8	487.0	490.3	493.4	505.3	523.2	538.0	550.3
60°	453.5	454.9	448.8	450.1	450.1	452.8	457.7	465.2	480.4	490.7	503.0
62.5°	418.9	417.0	415.3	413.2	413.2	414.3	420.8	426.8	439.7	445.0	454.6
65°	364.9	364.9	360.8	362.1	362.8	358.0	361.4	368.3	376.6	378.7	387.6
67.5°	310.2	308.3	306.0	303.9	303.9	303.5	305.3	308.7	314.9	315.6	322.4
70°	272.9	271.5	270.7	268.7	266.0	269.4	267.3	270.7	274.2	274.9	279.0
72.5°	236.5	235.2	233.9	231.9	230.8	230.4	230.5	234.5	236.8	235.8	240.5
75°	184.9	183.5	182.1	178.6	178.6	176.6	177.3	180.1	182.8	180.8	184.9
77.5°	135.8	131.5	131.3	132.2	129.9	130.3	129.5	129.1	130.3	130.5	134.1
80°	104.4	99.7	101.0	100.4	99.7	99.0	97.6	98.3	99.0	99.7	101.7
82.5°	75.3	74.9	73.5	73.4	72.7	70.9	70.1	71.3	72.0	71.6	73.1
85°	38.5	36.5	37.8	37.1	37.8	37.1	35.0	35.0	36.5	35.7	37.1
87.5°	14.4	14.3	13.4	13.6	12.7	13.0	12.1	12.4	12.7	12.4	13.3
90°	14.3	13.8	12.1	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6
92.5°	15.6	14.7	13.5	12.2	11.0	9.7	9.3	9.6	10.0	10.4	10.7
95°	18.8	17.9	16.5	15.0	13.6	12.2	14.1	19.4	24.6	29.9	35.1
97.5°	19.6	18.6	27.8	37.0	46.2	55.4	61.2	63.5	65.9	68.3	70.6
100°	20.0	19.0	39.0	59.0	78.9	98.9	107.6	105.0	102.5	99.9	97.4
102.5°	34.7	37.9	59.7	81.5	103.3	125.1	135.1	133.3	131.5	129.6	127.7
105°	103.5	126.1	137.6	149.2	160.7	172.2	177.2	175.8	174.5	173.1	171.7
107.5°	214.6	231.2	229.3	227.5	225.7	223.9	222.5	221.4	220.3	219.0	217.9
110°	255.5	259.7	258.3	256.9	255.5	254.2	252.9	251.9	250.9	249.8	248.8



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	288.9	288.8	287.4	286.0	284.6	283.2	282.0	281.0	280.1	279.2	278.3
115°	331.9	330.6	329.4	328.3	327.2	326.0	325.1	324.3	323.5	322.8	321.9
117.5°	372.2	371.1	370.6	370.0	369.4	368.8	368.0	367.1	366.2	365.2	364.3
120°	398.5	397.4	397.1	396.7	396.3	395.9	395.2	393.9	392.8	391.6	390.5
122.5°	424.4	423.7	423.2	422.7	422.2	421.7	421.0	420.1	419.1	418.2	417.3
125°	461.0	460.8	460.3	459.8	459.3	458.8	458.0	457.0	456.0	454.9	453.8
127.5°	497.2	496.8	496.1	495.5	494.8	494.2	493.4	492.4	491.4	490.4	489.4
130°	518.9	518.4	517.9	517.4	516.8	516.3	515.5	514.5	513.5	512.5	511.5
132.5°	539.7	539.2	538.7	538.3	537.9	537.5	536.7	535.7	534.7	533.7	532.7
135°	571.2	570.8	570.3	569.8	569.3	568.8	568.2	567.3	566.5	565.8	565.0
137.5°	599.0	598.3	598.0	597.7	597.4	597.2	596.5	595.6	594.6	593.7	592.7
140°	616.8	616.3	615.9	615.5	615.1	614.8	614.2	613.4	612.7	611.9	611.1
142.5°	633.8	633.4	633.0	632.6	632.2	631.8	631.3	630.5	629.8	628.9	628.1
145°	657.4	657.2	656.9	656.7	656.4	656.2	655.6	654.7	653.8	652.9	652.0
147.5°	678.5	678.3	678.0	677.7	677.5	677.2	676.8	676.2	675.7	675.1	674.5
150°	691.5	691.2	690.9	690.6	690.4	690.1	689.8	689.4	689.0	688.7	688.3
152.5°	702.7	702.3	702.1	702.0	701.8	701.7	701.5	701.3	701.0	700.9	700.7
155°	718.3	717.7	717.5	717.4	717.3	717.2	717.2	717.5	717.7	718.0	718.2
157.5°	732.0	731.1	731.2	731.4	731.5	731.6	731.7	731.7	731.7	731.8	731.8
160°	739.7	739.0	739.1	739.2	739.3	739.5	739.6	739.7	739.9	740.0	740.1
162.5°	746.8	745.9	746.0	746.2	746.3	746.4	746.6	747.0	747.3	747.6	748.0
165°	756.2	755.1	755.3	755.4	755.5	755.6	755.9	756.3	756.7	757.0	757.4
167.5°	763.6	762.4	762.4	762.4	762.4	762.4	762.8	763.3	763.8	764.3	764.8
170°	767.7	766.6	766.6	766.6	766.6	766.6	766.9	767.4	767.9	768.4	768.9
172.5°	770.4	769.4	769.3	769.2	769.1	769.0	769.2	769.8	770.4	771.1	771.7
175°	773.9	773.0	772.8	772.7	772.5	772.4	772.7	773.4	774.0	774.7	775.3
177.5°	775.2	774.4	774.3	774.2	774.1	774.0	774.2	774.7	775.2	775.7	776.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1427.1	1430.0	1439.3	1445.9	1453.6	1457.9	1462.4	1465.7	1470.1	1471.2	1487.1
5°	1433.5	1447.2	1471.3	1489.1	1511.2	1535.2	1551.7	1559.2	1579.2	1595.7	1628.7
7.5°	1431.7	1461.0	1497.3	1534.9	1575.4	1612.8	1645.2	1683.6	1711.0	1752.1	1792.6
10°	1430.1	1469.3	1516.0	1564.1	1620.4	1672.6	1719.4	1771.6	1814.9	1872.0	1920.8
12.5°	1425.1	1472.6	1537.4	1594.3	1662.7	1734.7	1804.0	1871.1	1909.5	2004.5	2049.4
15°	1412.9	1469.3	1550.3	1636.9	1731.1	1816.2	1904.2	1974.4	2087.7	2170.9	2223.8
17.5°	1389.6	1468.4	1564.6	1669.1	1783.5	1895.8	1995.5	2101.9	2222.1	2322.8	2429.9
20°	1378.6	1465.1	1572.4	1687.8	1806.6	1933.8	2047.2	2175.0	2306.2	2405.2	2542.6
22.5°	1358.2	1456.3	1571.8	1700.4	1827.6	1959.0	2091.7	2220.6	2372.3	2508.6	2639.4
25°	1324.9	1434.9	1554.5	1698.1	1847.2	1979.1	2137.9	2309.1	2467.1	2642.3	2772.9
27.5°	1290.0	1407.3	1527.2	1660.8	1821.2	1977.8	2177.5	2370.9	2564.0	2715.4	2812.1
30°	1263.0	1377.2	1500.9	1635.6	1794.3	1980.5	2203.8	2414.8	2603.1	2733.0	2787.3
32.5°	1234.0	1349.7	1459.1	1600.3	1769.6	1978.8	2220.4	2440.6	2605.4	2691.8	2681.2
35°	1188.2	1285.1	1391.6	1527.6	1727.0	1966.8	2230.0	2443.0	2544.1	2525.5	2385.3
37.5°	1122.2	1203.7	1308.6	1457.5	1677.5	1941.4	2210.7	2370.6	2364.0	2212.9	2009.8
40°	1081.0	1150.3	1251.4	1408.1	1639.0	1924.9	2180.5	2284.3	2196.4	1985.3	1742.0
42.5°	1027.1	1091.0	1192.0	1353.1	1596.7	1891.3	2122.7	2152.8	1980.7	1738.0	1515.0
45°	943.5	999.9	1104.3	1270.6	1533.2	1818.4	1981.9	1908.3	1676.8	1425.9	1256.2
47.5°	853.7	912.3	1012.8	1183.7	1441.4	1708.5	1786.5	1630.0	1392.3	1188.8	1033.0
50°	797.2	853.5	951.8	1124.3	1379.2	1618.4	1650.6	1448.7	1230.1	1051.5	923.6
52.5°	740.0	793.0	889.7	1062.7	1306.7	1513.9	1494.0	1288.1	1087.1	934.8	834.6
55°	654.9	705.1	797.2	959.4	1181.3	1345.5	1273.4	1076.8	910.6	792.3	716.1
57.5°	578.8	626.8	706.3	852.8	1045.8	1158.6	1066.8	901.2	769.0	678.0	621.1
60°	527.0	569.7	645.3	781.3	949.1	1034.9	944.2	797.9	686.5	613.7	562.8
62.5°	478.2	515.2	585.3	708.8	854.4	926.7	834.9	710.9	616.1	551.6	508.4
65°	404.0	437.8	499.6	595.8	715.4	763.5	684.5	584.1	510.6	462.5	433.6
67.5°	336.5	365.1	418.5	494.2	582.2	617.2	557.0	479.4	424.0	385.4	362.4
70°	291.3	316.1	358.0	423.3	503.0	529.9	473.5	409.6	369.0	338.1	316.8
72.5°	253.5	271.6	309.6	360.1	426.6	447.9	408.6	352.4	314.6	291.3	274.5
75°	193.1	208.2	233.0	273.5	319.5	331.9	302.4	267.3	241.9	225.4	212.4
77.5°	139.3	150.4	168.2	193.3	225.1	236.3	217.5	194.2	175.6	164.5	157.2
80°	105.1	114.1	129.2	149.8	169.1	175.2	164.2	146.3	133.3	127.1	121.0
82.5°	77.7	82.7	91.8	105.8	119.1	126.3	116.9	106.2	99.3	93.6	91.3
85°	39.2	41.9	46.0	51.5	59.8	62.5	59.1	56.4	52.2	48.8	48.8
87.5°	14.6	14.9	16.9	18.2	20.7	22.6	22.4	21.7	21.4	21.0	20.6
90°	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8
92.5°	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6	16.4
95°	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8	19.7
97.5°	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6	20.6
100°	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0	21.0
102.5°	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7	31.5
105°	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5	80.8
107.5°	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6	197.9
110°	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5	251.4





TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9	288.9
115°	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9	333.2
117.5°	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2	373.2
120°	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5	399.5
122.5°	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4	425.2
125°	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0	461.3
127.5°	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2	497.6
130°	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9	519.4
132.5°	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7	540.2
135°	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2	571.6
137.5°	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0	599.6
140°	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8	617.3
142.5°	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8	634.2
145°	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4	657.7
147.5°	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5	678.8
150°	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5	691.7
152.5°	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7	703.2
155°	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3	718.9
157.5°	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0	732.7
160°	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7	740.5
162.5°	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8	747.6
165°	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2	757.2
167.5°	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6	764.6
170°	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7	768.7
172.5°	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4	771.4
175°	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9	774.8
177.5°	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2	776.0
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1492.6	1493.2	1499.2	1503.6	1501.4	1504.2	1505.2
5°	1630.7	1655.5	1668.5	1678.2	1678.8	1679.5	1685.1
7.5°	1826.5	1853.1	1872.5	1901.9	1910.7	1920.8	1917.8
10°	1969.5	2008.7	2042.4	2060.2	2079.5	2107.7	2085.0
12.5°	2103.1	2172.5	2223.8	2251.6	2269.7	2275.3	2264.2
15°	2323.4	2414.2	2463.0	2461.5	2523.5	2550.2	2508.3
17.5°	2525.5	2609.2	2676.2	2710.6	2762.2	2773.6	2768.3
20°	2649.2	2740.6	2792.8	2851.9	2878.7	2902.8	2906.9
22.5°	2755.8	2837.9	2894.0	2943.2	2965.6	2977.0	2983.8
25°	2865.6	2930.2	2964.0	2981.1	2987.3	2985.9	2977.0
27.5°	2858.1	2863.1	2825.9	2789.6	2756.9	2720.3	2707.5
30°	2783.9	2726.1	2623.0	2564.7	2478.7	2410.7	2438.2
32.5°	2588.7	2473.8	2358.0	2230.4	2124.7	2094.6	2064.4
35°	2209.4	2007.3	1889.2	1751.7	1696.7	1641.7	1604.0
37.5°	1787.5	1631.1	1491.0	1401.1	1345.9	1311.2	1292.5
40°	1545.5	1404.6	1289.2	1216.4	1174.5	1135.3	1129.7
42.5°	1352.5	1221.5	1134.7	1076.7	1036.4	1019.8	1007.7
45°	1107.8	1016.3	958.0	916.8	889.9	879.6	865.9
47.5°	937.7	873.0	829.2	801.1	780.9	773.3	772.1
50°	842.5	788.9	756.6	734.6	718.8	716.1	705.1
52.5°	771.0	724.6	699.4	680.2	668.8	661.1	657.8
55°	669.3	638.4	615.7	604.7	595.8	588.2	588.2
57.5°	585.6	559.8	544.8	535.4	532.7	527.4	523.9
60°	533.9	512.0	500.3	492.0	486.6	487.3	481.0
62.5°	483.4	469.1	458.0	449.7	443.1	443.2	443.6
65°	411.6	400.6	392.4	389.6	385.6	380.7	382.1
67.5°	348.8	338.5	332.0	327.4	326.0	323.4	327.4
70°	303.8	296.2	291.3	287.2	285.9	286.6	290.0
72.5°	262.5	257.1	254.0	252.1	249.0	249.1	251.6
75°	206.1	202.1	199.2	197.2	196.5	196.5	196.5
77.5°	151.5	150.5	149.3	146.2	146.3	147.2	147.3
80°	119.6	117.5	116.8	115.4	113.4	112.0	115.4
82.5°	89.4	87.3	86.5	86.3	83.1	82.9	85.7
85°	48.1	46.0	46.8	46.0	46.0	45.3	45.3
87.5°	20.1	19.7	19.2	19.8	19.3	18.8	20.0
90°	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	247.1	242.9	231.6	213.3	195.0	176.7	158.3



TEST NUMBER: P332009-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)