

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332016-840

Luminaire Tested: **S123DIP-S1000D585U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332016-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D585U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6193.2 lumens  
Efficiency: N/A  
Efficacy: 126.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	89	96	92	88	85	81	79	76	72	70	68	63	62	61	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	56	53	51	47
3	84	75	67	61	79	70	64	58	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	72	63	55	49	56	50	45	50	45	41	44	40	37	34
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	65	53	45	39	61	50	43	37	45	39	34	41	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.6	2.4
10°-20°	425.2	6.9
20°-30°	628.0	10.1
30°-40°	733.6	11.8
40°-50°	737.6	11.9
50°-60°	647.9	10.5
60°-70°	482.7	7.8
70°-80°	275.0	4.4
80°-90°	81.1	1.3
90°-100°	47.8	0.8
100°-110°	143.0	2.3
110°-120°	243.2	3.9
120°-130°	319.9	5.2
130°-140°	359.5	5.8
140°-150°	353.4	5.7
150°-160°	297.5	4.8
160°-170°	198.0	3.2
170°-180°	69.3	1.1
0°-30°	1203.8	19.4
0°-40°	1937.4	31.3
0°-60°	3322.8	53.7
0°-90°	4161.6	67.2
90°-120°	433.9	7.0
90°-150°	1466.7	23.7
90°-180°	2032.0	32.8
0°-180°	6193.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	1	6	14	16	17	6
95°	34	38	43	45	45	38
105°	130	131	136	136	137	139
115°	245	246	245	246	245	242
125°	358	360	359	357	354	319
135°	465	468	468	465	464	358
145°	564	565	567	566	564	352
155°	646	646	646	648	645	297
165°	703	702	702	705	701	198
175°	732	729	729	732	729	69
180°	733	733	733	733	733	



TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.7	28.3	27.8	27.3	26.8	26.6	26.7	26.8	26.9	27.0	26.9
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	13.9	14.8	15.7	16.6	17.5	18.4	19.3	20.2	21.2	22.1	22.5
95°	34.0	34.8	35.7	36.7	37.6	38.6	39.6	40.6	41.6	42.6	43.1
97.5°	60.4	61.0	61.7	62.4	63.0	63.7	64.4	65.2	65.9	66.8	67.3
100°	78.4	79.1	79.9	80.7	81.4	82.1	82.7	83.4	84.0	84.6	85.0
102.5°	99.1	99.6	100.0	100.5	100.9	101.6	102.4	103.3	104.1	104.9	105.3
105°	129.6	129.9	130.1	130.4	130.7	131.3	132.5	133.6	134.8	135.9	135.9
107.5°	165.1	165.2	165.4	165.5	165.7	166.0	166.4	166.9	167.4	167.8	168.2
110°	187.2	187.4	187.7	187.9	188.2	188.4	188.7	189.0	189.2	189.6	190.1



TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	210.4	210.6	210.7	210.9	211.0	211.1	211.1	211.2	211.2	211.8
115°	244.8	245.2	245.6	246.0	246.3	246.4	246.1	245.9	245.6	245.4	245.5
117.5°	279.6	279.8	280.1	280.3	280.6	280.5	280.2	279.9	279.6	279.2	279.2
120°	301.2	302.1	302.8	303.6	304.4	304.4	303.8	303.2	302.5	301.8	301.7
122.5°	323.9	324.4	325.0	325.5	326.1	326.2	325.9	325.6	325.2	324.9	324.6
125°	358.3	358.7	359.0	359.4	359.8	359.9	359.6	359.4	359.1	358.9	358.3
127.5°	390.1	390.9	391.7	392.5	393.3	393.6	393.3	393.0	392.7	392.5	391.8
130°	411.3	412.3	413.3	414.3	415.4	415.7	415.4	415.0	414.5	414.1	413.6
132.5°	432.4	433.5	434.5	435.6	436.6	437.0	436.7	436.4	436.1	435.9	435.2
135°	464.8	465.6	466.4	467.2	467.9	468.3	468.1	468.0	467.9	467.8	467.3
137.5°	494.8	495.4	496.0	496.8	497.4	497.9	498.2	498.5	498.9	499.2	498.7
140°	515.5	516.1	516.8	517.5	518.1	518.5	518.6	518.8	518.9	519.0	518.9
142.5°	534.4	535.0	535.7	536.3	536.9	537.5	537.7	537.9	538.2	538.4	538.3
145°	563.9	564.2	564.4	564.7	564.9	565.2	565.6	566.0	566.4	566.8	566.6
147.5°	589.8	590.2	590.7	591.1	591.6	592.0	592.4	592.7	593.1	593.4	593.4
150°	607.7	607.9	608.2	608.4	608.7	608.9	609.3	609.5	609.8	610.0	610.0
152.5°	622.5	622.8	623.2	623.5	623.9	624.1	624.3	624.4	624.6	624.7	624.9
155°	645.7	645.7	645.7	645.7	645.7	645.8	645.9	646.0	646.2	646.3	646.8
157.5°	665.5	665.4	665.2	665.1	664.9	664.9	665.0	665.1	665.2	665.3	665.8
160°	677.9	677.7	677.4	677.2	676.9	676.8	676.8	676.8	676.8	676.8	677.4
162.5°	689.0	688.6	688.3	687.9	687.6	687.5	687.6	687.7	687.8	687.9	688.5
165°	703.3	703.0	702.6	702.2	701.8	701.6	701.6	701.6	701.6	701.6	702.4
167.5°	714.7	714.2	713.7	713.2	712.7	712.5	712.6	712.7	712.8	712.9	713.7
170°	721.1	720.6	720.1	719.6	719.1	718.8	718.8	718.8	718.8	718.8	719.7
172.5°	726.2	725.7	725.2	724.7	724.2	724.0	724.0	724.0	724.0	724.0	724.8
175°	731.5	731.0	730.5	730.0	729.5	729.2	729.2	729.2	729.2	729.2	730.0
177.5°	733.8	733.4	733.0	732.5	732.1	731.8	731.8	731.8	731.8	731.8	732.5
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	26.7	26.6	26.4	26.4	26.4	26.5	26.5	26.6
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	22.9	23.3	23.7	23.9	23.7	23.5	23.4	23.2
95°	43.6	44.1	44.6	44.9	44.9	44.9	44.9	44.9
97.5°	67.9	68.5	69.1	69.3	69.3	69.2	69.2	69.1
100°	85.4	85.8	86.2	86.5	86.7	87.1	87.3	87.6
102.5°	105.7	106.1	106.4	106.6	106.6	106.5	106.5	106.4
105°	135.9	135.9	135.9	136.0	136.3	136.5	136.8	137.1
107.5°	168.6	169.1	169.5	169.7	169.5	169.4	169.2	169.1
110°	190.6	191.1	191.6	191.7	191.5	191.2	191.0	190.7





TEST NUMBER: P332016-840

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.4	213.0	213.6	213.9	213.9	213.8	213.8	213.7
115°	245.6	245.8	245.9	245.9	245.8	245.6	245.5	245.4
117.5°	279.2	279.1	279.1	278.9	278.6	278.2	277.9	277.5
120°	301.5	301.4	301.3	301.1	300.8	300.6	300.3	300.1
122.5°	324.2	323.9	323.6	323.2	322.9	322.4	322.1	321.7
125°	357.8	357.3	356.8	356.3	355.8	355.3	354.8	354.3
127.5°	391.0	390.3	389.6	389.0	388.4	387.8	387.2	386.6
130°	413.1	412.6	412.1	411.4	410.5	409.6	408.7	407.8
132.5°	434.5	433.9	433.3	432.7	432.0	431.3	430.6	429.9
135°	466.7	466.2	465.6	465.2	465.0	464.7	464.5	464.2
137.5°	498.1	497.6	497.1	496.6	496.0	495.5	495.0	494.5
140°	518.8	518.6	518.5	518.0	517.1	516.1	515.2	514.4
142.5°	538.1	538.0	537.9	537.5	536.7	536.0	535.3	534.6
145°	566.5	566.4	566.3	565.9	565.4	564.9	564.4	563.9
147.5°	593.4	593.4	593.4	593.0	592.3	591.5	590.8	590.0
150°	610.0	610.0	610.0	609.7	608.8	608.0	607.3	606.5
152.5°	625.2	625.4	625.6	625.3	624.7	624.0	623.4	622.7
155°	647.3	647.8	648.3	648.1	647.2	646.3	645.5	644.6
157.5°	666.4	666.9	667.4	667.3	666.6	665.9	665.2	664.5
160°	678.1	678.7	679.3	679.4	678.9	678.4	677.9	677.4
162.5°	689.1	689.8	690.4	690.3	689.5	688.7	687.9	687.1
165°	703.2	703.9	704.7	704.6	703.7	702.8	702.0	701.0
167.5°	714.5	715.3	716.1	716.1	715.3	714.5	713.7	712.9
170°	720.6	721.5	722.5	722.5	721.5	720.6	719.7	718.8
172.5°	725.5	726.3	727.1	727.1	726.2	725.3	724.4	723.5
175°	730.7	731.5	732.4	732.3	731.3	730.4	729.5	728.6
177.5°	733.2	733.8	734.4	734.3	733.6	732.9	732.2	731.4
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3

(END OF REPORT)