

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332287-940

Luminaire Tested: **S123RDIP-S560D805U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332287-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4496.4 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	74	63	55	50	67	58	51	46	48	43	40	39	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	23	21	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.8
10°-20°	220.1	4.9
20°-30°	316.9	7.0
30°-40°	356.9	7.9
40°-50°	341.4	7.6
50°-60°	279.6	6.2
60°-70°	188.7	4.2
70°-80°	94.9	2.1
80°-90°	27.8	0.6
90°-100°	191.7	4.3
100°-110°	542.7	12.1
110°-120°	533.9	11.9
120°-130°	425.8	9.5
130°-140°	335.7	7.5
140°-150°	250.6	5.6
150°-160°	174.7	3.9
160°-170°	102.6	2.3
170°-180°	33.4	0.7
0°-30°	616.0	13.7
0°-40°	972.9	21.6
0°-60°	1594.0	35.5
0°-90°	1905.3	42.4
90°-120°	1268.2	28.2
90°-150°	2280.4	50.7
90°-180°	2591.0	57.6
0°-180°	4496.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	8	17	20	20	3
95°	24	77	413	121	81	26
105°	81	120	560	980	887	86
115°	143	178	429	940	1078	141
125°	199	235	400	725	850	176
135°	233	278	395	597	690	180
145°	266	304	390	490	539	166
155°	302	326	377	429	447	139
165°	330	339	361	383	390	93
175°	344	344	346	351	351	33
180°	344	344	344	344	344	



TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.4	12.3	11.2	10.3	9.3	8.9	9.4	9.7	10.2	10.6	10.3
90°	1.4	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8
92.5°	8.6	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9
95°	23.7	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4
97.5°	40.4	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5
100°	51.6	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5
102.5°	63.3	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2
105°	80.9	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6
107.5°	99.5	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2
110°	113.0	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3



TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.2	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6
115°	142.9	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4
117.5°	160.6	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7
120°	172.9	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1
122.5°	183.5	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2
125°	198.7	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7
127.5°	210.3	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3
130°	217.5	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5
132.5°	223.1	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2
135°	232.8	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7
137.5°	242.0	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5
140°	248.2	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5
142.5°	254.9	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0
145°	265.6	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1
147.5°	276.5	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2
150°	283.7	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3
152.5°	291.0	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8
155°	301.8	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1
157.5°	310.5	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6
160°	317.2	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5
162.5°	322.3	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5
165°	329.8	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7
167.5°	335.5	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2
170°	338.9	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2
172.5°	341.1	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3
175°	343.7	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9
177.5°	344.9	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	10.3	10.3	10.3	10.5	10.3	10.3	10.3	10.1
90°	17.4	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	58.7	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	251.0	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	625.6	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	822.0	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	887.2	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	906.3	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	851.4	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	799.0	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P332287-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	747.1	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	678.3	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	628.6	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	602.4	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	581.8	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	554.2	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	530.3	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	515.2	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	501.2	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	482.4	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	465.3	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	455.2	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	445.8	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	434.4	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	425.0	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	418.3	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	412.1	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	403.0	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	393.2	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	387.6	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	380.9	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	372.3	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	364.7	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	359.7	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	355.3	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	349.3	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	345.5	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)