

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332052-840

Luminaire Tested: **S123DIP-S1165D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332052-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6063.9 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	104	100	96	92	99	95	92	88	87	85	82	80	78	76	73	72	70	67
2	95	87	81	75	90	83	78	73	77	72	68	70	67	63	64	61	59	56
3	87	77	69	63	82	73	66	61	68	62	57	62	57	53	57	53	50	47
4	79	68	59	53	75	65	58	52	60	54	49	55	50	46	51	47	43	40
5	73	61	52	46	69	58	50	45	54	47	42	50	44	40	46	41	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31
7	62	49	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29	38	32	28	35	30	26	24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	28	24	22
10	51	38	30	25	49	37	30	25	34	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	2.9
10°-20°	491.0	8.1
20°-30°	725.3	12.0
30°-40°	847.3	14.0
40°-50°	851.8	14.0
50°-60°	748.3	12.3
60°-70°	557.5	9.2
70°-80°	317.6	5.2
80°-90°	92.5	1.5
90°-100°	29.6	0.5
100°-110°	88.6	1.5
110°-120°	150.7	2.5
120°-130°	198.2	3.3
130°-140°	222.7	3.7
140°-150°	219.0	3.6
150°-160°	184.3	3.0
160°-170°	122.7	2.0
170°-180°	43.0	0.7
0°-30°	1390.3	22.9
0°-40°	2237.6	36.9
0°-60°	3837.7	63.3
0°-90°	4805.2	79.2
90°-120°	268.8	4.4
90°-150°	908.7	15.0
90°-180°	1259.0	20.8
0°-180°	6063.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	0	4	9	10	11	6
95°	21	24	26	28	28	24
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	219	198
135°	288	290	290	288	288	222
145°	349	350	351	351	349	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.1	32.4	31.7	31.0	30.3	30.0	29.9	29.8	29.7	29.7	29.4
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	8.7	9.2	9.7	10.3	10.8	11.3	11.9	12.5	13.1	13.7	13.9
95°	21.1	21.6	22.1	22.7	23.2	23.8	24.5	25.1	25.8	26.5	26.8
97.5°	37.4	37.8	38.3	38.7	39.1	39.5	40.0	40.4	40.9	41.3	41.7
100°	48.6	49.0	49.5	50.0	50.4	50.9	51.3	51.7	52.1	52.4	52.7
102.5°	61.4	61.7	61.9	62.2	62.5	62.9	63.4	64.0	64.5	65.0	65.2
105°	80.3	80.5	80.6	80.8	80.9	81.4	82.1	82.8	83.5	84.2	84.2
107.5°	102.3	102.4	102.5	102.6	102.7	102.8	103.1	103.4	103.7	104.0	104.2
110°	116.0	116.1	116.3	116.4	116.6	116.7	116.9	117.1	117.2	117.4	117.8



TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	130.4	130.5	130.6	130.7	130.7	130.8	130.8	130.8	130.9	131.2
115°	151.7	151.9	152.2	152.4	152.6	152.7	152.5	152.4	152.2	152.0	152.1
117.5°	173.2	173.4	173.6	173.7	173.9	173.8	173.6	173.4	173.2	173.0	173.0
120°	186.6	187.1	187.6	188.0	188.5	188.5	188.2	187.8	187.4	187.0	186.9
122.5°	200.7	201.0	201.4	201.7	202.1	202.1	201.9	201.7	201.5	201.3	201.1
125°	222.0	222.2	222.5	222.7	223.0	223.0	222.8	222.7	222.5	222.4	222.0
127.5°	241.7	242.2	242.7	243.2	243.7	243.9	243.7	243.5	243.4	243.2	242.8
130°	254.8	255.4	256.1	256.7	257.3	257.5	257.3	257.1	256.8	256.6	256.3
132.5°	267.9	268.6	269.2	269.8	270.4	270.7	270.5	270.3	270.1	270.0	269.6
135°	288.0	288.5	288.9	289.4	289.9	290.1	290.0	289.9	289.8	289.8	289.4
137.5°	306.6	307.0	307.3	307.7	308.1	308.4	308.6	308.8	309.0	309.2	308.9
140°	319.4	319.8	320.2	320.6	321.0	321.2	321.3	321.3	321.4	321.5	321.4
142.5°	331.1	331.5	331.9	332.3	332.6	333.0	333.2	333.3	333.4	333.6	333.5
145°	349.4	349.5	349.7	349.8	350.0	350.2	350.4	350.7	350.9	351.1	351.1
147.5°	365.4	365.7	366.0	366.3	366.5	366.8	367.0	367.2	367.4	367.7	367.7
150°	376.5	376.7	376.8	377.0	377.2	377.3	377.5	377.6	377.8	377.9	377.9
152.5°	385.7	385.9	386.1	386.3	386.6	386.7	386.8	386.9	387.0	387.1	387.2
155°	400.1	400.1	400.1	400.1	400.1	400.1	400.2	400.2	400.3	400.4	400.7
157.5°	412.3	412.2	412.1	412.0	411.9	411.9	412.0	412.0	412.1	412.2	412.5
160°	420.0	419.9	419.7	419.6	419.4	419.3	419.3	419.3	419.3	419.3	419.7
162.5°	426.9	426.7	426.5	426.3	426.0	426.0	426.0	426.1	426.2	426.2	426.6
165°	435.8	435.6	435.3	435.0	434.7	434.6	434.6	434.6	434.6	434.6	435.2
167.5°	442.8	442.5	442.2	441.8	441.5	441.4	441.5	441.5	441.6	441.7	442.1
170°	446.8	446.5	446.2	445.9	445.6	445.4	445.4	445.4	445.4	445.4	446.0
172.5°	450.0	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.2	452.9	452.6	452.3	452.0	451.8	451.8	451.8	451.8	451.8	452.3
177.5°	454.5	454.3	454.0	453.8	453.5	453.4	453.4	453.4	453.4	453.4	453.8
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3



TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	29.2	29.0	28.8	28.7	28.7	28.8	28.8	28.8
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.2	14.4	14.7	14.8	14.7	14.6	14.5	14.4
95°	27.1	27.4	27.7	27.9	27.9	27.9	27.9	27.9
97.5°	42.0	42.4	42.8	42.9	42.9	42.9	42.8	42.8
100°	52.9	53.2	53.4	53.6	53.7	53.9	54.1	54.2
102.5°	65.5	65.7	65.9	66.0	66.0	66.0	65.9	65.9
105°	84.2	84.2	84.2	84.3	84.4	84.6	84.8	84.9
107.5°	104.5	104.7	105.0	105.1	105.0	104.9	104.8	104.7
110°	118.1	118.4	118.7	118.8	118.6	118.5	118.3	118.2



TEST NUMBER: P332052-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.6	132.0	132.4	132.5	132.5	132.5	132.4	132.4
115°	152.2	152.3	152.4	152.4	152.3	152.2	152.1	152.0
117.5°	173.0	173.0	173.0	172.8	172.6	172.4	172.2	172.0
120°	186.8	186.7	186.7	186.5	186.4	186.2	186.1	185.9
122.5°	200.9	200.7	200.5	200.3	200.1	199.8	199.5	199.3
125°	221.7	221.4	221.1	220.8	220.5	220.2	219.7	219.4
127.5°	242.3	241.9	241.4	241.0	240.7	240.2	239.9	239.5
130°	256.0	255.6	255.3	254.9	254.4	253.8	253.3	252.7
132.5°	269.2	268.8	268.5	268.1	267.6	267.2	266.8	266.4
135°	289.1	288.8	288.5	288.3	288.1	287.9	287.8	287.6
137.5°	308.6	308.3	307.9	307.6	307.3	307.0	306.7	306.4
140°	321.3	321.3	321.2	320.9	320.3	319.8	319.2	318.7
142.5°	333.4	333.3	333.3	333.0	332.5	332.1	331.6	331.2
145°	351.0	350.9	350.8	350.6	350.3	350.0	349.7	349.4
147.5°	367.7	367.7	367.7	367.4	367.0	366.5	366.0	365.5
150°	377.9	377.9	377.9	377.7	377.2	376.8	376.3	375.8
152.5°	387.3	387.5	387.6	387.4	387.0	386.6	386.2	385.8
155°	401.0	401.3	401.7	401.5	401.0	400.4	399.9	399.3
157.5°	412.8	413.2	413.5	413.4	413.0	412.6	412.1	411.7
160°	420.1	420.5	420.9	420.9	420.6	420.3	420.0	419.7
162.5°	427.0	427.4	427.8	427.7	427.2	426.7	426.2	425.7
165°	435.7	436.1	436.6	436.6	436.0	435.5	434.8	434.3
167.5°	442.6	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.5	447.1	447.6	447.6	447.1	446.5	446.0	445.4
172.5°	449.5	450.0	450.5	450.5	449.9	449.4	448.8	448.3
175°	452.7	453.2	453.7	453.6	453.1	452.5	452.0	451.4
177.5°	454.2	454.5	454.9	454.9	454.5	454.0	453.6	453.1
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

(END OF REPORT)