

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332314-940

Luminaire Tested: **S123RDIP-S775D805U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332314-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5309.1 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11739	11739	11739	11739
5°	13993	11788	10381	11788
10°	17472	11721	9379	11721
15°	20508	11602	8553	11602
20°	22888	11423	7851	11423
25°	22523	11233	7418	11233
30°	16189	11059	6975	11059
35°	10809	10834	6687	10834
40°	7964	10561	6389	10561
45°	6680	10085	6098	10085
50°	5894	9460	5690	9460
55°	5168	8743	5134	8743
60°	4603	8060	4704	8060
65°	4042	7325	4376	7325
70°	3175	6672	3997	6672
75°	2795	5827	3647	5827
80°	2430	4947	3589	4947
85°	1964	3977	3816	3977



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	2.0
10°-20°	335.1	6.3
20°-30°	526.4	9.9
30°-40°	549.2	10.3
40°-50°	470.0	8.9
50°-60°	358.2	6.7
60°-70°	229.6	4.3
70°-80°	110.5	2.1
80°-90°	31.9	0.6
90°-100°	191.7	3.6
100°-110°	542.7	10.2
110°-120°	533.9	10.1
120°-130°	425.8	8.0
130°-140°	335.7	6.3
140°-150°	250.6	4.7
150°-160°	174.7	3.3
160°-170°	102.6	1.9
170°-180°	33.4	0.6
0°-30°	968.7	18.2
0°-40°	1517.9	28.6
0°-60°	2346.1	44.2
0°-90°	2718.0	51.2
90°-120°	1268.2	23.9
90°-150°	2280.4	43.0
90°-180°	2591.0	48.8
0°-180°	5309.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1295	1091	961	1091	1295	134
15°	1840	1041	768	1041	1840	522
25°	1896	946	625	946	1896	815
35°	823	824	509	824	823	539
45°	439	662	401	662	439	345
55°	275	466	274	466	275	249
65°	159	288	172	288	159	156
75°	67	140	88	140	67	72
85°	16	32	31	32	16	19
90°	20	1	20	1	20	11
95°	81	24	81	24	81	146
105°	887	81	887	81	887	875
115°	1078	143	1078	143	1078	1048
125°	850	199	850	199	850	771
135°	690	233	690	233	690	535
145°	539	266	539	266	539	343
155°	447	302	447	302	447	208
165°	390	330	390	330	390	111
175°	351	344	351	344	351	34
180°	344	344	344	344	344	



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1161.5	1163.1	1158.2	1157.4	1151.8	1150.3	1150.3	1142.5	1137.6	1131.3	1127.6
5°	1295.0	1302.5	1298.8	1290.4	1276.4	1273.1	1264.3	1250.3	1234.4	1214.8	1205.4
7.5°	1461.8	1472.0	1468.1	1455.1	1440.5	1428.6	1403.6	1380.3	1347.7	1319.1	1294.7
10°	1598.5	1587.8	1579.4	1566.7	1553.3	1531.2	1505.1	1469.2	1427.6	1395.0	1358.5
12.5°	1700.8	1699.1	1688.5	1675.4	1656.4	1635.5	1603.4	1559.6	1511.3	1464.1	1422.5
15°	1840.3	1843.2	1836.1	1822.6	1795.5	1758.6	1710.1	1691.8	1622.8	1571.5	1520.1
17.5°	1936.9	1936.4	1935.4	1916.6	1889.0	1862.8	1817.8	1769.9	1707.3	1635.0	1565.8
20°	1998.1	1993.5	1994.4	1973.4	1952.8	1922.5	1878.7	1809.1	1757.7	1674.2	1602.7
22.5°	1996.6	1995.7	1999.3	1992.1	1977.1	1953.9	1919.3	1860.6	1795.1	1710.7	1630.3
25°	1896.4	1892.7	1914.6	1920.7	1944.5	1948.7	1938.4	1906.2	1844.1	1757.2	1657.8
27.5°	1587.2	1585.1	1625.8	1676.8	1741.3	1791.6	1840.1	1863.6	1844.1	1781.9	1682.3
30°	1302.5	1346.4	1367.0	1440.7	1522.9	1621.0	1706.8	1788.5	1808.6	1781.5	1699.8
32.5°	1081.5	1119.7	1136.8	1200.2	1276.8	1391.6	1520.5	1636.1	1717.9	1738.6	1689.3
35°	822.6	823.0	862.3	890.3	961.3	1079.3	1204.5	1359.5	1513.5	1630.2	1642.4
37.5°	656.4	658.7	682.4	710.3	763.6	826.1	936.2	1065.1	1243.0	1422.2	1527.2
40°	566.8	571.0	588.7	616.3	654.5	701.7	787.6	909.0	1057.4	1256.8	1419.7
42.5°	509.3	516.0	525.2	546.4	570.2	614.3	683.8	777.5	912.5	1101.0	1289.0
45°	438.8	442.6	449.6	459.4	480.9	511.7	558.4	621.3	733.4	885.2	1073.3
47.5°	387.1	385.1	392.5	400.5	414.7	435.8	467.1	518.5	598.4	720.1	879.8
50°	352.0	351.5	356.7	362.7	376.3	391.7	417.4	456.1	519.6	620.5	766.6
52.5°	319.1	320.9	324.6	332.2	341.9	354.4	377.4	405.3	459.9	546.9	668.7
55°	275.4	276.9	282.0	286.1	293.2	305.8	320.3	343.6	380.9	441.7	542.0
57.5°	238.4	237.8	242.7	243.8	251.7	262.0	273.2	291.3	318.4	363.5	431.1
60°	213.8	212.4	216.6	219.9	224.1	232.5	241.8	259.6	281.1	314.1	372.1
62.5°	191.5	190.7	193.9	197.1	200.5	208.2	216.1	229.7	246.6	274.6	320.6
65°	158.7	160.2	161.5	162.9	164.8	169.4	176.9	186.3	198.0	217.6	250.7
67.5°	124.8	126.2	126.6	129.5	133.5	136.4	141.0	149.3	157.4	174.0	192.8
70°	100.9	100.4	100.9	102.3	107.4	112.5	118.6	124.7	129.7	141.4	157.3
72.5°	86.7	85.8	87.0	87.3	89.8	91.2	95.1	100.8	107.4	115.3	126.7
75°	67.2	67.2	67.2	67.2	69.1	70.0	71.4	72.9	75.2	78.9	87.3
77.5°	49.7	49.8	50.4	50.9	51.3	51.8	52.7	54.0	54.9	56.9	60.5
80°	39.2	39.7	39.2	39.7	39.7	40.6	41.1	42.4	43.0	45.3	46.7
82.5°	29.5	29.2	29.5	30.0	30.0	30.9	31.0	32.0	32.1	33.3	34.8
85°	15.9	15.0	15.9	15.4	16.3	15.4	15.9	16.8	16.8	17.3	19.2
87.5°	7.8	8.6	7.8	8.0	8.1	8.2	8.1	7.9	8.6	8.4	8.3
90°	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4	16.8	17.4	15.3
92.5°	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7	80.9	107.2	118.0
95°	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0	335.4	413.4	368.1
97.5°	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6	685.5	640.7	469.0
100°	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0	797.5	660.2	446.2
102.5°	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2	803.2	623.9	412.7
105°	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3	760.6	560.5	371.6
107.5°	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4	686.2	504.4	345.4
110°	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0	639.3	472.7	335.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1	598.6	451.5	329.8
115°	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3	549.4	428.7	327.7
117.5°	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6	519.7	415.4	329.0
120°	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4	504.1	409.2	331.2
122.5°	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8	491.2	405.4	335.0
125°	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2	474.7	400.2	340.9
127.5°	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3	460.3	397.7	347.6
130°	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2	452.5	396.0	352.0
132.5°	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2	445.2	395.4	355.4
135°	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4	435.7	394.6	360.4
137.5°	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3	427.5	393.1	363.8
140°	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2	422.5	392.5	366.0
142.5°	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8	418.0	391.4	367.7
145°	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4	412.1	389.7	368.8
147.5°	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0	406.2	387.1	368.8
150°	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3	402.3	384.9	368.8
152.5°	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1	397.8	382.0	367.1
155°	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0	391.1	377.2	365.3
157.5°	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2	383.6	372.8	362.9
160°	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6	378.5	369.5	361.9
162.5°	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9	373.5	366.1	359.6
165°	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3	366.7	361.1	356.2
167.5°	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7	360.2	356.1	352.9
170°	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7	356.2	352.8	350.7
172.5°	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3	352.3	350.0	349.0
175°	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3	347.9	346.5	346.5
177.5°	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1126.1	1124.9	1119.7	1113.7	1105.9	1100.6	1096.5	1094.3	1087.6	1079.3	1073.8
5°	1195.6	1181.6	1166.7	1148.4	1131.7	1114.4	1103.7	1091.0	1075.7	1058.4	1046.2
7.5°	1270.2	1242.7	1213.1	1182.6	1152.4	1125.3	1101.4	1080.9	1056.4	1031.6	1014.3
10°	1327.3	1287.1	1245.5	1203.1	1164.3	1127.9	1099.9	1072.4	1042.9	1014.5	993.0
12.5°	1379.2	1326.3	1278.4	1226.3	1176.7	1133.2	1092.8	1060.4	1025.0	994.7	970.2
15°	1444.9	1390.8	1332.8	1253.5	1187.7	1132.6	1083.6	1041.1	998.2	960.8	937.0
17.5°	1506.4	1424.9	1347.1	1280.9	1195.3	1126.5	1066.7	1015.8	968.8	929.2	899.8
20°	1531.8	1452.9	1368.3	1283.9	1199.8	1122.8	1053.2	997.2	948.2	903.4	876.3
22.5°	1547.0	1457.7	1368.7	1277.9	1188.7	1108.6	1039.8	978.1	925.1	882.4	849.0
25°	1564.9	1458.5	1360.4	1270.8	1179.7	1092.9	1011.2	945.8	888.4	843.1	807.6
27.5°	1576.6	1451.4	1335.6	1235.9	1143.6	1057.1	982.2	913.0	854.7	806.8	768.7
30°	1578.9	1445.8	1316.5	1208.7	1114.8	1035.5	956.1	889.8	828.2	777.3	741.8
32.5°	1581.9	1432.0	1290.8	1176.2	1080.1	1001.5	929.6	866.3	803.2	753.0	716.8
35°	1569.6	1424.4	1251.6	1120.0	1023.8	947.7	882.8	824.5	762.4	713.8	676.9
37.5°	1516.5	1394.0	1211.1	1056.7	956.1	885.6	832.8	781.9	725.0	672.5	637.8
40°	1463.1	1364.1	1179.7	1018.2	913.2	840.8	793.2	751.6	696.5	647.6	610.2
42.5°	1383.6	1323.5	1149.9	977.9	864.6	794.9	754.7	715.8	667.4	617.7	582.6
45°	1237.6	1245.5	1088.7	913.6	797.4	727.4	689.6	662.5	619.6	578.5	542.5
47.5°	1054.6	1128.8	1016.9	845.2	726.5	660.8	627.8	604.1	575.2	534.8	502.0
50°	935.1	1041.1	959.4	799.2	682.1	616.7	584.1	564.9	539.7	507.9	476.6
52.5°	824.9	938.8	889.9	748.1	633.9	574.2	542.2	526.5	506.4	476.5	448.3
55°	672.7	788.1	776.9	670.8	561.6	507.9	483.7	465.9	452.4	430.0	407.6
57.5°	544.2	653.5	659.3	585.0	497.9	444.9	424.0	410.6	401.8	384.9	364.2
60°	463.2	563.5	583.1	527.1	452.4	405.7	385.1	374.4	367.4	353.9	338.0
62.5°	395.9	481.3	503.5	463.2	408.7	365.0	348.9	338.6	333.8	322.1	308.1
65°	303.0	374.0	395.4	373.0	344.6	309.5	296.5	287.6	283.4	276.9	266.5
67.5°	227.8	279.6	303.1	287.3	277.1	254.9	246.6	241.8	238.1	233.6	225.1
70°	183.0	221.3	245.6	241.4	233.0	221.3	215.3	212.0	208.2	204.5	197.0
72.5°	147.1	173.5	196.3	198.4	191.5	189.1	183.9	182.4	180.2	175.8	171.7
75°	97.6	115.7	131.6	137.7	140.5	142.9	140.5	140.1	139.6	135.9	133.5
77.5°	63.9	73.7	83.7	94.1	98.5	101.7	102.5	104.2	102.9	100.9	99.8
80°	49.0	51.4	58.3	67.2	74.2	77.0	78.9	79.8	79.4	78.9	77.0
82.5°	35.6	37.5	40.8	47.1	53.0	57.6	58.8	58.6	59.6	59.8	58.3
85°	19.2	19.6	20.5	21.5	24.7	29.9	31.3	32.2	33.2	33.2	30.3
87.5°	8.6	7.8	8.2	7.8	8.7	8.6	10.6	12.2	12.8	11.7	12.1
90°	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4	2.8	4.2	6.2
92.5°	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6	12.8	18.7	24.2
95°	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7	25.8	33.4	45.3
97.5°	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4	41.1	47.2	57.4
100°	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6	52.3	57.2	67.0
102.5°	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3	64.6	68.8	78.1
105°	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9	82.9	87.1	95.5
107.5°	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5	101.7	105.7	113.9
110°	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0	115.0	118.5	126.2



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2	127.3	130.8	138.5
115°	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9	145.7	149.9	156.9
117.5°	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6	163.8	167.3	173.7
120°	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9	175.0	178.4	185.5
122.5°	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5	185.6	189.0	196.6
125°	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7	200.1	204.3	212.0
127.5°	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3	212.3	217.5	225.3
130°	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5	219.6	225.9	234.3
132.5°	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1	225.8	232.6	242.6
135°	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8	235.7	243.3	253.8
137.5°	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0	245.0	252.5	263.7
140°	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2	251.6	258.7	269.8
142.5°	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9	257.8	265.4	275.4
145°	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6	267.7	274.0	284.5
147.5°	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5	277.8	283.9	292.9
150°	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7	284.5	290.0	299.1
152.5°	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0	291.1	296.7	304.7
155°	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8	301.8	306.0	313.0
157.5°	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5	311.0	314.4	320.6
160°	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2	317.2	320.0	325.6
162.5°	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3	322.3	324.5	329.0
165°	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8	329.0	330.5	333.9
167.5°	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5	334.7	335.4	338.0
170°	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9	337.4	338.1	340.2
172.5°	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1	340.2	340.4	341.9
175°	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7	343.0	342.3	343.7
177.5°	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9	344.4	343.8	344.4
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1071.9	1067.0	1063.7	1056.2	1051.3	1046.2	1040.9	1044.3	1043.9	1043.5	1043.5
5°	1036.0	1025.2	1015.4	1002.8	994.9	985.1	977.6	976.7	978.6	972.0	968.2
7.5°	1000.3	985.6	971.7	957.8	943.1	931.3	923.9	920.4	915.7	911.7	907.5
10°	975.3	958.0	944.4	927.2	911.3	897.3	888.4	882.3	879.0	875.8	869.8
12.5°	949.5	932.6	915.3	895.8	880.7	864.4	857.8	851.0	844.7	841.1	832.8
15°	911.8	889.8	871.6	851.0	834.3	818.4	809.0	795.5	793.6	789.0	780.6
17.5°	874.0	850.2	825.0	809.9	790.9	774.4	760.1	755.5	742.2	737.2	729.9
20°	844.1	822.2	803.0	782.9	755.4	739.9	728.8	722.7	711.9	705.4	700.7
22.5°	818.3	796.0	773.8	750.5	727.7	710.4	702.2	692.8	687.0	677.8	672.7
25°	781.5	757.2	730.7	705.4	689.1	676.0	662.9	654.5	646.1	641.9	632.6
27.5°	738.8	713.4	688.5	669.4	649.3	636.4	624.6	617.1	607.0	599.9	594.8
30°	715.2	685.4	663.9	646.6	620.9	608.8	599.9	590.6	583.1	575.6	570.5
32.5°	688.0	660.7	640.3	618.9	599.2	586.0	574.5	566.3	559.9	552.9	547.7
35°	645.2	622.3	601.3	579.8	565.3	551.8	538.3	531.3	525.2	518.7	514.0
37.5°	606.5	585.1	565.2	544.8	526.9	515.9	505.0	499.6	491.4	487.1	482.2
40°	582.6	561.6	540.1	520.6	501.9	493.5	483.7	475.7	468.2	465.0	459.9
42.5°	556.5	535.5	517.4	496.2	481.0	469.6	460.5	451.8	446.2	441.5	438.5
45°	517.7	499.1	481.3	460.3	445.9	436.0	425.8	417.9	412.7	409.5	404.3
47.5°	480.1	461.5	443.4	425.1	411.1	399.9	389.7	384.1	377.3	373.3	369.9
50°	452.8	436.0	416.9	400.1	386.1	374.9	366.5	359.4	353.4	348.3	346.0
52.5°	427.8	409.9	393.3	377.7	362.9	350.3	342.6	335.2	330.6	324.8	322.0
55°	386.6	369.3	355.3	339.8	325.4	314.7	305.3	298.8	294.1	287.6	283.8
57.5°	347.8	332.3	315.6	302.2	287.3	278.2	270.5	261.6	255.9	250.8	247.2
60°	321.6	303.9	289.4	276.9	263.8	252.1	245.1	238.1	232.0	226.9	223.6
62.5°	294.4	278.9	265.2	251.5	239.5	229.3	221.2	215.3	210.0	206.7	203.5
65°	252.5	240.4	226.4	215.3	204.0	196.5	190.0	184.9	181.1	178.8	176.0
67.5°	214.1	202.3	190.1	179.1	171.7	165.9	161.7	157.2	155.3	152.4	150.5
70°	189.0	176.9	166.2	157.8	150.3	146.2	143.3	140.1	138.2	134.5	132.6
72.5°	161.8	153.0	145.3	138.4	132.4	128.6	125.0	121.0	118.1	113.9	112.1
75°	127.4	119.5	113.4	108.8	105.0	99.9	94.8	90.6	89.2	87.7	87.3
77.5°	94.4	89.3	85.0	81.1	76.4	72.7	71.5	70.6	70.3	69.6	69.6
80°	74.2	69.6	66.3	61.6	58.9	58.9	58.9	57.9	58.3	58.3	58.3
82.5°	55.2	50.9	49.1	47.4	46.9	47.3	47.3	47.4	47.2	47.9	47.5
85°	28.4	29.0	29.9	29.4	29.9	29.9	30.9	30.3	30.9	29.9	30.9
87.5°	11.9	13.4	14.2	15.0	15.8	15.8	16.1	16.1	16.7	16.9	17.1
90°	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4	18.1	18.8	20.2
92.5°	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7	46.5	41.1	37.5
95°	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0	170.1	133.1	108.1
97.5°	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6	501.1	411.2	327.8
100°	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0	765.4	683.9	584.9
102.5°	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2	885.4	837.9	775.1
105°	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3	976.0	989.3	971.2
107.5°	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4	964.6	1025.6	1050.4
110°	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0	927.2	1015.0	1063.9



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1	878.2	976.6	1039.3
115°	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3	799.6	902.1	978.1
117.5°	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6	733.3	825.3	902.4
120°	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4	696.4	780.2	850.5
122.5°	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8	666.9	744.4	809.9
125°	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2	630.3	697.1	753.0
127.5°	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3	598.0	658.4	709.2
130°	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2	577.9	634.5	681.8
132.5°	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2	559.0	611.5	656.7
135°	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4	531.9	577.2	617.0
137.5°	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3	505.9	544.9	579.3
140°	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2	490.8	524.2	554.2
142.5°	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8	476.3	505.3	531.4
145°	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4	457.4	479.7	499.9
147.5°	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0	443.3	461.3	475.6
150°	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3	434.4	449.0	462.2
152.5°	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1	426.0	438.9	450.0
155°	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0	414.1	424.5	432.9
157.5°	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2	402.5	410.6	417.1
160°	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6	395.3	402.3	407.2
162.5°	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9	387.4	393.9	398.2
165°	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3	376.5	381.4	384.9
167.5°	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7	367.9	370.8	373.3
170°	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7	361.9	364.6	366.0
172.5°	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3	356.8	359.0	359.9
175°	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3	350.0	351.3	351.3
177.5°	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5	346.1	346.6	346.6
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1039.0	1038.7	1039.0	1037.5	1039.0	1038.7	1039.0	1043.5	1043.5	1043.9	1044.3
5°	966.9	966.3	965.0	960.8	965.0	966.3	966.9	968.2	972.0	978.6	976.7
7.5°	903.8	903.2	899.1	899.2	899.1	903.2	903.8	907.5	911.7	915.7	920.4
10°	866.5	866.9	861.4	858.1	861.4	866.9	866.5	869.8	875.8	879.0	882.3
12.5°	830.3	828.1	823.6	820.0	823.6	828.1	830.3	832.8	841.1	844.7	851.0
15°	782.5	777.8	766.6	767.5	766.6	777.8	782.5	780.6	789.0	793.6	795.5
17.5°	726.1	722.7	722.5	716.0	722.5	722.7	726.1	729.9	737.2	742.2	755.5
20°	693.3	691.0	691.9	685.4	691.9	691.0	693.3	700.7	705.4	711.9	722.7
22.5°	667.5	665.2	661.3	659.2	661.3	665.2	667.5	672.7	677.8	687.0	692.8
25°	629.8	626.1	622.3	624.6	622.3	626.1	629.8	632.6	641.9	646.1	654.5
27.5°	592.1	589.2	585.5	585.1	585.5	589.2	592.1	594.8	599.9	607.0	617.1
30°	568.2	565.3	563.5	561.2	563.5	565.3	568.2	570.5	575.6	583.1	590.6
32.5°	543.9	543.3	539.9	539.5	539.9	543.3	543.9	547.7	552.9	559.9	566.3
35°	512.1	509.3	508.4	508.9	508.4	509.3	512.1	514.0	518.7	525.2	531.3
37.5°	482.0	478.2	476.5	474.9	476.5	478.2	482.0	482.2	487.1	491.4	499.6
40°	460.3	456.6	455.7	454.7	455.7	456.6	460.3	459.9	465.0	468.2	475.7
42.5°	436.0	434.5	434.0	432.3	434.0	434.5	436.0	438.5	441.5	446.2	451.8
45°	402.9	402.4	399.7	400.6	399.7	402.4	402.9	404.3	409.5	412.7	417.9
47.5°	368.0	366.0	364.0	365.2	364.0	366.0	368.0	369.9	373.3	377.3	384.1
50°	344.1	343.1	338.9	339.8	338.9	343.1	344.1	346.0	348.3	353.4	359.4
52.5°	320.2	316.6	315.0	314.5	315.0	316.6	320.2	322.0	324.8	330.6	335.2
55°	280.6	276.3	274.5	273.6	274.5	276.3	280.6	283.8	287.6	294.1	298.8
57.5°	241.7	240.6	239.2	240.1	239.2	240.6	241.7	247.2	250.8	255.9	261.6
60°	218.9	218.9	218.9	218.5	218.9	218.9	218.9	223.6	226.9	232.0	238.1
62.5°	201.4	200.3	199.9	200.5	199.9	200.3	201.4	203.5	206.7	210.0	215.3
65°	174.6	174.2	172.3	171.8	172.3	174.2	174.6	176.0	178.8	181.1	184.9
67.5°	149.3	147.6	147.0	146.4	147.0	147.6	149.3	150.5	152.4	155.3	157.2
70°	130.3	129.3	126.5	127.0	126.5	129.3	130.3	132.6	134.5	138.2	140.1
72.5°	109.7	108.8	108.3	107.5	108.3	108.8	109.7	112.1	113.9	118.1	121.0
75°	86.9	86.4	85.9	87.7	85.9	86.4	86.9	87.3	87.7	89.2	90.6
77.5°	69.6	69.6	69.8	69.1	69.8	69.6	69.6	69.6	69.6	70.3	70.6
80°	58.3	58.3	57.9	57.9	57.9	58.3	58.3	58.3	58.3	58.3	57.9
82.5°	46.8	47.2	47.4	46.7	47.4	47.2	46.8	47.5	47.9	47.2	47.4
85°	30.9	30.3	31.3	30.9	31.3	30.3	30.9	30.9	29.9	30.9	30.3
87.5°	17.7	17.1	17.3	17.5	17.3	17.1	17.7	17.1	16.9	16.7	16.1
90°	19.5	20.2	21.0	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4
92.5°	36.3	34.2	34.9	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7
95°	94.8	88.5	83.6	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0
97.5°	276.3	245.0	226.1	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6
100°	514.5	463.6	436.4	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0
102.5°	720.3	680.0	657.3	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2
105°	939.1	912.6	890.3	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3
107.5°	1051.1	1042.1	1034.6	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4
110°	1083.3	1089.0	1087.5	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1075.0	1092.3	1097.6	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1
115°	1030.4	1061.0	1075.0	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3
117.5°	956.9	992.0	1012.1	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6
120°	905.6	944.7	961.4	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4
122.5°	858.7	893.9	912.3	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8
125°	797.5	828.2	845.6	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2
127.5°	748.9	775.1	790.9	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3
130°	718.8	743.9	758.5	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2
132.5°	691.4	716.6	729.5	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2
135°	651.1	672.1	684.6	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4
137.5°	608.1	629.3	639.9	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3
140°	580.8	600.2	611.4	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2
142.5°	553.9	571.2	581.3	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8
145°	517.3	531.9	537.5	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4
147.5°	488.8	498.7	504.1	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0
150°	472.7	480.4	484.6	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3
152.5°	458.2	465.3	467.8	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1
155°	439.2	444.8	446.2	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0
157.5°	422.6	426.8	427.9	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2
160°	412.1	416.2	416.2	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6
162.5°	401.4	405.0	405.0	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9
165°	387.6	390.4	389.7	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3
167.5°	374.5	376.5	375.8	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7
170°	366.7	368.1	367.4	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7
172.5°	360.0	361.4	360.2	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3
175°	351.3	352.0	351.3	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3
177.5°	346.1	346.6	345.5	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1040.9	1046.2	1051.3	1056.2	1063.7	1067.0	1071.9	1073.8	1079.3	1087.6	1094.3
5°	977.6	985.1	994.9	1002.8	1015.4	1025.2	1036.0	1046.2	1058.4	1075.7	1091.0
7.5°	923.9	931.3	943.1	957.8	971.7	985.6	1000.3	1014.3	1031.6	1056.4	1080.9
10°	888.4	897.3	911.3	927.2	944.4	958.0	975.3	993.0	1014.5	1042.9	1072.4
12.5°	857.8	864.4	880.7	895.8	915.3	932.6	949.5	970.2	994.7	1025.0	1060.4
15°	809.0	818.4	834.3	851.0	871.6	889.8	911.8	937.0	960.8	998.2	1041.1
17.5°	760.1	774.4	790.9	809.9	825.0	850.2	874.0	899.8	929.2	968.8	1015.8
20°	728.8	739.9	755.4	782.9	803.0	822.2	844.1	876.3	903.4	948.2	997.2
22.5°	702.2	710.4	727.7	750.5	773.8	796.0	818.3	849.0	882.4	925.1	978.1
25°	662.9	676.0	689.1	705.4	730.7	757.2	781.5	807.6	843.1	888.4	945.8
27.5°	624.6	636.4	649.3	669.4	688.5	713.4	738.8	768.7	806.8	854.7	913.0
30°	599.9	608.8	620.9	646.6	663.9	685.4	715.2	741.8	777.3	828.2	889.8
32.5°	574.5	586.0	599.2	618.9	640.3	660.7	688.0	716.8	753.0	803.2	866.3
35°	538.3	551.8	565.3	579.8	601.3	622.3	645.2	676.9	713.8	762.4	824.5
37.5°	505.0	515.9	526.9	544.8	565.2	585.1	606.5	637.8	672.5	725.0	781.9
40°	483.7	493.5	501.9	520.6	540.1	561.6	582.6	610.2	647.6	696.5	751.6
42.5°	460.5	469.6	481.0	496.2	517.4	535.5	556.5	582.6	617.7	667.4	715.8
45°	425.8	436.0	445.9	460.3	481.3	499.1	517.7	542.5	578.5	619.6	662.5
47.5°	389.7	399.9	411.1	425.1	443.4	461.5	480.1	502.0	534.8	575.2	604.1
50°	366.5	374.9	386.1	400.1	416.9	436.0	452.8	476.6	507.9	539.7	564.9
52.5°	342.6	350.3	362.9	377.7	393.3	409.9	427.8	448.3	476.5	506.4	526.5
55°	305.3	314.7	325.4	339.8	355.3	369.3	386.6	407.6	430.0	452.4	465.9
57.5°	270.5	278.2	287.3	302.2	315.6	332.3	347.8	364.2	384.9	401.8	410.6
60°	245.1	252.1	263.8	276.9	289.4	303.9	321.6	338.0	353.9	367.4	374.4
62.5°	221.2	229.3	239.5	251.5	265.2	278.9	294.4	308.1	322.1	333.8	338.6
65°	190.0	196.5	204.0	215.3	226.4	240.4	252.5	266.5	276.9	283.4	287.6
67.5°	161.7	165.9	171.7	179.1	190.1	202.3	214.1	225.1	233.6	238.1	241.8
70°	143.3	146.2	150.3	157.8	166.2	176.9	189.0	197.0	204.5	208.2	212.0
72.5°	125.0	128.6	132.4	138.4	145.3	153.0	161.8	171.7	175.8	180.2	182.4
75°	94.8	99.9	105.0	108.8	113.4	119.5	127.4	133.5	135.9	139.6	140.1
77.5°	71.5	72.7	76.4	81.1	85.0	89.3	94.4	99.8	100.9	102.9	104.2
80°	58.9	58.9	58.9	61.6	66.3	69.6	74.2	77.0	78.9	79.4	79.8
82.5°	47.3	47.3	46.9	47.4	49.1	50.9	55.2	58.3	59.8	59.6	58.6
85°	30.9	29.9	29.9	29.4	29.9	29.0	28.4	30.3	33.2	33.2	32.2
87.5°	16.1	15.8	15.8	15.0	14.2	13.4	11.9	12.1	11.7	12.8	12.2
90°	16.8	17.4	15.3	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4
92.5°	80.9	107.2	118.0	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6
95°	335.4	413.4	368.1	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7
97.5°	685.5	640.7	469.0	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4
100°	797.5	660.2	446.2	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6
102.5°	803.2	623.9	412.7	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3
105°	760.6	560.5	371.6	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9
107.5°	686.2	504.4	345.4	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5
110°	639.3	472.7	335.4	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	598.6	451.5	329.8	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2
115°	549.4	428.7	327.7	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9
117.5°	519.7	415.4	329.0	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6
120°	504.1	409.2	331.2	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9
122.5°	491.2	405.4	335.0	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5
125°	474.7	400.2	340.9	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7
127.5°	460.3	397.7	347.6	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3
130°	452.5	396.0	352.0	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5
132.5°	445.2	395.4	355.4	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1
135°	435.7	394.6	360.4	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8
137.5°	427.5	393.1	363.8	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0
140°	422.5	392.5	366.0	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2
142.5°	418.0	391.4	367.7	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9
145°	412.1	389.7	368.8	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6
147.5°	406.2	387.1	368.8	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5
150°	402.3	384.9	368.8	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7
152.5°	397.8	382.0	367.1	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0
155°	391.1	377.2	365.3	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8
157.5°	383.6	372.8	362.9	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5
160°	378.5	369.5	361.9	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2
162.5°	373.5	366.1	359.6	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3
165°	366.7	361.1	356.2	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8
167.5°	360.2	356.1	352.9	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5
170°	356.2	352.8	350.7	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9
172.5°	352.3	350.0	349.0	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1
175°	347.9	346.5	346.5	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7
177.5°	344.9	344.4	344.9	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1096.5	1100.6	1105.9	1113.7	1119.7	1124.9	1126.1	1127.6	1131.3	1137.6	1142.5
5°	1103.7	1114.4	1131.7	1148.4	1166.7	1181.6	1195.6	1205.4	1214.8	1234.4	1250.3
7.5°	1101.4	1125.3	1152.4	1182.6	1213.1	1242.7	1270.2	1294.7	1319.1	1347.7	1380.3
10°	1099.9	1127.9	1164.3	1203.1	1245.5	1287.1	1327.3	1358.5	1395.0	1427.6	1469.2
12.5°	1092.8	1133.2	1176.7	1226.3	1278.4	1326.3	1379.2	1422.5	1464.1	1511.3	1559.6
15°	1083.6	1132.6	1187.7	1253.5	1332.8	1390.8	1444.9	1520.1	1571.5	1622.8	1691.8
17.5°	1066.7	1126.5	1195.3	1280.9	1347.1	1424.9	1506.4	1565.8	1635.0	1707.3	1769.9
20°	1053.2	1122.8	1199.8	1283.9	1368.3	1452.9	1531.8	1602.7	1674.2	1757.7	1809.1
22.5°	1039.8	1108.6	1188.7	1277.9	1368.7	1457.7	1547.0	1630.3	1710.7	1795.1	1860.6
25°	1011.2	1092.9	1179.7	1270.8	1360.4	1458.5	1564.9	1657.8	1757.2	1844.1	1906.2
27.5°	982.2	1057.1	1143.6	1235.9	1335.6	1451.4	1576.6	1682.3	1781.9	1844.1	1863.6
30°	956.1	1035.5	1114.8	1208.7	1316.5	1445.8	1578.9	1699.8	1781.5	1808.6	1788.5
32.5°	929.6	1001.5	1080.1	1176.2	1290.8	1432.0	1581.9	1689.3	1738.6	1717.9	1636.1
35°	882.8	947.7	1023.8	1120.0	1251.6	1424.4	1569.6	1642.4	1630.2	1513.5	1359.5
37.5°	832.8	885.6	956.1	1056.7	1211.1	1394.0	1516.5	1527.2	1422.2	1243.0	1065.1
40°	793.2	840.8	913.2	1018.2	1179.7	1364.1	1463.1	1419.7	1256.8	1057.4	909.0
42.5°	754.7	794.9	864.6	977.9	1149.9	1323.5	1383.6	1289.0	1101.0	912.5	777.5
45°	689.6	727.4	797.4	913.6	1088.7	1245.5	1237.6	1073.3	885.2	733.4	621.3
47.5°	627.8	660.8	726.5	845.2	1016.9	1128.8	1054.6	879.8	720.1	598.4	518.5
50°	584.1	616.7	682.1	799.2	959.4	1041.1	935.1	766.6	620.5	519.6	456.1
52.5°	542.2	574.2	633.9	748.1	889.9	938.8	824.9	668.7	546.9	459.9	405.3
55°	483.7	507.9	561.6	670.8	776.9	788.1	672.7	542.0	441.7	380.9	343.6
57.5°	424.0	444.9	497.9	585.0	659.3	653.5	544.2	431.1	363.5	318.4	291.3
60°	385.1	405.7	452.4	527.1	583.1	563.5	463.2	372.1	314.1	281.1	259.6
62.5°	348.9	365.0	408.7	463.2	503.5	481.3	395.9	320.6	274.6	246.6	229.7
65°	296.5	309.5	344.6	373.0	395.4	374.0	303.0	250.7	217.6	198.0	186.3
67.5°	246.6	254.9	277.1	287.3	303.1	279.6	227.8	192.8	174.0	157.4	149.3
70°	215.3	221.3	233.0	241.4	245.6	221.3	183.0	157.3	141.4	129.7	124.7
72.5°	183.9	189.1	191.5	198.4	196.3	173.5	147.1	126.7	115.3	107.4	100.8
75°	140.5	142.9	140.5	137.7	131.6	115.7	97.6	87.3	78.9	75.2	72.9
77.5°	102.5	101.7	98.5	94.1	83.7	73.7	63.9	60.5	56.9	54.9	54.0
80°	78.9	77.0	74.2	67.2	58.3	51.4	49.0	46.7	45.3	43.0	42.4
82.5°	58.8	57.6	53.0	47.1	40.8	37.5	35.6	34.8	33.3	32.1	32.0
85°	31.3	29.9	24.7	21.5	20.5	19.6	19.2	19.2	17.3	16.8	16.8
87.5°	10.6	8.6	8.7	7.8	8.2	7.8	8.6	8.3	8.4	8.6	7.9
90°	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4
92.5°	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7
95°	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0
97.5°	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6
100°	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0
102.5°	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2
105°	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3
107.5°	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4
110°	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1
115°	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3
117.5°	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6
120°	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4
122.5°	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8
125°	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2
127.5°	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3
130°	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2
132.5°	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2
135°	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4
137.5°	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3
140°	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2
142.5°	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8
145°	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4
147.5°	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0
150°	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3
152.5°	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1
155°	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0
157.5°	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2
160°	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6
162.5°	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9
165°	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3
167.5°	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7
170°	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7
172.5°	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3
175°	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3
177.5°	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1150.3	1150.3	1151.8	1157.4	1158.2	1163.1	1161.5
5°	1264.3	1273.1	1276.4	1290.4	1298.8	1302.5	1295.0
7.5°	1403.6	1428.6	1440.5	1455.1	1468.1	1472.0	1461.8
10°	1505.1	1531.2	1553.3	1566.7	1579.4	1587.8	1598.5
12.5°	1603.4	1635.5	1656.4	1675.4	1688.5	1699.1	1700.8
15°	1710.1	1758.6	1795.5	1822.6	1836.1	1843.2	1840.3
17.5°	1817.8	1862.8	1889.0	1916.6	1935.4	1936.4	1936.9
20°	1878.7	1922.5	1952.8	1973.4	1994.4	1993.5	1998.1
22.5°	1919.3	1953.9	1977.1	1992.1	1999.3	1995.7	1996.6
25°	1938.4	1948.7	1944.5	1920.7	1914.6	1892.7	1896.4
27.5°	1840.1	1791.6	1741.3	1676.8	1625.8	1585.1	1587.2
30°	1706.8	1621.0	1522.9	1440.7	1367.0	1346.4	1302.5
32.5°	1520.5	1391.6	1276.8	1200.2	1136.8	1119.7	1081.5
35°	1204.5	1079.3	961.3	890.3	862.3	823.0	822.6
37.5°	936.2	826.1	763.6	710.3	682.4	658.7	656.4
40°	787.6	701.7	654.5	616.3	588.7	571.0	566.8
42.5°	683.8	614.3	570.2	546.4	525.2	516.0	509.3
45°	558.4	511.7	480.9	459.4	449.6	442.6	438.8
47.5°	467.1	435.8	414.7	400.5	392.5	385.1	387.1
50°	417.4	391.7	376.3	362.7	356.7	351.5	352.0
52.5°	377.4	354.4	341.9	332.2	324.6	320.9	319.1
55°	320.3	305.8	293.2	286.1	282.0	276.9	275.4
57.5°	273.2	262.0	251.7	243.8	242.7	237.8	238.4
60°	241.8	232.5	224.1	219.9	216.6	212.4	213.8
62.5°	216.1	208.2	200.5	197.1	193.9	190.7	191.5
65°	176.9	169.4	164.8	162.9	161.5	160.2	158.7
67.5°	141.0	136.4	133.5	129.5	126.6	126.2	124.8
70°	118.6	112.5	107.4	102.3	100.9	100.4	100.9
72.5°	95.1	91.2	89.8	87.3	87.0	85.8	86.7
75°	71.4	70.0	69.1	67.2	67.2	67.2	67.2
77.5°	52.7	51.8	51.3	50.9	50.4	49.8	49.7
80°	41.1	40.6	39.7	39.7	39.2	39.7	39.2
82.5°	31.0	30.9	30.0	30.0	29.5	29.2	29.5
85°	15.9	15.4	16.3	15.4	15.9	15.0	15.9
87.5°	8.1	8.2	8.1	8.0	7.8	8.6	7.8
90°	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P332314-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)