

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332315-940

Luminaire Tested: **S123RDIP-S775D805U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332315-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5464.9 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35
3	81	72	65	59	75	67	61	56	56	52	48	47	44	41	38	36	34	30
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12392	12392	12392
5°	12440	12268	12338
10°	12369	12114	12073
15°	12237	11830	11705
20°	12054	11475	11208
25°	11866	11077	10723
30°	11616	10618	10038
35°	11361	10159	9410
40°	11126	9617	8633
45°	10816	9082	7931
50°	10474	8473	7145
55°	10128	7781	6412
60°	9810	7035	5608
65°	9393	6230	4804
70°	8875	5231	3877
75°	8114	4117	3647
80°	7234	3651	3353
85°	6113	3223	3001



TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	2.0
10°-20°	300.8	5.5
20°-30°	433.1	7.9
30°-40°	487.9	8.9
40°-50°	466.7	8.5
50°-60°	382.2	7.0
60°-70°	257.9	4.7
70°-80°	129.7	2.4
80°-90°	37.0	0.7
90°-100°	34.1	0.6
100°-110°	162.6	3.0
110°-120°	390.6	7.1
120°-130°	497.3	9.1
130°-140°	531.4	9.7
140°-150°	496.9	9.1
150°-160°	400.8	7.3
160°-170°	258.7	4.7
170°-180°	89.2	1.6
0°-30°	842.0	15.4
0°-40°	1329.9	24.3
0°-60°	2178.8	39.9
0°-90°	2603.4	47.6
90°-120°	587.3	10.7
90°-150°	2112.9	38.7
90°-180°	2862.0	52.4
0°-180°	5464.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1151	1146	1135	1143	1142	109
15°	1098	1087	1062	1057	1050	309
25°	999	975	933	914	903	459
35°	865	830	773	734	716	541
45°	710	667	597	545	521	548
55°	540	492	415	362	342	484
65°	369	316	245	201	189	365
75°	195	150	99	90	88	208
85°	50	30	26	24	24	56
90°	1	8	17	19	21	4
95°	42	16	22	26	26	53
105°	208	212	153	36	31	220
115°	390	394	400	407	410	385
125°	549	555	558	559	560	490
135°	684	688	691	693	691	526
145°	789	794	795	797	797	494
155°	869	868	869	872	868	400
165°	917	915	914	919	915	259
175°	938	935	936	940	935	89
180°	938	938	938	938	938	



TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1154.9	1154.3	1153.6	1153.0	1152.4	1151.0	1149.0	1147.0	1145.0	1143.0	1144.9
5°	1151.3	1150.2	1149.1	1148.2	1147.1	1145.3	1142.8	1140.3	1137.8	1135.4	1137.2
7.5°	1140.6	1139.5	1138.4	1137.2	1136.1	1133.9	1130.7	1127.5	1124.3	1121.0	1122.0
10°	1131.7	1130.2	1128.7	1127.3	1125.8	1123.2	1119.5	1115.8	1112.1	1108.3	1108.5
12.5°	1118.9	1117.3	1115.7	1114.1	1112.5	1109.4	1104.8	1100.3	1095.6	1091.1	1091.0
15°	1098.1	1095.7	1093.4	1091.2	1088.9	1084.9	1079.1	1073.3	1067.4	1061.6	1060.6
17.5°	1071.7	1069.1	1066.4	1063.7	1061.0	1056.1	1048.7	1041.3	1033.8	1026.5	1024.3
20°	1052.3	1048.9	1045.6	1042.3	1039.0	1033.4	1025.5	1017.6	1009.8	1001.8	999.2
22.5°	1030.6	1026.8	1023.0	1019.1	1015.3	1009.2	1000.9	992.5	984.1	975.7	972.3
25°	999.1	993.9	988.6	983.5	978.3	970.9	961.4	951.8	942.3	932.7	928.4
27.5°	960.7	955.0	949.3	943.6	937.9	929.7	919.1	908.5	897.8	887.2	881.1
30°	934.6	928.4	922.2	916.0	909.7	900.8	889.2	877.5	865.9	854.3	847.3
32.5°	908.5	901.4	894.4	887.3	880.3	870.6	858.3	846.1	833.7	821.4	813.8
35°	864.6	857.1	849.6	842.2	834.7	824.6	811.7	798.8	786.0	773.1	764.2
37.5°	820.2	811.8	803.5	795.2	786.9	776.0	762.2	748.5	734.8	721.0	710.9
40°	791.8	782.7	773.5	764.4	755.3	743.3	728.6	713.9	699.1	684.4	673.6
42.5°	759.6	750.6	741.4	732.3	723.2	711.0	695.7	680.5	665.3	650.1	638.3
45°	710.5	701.2	691.9	682.5	673.2	660.6	644.5	628.6	612.6	596.6	584.8
47.5°	661.5	651.2	641.0	630.7	620.5	607.3	591.4	575.3	559.4	543.4	530.6
50°	625.5	615.8	606.1	596.3	586.6	573.3	556.5	539.7	522.9	506.0	493.2
52.5°	593.4	582.9	572.3	561.7	551.2	537.5	520.8	504.3	487.6	470.9	457.6
55°	539.7	529.5	519.3	509.2	499.0	485.1	467.4	449.9	432.2	414.6	402.5
57.5°	490.0	478.9	467.9	456.7	445.7	431.3	413.6	395.8	378.1	360.4	349.0
60°	455.7	444.3	432.8	421.4	410.0	395.7	378.4	361.2	344.0	326.8	315.6
62.5°	421.2	409.8	398.4	387.0	375.7	361.3	344.1	326.9	309.7	292.4	281.9
65°	368.8	357.4	346.0	334.6	323.2	309.3	293.2	277.0	260.8	244.6	234.4
67.5°	316.4	304.8	293.3	281.7	270.2	256.6	241.1	225.6	210.1	194.6	187.0
70°	282.0	270.8	259.6	248.3	237.2	224.3	209.7	195.3	180.7	166.2	158.9
72.5°	247.6	236.6	225.5	214.5	203.5	191.4	178.2	165.0	151.8	138.6	132.6
75°	195.1	185.2	175.2	165.2	155.3	144.6	133.2	121.8	110.4	99.0	96.9
77.5°	147.3	138.3	129.3	120.3	111.3	103.2	95.8	88.5	81.1	73.7	72.7
80°	116.7	108.2	99.7	91.2	82.7	76.2	71.9	67.5	63.2	58.9	58.2
82.5°	87.6	80.3	72.9	65.5	58.2	53.5	51.5	49.4	47.4	45.4	44.8
85°	49.5	44.9	40.4	35.8	31.2	28.6	28.0	27.4	26.8	26.1	25.8
87.5°	18.1	16.6	15.1	13.6	12.0	11.4	11.9	12.2	12.7	13.0	13.0
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	12.9	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8
95°	42.5	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7
97.5°	85.4	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7
100°	117.8	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3
102.5°	154.6	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0
105°	207.8	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3
107.5°	263.8	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8
110°	301.1	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3



TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6
115°	389.7	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7
117.5°	440.9	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5
120°	472.7	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2
122.5°	505.0	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7
125°	549.4	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0
127.5°	592.3	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7
130°	619.0	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0
132.5°	644.7	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2
135°	683.9	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3
137.5°	717.4	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0
140°	739.7	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5
142.5°	760.3	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0
145°	789.2	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8
147.5°	816.4	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3
150°	833.0	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9
152.5°	848.1	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5
155°	869.3	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4
157.5°	885.7	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9
160°	895.8	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4
162.5°	905.3	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8
165°	916.8	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2
167.5°	925.7	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1
170°	930.7	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2
172.5°	934.0	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5
175°	938.3	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7
177.5°	939.4	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1146.7	1148.5	1150.3	1151.1	1150.8	1150.4	1150.0	1149.8
5°	1139.1	1140.9	1142.8	1143.5	1143.2	1142.7	1142.3	1141.9
7.5°	1123.1	1124.1	1125.2	1125.3	1124.6	1123.9	1123.2	1122.5
10°	1108.8	1108.9	1109.1	1108.8	1107.7	1106.6	1105.6	1104.6
12.5°	1090.8	1090.7	1090.7	1089.9	1088.8	1087.5	1086.4	1085.1
15°	1059.5	1058.5	1057.5	1056.2	1054.8	1053.3	1051.9	1050.4
17.5°	1022.1	1019.9	1017.7	1015.6	1013.3	1011.2	1009.1	1006.9
20°	996.5	993.7	991.0	988.5	986.0	983.5	981.0	978.5
22.5°	969.0	965.6	962.2	959.4	957.1	954.8	952.4	950.1
25°	924.1	919.7	915.3	912.0	909.7	907.4	905.2	902.9
27.5°	875.0	869.1	863.0	858.2	854.7	851.2	847.7	844.3
30°	840.3	833.1	826.1	820.9	817.6	814.3	810.9	807.6
32.5°	806.0	798.3	790.6	785.0	781.5	778.0	774.5	771.1
35°	755.3	746.4	737.4	731.1	727.4	723.6	719.9	716.1
37.5°	700.7	690.6	680.5	673.2	668.5	663.9	659.3	654.7
40°	662.8	652.0	641.2	633.5	628.7	623.9	619.1	614.4
42.5°	626.4	614.7	602.9	594.9	590.6	586.3	582.0	577.7
45°	573.0	561.2	549.3	540.9	535.9	530.9	526.0	521.0
47.5°	517.6	504.8	492.0	483.3	478.8	474.4	470.0	465.6
50°	480.4	467.4	454.6	445.8	441.0	436.2	431.5	426.7
52.5°	444.3	430.9	417.5	408.7	404.4	400.1	395.8	391.6
55°	390.5	378.4	366.4	358.3	354.2	350.0	345.9	341.7
57.5°	337.7	326.3	315.0	307.5	304.0	300.4	296.9	293.4
60°	304.3	293.2	282.0	274.6	271.1	267.5	264.0	260.5
62.5°	271.3	260.8	250.3	243.2	239.4	235.8	232.1	228.4
65°	224.3	214.1	203.9	197.7	195.5	193.1	190.9	188.6
67.5°	179.4	171.8	164.2	159.2	156.8	154.3	151.9	149.4
70°	151.7	144.4	137.1	132.4	130.1	127.8	125.6	123.2
72.5°	126.7	120.7	114.9	111.4	110.4	109.5	108.5	107.5
75°	94.8	92.7	90.7	89.4	89.0	88.6	88.2	87.7
77.5°	71.5	70.4	69.3	68.5	68.1	67.7	67.2	66.9
80°	57.6	57.0	56.4	55.8	55.4	55.0	54.6	54.1
82.5°	44.1	43.5	42.9	42.5	42.4	42.4	42.3	42.2
85°	25.3	24.9	24.5	24.3	24.3	24.3	24.3	24.3
87.5°	12.9	12.9	12.9	12.8	12.8	12.6	12.5	12.4
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	19.8	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	23.8	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	25.0	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	25.5	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	38.2	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	97.8	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	239.6	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	304.2	299.1	294.0	280.4	258.2	236.0	213.8	191.7



TEST NUMBER: P332315-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.7	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	403.2	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	451.7	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	483.5	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	514.5	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.3	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.2	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	628.7	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	653.7	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	725.7	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.2	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	767.6	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.0	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.5	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.1	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.0	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.2	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	886.8	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	896.3	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	904.9	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	916.4	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	933.7	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	937.7	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	939.2	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)