

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831135

Luminaire Tested: S123DIP-S1000D585U850-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831135
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U850-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7709.8 lumens
Efficiency: N/A
Efficacy: 153.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831135
CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66				
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	77	70	64	81	73	66	61	65	60	56	58	54	51	51	49	46	43				
4	79	69	61	55	74	65	58	53	58	53	49	52	48	44	47	43	40	37				
5	73	62	54	48	69	59	52	46	53	47	43	48	43	39	43	39	36	33				
6	68	56	48	42	64	53	46	41	48	42	38	43	39	35	39	35	32	30				
7	63	51	43	38	59	49	42	36	44	38	34	40	35	32	36	32	29	27				
8	59	47	39	34	56	45	38	33	41	35	31	37	32	29	33	29	27	24				
9	55	43	36	31	52	41	34	30	38	32	28	34	30	26	31	27	24	22				
10	52	40	33	28	49	38	32	27	35	29	26	32	27	24	29	25	22	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	34235	34235	34235	34235	34235
5°	43296	40864	34540	27835	25579
10°	43715	45038	34311	22189	19390
15°	32926	41815	34077	18790	16397
20°	22942	33837	33643	16433	14893
25°	17493	26021	32901	15118	13971
30°	15134	20673	31717	14189	13226
35°	14040	17454	30350	13517	12703
40°	13293	15657	28431	12878	12525
45°	12851	14490	25994	12379	12446
50°	12630	13569	23107	11925	12382
55°	12159	12892	20273	11494	12436
60°	11724	12170	17474	11089	12232
65°	11013	11484	15073	10656	11991
70°	10172	10612	12818	9939	11286
75°	9208	9515	10988	9237	10310
80°	7593	8325	8691	8052	8691
85°	6015	6743	6385	6830	6928

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 29678 cd/sqm



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	3.9
10°-20°	748.0	9.7
20°-30°	885.7	11.5
30°-40°	890.6	11.6
40°-50°	817.1	10.6
50°-60°	674.4	8.7
60°-70°	477.1	6.2
70°-80°	254.6	3.3
80°-90°	66.3	0.9
90°-100°	30.0	0.4
100°-110°	145.1	1.9
110°-120°	355.7	4.6
120°-130°	451.5	5.9
130°-140°	482.4	6.3
140°-150°	451.1	5.9
150°-160°	363.8	4.7
160°-170°	234.8	3.0
170°-180°	80.9	1.0
0°-30°	1934.4	25.1
0°-40°	2825.0	36.6
0°-60°	4316.4	56.0
0°-90°	5114.5	66.3
90°-120°	530.8	6.9
90°-150°	1915.8	24.8
90°-180°	2595.0	33.7
0°-180°	7709.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3180	3180	3180	3180	3180	
5°	4007	3782	3197	2576	2367	382
15°	2955	3752	3058	1686	1471	816
25°	1473	2191	2770	1273	1176	695
35°	1068	1328	2310	1029	967	671
45°	844	952	1708	813	818	654
55°	648	687	1080	612	663	580
65°	432	451	592	418	471	430
75°	221	229	264	222	248	233
85°	49	55	52	55	56	54
90°	19	15	1	15	19	11
95°	24	20	39	20	24	20
105°	28	138	188	138	28	58
115°	372	363	354	363	372	350
125°	508	506	498	506	508	454
135°	627	627	620	627	627	484
145°	723	722	716	722	723	451
155°	788	788	789	788	788	363
165°	830	829	832	829	830	234
175°	848	849	851	849	848	81
180°	851	851	851	851	851	



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5
2.5°	3584.9	3581.2	3577.5	3559.1	3540.6	3531.8	3522.9	3496.4	3469.8	3440.3	3410.8
5°	4007.0	4017.3	4027.7	4015.9	4004.1	3967.9	3931.7	3883.8	3835.8	3781.9	3728.1
7.5°	4201.8	4207.7	4213.6	4206.2	4198.9	4189.3	4179.7	4136.9	4094.1	4038.7	3983.4
10°	3999.6	4012.9	4026.2	4055.0	4083.7	4116.2	4148.7	4142.8	4136.9	4120.6	4104.4
12.5°	3555.4	3571.6	3587.9	3645.4	3703.0	3776.8	3850.6	3914.0	3977.5	4021.8	4066.0
15°	2954.7	2999.7	3044.7	3097.1	3149.5	3258.0	3366.5	3500.0	3633.6	3752.4	3871.2
17.5°	2433.7	2450.7	2467.7	2523.7	2579.8	2716.4	2852.9	3007.1	3161.3	3358.4	3555.4
20°	2002.8	2018.3	2033.8	2107.6	2181.3	2288.3	2395.3	2568.8	2742.2	2954.0	3165.8
22.5°	1682.5	1706.9	1731.2	1772.5	1813.9	1916.4	2019.0	2173.2	2327.5	2561.4	2795.3
25°	1472.9	1490.6	1508.3	1533.4	1558.5	1640.4	1722.3	1849.3	1976.2	2190.9	2405.7
27.5°	1329.8	1337.1	1344.5	1369.6	1394.7	1447.8	1501.0	1610.2	1719.4	1901.7	2083.9
30°	1217.6	1222.8	1227.9	1250.1	1272.2	1308.4	1344.5	1423.5	1502.4	1663.3	1824.2
32.5°	1139.4	1143.1	1146.8	1163.7	1180.7	1206.5	1232.4	1289.9	1347.5	1480.3	1613.1
35°	1068.5	1070.7	1073.0	1085.5	1098.1	1117.2	1136.4	1180.0	1223.5	1328.3	1433.1
37.5°	1006.5	1009.5	1012.5	1019.8	1027.2	1044.2	1061.2	1095.8	1130.5	1211.0	1291.4
40°	946.0	951.2	956.4	961.5	966.7	980.7	994.7	1021.3	1047.9	1114.3	1180.7
42.5°	894.4	899.5	904.7	906.9	909.1	917.3	925.4	949.7	974.1	1023.5	1073.0
45°	844.2	846.4	848.6	850.8	853.1	859.7	866.3	887.7	909.1	951.9	994.7
47.5°	798.4	798.4	798.4	799.9	801.4	807.3	813.2	828.7	844.2	877.4	910.6
50°	754.2	754.2	754.2	752.0	749.7	753.4	757.1	768.9	780.7	810.3	839.8
52.5°	701.0	701.0	701.0	701.8	702.5	702.5	702.5	712.8	723.2	749.7	776.3
55°	647.9	650.9	653.8	651.6	649.4	650.9	652.3	659.0	665.6	687.0	708.4
57.5°	594.8	596.3	597.7	597.0	596.3	597.0	597.7	603.6	609.5	625.8	642.0
60°	544.6	544.6	544.6	543.1	541.6	543.1	544.6	547.6	550.5	565.3	580.0
62.5°	488.5	489.3	490.0	490.7	491.5	490.0	488.5	492.2	495.9	507.0	518.0
65°	432.4	433.2	433.9	436.1	438.3	436.9	435.4	439.1	442.8	450.9	459.0
67.5°	382.3	380.8	379.3	380.0	380.8	383.0	385.2	385.9	386.7	395.5	404.4
70°	323.2	324.7	326.2	325.4	324.7	325.4	326.2	328.4	330.6	337.2	343.9
72.5°	270.1	270.8	271.6	271.6	271.6	273.0	274.5	276.7	278.9	282.6	286.3
75°	221.4	221.4	221.4	222.9	224.3	225.1	225.8	225.8	225.8	228.8	231.7
77.5°	168.2	171.9	175.6	174.9	174.2	175.6	177.1	179.3	181.5	183.0	184.5
80°	122.5	122.5	122.5	123.2	124.0	126.2	128.4	129.9	131.4	134.3	137.3
82.5°	78.2	79.0	79.7	81.9	84.1	85.6	87.1	89.3	91.5	91.5	91.5
85°	48.7	47.2	45.8	47.2	48.7	50.2	51.7	52.4	53.1	54.6	56.1
87.5°	23.6	23.6	23.6	23.6	23.6	24.4	25.1	25.1	25.1	25.1	25.1
90°	19.0	18.7	18.4	18.1	17.9	17.4	16.9	16.3	15.7	15.2	13.4
92.5°	21.5	21.4	21.2	21.1	20.9	20.4	19.4	18.4	17.4	16.4	15.2
95°	24.0	24.0	24.0	24.0	24.0	23.5	22.6	21.6	20.6	19.6	18.1
97.5°	25.9	25.8	25.7	25.5	25.4	24.7	23.6	22.5	21.4	20.2	27.4
100°	26.6	26.4	26.3	26.1	26.0	25.4	24.2	23.1	22.0	20.9	42.8
102.5°	27.2	26.9	26.6	26.4	26.1	28.3	32.9	37.5	42.2	46.8	71.3
105°	27.8	27.5	27.3	27.0	26.7	39.0	63.9	88.8	113.6	138.5	151.2
107.5°	65.8	84.2	102.6	121.0	139.4	159.5	181.1	202.8	224.4	246.1	243.9
110°	173.9	194.0	214.1	234.2	254.3	266.7	271.4	276.0	280.6	285.3	283.7



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.5	329.8	330.1	330.4	330.7	330.2	328.9	327.6	326.4	325.1	323.6
115°	371.9	371.4	370.8	370.2	369.7	368.7	367.3	365.9	364.5	363.1	361.8
117.5°	406.1	405.9	405.8	405.7	405.5	404.9	403.8	402.6	401.5	400.4	399.7
120°	441.5	441.5	441.5	441.5	441.5	440.9	439.8	438.7	437.6	436.4	436.0
122.5°	476.3	476.2	476.0	475.9	475.7	475.3	474.6	473.9	473.2	472.5	471.9
125°	508.5	508.3	508.0	507.7	507.4	507.1	506.9	506.6	506.3	506.0	505.5
127.5°	540.2	540.5	540.7	541.0	541.3	541.2	540.8	540.4	540.0	539.5	538.8
130°	570.5	570.8	571.1	571.4	571.7	571.5	571.0	570.4	569.8	569.3	568.7
132.5°	598.4	598.8	599.2	599.6	600.1	600.0	599.4	598.9	598.3	597.7	597.3
135°	626.8	627.3	627.7	628.1	628.5	628.5	628.1	627.7	627.3	626.8	626.3
137.5°	654.0	654.3	654.6	654.9	655.2	654.9	654.2	653.5	652.8	652.1	651.9
140°	678.1	678.3	678.6	678.9	679.2	679.1	678.5	677.9	677.4	676.8	676.4
142.5°	700.2	700.6	701.0	701.5	701.9	701.9	701.5	701.0	700.6	700.2	699.8
145°	723.0	723.0	723.0	723.0	723.0	722.8	722.6	722.3	722.0	721.7	721.4
147.5°	739.4	740.1	740.8	741.5	742.2	742.4	742.2	741.9	741.6	741.3	741.0
150°	758.4	758.8	759.2	759.7	760.1	760.2	759.9	759.6	759.3	759.0	758.7
152.5°	773.6	774.3	775.0	775.7	776.4	776.5	775.9	775.3	774.8	774.2	774.1
155°	787.5	788.3	789.2	790.0	790.9	790.9	790.2	789.5	788.8	788.1	788.0
157.5°	799.5	800.6	801.8	802.9	804.0	804.1	803.3	802.5	801.6	800.8	800.9
160°	810.9	811.9	812.9	813.8	814.8	814.9	814.1	813.2	812.4	811.5	811.7
162.5°	821.6	822.5	823.3	824.2	825.0	825.0	824.0	823.0	822.0	821.0	821.2
165°	829.9	830.9	831.8	832.8	833.8	833.7	832.6	831.5	830.4	829.2	829.4
167.5°	836.2	837.3	838.4	839.6	840.7	840.7	839.6	838.4	837.3	836.2	836.2
170°	841.9	843.0	844.1	845.3	846.4	846.4	845.3	844.1	843.0	841.9	841.9
172.5°	845.1	846.3	847.6	848.8	850.1	850.2	849.1	847.9	846.8	845.7	845.5
175°	848.2	849.3	850.5	851.6	852.7	852.8	851.8	850.8	849.8	848.8	848.7
177.5°	848.8	850.3	851.7	853.1	854.5	854.6	853.5	852.4	851.2	850.1	850.0
180°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5
2.5°	3401.9	3393.0	3360.6	3328.1	3291.2	3254.3	3227.0	3199.7	3159.1	3118.5	3085.3
5°	3686.7	3645.4	3576.8	3508.2	3415.2	3322.2	3259.5	3196.7	3112.6	3028.5	2961.3
7.5°	3912.5	3841.7	3745.8	3649.8	3528.1	3406.3	3291.2	3176.1	3047.7	2919.3	2814.5
10°	4056.4	4008.5	3897.8	3787.1	3624.0	3460.9	3300.1	3139.2	2973.9	2808.6	2669.9
12.5°	4070.5	4074.9	3973.1	3871.2	3686.7	3502.3	3306.7	3111.1	2903.0	2695.0	2533.3
15°	3947.2	4023.2	3967.2	3911.1	3725.1	3539.2	3298.6	3058.0	2818.2	2578.4	2391.7
17.5°	3718.5	3881.6	3889.7	3897.8	3711.8	3525.9	3259.5	2993.1	2721.5	2450.0	2253.7
20°	3406.3	3646.9	3729.5	3812.2	3660.9	3509.6	3223.3	2937.0	2633.0	2328.9	2123.0
22.5°	3087.5	3379.8	3531.0	3682.3	3570.1	3458.0	3153.2	2848.4	2527.4	2206.4	1997.6
25°	2724.5	3043.3	3275.7	3508.2	3439.5	3370.9	3070.6	2770.2	2428.6	2086.9	1873.6
27.5°	2407.9	2731.8	3012.3	3292.7	3277.9	3263.2	2965.0	2666.9	2317.1	1967.3	1761.5
30°	2126.0	2427.8	2741.4	3055.1	3091.2	3127.4	2839.6	2551.8	2201.3	1850.7	1652.2
32.5°	1876.6	2140.0	2476.5	2813.0	2883.9	2954.7	2695.0	2435.2	2088.4	1741.5	1550.4
35°	1672.2	1911.3	2247.8	2584.3	2672.8	2761.4	2535.6	2309.7	1971.8	1633.8	1451.5
37.5°	1491.4	1691.4	2019.7	2348.1	2456.6	2565.1	2362.9	2160.7	1844.1	1527.5	1360.0
40°	1341.6	1502.4	1804.3	2106.1	2231.5	2357.0	2190.2	2023.4	1723.1	1422.7	1268.5
42.5°	1216.1	1359.3	1633.1	1906.8	2027.1	2147.4	2006.5	1865.5	1598.4	1331.2	1190.3
45°	1109.1	1223.5	1472.2	1720.9	1835.3	1949.6	1828.6	1707.6	1472.2	1236.8	1105.4
47.5°	1008.8	1106.9	1319.4	1532.0	1633.8	1735.6	1641.2	1546.7	1347.5	1148.2	1029.4
50°	918.7	997.7	1183.7	1369.6	1458.2	1546.7	1463.3	1379.9	1216.1	1052.3	949.0
52.5°	840.5	904.7	1060.4	1216.1	1292.1	1368.1	1296.6	1225.0	1095.1	965.2	875.2
55°	763.0	817.6	952.7	1087.7	1139.4	1191.0	1135.7	1080.3	975.6	870.8	794.8
57.5°	690.7	739.4	850.1	960.8	1000.6	1040.5	990.3	940.1	861.2	782.2	718.8
60°	619.9	659.7	752.0	844.2	868.6	892.9	852.3	811.7	756.4	701.0	644.2
62.5°	554.2	590.4	659.0	727.6	743.8	760.1	729.1	698.1	656.0	614.0	569.7
65°	486.3	513.6	569.7	625.8	636.1	646.4	619.1	591.8	560.1	528.4	495.9
67.5°	423.6	442.8	488.5	534.3	535.0	535.7	513.6	491.5	473.8	456.0	430.2
70°	362.3	380.8	411.0	441.3	442.0	442.8	425.1	407.3	394.1	380.8	361.6
72.5°	299.6	312.9	335.8	358.6	357.2	355.7	344.6	333.5	323.2	312.9	298.9
75°	242.8	253.9	269.3	284.8	280.4	276.0	270.1	264.2	255.3	246.5	237.6
77.5°	191.1	197.8	206.6	215.5	212.5	209.6	204.4	199.2	192.6	186.0	182.3
80°	140.2	143.2	149.1	155.0	153.5	152.0	146.1	140.2	138.7	137.3	132.1
82.5°	95.2	98.9	100.4	101.8	101.1	100.4	95.9	91.5	90.0	88.6	87.8
85°	56.8	57.6	58.3	59.0	56.8	54.6	53.1	51.7	51.7	51.7	50.9
87.5°	25.8	26.6	26.6	26.6	25.8	25.1	23.6	22.1	22.9	23.6	23.6
90°	11.5	9.7	7.9	6.3	4.8	3.4	2.0	0.6	2.0	3.4	4.8
92.5°	13.9	12.7	11.4	11.2	12.0	12.9	13.7	14.5	13.7	12.9	12.0
95°	16.5	15.0	13.4	15.5	21.3	27.1	32.8	38.6	32.8	27.1	21.3
97.5°	34.6	41.7	48.9	54.5	58.4	62.3	66.3	70.2	66.3	62.3	58.4
100°	64.7	86.7	108.6	118.1	115.3	112.5	109.7	106.9	109.7	112.5	115.3
102.5°	95.7	120.2	144.6	156.0	154.1	152.3	150.5	148.6	150.5	152.3	154.1
105°	163.8	176.5	189.1	194.7	193.1	191.6	190.0	188.5	190.0	191.6	193.1
107.5°	241.8	239.7	237.6	235.9	234.7	233.4	232.1	230.9	232.1	233.4	234.7
110°	282.2	280.6	279.1	277.7	276.6	275.5	274.4	273.3	274.4	275.5	276.6



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	322.0	320.5	318.9	317.7	316.7	315.7	314.7	313.7	314.7	315.7	316.7
115°	360.5	359.3	358.0	357.0	356.1	355.3	354.4	353.6	354.4	355.3	356.1
117.5°	399.0	398.3	397.6	396.7	395.7	394.8	393.8	392.8	393.8	394.8	395.7
120°	435.6	435.2	434.8	433.9	432.6	431.4	430.1	428.9	430.1	431.4	432.6
122.5°	471.4	470.8	470.2	469.5	468.5	467.5	466.5	465.5	466.5	467.5	468.5
125°	504.9	504.3	503.8	502.9	501.8	500.7	499.6	498.4	499.6	500.7	501.8
127.5°	538.1	537.4	536.7	535.8	534.7	533.6	532.4	531.3	532.4	533.6	534.7
130°	568.1	567.6	567.0	566.2	565.1	563.9	562.8	561.7	562.8	563.9	565.1
132.5°	596.9	596.5	596.0	595.3	594.2	593.0	591.9	590.8	591.9	593.0	594.2
135°	625.7	625.1	624.6	623.9	623.0	622.2	621.3	620.5	621.3	622.2	623.0
137.5°	651.6	651.3	651.0	650.3	649.2	648.1	646.9	645.8	646.9	648.1	649.2
140°	676.0	675.5	675.1	674.5	673.6	672.8	672.0	671.1	672.0	672.8	673.6
142.5°	699.4	698.9	698.5	697.9	697.0	696.2	695.4	694.5	695.4	696.2	697.0
145°	721.1	720.9	720.6	720.0	719.0	718.0	717.0	716.0	717.0	718.0	719.0
147.5°	740.8	740.5	740.2	739.7	739.0	738.3	737.6	736.9	737.6	738.3	739.0
150°	758.5	758.2	757.9	757.6	757.1	756.7	756.3	755.9	756.3	756.7	757.1
152.5°	773.9	773.8	773.6	773.5	773.4	773.2	773.1	772.9	773.1	773.2	773.4
155°	787.8	787.7	787.6	787.6	787.9	788.2	788.5	788.8	788.5	788.2	787.9
157.5°	801.1	801.2	801.3	801.4	801.4	801.4	801.4	801.4	801.4	801.4	801.4
160°	811.8	812.0	812.1	812.2	812.4	812.5	812.7	812.8	812.7	812.5	812.4
162.5°	821.3	821.4	821.6	821.9	822.3	822.7	823.1	823.5	823.1	822.7	822.3
165°	829.5	829.7	829.8	830.1	830.5	830.9	831.3	831.8	831.3	830.9	830.5
167.5°	836.2	836.2	836.2	836.5	837.0	837.6	838.2	838.7	838.2	837.6	837.0
170°	841.9	841.9	841.9	842.2	842.7	843.3	843.9	844.4	843.9	843.3	842.7
172.5°	845.4	845.3	845.1	845.4	846.1	846.8	847.5	848.2	847.5	846.8	846.1
175°	848.6	848.4	848.3	848.6	849.3	850.0	850.7	851.4	850.7	850.0	849.3
177.5°	849.8	849.7	849.6	849.8	850.5	851.2	851.9	852.6	851.9	851.2	850.5
180°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5
2.5°	3052.1	3023.3	2994.6	2972.4	2950.3	2912.6	2875.0	2866.2	2857.3	2844.8	2832.2
5°	2894.2	2823.4	2752.5	2689.0	2625.6	2576.1	2526.7	2494.2	2461.8	2438.1	2414.5
7.5°	2709.7	2603.4	2497.2	2421.9	2346.6	2275.1	2203.5	2180.6	2157.7	2126.7	2095.7
10°	2531.1	2413.8	2296.5	2198.3	2100.2	2030.1	1960.0	1931.9	1903.9	1864.8	1825.7
12.5°	2371.7	2243.3	2114.9	2016.0	1917.2	1849.3	1781.4	1740.8	1700.2	1678.1	1655.9
15°	2205.0	2067.7	1930.4	1838.9	1747.4	1686.2	1624.9	1589.5	1554.1	1532.7	1511.3
17.5°	2057.4	1921.6	1785.8	1698.0	1610.2	1554.1	1498.0	1467.0	1436.0	1419.8	1403.6
20°	1917.2	1784.3	1651.5	1565.9	1480.3	1434.6	1388.8	1368.9	1349.0	1335.7	1322.4
22.5°	1788.8	1658.1	1527.5	1454.5	1381.4	1344.5	1307.6	1293.6	1279.6	1268.5	1257.4
25°	1660.4	1543.8	1427.2	1365.2	1303.2	1272.9	1242.7	1228.7	1214.6	1203.6	1192.5
27.5°	1555.6	1444.1	1332.7	1279.6	1226.5	1202.8	1179.2	1168.2	1157.1	1146.8	1136.4
30°	1453.7	1354.1	1254.5	1208.7	1163.0	1141.6	1120.2	1109.1	1098.1	1088.5	1078.9
32.5°	1359.3	1273.7	1188.1	1146.0	1104.0	1086.2	1068.5	1055.3	1042.0	1034.6	1027.2
35°	1269.3	1192.5	1115.8	1081.1	1046.4	1028.7	1011.0	999.9	988.8	982.9	977.0
37.5°	1192.5	1123.9	1055.3	1022.0	988.8	971.9	954.9	945.3	935.7	933.5	931.3
40°	1114.3	1055.3	996.2	963.7	931.3	916.5	901.8	895.9	890.0	888.5	887.0
42.5°	1049.3	991.8	934.2	904.7	875.2	862.6	850.1	847.2	844.2	846.4	848.6
45°	974.1	926.1	878.1	850.8	823.5	813.2	802.9	800.7	798.4	802.9	807.3
47.5°	910.6	866.3	822.1	796.2	770.4	763.0	755.6	754.9	754.2	760.1	766.0
50°	845.7	802.9	760.1	739.4	718.8	712.1	705.5	707.7	709.9	719.5	729.1
52.5°	785.2	745.3	705.5	686.3	667.1	662.7	658.2	663.4	668.6	678.9	689.2
55°	718.8	682.6	646.4	631.7	616.9	612.5	608.1	618.4	628.7	638.3	647.9
57.5°	655.3	623.6	591.8	578.5	565.3	564.5	563.8	573.4	583.0	593.3	603.6
60°	587.4	560.8	534.3	523.9	513.6	515.1	516.6	527.6	538.7	546.8	554.9
62.5°	525.4	503.3	481.1	471.5	461.9	465.6	469.3	480.4	491.5	501.1	510.7
65°	463.4	445.0	426.5	419.9	413.2	418.4	423.6	433.2	442.8	449.4	456.0
67.5°	404.4	388.9	373.4	368.2	363.1	368.2	373.4	383.0	392.6	399.2	405.9
70°	342.4	329.9	317.3	313.6	309.9	315.8	321.7	329.9	338.0	344.6	351.3
72.5°	284.8	275.3	265.7	264.9	264.2	269.3	274.5	282.6	290.7	295.2	299.6
75°	228.8	223.6	218.4	217.7	217.0	222.1	227.3	231.7	236.1	239.8	243.5
77.5°	178.6	174.2	169.7	170.5	171.2	174.9	178.6	183.0	187.4	189.7	191.9
80°	126.9	125.4	124.0	125.4	126.9	129.9	132.8	135.8	138.7	140.2	141.7
82.5°	87.1	85.6	84.1	86.3	88.6	90.8	93.0	95.2	97.4	98.1	98.9
85°	50.2	52.4	54.6	54.6	54.6	55.3	56.1	56.8	57.6	56.8	56.1
87.5°	23.6	24.4	25.1	25.1	25.1	25.8	26.6	26.6	26.6	25.8	25.1
90°	6.3	7.9	9.7	11.5	13.4	15.2	15.7	16.3	16.9	17.4	17.9
92.5°	11.2	11.4	12.7	13.9	15.2	16.4	17.4	18.4	19.4	20.4	20.9
95°	15.5	13.4	15.0	16.5	18.1	19.6	20.6	21.6	22.6	23.5	24.0
97.5°	54.5	48.9	41.7	34.6	27.4	20.2	21.4	22.5	23.6	24.7	25.4
100°	118.1	108.6	86.7	64.7	42.8	20.9	22.0	23.1	24.2	25.4	26.0
102.5°	156.0	144.6	120.2	95.7	71.3	46.8	42.2	37.5	32.9	28.3	26.1
105°	194.7	189.1	176.5	163.8	151.2	138.5	113.6	88.8	63.9	39.0	26.7
107.5°	235.9	237.6	239.7	241.8	243.9	246.1	224.4	202.8	181.1	159.5	139.4
110°	277.7	279.1	280.6	282.2	283.7	285.3	280.6	276.0	271.4	266.7	254.3



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	317.7	318.9	320.5	322.0	323.6	325.1	326.4	327.6	328.9	330.2	330.7
115°	357.0	358.0	359.3	360.5	361.8	363.1	364.5	365.9	367.3	368.7	369.7
117.5°	396.7	397.6	398.3	399.0	399.7	400.4	401.5	402.6	403.8	404.9	405.5
120°	433.9	434.8	435.2	435.6	436.0	436.4	437.6	438.7	439.8	440.9	441.5
122.5°	469.5	470.2	470.8	471.4	471.9	472.5	473.2	473.9	474.6	475.3	475.7
125°	502.9	503.8	504.3	504.9	505.5	506.0	506.3	506.6	506.9	507.1	507.4
127.5°	535.8	536.7	537.4	538.1	538.8	539.5	540.0	540.4	540.8	541.2	541.3
130°	566.2	567.0	567.6	568.1	568.7	569.3	569.8	570.4	571.0	571.5	571.7
132.5°	595.3	596.0	596.5	596.9	597.3	597.7	598.3	598.9	599.4	600.0	600.1
135°	623.9	624.6	625.1	625.7	626.3	626.8	627.3	627.7	628.1	628.5	628.5
137.5°	650.3	651.0	651.3	651.6	651.9	652.1	652.8	653.5	654.2	654.9	655.2
140°	674.5	675.1	675.5	676.0	676.4	676.8	677.4	677.9	678.5	679.1	679.2
142.5°	697.9	698.5	698.9	699.4	699.8	700.2	700.6	701.0	701.5	701.9	701.9
145°	720.0	720.6	720.9	721.1	721.4	721.7	722.0	722.3	722.6	722.8	723.0
147.5°	739.7	740.2	740.5	740.8	741.0	741.3	741.6	741.9	742.2	742.4	742.2
150°	757.6	757.9	758.2	758.5	758.7	759.0	759.3	759.6	759.9	760.2	760.1
152.5°	773.5	773.6	773.8	773.9	774.1	774.2	774.8	775.3	775.9	776.5	776.4
155°	787.6	787.6	787.7	787.8	788.0	788.1	788.8	789.5	790.2	790.9	790.9
157.5°	801.4	801.3	801.2	801.1	800.9	800.8	801.6	802.5	803.3	804.1	804.0
160°	812.2	812.1	812.0	811.8	811.7	811.5	812.4	813.2	814.1	814.9	814.8
162.5°	821.9	821.6	821.4	821.3	821.2	821.0	822.0	823.0	824.0	825.0	825.0
165°	830.1	829.8	829.7	829.5	829.4	829.2	830.4	831.5	832.6	833.7	833.8
167.5°	836.5	836.2	836.2	836.2	836.2	836.2	837.3	838.4	839.6	840.7	840.7
170°	842.2	841.9	841.9	841.9	841.9	841.9	843.0	844.1	845.3	846.4	846.4
172.5°	845.4	845.1	845.3	845.4	845.5	845.7	846.8	847.9	849.1	850.2	850.1
175°	848.6	848.3	848.4	848.6	848.7	848.8	849.8	850.8	851.8	852.8	852.7
177.5°	849.8	849.6	849.7	849.8	850.0	850.1	851.2	852.4	853.5	854.6	854.5
180°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3180.5	3180.5	3180.5	3180.5
2.5°	2827.0	2821.9	2801.2	2780.6
5°	2396.8	2379.1	2373.2	2367.3
7.5°	2094.3	2092.8	2061.8	2030.8
10°	1827.9	1830.1	1802.0	1774.0
12.5°	1637.5	1619.0	1616.8	1614.6
15°	1494.3	1477.4	1474.4	1471.4
17.5°	1393.2	1382.9	1379.9	1377.0
20°	1316.5	1310.6	1305.4	1300.2
22.5°	1250.1	1242.7	1238.3	1233.8
25°	1185.9	1179.2	1177.7	1176.3
27.5°	1128.3	1120.2	1120.2	1120.2
30°	1073.7	1068.5	1066.3	1064.1
32.5°	1022.8	1018.4	1018.4	1018.4
35°	974.8	972.6	969.7	966.7
37.5°	931.3	931.3	929.8	928.3
40°	889.2	891.4	891.4	891.4
42.5°	850.8	853.1	853.1	853.1
45°	811.0	814.7	816.2	817.6
47.5°	771.9	777.8	779.3	780.7
50°	733.5	737.9	738.7	739.4
52.5°	694.4	699.6	703.3	706.9
55°	653.1	658.2	660.5	662.7
57.5°	608.8	614.0	614.7	615.4
60°	560.1	565.3	566.7	568.2
62.5°	513.6	516.6	518.0	519.5
65°	460.5	464.9	467.9	470.8
67.5°	409.6	413.2	413.2	413.2
70°	352.7	354.2	356.4	358.6
72.5°	300.3	301.1	301.1	301.1
75°	245.0	246.5	247.2	247.9
77.5°	192.6	193.3	193.3	193.3
80°	140.9	140.2	140.2	140.2
82.5°	96.7	94.5	94.5	94.5
85°	55.3	54.6	55.3	56.1
87.5°	25.1	25.1	25.1	25.1
90°	18.1	18.4	18.7	19.0
92.5°	21.1	21.2	21.4	21.5
95°	24.0	24.0	24.0	24.0
97.5°	25.5	25.7	25.8	25.9
100°	26.1	26.3	26.4	26.6
102.5°	26.4	26.6	26.9	27.2
105°	27.0	27.3	27.5	27.8
107.5°	121.0	102.6	84.2	65.8
110°	234.2	214.1	194.0	173.9



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	330.4	330.1	329.8	329.5
115°	370.2	370.8	371.4	371.9
117.5°	405.7	405.8	405.9	406.1
120°	441.5	441.5	441.5	441.5
122.5°	475.9	476.0	476.2	476.3
125°	507.7	508.0	508.3	508.5
127.5°	541.0	540.7	540.5	540.2
130°	571.4	571.1	570.8	570.5
132.5°	599.6	599.2	598.8	598.4
135°	628.1	627.7	627.3	626.8
137.5°	654.9	654.6	654.3	654.0
140°	678.9	678.6	678.3	678.1
142.5°	701.5	701.0	700.6	700.2
145°	723.0	723.0	723.0	723.0
147.5°	741.5	740.8	740.1	739.4
150°	759.7	759.2	758.8	758.4
152.5°	775.7	775.0	774.3	773.6
155°	790.0	789.2	788.3	787.5
157.5°	802.9	801.8	800.6	799.5
160°	813.8	812.9	811.9	810.9
162.5°	824.2	823.3	822.5	821.6
165°	832.8	831.8	830.9	829.9
167.5°	839.6	838.4	837.3	836.2
170°	845.3	844.1	843.0	841.9
172.5°	848.8	847.6	846.3	845.1
175°	851.6	850.5	849.3	848.2
177.5°	853.1	851.7	850.3	848.8
180°	851.4	851.4	851.4	851.4



TEST NUMBER: P831135

CATALOG NUMBER: S123DIP-S1000D585U850-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.25	18.23	18.06	19.05	20.08	19.49	20.46	20.30	21.29	22.31
	3H	18.91	19.78	19.73	20.62	21.67	20.92	21.80	21.74	22.63	23.68
	4H	19.49	20.31	20.33	21.16	22.22	21.38	22.20	22.22	23.05	24.11
	6H	19.86	20.63	20.72	21.48	22.55	21.66	22.42	22.51	23.27	24.34
	8H	19.96	20.69	20.83	21.56	22.63	21.72	22.45	22.58	23.32	24.39
	12H	20.01	20.70	20.88	21.57	22.66	21.75	22.43	22.61	23.30	24.40
4H	2H	17.84	18.66	18.68	19.51	20.57	19.66	20.49	20.51	21.33	22.40
	3H	19.68	20.36	20.53	21.24	22.32	21.29	21.98	22.15	22.86	23.93
	4H	20.38	21.00	21.25	21.88	22.98	21.88	22.51	22.75	23.38	24.48
	6H	20.86	21.40	21.75	22.30	23.41	22.29	22.83	23.18	23.73	24.84
	8H	21.00	21.50	21.89	22.40	23.52	22.41	22.91	23.29	23.80	24.92
	12H	21.07	21.52	21.98	22.44	23.56	22.46	22.91	23.36	23.82	24.95
8H	4H	20.65	21.16	21.54	22.05	23.17	22.00	22.50	22.88	23.39	24.51
	6H	21.25	21.66	22.16	22.60	23.72	22.50	22.92	23.42	23.85	24.97
	8H	21.46	21.82	22.38	22.75	23.89	22.68	23.05	23.61	23.98	25.11
	12H	21.58	21.91	22.51	22.83	24.02	22.79	23.11	23.72	24.03	25.22
12H	4H	20.66	21.11	21.57	22.03	23.15	21.98	22.43	22.88	23.34	24.46
	6H	21.30	21.67	22.22	22.60	23.73	22.52	22.88	23.44	23.81	24.95
	8H	21.54	21.86	22.47	22.78	23.97	22.72	23.05	23.65	23.97	25.15