

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332062-840

Luminaire Tested: **S123DIP-S1165D585U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332062-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6946.9 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69
1	102	98	93	90	96	92	89	85	82	80	77	73	71	69	65	64	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	55	52	49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	46	40	36	41	37	33	31
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	2.5
10°-20°	491.0	7.1
20°-30°	725.3	10.4
30°-40°	847.3	12.2
40°-50°	851.8	12.3
50°-60°	748.3	10.8
60°-70°	557.5	8.0
70°-80°	317.6	4.6
80°-90°	93.4	1.3
90°-100°	158.3	2.3
100°-110°	448.4	6.5
110°-120°	441.1	6.3
120°-130°	351.8	5.1
130°-140°	277.4	4.0
140°-150°	207.0	3.0
150°-160°	144.3	2.1
160°-170°	84.8	1.2
170°-180°	27.6	0.4
0°-30°	1390.3	20.0
0°-40°	2237.6	32.2
0°-60°	3837.7	55.2
0°-90°	4806.1	69.2
90°-120°	1047.8	15.1
90°-150°	1884.1	27.1
90°-180°	2141.0	30.8
0°-180°	6946.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	1	7	14	16	17	6
95°	20	64	342	100	67	21
105°	67	99	463	810	733	71
115°	118	147	354	777	891	117
125°	164	194	331	599	703	146
135°	192	230	326	493	570	149
145°	219	251	322	405	445	138
155°	249	269	312	354	369	115
165°	272	280	298	316	322	77
175°	284	284	286	290	290	27
180°	285	285	285	285	285	



TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.2	32.6	32.0	31.5	30.9	30.6	30.6	30.7	30.8	30.8	30.4
90°	1.1	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8
92.5°	7.2	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9
95°	19.6	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0
97.5°	33.4	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3
100°	42.6	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9
102.5°	52.3	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6
105°	66.9	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4
107.5°	82.2	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9
110°	93.3	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2



TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.4	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5
115°	118.1	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9
117.5°	132.7	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4
120°	142.9	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5
122.5°	151.6	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9
125°	164.2	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2
127.5°	173.7	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3
130°	179.8	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9
132.5°	184.3	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8
135°	192.4	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0
137.5°	200.0	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3
140°	205.1	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0
142.5°	210.6	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4
145°	219.4	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4
147.5°	228.4	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6
150°	234.4	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3
152.5°	240.4	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7
155°	249.4	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2
157.5°	256.5	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9
160°	262.1	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8
162.5°	266.2	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6
165°	272.5	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0
167.5°	277.2	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6
170°	279.9	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4
172.5°	281.8	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1
175°	284.0	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4
177.5°	285.0	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	30.3	30.1	29.9	30.0	29.9	30.0	30.1	30.0
90°	14.4	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	48.5	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	207.3	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	516.9	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	679.1	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	733.1	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	748.8	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	703.4	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	660.0	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P332062-840

CATALOG NUMBER: S123DIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	617.2	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	560.5	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	519.3	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	497.7	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	480.6	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	457.9	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	438.1	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	425.7	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	414.1	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	398.6	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	384.5	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	376.2	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	368.3	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	358.8	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	351.1	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	345.6	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	340.5	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	333.0	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	324.9	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	320.2	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	314.8	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	307.6	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	301.3	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	297.2	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	293.6	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	288.6	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.5	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)