

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831379

Luminaire Tested: S123DIP-S340D365U850-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831379
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D365U850-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3133.7 lumens
Efficiency: N/A
Efficacy: 139.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 22.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	100	96	92	88	93	89	86	83	77	74	72	66	64	62	55	54	53	48				
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41				
3	84	75	68	62	78	70	64	59	61	56	52	52	49	46	44	42	40	36				
4	77	67	59	53	71	62	56	50	54	49	45	47	43	40	40	37	35	31				
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	33	31	28				
6	66	54	46	41	61	51	44	39	45	39	35	39	35	31	34	30	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	28	25	23				
8	57	45	37	32	53	42	36	31	38	32	28	33	29	25	29	25	23	21				
9	53	41	34	29	50	39	32	28	35	29	26	31	26	23	27	23	21	19				
10	50	38	31	26	47	36	30	25	32	27	23	29	24	21	25	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11720	11720	11720	11720	11720
5°	14822	13989	11825	9529	8756
10°	14966	15419	11746	7596	6638
15°	11272	14315	11666	6433	5613
20°	7853	11584	11518	5625	5098
25°	5989	8909	11264	5176	4783
30°	5180	7077	10858	4857	4528
35°	4807	5975	10390	4628	4348
40°	4551	5361	9733	4409	4288
45°	4399	4961	8899	4238	4261
50°	4324	4645	7911	4083	4238
55°	4162	4414	6942	3935	4258
60°	4013	4166	5983	3795	4187
65°	3769	3933	5160	3647	4106
70°	3484	3635	4390	3402	3865
75°	3152	3256	3760	3161	3531
80°	2597	2851	2975	2758	2975
85°	2062	2309	2186	2334	2371

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 10161 cd/sqm



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	3.3
10°-20°	256.1	8.2
20°-30°	303.2	9.7
30°-40°	304.9	9.7
40°-50°	279.7	8.9
50°-60°	230.9	7.4
60°-70°	163.3	5.2
70°-80°	87.2	2.8
80°-90°	23.2	0.7
90°-100°	32.1	1.0
100°-110°	97.2	3.1
110°-120°	165.5	5.3
120°-130°	217.7	6.9
130°-140°	244.7	7.8
140°-150°	240.6	7.7
150°-160°	202.5	6.5
160°-170°	134.8	4.3
170°-180°	47.2	1.5
0°-30°	662.3	21.1
0°-40°	967.1	30.9
0°-60°	1477.7	47.2
0°-90°	1751.4	55.9
90°-120°	294.8	9.4
90°-150°	997.8	31.8
90°-180°	1382.0	44.1
0°-180°	3133.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1089	1089	1089	1089	1089	
5°	1372	1295	1094	882	810	131
15°	1012	1285	1047	577	504	279
25°	504	750	948	436	403	238
35°	366	455	791	352	331	230
45°	289	326	585	278	280	224
55°	222	235	370	210	227	198
65°	148	154	203	143	161	147
75°	76	78	90	76	85	80
85°	17	19	18	19	19	19
90°	12	9	0	9	12	7
95°	31	29	23	29	31	31
105°	93	92	88	92	93	99
115°	167	167	167	167	167	165
125°	241	244	244	244	241	216
135°	316	318	316	318	316	243
145°	384	386	384	386	384	240
155°	438	440	439	440	438	202
165°	477	477	478	477	477	135
175°	496	496	498	496	496	47
180°	499	499	499	499	499	



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8
2.5°	1227.3	1226.0	1224.8	1218.4	1212.1	1209.1	1206.1	1197.0	1187.9	1177.8	1167.7
5°	1371.8	1375.3	1378.9	1374.8	1370.8	1358.4	1346.0	1329.6	1313.2	1294.7	1276.3
7.5°	1438.5	1440.5	1442.5	1440.0	1437.5	1434.2	1430.9	1416.3	1401.6	1382.7	1363.7
10°	1369.3	1373.8	1378.4	1388.2	1398.1	1409.2	1420.3	1418.3	1416.3	1410.7	1405.1
12.5°	1217.2	1222.7	1228.3	1248.0	1267.7	1293.0	1318.2	1340.0	1361.7	1376.8	1392.0
15°	1011.5	1026.9	1042.4	1060.3	1078.2	1115.4	1152.5	1198.2	1244.0	1284.6	1325.3
17.5°	833.2	839.0	844.8	864.0	883.2	929.9	976.7	1029.5	1082.3	1149.7	1217.2
20°	685.6	690.9	696.3	721.5	746.8	783.4	820.0	879.4	938.8	1011.3	1083.8
22.5°	576.0	584.3	592.7	606.8	621.0	656.1	691.2	744.0	796.8	876.9	957.0
25°	504.3	510.3	516.4	525.0	533.6	561.6	589.6	633.1	676.5	750.1	823.6
27.5°	455.2	457.8	460.3	468.9	477.5	495.7	513.9	551.2	588.6	651.0	713.4
30°	416.8	418.6	420.4	428.0	435.5	447.9	460.3	487.3	514.4	569.4	624.5
32.5°	390.1	391.3	392.6	398.4	404.2	413.1	421.9	441.6	461.3	506.8	552.3
35°	365.8	366.6	367.3	371.6	375.9	382.5	389.1	404.0	418.9	454.7	490.6
37.5°	344.6	345.6	346.6	349.1	351.7	357.5	363.3	375.2	387.0	414.6	442.1
40°	323.9	325.6	327.4	329.2	330.9	335.7	340.5	349.6	358.7	381.5	404.2
42.5°	306.2	308.0	309.7	310.5	311.2	314.0	316.8	325.1	333.5	350.4	367.3
45°	289.0	289.8	290.5	291.3	292.0	294.3	296.6	303.9	311.2	325.9	340.5
47.5°	273.3	273.3	273.3	273.9	274.4	276.4	278.4	283.7	289.0	300.4	311.7
50°	258.2	258.2	258.2	257.4	256.7	257.9	259.2	263.2	267.3	277.4	287.5
52.5°	240.0	240.0	240.0	240.3	240.5	240.5	240.5	244.0	247.6	256.7	265.8
55°	221.8	222.8	223.8	223.1	222.3	222.8	223.3	225.6	227.9	235.2	242.5
57.5°	203.6	204.1	204.6	204.4	204.1	204.4	204.6	206.7	208.7	214.2	219.8
60°	186.4	186.4	186.4	185.9	185.4	185.9	186.4	187.5	188.5	193.5	198.6
62.5°	167.2	167.5	167.7	168.0	168.3	167.7	167.2	168.5	169.8	173.6	177.3
65°	148.0	148.3	148.5	149.3	150.1	149.6	149.1	150.3	151.6	154.4	157.1
67.5°	130.9	130.4	129.9	130.1	130.4	131.1	131.9	132.1	132.4	135.4	138.4
70°	110.7	111.2	111.7	111.4	111.2	111.4	111.7	112.4	113.2	115.5	117.7
72.5°	92.5	92.7	93.0	93.0	93.0	93.5	94.0	94.7	95.5	96.8	98.0
75°	75.8	75.8	75.8	76.3	76.8	77.1	77.3	77.3	77.3	78.3	79.3
77.5°	57.6	58.9	60.1	59.9	59.6	60.1	60.6	61.4	62.1	62.7	63.2
80°	41.9	41.9	41.9	42.2	42.4	43.2	44.0	44.5	45.0	46.0	47.0
82.5°	26.8	27.0	27.3	28.0	28.8	29.3	29.8	30.6	31.3	31.3	31.3
85°	16.7	16.2	15.7	16.2	16.7	17.2	17.7	17.9	18.2	18.7	19.2
87.5°	8.1	8.1	8.1	8.1	8.1	8.3	8.6	8.6	8.6	8.6	8.6
90°	11.8	11.6	11.4	11.2	11.1	10.8	10.5	10.1	9.8	9.4	8.3
92.5°	16.9	17.0	17.2	17.4	17.5	17.5	17.2	17.0	16.7	16.5	15.9
95°	30.6	30.6	30.6	30.6	30.6	30.4	30.0	29.7	29.3	29.0	28.3
97.5°	43.9	44.0	44.1	44.2	44.2	44.1	43.6	43.2	42.8	42.3	41.8
100°	59.6	59.4	59.2	59.0	58.9	58.7	58.4	58.1	57.9	57.6	57.2
102.5°	75.6	75.7	75.8	75.9	76.0	75.9	75.6	75.4	75.1	74.9	74.2
105°	93.3	93.1	92.9	92.8	92.6	92.5	92.5	92.5	92.5	92.5	91.7
107.5°	111.3	111.4	111.5	111.6	111.7	111.6	111.3	111.0	110.8	110.5	110.2
110°	129.7	129.9	130.1	130.2	130.4	130.3	130.0	129.6	129.3	128.9	128.8



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.3	149.3	149.3	149.3	149.3	149.1	148.7	148.2	147.8	147.4	147.4
115°	167.0	167.0	167.1	167.2	167.3	167.3	167.2	167.1	167.0	167.0	167.1
117.5°	185.0	185.2	185.5	185.8	186.0	186.2	186.2	186.2	186.2	186.2	186.3
120°	204.2	204.4	204.5	204.7	204.9	205.0	205.1	205.2	205.3	205.4	205.8
122.5°	222.6	222.9	223.1	223.4	223.7	223.9	224.2	224.4	224.7	225.0	225.1
125°	241.0	241.4	241.7	242.1	242.4	242.8	243.1	243.5	243.8	244.2	244.3
127.5°	259.4	259.8	260.1	260.5	260.8	261.3	261.8	262.3	262.8	263.4	263.5
130°	277.5	278.1	278.7	279.3	279.9	280.4	280.7	281.1	281.4	281.8	282.0
132.5°	296.3	296.7	297.2	297.6	298.0	298.5	298.9	299.3	299.8	300.2	300.4
135°	315.9	316.1	316.2	316.4	316.6	316.8	317.2	317.5	317.9	318.2	318.3
137.5°	333.1	333.4	333.6	333.9	334.2	334.5	335.0	335.4	335.8	336.3	336.0
140°	350.0	350.6	351.2	351.8	352.4	352.8	352.9	352.9	353.0	353.1	353.0
142.5°	367.2	367.7	368.1	368.5	369.0	369.2	369.3	369.4	369.5	369.6	369.4
145°	383.7	384.0	384.4	384.7	385.1	385.3	385.4	385.5	385.6	385.6	385.4
147.5°	398.6	399.1	399.6	400.1	400.7	400.9	400.9	400.9	400.9	400.9	400.7
150°	412.7	413.2	413.7	414.2	414.8	415.0	415.0	415.0	415.0	415.0	414.9
152.5°	426.4	426.8	427.3	427.7	428.1	428.3	428.1	427.9	427.7	427.6	427.5
155°	438.5	439.2	439.8	440.4	441.0	441.1	440.8	440.4	440.1	439.7	439.6
157.5°	449.9	450.4	451.0	451.5	452.0	452.1	451.7	451.4	451.0	450.7	450.6
160°	460.9	461.2	461.6	461.9	462.3	462.2	461.8	461.4	460.9	460.5	460.5
162.5°	469.1	469.7	470.3	470.9	471.6	471.6	471.2	470.8	470.3	469.9	469.8
165°	477.0	477.6	478.2	478.8	479.4	479.4	478.9	478.4	477.9	477.3	477.3
167.5°	484.0	484.5	485.1	485.6	486.1	486.1	485.6	485.1	484.5	484.0	483.9
170°	489.1	489.7	490.3	490.9	491.5	491.5	490.9	490.3	489.7	489.1	489.1
172.5°	493.0	493.6	494.2	494.9	495.5	495.5	495.0	494.5	493.9	493.4	493.4
175°	495.8	496.4	497.0	497.6	498.2	498.2	497.7	497.2	496.7	496.2	496.2
177.5°	497.3	497.9	498.6	499.2	499.8	499.8	499.3	498.8	498.2	497.7	497.7
180°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8
2.5°	1164.6	1161.6	1150.5	1139.4	1126.7	1114.1	1104.8	1095.4	1081.5	1067.6	1056.3
5°	1262.1	1248.0	1224.5	1201.0	1169.2	1137.3	1115.9	1094.4	1065.6	1036.8	1013.8
7.5°	1339.5	1315.2	1282.4	1249.5	1207.8	1166.1	1126.7	1087.3	1043.4	999.4	963.5
10°	1388.7	1372.3	1334.4	1296.5	1240.7	1184.8	1129.8	1074.7	1018.1	961.5	914.0
12.5°	1393.5	1395.0	1360.2	1325.3	1262.1	1199.0	1132.0	1065.1	993.9	922.6	867.3
15°	1351.3	1377.3	1358.1	1338.9	1275.3	1211.6	1129.3	1046.9	964.8	882.7	818.8
17.5°	1273.0	1328.8	1331.6	1334.4	1270.7	1207.1	1115.9	1024.7	931.7	838.7	771.5
20°	1166.1	1248.5	1276.8	1305.1	1253.3	1201.5	1103.5	1005.5	901.4	797.3	726.8
22.5°	1057.0	1157.1	1208.8	1260.6	1222.2	1183.8	1079.5	975.2	865.3	755.4	683.9
25°	932.7	1041.9	1121.4	1201.0	1177.5	1154.0	1051.2	948.4	831.4	714.4	641.4
27.5°	824.3	935.2	1031.2	1127.2	1122.2	1117.1	1015.1	913.0	793.3	673.5	603.0
30°	727.8	831.2	938.5	1045.9	1058.3	1070.7	972.1	873.6	753.6	633.6	565.6
32.5°	642.4	732.6	847.8	963.0	987.3	1011.5	922.6	833.7	714.9	596.2	530.8
35°	572.5	654.3	769.5	884.7	915.0	945.3	868.0	790.7	675.0	559.3	496.9
37.5°	510.6	579.0	691.5	803.9	841.0	878.1	808.9	739.7	631.3	522.9	465.6
40°	459.3	514.4	617.7	721.0	764.0	806.9	749.8	692.7	589.9	487.1	434.3
42.5°	416.3	465.3	559.1	652.8	694.0	735.2	686.9	638.7	547.2	455.7	407.5
45°	379.7	418.9	504.0	589.1	628.3	667.5	626.0	584.6	504.0	423.4	378.4
47.5°	345.3	378.9	451.7	524.5	559.3	594.2	561.9	529.5	461.3	393.1	352.4
50°	314.5	341.6	405.2	468.9	499.2	529.5	501.0	472.4	416.3	360.3	324.9
52.5°	287.7	309.7	363.0	416.3	442.4	468.4	443.9	419.4	374.9	330.4	299.6
55°	261.2	279.9	326.1	372.4	390.1	407.7	388.8	369.9	334.0	298.1	272.1
57.5°	236.5	253.1	291.0	328.9	342.6	356.2	339.0	321.9	294.8	267.8	246.1
60°	212.2	225.9	257.4	289.0	297.3	305.7	291.8	277.9	258.9	240.0	220.5
62.5°	189.7	202.1	225.6	249.1	254.7	260.2	249.6	239.0	224.6	210.2	195.0
65°	166.5	175.8	195.0	214.2	217.8	221.3	212.0	202.6	191.7	180.9	169.8
67.5°	145.0	151.6	167.2	182.9	183.2	183.4	175.8	168.3	162.2	156.1	147.3
70°	124.0	130.4	140.7	151.1	151.3	151.6	145.5	139.5	134.9	130.4	123.8
72.5°	102.6	107.1	114.9	122.8	122.3	121.8	118.0	114.2	110.7	107.1	102.3
75°	83.1	86.9	92.2	97.5	96.0	94.5	92.5	90.4	87.4	84.4	81.3
77.5°	65.4	67.7	70.7	73.8	72.8	71.7	70.0	68.2	65.9	63.7	62.4
80°	48.0	49.0	51.0	53.1	52.5	52.0	50.0	48.0	47.5	47.0	45.2
82.5°	32.6	33.9	34.4	34.9	34.6	34.4	32.8	31.3	30.8	30.3	30.1
85°	19.5	19.7	20.0	20.2	19.5	18.7	18.2	17.7	17.7	17.7	17.4
87.5°	8.8	9.1	9.1	9.1	8.8	8.6	8.1	7.6	7.8	8.1	8.1
90°	7.1	6.0	4.9	3.9	3.0	2.1	1.3	0.4	1.3	2.1	3.0
92.5°	15.4	14.9	14.4	13.8	13.3	12.8	12.3	11.8	12.3	12.8	13.3
95°	27.6	26.9	26.2	25.6	25.0	24.3	23.7	23.1	23.7	24.3	25.0
97.5°	41.3	40.8	40.2	39.8	39.3	38.9	38.5	38.0	38.5	38.9	39.3
100°	56.7	56.3	55.9	55.4	54.9	54.3	53.8	53.3	53.8	54.3	54.9
102.5°	73.6	73.0	72.4	72.0	71.7	71.5	71.2	70.9	71.2	71.5	71.7
105°	90.9	90.1	89.4	88.9	88.7	88.5	88.4	88.2	88.4	88.5	88.7
107.5°	109.8	109.5	109.1	108.9	108.8	108.7	108.6	108.6	108.6	108.7	108.8
110°	128.6	128.4	128.2	128.1	127.9	127.7	127.5	127.4	127.5	127.7	127.9



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	147.4	147.4	147.4	147.3	147.2	147.1	147.1	147.0	147.1	147.1	147.2
115°	167.3	167.5	167.7	167.6	167.3	167.1	166.8	166.6	166.8	167.1	167.3
117.5°	186.5	186.7	186.9	186.9	186.8	186.7	186.6	186.5	186.6	186.7	186.8
120°	206.2	206.7	207.1	207.1	206.5	206.0	205.5	205.0	205.5	206.0	206.5
122.5°	225.3	225.5	225.7	225.6	225.2	224.9	224.5	224.2	224.5	224.9	225.2
125°	244.5	244.7	244.9	244.8	244.6	244.3	244.0	243.8	244.0	244.3	244.6
127.5°	263.7	263.9	264.1	263.9	263.4	262.8	262.3	261.8	262.3	262.8	263.4
130°	282.3	282.6	282.8	282.6	281.9	281.2	280.5	279.8	280.5	281.2	281.9
132.5°	300.6	300.7	300.9	300.6	299.9	299.2	298.5	297.9	298.5	299.2	299.9
135°	318.4	318.5	318.6	318.4	317.8	317.3	316.8	316.3	316.8	317.3	317.8
137.5°	335.7	335.5	335.2	334.9	334.4	334.0	333.6	333.1	333.6	334.0	334.4
140°	352.9	352.9	352.8	352.5	352.1	351.6	351.2	350.8	351.2	351.6	352.1
142.5°	369.2	369.0	368.9	368.6	368.1	367.7	367.3	366.8	367.3	367.7	368.1
145°	385.1	384.9	384.6	384.4	384.2	384.0	383.9	383.7	383.9	384.0	384.2
147.5°	400.4	400.1	399.9	399.6	399.2	398.9	398.5	398.2	398.5	398.9	399.2
150°	414.7	414.5	414.3	414.2	414.0	413.8	413.6	413.5	413.6	413.8	414.0
152.5°	427.4	427.3	427.2	427.1	426.8	426.5	426.3	426.0	426.3	426.5	426.8
155°	439.5	439.5	439.4	439.3	439.3	439.3	439.3	439.3	439.3	439.3	439.3
157.5°	450.5	450.4	450.3	450.3	450.4	450.5	450.6	450.7	450.6	450.5	450.4
160°	460.5	460.5	460.5	460.6	460.8	460.9	461.1	461.3	461.1	460.9	460.8
162.5°	469.7	469.6	469.6	469.6	469.9	470.2	470.4	470.7	470.4	470.2	469.9
165°	477.3	477.3	477.3	477.5	477.7	478.0	478.3	478.5	478.3	478.0	477.7
167.5°	483.8	483.7	483.7	483.8	484.1	484.5	484.8	485.2	484.8	484.5	484.1
170°	489.1	489.1	489.1	489.3	489.6	490.0	490.3	490.7	490.3	490.0	489.6
172.5°	493.4	493.4	493.4	493.6	493.9	494.3	494.6	495.0	494.6	494.3	493.9
175°	496.2	496.2	496.2	496.3	496.7	497.0	497.4	497.7	497.4	497.0	496.7
177.5°	497.7	497.7	497.7	497.9	498.2	498.6	498.9	499.3	498.9	498.6	498.2
180°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8
2.5°	1044.9	1035.0	1025.2	1017.6	1010.0	997.1	984.3	981.2	978.2	973.9	969.6
5°	990.8	966.6	942.3	920.6	898.9	881.9	865.0	853.9	842.8	834.7	826.6
7.5°	927.7	891.3	854.9	829.1	803.4	778.9	754.4	746.5	738.7	728.1	717.5
10°	866.5	826.4	786.2	752.6	719.0	695.0	671.0	661.4	651.8	638.4	625.0
12.5°	812.0	768.0	724.0	690.2	656.3	633.1	609.9	596.0	582.1	574.5	566.9
15°	754.9	707.9	660.9	629.6	598.2	577.3	556.3	544.2	532.0	524.7	517.4
17.5°	704.3	657.9	611.4	581.3	551.2	532.0	512.8	502.2	491.6	486.1	480.5
20°	656.3	610.9	565.4	536.1	506.8	491.1	475.5	468.6	461.8	457.3	452.7
22.5°	612.4	567.7	522.9	497.9	472.9	460.3	447.7	442.9	438.1	434.3	430.5
25°	568.4	528.5	488.6	467.4	446.1	435.8	425.4	420.6	415.8	412.0	408.3
27.5°	532.5	494.4	456.3	438.1	419.9	411.8	403.7	399.9	396.1	392.6	389.1
30°	497.7	463.6	429.5	413.8	398.1	390.8	383.5	379.7	375.9	372.6	369.3
32.5°	465.3	436.0	406.7	392.3	377.9	371.9	365.8	361.3	356.7	354.2	351.7
35°	434.5	408.3	382.0	370.1	358.2	352.2	346.1	342.3	338.5	336.5	334.5
37.5°	408.3	384.8	361.3	349.9	338.5	332.7	326.9	323.6	320.3	319.6	318.8
40°	381.5	361.3	341.1	329.9	318.8	313.8	308.7	306.7	304.7	304.2	303.7
42.5°	359.2	339.5	319.8	309.7	299.6	295.3	291.0	290.0	289.0	289.8	290.5
45°	333.5	317.1	300.6	291.3	281.9	278.4	274.9	274.1	273.3	274.9	276.4
47.5°	311.7	296.6	281.4	272.6	263.7	261.2	258.7	258.4	258.2	260.2	262.2
50°	289.5	274.9	260.2	253.1	246.1	243.8	241.5	242.3	243.0	246.3	249.6
52.5°	268.8	255.2	241.5	234.9	228.4	226.9	225.3	227.1	228.9	232.4	236.0
55°	246.1	233.7	221.3	216.3	211.2	209.7	208.2	211.7	215.2	218.5	221.8
57.5°	224.3	213.5	202.6	198.1	193.5	193.3	193.0	196.3	199.6	203.1	206.7
60°	201.1	192.0	182.9	179.4	175.8	176.3	176.8	180.6	184.4	187.2	190.0
62.5°	179.9	172.3	164.7	161.4	158.1	159.4	160.7	164.5	168.3	171.5	174.8
65°	158.7	152.3	146.0	143.7	141.5	143.2	145.0	148.3	151.6	153.9	156.1
67.5°	138.4	133.1	127.8	126.1	124.3	126.1	127.8	131.1	134.4	136.7	138.9
70°	117.2	112.9	108.6	107.4	106.1	108.1	110.1	112.9	115.7	118.0	120.3
72.5°	97.5	94.2	90.9	90.7	90.4	92.2	94.0	96.8	99.5	101.1	102.6
75°	78.3	76.5	74.8	74.5	74.3	76.0	77.8	79.3	80.8	82.1	83.4
77.5°	61.1	59.6	58.1	58.4	58.6	59.9	61.1	62.7	64.2	64.9	65.7
80°	43.5	42.9	42.4	42.9	43.5	44.5	45.5	46.5	47.5	48.0	48.5
82.5°	29.8	29.3	28.8	29.6	30.3	31.1	31.8	32.6	33.3	33.6	33.9
85°	17.2	17.9	18.7	18.7	18.7	18.9	19.2	19.5	19.7	19.5	19.2
87.5°	8.1	8.3	8.6	8.6	8.6	8.8	9.1	9.1	9.1	8.8	8.6
90°	3.9	4.9	6.0	7.1	8.3	9.4	9.8	10.1	10.5	10.8	11.1
92.5°	13.8	14.4	14.9	15.4	15.9	16.5	16.7	17.0	17.2	17.5	17.5
95°	25.6	26.2	26.9	27.6	28.3	29.0	29.3	29.7	30.0	30.4	30.6
97.5°	39.8	40.2	40.8	41.3	41.8	42.3	42.8	43.2	43.6	44.1	44.2
100°	55.4	55.9	56.3	56.7	57.2	57.6	57.9	58.1	58.4	58.7	58.9
102.5°	72.0	72.4	73.0	73.6	74.2	74.9	75.1	75.4	75.6	75.9	76.0
105°	88.9	89.4	90.1	90.9	91.7	92.5	92.5	92.5	92.5	92.5	92.6
107.5°	108.9	109.1	109.5	109.8	110.2	110.5	110.8	111.0	111.3	111.6	111.7
110°	128.1	128.2	128.4	128.6	128.8	128.9	129.3	129.6	130.0	130.3	130.4



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.3	147.4	147.4	147.4	147.4	147.4	147.8	148.2	148.7	149.1	149.3
115°	167.6	167.7	167.5	167.3	167.1	167.0	167.0	167.1	167.2	167.3	167.3
117.5°	186.9	186.9	186.7	186.5	186.3	186.2	186.2	186.2	186.2	186.2	186.0
120°	207.1	207.1	206.7	206.2	205.8	205.4	205.3	205.2	205.1	205.0	204.9
122.5°	225.6	225.7	225.5	225.3	225.1	225.0	224.7	224.4	224.2	223.9	223.7
125°	244.8	244.9	244.7	244.5	244.3	244.2	243.8	243.5	243.1	242.8	242.4
127.5°	263.9	264.1	263.9	263.7	263.5	263.4	262.8	262.3	261.8	261.3	260.8
130°	282.6	282.8	282.6	282.3	282.0	281.8	281.4	281.1	280.7	280.4	279.9
132.5°	300.6	300.9	300.7	300.6	300.4	300.2	299.8	299.3	298.9	298.5	298.0
135°	318.4	318.6	318.5	318.4	318.3	318.2	317.9	317.5	317.2	316.8	316.6
137.5°	334.9	335.2	335.5	335.7	336.0	336.3	335.8	335.4	335.0	334.5	334.2
140°	352.5	352.8	352.9	352.9	353.0	353.1	353.0	352.9	352.9	352.8	352.4
142.5°	368.6	368.9	369.0	369.2	369.4	369.6	369.5	369.4	369.3	369.2	369.0
145°	384.4	384.6	384.9	385.1	385.4	385.6	385.6	385.5	385.4	385.3	385.1
147.5°	399.6	399.9	400.1	400.4	400.7	400.9	400.9	400.9	400.9	400.9	400.7
150°	414.2	414.3	414.5	414.7	414.9	415.0	415.0	415.0	415.0	415.0	414.8
152.5°	427.1	427.2	427.3	427.4	427.5	427.6	427.7	427.9	428.1	428.3	428.1
155°	439.3	439.4	439.5	439.5	439.6	439.7	440.1	440.4	440.8	441.1	441.0
157.5°	450.3	450.3	450.4	450.5	450.6	450.7	451.0	451.4	451.7	452.1	452.0
160°	460.6	460.5	460.5	460.5	460.5	460.5	460.9	461.4	461.8	462.2	462.3
162.5°	469.6	469.6	469.6	469.7	469.8	469.9	470.3	470.8	471.2	471.6	471.6
165°	477.5	477.3	477.3	477.3	477.3	477.3	477.9	478.4	478.9	479.4	479.4
167.5°	483.8	483.7	483.7	483.8	483.9	484.0	484.5	485.1	485.6	486.1	486.1
170°	489.3	489.1	489.1	489.1	489.1	489.1	489.7	490.3	490.9	491.5	491.5
172.5°	493.6	493.4	493.4	493.4	493.4	493.4	493.9	494.5	495.0	495.5	495.5
175°	496.3	496.2	496.2	496.2	496.2	496.2	496.7	497.2	497.7	498.2	498.2
177.5°	497.9	497.7	497.7	497.7	497.7	497.7	498.2	498.8	499.3	499.8	499.8
180°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1088.8	1088.8	1088.8	1088.8
2.5°	967.8	966.1	959.0	951.9
5°	820.5	814.5	812.5	810.4
7.5°	717.0	716.5	705.9	695.2
10°	625.8	626.5	616.9	607.3
12.5°	560.6	554.3	553.5	552.8
15°	511.6	505.8	504.8	503.7
17.5°	477.0	473.4	472.4	471.4
20°	450.7	448.7	446.9	445.1
22.5°	428.0	425.4	423.9	422.4
25°	406.0	403.7	403.2	402.7
27.5°	386.3	383.5	383.5	383.5
30°	367.6	365.8	365.1	364.3
32.5°	350.1	348.6	348.6	348.6
35°	333.7	333.0	332.0	330.9
37.5°	318.8	318.8	318.3	317.8
40°	304.4	305.2	305.2	305.2
42.5°	291.3	292.0	292.0	292.0
45°	277.6	278.9	279.4	279.9
47.5°	264.3	266.3	266.8	267.3
50°	251.1	252.6	252.9	253.1
52.5°	237.7	239.5	240.8	242.0
55°	223.6	225.3	226.1	226.9
57.5°	208.4	210.2	210.4	210.7
60°	191.7	193.5	194.0	194.5
62.5°	175.8	176.8	177.3	177.9
65°	157.6	159.2	160.2	161.2
67.5°	140.2	141.5	141.5	141.5
70°	120.8	121.3	122.0	122.8
72.5°	102.8	103.1	103.1	103.1
75°	83.9	84.4	84.6	84.9
77.5°	65.9	66.2	66.2	66.2
80°	48.3	48.0	48.0	48.0
82.5°	33.1	32.3	32.3	32.3
85°	18.9	18.7	18.9	19.2
87.5°	8.6	8.6	8.6	8.6
90°	11.2	11.4	11.6	11.8
92.5°	17.4	17.2	17.0	16.9
95°	30.6	30.6	30.6	30.6
97.5°	44.2	44.1	44.0	43.9
100°	59.0	59.2	59.4	59.6
102.5°	75.9	75.8	75.7	75.6
105°	92.8	92.9	93.1	93.3
107.5°	111.6	111.5	111.4	111.3
110°	130.2	130.1	129.9	129.7



TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	149.3	149.3	149.3	149.3
115°	167.2	167.1	167.0	167.0
117.5°	185.8	185.5	185.2	185.0
120°	204.7	204.5	204.4	204.2
122.5°	223.4	223.1	222.9	222.6
125°	242.1	241.7	241.4	241.0
127.5°	260.5	260.1	259.8	259.4
130°	279.3	278.7	278.1	277.5
132.5°	297.6	297.2	296.7	296.3
135°	316.4	316.2	316.1	315.9
137.5°	333.9	333.6	333.4	333.1
140°	351.8	351.2	350.6	350.0
142.5°	368.5	368.1	367.7	367.2
145°	384.7	384.4	384.0	383.7
147.5°	400.1	399.6	399.1	398.6
150°	414.2	413.7	413.2	412.7
152.5°	427.7	427.3	426.8	426.4
155°	440.4	439.8	439.2	438.5
157.5°	451.5	451.0	450.4	449.9
160°	461.9	461.6	461.2	460.9
162.5°	470.9	470.3	469.7	469.1
165°	478.8	478.2	477.6	477.0
167.5°	485.6	485.1	484.5	484.0
170°	490.9	490.3	489.7	489.1
172.5°	494.9	494.2	493.6	493.0
175°	497.6	497.0	496.4	495.8
177.5°	499.2	498.6	497.9	497.3
180°	498.9	498.9	498.9	498.9

TEST NUMBER: P831379

CATALOG NUMBER: S123DIP-S340D365U850-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.65	13.53	13.57	14.45	15.64	14.89	15.76	15.80	16.69	17.88
	3H	14.30	15.08	15.23	16.02	17.23	16.32	17.10	17.24	18.03	19.25
	4H	14.88	15.62	15.82	16.56	17.78	16.77	17.51	17.71	18.45	19.67
	6H	15.25	15.93	16.20	16.88	18.11	17.04	17.72	17.99	18.67	19.90
	8H	15.35	16.00	16.30	16.96	18.19	17.11	17.75	18.06	18.72	19.95
	12H	15.39	16.01	16.36	16.97	18.22	17.12	17.74	18.09	18.70	19.95
4H	2H	13.23	13.97	14.17	14.91	16.13	15.05	15.80	16.00	16.74	17.96
	3H	15.06	15.68	16.01	16.65	17.88	16.67	17.29	17.63	18.26	19.50
	4H	15.76	16.32	16.72	17.29	18.55	17.26	17.82	18.22	18.79	20.05
	6H	16.23	16.72	17.21	17.71	18.97	17.66	18.15	18.64	19.14	20.40
	8H	16.37	16.82	17.35	17.81	19.08	17.78	18.23	18.75	19.21	20.48
	12H	16.44	16.85	17.44	17.85	19.12	17.82	18.23	18.82	19.23	20.51
8H	4H	16.03	16.48	17.00	17.46	18.73	17.37	17.82	18.34	18.80	20.07
	6H	16.62	16.99	17.62	18.01	19.28	17.87	18.24	18.87	19.27	20.54
	8H	16.82	17.15	17.84	18.16	19.45	18.05	18.38	19.06	19.39	20.68
	12H	16.95	17.24	17.96	18.24	19.58	18.15	18.44	19.17	19.44	20.78
12H	4H	16.03	16.43	17.02	17.43	18.71	17.34	17.75	18.34	18.75	20.03
	6H	16.67	16.99	17.68	18.01	19.30	17.88	18.21	18.89	19.22	20.51
	8H	16.90	17.19	17.92	18.20	19.53	18.08	18.37	19.10	19.38	20.71