

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831514

Luminaire Tested: S123DIP-S560D365U850-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831514
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U850-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4261.0 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 29.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68				
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58				
2	94	87	81	76	88	82	77	72	73	69	66	65	62	60	58	56	54	50				
3	86	77	70	64	81	73	67	62	66	61	56	59	55	51	52	49	47	43				
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	47	44	41	38				
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	39	36	34				
6	68	56	48	43	64	54	46	41	49	43	38	44	39	35	40	36	33	30				
7	63	51	43	38	60	49	42	37	45	39	34	40	36	32	37	33	30	27				
8	59	47	39	34	56	45	38	33	41	35	31	37	33	29	34	30	27	25				
9	55	43	36	31	52	41	35	30	38	32	28	35	30	26	32	28	25	23				
10	52	40	33	28	49	38	32	27	35	30	26	32	28	24	30	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	19268	19268	19268	19268	19268
5°	24368	23000	19440	15666	14397
10°	24604	25349	19311	12489	10912
15°	18532	23534	19179	10575	9229
20°	12912	19045	18935	9249	8383
25°	9846	14645	18517	8508	7862
30°	8518	11635	17851	7986	7444
35°	7903	9824	17082	7608	7150
40°	7481	8812	16002	7248	7050
45°	7232	8156	14630	6967	7005
50°	7109	7636	13006	6712	6970
55°	6844	7257	11410	6469	7000
60°	6598	6848	9836	6241	6885
65°	6199	6464	8484	5998	6749
70°	5725	5973	7216	5596	6351
75°	5182	5357	6184	5199	5802
80°	4271	4686	4891	4531	4891
85°	3384	3792	3594	3841	3903

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 16704 cd/sqm



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.2	4.0
10°-20°	421.0	9.9
20°-30°	498.5	11.7
30°-40°	501.2	11.8
40°-50°	459.9	10.8
50°-60°	379.6	8.9
60°-70°	268.5	6.3
70°-80°	143.3	3.4
80°-90°	37.4	0.9
90°-100°	32.1	0.8
100°-110°	97.2	2.3
110°-120°	165.5	3.9
120°-130°	217.7	5.1
130°-140°	244.7	5.7
140°-150°	240.6	5.6
150°-160°	202.5	4.8
160°-170°	134.8	3.2
170°-180°	47.2	1.1
0°-30°	1088.7	25.6
0°-40°	1590.0	37.3
0°-60°	2429.4	57.0
0°-90°	2878.6	67.6
90°-120°	294.8	6.9
90°-150°	997.8	23.4
90°-180°	1382.0	32.4
0°-180°	4261.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1790	1790	1790	1790	1790	
5°	2255	2129	1799	1450	1332	215
15°	1663	2112	1721	949	828	459
25°	829	1233	1559	716	662	391
35°	601	748	1300	579	544	378
45°	475	536	961	458	460	368
55°	365	387	608	345	373	326
65°	243	254	333	236	265	242
75°	125	129	149	125	140	131
85°	27	31	29	31	32	31
90°	12	9	0	9	12	7
95°	31	29	23	29	31	31
105°	93	92	88	92	93	99
115°	167	167	167	167	167	165
125°	241	244	244	244	241	216
135°	316	318	316	318	316	243
145°	384	386	384	386	384	240
155°	438	440	439	440	438	202
165°	477	477	478	477	477	135
175°	496	496	498	496	496	47
180°	499	499	499	499	499	



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1
2.5°	2017.7	2015.6	2013.5	2003.1	1992.7	1987.8	1982.8	1967.8	1952.9	1936.3	1919.6
5°	2255.2	2261.0	2266.9	2260.2	2253.6	2233.2	2212.9	2185.9	2158.9	2128.6	2098.2
7.5°	2364.9	2368.2	2371.5	2367.4	2363.2	2357.8	2352.4	2328.3	2304.2	2273.1	2241.9
10°	2251.1	2258.5	2266.0	2282.2	2298.4	2316.7	2335.0	2331.6	2328.3	2319.2	2310.0
12.5°	2001.0	2010.2	2019.3	2051.7	2084.1	2125.6	2167.2	2202.9	2238.6	2263.5	2288.5
15°	1663.0	1688.3	1713.6	1743.1	1772.6	1833.7	1894.7	1969.9	2045.1	2111.9	2178.8
17.5°	1369.7	1379.3	1388.9	1420.4	1452.0	1528.8	1605.7	1692.5	1779.3	1890.2	2001.0
20°	1127.2	1135.9	1144.6	1186.2	1227.7	1287.9	1348.2	1445.8	1543.4	1662.6	1781.8
22.5°	946.9	960.7	974.4	997.6	1020.9	1078.6	1136.3	1223.1	1309.9	1441.6	1573.3
25°	829.0	839.0	848.9	863.0	877.2	923.3	969.4	1040.8	1112.2	1233.1	1354.0
27.5°	748.4	752.6	756.7	770.8	785.0	814.9	844.8	906.2	967.7	1070.3	1172.9
30°	685.3	688.2	691.1	703.6	716.0	736.4	756.7	801.2	845.6	936.1	1026.7
32.5°	641.3	643.3	645.4	655.0	664.5	679.1	693.6	726.0	758.4	833.1	907.9
35°	601.4	602.6	603.9	610.9	618.0	628.8	639.6	664.1	688.6	747.6	806.6
37.5°	566.5	568.2	569.8	574.0	578.1	587.7	597.2	616.8	636.3	681.6	726.8
40°	532.4	535.4	538.3	541.2	544.1	552.0	559.9	574.8	589.8	627.1	664.5
42.5°	503.4	506.3	509.2	510.4	511.7	516.3	520.8	534.5	548.2	576.1	603.9
45°	475.1	476.4	477.6	478.9	480.1	483.9	487.6	499.6	511.7	535.8	559.9
47.5°	449.4	449.4	449.4	450.2	451.0	454.4	457.7	466.4	475.1	493.8	512.5
50°	424.5	424.5	424.5	423.2	422.0	424.0	426.1	432.8	439.4	456.0	472.6
52.5°	394.6	394.6	394.6	395.0	395.4	395.4	395.4	401.2	407.0	422.0	436.9
55°	364.7	366.3	368.0	366.7	365.5	366.3	367.1	370.9	374.6	386.7	398.7
57.5°	334.8	335.6	336.4	336.0	335.6	336.0	336.4	339.7	343.1	352.2	361.3
60°	306.5	306.5	306.5	305.7	304.9	305.7	306.5	308.2	309.8	318.1	326.4
62.5°	274.9	275.4	275.8	276.2	276.6	275.8	274.9	277.0	279.1	285.3	291.6
65°	243.4	243.8	244.2	245.5	246.7	245.9	245.0	247.1	249.2	253.8	258.3
67.5°	215.1	214.3	213.5	213.9	214.3	215.6	216.8	217.2	217.6	222.6	227.6
70°	181.9	182.7	183.6	183.2	182.7	183.2	183.6	184.8	186.1	189.8	193.5
72.5°	152.0	152.4	152.8	152.8	152.8	153.7	154.5	155.7	157.0	159.1	161.1
75°	124.6	124.6	124.6	125.4	126.3	126.7	127.1	127.1	127.1	128.8	130.4
77.5°	94.7	96.8	98.8	98.4	98.0	98.8	99.7	100.9	102.2	103.0	103.8
80°	68.9	68.9	68.9	69.4	69.8	71.0	72.3	73.1	73.9	75.6	77.3
82.5°	44.0	44.4	44.9	46.1	47.3	48.2	49.0	50.3	51.5	51.5	51.5
85°	27.4	26.6	25.8	26.6	27.4	28.2	29.1	29.5	29.9	30.7	31.6
87.5°	13.3	13.3	13.3	13.3	13.3	13.7	14.1	14.1	14.1	14.1	14.1
90°	11.8	11.6	11.4	11.2	11.1	10.8	10.5	10.1	9.8	9.4	8.3
92.5°	16.9	17.0	17.2	17.4	17.5	17.5	17.2	17.0	16.7	16.5	15.9
95°	30.6	30.6	30.6	30.6	30.6	30.4	30.0	29.7	29.3	29.0	28.3
97.5°	43.9	44.0	44.1	44.2	44.2	44.1	43.6	43.2	42.8	42.3	41.8
100°	59.6	59.4	59.2	59.0	58.9	58.7	58.4	58.1	57.9	57.6	57.2
102.5°	75.6	75.7	75.8	75.9	76.0	75.9	75.6	75.4	75.1	74.9	74.2
105°	93.3	93.1	92.9	92.8	92.6	92.5	92.5	92.5	92.5	92.5	91.7
107.5°	111.3	111.4	111.5	111.6	111.7	111.6	111.3	111.0	110.8	110.5	110.2
110°	129.7	129.9	130.1	130.2	130.4	130.3	130.0	129.6	129.3	128.9	128.8



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.3	149.3	149.3	149.3	149.3	149.1	148.7	148.2	147.8	147.4	147.4
115°	167.0	167.0	167.1	167.2	167.3	167.3	167.2	167.1	167.0	167.0	167.1
117.5°	185.0	185.2	185.5	185.8	186.0	186.2	186.2	186.2	186.2	186.2	186.3
120°	204.2	204.4	204.5	204.7	204.9	205.0	205.1	205.2	205.3	205.4	205.8
122.5°	222.6	222.9	223.1	223.4	223.7	223.9	224.2	224.4	224.7	225.0	225.1
125°	241.0	241.4	241.7	242.1	242.4	242.8	243.1	243.5	243.8	244.2	244.3
127.5°	259.4	259.8	260.1	260.5	260.8	261.3	261.8	262.3	262.8	263.4	263.5
130°	277.5	278.1	278.7	279.3	279.9	280.4	280.7	281.1	281.4	281.8	282.0
132.5°	296.3	296.7	297.2	297.6	298.0	298.5	298.9	299.3	299.8	300.2	300.4
135°	315.9	316.1	316.2	316.4	316.6	316.8	317.2	317.5	317.9	318.2	318.3
137.5°	333.1	333.4	333.6	333.9	334.2	334.5	335.0	335.4	335.8	336.3	336.0
140°	350.0	350.6	351.2	351.8	352.4	352.8	352.9	352.9	353.0	353.1	353.0
142.5°	367.2	367.7	368.1	368.5	369.0	369.2	369.3	369.4	369.5	369.6	369.4
145°	383.7	384.0	384.4	384.7	385.1	385.3	385.4	385.5	385.6	385.6	385.4
147.5°	398.6	399.1	399.6	400.1	400.7	400.9	400.9	400.9	400.9	400.9	400.7
150°	412.7	413.2	413.7	414.2	414.8	415.0	415.0	415.0	415.0	415.0	414.9
152.5°	426.4	426.8	427.3	427.7	428.1	428.3	428.1	427.9	427.7	427.6	427.5
155°	438.5	439.2	439.8	440.4	441.0	441.1	440.8	440.4	440.1	439.7	439.6
157.5°	449.9	450.4	451.0	451.5	452.0	452.1	451.7	451.4	451.0	450.7	450.6
160°	460.9	461.2	461.6	461.9	462.3	462.2	461.8	461.4	460.9	460.5	460.5
162.5°	469.1	469.7	470.3	470.9	471.6	471.6	471.2	470.8	470.3	469.9	469.8
165°	477.0	477.6	478.2	478.8	479.4	479.4	478.9	478.4	477.9	477.3	477.3
167.5°	484.0	484.5	485.1	485.6	486.1	486.1	485.6	485.1	484.5	484.0	483.9
170°	489.1	489.7	490.3	490.9	491.5	491.5	490.9	490.3	489.7	489.1	489.1
172.5°	493.0	493.6	494.2	494.9	495.5	495.5	495.0	494.5	493.9	493.4	493.4
175°	495.8	496.4	497.0	497.6	498.2	498.2	497.7	497.2	496.7	496.2	496.2
177.5°	497.3	497.9	498.6	499.2	499.8	499.8	499.3	498.8	498.2	497.7	497.7
180°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1
2.5°	1914.7	1909.7	1891.4	1873.1	1852.4	1831.6	1816.2	1800.9	1778.0	1755.2	1736.5
5°	2075.0	2051.7	2013.1	1974.5	1922.1	1869.8	1834.5	1799.2	1751.8	1704.5	1666.7
7.5°	2202.1	2162.2	2108.2	2054.2	1985.7	1917.1	1852.4	1787.6	1715.3	1643.0	1584.1
10°	2283.1	2256.1	2193.8	2131.5	2039.7	1947.9	1857.3	1766.8	1673.8	1580.7	1502.7
12.5°	2290.9	2293.4	2236.1	2178.8	2075.0	1971.1	1861.1	1751.0	1633.9	1516.8	1425.8
15°	2221.6	2264.4	2232.8	2201.2	2096.6	1991.9	1856.5	1721.1	1586.1	1451.2	1346.1
17.5°	2092.8	2184.6	2189.2	2193.8	2089.1	1984.4	1834.5	1684.6	1531.7	1378.9	1268.4
20°	1917.1	2052.5	2099.1	2145.6	2060.4	1975.3	1814.1	1653.0	1481.9	1310.8	1194.9
22.5°	1737.7	1902.2	1987.3	2072.5	2009.4	1946.2	1774.7	1603.2	1422.5	1241.8	1124.3
25°	1533.4	1712.8	1843.6	1974.5	1935.8	1897.2	1728.2	1559.1	1366.8	1174.5	1054.5
27.5°	1355.2	1537.5	1695.4	1853.2	1844.9	1836.6	1668.8	1501.0	1304.1	1107.3	991.4
30°	1196.6	1366.4	1542.9	1719.5	1739.8	1760.2	1598.2	1436.2	1238.9	1041.6	929.9
32.5°	1056.2	1204.4	1393.8	1583.2	1623.1	1663.0	1516.8	1370.6	1175.4	980.2	872.6
35°	941.1	1075.7	1265.1	1454.5	1504.3	1554.2	1427.1	1300.0	1109.8	919.5	816.9
37.5°	839.4	951.9	1136.8	1321.6	1382.6	1443.7	1329.9	1216.1	1037.9	859.7	765.4
40°	755.1	845.6	1015.5	1185.3	1255.9	1326.6	1232.7	1138.8	969.8	800.8	713.9
42.5°	684.5	765.0	919.1	1073.2	1140.9	1208.6	1129.3	1049.9	899.6	749.3	669.9
45°	624.2	688.6	828.6	968.5	1032.9	1097.3	1029.2	961.1	828.6	696.1	622.2
47.5°	567.8	623.0	742.6	862.2	919.5	976.8	923.7	870.5	758.4	646.2	579.4
50°	517.1	561.5	666.2	770.8	820.7	870.5	823.6	776.7	684.5	592.3	534.1
52.5°	473.1	509.2	596.8	684.5	727.2	770.0	729.7	689.4	616.3	543.2	492.6
55°	429.4	460.2	536.2	612.2	641.3	670.3	639.2	608.0	549.1	490.1	447.3
57.5°	388.7	416.2	478.5	540.8	563.2	585.6	557.4	529.1	484.7	440.2	404.5
60°	348.9	371.3	423.2	475.1	488.8	502.5	479.7	456.9	425.7	394.6	362.6
62.5°	311.9	332.3	370.9	409.5	418.6	427.8	410.3	392.9	369.2	345.6	320.6
65°	273.7	289.1	320.6	352.2	358.0	363.8	348.5	333.1	315.2	297.4	279.1
67.5°	238.4	249.2	274.9	300.7	301.1	301.5	289.1	276.6	266.6	256.7	242.1
70°	203.9	214.3	231.3	248.4	248.8	249.2	239.2	229.3	221.8	214.3	203.5
72.5°	168.6	176.1	189.0	201.8	201.0	200.2	194.0	187.7	181.9	176.1	168.2
75°	136.6	142.9	151.6	160.3	157.8	155.3	152.0	148.7	143.7	138.7	133.7
77.5°	107.6	111.3	116.3	121.3	119.6	118.0	115.0	112.1	108.4	104.7	102.6
80°	78.9	80.6	83.9	87.2	86.4	85.6	82.2	78.9	78.1	77.3	74.3
82.5°	53.6	55.7	56.5	57.3	56.9	56.5	54.0	51.5	50.7	49.8	49.4
85°	32.0	32.4	32.8	33.2	32.0	30.7	29.9	29.1	29.1	29.1	28.7
87.5°	14.5	15.0	15.0	15.0	14.5	14.1	13.3	12.5	12.9	13.3	13.3
90°	7.1	6.0	4.9	3.9	3.0	2.1	1.3	0.4	1.3	2.1	3.0
92.5°	15.4	14.9	14.4	13.8	13.3	12.8	12.3	11.8	12.3	12.8	13.3
95°	27.6	26.9	26.2	25.6	25.0	24.3	23.7	23.1	23.7	24.3	25.0
97.5°	41.3	40.8	40.2	39.8	39.3	38.9	38.5	38.0	38.5	38.9	39.3
100°	56.7	56.3	55.9	55.4	54.9	54.3	53.8	53.3	53.8	54.3	54.9
102.5°	73.6	73.0	72.4	72.0	71.7	71.5	71.2	70.9	71.2	71.5	71.7
105°	90.9	90.1	89.4	88.9	88.7	88.5	88.4	88.2	88.4	88.5	88.7
107.5°	109.8	109.5	109.1	108.9	108.8	108.7	108.6	108.6	108.6	108.7	108.8
110°	128.6	128.4	128.2	128.1	127.9	127.7	127.5	127.4	127.5	127.7	127.9



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	147.4	147.4	147.4	147.3	147.2	147.1	147.1	147.0	147.1	147.1	147.2
115°	167.3	167.5	167.7	167.6	167.3	167.1	166.8	166.6	166.8	167.1	167.3
117.5°	186.5	186.7	186.9	186.9	186.8	186.7	186.6	186.5	186.6	186.7	186.8
120°	206.2	206.7	207.1	207.1	206.5	206.0	205.5	205.0	205.5	206.0	206.5
122.5°	225.3	225.5	225.7	225.6	225.2	224.9	224.5	224.2	224.5	224.9	225.2
125°	244.5	244.7	244.9	244.8	244.6	244.3	244.0	243.8	244.0	244.3	244.6
127.5°	263.7	263.9	264.1	263.9	263.4	262.8	262.3	261.8	262.3	262.8	263.4
130°	282.3	282.6	282.8	282.6	281.9	281.2	280.5	279.8	280.5	281.2	281.9
132.5°	300.6	300.7	300.9	300.6	299.9	299.2	298.5	297.9	298.5	299.2	299.9
135°	318.4	318.5	318.6	318.4	317.8	317.3	316.8	316.3	316.8	317.3	317.8
137.5°	335.7	335.5	335.2	334.9	334.4	334.0	333.6	333.1	333.6	334.0	334.4
140°	352.9	352.9	352.8	352.5	352.1	351.6	351.2	350.8	351.2	351.6	352.1
142.5°	369.2	369.0	368.9	368.6	368.1	367.7	367.3	366.8	367.3	367.7	368.1
145°	385.1	384.9	384.6	384.4	384.2	384.0	383.9	383.7	383.9	384.0	384.2
147.5°	400.4	400.1	399.9	399.6	399.2	398.9	398.5	398.2	398.5	398.9	399.2
150°	414.7	414.5	414.3	414.2	414.0	413.8	413.6	413.5	413.6	413.8	414.0
152.5°	427.4	427.3	427.2	427.1	426.8	426.5	426.3	426.0	426.3	426.5	426.8
155°	439.5	439.5	439.4	439.3	439.3	439.3	439.3	439.3	439.3	439.3	439.3
157.5°	450.5	450.4	450.3	450.3	450.4	450.5	450.6	450.7	450.6	450.5	450.4
160°	460.5	460.5	460.5	460.6	460.8	460.9	461.1	461.3	461.1	460.9	460.8
162.5°	469.7	469.6	469.6	469.6	469.9	470.2	470.4	470.7	470.4	470.2	469.9
165°	477.3	477.3	477.3	477.5	477.7	478.0	478.3	478.5	478.3	478.0	477.7
167.5°	483.8	483.7	483.7	483.8	484.1	484.5	484.8	485.2	484.8	484.5	484.1
170°	489.1	489.1	489.1	489.3	489.6	490.0	490.3	490.7	490.3	490.0	489.6
172.5°	493.4	493.4	493.4	493.6	493.9	494.3	494.6	495.0	494.6	494.3	493.9
175°	496.2	496.2	496.2	496.3	496.7	497.0	497.4	497.7	497.4	497.0	496.7
177.5°	497.7	497.7	497.7	497.9	498.2	498.6	498.9	499.3	498.9	498.6	498.2
180°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1	1790.1
2.5°	1717.8	1701.6	1685.4	1672.9	1660.5	1639.3	1618.1	1613.1	1608.1	1601.1	1594.0
5°	1628.9	1589.0	1549.2	1513.5	1477.7	1449.9	1422.1	1403.8	1385.5	1372.2	1359.0
7.5°	1525.1	1465.3	1405.5	1363.1	1320.7	1280.5	1240.2	1227.3	1214.4	1197.0	1179.5
10°	1424.6	1358.5	1292.5	1237.3	1182.0	1142.6	1103.1	1087.3	1071.5	1049.5	1027.5
12.5°	1334.9	1262.6	1190.3	1134.7	1079.0	1040.8	1002.6	979.8	956.9	944.5	932.0
15°	1241.0	1163.7	1086.5	1035.0	983.5	949.0	914.6	894.6	874.7	862.6	850.6
17.5°	1157.9	1081.5	1005.1	955.7	906.2	874.7	843.1	825.7	808.2	799.1	790.0
20°	1079.0	1004.3	929.5	881.3	833.1	807.4	781.6	770.4	759.2	751.7	744.3
22.5°	1006.8	933.2	859.7	818.6	777.5	756.7	736.0	728.1	720.2	713.9	707.7
25°	934.5	868.9	803.2	768.4	733.5	716.4	699.4	691.5	683.6	677.4	671.2
27.5°	875.5	812.8	750.1	720.2	690.3	677.0	663.7	657.5	651.2	645.4	639.6
30°	818.2	762.1	706.1	680.3	654.6	642.5	630.5	624.2	618.0	612.6	607.2
32.5°	765.0	716.9	668.7	645.0	621.3	611.4	601.4	593.9	586.4	582.3	578.1
35°	714.4	671.2	628.0	608.5	588.9	579.0	569.0	562.8	556.5	553.2	549.9
37.5°	671.2	632.5	593.9	575.2	556.5	547.0	537.4	532.0	526.6	525.4	524.1
40°	627.1	593.9	560.7	542.4	524.1	515.8	507.5	504.2	500.9	500.1	499.2
42.5°	590.6	558.2	525.8	509.2	492.6	485.5	478.5	476.8	475.1	476.4	477.6
45°	548.2	521.2	494.2	478.9	463.5	457.7	451.9	450.6	449.4	451.9	454.4
47.5°	512.5	487.6	462.7	448.1	433.6	429.4	425.3	424.9	424.5	427.8	431.1
50°	476.0	451.9	427.8	416.2	404.5	400.8	397.1	398.3	399.5	404.9	410.3
52.5°	441.9	419.5	397.1	386.3	375.5	373.0	370.5	373.4	376.3	382.1	387.9
55°	404.5	384.2	363.8	355.5	347.2	344.7	342.2	348.0	353.9	359.3	364.7
57.5°	368.8	351.0	333.1	325.6	318.1	317.7	317.3	322.7	328.1	333.9	339.7
60°	330.6	315.6	300.7	294.9	289.1	289.9	290.7	297.0	303.2	307.8	312.3
62.5°	295.7	283.3	270.8	265.4	260.0	262.1	264.1	270.4	276.6	282.0	287.4
65°	260.8	250.4	240.1	236.3	232.6	235.5	238.4	243.8	249.2	252.9	256.7
67.5°	227.6	218.9	210.2	207.2	204.3	207.2	210.2	215.6	221.0	224.7	228.4
70°	192.7	185.7	178.6	176.5	174.4	177.8	181.1	185.7	190.2	194.0	197.7
72.5°	160.3	154.9	149.5	149.1	148.7	151.6	154.5	159.1	163.6	166.1	168.6
75°	128.8	125.8	122.9	122.5	122.1	125.0	127.9	130.4	132.9	135.0	137.1
77.5°	100.5	98.0	95.5	95.9	96.4	98.4	100.5	103.0	105.5	106.7	108.0
80°	71.4	70.6	69.8	70.6	71.4	73.1	74.8	76.4	78.1	78.9	79.7
82.5°	49.0	48.2	47.3	48.6	49.8	51.1	52.3	53.6	54.8	55.2	55.7
85°	28.2	29.5	30.7	30.7	30.7	31.1	31.6	32.0	32.4	32.0	31.6
87.5°	13.3	13.7	14.1	14.1	14.1	14.5	15.0	15.0	15.0	14.5	14.1
90°	3.9	4.9	6.0	7.1	8.3	9.4	9.8	10.1	10.5	10.8	11.1
92.5°	13.8	14.4	14.9	15.4	15.9	16.5	16.7	17.0	17.2	17.5	17.5
95°	25.6	26.2	26.9	27.6	28.3	29.0	29.3	29.7	30.0	30.4	30.6
97.5°	39.8	40.2	40.8	41.3	41.8	42.3	42.8	43.2	43.6	44.1	44.2
100°	55.4	55.9	56.3	56.7	57.2	57.6	57.9	58.1	58.4	58.7	58.9
102.5°	72.0	72.4	73.0	73.6	74.2	74.9	75.1	75.4	75.6	75.9	76.0
105°	88.9	89.4	90.1	90.9	91.7	92.5	92.5	92.5	92.5	92.5	92.6
107.5°	108.9	109.1	109.5	109.8	110.2	110.5	110.8	111.0	111.3	111.6	111.7
110°	128.1	128.2	128.4	128.6	128.8	128.9	129.3	129.6	130.0	130.3	130.4



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.3	147.4	147.4	147.4	147.4	147.4	147.8	148.2	148.7	149.1	149.3
115°	167.6	167.7	167.5	167.3	167.1	167.0	167.0	167.1	167.2	167.3	167.3
117.5°	186.9	186.9	186.7	186.5	186.3	186.2	186.2	186.2	186.2	186.2	186.0
120°	207.1	207.1	206.7	206.2	205.8	205.4	205.3	205.2	205.1	205.0	204.9
122.5°	225.6	225.7	225.5	225.3	225.1	225.0	224.7	224.4	224.2	223.9	223.7
125°	244.8	244.9	244.7	244.5	244.3	244.2	243.8	243.5	243.1	242.8	242.4
127.5°	263.9	264.1	263.9	263.7	263.5	263.4	262.8	262.3	261.8	261.3	260.8
130°	282.6	282.8	282.6	282.3	282.0	281.8	281.4	281.1	280.7	280.4	279.9
132.5°	300.6	300.9	300.7	300.6	300.4	300.2	299.8	299.3	298.9	298.5	298.0
135°	318.4	318.6	318.5	318.4	318.3	318.2	317.9	317.5	317.2	316.8	316.6
137.5°	334.9	335.2	335.5	335.7	336.0	336.3	335.8	335.4	335.0	334.5	334.2
140°	352.5	352.8	352.9	352.9	353.0	353.1	353.0	352.9	352.9	352.8	352.4
142.5°	368.6	368.9	369.0	369.2	369.4	369.6	369.5	369.4	369.3	369.2	369.0
145°	384.4	384.6	384.9	385.1	385.4	385.6	385.6	385.5	385.4	385.3	385.1
147.5°	399.6	399.9	400.1	400.4	400.7	400.9	400.9	400.9	400.9	400.9	400.7
150°	414.2	414.3	414.5	414.7	414.9	415.0	415.0	415.0	415.0	415.0	414.8
152.5°	427.1	427.2	427.3	427.4	427.5	427.6	427.7	427.9	428.1	428.3	428.1
155°	439.3	439.4	439.5	439.5	439.6	439.7	440.1	440.4	440.8	441.1	441.0
157.5°	450.3	450.3	450.4	450.5	450.6	450.7	451.0	451.4	451.7	452.1	452.0
160°	460.6	460.5	460.5	460.5	460.5	460.5	460.9	461.4	461.8	462.2	462.3
162.5°	469.6	469.6	469.6	469.7	469.8	469.9	470.3	470.8	471.2	471.6	471.6
165°	477.5	477.3	477.3	477.3	477.3	477.3	477.9	478.4	478.9	479.4	479.4
167.5°	483.8	483.7	483.7	483.8	483.9	484.0	484.5	485.1	485.6	486.1	486.1
170°	489.3	489.1	489.1	489.1	489.1	489.1	489.7	490.3	490.9	491.5	491.5
172.5°	493.6	493.4	493.4	493.4	493.4	493.4	493.9	494.5	495.0	495.5	495.5
175°	496.3	496.2	496.2	496.2	496.2	496.2	496.7	497.2	497.7	498.2	498.2
177.5°	497.9	497.7	497.7	497.7	497.7	497.7	498.2	498.8	499.3	499.8	499.8
180°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1790.1	1790.1	1790.1	1790.1
2.5°	1591.1	1588.2	1576.6	1565.0
5°	1349.0	1339.0	1335.7	1332.4
7.5°	1178.7	1177.9	1160.4	1143.0
10°	1028.8	1030.0	1014.2	998.4
12.5°	921.6	911.2	910.0	908.7
15°	841.0	831.5	829.8	828.2
17.5°	784.1	778.3	776.7	775.0
20°	740.9	737.6	734.7	731.8
22.5°	703.6	699.4	696.9	694.4
25°	667.4	663.7	662.9	662.0
27.5°	635.0	630.5	630.5	630.5
30°	604.3	601.4	600.1	598.9
32.5°	575.6	573.2	573.2	573.2
35°	548.6	547.4	545.7	544.1
37.5°	524.1	524.1	523.3	522.5
40°	500.5	501.7	501.7	501.7
42.5°	478.9	480.1	480.1	480.1
45°	456.4	458.5	459.4	460.2
47.5°	434.4	437.8	438.6	439.4
50°	412.8	415.3	415.7	416.2
52.5°	390.8	393.7	395.8	397.9
55°	367.6	370.5	371.7	373.0
57.5°	342.6	345.6	346.0	346.4
60°	315.2	318.1	319.0	319.8
62.5°	289.1	290.7	291.6	292.4
65°	259.2	261.7	263.3	265.0
67.5°	230.5	232.6	232.6	232.6
70°	198.5	199.4	200.6	201.8
72.5°	169.0	169.5	169.5	169.5
75°	137.9	138.7	139.1	139.5
77.5°	108.4	108.8	108.8	108.8
80°	79.3	78.9	78.9	78.9
82.5°	54.4	53.2	53.2	53.2
85°	31.1	30.7	31.1	31.6
87.5°	14.1	14.1	14.1	14.1
90°	11.2	11.4	11.6	11.8
92.5°	17.4	17.2	17.0	16.9
95°	30.6	30.6	30.6	30.6
97.5°	44.2	44.1	44.0	43.9
100°	59.0	59.2	59.4	59.6
102.5°	75.9	75.8	75.7	75.6
105°	92.8	92.9	93.1	93.3
107.5°	111.6	111.5	111.4	111.3
110°	130.2	130.1	129.9	129.7



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	149.3	149.3	149.3	149.3
115°	167.2	167.1	167.0	167.0
117.5°	185.8	185.5	185.2	185.0
120°	204.7	204.5	204.4	204.2
122.5°	223.4	223.1	222.9	222.6
125°	242.1	241.7	241.4	241.0
127.5°	260.5	260.1	259.8	259.4
130°	279.3	278.7	278.1	277.5
132.5°	297.6	297.2	296.7	296.3
135°	316.4	316.2	316.1	315.9
137.5°	333.9	333.6	333.4	333.1
140°	351.8	351.2	350.6	350.0
142.5°	368.5	368.1	367.7	367.2
145°	384.7	384.4	384.0	383.7
147.5°	400.1	399.6	399.1	398.6
150°	414.2	413.7	413.2	412.7
152.5°	427.7	427.3	426.8	426.4
155°	440.4	439.8	439.2	438.5
157.5°	451.5	451.0	450.4	449.9
160°	461.9	461.6	461.2	460.9
162.5°	470.9	470.3	469.7	469.1
165°	478.8	478.2	477.6	477.0
167.5°	485.6	485.1	484.5	484.0
170°	490.9	490.3	489.7	489.1
172.5°	494.9	494.2	493.6	493.0
175°	497.6	497.0	496.4	495.8
177.5°	499.2	498.6	497.9	497.3
180°	498.9	498.9	498.9	498.9



TEST NUMBER: P831514

CATALOG NUMBER: S123DIP-S560D365U850-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.35	16.34	16.15	17.16	18.15	17.59	18.58	18.39	19.39	20.39
	3H	17.01	17.89	17.82	18.72	19.75	19.02	19.91	19.83	20.73	21.76
	4H	17.59	18.43	18.42	19.26	20.30	19.48	20.31	20.31	21.15	22.19
	6H	17.97	18.74	18.81	19.58	20.63	19.76	20.53	20.60	21.37	22.42
	8H	18.07	18.80	18.92	19.66	20.71	19.83	20.56	20.68	21.42	22.47
	12H	18.12	18.81	18.97	19.67	20.75	19.85	20.55	20.70	21.40	22.48
4H	2H	15.94	16.78	16.77	17.61	18.65	17.77	18.60	18.60	19.43	20.48
	3H	17.78	18.48	18.62	19.34	20.40	19.40	20.09	20.24	20.96	22.01
	4H	18.48	19.12	19.34	19.98	21.06	19.98	20.62	20.84	21.48	22.56
	6H	18.97	19.51	19.84	20.40	21.49	20.40	20.94	21.27	21.83	22.92
	8H	19.10	19.61	19.98	20.50	21.60	20.51	21.02	21.39	21.90	23.00
	12H	19.18	19.64	20.07	20.54	21.64	20.56	21.02	21.46	21.92	23.03
8H	4H	18.76	19.27	19.63	20.15	21.25	20.10	20.61	20.97	21.49	22.59
	6H	19.35	19.77	20.26	20.70	21.80	20.61	21.03	21.51	21.95	23.05
	8H	19.56	19.93	20.47	20.85	21.97	20.79	21.16	21.70	22.08	23.19
	12H	19.69	20.02	20.61	20.93	22.10	20.89	21.22	21.81	22.13	23.30
12H	4H	18.77	19.22	19.66	20.13	21.23	20.08	20.54	20.97	21.44	22.55
	6H	19.40	19.78	20.32	20.70	21.81	20.62	20.99	21.53	21.91	23.03
	8H	19.64	19.97	20.56	20.88	22.05	20.83	21.15	21.74	22.06	23.23