

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331899-840

Luminaire Tested: **S123DIP-S340D1025U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331899-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4983.2 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	71	67	75	69	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	15
5	65	53	45	40	58	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	17	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5890	5890	5890
5°	5919	5837	5877
10°	5879	5786	5822
15°	5810	5721	5731
20°	5730	5628	5632
25°	5621	5516	5505
30°	5504	5392	5351
35°	5380	5261	5194
40°	5251	5117	5039
45°	5107	4985	4864
50°	4963	4823	4687
55°	4778	4654	4511
60°	4590	4456	4316
65°	4422	4241	4111
70°	4176	3997	3821
75°	3818	3681	3523
80°	3440	3298	3267
85°	3013	2902	2791



TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	1.0
10°-20°	145.6	2.9
20°-30°	215.0	4.3
30°-40°	251.2	5.0
40°-50°	252.5	5.1
50°-60°	221.8	4.5
60°-70°	165.2	3.3
70°-80°	94.1	1.9
80°-90°	30.8	0.6
90°-100°	83.6	1.7
100°-110°	250.2	5.0
110°-120°	425.6	8.5
120°-130°	559.8	11.2
130°-140°	629.2	12.6
140°-150°	618.5	12.4
150°-160°	520.7	10.4
160°-170°	346.6	7.0
170°-180°	121.4	2.4
0°-30°	412.1	8.3
0°-40°	663.3	13.3
0°-60°	1137.6	22.8
0°-90°	1427.8	28.7
90°-120°	759.4	15.2
90°-150°	2566.9	51.5
90°-180°	3555.0	71.3
0°-180°	4983.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	548	545	540	545	544	52
15°	521	519	513	517	514	147
25°	473	470	464	465	464	218
35°	409	406	400	398	395	256
45°	336	333	328	322	320	259
55°	255	254	248	243	240	228
65°	174	171	166	163	161	171
75°	92	90	88	86	85	98
85°	24	24	24	23	23	27
90°	1	11	24	28	30	5
95°	60	67	75	78	79	67
105°	227	229	238	238	240	243
115°	428	431	429	430	429	424
125°	627	630	628	624	620	559
135°	814	819	818	815	812	627
145°	987	989	992	991	987	616
155°	1130	1130	1131	1134	1128	520
165°	1231	1228	1228	1233	1227	347
175°	1280	1276	1276	1282	1275	122
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	549.2	548.8	548.5	548.2	547.8	547.1	546.2	545.3	544.4	543.5	544.3
5°	547.8	547.1	546.6	546.1	545.6	544.8	543.6	542.5	541.3	540.2	541.2
7.5°	542.4	541.8	541.3	540.8	540.3	539.4	538.3	537.0	535.8	534.6	535.5
10°	537.9	537.3	536.7	536.2	535.7	534.8	533.4	532.1	530.7	529.4	530.3
12.5°	531.8	531.4	530.9	530.5	530.1	529.2	528.0	526.6	525.3	524.1	524.8
15°	521.4	521.0	520.5	520.1	519.7	518.8	517.5	516.0	514.7	513.4	514.2
17.5°	509.2	508.7	508.2	507.6	507.1	506.1	504.7	503.4	502.0	500.7	501.2
20°	500.2	499.6	499.0	498.3	497.7	496.7	495.3	493.9	492.6	491.3	491.7
22.5°	490.0	489.4	488.8	488.2	487.6	486.6	485.1	483.8	482.4	481.1	481.4
25°	473.3	472.7	472.1	471.5	470.9	469.9	468.5	467.2	465.7	464.4	464.5
27.5°	455.6	454.9	454.3	453.7	453.1	452.1	450.7	449.2	447.8	446.3	446.4
30°	442.8	442.2	441.7	441.2	440.7	439.7	438.3	436.8	435.4	433.8	433.8
32.5°	430.0	429.3	428.6	427.9	427.3	426.3	425.2	424.0	422.9	421.8	421.2
35°	409.4	408.8	408.1	407.5	406.9	405.9	404.6	403.1	401.8	400.4	399.8
37.5°	388.3	387.5	386.7	385.9	385.2	384.1	382.6	381.2	379.9	378.5	377.8
40°	373.7	372.9	372.3	371.7	371.1	370.0	368.6	367.1	365.7	364.2	363.3
42.5°	358.9	358.2	357.5	356.8	356.1	355.0	353.6	352.0	350.6	349.1	348.3
45°	335.5	335.1	334.7	334.3	333.9	333.0	331.5	330.2	328.8	327.5	326.3
47.5°	312.3	311.6	311.0	310.4	309.8	308.9	307.6	306.3	305.1	303.8	302.6
50°	296.4	295.9	295.4	294.9	294.4	293.4	292.1	290.7	289.3	288.0	286.8
52.5°	279.8	279.5	279.1	278.8	278.4	277.5	276.1	274.7	273.3	271.8	270.8
55°	254.6	254.5	254.4	254.3	254.2	253.4	252.1	250.6	249.3	248.0	246.8
57.5°	230.5	230.1	229.7	229.4	229.0	228.3	227.2	226.1	225.1	224.0	223.0
60°	213.2	213.1	213.0	212.9	212.8	212.1	210.8	209.5	208.3	207.0	206.1
62.5°	197.7	197.4	197.2	196.9	196.6	195.9	194.6	193.4	192.1	190.9	190.0
65°	173.6	173.1	172.6	172.1	171.6	170.8	169.8	168.6	167.6	166.5	165.7
67.5°	148.1	147.6	147.2	146.7	146.3	145.6	144.9	144.1	143.3	142.5	141.8
70°	132.7	132.1	131.5	130.8	130.2	129.6	129.0	128.3	127.6	127.0	126.3
72.5°	116.5	116.0	115.6	115.1	114.6	114.1	113.4	112.7	112.0	111.3	110.6
75°	91.8	91.3	90.9	90.5	90.1	89.7	89.4	89.1	88.8	88.5	88.0
77.5°	69.8	69.6	69.4	69.2	68.9	68.6	68.3	67.9	67.5	67.1	66.8
80°	55.5	55.2	54.9	54.6	54.2	54.0	53.8	53.6	53.4	53.2	53.0
82.5°	41.6	41.5	41.5	41.4	41.3	41.3	41.2	41.2	41.2	41.1	40.9
85°	24.4	24.2	24.0	23.8	23.6	23.5	23.5	23.5	23.5	23.5	23.3
87.5°	10.0	10.2	10.4	10.6	10.8	11.1	11.6	12.1	12.6	13.1	13.2
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	24.4	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4
95°	59.5	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5
97.5°	105.6	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8
100°	137.1	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9
102.5°	173.4	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3
105°	226.8	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9
107.5°	288.9	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5
110°	327.6	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5



TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	367.9	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6
115°	428.4	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7
117.5°	489.3	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7
120°	527.3	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0
122.5°	566.7	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9
125°	627.0	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1
127.5°	682.7	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6
130°	719.7	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9
132.5°	756.9	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6
135°	813.5	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7
137.5°	866.0	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6
140°	902.2	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.2	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9
145°	986.8	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7
147.5°	1032.1	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5
150°	1063.5	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5
152.5°	1089.3	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7
155°	1130.0	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0
157.5°	1164.7	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3
160°	1186.5	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6
162.5°	1205.9	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0
165°	1230.8	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1
167.5°	1250.8	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0
170°	1262.1	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6
172.5°	1270.9	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3
175°	1280.2	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6
177.5°	1284.0	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	545.1	546.0	546.8	547.2	547.1	547.0	546.9	546.8
5°	542.3	543.3	544.4	544.8	544.6	544.4	544.1	543.9
7.5°	536.5	537.5	538.4	538.8	538.7	538.6	538.5	538.3
10°	531.3	532.2	533.1	533.5	533.3	533.1	532.9	532.7
12.5°	525.4	526.1	526.8	527.1	527.0	526.8	526.7	526.6
15°	515.0	515.8	516.7	516.8	516.1	515.5	514.9	514.3
17.5°	501.8	502.4	503.0	503.2	502.9	502.7	502.5	502.3
20°	492.1	492.5	492.9	493.0	492.6	492.3	492.0	491.7
22.5°	481.7	482.1	482.4	482.4	482.0	481.6	481.2	480.8
25°	464.6	464.7	464.8	464.7	464.4	464.1	463.8	463.5
27.5°	446.5	446.6	446.6	446.5	446.1	445.7	445.2	444.8
30°	433.8	433.8	433.8	433.4	432.7	432.0	431.3	430.5
32.5°	420.6	420.0	419.5	419.0	418.6	418.2	417.8	417.4
35°	399.2	398.6	397.9	397.4	396.9	396.3	395.8	395.3
37.5°	377.0	376.3	375.5	375.0	374.7	374.3	374.0	373.7
40°	362.5	361.7	360.8	360.2	359.8	359.4	359.0	358.6
42.5°	347.5	346.6	345.8	345.2	344.8	344.4	344.0	343.5
45°	325.0	323.8	322.4	321.6	321.0	320.5	320.0	319.5
47.5°	301.3	300.1	298.8	298.0	297.5	297.1	296.6	296.2
50°	285.7	284.5	283.4	282.5	281.9	281.2	280.6	279.9
52.5°	269.8	268.8	267.8	267.0	266.4	265.8	265.2	264.6
55°	245.7	244.5	243.4	242.6	242.1	241.5	241.0	240.4
57.5°	222.0	220.9	219.8	219.0	218.4	217.8	217.2	216.6
60°	205.2	204.2	203.3	202.6	202.0	201.5	201.0	200.5
62.5°	188.9	188.0	187.1	186.4	186.1	185.7	185.4	185.0
65°	164.9	164.1	163.2	162.7	162.4	162.0	161.7	161.4
67.5°	141.0	140.3	139.6	139.0	138.6	138.0	137.6	137.2
70°	125.6	124.8	124.1	123.5	123.0	122.5	121.9	121.4
72.5°	110.0	109.3	108.7	108.2	108.0	107.7	107.3	107.0
75°	87.5	86.8	86.3	85.9	85.6	85.3	85.0	84.7
77.5°	66.3	66.0	65.6	65.5	65.5	65.5	65.5	65.5
80°	52.9	52.8	52.7	52.7	52.7	52.7	52.7	52.7
82.5°	40.8	40.6	40.4	40.2	40.2	40.1	40.0	39.9
85°	23.1	22.9	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	13.3	13.4	13.5	13.6	13.7	13.7	13.8	13.9
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.2	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	76.3	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	118.8	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	149.6	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.0	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.2	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	333.5	334.4	335.3	335.5	335.0	334.6	334.2	333.7



TEST NUMBER: P331899-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	371.7	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.8	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	567.3	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	626.2	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	684.4	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	723.0	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	760.5	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	816.8	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	871.7	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.8	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.7	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.5	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.1	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1132.9	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1166.2	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1186.7	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1206.1	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1230.5	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1269.7	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1278.9	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1283.0	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)