

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331882-840

Luminaire Tested: **S123DIP-S340D585U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331882-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D585U840-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3566.9 lumens  
Efficiency: N/A  
Efficacy: 139.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	68	79	73	67	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	16	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5890	5890	5890
5°	5919	5837	5877
10°	5879	5786	5822
15°	5810	5721	5731
20°	5730	5628	5632
25°	5621	5516	5505
30°	5504	5392	5351
35°	5380	5261	5194
40°	5251	5117	5039
45°	5107	4985	4864
50°	4963	4823	4687
55°	4778	4654	4511
60°	4590	4456	4316
65°	4422	4241	4111
70°	4176	3997	3821
75°	3818	3681	3523
80°	3440	3298	3267
85°	3013	2902	2791



TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.5	1.4
10°-20°	145.6	4.1
20°-30°	215.0	6.0
30°-40°	251.2	7.0
40°-50°	252.5	7.1
50°-60°	221.8	6.2
60°-70°	165.2	4.6
70°-80°	94.1	2.6
80°-90°	29.2	0.8
90°-100°	158.3	4.4
100°-110°	448.4	12.6
110°-120°	441.1	12.4
120°-130°	351.8	9.9
130°-140°	277.4	7.8
140°-150°	207.0	5.8
150°-160°	144.3	4.0
160°-170°	84.8	2.4
170°-180°	27.6	0.8
0°-30°	412.1	11.6
0°-40°	663.3	18.6
0°-60°	1137.6	31.9
0°-90°	1426.2	40.0
90°-120°	1047.8	29.4
90°-150°	1884.1	52.8
90°-180°	2141.0	60.0
0°-180°	3566.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	548	545	540	545	544	52
15°	521	519	513	517	514	147
25°	473	470	464	465	464	218
35°	409	406	400	398	395	256
45°	336	333	328	322	320	259
55°	255	254	248	243	240	228
65°	174	171	166	163	161	171
75°	92	90	88	86	85	98
85°	24	24	24	23	23	27
90°	1	7	14	16	17	3
95°	20	64	342	100	67	21
105°	67	99	463	810	733	71
115°	118	147	354	777	891	117
125°	164	194	331	599	703	146
135°	192	230	326	493	570	149
145°	219	251	322	405	445	138
155°	249	269	312	354	369	115
165°	272	280	298	316	322	77
175°	284	284	286	290	290	27
180°	285	285	285	285	285	



TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	549.2	548.8	548.5	548.2	547.8	547.1	546.2	545.3	544.4	543.5	544.3
5°	547.8	547.1	546.6	546.1	545.6	544.8	543.6	542.5	541.3	540.2	541.2
7.5°	542.4	541.8	541.3	540.8	540.3	539.4	538.3	537.0	535.8	534.6	535.5
10°	537.9	537.3	536.7	536.2	535.7	534.8	533.4	532.1	530.7	529.4	530.3
12.5°	531.8	531.4	530.9	530.5	530.1	529.2	528.0	526.6	525.3	524.1	524.8
15°	521.4	521.0	520.5	520.1	519.7	518.8	517.5	516.0	514.7	513.4	514.2
17.5°	509.2	508.7	508.2	507.6	507.1	506.1	504.7	503.4	502.0	500.7	501.2
20°	500.2	499.6	499.0	498.3	497.7	496.7	495.3	493.9	492.6	491.3	491.7
22.5°	490.0	489.4	488.8	488.2	487.6	486.6	485.1	483.8	482.4	481.1	481.4
25°	473.3	472.7	472.1	471.5	470.9	469.9	468.5	467.2	465.7	464.4	464.5
27.5°	455.6	454.9	454.3	453.7	453.1	452.1	450.7	449.2	447.8	446.3	446.4
30°	442.8	442.2	441.7	441.2	440.7	439.7	438.3	436.8	435.4	433.8	433.8
32.5°	430.0	429.3	428.6	427.9	427.3	426.3	425.2	424.0	422.9	421.8	421.2
35°	409.4	408.8	408.1	407.5	406.9	405.9	404.6	403.1	401.8	400.4	399.8
37.5°	388.3	387.5	386.7	385.9	385.2	384.1	382.6	381.2	379.9	378.5	377.8
40°	373.7	372.9	372.3	371.7	371.1	370.0	368.6	367.1	365.7	364.2	363.3
42.5°	358.9	358.2	357.5	356.8	356.1	355.0	353.6	352.0	350.6	349.1	348.3
45°	335.5	335.1	334.7	334.3	333.9	333.0	331.5	330.2	328.8	327.5	326.3
47.5°	312.3	311.6	311.0	310.4	309.8	308.9	307.6	306.3	305.1	303.8	302.6
50°	296.4	295.9	295.4	294.9	294.4	293.4	292.1	290.7	289.3	288.0	286.8
52.5°	279.8	279.5	279.1	278.8	278.4	277.5	276.1	274.7	273.3	271.8	270.8
55°	254.6	254.5	254.4	254.3	254.2	253.4	252.1	250.6	249.3	248.0	246.8
57.5°	230.5	230.1	229.7	229.4	229.0	228.3	227.2	226.1	225.1	224.0	223.0
60°	213.2	213.1	213.0	212.9	212.8	212.1	210.8	209.5	208.3	207.0	206.1
62.5°	197.7	197.4	197.2	196.9	196.6	195.9	194.6	193.4	192.1	190.9	190.0
65°	173.6	173.1	172.6	172.1	171.6	170.8	169.8	168.6	167.6	166.5	165.7
67.5°	148.1	147.6	147.2	146.7	146.3	145.6	144.9	144.1	143.3	142.5	141.8
70°	132.7	132.1	131.5	130.8	130.2	129.6	129.0	128.3	127.6	127.0	126.3
72.5°	116.5	116.0	115.6	115.1	114.6	114.1	113.4	112.7	112.0	111.3	110.6
75°	91.8	91.3	90.9	90.5	90.1	89.7	89.4	89.1	88.8	88.5	88.0
77.5°	69.8	69.6	69.4	69.2	68.9	68.6	68.3	67.9	67.5	67.1	66.8
80°	55.5	55.2	54.9	54.6	54.2	54.0	53.8	53.6	53.4	53.2	53.0
82.5°	41.6	41.5	41.5	41.4	41.3	41.3	41.2	41.2	41.2	41.1	40.9
85°	24.4	24.2	24.0	23.8	23.6	23.5	23.5	23.5	23.5	23.5	23.3
87.5°	10.0	10.0	10.0	10.1	10.1	10.1	10.4	10.6	10.9	11.2	11.0
90°	1.1	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8
92.5°	7.2	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9
95°	19.6	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0
97.5°	33.4	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3
100°	42.6	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9
102.5°	52.3	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6
105°	66.9	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4
107.5°	82.2	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9
110°	93.3	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2



TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.4	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5
115°	118.1	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9
117.5°	132.7	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4
120°	142.9	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5
122.5°	151.6	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9
125°	164.2	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2
127.5°	173.7	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3
130°	179.8	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9
132.5°	184.3	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8
135°	192.4	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0
137.5°	200.0	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3
140°	205.1	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0
142.5°	210.6	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4
145°	219.4	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4
147.5°	228.4	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6
150°	234.4	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3
152.5°	240.4	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7
155°	249.4	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2
157.5°	256.5	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9
160°	262.1	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8
162.5°	266.2	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6
165°	272.5	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0
167.5°	277.2	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6
170°	279.9	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4
172.5°	281.8	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1
175°	284.0	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4
177.5°	285.0	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	545.1	546.0	546.8	547.2	547.1	547.0	546.9	546.8
5°	542.3	543.3	544.4	544.8	544.6	544.4	544.1	543.9
7.5°	536.5	537.5	538.4	538.8	538.7	538.6	538.5	538.3
10°	531.3	532.2	533.1	533.5	533.3	533.1	532.9	532.7
12.5°	525.4	526.1	526.8	527.1	527.0	526.8	526.7	526.6
15°	515.0	515.8	516.7	516.8	516.1	515.5	514.9	514.3
17.5°	501.8	502.4	503.0	503.2	502.9	502.7	502.5	502.3
20°	492.1	492.5	492.9	493.0	492.6	492.3	492.0	491.7
22.5°	481.7	482.1	482.4	482.4	482.0	481.6	481.2	480.8
25°	464.6	464.7	464.8	464.7	464.4	464.1	463.8	463.5
27.5°	446.5	446.6	446.6	446.5	446.1	445.7	445.2	444.8
30°	433.8	433.8	433.8	433.4	432.7	432.0	431.3	430.5
32.5°	420.6	420.0	419.5	419.0	418.6	418.2	417.8	417.4
35°	399.2	398.6	397.9	397.4	396.9	396.3	395.8	395.3
37.5°	377.0	376.3	375.5	375.0	374.7	374.3	374.0	373.7
40°	362.5	361.7	360.8	360.2	359.8	359.4	359.0	358.6
42.5°	347.5	346.6	345.8	345.2	344.8	344.4	344.0	343.5
45°	325.0	323.8	322.4	321.6	321.0	320.5	320.0	319.5
47.5°	301.3	300.1	298.8	298.0	297.5	297.1	296.6	296.2
50°	285.7	284.5	283.4	282.5	281.9	281.2	280.6	279.9
52.5°	269.8	268.8	267.8	267.0	266.4	265.8	265.2	264.6
55°	245.7	244.5	243.4	242.6	242.1	241.5	241.0	240.4
57.5°	222.0	220.9	219.8	219.0	218.4	217.8	217.2	216.6
60°	205.2	204.2	203.3	202.6	202.0	201.5	201.0	200.5
62.5°	188.9	188.0	187.1	186.4	186.1	185.7	185.4	185.0
65°	164.9	164.1	163.2	162.7	162.4	162.0	161.7	161.4
67.5°	141.0	140.3	139.6	139.0	138.6	138.0	137.6	137.2
70°	125.6	124.8	124.1	123.5	123.0	122.5	121.9	121.4
72.5°	110.0	109.3	108.7	108.2	108.0	107.7	107.3	107.0
75°	87.5	86.8	86.3	85.9	85.6	85.3	85.0	84.7
77.5°	66.3	66.0	65.6	65.5	65.5	65.5	65.5	65.5
80°	52.9	52.8	52.7	52.7	52.7	52.7	52.7	52.7
82.5°	40.8	40.6	40.4	40.2	40.2	40.1	40.0	39.9
85°	23.1	22.9	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	11.0	11.0	11.0	11.2	11.1	11.2	11.4	11.2
90°	14.4	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	48.5	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	207.3	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	516.9	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	679.1	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	733.1	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	748.8	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	703.4	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	660.0	766.1	838.7	879.0	895.1	899.7	898.6	897.4





TEST NUMBER: P331882-840

CATALOG NUMBER: S123DIP-S340D585U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	617.2	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	560.5	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	519.3	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	497.7	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	480.6	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	457.9	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	438.1	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	425.7	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	414.1	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	398.6	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	384.5	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	376.2	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	368.3	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	358.8	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	351.1	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	345.6	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	340.5	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	333.0	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	324.9	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	320.2	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	314.8	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	307.6	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	301.3	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	297.2	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	293.6	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	288.6	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.5	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)