

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831884

Luminaire Tested: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831884  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U850-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7995.6 lumens  
Efficiency: N/A  
Efficacy: 143.5 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60				
1	101	97	93	90	94	91	88	85	79	77	75	69	67	66	59	58	57	52				
2	93	86	80	75	87	81	76	71	71	67	64	62	59	56	53	51	49	45				
3	85	76	70	64	80	72	66	61	63	59	55	55	52	49	48	46	43	40				
4	79	68	61	55	73	65	58	53	57	52	48	50	46	43	44	41	38	35				
5	73	62	54	48	68	58	51	46	52	46	42	46	41	38	40	37	34	31				
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31	28				
7	63	51	43	38	59	48	42	37	43	38	34	39	34	31	34	31	28	26				
8	59	47	39	34	55	44	38	33	40	34	31	36	31	28	32	28	26	23				
9	55	43	36	31	52	41	35	30	37	32	28	33	29	26	30	26	24	22				
10	52	40	33	28	49	38	32	27	34	29	26	31	27	24	28	24	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	38736	38736	38736	38736	38736
5°	45995	44529	38980	31511	29255
10°	41673	45228	38786	25247	21659
15°	28691	38780	38376	20635	17133
20°	19961	29857	37606	17400	15060
25°	15210	22755	36485	15465	13879
30°	13241	18192	35082	14359	12855
35°	12156	15347	33097	13427	11924
40°	11092	13704	30498	12513	11071
45°	10018	12533	27694	11645	10219
50°	9093	11563	24387	10798	9167
55°	8223	10620	21210	9969	7863
60°	7369	9655	18424	9052	7434
65°	6803	8568	15860	8135	7027
70°	5526	7405	13838	7361	5712
75°	4849	5889	11720	6105	5032
80°	4389	4984	9602	5120	4754
85°	4014	4372	7287	4644	4372

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 29221 cd/sqm



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	328.0	4.1
10°-20°	759.0	9.5
20°-30°	870.9	10.9
30°-40°	858.4	10.7
40°-50°	757.0	9.5
50°-60°	582.4	7.3
60°-70°	382.9	4.8
70°-80°	185.9	2.3
80°-90°	49.2	0.6
90°-100°	232.4	2.9
100°-110°	680.5	8.5
110°-120°	664.5	8.3
120°-130°	529.2	6.6
130°-140°	417.5	5.2
140°-150°	311.5	3.9
150°-160°	217.2	2.7
160°-170°	127.6	1.6
170°-180°	41.5	0.5
0°-30°	1957.9	24.5
0°-40°	2816.3	35.2
0°-60°	4155.7	52.0
0°-90°	4773.7	59.7
90°-120°	1577.4	19.7
90°-150°	2835.6	35.5
90°-180°	3222.0	40.3
0°-180°	7995.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3599	3599	3599	3599	3599	
5°	4257	4121	3608	2916	2708	389
15°	2575	3480	3444	1852	1538	727
25°	1281	1916	3072	1302	1169	605
35°	925	1168	2519	1022	907	577
45°	658	823	1819	765	671	511
55°	438	566	1130	531	419	393
65°	267	336	623	319	276	262
75°	117	142	282	147	121	125
85°	32	35	59	38	35	35
90°	25	22	2	22	25	15
95°	101	514	30	514	101	163
105°	1103	697	101	697	1103	1100
115°	1341	533	178	533	1341	1308
125°	1058	498	247	498	1058	957
135°	858	491	290	491	858	665
145°	670	485	330	485	670	426
155°	556	469	375	469	556	259
165°	485	449	410	449	485	138
175°	436	431	427	431	436	42
180°	428	428	428	428	428	



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7
2.5°	3988.3	3975.7	3963.2	3959.5	3955.8	3944.0	3932.2	3905.6	3879.1	3851.8	3824.5
5°	4256.8	4258.3	4259.7	4256.1	4252.4	4236.9	4221.4	4188.9	4156.5	4121.1	4085.6
7.5°	4174.2	4197.8	4221.4	4225.8	4230.2	4242.0	4253.8	4246.5	4239.1	4225.8	4212.5
10°	3812.7	3811.2	3809.7	3836.3	3862.8	3941.8	4020.7	4061.3	4101.9	4138.0	4174.2
12.5°	3222.5	3224.7	3226.9	3314.0	3401.0	3475.5	3550.0	3653.3	3756.6	3868.0	3979.4
15°	2574.7	2610.9	2647.0	2724.5	2802.0	2914.1	3026.2	3164.9	3303.6	3480.0	3656.3
17.5°	2114.4	2129.9	2145.4	2219.9	2294.4	2400.6	2506.9	2664.0	2821.1	3048.4	3275.6
20°	1742.6	1756.6	1770.6	1824.4	1878.3	1980.1	2081.9	2231.7	2381.4	2606.5	2831.5
22.5°	1454.8	1482.1	1509.4	1545.6	1581.7	1655.5	1729.3	1882.0	2034.7	2239.8	2444.9
25°	1280.7	1293.3	1305.8	1336.8	1367.8	1438.6	1509.4	1610.5	1711.6	1915.9	2120.3
27.5°	1162.7	1166.4	1170.1	1192.9	1215.8	1261.5	1307.3	1401.0	1494.7	1662.9	1831.1
30°	1065.3	1071.9	1078.6	1096.3	1114.0	1147.2	1180.4	1246.8	1313.2	1463.7	1614.2
32.5°	990.1	993.7	997.4	1012.2	1026.9	1051.3	1075.6	1128.0	1180.4	1295.5	1410.6
35°	925.1	925.9	926.6	937.7	948.7	972.4	996.0	1039.5	1083.0	1167.9	1252.7
37.5°	851.4	856.5	861.7	869.8	877.9	898.6	919.2	954.6	990.1	1060.1	1130.2
40°	789.4	793.8	798.2	807.8	817.4	833.7	849.9	882.3	914.8	975.3	1035.8
42.5°	727.4	730.4	733.3	742.9	752.5	772.4	792.3	818.2	844.0	894.1	944.3
45°	658.1	665.4	672.8	683.2	693.5	710.4	727.4	754.0	780.5	823.3	866.1
47.5°	600.5	604.2	607.9	616.8	625.6	646.3	666.9	690.5	714.1	754.0	793.8
50°	543.0	544.5	545.9	554.0	562.2	580.6	599.1	626.3	653.6	690.5	727.4
52.5°	488.4	492.1	495.8	503.9	512.0	524.5	537.1	565.1	593.1	629.3	665.4
55°	438.2	440.4	442.6	448.5	454.5	469.2	484.0	508.3	532.7	565.9	599.1
57.5°	391.0	394.0	396.9	401.3	405.8	419.0	432.3	453.7	475.1	508.3	541.5
60°	342.3	346.0	349.7	354.9	360.0	370.3	380.7	399.9	419.0	448.5	478.1
62.5°	306.9	307.6	308.4	312.8	317.2	324.6	332.0	347.5	363.0	392.5	422.0
65°	267.1	269.3	271.5	273.7	275.9	281.8	287.7	301.0	314.3	336.4	358.5
67.5°	225.8	228.0	230.2	233.9	237.6	242.7	247.9	256.7	265.6	286.2	306.9
70°	175.6	175.6	175.6	181.5	187.4	196.2	205.1	211.7	218.4	235.3	252.3
72.5°	143.1	143.9	144.6	145.3	146.1	151.2	156.4	167.5	178.5	188.9	199.2
75°	116.6	117.3	118.0	118.8	119.5	121.0	122.5	126.2	129.8	141.6	153.5
77.5°	93.0	93.7	94.4	95.2	95.9	97.4	98.9	100.3	101.8	106.2	110.7
80°	70.8	71.6	72.3	73.0	73.8	74.5	75.3	76.7	78.2	80.4	82.6
82.5°	51.6	51.6	51.6	51.6	51.6	53.1	54.6	54.6	54.6	56.1	57.5
85°	32.5	32.5	32.5	33.2	33.9	33.9	33.9	34.7	35.4	35.4	35.4
87.5°	14.8	14.0	13.3	14.0	14.8	14.8	14.8	15.5	16.2	16.2	16.2
90°	25.1	26.0	25.1	24.3	25.1	23.4	22.5	21.7	20.8	21.7	19.1
92.5°	46.0	47.7	46.8	50.3	52.0	58.1	66.8	85.8	120.5	161.3	178.6
95°	100.6	104.0	110.1	117.9	134.4	165.6	211.6	312.1	417.0	514.2	457.8
97.5°	206.4	215.9	236.7	269.6	327.7	426.6	541.0	717.0	817.6	790.7	590.5
100°	543.6	542.8	576.6	639.9	727.4	850.6	952.0	1022.2	991.9	821.1	554.9
102.5°	861.0	886.1	913.0	959.8	1023.1	1089.9	1138.4	1123.7	1000.6	764.7	502.9
105°	1102.9	1107.2	1135.0	1167.9	1207.8	1230.3	1213.9	1127.1	945.9	697.1	462.1
107.5°	1260.7	1270.2	1281.5	1297.1	1302.3	1278.9	1211.3	1075.1	867.9	637.3	432.7
110°	1350.8	1352.6	1354.3	1347.4	1323.1	1262.4	1153.2	993.6	795.1	587.9	417.0



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1369.1	1368.2	1359.5	1334.4	1285.0	1202.6	1076.9	913.0	731.8	554.9	408.4
115°	1341.3	1337.0	1319.6	1281.5	1216.5	1121.9	994.5	843.6	683.2	533.2	407.5
117.5°	1280.6	1274.5	1248.5	1206.1	1138.4	1040.4	923.4	789.9	651.1	518.5	408.4
120°	1200.8	1195.6	1174.8	1126.3	1057.8	970.2	866.2	749.1	626.9	509.0	411.8
122.5°	1126.3	1119.3	1095.9	1053.5	994.5	914.7	820.2	717.0	606.9	502.9	417.9
125°	1057.8	1051.7	1030.0	991.9	936.4	867.0	783.8	689.3	590.5	497.7	424.0
127.5°	998.8	993.6	973.7	940.7	890.4	826.3	750.0	664.2	574.8	495.1	430.9
130°	950.3	943.3	925.1	893.9	848.0	789.0	718.8	640.7	562.7	492.5	437.9
132.5°	902.6	898.3	882.6	851.4	808.9	753.5	689.3	619.1	551.4	491.6	443.1
135°	857.5	851.4	835.8	809.8	767.3	717.9	661.6	600.0	541.9	490.7	448.3
137.5°	809.8	804.6	791.6	764.7	728.3	684.1	633.8	581.8	533.2	489.0	451.7
140°	759.5	760.4	746.5	722.2	689.3	652.0	610.4	566.2	525.4	488.1	455.2
142.5°	712.7	713.6	701.4	680.6	653.7	622.5	587.9	551.4	518.5	486.4	457.8
145°	670.2	668.5	661.6	643.3	621.7	596.5	568.8	540.2	512.4	484.7	458.7
147.5°	633.8	632.9	626.0	613.0	595.7	577.4	554.0	530.6	506.4	482.1	458.7
150°	602.6	602.6	597.4	587.9	574.8	558.4	540.2	520.2	500.3	478.6	458.7
152.5°	576.6	576.6	574.0	565.3	555.8	542.8	527.2	510.7	493.3	474.3	456.1
155°	555.8	554.9	553.2	546.2	538.4	528.0	515.0	501.1	486.4	469.1	454.3
157.5°	535.8	535.8	534.1	528.9	522.0	513.3	502.9	490.7	478.6	464.7	451.7
160°	516.8	517.6	517.6	512.4	506.4	500.3	491.6	482.1	470.8	459.5	450.0
162.5°	499.4	500.3	500.3	495.9	492.5	487.3	479.5	471.7	463.0	454.3	446.5
165°	484.7	484.7	485.5	482.1	478.6	474.3	468.2	463.0	456.1	449.1	443.1
167.5°	469.9	469.9	470.8	468.2	466.5	463.0	459.5	455.2	449.1	443.9	439.6
170°	456.9	456.9	457.8	456.1	455.2	453.5	450.0	447.4	443.1	438.7	436.1
172.5°	444.8	445.7	447.4	445.7	445.7	444.8	442.2	440.5	437.0	434.4	433.5
175°	436.1	437.0	437.9	437.0	437.0	437.0	435.3	434.4	432.7	430.9	430.9
177.5°	430.1	430.1	431.8	430.9	431.8	431.8	430.9	430.1	429.2	428.3	429.2
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7
2.5°	3820.8	3817.1	3781.7	3746.3	3711.6	3676.9	3651.1	3625.3	3581.8	3538.2	3510.9
5°	4057.6	4029.6	3973.5	3917.4	3833.3	3749.2	3678.4	3607.6	3517.6	3427.6	3352.3
7.5°	4189.7	4166.8	4098.9	4031.0	3919.6	3808.2	3697.6	3586.9	3454.1	3321.3	3207.7
10°	4193.4	4212.5	4156.5	4100.4	3975.0	3849.6	3699.1	3548.6	3370.0	3191.5	3044.7
12.5°	4062.0	4144.7	4132.9	4121.1	3993.4	3865.8	3682.8	3499.9	3280.8	3061.6	2877.9
15°	3816.4	3976.5	4023.7	4070.9	3965.4	3859.9	3651.8	3443.8	3186.3	2928.9	2717.9
17.5°	3499.9	3724.1	3848.8	3973.5	3896.8	3820.1	3592.1	3364.1	3074.2	2784.3	2554.8
20°	3125.1	3418.7	3614.2	3809.7	3781.7	3753.7	3518.3	3283.0	2970.2	2657.4	2408.7
22.5°	2754.7	3064.6	3334.6	3604.6	3633.4	3662.2	3424.6	3187.1	2844.8	2502.4	2249.4
25°	2435.3	2750.3	3072.0	3393.6	3458.6	3523.5	3297.7	3072.0	2717.1	2362.3	2110.7
27.5°	2130.6	2430.1	2784.3	3138.4	3256.4	3374.5	3167.9	2961.3	2591.7	2222.1	1971.3
30°	1882.0	2149.8	2511.3	2872.8	3037.3	3201.8	3012.2	2822.6	2456.0	2089.3	1843.6
32.5°	1650.3	1890.1	2253.1	2616.0	2807.1	2998.2	2834.4	2670.6	2318.0	1965.4	1722.6
35°	1467.4	1682.1	2020.7	2359.3	2573.3	2787.2	2652.9	2518.7	2174.1	1829.6	1600.2
37.5°	1310.2	1490.2	1808.2	2126.2	2353.4	2580.6	2468.5	2356.4	2032.5	1708.6	1491.7
40°	1180.4	1325.0	1620.8	1916.7	2139.5	2362.3	2266.4	2170.5	1880.5	1590.6	1387.7
42.5°	1069.0	1193.7	1459.3	1724.9	1929.2	2133.6	2070.1	2006.7	1744.0	1481.4	1293.3
45°	970.9	1075.6	1309.5	1543.4	1731.5	1919.6	1869.4	1819.3	1592.8	1366.3	1193.7
47.5°	883.8	973.8	1182.6	1391.4	1560.3	1729.3	1682.8	1636.3	1448.9	1261.5	1104.4
50°	804.1	880.9	1055.0	1229.1	1381.1	1533.0	1494.7	1456.3	1301.4	1146.5	1010.7
52.5°	728.9	792.3	948.7	1105.1	1227.6	1350.1	1320.6	1291.1	1171.5	1052.0	928.8
55°	657.3	715.6	847.7	979.7	1084.5	1189.2	1159.7	1130.2	1037.3	944.3	835.9
57.5°	592.4	643.3	750.3	857.3	940.6	1024.0	1010.0	996.0	918.5	841.0	751.8
60°	523.8	569.5	661.8	754.0	821.1	888.2	872.0	855.8	800.5	745.1	668.4
62.5°	462.6	503.1	576.9	650.7	705.3	759.9	748.1	736.3	694.2	652.2	588.7
65°	398.4	438.2	498.0	557.7	600.5	643.3	633.0	622.7	590.9	559.2	508.3
67.5°	340.1	373.3	424.9	476.6	505.4	534.1	528.2	522.3	498.0	473.6	433.8
70°	281.1	309.9	352.6	395.4	415.4	435.3	437.5	439.7	417.6	395.4	365.9
72.5°	222.1	244.9	284.8	324.6	340.1	355.6	354.9	354.1	340.8	327.6	301.0
75°	170.4	187.4	218.4	249.4	262.6	275.9	278.9	281.8	269.3	256.7	242.0
77.5°	122.5	134.3	157.9	181.5	196.2	211.0	212.5	213.9	208.0	202.1	188.1
80°	86.3	90.0	104.8	119.5	135.0	150.5	152.7	154.9	149.0	143.1	134.3
82.5°	59.8	62.0	67.1	72.3	84.8	97.4	100.3	103.3	100.3	97.4	87.8
85°	36.1	36.9	39.1	41.3	47.2	53.1	56.1	59.0	57.5	56.1	50.9
87.5°	16.2	16.2	17.0	17.7	19.2	20.7	24.3	28.0	25.8	23.6	21.4
90°	16.5	13.9	11.3	9.5	7.8	5.2	3.5	1.7	3.5	5.2	7.8
92.5°	133.5	87.6	59.8	44.2	35.5	27.7	19.1	13.0	19.1	27.7	35.5
95°	315.6	186.4	112.7	78.9	56.4	41.6	32.1	29.5	32.1	41.6	56.4
97.5°	351.2	201.2	128.3	91.0	68.5	55.5	47.7	46.8	47.7	55.5	68.5
100°	326.9	198.6	137.9	104.0	83.2	71.1	65.0	64.2	65.0	71.1	83.2
102.5°	306.1	202.0	149.1	118.8	100.6	89.3	84.1	82.4	84.1	89.3	100.6
105°	298.3	209.0	162.1	135.3	118.8	108.4	103.2	100.6	103.2	108.4	118.8
107.5°	296.5	220.2	178.6	153.5	137.9	127.5	122.3	119.7	122.3	127.5	137.9
110°	300.9	235.0	196.0	171.7	156.9	147.4	143.1	140.5	143.1	147.4	156.9





TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	309.5	249.7	214.2	190.7	176.0	166.5	162.1	159.5	162.1	166.5	176.0
115°	319.1	266.2	233.2	209.8	195.1	186.4	181.2	177.7	181.2	186.4	195.1
117.5°	331.2	283.5	250.6	228.9	212.4	204.6	200.3	196.0	200.3	204.6	212.4
120°	345.1	300.0	268.8	247.1	230.6	222.0	217.6	215.0	217.6	222.0	230.6
122.5°	358.1	317.3	287.0	263.6	248.0	238.4	234.1	231.5	234.1	238.4	248.0
125°	372.0	333.8	303.5	280.1	263.6	254.0	248.8	247.1	248.8	254.0	263.6
127.5°	383.2	348.5	319.1	295.7	277.5	267.9	261.8	259.2	261.8	267.9	277.5
130°	394.5	361.6	332.9	309.5	291.3	280.9	273.1	270.5	273.1	280.9	291.3
132.5°	404.9	372.8	345.1	322.5	304.3	291.3	282.7	279.2	282.7	291.3	304.3
135°	413.6	384.1	357.2	333.8	315.6	302.6	293.1	289.6	293.1	302.6	315.6
137.5°	420.5	391.9	365.9	344.2	326.0	312.1	302.6	299.1	302.6	312.1	326.0
140°	425.7	399.7	374.6	352.9	335.5	321.7	313.0	308.7	313.0	321.7	335.5
142.5°	430.9	405.8	381.5	361.6	344.2	332.1	322.5	319.1	322.5	332.1	344.2
145°	434.4	411.0	388.4	368.5	353.8	340.7	332.9	330.3	332.9	340.7	353.8
147.5°	437.0	415.3	394.5	377.2	362.4	351.2	343.3	341.6	343.3	351.2	362.4
150°	437.9	419.6	399.7	384.1	372.0	360.7	353.8	352.9	353.8	360.7	372.0
152.5°	439.6	422.2	405.8	391.0	380.6	371.1	364.2	364.2	364.2	371.1	380.6
155°	439.6	425.7	411.0	398.8	389.3	380.6	375.4	375.4	375.4	380.6	389.3
157.5°	440.5	427.4	415.3	405.8	397.1	389.3	385.0	384.1	385.0	389.3	397.1
160°	440.5	430.1	419.6	411.0	404.9	398.0	394.5	394.5	394.5	398.0	404.9
162.5°	439.6	430.9	422.2	415.3	410.1	404.9	402.3	402.3	402.3	404.9	410.1
165°	437.9	431.8	424.8	418.8	415.3	411.0	409.2	410.1	409.2	411.0	415.3
167.5°	437.0	431.8	426.6	422.2	419.6	416.2	415.3	416.2	415.3	416.2	419.6
170°	434.4	430.9	426.6	424.8	423.1	420.5	419.6	421.4	419.6	420.5	423.1
172.5°	433.5	430.9	427.4	426.6	425.7	424.0	424.0	424.8	424.0	424.0	425.7
175°	431.8	430.1	428.3	427.4	427.4	425.7	426.6	427.4	426.6	425.7	427.4
177.5°	430.9	429.2	428.3	428.3	428.3	427.4	428.3	429.2	428.3	427.4	428.3
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7
2.5°	3483.6	3441.6	3399.5	3369.3	3339.0	3301.4	3263.8	3262.3	3260.8	3232.8	3204.8
5°	3277.1	3204.0	3131.0	3059.4	2987.9	2916.3	2844.8	2828.5	2812.3	2787.9	2763.6
7.5°	3094.1	2977.5	2861.0	2769.5	2678.0	2606.5	2534.9	2486.2	2437.5	2399.9	2362.3
10°	2897.9	2753.3	2608.7	2498.0	2387.3	2309.9	2232.4	2176.4	2120.3	2093.7	2067.2
12.5°	2694.3	2537.1	2380.0	2271.5	2163.1	2070.1	1977.2	1926.3	1875.4	1838.5	1801.6
15°	2506.9	2337.9	2169.0	2053.9	1938.8	1851.7	1764.7	1713.8	1662.9	1626.0	1589.1
17.5°	2325.4	2155.0	1984.5	1868.0	1751.4	1672.5	1593.5	1544.1	1494.7	1471.8	1448.9
20°	2160.1	1988.2	1816.3	1706.4	1596.5	1519.0	1441.6	1415.0	1388.4	1367.0	1345.6
22.5°	1996.3	1831.1	1665.8	1560.3	1454.8	1398.8	1342.7	1321.3	1299.9	1283.7	1267.4
25°	1859.1	1694.6	1530.1	1437.9	1345.6	1302.1	1258.6	1244.6	1230.6	1214.3	1198.1
27.5°	1720.4	1564.0	1407.6	1333.8	1260.1	1224.7	1189.2	1171.5	1153.8	1140.6	1127.3
30°	1598.0	1453.4	1308.8	1247.5	1186.3	1155.3	1124.3	1105.1	1086.0	1073.4	1060.9
32.5°	1479.9	1351.6	1223.2	1170.8	1118.4	1088.2	1057.9	1039.5	1021.0	1006.3	991.5
35°	1370.7	1259.3	1147.9	1100.0	1052.0	1021.8	991.5	973.1	954.6	939.9	925.1
37.5°	1274.8	1173.8	1072.7	1027.7	982.7	956.1	929.6	910.4	891.2	875.7	860.2
40°	1184.8	1095.6	1006.3	962.8	919.2	890.5	861.7	844.7	827.8	813.7	799.7
42.5°	1105.1	1023.3	941.4	898.6	855.8	828.5	801.2	781.3	761.4	753.2	745.1
45°	1021.0	948.7	876.4	835.1	793.8	765.0	736.3	719.3	702.3	695.0	687.6
47.5°	947.3	880.1	813.0	772.4	731.8	706.0	680.2	666.9	653.6	643.3	633.0
50°	875.0	810.0	745.1	706.0	666.9	644.8	622.7	606.4	590.2	582.8	575.4
52.5°	805.6	746.6	687.6	647.7	607.9	586.5	565.1	551.1	537.1	521.6	506.1
55°	727.4	675.8	624.1	588.7	553.3	531.2	509.0	492.8	476.6	460.4	444.1
57.5°	662.5	611.6	560.7	529.0	497.2	475.8	454.5	436.7	419.0	405.8	392.5
60°	591.7	547.4	503.1	472.2	441.2	420.5	399.9	382.9	365.9	359.3	352.6
62.5°	525.3	484.0	442.6	415.4	388.1	368.1	348.2	337.2	326.1	321.7	317.2
65°	457.4	422.0	386.6	361.5	336.4	319.4	302.5	297.3	292.1	288.5	284.8
67.5°	394.0	363.7	333.5	311.3	289.2	277.4	265.6	259.7	253.8	249.4	244.9
70°	336.4	309.9	283.3	264.1	244.9	233.9	222.8	217.6	212.5	204.4	196.2
72.5°	274.4	253.8	233.1	218.4	203.6	194.0	184.4	174.1	163.8	156.4	149.0
75°	227.2	206.6	185.9	171.9	157.9	146.8	135.7	132.1	128.4	126.2	123.9
77.5°	174.1	156.4	138.7	127.6	116.6	111.4	106.2	104.0	101.8	101.1	100.3
80°	125.4	110.7	95.9	90.0	84.1	82.6	81.2	79.7	78.2	77.5	76.7
82.5°	78.2	70.8	63.4	62.0	60.5	59.8	59.0	58.3	57.5	56.8	56.1
85°	45.7	42.8	39.8	39.1	38.4	37.6	36.9	36.9	36.9	36.9	36.9
87.5°	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	18.4	17.7
90°	9.5	11.3	13.9	16.5	19.1	21.7	20.8	21.7	22.5	23.4	25.1
92.5°	44.2	59.8	87.6	133.5	178.6	161.3	120.5	85.8	66.8	58.1	52.0
95°	78.9	112.7	186.4	315.6	457.8	514.2	417.0	312.1	211.6	165.6	134.4
97.5°	91.0	128.3	201.2	351.2	590.5	790.7	817.6	717.0	541.0	426.6	327.7
100°	104.0	137.9	198.6	326.9	554.9	821.1	991.9	1022.2	952.0	850.6	727.4
102.5°	118.8	149.1	202.0	306.1	502.9	764.7	1000.6	1123.7	1138.4	1089.9	1023.1
105°	135.3	162.1	209.0	298.3	462.1	697.1	945.9	1127.1	1213.9	1230.3	1207.8
107.5°	153.5	178.6	220.2	296.5	432.7	637.3	867.9	1075.1	1211.3	1278.9	1302.3
110°	171.7	196.0	235.0	300.9	417.0	587.9	795.1	993.6	1153.2	1262.4	1323.1



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	190.7	214.2	249.7	309.5	408.4	554.9	731.8	913.0	1076.9	1202.6	1285.0
115°	209.8	233.2	266.2	319.1	407.5	533.2	683.2	843.6	994.5	1121.9	1216.5
117.5°	228.9	250.6	283.5	331.2	408.4	518.5	651.1	789.9	923.4	1040.4	1138.4
120°	247.1	268.8	300.0	345.1	411.8	509.0	626.9	749.1	866.2	970.2	1057.8
122.5°	263.6	287.0	317.3	358.1	417.9	502.9	606.9	717.0	820.2	914.7	994.5
125°	280.1	303.5	333.8	372.0	424.0	497.7	590.5	689.3	783.8	867.0	936.4
127.5°	295.7	319.1	348.5	383.2	430.9	495.1	574.8	664.2	750.0	826.3	890.4
130°	309.5	332.9	361.6	394.5	437.9	492.5	562.7	640.7	718.8	789.0	848.0
132.5°	322.5	345.1	372.8	404.9	443.1	491.6	551.4	619.1	689.3	753.5	808.9
135°	333.8	357.2	384.1	413.6	448.3	490.7	541.9	600.0	661.6	717.9	767.3
137.5°	344.2	365.9	391.9	420.5	451.7	489.0	533.2	581.8	633.8	684.1	728.3
140°	352.9	374.6	399.7	425.7	455.2	488.1	525.4	566.2	610.4	652.0	689.3
142.5°	361.6	381.5	405.8	430.9	457.8	486.4	518.5	551.4	587.9	622.5	653.7
145°	368.5	388.4	411.0	434.4	458.7	484.7	512.4	540.2	568.8	596.5	621.7
147.5°	377.2	394.5	415.3	437.0	458.7	482.1	506.4	530.6	554.0	577.4	595.7
150°	384.1	399.7	419.6	437.9	458.7	478.6	500.3	520.2	540.2	558.4	574.8
152.5°	391.0	405.8	422.2	439.6	456.1	474.3	493.3	510.7	527.2	542.8	555.8
155°	398.8	411.0	425.7	439.6	454.3	469.1	486.4	501.1	515.0	528.0	538.4
157.5°	405.8	415.3	427.4	440.5	451.7	464.7	478.6	490.7	502.9	513.3	522.0
160°	411.0	419.6	430.1	440.5	450.0	459.5	470.8	482.1	491.6	500.3	506.4
162.5°	415.3	422.2	430.9	439.6	446.5	454.3	463.0	471.7	479.5	487.3	492.5
165°	418.8	424.8	431.8	437.9	443.1	449.1	456.1	463.0	468.2	474.3	478.6
167.5°	422.2	426.6	431.8	437.0	439.6	443.9	449.1	455.2	459.5	463.0	466.5
170°	424.8	426.6	430.9	434.4	436.1	438.7	443.1	447.4	450.0	453.5	455.2
172.5°	426.6	427.4	430.9	433.5	433.5	434.4	437.0	440.5	442.2	444.8	445.7
175°	427.4	428.3	430.1	431.8	430.9	430.9	432.7	434.4	435.3	437.0	437.0
177.5°	428.3	428.3	429.2	430.9	429.2	428.3	429.2	430.1	430.9	431.8	431.8
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3598.7	3598.7	3598.7	3598.7
2.5°	3197.4	3190.0	3187.1	3184.1
5°	2740.7	2717.9	2712.7	2707.5
7.5°	2352.7	2343.1	2311.4	2279.6
10°	2037.7	2008.1	1994.9	1981.6
12.5°	1774.3	1747.0	1742.6	1738.1
15°	1569.9	1550.7	1544.1	1537.5
17.5°	1435.7	1422.4	1414.3	1406.1
20°	1336.1	1326.5	1320.6	1314.7
22.5°	1260.1	1252.7	1248.3	1243.8
25°	1187.0	1176.0	1172.3	1168.6
27.5°	1117.7	1108.1	1104.4	1100.7
30°	1052.8	1044.6	1039.5	1034.3
32.5°	981.9	972.4	969.4	966.4
35°	919.2	913.3	910.4	907.4
37.5°	852.8	845.5	841.0	836.6
40°	796.0	792.3	790.1	787.9
42.5°	738.5	731.8	731.1	730.4
45°	680.9	674.3	672.8	671.3
47.5°	627.1	621.2	620.4	619.7
50°	567.3	559.2	553.3	547.4
52.5°	498.7	491.3	486.2	481.0
55°	436.0	427.9	423.5	419.0
57.5°	388.8	385.1	382.9	380.7
60°	350.4	348.2	346.7	345.3
62.5°	315.0	312.8	312.8	312.8
65°	282.6	280.3	278.1	275.9
67.5°	240.5	236.1	235.3	234.6
70°	189.6	183.0	182.2	181.5
72.5°	148.3	147.5	146.1	144.6
75°	122.5	121.0	121.0	121.0
77.5°	98.9	97.4	97.4	97.4
80°	76.0	75.3	76.0	76.7
82.5°	56.1	56.1	55.3	54.6
85°	36.1	35.4	35.4	35.4
87.5°	17.7	17.7	17.7	17.7
90°	24.3	25.1	26.0	25.1
92.5°	50.3	46.8	47.7	46.0
95°	117.9	110.1	104.0	100.6
97.5°	269.6	236.7	215.9	206.4
100°	639.9	576.6	542.8	543.6
102.5°	959.8	913.0	886.1	861.0
105°	1167.9	1135.0	1107.2	1102.9
107.5°	1297.1	1281.5	1270.2	1260.7
110°	1347.4	1354.3	1352.6	1350.8



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1334.4	1359.5	1368.2	1369.1
115°	1281.5	1319.6	1337.0	1341.3
117.5°	1206.1	1248.5	1274.5	1280.6
120°	1126.3	1174.8	1195.6	1200.8
122.5°	1053.5	1095.9	1119.3	1126.3
125°	991.9	1030.0	1051.7	1057.8
127.5°	940.7	973.7	993.6	998.8
130°	893.9	925.1	943.3	950.3
132.5°	851.4	882.6	898.3	902.6
135°	809.8	835.8	851.4	857.5
137.5°	764.7	791.6	804.6	809.8
140°	722.2	746.5	760.4	759.5
142.5°	680.6	701.4	713.6	712.7
145°	643.3	661.6	668.5	670.2
147.5°	613.0	626.0	632.9	633.8
150°	587.9	597.4	602.6	602.6
152.5°	565.3	574.0	576.6	576.6
155°	546.2	553.2	554.9	555.8
157.5°	528.9	534.1	535.8	535.8
160°	512.4	517.6	517.6	516.8
162.5°	495.9	500.3	500.3	499.4
165°	482.1	485.5	484.7	484.7
167.5°	468.2	470.8	469.9	469.9
170°	456.1	457.8	456.9	456.9
172.5°	445.7	447.4	445.7	444.8
175°	437.0	437.9	437.0	436.1
177.5°	430.9	431.8	430.1	430.1
180°	428.3	428.3	428.3	428.3



TEST NUMBER: P831884

CATALOG NUMBER: S123RDIP-S1000D805U850-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.32	15.21	15.20	16.10	17.23	18.98	19.87	19.86	20.76	21.89
	3H	15.54	16.34	16.44	17.24	18.40	20.49	21.28	21.38	22.18	23.34
	4H	15.93	16.68	16.84	17.59	18.75	20.98	21.73	21.89	22.64	23.80
	6H	16.21	16.90	17.13	17.82	19.00	21.29	21.98	22.21	22.90	24.08
	8H	16.30	16.96	17.23	17.89	19.07	21.37	22.03	22.30	22.96	24.14
	12H	16.36	16.98	17.29	17.90	19.11	21.41	22.03	22.34	22.96	24.16
4H	2H	15.05	15.80	15.96	16.71	17.87	18.98	19.73	19.90	20.64	21.81
	3H	16.42	17.04	17.35	17.98	19.16	20.65	21.27	21.57	22.21	23.39
	4H	16.88	17.45	17.82	18.38	19.59	21.26	21.82	22.19	22.76	23.96
	6H	17.25	17.74	18.20	18.70	19.90	21.70	22.18	22.65	23.14	24.35
	8H	17.38	17.83	18.33	18.78	20.00	21.83	22.28	22.78	23.24	24.46
	12H	17.46	17.86	18.42	18.83	20.06	21.89	22.30	22.86	23.27	24.50
8H	4H	17.20	17.65	18.15	18.60	19.82	21.23	21.68	22.18	22.63	23.85
	6H	17.66	18.04	18.64	19.03	20.25	21.73	22.10	22.70	23.09	24.31
	8H	17.86	18.19	18.84	19.17	20.41	21.91	22.24	22.90	23.23	24.46
	12H	18.00	18.29	18.99	19.27	20.55	22.03	22.32	23.02	23.30	24.58
12H	4H	17.21	17.62	18.18	18.59	19.82	21.18	21.59	22.15	22.56	23.78
	6H	17.72	18.05	18.71	19.04	20.27	21.70	22.03	22.68	23.01	24.25
	8H	17.94	18.23	18.93	19.21	20.50	21.90	22.19	22.88	23.16	24.45