

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331943-840

Luminaire Tested: **S123DIP-S560D1025U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331943-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6482.3 lumens
Efficiency: N/A
Efficacy: 145.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	20	16
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9684	9684	9684
5°	9729	9596	9662
10°	9664	9512	9571
15°	9551	9404	9423
20°	9419	9251	9260
25°	9242	9069	9049
30°	9047	8866	8797
35°	8843	8650	8539
40°	8630	8413	8283
45°	8397	8196	7995
50°	8162	7927	7708
55°	7854	7651	7418
60°	7543	7326	7093
65°	7272	6976	6757
70°	6864	6571	6279
75°	6276	6047	5793
80°	5659	5424	5368
85°	4965	4780	4594



TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	1.3
10°-20°	239.3	3.7
20°-30°	353.5	5.5
30°-40°	412.9	6.4
40°-50°	415.1	6.4
50°-60°	364.6	5.6
60°-70°	271.7	4.2
70°-80°	154.8	2.4
80°-90°	48.2	0.7
90°-100°	49.3	0.8
100°-110°	235.1	3.6
110°-120°	564.7	8.7
120°-130°	719.1	11.1
130°-140°	768.3	11.9
140°-150°	718.5	11.1
150°-160°	579.5	8.9
160°-170°	374.0	5.8
170°-180°	128.9	2.0
0°-30°	677.5	10.5
0°-40°	1090.4	16.8
0°-60°	1870.2	28.9
0°-90°	2344.9	36.2
90°-120°	849.1	13.1
90°-150°	3055.0	47.1
90°-180°	4137.0	63.8
0°-180°	6482.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	900	900	900	900	900	
5°	900	896	888	895	894	85
15°	857	854	844	850	846	242
25°	778	773	764	764	762	358
35°	673	668	658	654	650	421
45°	552	548	538	529	525	426
55°	418	417	408	399	395	375
65°	286	281	274	268	265	282
75°	151	148	145	142	139	161
85°	40	39	39	37	37	44
90°	1	11	24	28	30	5
95°	62	23	31	38	38	76
105°	300	306	221	52	44	318
115°	564	570	579	588	593	556
125°	794	802	806	808	810	709
135°	989	995	999	1002	999	761
145°	1141	1148	1150	1152	1152	714
155°	1257	1255	1256	1260	1255	579
165°	1326	1323	1322	1329	1322	374
175°	1357	1352	1353	1359	1352	129
180°	1357	1357	1357	1357	1357	



TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	902.7	902.2	901.7	901.1	900.6	899.5	898.0	896.5	895.0	893.5	894.8
5°	900.4	899.6	898.7	897.9	897.0	895.6	893.7	891.8	890.0	888.1	889.8
7.5°	891.6	890.8	889.9	889.1	888.2	886.8	884.8	882.8	880.9	879.0	880.5
10°	884.2	883.3	882.5	881.6	880.8	879.2	877.0	874.7	872.5	870.3	871.8
12.5°	874.3	873.5	872.8	872.1	871.4	870.0	867.9	865.8	863.7	861.6	862.7
15°	857.1	856.5	855.8	855.1	854.3	852.9	850.7	848.5	846.2	843.9	845.4
17.5°	837.2	836.3	835.4	834.5	833.5	832.0	829.8	827.6	825.4	823.0	824.0
20°	822.3	821.3	820.2	819.2	818.2	816.6	814.4	812.1	809.8	807.6	808.3
22.5°	805.6	804.6	803.5	802.5	801.4	799.8	797.6	795.4	793.1	790.9	791.4
25°	778.2	777.2	776.2	775.2	774.1	772.4	770.2	768.0	765.8	763.6	763.7
27.5°	749.0	748.0	747.0	746.0	745.0	743.3	740.8	738.5	736.1	733.7	733.8
30°	727.9	727.1	726.2	725.4	724.5	722.9	720.4	718.0	715.7	713.3	713.3
32.5°	706.9	705.8	704.6	703.5	702.4	700.8	699.0	697.1	695.3	693.5	692.5
35°	673.0	672.0	671.0	669.9	668.9	667.2	665.0	662.8	660.6	658.3	657.3
37.5°	638.3	637.0	635.7	634.4	633.1	631.4	629.0	626.8	624.5	622.3	621.1
40°	614.2	613.2	612.2	611.2	610.1	608.3	605.9	603.6	601.2	598.7	597.3
42.5°	590.1	589.0	587.7	586.5	585.4	583.6	581.2	578.9	576.4	574.0	572.6
45°	551.6	550.9	550.2	549.5	548.8	547.3	545.1	542.9	540.7	538.4	536.3
47.5°	513.3	512.3	511.4	510.4	509.4	507.8	505.7	503.6	501.5	499.4	497.4
50°	487.4	486.5	485.6	484.7	483.9	482.4	480.1	477.9	475.6	473.4	471.5
52.5°	460.1	459.5	459.0	458.4	457.8	456.3	453.9	451.6	449.2	446.9	445.2
55°	418.5	418.3	418.2	418.0	417.8	416.6	414.3	412.1	409.9	407.7	405.8
57.5°	378.9	378.3	377.7	377.2	376.6	375.4	373.5	371.8	370.0	368.2	366.6
60°	350.4	350.2	350.1	349.9	349.7	348.6	346.6	344.5	342.4	340.3	338.8
62.5°	325.1	324.6	324.2	323.8	323.3	322.0	319.9	317.9	315.8	313.8	312.3
65°	285.5	284.6	283.8	282.9	282.1	280.7	279.0	277.3	275.6	273.9	272.5
67.5°	243.5	242.8	242.0	241.3	240.4	239.4	238.1	236.8	235.5	234.3	233.1
70°	218.1	217.1	216.1	215.1	214.0	213.0	212.0	211.0	209.8	208.8	207.6
72.5°	191.6	190.8	190.1	189.2	188.5	187.5	186.4	185.2	184.0	182.9	181.8
75°	150.9	150.2	149.5	148.8	148.1	147.5	146.9	146.4	145.9	145.4	144.6
77.5°	114.8	114.4	114.0	113.7	113.3	112.8	112.2	111.6	110.9	110.3	109.8
80°	91.3	90.8	90.3	89.8	89.2	88.8	88.5	88.1	87.8	87.5	87.3
82.5°	68.4	68.3	68.2	68.1	68.0	67.9	67.9	67.8	67.7	67.7	67.3
85°	40.2	39.9	39.6	39.2	38.9	38.7	38.7	38.7	38.7	38.7	38.4
87.5°	16.3	16.4	16.4	16.4	16.5	16.7	17.2	17.6	18.0	18.5	18.5
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	18.8	18.1	17.5	16.9	16.3	17.1	19.2	21.4	23.6	25.9	27.3
95°	61.5	52.3	43.1	33.9	24.7	21.4	23.8	26.4	28.8	31.2	32.8
97.5°	123.6	119.5	115.3	111.2	107.0	96.9	80.9	64.7	48.6	32.4	34.2
100°	170.4	174.8	179.4	183.8	188.2	173.0	138.0	103.1	68.2	33.2	35.0
102.5°	223.6	226.8	230.0	233.3	236.5	219.0	180.9	142.7	104.5	66.3	60.8
105°	300.3	302.9	305.3	307.8	310.2	301.3	281.2	261.1	241.0	220.8	181.1
107.5°	381.4	383.4	385.4	387.4	389.3	391.9	395.1	398.3	401.4	404.7	375.6
110°	435.5	437.3	439.0	440.8	442.6	444.7	447.2	449.7	452.1	454.6	447.2



TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.1	488.7	490.3	491.9	493.5	495.5	498.1	500.5	502.9	505.4	505.5
115°	563.5	564.8	566.1	567.5	568.9	570.6	572.5	574.5	576.5	578.6	580.9
117.5°	637.4	639.1	640.8	642.5	644.1	645.4	646.4	647.5	648.5	649.5	651.4
120°	683.4	685.4	687.4	689.4	691.5	692.9	693.5	694.2	694.9	695.5	697.3
122.5°	730.2	731.8	733.5	735.2	736.8	738.1	738.9	739.8	740.6	741.4	742.8
125°	794.3	796.1	797.9	799.7	801.4	802.8	803.8	804.6	805.5	806.4	806.9
127.5°	856.4	858.2	860.0	861.7	863.5	864.9	866.1	867.2	868.2	869.3	870.0
130°	895.1	896.9	898.7	900.5	902.3	903.6	904.5	905.4	906.3	907.2	908.1
132.5°	932.2	934.0	935.7	937.6	939.4	940.6	941.3	942.0	942.8	943.5	944.4
135°	988.9	990.2	991.5	992.9	994.2	995.3	996.2	997.1	998.0	999.0	999.6
137.5°	1037.2	1038.9	1040.7	1042.4	1044.0	1045.1	1045.6	1046.1	1046.6	1047.1	1048.1
140°	1069.4	1070.9	1072.2	1073.5	1074.9	1075.9	1076.5	1077.2	1077.9	1078.5	1079.4
142.5°	1099.3	1100.7	1102.0	1103.4	1104.7	1105.7	1106.4	1107.0	1107.7	1108.4	1109.1
145°	1141.0	1142.7	1144.2	1145.8	1147.3	1148.3	1148.8	1149.2	1149.6	1150.1	1150.5
147.5°	1180.3	1181.4	1182.5	1183.5	1184.5	1185.2	1185.7	1186.1	1186.6	1187.0	1187.5
150°	1204.6	1205.3	1205.9	1206.6	1207.2	1207.8	1208.2	1208.7	1209.1	1209.6	1210.0
152.5°	1226.3	1226.7	1227.0	1227.3	1227.6	1227.9	1228.1	1228.4	1228.7	1228.9	1229.7
155°	1257.0	1256.5	1256.1	1255.7	1255.2	1255.1	1255.3	1255.5	1255.8	1256.0	1257.1
157.5°	1280.7	1280.7	1280.7	1280.6	1280.6	1280.4	1280.2	1280.0	1279.8	1279.5	1280.9
160°	1295.3	1295.1	1294.8	1294.6	1294.3	1294.1	1293.9	1293.7	1293.4	1293.2	1294.6
162.5°	1309.0	1308.4	1307.8	1307.3	1306.7	1306.3	1306.1	1305.8	1305.6	1305.4	1306.9
165°	1325.5	1324.8	1324.1	1323.5	1322.8	1322.4	1322.1	1321.9	1321.7	1321.5	1323.2
167.5°	1338.4	1337.6	1336.7	1335.7	1334.8	1334.3	1334.3	1334.3	1334.3	1334.3	1336.2
170°	1345.6	1344.7	1343.9	1343.0	1342.1	1341.6	1341.6	1341.6	1341.6	1341.6	1343.4
172.5°	1350.5	1349.5	1348.4	1347.3	1346.3	1345.7	1345.9	1346.2	1346.3	1346.5	1348.3
175°	1356.8	1355.6	1354.5	1353.4	1352.3	1351.8	1352.0	1352.3	1352.5	1352.7	1354.3
177.5°	1358.4	1357.5	1356.6	1355.6	1354.8	1354.4	1354.6	1354.8	1354.9	1355.1	1356.6
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	896.3	897.6	899.0	899.6	899.5	899.3	899.2	899.1
5°	891.5	893.2	894.9	895.6	895.2	894.9	894.6	894.2
7.5°	882.0	883.5	885.1	885.8	885.6	885.3	885.1	884.9
10°	873.3	874.9	876.5	877.1	876.8	876.4	876.1	875.7
12.5°	863.8	865.1	866.2	866.6	866.4	866.2	866.0	865.8
15°	846.8	848.1	849.5	849.6	848.6	847.6	846.6	845.6
17.5°	825.1	826.0	827.0	827.2	826.9	826.5	826.1	825.7
20°	809.0	809.7	810.3	810.4	809.9	809.4	808.9	808.4
22.5°	792.0	792.5	793.1	793.0	792.4	791.7	791.1	790.4
25°	763.9	764.1	764.2	764.1	763.6	763.1	762.4	761.9
27.5°	734.0	734.1	734.2	734.0	733.3	732.7	732.0	731.3
30°	713.3	713.3	713.3	712.7	711.4	710.2	709.0	707.8
32.5°	691.6	690.5	689.5	688.7	688.1	687.5	686.8	686.2
35°	656.2	655.2	654.2	653.3	652.4	651.6	650.7	649.8
37.5°	619.8	618.5	617.3	616.4	615.9	615.3	614.8	614.2
40°	596.0	594.6	593.3	592.2	591.5	590.9	590.2	589.5
42.5°	571.3	569.9	568.5	567.4	566.7	566.1	565.4	564.7
45°	534.3	532.2	530.2	528.7	527.9	526.9	526.1	525.2
47.5°	495.3	493.3	491.3	489.9	489.2	488.4	487.7	486.9
50°	469.7	467.8	465.9	464.4	463.3	462.3	461.3	460.3
52.5°	443.6	442.0	440.4	439.0	438.0	437.0	436.0	434.9
55°	403.8	402.0	400.1	398.7	397.9	397.0	396.2	395.3
57.5°	364.9	363.1	361.5	360.1	359.1	358.2	357.2	356.2
60°	337.3	335.8	334.2	333.0	332.1	331.2	330.4	329.5
62.5°	310.6	309.1	307.6	306.5	305.9	305.4	304.8	304.2
65°	271.0	269.7	268.3	267.4	266.9	266.4	265.9	265.3
67.5°	231.9	230.7	229.4	228.4	227.7	227.0	226.3	225.6
70°	206.4	205.3	204.1	203.0	202.2	201.3	200.5	199.5
72.5°	180.8	179.7	178.6	177.8	177.4	176.9	176.5	176.0
75°	143.7	142.9	142.0	141.3	140.8	140.3	139.8	139.3
77.5°	109.2	108.6	108.0	107.7	107.7	107.7	107.7	107.7
80°	87.1	86.8	86.7	86.6	86.6	86.6	86.6	86.6
82.5°	67.0	66.7	66.3	66.1	66.0	65.8	65.7	65.6
85°	38.0	37.7	37.3	37.2	37.2	37.2	37.2	37.2
87.5°	18.6	18.6	18.6	18.7	18.8	18.9	19.0	19.1
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	28.7	30.1	31.5	32.4	32.6	32.9	33.2	33.4
95°	34.3	36.0	37.6	38.3	38.3	38.3	38.3	38.3
97.5°	36.1	37.9	39.6	40.6	40.9	41.1	41.3	41.5
100°	36.9	38.7	40.4	41.4	41.7	41.9	42.1	42.3
102.5°	55.2	49.7	44.1	41.5	41.9	42.3	42.7	43.1
105°	141.5	101.8	62.2	42.5	43.0	43.4	43.9	44.3
107.5°	346.5	317.4	288.3	258.8	228.9	199.0	169.2	139.3
110°	439.8	432.4	425.1	405.4	373.2	341.2	309.2	277.2



TEST NUMBER: P331943-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	505.6	505.8	505.9	502.6	495.8	489.1	482.3	475.5
115°	583.1	585.3	587.5	589.2	590.0	590.9	591.8	592.7
117.5°	653.2	654.9	656.7	657.7	657.9	658.0	658.2	658.4
120°	699.1	700.8	702.7	703.6	703.6	703.6	703.6	703.6
122.5°	744.0	745.3	746.5	747.2	747.4	747.6	747.7	747.9
125°	807.3	807.7	808.2	808.6	809.1	809.5	810.0	810.4
127.5°	870.7	871.4	872.1	872.3	871.8	871.4	870.9	870.5
130°	909.0	909.9	910.8	911.0	910.6	910.1	909.7	909.2
132.5°	945.2	946.1	947.1	947.2	946.5	945.9	945.3	944.7
135°	1000.3	1001.0	1001.6	1001.6	1001.0	1000.3	999.6	999.0
137.5°	1049.2	1050.4	1051.4	1051.7	1051.3	1050.9	1050.4	1050.0
140°	1080.4	1081.3	1082.2	1082.4	1081.9	1081.5	1081.1	1080.6
142.5°	1109.8	1110.5	1111.3	1111.3	1110.6	1110.0	1109.4	1108.8
145°	1151.0	1151.4	1152.0	1152.2	1152.2	1152.2	1152.2	1152.2
147.5°	1187.9	1188.3	1188.8	1188.5	1187.5	1186.5	1185.4	1184.4
150°	1210.5	1210.9	1211.4	1211.2	1210.6	1209.9	1209.2	1208.6
152.5°	1230.5	1231.3	1232.1	1232.0	1231.0	1230.0	1229.0	1227.9
155°	1258.2	1259.3	1260.4	1260.3	1259.0	1257.7	1256.3	1255.0
157.5°	1282.2	1283.5	1285.0	1284.8	1282.9	1281.2	1279.5	1277.8
160°	1296.0	1297.3	1298.6	1298.5	1297.0	1295.4	1293.8	1292.2
162.5°	1308.4	1309.9	1311.4	1311.5	1310.1	1308.7	1307.4	1306.0
165°	1325.0	1326.9	1328.7	1328.8	1327.2	1325.6	1324.0	1322.5
167.5°	1338.0	1339.8	1341.5	1341.5	1339.8	1338.0	1336.2	1334.3
170°	1345.2	1347.1	1348.8	1348.8	1347.1	1345.2	1343.4	1341.6
172.5°	1350.1	1351.8	1353.6	1353.5	1351.6	1349.6	1347.7	1345.6
175°	1355.8	1357.5	1359.0	1358.9	1357.1	1355.3	1353.5	1351.7
177.5°	1358.0	1359.5	1360.9	1360.7	1358.9	1357.2	1355.3	1353.5
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8

(END OF REPORT)