

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331944-840

Luminaire Tested: **S123DIP-S560D1025U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331944-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1025U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5900.3 lumens  
Efficiency: N/A  
Efficacy: 132.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	73	68	79	73	67	63	59	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	50	44	46	41	37	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	36	31	51	41	34	29	34	29	25	27	23	20	21	19	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9684	9684	9684
5°	9729	9596	9662
10°	9664	9512	9571
15°	9551	9404	9423
20°	9419	9251	9260
25°	9242	9069	9049
30°	9047	8866	8797
35°	8843	8650	8539
40°	8630	8413	8283
45°	8397	8196	7995
50°	8162	7927	7708
55°	7854	7651	7418
60°	7543	7326	7093
65°	7272	6976	6757
70°	6864	6571	6279
75°	6276	6047	5793
80°	5659	5424	5368
85°	4965	4780	4594



TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.7	1.4
10°-20°	239.3	4.1
20°-30°	353.5	6.0
30°-40°	412.9	7.0
40°-50°	415.1	7.0
50°-60°	364.6	6.2
60°-70°	271.7	4.6
70°-80°	154.8	2.6
80°-90°	48.2	0.8
90°-100°	83.6	1.4
100°-110°	250.2	4.2
110°-120°	425.6	7.2
120°-130°	559.8	9.5
130°-140°	629.2	10.7
140°-150°	618.5	10.5
150°-160°	520.7	8.8
160°-170°	346.6	5.9
170°-180°	121.4	2.1
0°-30°	677.5	11.5
0°-40°	1090.4	18.5
0°-60°	1870.2	31.7
0°-90°	2344.9	39.7
90°-120°	759.4	12.9
90°-150°	2566.9	43.5
90°-180°	3555.0	60.3
0°-180°	5900.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	900	900	900	900	900	
5°	900	896	888	895	894	85
15°	857	854	844	850	846	242
25°	778	773	764	764	762	358
35°	673	668	658	654	650	421
45°	552	548	538	529	525	426
55°	418	417	408	399	395	375
65°	286	281	274	268	265	282
75°	151	148	145	142	139	161
85°	40	39	39	37	37	44
90°	1	11	24	28	30	6
95°	60	67	75	78	79	67
105°	227	229	238	238	240	243
115°	428	431	429	430	429	424
125°	627	630	628	624	620	559
135°	814	819	818	815	812	627
145°	987	989	992	991	987	616
155°	1130	1130	1131	1134	1128	520
165°	1231	1228	1228	1233	1227	347
175°	1280	1276	1276	1282	1275	122
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	902.7	902.2	901.7	901.1	900.6	899.5	898.0	896.5	895.0	893.5	894.8
5°	900.4	899.6	898.7	897.9	897.0	895.6	893.7	891.8	890.0	888.1	889.8
7.5°	891.6	890.8	889.9	889.1	888.2	886.8	884.8	882.8	880.9	879.0	880.5
10°	884.2	883.3	882.5	881.6	880.8	879.2	877.0	874.7	872.5	870.3	871.8
12.5°	874.3	873.5	872.8	872.1	871.4	870.0	867.9	865.8	863.7	861.6	862.7
15°	857.1	856.5	855.8	855.1	854.3	852.9	850.7	848.5	846.2	843.9	845.4
17.5°	837.2	836.3	835.4	834.5	833.5	832.0	829.8	827.6	825.4	823.0	824.0
20°	822.3	821.3	820.2	819.2	818.2	816.6	814.4	812.1	809.8	807.6	808.3
22.5°	805.6	804.6	803.5	802.5	801.4	799.8	797.6	795.4	793.1	790.9	791.4
25°	778.2	777.2	776.2	775.2	774.1	772.4	770.2	768.0	765.8	763.6	763.7
27.5°	749.0	748.0	747.0	746.0	745.0	743.3	740.8	738.5	736.1	733.7	733.8
30°	727.9	727.1	726.2	725.4	724.5	722.9	720.4	718.0	715.7	713.3	713.3
32.5°	706.9	705.8	704.6	703.5	702.4	700.8	699.0	697.1	695.3	693.5	692.5
35°	673.0	672.0	671.0	669.9	668.9	667.2	665.0	662.8	660.6	658.3	657.3
37.5°	638.3	637.0	635.7	634.4	633.1	631.4	629.0	626.8	624.5	622.3	621.1
40°	614.2	613.2	612.2	611.2	610.1	608.3	605.9	603.6	601.2	598.7	597.3
42.5°	590.1	589.0	587.7	586.5	585.4	583.6	581.2	578.9	576.4	574.0	572.6
45°	551.6	550.9	550.2	549.5	548.8	547.3	545.1	542.9	540.7	538.4	536.3
47.5°	513.3	512.3	511.4	510.4	509.4	507.8	505.7	503.6	501.5	499.4	497.4
50°	487.4	486.5	485.6	484.7	483.9	482.4	480.1	477.9	475.6	473.4	471.5
52.5°	460.1	459.5	459.0	458.4	457.8	456.3	453.9	451.6	449.2	446.9	445.2
55°	418.5	418.3	418.2	418.0	417.8	416.6	414.3	412.1	409.9	407.7	405.8
57.5°	378.9	378.3	377.7	377.2	376.6	375.4	373.5	371.8	370.0	368.2	366.6
60°	350.4	350.2	350.1	349.9	349.7	348.6	346.6	344.5	342.4	340.3	338.8
62.5°	325.1	324.6	324.2	323.8	323.3	322.0	319.9	317.9	315.8	313.8	312.3
65°	285.5	284.6	283.8	282.9	282.1	280.7	279.0	277.3	275.6	273.9	272.5
67.5°	243.5	242.8	242.0	241.3	240.4	239.4	238.1	236.8	235.5	234.3	233.1
70°	218.1	217.1	216.1	215.1	214.0	213.0	212.0	211.0	209.8	208.8	207.6
72.5°	191.6	190.8	190.1	189.2	188.5	187.5	186.4	185.2	184.0	182.9	181.8
75°	150.9	150.2	149.5	148.8	148.1	147.5	146.9	146.4	145.9	145.4	144.6
77.5°	114.8	114.4	114.0	113.7	113.3	112.8	112.2	111.6	110.9	110.3	109.8
80°	91.3	90.8	90.3	89.8	89.2	88.8	88.5	88.1	87.8	87.5	87.3
82.5°	68.4	68.3	68.2	68.1	68.0	67.9	67.9	67.8	67.7	67.7	67.3
85°	40.2	39.9	39.6	39.2	38.9	38.7	38.7	38.7	38.7	38.7	38.4
87.5°	16.3	16.4	16.4	16.4	16.5	16.7	17.2	17.6	18.0	18.5	18.5
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	24.4	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4
95°	59.5	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5
97.5°	105.6	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8
100°	137.1	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9
102.5°	173.4	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3
105°	226.8	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9
107.5°	288.9	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5
110°	327.6	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5



TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	367.9	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6
115°	428.4	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7
117.5°	489.3	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7
120°	527.3	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0
122.5°	566.7	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9
125°	627.0	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1
127.5°	682.7	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6
130°	719.7	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9
132.5°	756.9	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6
135°	813.5	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7
137.5°	866.0	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6
140°	902.2	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.2	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9
145°	986.8	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7
147.5°	1032.1	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5
150°	1063.5	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5
152.5°	1089.3	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7
155°	1130.0	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0
157.5°	1164.7	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3
160°	1186.5	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6
162.5°	1205.9	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0
165°	1230.8	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1
167.5°	1250.8	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0
170°	1262.1	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6
172.5°	1270.9	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3
175°	1280.2	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6
177.5°	1284.0	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	896.3	897.6	899.0	899.6	899.5	899.3	899.2	899.1
5°	891.5	893.2	894.9	895.6	895.2	894.9	894.6	894.2
7.5°	882.0	883.5	885.1	885.8	885.6	885.3	885.1	884.9
10°	873.3	874.9	876.5	877.1	876.8	876.4	876.1	875.7
12.5°	863.8	865.1	866.2	866.6	866.4	866.2	866.0	865.8
15°	846.8	848.1	849.5	849.6	848.6	847.6	846.6	845.6
17.5°	825.1	826.0	827.0	827.2	826.9	826.5	826.1	825.7
20°	809.0	809.7	810.3	810.4	809.9	809.4	808.9	808.4
22.5°	792.0	792.5	793.1	793.0	792.4	791.7	791.1	790.4
25°	763.9	764.1	764.2	764.1	763.6	763.1	762.4	761.9
27.5°	734.0	734.1	734.2	734.0	733.3	732.7	732.0	731.3
30°	713.3	713.3	713.3	712.7	711.4	710.2	709.0	707.8
32.5°	691.6	690.5	689.5	688.7	688.1	687.5	686.8	686.2
35°	656.2	655.2	654.2	653.3	652.4	651.6	650.7	649.8
37.5°	619.8	618.5	617.3	616.4	615.9	615.3	614.8	614.2
40°	596.0	594.6	593.3	592.2	591.5	590.9	590.2	589.5
42.5°	571.3	569.9	568.5	567.4	566.7	566.1	565.4	564.7
45°	534.3	532.2	530.2	528.7	527.9	526.9	526.1	525.2
47.5°	495.3	493.3	491.3	489.9	489.2	488.4	487.7	486.9
50°	469.7	467.8	465.9	464.4	463.3	462.3	461.3	460.3
52.5°	443.6	442.0	440.4	439.0	438.0	437.0	436.0	434.9
55°	403.8	402.0	400.1	398.7	397.9	397.0	396.2	395.3
57.5°	364.9	363.1	361.5	360.1	359.1	358.2	357.2	356.2
60°	337.3	335.8	334.2	333.0	332.1	331.2	330.4	329.5
62.5°	310.6	309.1	307.6	306.5	305.9	305.4	304.8	304.2
65°	271.0	269.7	268.3	267.4	266.9	266.4	265.9	265.3
67.5°	231.9	230.7	229.4	228.4	227.7	227.0	226.3	225.6
70°	206.4	205.3	204.1	203.0	202.2	201.3	200.5	199.5
72.5°	180.8	179.7	178.6	177.8	177.4	176.9	176.5	176.0
75°	143.7	142.9	142.0	141.3	140.8	140.3	139.8	139.3
77.5°	109.2	108.6	108.0	107.7	107.7	107.7	107.7	107.7
80°	87.1	86.8	86.7	86.6	86.6	86.6	86.6	86.6
82.5°	67.0	66.7	66.3	66.1	66.0	65.8	65.7	65.6
85°	38.0	37.7	37.3	37.2	37.2	37.2	37.2	37.2
87.5°	18.6	18.6	18.6	18.7	18.8	18.9	19.0	19.1
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.2	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	76.3	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	118.8	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	149.6	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.0	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.2	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	333.5	334.4	335.3	335.5	335.0	334.6	334.2	333.7





TEST NUMBER: P331944-840

CATALOG NUMBER: S123DIP-S560D1025U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	371.7	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.8	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	567.3	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	626.2	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	684.4	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	723.0	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	760.5	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	816.8	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	871.7	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.8	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.7	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.5	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.1	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1132.9	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1166.2	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1186.7	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1206.1	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1230.5	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1269.7	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1278.9	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1283.0	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)