

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832208

Luminaire Tested: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832208  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D1195U850-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7476.9 lumens  
Efficiency: N/A  
Efficacy: 147.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 50.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36		
1	95	91	88	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31		
2	87	80	75	70	79	73	68	64	59	56	53	47	45	43	35	34	33	27		
3	80	71	64	59	72	65	59	54	53	49	45	42	39	37	32	30	28	24		
4	73	63	56	50	66	58	51	47	47	43	39	38	35	32	29	27	25	21		
5	68	57	49	44	61	52	45	40	43	38	34	34	31	28	26	24	22	19		
6	62	51	44	38	57	47	40	35	39	34	30	31	28	25	24	22	20	17		
7	58	46	39	34	52	43	36	31	35	30	27	29	25	23	22	20	18	15		
8	54	42	35	30	49	39	32	28	32	28	24	26	23	20	21	18	17	14		
9	50	39	32	27	46	36	29	25	30	25	22	24	21	18	19	17	15	13		
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	21801	21801	21801	21801	21801
5°	25887	25061	21939	17735	16466
10°	23455	25456	21829	14210	12190
15°	16148	21826	21599	11614	9643
20°	11234	16804	21165	9793	8475
25°	8561	12807	20535	8704	7811
30°	7452	10239	19745	8081	7235
35°	6842	8637	18628	7557	6711
40°	6243	7713	17165	7043	6232
45°	5638	7054	15586	6555	5751
50°	5117	6507	13725	6077	5159
55°	4628	5977	11937	5611	4425
60°	4148	5436	10370	5096	4183
65°	3828	4821	8925	4579	3955
70°	3109	4170	7789	4142	3213
75°	2728	3315	6596	3435	2832
80°	2473	2808	5405	2882	2678
85°	2260	2458	4100	2618	2458

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 16446 cd/sqm



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.6	2.5
10°-20°	427.2	5.7
20°-30°	490.1	6.6
30°-40°	483.1	6.5
40°-50°	426.0	5.7
50°-60°	327.8	4.4
60°-70°	215.5	2.9
70°-80°	104.7	1.4
80°-90°	29.9	0.4
90°-100°	345.4	4.6
100°-110°	1011.2	13.5
110°-120°	987.5	13.2
120°-130°	786.4	10.5
130°-140°	620.5	8.3
140°-150°	462.9	6.2
150°-160°	322.7	4.3
160°-170°	189.6	2.5
170°-180°	61.7	0.8
0°-30°	1102.0	14.7
0°-40°	1585.1	21.2
0°-60°	2338.9	31.3
0°-90°	2689.0	36.0
90°-120°	2344.1	31.4
90°-150°	4213.9	56.4
90°-180°	4788.0	64.0
0°-180°	7476.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2025	2025	2025	2025	2025	
5°	2396	2319	2030	1641	1524	219
15°	1449	1959	1938	1042	865	409
25°	721	1078	1729	733	658	340
35°	521	657	1418	575	511	325
45°	370	463	1024	431	378	288
55°	247	318	636	299	236	221
65°	150	189	350	180	155	147
75°	66	80	159	83	68	71
85°	18	20	33	21	20	19
90°	37	32	3	32	37	21
95°	150	764	44	764	150	243
105°	1639	1036	150	1036	1639	1635
115°	1993	792	264	792	1993	1944
125°	1572	740	367	740	1572	1423
135°	1274	729	430	729	1274	988
145°	996	720	491	720	996	632
155°	826	697	558	697	826	385
165°	720	667	610	667	720	206
175°	648	640	635	640	648	63
180°	636	636	636	636	636	



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	2244.7	2237.6	2230.6	2228.5	2226.4	2219.8	2213.1	2198.2	2183.2	2167.9	2152.5
5°	2395.8	2396.6	2397.5	2395.4	2393.3	2384.6	2375.9	2357.6	2339.3	2319.4	2299.5
7.5°	2349.3	2362.6	2375.9	2378.4	2380.9	2387.5	2394.2	2390.0	2385.8	2378.4	2370.9
10°	2145.9	2145.0	2144.2	2159.1	2174.1	2218.5	2262.9	2285.8	2308.6	2329.0	2349.3
12.5°	1813.7	1814.9	1816.2	1865.2	1914.2	1956.1	1998.0	2056.2	2114.3	2177.0	2239.7
15°	1449.1	1469.5	1489.8	1533.4	1577.0	1640.1	1703.2	1781.3	1859.4	1958.6	2057.8
17.5°	1190.0	1198.7	1207.5	1249.4	1291.3	1351.1	1410.9	1499.4	1587.8	1715.7	1843.6
20°	980.7	988.6	996.5	1026.8	1057.1	1114.4	1171.7	1256.0	1340.3	1467.0	1593.6
22.5°	818.8	834.2	849.5	869.9	890.2	931.8	973.3	1059.2	1145.2	1260.6	1376.0
25°	720.8	727.9	734.9	752.4	769.8	809.7	849.5	906.4	963.3	1078.3	1193.3
27.5°	654.4	656.5	658.5	671.4	684.3	710.0	735.8	788.5	841.2	935.9	1030.6
30°	599.6	603.3	607.1	617.0	627.0	645.7	664.4	701.7	739.1	823.8	908.5
32.5°	557.2	559.3	561.4	569.7	578.0	591.7	605.4	634.9	664.4	729.1	793.9
35°	520.7	521.1	521.5	527.7	534.0	547.3	560.5	585.0	609.5	657.3	705.0
37.5°	479.2	482.1	485.0	489.5	494.1	505.7	517.4	537.3	557.2	596.7	636.1
40°	444.3	446.8	449.3	454.7	460.1	469.2	478.3	496.6	514.9	548.9	583.0
42.5°	409.4	411.1	412.7	418.1	423.5	434.7	445.9	460.5	475.0	503.2	531.5
45°	370.4	374.5	378.7	384.5	390.3	399.9	409.4	424.4	439.3	463.4	487.5
47.5°	338.0	340.1	342.1	347.1	352.1	363.7	375.4	388.6	401.9	424.4	446.8
50°	305.6	306.4	307.3	311.8	316.4	326.8	337.2	352.5	367.9	388.6	409.4
52.5°	274.9	277.0	279.0	283.6	288.2	295.2	302.3	318.1	333.8	354.2	374.5
55°	246.6	247.9	249.1	252.5	255.8	264.1	272.4	286.1	299.8	318.5	337.2
57.5°	220.1	221.7	223.4	225.9	228.4	235.8	243.3	255.4	267.4	286.1	304.8
60°	192.7	194.7	196.8	199.7	202.6	208.4	214.3	225.0	235.8	252.5	269.1
62.5°	172.7	173.1	173.6	176.1	178.5	182.7	186.8	195.6	204.3	220.9	237.5
65°	150.3	151.6	152.8	154.0	155.3	158.6	161.9	169.4	176.9	189.3	201.8
67.5°	127.1	128.3	129.5	131.6	133.7	136.6	139.5	144.5	149.5	161.1	172.7
70°	98.8	98.8	98.8	102.1	105.5	110.4	115.4	119.2	122.9	132.5	142.0
72.5°	80.6	81.0	81.4	81.8	82.2	85.1	88.0	94.3	100.5	106.3	112.1
75°	65.6	66.0	66.4	66.9	67.3	68.1	68.9	71.0	73.1	79.7	86.4
77.5°	52.3	52.7	53.1	53.6	54.0	54.8	55.6	56.5	57.3	59.8	62.3
80°	39.9	40.3	40.7	41.1	41.5	41.9	42.4	43.2	44.0	45.3	46.5
82.5°	29.1	29.1	29.1	29.1	29.1	29.9	30.7	30.7	30.7	31.6	32.4
85°	18.3	18.3	18.3	18.7	19.1	19.1	19.1	19.5	19.9	19.9	19.9
87.5°	8.3	7.9	7.5	7.9	8.3	8.3	8.3	8.7	9.1	9.1	9.1
90°	37.4	38.7	37.4	36.1	37.4	34.8	33.5	32.2	30.9	32.2	28.3
92.5°	68.3	70.9	69.6	74.7	77.3	86.3	99.2	127.6	179.1	239.7	265.4
95°	149.5	154.6	163.6	175.2	199.7	246.1	314.4	463.9	619.8	764.1	680.3
97.5°	306.7	320.8	351.8	400.7	487.0	633.9	804.0	1065.6	1215.0	1175.1	877.5
100°	807.9	806.6	856.8	950.9	1081.0	1264.0	1414.8	1519.1	1474.0	1220.2	824.6
102.5°	1279.5	1316.8	1356.8	1426.4	1520.4	1619.6	1691.8	1669.9	1486.9	1136.4	747.3
105°	1639.0	1645.4	1686.6	1735.6	1794.9	1828.4	1803.9	1675.0	1405.7	1035.9	686.8
107.5°	1873.5	1887.6	1904.4	1927.6	1935.3	1900.5	1800.0	1597.7	1289.8	947.0	643.0
110°	2007.5	2010.0	2012.6	2002.3	1966.2	1876.0	1713.7	1476.6	1181.5	873.6	619.8



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	2034.5	2033.2	2020.4	1983.0	1909.5	1787.1	1600.3	1356.8	1087.5	824.6	606.9
115°	1993.3	1986.9	1961.1	1904.4	1807.8	1667.3	1477.9	1253.7	1015.3	792.4	605.6
117.5°	1903.1	1894.1	1855.4	1792.3	1691.8	1546.2	1372.2	1173.8	967.7	770.5	606.9
120°	1784.6	1776.8	1745.9	1673.7	1572.0	1441.8	1287.2	1113.3	931.6	756.3	612.0
122.5°	1673.7	1663.4	1628.7	1565.5	1477.9	1359.4	1218.9	1065.6	901.9	747.3	621.1
125°	1572.0	1562.9	1530.7	1474.0	1391.6	1288.5	1164.8	1024.3	877.5	739.6	630.1
127.5°	1484.3	1476.6	1447.0	1398.0	1323.3	1227.9	1114.5	987.0	854.3	735.7	640.4
130°	1412.2	1401.9	1374.8	1328.4	1260.1	1172.5	1068.2	952.2	836.2	731.9	650.7
132.5°	1341.3	1334.9	1311.7	1265.3	1202.2	1119.7	1024.3	920.0	819.5	730.6	658.4
135°	1274.3	1265.3	1242.1	1203.4	1140.3	1066.9	983.1	891.6	805.3	729.3	666.1
137.5°	1203.4	1195.7	1176.4	1136.4	1082.3	1016.6	941.9	864.6	792.4	726.7	671.3
140°	1128.7	1130.0	1109.4	1073.3	1024.3	968.9	907.1	841.4	780.8	725.4	676.5
142.5°	1059.1	1060.4	1042.4	1011.5	971.5	925.1	873.6	819.5	770.5	722.8	680.3
145°	996.0	993.4	983.1	956.1	923.8	886.5	845.2	802.7	761.5	720.3	681.6
147.5°	941.9	940.6	930.3	911.0	885.2	858.1	823.3	788.6	752.5	716.4	681.6
150°	895.5	895.5	887.8	873.6	854.3	829.8	802.7	773.1	743.5	711.2	681.6
152.5°	856.8	856.8	853.0	840.1	825.9	806.6	783.4	758.9	733.2	704.8	677.7
155°	825.9	824.6	822.1	811.7	800.2	784.7	765.4	744.7	722.8	697.1	675.2
157.5°	796.3	796.3	793.7	786.0	775.7	762.8	747.3	729.3	711.2	690.6	671.3
160°	767.9	769.2	769.2	761.5	752.5	743.5	730.6	716.4	699.6	682.9	668.7
162.5°	742.2	743.5	743.5	737.0	731.9	724.1	712.5	700.9	688.1	675.2	663.6
165°	720.3	720.3	721.6	716.4	711.2	704.8	695.8	688.1	677.7	667.4	658.4
167.5°	698.4	698.4	699.6	695.8	693.2	688.1	682.9	676.5	667.4	659.7	653.3
170°	679.0	679.0	680.3	677.7	676.5	673.9	668.7	664.9	658.4	652.0	648.1
172.5°	661.0	662.3	664.9	662.3	662.3	661.0	657.1	654.6	649.4	645.5	644.2
175°	648.1	649.4	650.7	649.4	649.4	649.4	646.8	645.5	643.0	640.4	640.4
177.5°	639.1	639.1	641.7	640.4	641.7	641.7	640.4	639.1	637.8	636.5	637.8
180°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	2150.4	2148.3	2128.4	2108.5	2089.0	2069.5	2054.9	2040.4	2015.9	1991.4	1976.0
5°	2283.7	2267.9	2236.4	2204.8	2157.5	2110.1	2070.3	2030.4	1979.8	1929.1	1886.8
7.5°	2358.0	2345.2	2307.0	2268.8	2206.1	2143.4	2081.1	2018.8	1944.1	1869.3	1805.4
10°	2360.1	2370.9	2339.3	2307.8	2237.2	2166.6	2081.9	1997.2	1896.7	1796.2	1713.6
12.5°	2286.2	2332.7	2326.1	2319.4	2247.6	2175.7	2072.8	1969.8	1846.5	1723.2	1619.8
15°	2147.9	2238.0	2264.6	2291.2	2231.8	2172.4	2055.3	1938.2	1793.3	1648.4	1529.7
17.5°	1969.8	2096.0	2166.2	2236.4	2193.2	2150.0	2021.7	1893.4	1730.2	1567.0	1437.9
20°	1758.9	1924.1	2034.2	2144.2	2128.4	2112.6	1980.2	1847.7	1671.7	1495.6	1355.7
22.5°	1550.4	1724.8	1876.8	2028.8	2045.0	2061.1	1927.4	1793.7	1601.1	1408.4	1266.0
25°	1370.6	1547.9	1729.0	1910.0	1946.5	1983.1	1856.0	1729.0	1529.3	1329.5	1187.9
27.5°	1199.2	1367.7	1567.0	1766.3	1832.8	1899.2	1783.0	1666.7	1458.7	1250.6	1109.5
30°	1059.2	1209.9	1413.4	1616.9	1709.5	1802.1	1695.3	1588.6	1382.3	1175.9	1037.6
32.5°	928.8	1063.8	1268.1	1472.4	1579.9	1687.5	1595.3	1503.1	1304.6	1106.1	969.5
35°	825.9	946.7	1137.3	1327.9	1448.3	1568.7	1493.1	1417.6	1223.7	1029.7	900.6
37.5°	737.4	838.7	1017.7	1196.7	1324.5	1452.4	1389.3	1326.2	1143.9	961.6	839.6
40°	664.4	745.7	912.2	1078.7	1204.1	1329.5	1275.6	1221.6	1058.4	895.2	781.0
42.5°	601.7	671.8	821.3	970.8	1085.8	1200.8	1165.1	1129.4	981.6	833.8	727.9
45°	546.4	605.4	737.0	868.6	974.5	1080.4	1052.2	1023.9	896.5	769.0	671.8
47.5°	497.4	548.1	665.6	783.1	878.2	973.3	947.1	921.0	815.5	710.0	621.6
50°	452.6	495.8	593.8	691.8	777.3	862.8	841.2	819.6	732.4	645.3	568.9
52.5°	410.2	445.9	534.0	622.0	690.9	759.9	743.2	726.6	659.4	592.1	522.8
55°	370.0	402.8	477.1	551.4	610.4	669.3	652.7	636.1	583.8	531.5	470.4
57.5°	333.4	362.1	422.3	482.5	529.4	576.3	568.4	560.5	516.9	473.3	423.1
60°	294.8	320.5	372.5	424.4	462.1	499.9	490.8	481.7	450.5	419.4	376.2
62.5°	260.3	283.2	324.7	366.2	396.9	427.7	421.0	414.4	390.7	367.1	331.3
65°	224.2	246.6	280.3	313.9	338.0	362.1	356.3	350.4	332.6	314.7	286.1
67.5°	191.4	210.1	239.2	268.2	284.4	300.6	297.3	294.0	280.3	266.6	244.1
70°	158.2	174.4	198.5	222.6	233.8	245.0	246.2	247.5	235.0	222.6	205.9
72.5°	125.0	137.9	160.3	182.7	191.4	200.1	199.7	199.3	191.8	184.4	169.4
75°	95.9	105.5	122.9	140.3	147.8	155.3	157.0	158.6	151.6	144.5	136.2
77.5°	68.9	75.6	88.9	102.1	110.4	118.8	119.6	120.4	117.1	113.8	105.9
80°	48.6	50.7	59.0	67.3	76.0	84.7	86.0	87.2	83.9	80.6	75.6
82.5°	33.6	34.9	37.8	40.7	47.8	54.8	56.5	58.1	56.5	54.8	49.4
85°	20.3	20.8	22.0	23.3	26.6	29.9	31.6	33.2	32.4	31.6	28.7
87.5°	9.1	9.1	9.6	10.0	10.8	11.6	13.7	15.8	14.5	13.3	12.0
90°	24.5	20.6	16.8	14.2	11.6	7.7	5.2	2.6	5.2	7.7	11.6
92.5°	198.4	130.1	88.9	65.7	52.8	41.2	28.3	19.3	28.3	41.2	52.8
95°	469.0	277.0	167.5	117.3	83.8	61.8	47.7	43.8	47.7	61.8	83.8
97.5°	521.8	298.9	190.7	135.3	101.8	82.5	70.9	69.6	70.9	82.5	101.8
100°	485.8	295.1	204.9	154.6	123.7	105.7	96.6	95.3	96.6	105.7	123.7
102.5°	454.8	300.2	221.6	176.5	149.5	132.7	125.0	122.4	125.0	132.7	149.5
105°	443.2	310.5	240.9	201.0	176.5	161.1	153.3	149.5	153.3	161.1	176.5
107.5°	440.7	327.3	265.4	228.1	204.9	189.4	181.7	177.8	181.7	189.4	204.9
110°	447.1	349.2	291.2	255.1	233.2	219.0	212.6	208.7	212.6	219.0	233.2





TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	460.0	371.1	318.3	283.5	261.6	247.4	240.9	237.1	240.9	247.4	261.6
115°	474.2	395.6	346.6	311.8	289.9	277.0	269.3	264.1	269.3	277.0	289.9
117.5°	492.2	421.3	372.4	340.2	315.7	304.1	297.6	291.2	297.6	304.1	315.7
120°	512.8	445.8	399.4	367.2	342.7	329.9	323.4	319.5	323.4	329.9	342.7
122.5°	532.1	471.6	426.5	391.7	368.5	354.3	347.9	344.0	347.9	354.3	368.5
125°	552.8	496.1	451.0	416.2	391.7	377.5	369.8	367.2	369.8	377.5	391.7
127.5°	569.5	518.0	474.2	439.4	412.3	398.1	389.1	385.3	389.1	398.1	412.3
130°	586.3	537.3	494.8	460.0	432.9	417.5	405.9	402.0	405.9	417.5	432.9
132.5°	601.7	554.1	512.8	479.3	452.3	432.9	420.0	414.9	420.0	432.9	452.3
135°	614.6	570.8	530.9	496.1	469.0	449.7	435.5	430.4	435.5	449.7	469.0
137.5°	624.9	582.4	543.7	511.5	484.5	463.9	449.7	444.5	449.7	463.9	484.5
140°	632.6	594.0	556.6	524.4	498.6	478.0	465.1	458.7	465.1	478.0	498.6
142.5°	640.4	603.0	566.9	537.3	511.5	493.5	479.3	474.2	479.3	493.5	511.5
145°	645.5	610.7	577.2	547.6	525.7	506.4	494.8	490.9	494.8	506.4	525.7
147.5°	649.4	617.2	586.3	560.5	538.6	521.8	510.2	507.7	510.2	521.8	538.6
150°	650.7	623.6	594.0	570.8	552.8	536.0	525.7	524.4	525.7	536.0	552.8
152.5°	653.3	627.5	603.0	581.1	565.6	551.5	541.2	541.2	541.2	551.5	565.6
155°	653.3	632.6	610.7	592.7	578.5	565.6	557.9	557.9	557.9	565.6	578.5
157.5°	654.6	635.2	617.2	603.0	590.1	578.5	572.1	570.8	572.1	578.5	590.1
160°	654.6	639.1	623.6	610.7	601.7	591.4	586.3	586.3	586.3	591.4	601.7
162.5°	653.3	640.4	627.5	617.2	609.5	601.7	597.9	597.9	597.9	601.7	609.5
165°	650.7	641.7	631.4	622.3	617.2	610.7	608.2	609.5	608.2	610.7	617.2
167.5°	649.4	641.7	633.9	627.5	623.6	618.5	617.2	618.5	617.2	618.5	623.6
170°	645.5	640.4	633.9	631.4	628.8	624.9	623.6	626.2	623.6	624.9	628.8
172.5°	644.2	640.4	635.2	633.9	632.6	630.1	630.1	631.4	630.1	630.1	632.6
175°	641.7	639.1	636.5	635.2	635.2	632.6	633.9	635.2	633.9	632.6	635.2
177.5°	640.4	637.8	636.5	636.5	636.5	635.2	636.5	637.8	636.5	635.2	636.5
180°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	1960.7	1937.0	1913.3	1896.3	1879.3	1858.1	1836.9	1836.1	1835.3	1819.5	1803.7
5°	1844.4	1803.3	1762.2	1721.9	1681.6	1641.4	1601.1	1592.0	1582.8	1569.1	1555.4
7.5°	1741.4	1675.8	1610.2	1558.7	1507.2	1467.0	1426.7	1399.3	1371.9	1350.7	1329.5
10°	1631.0	1549.6	1468.2	1405.9	1343.6	1300.1	1256.5	1224.9	1193.3	1178.4	1163.4
12.5°	1516.4	1427.9	1339.5	1278.5	1217.4	1165.1	1112.8	1084.1	1055.5	1034.7	1014.0
15°	1410.9	1315.8	1220.7	1156.0	1091.2	1042.2	993.2	964.6	935.9	915.1	894.4
17.5°	1308.8	1212.9	1116.9	1051.3	985.7	941.3	896.9	869.1	841.2	828.4	815.5
20°	1215.8	1119.0	1022.3	960.4	898.5	854.9	811.3	796.4	781.4	769.4	757.4
22.5°	1123.6	1030.6	937.6	878.2	818.8	787.3	755.7	743.7	731.6	722.5	713.3
25°	1046.4	953.8	861.2	809.3	757.4	732.9	708.4	700.5	692.6	683.5	674.3
27.5°	968.3	880.3	792.2	750.7	709.2	689.3	669.3	659.4	649.4	641.9	634.5
30°	899.4	818.0	736.6	702.1	667.7	650.2	632.8	622.0	611.2	604.1	597.1
32.5°	832.9	760.7	688.4	659.0	629.5	612.4	595.4	585.0	574.7	566.4	558.1
35°	771.5	708.8	646.1	619.1	592.1	575.1	558.1	547.7	537.3	529.0	520.7
37.5°	717.5	660.6	603.7	578.4	553.1	538.1	523.2	512.4	501.6	492.9	484.1
40°	666.8	616.6	566.4	541.9	517.4	501.2	485.0	475.4	465.9	458.0	450.1
42.5°	622.0	575.9	529.8	505.7	481.7	466.3	450.9	439.7	428.5	423.9	419.4
45°	574.7	534.0	493.3	470.0	446.8	430.6	414.4	404.8	395.3	391.1	387.0
47.5°	533.1	495.4	457.6	434.7	411.9	397.4	382.8	375.4	367.9	362.1	356.3
50°	492.5	455.9	419.4	397.4	375.4	362.9	350.4	341.3	332.2	328.0	323.9
52.5°	453.4	420.2	387.0	364.6	342.1	330.1	318.1	310.2	302.3	293.6	284.8
55°	409.4	380.3	351.3	331.3	311.4	299.0	286.5	277.4	268.2	259.1	250.0
57.5°	372.9	344.2	315.6	297.7	279.9	267.8	255.8	245.8	235.8	228.4	220.9
60°	333.0	308.1	283.2	265.7	248.3	236.7	225.0	215.5	205.9	202.2	198.5
62.5°	295.6	272.4	249.1	233.8	218.4	207.2	196.0	189.8	183.5	181.0	178.5
65°	257.4	237.5	217.6	203.5	189.3	179.8	170.2	167.3	164.4	162.4	160.3
67.5°	221.7	204.7	187.7	175.2	162.8	156.1	149.5	146.2	142.8	140.3	137.9
70°	189.3	174.4	159.4	148.6	137.9	131.6	125.4	122.5	119.6	115.0	110.4
72.5°	154.5	142.8	131.2	122.9	114.6	109.2	103.8	98.0	92.2	88.0	83.9
75°	127.9	116.3	104.6	96.7	88.9	82.6	76.4	74.3	72.2	71.0	69.8
77.5°	98.0	88.0	78.1	71.8	65.6	62.7	59.8	58.5	57.3	56.9	56.5
80°	70.6	62.3	54.0	50.7	47.3	46.5	45.7	44.8	44.0	43.6	43.2
82.5°	44.0	39.9	35.7	34.9	34.0	33.6	33.2	32.8	32.4	32.0	31.6
85°	25.7	24.1	22.4	22.0	21.6	21.2	20.8	20.8	20.8	20.8	20.8
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.4	10.0
90°	14.2	16.8	20.6	24.5	28.3	32.2	30.9	32.2	33.5	34.8	37.4
92.5°	65.7	88.9	130.1	198.4	265.4	239.7	179.1	127.6	99.2	86.3	77.3
95°	117.3	167.5	277.0	469.0	680.3	764.1	619.8	463.9	314.4	246.1	199.7
97.5°	135.3	190.7	298.9	521.8	877.5	1175.1	1215.0	1065.6	804.0	633.9	487.0
100°	154.6	204.9	295.1	485.8	824.6	1220.2	1474.0	1519.1	1414.8	1264.0	1081.0
102.5°	176.5	221.6	300.2	454.8	747.3	1136.4	1486.9	1669.9	1691.8	1619.6	1520.4
105°	201.0	240.9	310.5	443.2	686.8	1035.9	1405.7	1675.0	1803.9	1828.4	1794.9
107.5°	228.1	265.4	327.3	440.7	643.0	947.0	1289.8	1597.7	1800.0	1900.5	1935.3
110°	255.1	291.2	349.2	447.1	619.8	873.6	1181.5	1476.6	1713.7	1876.0	1966.2



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.5	318.3	371.1	460.0	606.9	824.6	1087.5	1356.8	1600.3	1787.1	1909.5
115°	311.8	346.6	395.6	474.2	605.6	792.4	1015.3	1253.7	1477.9	1667.3	1807.8
117.5°	340.2	372.4	421.3	492.2	606.9	770.5	967.7	1173.8	1372.2	1546.2	1691.8
120°	367.2	399.4	445.8	512.8	612.0	756.3	931.6	1113.3	1287.2	1441.8	1572.0
122.5°	391.7	426.5	471.6	532.1	621.1	747.3	901.9	1065.6	1218.9	1359.4	1477.9
125°	416.2	451.0	496.1	552.8	630.1	739.6	877.5	1024.3	1164.8	1288.5	1391.6
127.5°	439.4	474.2	518.0	569.5	640.4	735.7	854.3	987.0	1114.5	1227.9	1323.3
130°	460.0	494.8	537.3	586.3	650.7	731.9	836.2	952.2	1068.2	1172.5	1260.1
132.5°	479.3	512.8	554.1	601.7	658.4	730.6	819.5	920.0	1024.3	1119.7	1202.2
135°	496.1	530.9	570.8	614.6	666.1	729.3	805.3	891.6	983.1	1066.9	1140.3
137.5°	511.5	543.7	582.4	624.9	671.3	726.7	792.4	864.6	941.9	1016.6	1082.3
140°	524.4	556.6	594.0	632.6	676.5	725.4	780.8	841.4	907.1	968.9	1024.3
142.5°	537.3	566.9	603.0	640.4	680.3	722.8	770.5	819.5	873.6	925.1	971.5
145°	547.6	577.2	610.7	645.5	681.6	720.3	761.5	802.7	845.2	886.5	923.8
147.5°	560.5	586.3	617.2	649.4	681.6	716.4	752.5	788.6	823.3	858.1	885.2
150°	570.8	594.0	623.6	650.7	681.6	711.2	743.5	773.1	802.7	829.8	854.3
152.5°	581.1	603.0	627.5	653.3	677.7	704.8	733.2	758.9	783.4	806.6	825.9
155°	592.7	610.7	632.6	653.3	675.2	697.1	722.8	744.7	765.4	784.7	800.2
157.5°	603.0	617.2	635.2	654.6	671.3	690.6	711.2	729.3	747.3	762.8	775.7
160°	610.7	623.6	639.1	654.6	668.7	682.9	699.6	716.4	730.6	743.5	752.5
162.5°	617.2	627.5	640.4	653.3	663.6	675.2	688.1	700.9	712.5	724.1	731.9
165°	622.3	631.4	641.7	650.7	658.4	667.4	677.7	688.1	695.8	704.8	711.2
167.5°	627.5	633.9	641.7	649.4	653.3	659.7	667.4	676.5	682.9	688.1	693.2
170°	631.4	633.9	640.4	645.5	648.1	652.0	658.4	664.9	668.7	673.9	676.5
172.5°	633.9	635.2	640.4	644.2	644.2	645.5	649.4	654.6	657.1	661.0	662.3
175°	635.2	636.5	639.1	641.7	640.4	640.4	643.0	645.5	646.8	649.4	649.4
177.5°	636.5	636.5	637.8	640.4	637.8	636.5	637.8	639.1	640.4	641.7	641.7
180°	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5	636.5



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2025.4	2025.4	2025.4	2025.4
2.5°	1799.6	1795.4	1793.7	1792.1
5°	1542.5	1529.7	1526.8	1523.9
7.5°	1324.1	1318.7	1300.9	1283.0
10°	1146.8	1130.2	1122.8	1115.3
12.5°	998.6	983.2	980.7	978.3
15°	883.6	872.8	869.1	865.3
17.5°	808.0	800.5	796.0	791.4
20°	752.0	746.6	743.2	739.9
22.5°	709.2	705.0	702.6	700.1
25°	668.1	661.9	659.8	657.7
27.5°	629.1	623.7	621.6	619.5
30°	592.5	588.0	585.0	582.1
32.5°	552.7	547.3	545.6	543.9
35°	517.4	514.0	512.4	510.7
37.5°	480.0	475.8	473.3	470.9
40°	448.0	445.9	444.7	443.5
42.5°	415.6	411.9	411.5	411.1
45°	383.2	379.5	378.7	377.8
47.5°	352.9	349.6	349.2	348.8
50°	319.3	314.7	311.4	308.1
52.5°	280.7	276.5	273.6	270.7
55°	245.4	240.8	238.3	235.8
57.5°	218.8	216.7	215.5	214.3
60°	197.2	196.0	195.2	194.3
62.5°	177.3	176.1	176.1	176.1
65°	159.0	157.8	156.5	155.3
67.5°	135.4	132.9	132.5	132.0
70°	106.7	103.0	102.6	102.1
72.5°	83.5	83.0	82.2	81.4
75°	68.9	68.1	68.1	68.1
77.5°	55.6	54.8	54.8	54.8
80°	42.8	42.4	42.8	43.2
82.5°	31.6	31.6	31.1	30.7
85°	20.3	19.9	19.9	19.9
87.5°	10.0	10.0	10.0	10.0
90°	36.1	37.4	38.7	37.4
92.5°	74.7	69.6	70.9	68.3
95°	175.2	163.6	154.6	149.5
97.5°	400.7	351.8	320.8	306.7
100°	950.9	856.8	806.6	807.9
102.5°	1426.4	1356.8	1316.8	1279.5
105°	1735.6	1686.6	1645.4	1639.0
107.5°	1927.6	1904.4	1887.6	1873.5
110°	2002.3	2012.6	2010.0	2007.5



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1983.0	2020.4	2033.2	2034.5
115°	1904.4	1961.1	1986.9	1993.3
117.5°	1792.3	1855.4	1894.1	1903.1
120°	1673.7	1745.9	1776.8	1784.6
122.5°	1565.5	1628.7	1663.4	1673.7
125°	1474.0	1530.7	1562.9	1572.0
127.5°	1398.0	1447.0	1476.6	1484.3
130°	1328.4	1374.8	1401.9	1412.2
132.5°	1265.3	1311.7	1334.9	1341.3
135°	1203.4	1242.1	1265.3	1274.3
137.5°	1136.4	1176.4	1195.7	1203.4
140°	1073.3	1109.4	1130.0	1128.7
142.5°	1011.5	1042.4	1060.4	1059.1
145°	956.1	983.1	993.4	996.0
147.5°	911.0	930.3	940.6	941.9
150°	873.6	887.8	895.5	895.5
152.5°	840.1	853.0	856.8	856.8
155°	811.7	822.1	824.6	825.9
157.5°	786.0	793.7	796.3	796.3
160°	761.5	769.2	769.2	767.9
162.5°	737.0	743.5	743.5	742.2
165°	716.4	721.6	720.3	720.3
167.5°	695.8	699.6	698.4	698.4
170°	677.7	680.3	679.0	679.0
172.5°	662.3	664.9	662.3	661.0
175°	649.4	650.7	649.4	648.1
177.5°	640.4	641.7	639.1	639.1
180°	636.5	636.5	636.5	636.5



TEST NUMBER: P832208

CATALOG NUMBER: S123RDIP-S560D1195U850-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.97	10.69	11.05	11.76	13.22	14.64	15.35	15.71	16.42	17.88
	3H	11.18	11.82	12.27	12.90	14.38	16.13	16.76	17.21	17.84	19.32
	4H	11.56	12.16	12.66	13.25	14.73	16.61	17.21	17.71	18.30	19.78
	6H	11.84	12.39	12.94	13.48	14.98	16.92	17.47	18.02	18.56	20.06
	8H	11.92	12.45	13.03	13.55	15.04	16.99	17.52	18.10	18.62	20.11
	12H	11.97	12.47	13.08	13.56	15.08	17.02	17.52	18.14	18.62	20.13
4H	2H	10.68	11.28	11.79	12.37	13.85	14.62	15.22	15.72	16.30	17.79
	3H	12.04	12.54	13.15	13.65	15.15	16.26	16.77	17.38	17.88	19.37
	4H	12.49	12.95	13.61	14.05	15.57	16.87	17.33	17.98	18.43	19.95
	6H	12.85	13.25	13.97	14.37	15.88	17.30	17.69	18.42	18.82	20.33
	8H	12.98	13.34	14.10	14.46	15.99	17.43	17.80	18.55	18.91	20.44
	12H	13.05	13.38	14.19	14.51	16.04	17.48	17.82	18.62	18.94	20.48
8H	4H	12.80	13.16	13.92	14.28	15.81	16.83	17.19	17.95	18.31	19.84
	6H	13.26	13.56	14.40	14.72	16.24	17.32	17.62	18.46	18.78	20.30
	8H	13.45	13.71	14.60	14.85	16.40	17.50	17.77	18.65	18.91	20.45
	12H	13.59	13.82	14.74	14.95	16.53	17.62	17.85	18.77	18.98	20.56
12H	4H	12.80	13.14	13.94	14.26	15.79	16.77	17.10	17.91	18.23	19.76
	6H	13.32	13.58	14.46	14.72	16.26	17.29	17.56	18.44	18.69	20.24
	8H	13.53	13.76	14.68	14.89	16.48	17.48	17.71	18.63	18.85	20.43