

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831366

Luminaire Tested: S123DIP-S340D1195U950-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831366
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U950-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6056.5 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	21				21
2	84	77	72	67	75	69	64	60	54	51	48	40	37	36	26	25	24	18				18
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16				16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14				14
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12				12
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	14	11				11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				10
8	51	40	32	27	46	36	29	25	28	24	21	21	18	16	15	13	12	9				9
9	48	36	29	24	42	33	27	22	26	22	18	20	17	15	14	12	11	8				8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10083	10083	10083	10083	10083
5°	12751	12035	10172	8198	7533
10°	12874	13264	10105	6535	5710
15°	9697	12315	10036	5534	4829
20°	6756	9964	9907	4840	4386
25°	5152	7663	9689	4453	4114
30°	4457	6088	9340	4179	3895
35°	4135	5140	8938	3980	3741
40°	3915	4612	8373	3792	3688
45°	3784	4267	7655	3646	3666
50°	3719	3996	6805	3512	3647
55°	3581	3796	5971	3385	3663
60°	3453	3584	5147	3266	3602
65°	3245	3382	4439	3138	3533
70°	2996	3125	3777	2927	3323
75°	2712	2803	3236	2720	3036
80°	2238	2455	2560	2368	2560
85°	1766	1988	1877	2013	2038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8741 cd/sqm



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	1.5
10°-20°	220.3	3.6
20°-30°	260.8	4.3
30°-40°	262.3	4.3
40°-50°	240.6	4.0
50°-60°	198.6	3.3
60°-70°	140.5	2.3
70°-80°	75.0	1.2
80°-90°	22.0	0.4
90°-100°	52.6	0.9
100°-110°	254.3	4.2
110°-120°	623.3	10.3
120°-130°	791.2	13.1
130°-140°	845.3	14.0
140°-150°	790.4	13.1
150°-160°	637.6	10.5
160°-170°	411.4	6.8
170°-180°	141.8	2.3
0°-30°	569.7	9.4
0°-40°	832.0	13.7
0°-60°	1271.2	21.0
0°-90°	1508.7	24.9
90°-120°	930.1	15.4
90°-150°	3357.1	55.4
90°-180°	4548.0	75.1
0°-180°	6056.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	937	937	937	937	937	
5°	1180	1114	941	759	697	112
15°	870	1105	901	497	433	240
25°	434	645	816	375	346	205
35°	315	391	680	303	285	198
45°	249	280	503	240	241	193
55°	191	202	318	180	195	171
65°	127	133	174	123	139	127
75°	65	67	78	65	73	68
85°	14	16	15	16	16	16
90°	33	27	1	27	33	15
95°	42	34	68	34	42	35
105°	49	243	330	243	49	102
115°	652	636	620	636	652	613
125°	891	887	873	887	891	796
135°	1098	1098	1087	1098	1098	847
145°	1267	1265	1255	1265	1267	791
155°	1380	1381	1382	1381	1380	637
165°	1454	1453	1458	1453	1454	411
175°	1486	1487	1492	1487	1486	141
180°	1492	1492	1492	1492	1492	



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7
2.5°	1055.8	1054.7	1053.6	1048.1	1042.7	1040.1	1037.5	1029.7	1021.9	1013.2	1004.5
5°	1180.1	1183.1	1186.1	1182.7	1179.2	1168.5	1157.9	1143.8	1129.6	1113.8	1097.9
7.5°	1237.4	1239.2	1240.9	1238.7	1236.6	1233.7	1230.9	1218.3	1205.7	1189.4	1173.1
10°	1177.9	1181.8	1185.7	1194.2	1202.7	1212.2	1221.8	1220.1	1218.3	1213.5	1208.7
12.5°	1047.1	1051.8	1056.6	1073.6	1090.5	1112.3	1134.0	1152.7	1171.4	1184.4	1197.4
15°	870.2	883.4	896.7	912.1	927.5	959.5	991.4	1030.8	1070.1	1105.1	1140.1
17.5°	716.7	721.7	726.7	743.2	759.8	800.0	840.2	885.6	931.0	989.0	1047.1
20°	589.8	594.4	598.9	620.7	642.4	673.9	705.4	756.5	807.6	869.9	932.3
22.5°	495.5	502.7	509.8	522.0	534.2	564.4	594.6	640.0	685.4	754.3	823.2
25°	433.8	439.0	444.2	451.6	459.0	483.1	507.2	544.6	582.0	645.2	708.5
27.5°	391.6	393.8	396.0	403.4	410.7	426.4	442.0	474.2	506.4	560.0	613.7
30°	358.6	360.1	361.6	368.1	374.7	385.3	396.0	419.2	442.5	489.8	537.2
32.5°	335.5	336.6	337.7	342.7	347.7	355.3	362.9	379.9	396.8	435.9	475.1
35°	314.7	315.3	316.0	319.7	323.4	329.0	334.7	347.5	360.3	391.2	422.0
37.5°	296.4	297.3	298.2	300.3	302.5	307.5	312.5	322.7	332.9	356.6	380.3
40°	278.6	280.1	281.7	283.2	284.7	288.8	293.0	300.8	308.6	328.2	347.7
42.5°	263.4	264.9	266.4	267.1	267.7	270.1	272.5	279.7	286.9	301.4	316.0
45°	248.6	249.3	249.9	250.6	251.2	253.2	255.1	261.4	267.7	280.3	293.0
47.5°	235.1	235.1	235.1	235.6	236.0	237.8	239.5	244.1	248.6	258.4	268.2
50°	222.1	222.1	222.1	221.5	220.8	221.9	223.0	226.5	229.9	238.6	247.3
52.5°	206.5	206.5	206.5	206.7	206.9	206.9	206.9	209.9	213.0	220.8	228.6
55°	190.8	191.7	192.5	191.9	191.2	191.7	192.1	194.1	196.0	202.3	208.6
57.5°	175.2	175.6	176.0	175.8	175.6	175.8	176.0	177.8	179.5	184.3	189.1
60°	160.4	160.4	160.4	159.9	159.5	159.9	160.4	161.3	162.1	166.5	170.8
62.5°	143.9	144.1	144.3	144.5	144.7	144.3	143.9	145.0	146.0	149.3	152.6
65°	127.4	127.6	127.8	128.4	129.1	128.7	128.2	129.3	130.4	132.8	135.2
67.5°	112.6	112.1	111.7	111.9	112.1	112.8	113.4	113.7	113.9	116.5	119.1
70°	95.2	95.6	96.1	95.8	95.6	95.8	96.1	96.7	97.4	99.3	101.3
72.5°	79.5	79.8	80.0	80.0	80.0	80.4	80.8	81.5	82.1	83.2	84.3
75°	65.2	65.2	65.2	65.6	66.1	66.3	66.5	66.5	66.5	67.4	68.2
77.5°	49.5	50.6	51.7	51.5	51.3	51.7	52.2	52.8	53.5	53.9	54.3
80°	36.1	36.1	36.1	36.3	36.5	37.2	37.8	38.2	38.7	39.6	40.4
82.5°	23.0	23.3	23.5	24.1	24.8	25.2	25.6	26.3	26.9	26.9	26.9
85°	14.3	13.9	13.5	13.9	14.3	14.8	15.2	15.4	15.6	16.1	16.5
87.5°	7.0	7.0	7.0	7.0	7.0	7.2	7.4	7.4	7.4	7.4	7.4
90°	33.3	32.8	32.3	31.8	31.3	30.5	29.6	28.6	27.6	26.6	23.4
92.5°	37.7	37.4	37.2	36.9	36.7	35.7	34.0	32.3	30.5	28.8	26.6
95°	42.1	42.1	42.1	42.1	42.1	41.3	39.5	37.8	36.1	34.4	31.7
97.5°	45.4	45.2	45.0	44.7	44.5	43.3	41.4	39.4	37.4	35.5	48.0
100°	46.6	46.3	46.1	45.8	45.6	44.5	42.5	40.5	38.5	36.6	75.0
102.5°	47.7	47.2	46.7	46.2	45.7	49.5	57.6	65.8	73.9	82.0	124.9
105°	48.8	48.3	47.8	47.3	46.8	68.3	111.9	155.5	199.1	242.7	264.9
107.5°	115.3	147.5	179.8	212.1	244.3	279.4	317.4	355.3	393.2	431.2	427.5
110°	304.8	340.0	375.2	410.5	445.7	467.4	475.5	483.6	491.7	499.9	497.2



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	577.5	578.0	578.4	578.9	579.4	578.6	576.4	574.1	571.9	569.7	567.0
115°	651.7	650.7	649.7	648.8	647.8	646.1	643.6	641.1	638.7	636.2	634.0
117.5°	711.6	711.3	711.1	710.8	710.6	709.5	707.5	705.5	703.6	701.6	700.4
120°	773.6	773.6	773.6	773.6	773.6	772.7	770.7	768.7	766.7	764.8	764.0
122.5°	834.6	834.4	834.1	833.9	833.6	832.9	831.6	830.4	829.2	827.9	827.0
125°	891.1	890.6	890.1	889.6	889.2	888.7	888.2	887.7	887.2	886.7	885.7
127.5°	946.5	947.0	947.5	948.0	948.5	948.4	947.7	946.9	946.2	945.4	944.2
130°	999.7	1000.2	1000.7	1001.2	1001.7	1001.5	1000.5	999.5	998.5	997.5	996.5
132.5°	1048.5	1049.3	1050.0	1050.7	1051.5	1051.3	1050.4	1049.4	1048.4	1047.4	1046.7
135°	1098.4	1099.1	1099.9	1100.6	1101.3	1101.3	1100.6	1099.9	1099.1	1098.4	1097.4
137.5°	1146.1	1146.5	1147.0	1147.5	1148.0	1147.7	1146.4	1145.2	1144.0	1142.7	1142.2
140°	1188.2	1188.7	1189.2	1189.6	1190.1	1189.9	1188.9	1187.9	1186.9	1186.0	1185.2
142.5°	1227.0	1227.7	1228.4	1229.2	1229.9	1229.9	1229.2	1228.4	1227.7	1227.0	1226.2
145°	1266.9	1266.9	1266.9	1266.9	1266.9	1266.6	1266.1	1265.6	1265.1	1264.6	1264.2
147.5°	1295.7	1296.9	1298.1	1299.4	1300.6	1301.0	1300.5	1300.0	1299.5	1299.0	1298.5
150°	1328.9	1329.7	1330.4	1331.1	1331.9	1332.0	1331.5	1331.0	1330.5	1330.0	1329.5
152.5°	1355.5	1356.8	1358.0	1359.2	1360.5	1360.6	1359.6	1358.6	1357.6	1356.6	1356.4
155°	1379.9	1381.4	1382.9	1384.3	1385.8	1386.0	1384.7	1383.5	1382.3	1381.0	1380.8
157.5°	1401.0	1402.9	1404.9	1406.9	1408.9	1409.1	1407.6	1406.1	1404.7	1403.2	1403.4
160°	1420.9	1422.7	1424.4	1426.1	1427.8	1427.9	1426.5	1425.0	1423.5	1422.0	1422.3
162.5°	1439.8	1441.2	1442.7	1444.2	1445.7	1445.6	1443.8	1442.1	1440.4	1438.7	1438.9
165°	1454.2	1455.9	1457.6	1459.3	1461.1	1461.0	1459.0	1457.0	1455.0	1453.1	1453.3
167.5°	1465.3	1467.2	1469.2	1471.2	1473.1	1473.1	1471.2	1469.2	1467.2	1465.3	1465.3
170°	1475.2	1477.2	1479.2	1481.1	1483.1	1483.1	1481.1	1479.2	1477.2	1475.2	1475.2
172.5°	1480.8	1483.0	1485.2	1487.4	1489.6	1489.8	1487.8	1485.8	1483.9	1481.9	1481.6
175°	1486.3	1488.3	1490.3	1492.2	1494.2	1494.3	1492.6	1490.9	1489.2	1487.4	1487.2
177.5°	1487.4	1489.9	1492.4	1494.8	1497.3	1497.5	1495.6	1493.6	1491.6	1489.6	1489.4
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7
2.5°	1001.9	999.3	989.7	980.1	969.3	958.4	950.4	942.3	930.4	918.4	908.6
5°	1085.7	1073.6	1053.4	1033.2	1005.8	978.4	959.9	941.4	916.7	891.9	872.1
7.5°	1152.2	1131.4	1103.1	1074.9	1039.0	1003.2	969.3	935.4	897.5	859.7	828.9
10°	1194.6	1180.5	1147.9	1115.3	1067.3	1019.2	971.9	924.5	875.8	827.1	786.3
12.5°	1198.8	1200.1	1170.1	1140.1	1085.7	1031.4	973.8	916.2	854.9	793.7	746.1
15°	1162.5	1184.8	1168.3	1151.8	1097.0	1042.3	971.4	900.6	830.0	759.3	704.3
17.5°	1095.1	1143.1	1145.5	1147.9	1093.1	1038.4	959.9	881.5	801.5	721.5	663.7
20°	1003.2	1074.0	1098.3	1122.7	1078.1	1033.6	949.3	864.9	775.4	685.9	625.2
22.5°	909.3	995.3	1039.9	1084.4	1051.4	1018.4	928.6	838.9	744.3	649.8	588.3
25°	802.4	896.2	964.7	1033.2	1012.9	992.7	904.3	815.8	715.2	614.6	551.8
27.5°	709.1	804.5	887.1	969.7	965.3	961.0	873.2	785.4	682.4	579.4	518.7
30°	626.1	715.0	807.4	899.7	910.4	921.0	836.3	751.5	648.3	545.0	486.6
32.5°	552.7	630.2	729.3	828.4	849.3	870.2	793.7	717.2	615.0	512.9	456.6
35°	492.5	562.9	662.0	761.1	787.1	813.2	746.7	680.2	580.7	481.2	427.5
37.5°	439.2	498.1	594.8	691.5	723.5	755.4	695.9	636.3	543.1	449.9	400.5
40°	395.1	442.5	531.4	620.2	657.2	694.1	645.0	595.9	507.4	419.0	373.6
42.5°	358.1	400.3	480.9	561.6	597.0	632.4	590.9	549.4	470.7	392.1	350.5
45°	326.6	360.3	433.6	506.8	540.5	574.2	538.5	502.9	433.6	364.2	325.5
47.5°	297.1	326.0	388.6	451.2	481.2	511.1	483.3	455.5	396.8	338.2	303.2
50°	270.6	293.8	348.6	403.4	429.4	455.5	431.0	406.4	358.1	309.9	279.5
52.5°	247.5	266.4	312.3	358.1	380.5	402.9	381.8	360.8	322.5	284.3	257.7
55°	224.7	240.8	280.6	320.3	335.5	350.8	334.5	318.2	287.3	256.4	234.1
57.5°	203.4	217.8	250.4	283.0	294.7	306.4	291.6	276.9	253.6	230.4	211.7
60°	182.6	194.3	221.5	248.6	255.8	263.0	251.0	239.1	222.8	206.5	189.7
62.5°	163.2	173.9	194.1	214.3	219.1	223.8	214.7	205.6	193.2	180.8	167.8
65°	143.2	151.3	167.8	184.3	187.3	190.4	182.3	174.3	164.9	155.6	146.0
67.5°	124.7	130.4	143.9	157.3	157.6	157.8	151.3	144.7	139.5	134.3	126.7
70°	106.7	112.1	121.0	130.0	130.2	130.4	125.2	120.0	116.1	112.1	106.5
72.5°	88.2	92.1	98.9	105.6	105.2	104.7	101.5	98.2	95.2	92.1	88.0
75°	71.5	74.8	79.3	83.9	82.6	81.3	79.5	77.8	75.2	72.6	70.0
77.5°	56.3	58.2	60.9	63.5	62.6	61.7	60.2	58.7	56.7	54.8	53.7
80°	41.3	42.2	43.9	45.6	45.2	44.8	43.0	41.3	40.9	40.4	38.9
82.5°	28.0	29.1	29.6	30.0	29.8	29.6	28.3	26.9	26.5	26.1	25.9
85°	16.7	17.0	17.2	17.4	16.7	16.1	15.6	15.2	15.2	15.2	15.0
87.5°	7.6	7.8	7.8	7.8	7.6	7.4	7.0	6.5	6.7	7.0	7.0
90°	20.2	17.0	13.8	11.0	8.5	6.0	3.6	1.1	3.6	6.0	8.5
92.5°	24.4	22.2	20.0	19.6	21.1	22.5	24.0	25.5	24.0	22.5	21.1
95°	28.9	26.2	23.5	27.2	37.3	47.4	57.5	67.6	57.5	47.4	37.3
97.5°	60.6	73.2	85.7	95.4	102.3	109.2	116.1	123.0	116.1	109.2	102.3
100°	113.4	151.8	190.3	207.0	202.1	197.2	192.2	187.3	192.2	197.2	202.1
102.5°	167.7	210.6	253.4	273.3	270.1	266.9	263.7	260.5	263.7	266.9	270.1
105°	287.1	309.2	331.4	341.1	338.4	335.7	333.0	330.3	333.0	335.7	338.4
107.5°	423.8	420.1	416.4	413.4	411.2	409.0	406.8	404.6	406.8	409.0	411.2
110°	494.5	491.7	489.0	486.7	484.7	482.8	480.8	478.8	480.8	482.8	484.7



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.3	561.6	558.9	556.6	554.9	553.2	551.5	549.7	551.5	553.2	554.9
115°	631.8	629.6	627.3	625.5	624.0	622.5	621.1	619.6	621.1	622.5	624.0
117.5°	699.1	697.9	696.7	695.2	693.5	691.7	690.0	688.3	690.0	691.7	693.5
120°	763.3	762.6	761.8	760.3	758.1	755.9	753.7	751.5	753.7	755.9	758.1
122.5°	826.0	825.0	824.0	822.7	820.9	819.2	817.5	815.8	817.5	819.2	820.9
125°	884.7	883.7	882.8	881.3	879.3	877.3	875.4	873.4	875.4	877.3	879.3
127.5°	943.0	941.7	940.5	938.9	936.9	935.0	933.0	931.0	933.0	935.0	936.9
130°	995.6	994.6	993.6	992.1	990.1	988.2	986.2	984.2	986.2	988.2	990.1
132.5°	1045.9	1045.2	1044.5	1043.1	1041.1	1039.2	1037.2	1035.2	1037.2	1039.2	1041.1
135°	1096.4	1095.4	1094.5	1093.2	1091.7	1090.3	1088.8	1087.3	1088.8	1090.3	1091.7
137.5°	1141.7	1141.2	1140.8	1139.5	1137.6	1135.6	1133.6	1131.6	1133.6	1135.6	1137.6
140°	1184.5	1183.7	1183.0	1181.9	1180.4	1178.9	1177.5	1176.0	1177.5	1178.9	1180.4
142.5°	1225.5	1224.7	1224.0	1222.9	1221.4	1219.9	1218.5	1217.0	1218.5	1219.9	1221.4
145°	1263.7	1263.2	1262.7	1261.6	1259.8	1258.1	1256.4	1254.7	1256.4	1258.1	1259.8
147.5°	1298.0	1297.5	1297.0	1296.2	1294.9	1293.7	1292.5	1291.2	1292.5	1293.7	1294.9
150°	1329.1	1328.6	1328.1	1327.5	1326.7	1326.0	1325.2	1324.5	1325.2	1326.0	1326.7
152.5°	1356.1	1355.9	1355.7	1355.4	1355.2	1354.9	1354.7	1354.4	1354.7	1354.9	1355.2
155°	1380.5	1380.3	1380.0	1380.2	1380.7	1381.1	1381.6	1382.1	1381.6	1381.1	1380.7
157.5°	1403.7	1403.9	1404.2	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3
160°	1422.5	1422.8	1423.0	1423.3	1423.5	1423.8	1424.0	1424.3	1424.0	1423.8	1423.5
162.5°	1439.2	1439.4	1439.6	1440.1	1440.9	1441.6	1442.4	1443.1	1442.4	1441.6	1440.9
165°	1453.6	1453.8	1454.1	1454.5	1455.3	1456.0	1456.8	1457.5	1456.8	1456.0	1455.3
167.5°	1465.3	1465.3	1465.3	1465.8	1466.7	1467.7	1468.7	1469.7	1468.7	1467.7	1466.7
170°	1475.2	1475.2	1475.2	1475.7	1476.7	1477.7	1478.7	1479.7	1478.7	1477.7	1476.7
172.5°	1481.4	1481.1	1480.9	1481.4	1482.6	1483.9	1485.1	1486.3	1485.1	1483.9	1482.6
175°	1486.9	1486.7	1486.4	1486.9	1488.2	1489.4	1490.6	1491.9	1490.6	1489.4	1488.2
177.5°	1489.2	1488.9	1488.7	1489.2	1490.4	1491.6	1492.8	1494.1	1492.8	1491.6	1490.4
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7
2.5°	898.8	890.4	881.9	875.4	868.9	857.8	846.7	844.1	841.5	837.8	834.1
5°	852.3	831.5	810.6	791.9	773.2	758.7	744.1	734.6	725.0	718.0	711.1
7.5°	798.0	766.7	735.4	713.3	691.1	670.0	648.9	642.2	635.5	626.3	617.2
10°	745.4	710.9	676.3	647.4	618.5	597.9	577.2	569.0	560.7	549.2	537.7
12.5°	698.5	660.7	622.8	593.7	564.6	544.6	524.6	512.7	500.7	494.2	487.7
15°	649.4	608.9	568.5	541.6	514.6	496.6	478.5	468.1	457.7	451.4	445.1
17.5°	605.9	565.9	525.9	500.1	474.2	457.7	441.2	432.0	422.9	418.1	413.3
20°	564.6	525.5	486.4	461.2	435.9	422.5	409.0	403.1	397.3	393.4	389.4
22.5°	526.8	488.3	449.9	428.3	406.8	396.0	385.1	381.0	376.8	373.6	370.3
25°	489.0	454.6	420.3	402.0	383.8	374.9	366.0	361.8	357.7	354.5	351.2
27.5°	458.1	425.3	392.5	376.8	361.2	354.2	347.3	344.0	340.8	337.7	334.7
30°	428.1	398.8	369.4	356.0	342.5	336.2	329.9	326.6	323.4	320.6	317.7
32.5°	400.3	375.1	349.9	337.5	325.1	319.9	314.7	310.8	306.9	304.7	302.5
35°	373.8	351.2	328.6	318.4	308.2	302.9	297.7	294.5	291.2	289.5	287.7
37.5°	351.2	331.0	310.8	301.0	291.2	286.2	281.2	278.4	275.6	274.9	274.3
40°	328.2	310.8	293.4	283.8	274.3	269.9	265.6	263.8	262.1	261.7	261.2
42.5°	309.0	292.1	275.1	266.4	257.7	254.1	250.4	249.5	248.6	249.3	249.9
45°	286.9	272.7	258.6	250.6	242.5	239.5	236.4	235.8	235.1	236.4	237.8
47.5°	268.2	255.1	242.1	234.5	226.9	224.7	222.5	222.3	222.1	223.8	225.6
50°	249.1	236.4	223.8	217.8	211.7	209.7	207.8	208.4	209.1	211.9	214.7
52.5°	231.2	219.5	207.8	202.1	196.5	195.2	193.9	195.4	196.9	199.9	203.0
55°	211.7	201.0	190.4	186.0	181.7	180.4	179.1	182.1	185.2	188.0	190.8
57.5°	193.0	183.6	174.3	170.4	166.5	166.3	166.0	168.9	171.7	174.7	177.8
60°	173.0	165.2	157.3	154.3	151.3	151.7	152.1	155.4	158.6	161.0	163.4
62.5°	154.7	148.2	141.7	138.9	136.0	137.1	138.2	141.5	144.7	147.6	150.4
65°	136.5	131.0	125.6	123.7	121.7	123.2	124.7	127.6	130.4	132.3	134.3
67.5°	119.1	114.5	110.0	108.4	106.9	108.4	110.0	112.8	115.6	117.6	119.5
70°	100.8	97.1	93.4	92.4	91.3	93.0	94.8	97.1	99.5	101.5	103.4
72.5°	83.9	81.1	78.2	78.0	77.8	79.3	80.8	83.2	85.6	86.9	88.2
75°	67.4	65.8	64.3	64.1	63.9	65.4	66.9	68.2	69.5	70.6	71.7
77.5°	52.6	51.3	50.0	50.2	50.4	51.5	52.6	53.9	55.2	55.9	56.5
80°	37.4	36.9	36.5	36.9	37.4	38.2	39.1	40.0	40.9	41.3	41.7
82.5°	25.6	25.2	24.8	25.4	26.1	26.7	27.4	28.0	28.7	28.9	29.1
85°	14.8	15.4	16.1	16.1	16.1	16.3	16.5	16.7	17.0	16.7	16.5
87.5°	7.0	7.2	7.4	7.4	7.4	7.6	7.8	7.8	7.8	7.6	7.4
90°	11.0	13.8	17.0	20.2	23.4	26.6	27.6	28.6	29.6	30.5	31.3
92.5°	19.6	20.0	22.2	24.4	26.6	28.8	30.5	32.3	34.0	35.7	36.7
95°	27.2	23.5	26.2	28.9	31.7	34.4	36.1	37.8	39.5	41.3	42.1
97.5°	95.4	85.7	73.2	60.6	48.0	35.5	37.4	39.4	41.4	43.3	44.5
100°	207.0	190.3	151.8	113.4	75.0	36.6	38.5	40.5	42.5	44.5	45.6
102.5°	273.3	253.4	210.6	167.7	124.9	82.0	73.9	65.8	57.6	49.5	45.7
105°	341.1	331.4	309.2	287.1	264.9	242.7	199.1	155.5	111.9	68.3	46.8
107.5°	413.4	416.4	420.1	423.8	427.5	431.2	393.2	355.3	317.4	279.4	244.3
110°	486.7	489.0	491.7	494.5	497.2	499.9	491.7	483.6	475.5	467.4	445.7



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	556.6	558.9	561.6	564.3	567.0	569.7	571.9	574.1	576.4	578.6	579.4
115°	625.5	627.3	629.6	631.8	634.0	636.2	638.7	641.1	643.6	646.1	647.8
117.5°	695.2	696.7	697.9	699.1	700.4	701.6	703.6	705.5	707.5	709.5	710.6
120°	760.3	761.8	762.6	763.3	764.0	764.8	766.7	768.7	770.7	772.7	773.6
122.5°	822.7	824.0	825.0	826.0	827.0	827.9	829.2	830.4	831.6	832.9	833.6
125°	881.3	882.8	883.7	884.7	885.7	886.7	887.2	887.7	888.2	888.7	889.2
127.5°	938.9	940.5	941.7	943.0	944.2	945.4	946.2	946.9	947.7	948.4	948.5
130°	992.1	993.6	994.6	995.6	996.5	997.5	998.5	999.5	1000.5	1001.5	1001.7
132.5°	1043.1	1044.5	1045.2	1045.9	1046.7	1047.4	1048.4	1049.4	1050.4	1051.3	1051.5
135°	1093.2	1094.5	1095.4	1096.4	1097.4	1098.4	1099.1	1099.9	1100.6	1101.3	1101.3
137.5°	1139.5	1140.8	1141.2	1141.7	1142.2	1142.7	1144.0	1145.2	1146.4	1147.7	1148.0
140°	1181.9	1183.0	1183.7	1184.5	1185.2	1186.0	1186.9	1187.9	1188.9	1189.9	1190.1
142.5°	1222.9	1224.0	1224.7	1225.5	1226.2	1227.0	1227.7	1228.4	1229.2	1229.9	1229.9
145°	1261.6	1262.7	1263.2	1263.7	1264.2	1264.6	1265.1	1265.6	1266.1	1266.6	1266.9
147.5°	1296.2	1297.0	1297.5	1298.0	1298.5	1299.0	1299.5	1300.0	1300.5	1301.0	1300.6
150°	1327.5	1328.1	1328.6	1329.1	1329.5	1330.0	1330.5	1331.0	1331.5	1332.0	1331.9
152.5°	1355.4	1355.7	1355.9	1356.1	1356.4	1356.6	1357.6	1358.6	1359.6	1360.6	1360.5
155°	1380.2	1380.0	1380.3	1380.5	1380.8	1381.0	1382.3	1383.5	1384.7	1386.0	1385.8
157.5°	1404.3	1404.2	1403.9	1403.7	1403.4	1403.2	1404.7	1406.1	1407.6	1409.1	1408.9
160°	1423.3	1423.0	1422.8	1422.5	1422.3	1422.0	1423.5	1425.0	1426.5	1427.9	1427.8
162.5°	1440.1	1439.6	1439.4	1439.2	1438.9	1438.7	1440.4	1442.1	1443.8	1445.6	1445.7
165°	1454.5	1454.1	1453.8	1453.6	1453.3	1453.1	1455.0	1457.0	1459.0	1461.0	1461.1
167.5°	1465.8	1465.3	1465.3	1465.3	1465.3	1465.3	1467.2	1469.2	1471.2	1473.1	1473.1
170°	1475.7	1475.2	1475.2	1475.2	1475.2	1475.2	1477.2	1479.2	1481.1	1483.1	1483.1
172.5°	1481.4	1480.9	1481.1	1481.4	1481.6	1481.9	1483.9	1485.8	1487.8	1489.8	1489.6
175°	1486.9	1486.4	1486.7	1486.9	1487.2	1487.4	1489.2	1490.9	1492.6	1494.3	1494.2
177.5°	1489.2	1488.7	1488.9	1489.2	1489.4	1489.6	1491.6	1493.6	1495.6	1497.5	1497.3
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9

TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	936.7	936.7	936.7	936.7
2.5°	832.6	831.0	825.0	818.9
5°	705.9	700.6	698.9	697.2
7.5°	616.8	616.3	607.2	598.1
10°	538.3	539.0	530.7	522.4
12.5°	482.2	476.8	476.2	475.5
15°	440.1	435.1	434.2	433.3
17.5°	410.3	407.3	406.4	405.5
20°	387.7	386.0	384.4	382.9
22.5°	368.1	366.0	364.7	363.4
25°	349.2	347.3	346.8	346.4
27.5°	332.3	329.9	329.9	329.9
30°	316.2	314.7	314.0	313.4
32.5°	301.2	299.9	299.9	299.9
35°	287.1	286.4	285.6	284.7
37.5°	274.3	274.3	273.8	273.4
40°	261.9	262.5	262.5	262.5
42.5°	250.6	251.2	251.2	251.2
45°	238.8	239.9	240.4	240.8
47.5°	227.3	229.1	229.5	229.9
50°	216.0	217.3	217.5	217.8
52.5°	204.5	206.0	207.1	208.2
55°	192.3	193.9	194.5	195.2
57.5°	179.3	180.8	181.0	181.2
60°	164.9	166.5	166.9	167.3
62.5°	151.3	152.1	152.6	153.0
65°	135.6	136.9	137.8	138.7
67.5°	120.6	121.7	121.7	121.7
70°	103.9	104.3	105.0	105.6
72.5°	88.5	88.7	88.7	88.7
75°	72.2	72.6	72.8	73.0
77.5°	56.7	56.9	56.9	56.9
80°	41.5	41.3	41.3	41.3
82.5°	28.5	27.8	27.8	27.8
85°	16.3	16.1	16.3	16.5
87.5°	7.4	7.4	7.4	7.4
90°	31.8	32.3	32.8	33.3
92.5°	36.9	37.2	37.4	37.7
95°	42.1	42.1	42.1	42.1
97.5°	44.7	45.0	45.2	45.4
100°	45.8	46.1	46.3	46.6
102.5°	46.2	46.7	47.2	47.7
105°	47.3	47.8	48.3	48.8
107.5°	212.1	179.8	147.5	115.3
110°	410.5	375.2	340.0	304.8



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	578.9	578.4	578.0	577.5
115°	648.8	649.7	650.7	651.7
117.5°	710.8	711.1	711.3	711.6
120°	773.6	773.6	773.6	773.6
122.5°	833.9	834.1	834.4	834.6
125°	889.6	890.1	890.6	891.1
127.5°	948.0	947.5	947.0	946.5
130°	1001.2	1000.7	1000.2	999.7
132.5°	1050.7	1050.0	1049.3	1048.5
135°	1100.6	1099.9	1099.1	1098.4
137.5°	1147.5	1147.0	1146.5	1146.1
140°	1189.6	1189.2	1188.7	1188.2
142.5°	1229.2	1228.4	1227.7	1227.0
145°	1266.9	1266.9	1266.9	1266.9
147.5°	1299.4	1298.1	1296.9	1295.7
150°	1331.1	1330.4	1329.7	1328.9
152.5°	1359.2	1358.0	1356.8	1355.5
155°	1384.3	1382.9	1381.4	1379.9
157.5°	1406.9	1404.9	1402.9	1401.0
160°	1426.1	1424.4	1422.7	1420.9
162.5°	1444.2	1442.7	1441.2	1439.8
165°	1459.3	1457.6	1455.9	1454.2
167.5°	1471.2	1469.2	1467.2	1465.3
170°	1481.1	1479.2	1477.2	1475.2
172.5°	1487.4	1485.2	1483.0	1480.8
175°	1492.2	1490.3	1488.3	1486.3
177.5°	1494.8	1492.4	1489.9	1487.4
180°	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P831366

CATALOG NUMBER: S123DIP-S340D1195U950-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.61	9.26	9.76	10.40	11.99	10.84	11.50	11.99	12.64	14.23
	3H	10.24	10.83	11.40	11.97	13.58	12.25	12.84	13.41	13.99	15.59
	4H	10.81	11.37	11.97	12.51	14.12	12.69	13.25	13.86	14.40	16.01
	6H	11.17	11.68	12.34	12.83	14.45	12.96	13.47	14.13	14.62	16.24
	8H	11.26	11.75	12.43	12.91	14.52	13.02	13.51	14.19	14.67	16.28
	12H	11.30	11.76	12.48	12.91	14.55	13.03	13.49	14.21	14.65	16.28
4H	2H	9.16	9.72	10.33	10.86	12.47	10.98	11.54	12.16	12.69	14.30
	3H	10.97	11.43	12.15	12.60	14.23	12.58	13.05	13.76	14.22	15.84
	4H	11.66	12.09	12.84	13.25	14.89	13.16	13.59	14.34	14.75	16.39
	6H	12.12	12.49	13.31	13.67	15.30	13.55	13.92	14.74	15.10	16.73
	8H	12.26	12.60	13.44	13.77	15.42	13.66	14.00	14.84	15.18	16.82
	12H	12.31	12.62	13.51	13.81	15.46	13.70	14.01	14.90	15.19	16.84
8H	4H	11.91	12.25	13.09	13.42	15.07	13.25	13.59	14.43	14.76	16.41
	6H	12.49	12.77	13.69	13.99	15.63	13.75	14.03	14.95	15.24	16.89
	8H	12.70	12.94	13.91	14.13	15.80	13.92	14.17	15.13	15.36	17.03
	12H	12.81	13.03	14.02	14.22	15.91	14.02	14.23	15.23	15.42	17.12
12H	4H	11.90	12.21	13.10	13.39	15.05	13.22	13.53	14.42	14.71	16.36
	6H	12.54	12.79	13.75	13.98	15.64	13.76	14.00	14.97	15.20	16.86
	8H	12.77	12.98	13.98	14.17	15.87	13.95	14.16	15.16	15.35	17.05