

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331930-840

Luminaire Tested: **S123DIP-S560D805U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331930-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5346.8 lumens
Efficiency: N/A
Efficacy: 139.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	32	53	42	35	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8593	8593	8593	8593
5°	10247	8630	7648	8630
10°	12826	8587	6908	8587
15°	15731	8517	6430	8517
20°	18741	8409	6123	8409
25°	19899	8278	6055	8278
30°	17056	8182	6087	8182
35°	11862	8046	6150	8046
40°	8934	7886	6131	7886
45°	7419	7648	6052	7648
50°	6646	7164	5998	7164
55°	6212	6641	5923	6641
60°	5828	6097	5862	6097
65°	5476	5555	5675	5555
70°	5136	4941	5404	4941
75°	4600	4325	4957	4325
80°	4023	3552	4271	3552
85°	3149	2581	2865	2581



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	1.5
10°-20°	252.2	4.7
20°-30°	423.2	7.9
30°-40°	479.2	9.0
40°-50°	429.7	8.0
50°-60°	346.8	6.5
60°-70°	241.7	4.5
70°-80°	127.0	2.4
80°-90°	34.1	0.6
90°-100°	217.1	4.1
100°-110°	614.6	11.5
110°-120°	604.6	11.3
120°-130°	482.3	9.0
130°-140°	380.2	7.1
140°-150°	283.8	5.3
150°-160°	197.8	3.7
160°-170°	116.2	2.2
170°-180°	37.8	0.7
0°-30°	754.0	14.1
0°-40°	1233.2	23.1
0°-60°	2009.7	37.6
0°-90°	2412.5	45.1
90°-120°	1436.3	26.9
90°-150°	2582.6	48.3
90°-180°	2934.0	54.9
0°-180°	5346.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	948	799	708	799	948	98
15°	1412	764	577	764	1412	408
25°	1676	697	510	697	1676	735
35°	903	612	468	612	903	586
45°	487	502	398	502	487	386
55°	331	354	316	354	331	297
65°	215	218	223	218	215	214
75°	111	104	119	104	111	118
85°	26	21	23	21	26	31
90°	23	2	23	2	23	13
95°	92	27	92	27	92	165
105°	1004	92	1004	92	1004	991
115°	1221	162	1221	162	1221	1187
125°	963	225	963	225	963	873
135°	781	264	781	264	781	606
145°	610	301	610	301	610	388
155°	506	342	506	342	506	236
165°	441	373	441	373	441	126
175°	397	389	397	389	397	39
180°	390	390	390	390	390	



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	847.2	846.6	845.1	846.3	843.7	840.4	840.1	837.0	828.0	827.4	825.0
5°	948.4	945.2	944.9	944.5	939.1	931.7	917.8	916.7	898.1	888.8	877.6
7.5°	1079.4	1081.1	1075.4	1070.5	1053.9	1043.0	1028.0	1009.0	986.1	963.0	947.6
10°	1173.5	1186.2	1170.3	1159.5	1149.5	1130.5	1108.5	1081.1	1053.6	1021.5	997.1
12.5°	1274.3	1280.6	1277.5	1267.2	1251.6	1222.7	1183.7	1153.5	1128.1	1074.7	1053.1
15°	1411.7	1435.3	1420.3	1385.4	1386.2	1358.8	1307.7	1251.6	1221.8	1175.0	1111.2
17.5°	1558.1	1561.0	1554.6	1525.6	1506.2	1468.5	1421.4	1367.7	1307.3	1250.7	1183.0
20°	1636.1	1633.8	1620.2	1605.1	1571.9	1542.5	1491.0	1431.1	1353.7	1298.0	1224.2
22.5°	1679.4	1675.5	1669.1	1656.5	1628.8	1597.2	1551.1	1485.5	1411.9	1335.1	1249.8
25°	1675.5	1680.5	1681.3	1677.8	1668.2	1649.2	1612.9	1560.6	1487.1	1388.6	1299.6
27.5°	1523.9	1531.0	1551.7	1570.0	1590.5	1611.3	1608.6	1582.7	1528.3	1443.1	1334.3
30°	1372.3	1356.8	1395.1	1443.4	1476.3	1534.3	1566.8	1568.7	1538.2	1465.1	1359.1
32.5°	1161.8	1178.9	1195.8	1255.3	1327.2	1392.3	1456.9	1509.0	1515.0	1466.3	1373.6
35°	902.7	924.0	954.9	985.9	1063.3	1129.7	1243.4	1342.5	1421.4	1431.8	1374.9
37.5°	727.4	738.0	757.5	788.5	839.1	918.1	1006.0	1131.1	1245.5	1330.5	1334.2
40°	635.8	638.9	661.0	684.6	725.6	790.5	869.9	980.5	1117.4	1236.2	1285.7
42.5°	567.1	574.0	583.3	606.0	638.6	687.5	761.2	852.7	978.2	1114.8	1211.6
45°	487.4	495.0	500.9	515.9	539.2	572.0	623.5	707.0	802.5	943.7	1074.1
47.5°	434.5	435.2	439.5	450.9	466.7	491.4	527.8	581.4	669.1	783.6	917.5
50°	396.9	403.0	404.6	413.4	425.9	444.0	474.2	519.8	591.8	692.4	815.4
52.5°	370.2	372.0	376.4	382.8	393.6	407.8	433.9	469.7	526.1	611.9	725.0
55°	331.0	331.0	335.4	340.3	346.6	359.3	376.7	403.0	446.0	512.5	606.1
57.5°	294.9	296.8	299.8	301.3	306.6	315.1	329.6	349.6	381.6	432.8	507.3
60°	270.7	274.2	273.9	276.9	281.6	288.1	300.5	316.8	345.4	386.4	449.1
62.5°	249.7	249.4	249.4	253.1	257.7	264.0	272.1	286.1	310.4	346.8	400.1
65°	215.0	214.3	217.0	219.3	220.9	225.5	231.7	244.1	260.3	287.4	328.7
67.5°	184.3	182.0	183.5	184.3	186.9	190.6	196.3	204.0	216.9	238.6	269.8
70°	163.2	161.3	160.9	161.7	164.0	166.7	171.0	178.3	190.3	207.7	230.6
72.5°	141.6	140.3	140.2	141.9	143.0	144.7	147.7	154.5	164.0	177.0	198.3
75°	110.6	110.6	110.6	111.0	112.2	113.7	116.0	119.5	126.8	136.1	150.5
77.5°	82.9	82.8	82.4	82.3	84.0	84.7	85.2	88.5	92.6	98.9	109.3
80°	64.9	63.0	63.8	64.9	65.7	66.1	67.3	68.1	71.6	75.0	82.4
82.5°	48.3	46.7	46.8	48.6	48.8	49.1	50.3	51.4	52.7	55.8	59.8
85°	25.5	25.5	26.0	26.0	26.3	26.0	27.1	27.5	27.5	29.4	31.7
87.5°	13.8	13.4	13.5	13.7	13.5	13.5	13.7	13.8	14.0	14.4	14.3
90°	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7	19.0	19.7	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4	91.6	121.4	133.6
95°	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3	379.8	468.2	416.9
97.5°	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5	776.3	725.6	531.2
100°	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9	903.2	747.7	505.3
102.5°	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7	909.6	706.6	467.4
105°	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4	861.4	634.8	420.8
107.5°	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2	777.1	571.3	391.1
110°	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8	724.0	535.3	379.8



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1	677.9	511.3	373.4
115°	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2	622.2	485.5	371.1
117.5°	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9	588.5	470.4	372.5
120°	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2	570.9	463.4	375.1
122.5°	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8	556.3	459.1	379.4
125°	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6	537.7	453.2	386.1
127.5°	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6	521.3	450.4	393.6
130°	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5	512.4	448.5	398.7
132.5°	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6	504.2	447.8	402.5
135°	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3	493.4	446.9	408.2
137.5°	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9	484.1	445.1	412.0
140°	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5	478.5	444.5	414.5
142.5°	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8	473.4	443.2	416.4
145°	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9	466.7	441.3	417.7
147.5°	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3	460.0	438.4	417.7
150°	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7	455.6	435.9	417.7
152.5°	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8	450.5	432.6	415.8
155°	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4	442.9	427.2	413.7
157.5°	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2	434.4	422.2	411.0
160°	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0	428.7	418.5	409.8
162.5°	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4	423.0	414.7	407.3
165°	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6	415.3	409.0	403.4
167.5°	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0	407.9	403.3	399.7
170°	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4	403.4	399.5	397.2
172.5°	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3	399.0	396.4	395.3
175°	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6	393.9	392.4	392.4
177.5°	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	823.0	820.6	818.1	813.7	810.0	804.8	803.2	801.4	795.9	790.8	787.2
5°	873.3	864.0	850.5	838.1	828.1	814.6	806.8	798.7	787.1	776.7	768.1
7.5°	925.9	907.7	886.7	863.9	842.7	822.2	805.8	791.1	774.9	759.4	747.5
10°	967.8	941.4	912.0	880.3	853.2	826.9	804.9	785.6	764.7	746.5	731.3
12.5°	1015.3	976.3	935.8	897.3	865.3	828.8	802.1	777.5	753.9	732.0	715.0
15°	1071.8	1022.3	974.3	921.3	872.5	826.9	795.2	764.3	736.8	714.4	692.7
17.5°	1123.1	1067.0	1003.8	939.4	880.6	826.5	782.0	747.1	712.8	685.3	663.7
20°	1152.2	1088.3	1016.8	949.9	884.9	824.6	775.9	734.1	697.0	667.9	643.6
22.5°	1177.3	1102.6	1028.5	957.0	884.6	819.6	764.5	721.4	681.2	652.8	626.9
25°	1203.3	1113.9	1039.7	955.7	874.8	807.6	745.7	697.0	656.7	623.5	596.8
27.5°	1225.6	1113.2	1025.0	934.7	859.6	792.1	726.1	673.8	631.1	594.9	567.8
30°	1240.4	1114.7	1009.9	920.5	844.8	775.1	710.8	658.3	613.4	576.6	551.2
32.5°	1249.7	1113.8	995.9	900.7	821.2	759.6	694.5	640.1	593.9	557.8	533.2
35°	1255.1	1106.9	972.0	859.8	783.3	723.3	668.7	612.3	563.9	530.3	502.4
37.5°	1244.3	1092.7	944.1	820.3	736.5	677.5	631.6	583.5	537.2	500.2	476.2
40°	1227.2	1083.4	922.4	792.5	704.3	647.4	608.4	561.2	515.5	480.4	458.0
42.5°	1194.8	1064.5	898.7	761.5	670.9	614.0	578.0	538.7	495.4	462.4	440.0
45°	1115.5	1023.4	862.9	715.2	621.6	562.8	531.1	502.4	463.3	431.2	411.9
47.5°	1005.4	961.6	811.2	666.2	570.1	513.5	480.5	457.5	428.9	403.0	384.5
50°	929.1	910.9	776.3	632.8	535.6	480.4	448.7	427.8	407.3	381.3	364.4
52.5°	840.8	852.0	735.4	598.1	500.7	446.4	416.5	399.9	381.3	360.0	345.2
55°	716.7	757.3	664.9	540.0	448.7	396.9	368.6	353.9	343.1	327.2	314.5
57.5°	600.5	652.1	588.5	480.0	397.5	352.8	325.8	309.7	302.8	294.5	284.5
60°	531.4	582.5	534.1	439.8	363.1	320.6	296.7	283.2	276.2	270.3	261.9
62.5°	469.9	521.5	480.9	398.9	329.4	290.0	269.1	255.9	250.4	247.4	240.1
65°	385.3	429.7	402.6	335.4	281.1	246.4	227.4	218.1	213.1	212.0	207.3
67.5°	313.6	347.4	327.7	278.1	235.5	205.4	189.3	181.5	177.6	177.2	173.7
70°	266.5	298.2	283.2	238.2	201.5	177.9	164.0	157.0	154.7	154.3	152.4
72.5°	229.9	252.1	240.1	202.7	174.3	152.9	142.6	135.3	132.7	133.3	132.0
75°	170.2	186.8	179.9	153.9	131.1	117.1	108.7	104.0	101.7	102.9	101.3
77.5°	122.5	133.0	126.7	108.8	94.7	84.6	78.4	75.5	73.4	73.3	72.6
80°	92.4	98.7	95.1	84.3	72.7	64.2	59.2	57.3	56.0	55.7	55.3
82.5°	65.8	71.1	67.0	59.6	51.7	46.6	43.7	41.2	40.3	40.5	40.2
85°	33.2	35.2	33.6	29.0	26.0	23.6	22.0	20.9	20.1	20.5	19.7
87.5°	14.4	14.2	12.9	11.3	10.4	9.0	8.7	7.8	7.5	7.8	7.9
90°	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6	3.1	4.7	7.1
92.5°	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8	14.5	21.2	27.4
95°	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9	29.2	37.9	51.3
97.5°	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7	46.6	53.4	65.0
100°	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5	59.2	64.7	75.8
102.5°	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7	73.1	78.0	88.5
105°	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6	93.9	98.7	108.2
107.5°	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7	115.1	119.7	129.0
110°	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9	130.3	134.2	142.9



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8	144.2	148.1	156.8
115°	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9	165.0	169.8	177.6
117.5°	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9	185.5	189.5	196.7
120°	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8	198.1	202.1	210.1
122.5°	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8	210.2	214.1	222.7
125°	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0	226.6	231.4	240.0
127.5°	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1	240.4	246.3	255.2
130°	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3	248.7	255.8	265.3
132.5°	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7	255.7	263.4	274.8
135°	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7	266.9	275.6	287.4
137.5°	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1	277.4	286.0	298.6
140°	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0	285.0	293.0	305.6
142.5°	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6	292.0	300.5	311.8
145°	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8	303.2	310.3	322.1
147.5°	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2	314.6	321.5	331.7
150°	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3	322.1	328.4	338.7
152.5°	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5	329.7	336.0	345.1
155°	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8	341.8	346.6	354.5
157.5°	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6	352.2	356.1	363.0
160°	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2	359.2	362.4	368.7
162.5°	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0	365.0	367.5	372.5
165°	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4	372.6	374.3	378.2
167.5°	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9	379.0	379.8	382.7
170°	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7	382.1	382.9	385.3
172.5°	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3	385.3	385.5	387.2
175°	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2	388.5	387.7	389.2
177.5°	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6	390.0	389.4	390.0
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	785.0	782.8	779.7	775.1	771.3	765.5	765.5	766.4	766.4	766.1	765.5
5°	761.1	755.4	748.4	740.3	731.7	723.3	721.8	718.6	716.3	714.8	712.9
7.5°	736.0	725.8	715.6	704.3	693.9	685.3	679.3	674.4	671.2	667.8	665.3
10°	719.0	706.2	694.3	682.3	669.1	658.6	652.1	647.4	644.0	640.9	639.3
12.5°	698.9	684.3	671.1	659.6	645.3	634.5	628.2	626.1	622.0	615.5	612.1
15°	669.5	656.0	640.2	622.7	615.7	602.6	595.2	591.8	589.5	584.4	582.9
17.5°	644.4	626.6	608.8	595.8	582.9	572.3	568.2	563.8	560.8	556.6	555.4
20°	624.3	608.4	592.2	578.2	564.7	553.1	549.6	546.5	543.4	541.5	540.0
22.5°	603.8	587.9	574.5	561.5	547.0	539.5	535.6	532.3	530.1	528.8	527.3
25°	575.1	561.2	546.1	534.5	522.9	517.9	515.5	513.6	512.1	510.2	509.8
27.5°	549.5	534.3	522.1	511.2	502.9	498.7	496.4	495.5	495.8	496.6	497.0
30°	530.3	516.3	506.2	497.0	489.3	485.4	485.0	485.0	486.6	487.0	487.8
32.5°	512.6	501.2	491.1	482.1	476.3	473.6	475.1	475.1	476.4	477.4	478.8
35°	487.0	476.9	469.2	461.4	456.4	457.6	458.3	459.1	461.0	463.3	464.9
37.5°	462.4	453.7	445.7	439.6	437.3	439.4	441.2	442.8	445.1	446.9	448.4
40°	444.7	438.2	430.5	425.1	425.9	427.0	428.6	430.5	432.4	433.5	435.2
42.5°	428.4	421.5	415.7	411.1	412.2	413.7	414.7	415.7	417.9	420.0	420.9
45°	403.4	398.0	392.5	389.9	390.6	391.4	392.2	393.3	395.3	396.9	397.2
47.5°	375.4	371.5	367.9	365.3	366.5	366.2	367.2	369.7	370.3	371.2	373.3
50°	357.4	353.9	349.6	348.9	348.9	348.9	349.2	352.3	352.3	353.9	355.5
52.5°	337.6	335.4	332.6	331.2	330.6	330.6	332.2	333.8	334.4	336.6	338.1
55°	308.2	305.9	303.7	302.5	301.6	302.5	305.6	306.3	308.2	309.4	310.5
57.5°	277.7	275.9	274.1	273.5	273.3	274.3	276.0	278.3	278.8	282.4	284.1
60°	257.6	254.9	253.4	253.4	252.6	256.0	255.3	259.1	259.9	262.3	265.0
62.5°	236.8	233.2	232.6	232.6	233.7	234.7	235.8	237.5	239.5	242.5	244.5
65°	203.5	201.5	204.2	203.8	203.1	205.4	205.4	207.3	209.6	212.4	216.6
67.5°	171.8	170.8	171.1	171.1	172.2	173.5	174.6	176.3	179.0	182.0	184.7
70°	150.5	151.6	149.7	151.3	152.4	152.8	153.5	155.8	159.0	160.9	164.0
72.5°	129.8	129.7	129.9	130.5	131.7	132.4	133.1	135.7	139.2	140.8	143.3
75°	99.8	99.4	100.6	100.6	102.5	103.3	104.0	105.2	108.3	110.6	112.6
77.5°	72.9	73.3	73.1	74.4	73.9	74.0	76.4	77.6	77.9	82.5	83.5
80°	54.9	55.7	56.0	56.5	56.9	56.0	58.8	60.0	60.0	62.6	64.6
82.5°	39.5	39.9	40.9	41.3	41.4	42.1	42.4	43.2	44.1	45.3	47.9
85°	19.7	20.9	21.3	20.9	21.3	20.5	21.6	22.0	22.4	22.4	22.4
87.5°	7.9	8.6	8.7	9.5	9.7	10.4	10.3	9.8	10.0	11.1	10.1
90°	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7	20.5	21.3	22.9
92.5°	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4	52.7	46.6	42.5
95°	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3	192.7	150.8	122.4
97.5°	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5	567.5	465.6	371.2
100°	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9	866.9	774.6	662.4
102.5°	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7	1002.7	948.9	877.8
105°	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4	1105.3	1120.3	1099.8
107.5°	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2	1092.4	1161.5	1189.6
110°	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8	1050.1	1149.5	1204.9



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1	994.5	1106.0	1177.0
115°	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2	905.5	1021.7	1107.7
117.5°	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9	830.4	934.6	1022.0
120°	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2	788.7	883.5	963.2
122.5°	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8	755.3	843.0	917.2
125°	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6	713.8	789.5	852.7
127.5°	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6	677.2	745.7	803.1
130°	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5	654.5	718.5	772.1
132.5°	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6	633.1	692.6	743.8
135°	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3	602.4	653.7	698.7
137.5°	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9	572.9	617.1	656.1
140°	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5	555.8	593.7	627.6
142.5°	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8	539.4	572.3	601.8
145°	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9	518.0	543.2	566.1
147.5°	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3	502.0	522.4	538.7
150°	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7	491.9	508.5	523.4
152.5°	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8	482.4	497.1	509.6
155°	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4	469.0	480.8	490.3
157.5°	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2	455.9	465.0	472.4
160°	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0	447.7	455.6	461.1
162.5°	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4	438.8	446.1	451.0
165°	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6	426.4	431.9	435.9
167.5°	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0	416.7	419.9	422.7
170°	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4	409.8	412.9	414.5
172.5°	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3	404.0	406.6	407.6
175°	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6	396.4	397.9	397.9
177.5°	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3	391.9	392.5	392.5
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	763.4	763.1	765.2	763.7	765.2	763.1	763.4	765.5	766.1	766.4	766.4
5°	710.5	711.7	707.8	707.8	707.8	711.7	710.5	712.9	714.8	716.3	718.6
7.5°	663.5	661.8	662.0	659.8	662.0	661.8	663.5	665.3	667.8	671.2	674.4
10°	634.7	632.4	631.6	632.0	631.6	632.4	634.7	639.3	640.9	644.0	647.4
12.5°	610.9	610.4	605.3	605.4	605.3	610.4	610.9	612.1	615.5	622.0	626.1
15°	582.9	575.5	574.7	577.0	574.7	575.5	582.9	582.9	584.4	589.5	591.8
17.5°	554.8	550.9	551.2	550.0	551.2	550.9	554.8	555.4	556.6	560.8	563.8
20°	540.0	537.7	537.2	534.5	537.2	537.7	540.0	540.0	541.5	543.4	546.5
22.5°	526.3	525.5	525.7	522.8	525.7	525.5	526.3	527.3	528.8	530.1	532.3
25°	509.4	511.3	509.8	509.8	509.8	511.3	509.4	509.8	510.2	512.1	513.6
27.5°	498.0	497.9	497.1	497.1	497.1	497.9	498.0	497.0	496.6	495.8	495.5
30°	489.3	488.9	489.7	489.7	489.7	488.9	489.3	487.8	487.0	486.6	485.0
32.5°	480.6	481.1	481.3	481.6	481.3	481.1	480.6	478.8	477.4	476.4	475.1
35°	467.3	467.6	468.8	468.0	468.8	467.6	467.3	464.9	463.3	461.0	459.1
37.5°	449.1	450.9	450.5	451.1	450.5	450.9	449.1	448.4	446.9	445.1	442.8
40°	435.6	436.7	436.3	436.3	436.3	436.7	435.6	435.2	433.5	432.4	430.5
42.5°	421.6	422.4	421.4	420.8	421.4	422.4	421.6	420.9	420.0	417.9	415.7
45°	398.8	398.0	399.2	397.6	399.2	398.0	398.8	397.2	396.9	395.3	393.3
47.5°	373.2	374.1	374.4	375.5	374.4	374.1	373.2	373.3	371.2	370.3	369.7
50°	356.2	358.5	358.5	358.2	358.5	358.5	356.2	355.5	353.9	352.3	352.3
52.5°	339.5	340.6	342.1	342.0	342.1	340.6	339.5	338.1	336.6	334.4	333.8
55°	313.7	314.5	315.2	315.6	315.2	314.5	313.7	310.5	309.4	308.2	306.3
57.5°	286.9	286.6	288.4	289.0	288.4	286.6	286.9	284.1	282.4	278.8	278.3
60°	268.0	268.0	271.1	272.3	271.1	268.0	268.0	265.0	262.3	259.9	259.1
62.5°	247.9	249.1	252.3	250.6	252.3	249.1	247.9	244.5	242.5	239.5	237.5
65°	218.5	221.7	221.3	222.8	221.3	221.7	218.5	216.6	212.4	209.6	207.3
67.5°	187.8	189.8	192.6	192.8	192.6	189.8	187.8	184.7	182.0	179.0	176.3
70°	167.1	169.1	170.6	171.7	170.6	169.1	167.1	164.0	160.9	159.0	155.8
72.5°	146.9	147.9	151.7	150.1	151.7	147.9	146.9	143.3	140.8	139.2	135.7
75°	115.2	118.0	120.3	119.2	120.3	118.0	115.2	112.6	110.6	108.3	105.2
77.5°	85.2	88.0	89.1	88.1	89.1	88.0	85.2	83.5	82.5	77.9	77.6
80°	67.3	67.0	69.3	68.9	69.3	67.0	67.3	64.6	62.6	60.0	60.0
82.5°	49.4	49.0	50.1	50.3	50.1	49.0	49.4	47.9	45.3	44.1	43.2
85°	23.9	25.1	23.6	23.2	23.6	25.1	23.9	22.4	22.4	22.4	22.0
87.5°	10.0	10.1	10.0	9.5	10.0	10.1	10.0	10.1	11.1	10.0	9.8
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4
95°	107.3	100.3	94.7	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3
97.5°	313.0	277.4	256.1	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5
100°	582.7	525.0	494.2	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9
102.5°	815.8	770.1	744.4	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7
105°	1063.5	1033.5	1008.2	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4
107.5°	1190.3	1180.2	1171.6	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2
110°	1226.9	1233.2	1231.6	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.5	1237.1	1243.0	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1
115°	1166.9	1201.6	1217.5	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2
117.5°	1083.7	1123.5	1146.2	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9
120°	1025.6	1069.9	1088.7	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2
122.5°	972.5	1012.3	1033.2	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8
125°	903.2	938.0	957.7	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6
127.5°	848.1	877.8	895.6	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6
130°	814.1	842.4	859.0	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5
132.5°	783.0	811.5	826.2	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6
135°	737.4	761.1	775.3	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3
137.5°	688.6	712.7	724.7	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9
140°	657.7	679.7	692.5	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5
142.5°	627.3	646.9	658.3	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8
145°	585.8	602.4	608.7	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9
147.5°	553.6	564.8	570.9	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3
150°	535.3	544.0	548.8	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7
152.5°	518.9	526.9	529.8	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8
155°	497.4	503.7	505.3	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4
157.5°	478.6	483.3	484.6	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2
160°	466.7	471.3	471.3	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0
162.5°	454.6	458.7	458.7	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4
165°	439.0	442.1	441.3	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6
167.5°	424.1	426.4	425.6	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0
170°	415.3	416.9	416.1	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4
172.5°	407.7	409.3	407.9	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3
175°	397.9	398.7	397.9	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6
177.5°	391.9	392.5	391.3	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	765.5	765.5	771.3	775.1	779.7	782.8	785.0	787.2	790.8	795.9	801.4
5°	721.8	723.3	731.7	740.3	748.4	755.4	761.1	768.1	776.7	787.1	798.7
7.5°	679.3	685.3	693.9	704.3	715.6	725.8	736.0	747.5	759.4	774.9	791.1
10°	652.1	658.6	669.1	682.3	694.3	706.2	719.0	731.3	746.5	764.7	785.6
12.5°	628.2	634.5	645.3	659.6	671.1	684.3	698.9	715.0	732.0	753.9	777.5
15°	595.2	602.6	615.7	622.7	640.2	656.0	669.5	692.7	714.4	736.8	764.3
17.5°	568.2	572.3	582.9	595.8	608.8	626.6	644.4	663.7	685.3	712.8	747.1
20°	549.6	553.1	564.7	578.2	592.2	608.4	624.3	643.6	667.9	697.0	734.1
22.5°	535.6	539.5	547.0	561.5	574.5	587.9	603.8	626.9	652.8	681.2	721.4
25°	515.5	517.9	522.9	534.5	546.1	561.2	575.1	596.8	623.5	656.7	697.0
27.5°	496.4	498.7	502.9	511.2	522.1	534.3	549.5	567.8	594.9	631.1	673.8
30°	485.0	485.4	489.3	497.0	506.2	516.3	530.3	551.2	576.6	613.4	658.3
32.5°	475.1	473.6	476.3	482.1	491.1	501.2	512.6	533.2	557.8	593.9	640.1
35°	458.3	457.6	456.4	461.4	469.2	476.9	487.0	502.4	530.3	563.9	612.3
37.5°	441.2	439.4	437.3	439.6	445.7	453.7	462.4	476.2	500.2	537.2	583.5
40°	428.6	427.0	425.9	425.1	430.5	438.2	444.7	458.0	480.4	515.5	561.2
42.5°	414.7	413.7	412.2	411.1	415.7	421.5	428.4	440.0	462.4	495.4	538.7
45°	392.2	391.4	390.6	389.9	392.5	398.0	403.4	411.9	431.2	463.3	502.4
47.5°	367.2	366.2	366.5	365.3	367.9	371.5	375.4	384.5	403.0	428.9	457.5
50°	349.2	348.9	348.9	348.9	349.6	353.9	357.4	364.4	381.3	407.3	427.8
52.5°	332.2	330.6	330.6	331.2	332.6	335.4	337.6	345.2	360.0	381.3	399.9
55°	305.6	302.5	301.6	302.5	303.7	305.9	308.2	314.5	327.2	343.1	353.9
57.5°	276.0	274.3	273.3	273.5	274.1	275.9	277.7	284.5	294.5	302.8	309.7
60°	255.3	256.0	252.6	253.4	253.4	254.9	257.6	261.9	270.3	276.2	283.2
62.5°	235.8	234.7	233.7	232.6	232.6	233.2	236.8	240.1	247.4	250.4	255.9
65°	205.4	205.4	203.1	203.8	204.2	201.5	203.5	207.3	212.0	213.1	218.1
67.5°	174.6	173.5	172.2	171.1	171.1	170.8	171.8	173.7	177.2	177.6	181.5
70°	153.5	152.8	152.4	151.3	149.7	151.6	150.5	152.4	154.3	154.7	157.0
72.5°	133.1	132.4	131.7	130.5	129.9	129.7	129.8	132.0	133.3	132.7	135.3
75°	104.0	103.3	102.5	100.6	100.6	99.4	99.8	101.3	102.9	101.7	104.0
77.5°	76.4	74.0	73.9	74.4	73.1	73.3	72.9	72.6	73.3	73.4	75.5
80°	58.8	56.0	56.9	56.5	56.0	55.7	54.9	55.3	55.7	56.0	57.3
82.5°	42.4	42.1	41.4	41.3	40.9	39.9	39.5	40.2	40.5	40.3	41.2
85°	21.6	20.5	21.3	20.9	21.3	20.9	19.7	19.7	20.5	20.1	20.9
87.5°	10.3	10.4	9.7	9.5	8.7	8.6	7.9	7.9	7.8	7.5	7.8
90°	19.0	19.7	17.4	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6
92.5°	91.6	121.4	133.6	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8
95°	379.8	468.2	416.9	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9
97.5°	776.3	725.6	531.2	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7
100°	903.2	747.7	505.3	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5
102.5°	909.6	706.6	467.4	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7
105°	861.4	634.8	420.8	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6
107.5°	777.1	571.3	391.1	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7
110°	724.0	535.3	379.8	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	677.9	511.3	373.4	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8
115°	622.2	485.5	371.1	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9
117.5°	588.5	470.4	372.5	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9
120°	570.9	463.4	375.1	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8
122.5°	556.3	459.1	379.4	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8
125°	537.7	453.2	386.1	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0
127.5°	521.3	450.4	393.6	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1
130°	512.4	448.5	398.7	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3
132.5°	504.2	447.8	402.5	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7
135°	493.4	446.9	408.2	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7
137.5°	484.1	445.1	412.0	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1
140°	478.5	444.5	414.5	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0
142.5°	473.4	443.2	416.4	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6
145°	466.7	441.3	417.7	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8
147.5°	460.0	438.4	417.7	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2
150°	455.6	435.9	417.7	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3
152.5°	450.5	432.6	415.8	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5
155°	442.9	427.2	413.7	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8
157.5°	434.4	422.2	411.0	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6
160°	428.7	418.5	409.8	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2
162.5°	423.0	414.7	407.3	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0
165°	415.3	409.0	403.4	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4
167.5°	407.9	403.3	399.7	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9
170°	403.4	399.5	397.2	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7
172.5°	399.0	396.4	395.3	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3
175°	393.9	392.4	392.4	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2
177.5°	390.6	390.0	390.6	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	803.2	804.8	810.0	813.7	818.1	820.6	823.0	825.0	827.4	828.0	837.0
5°	806.8	814.6	828.1	838.1	850.5	864.0	873.3	877.6	888.8	898.1	916.7
7.5°	805.8	822.2	842.7	863.9	886.7	907.7	925.9	947.6	963.0	986.1	1009.0
10°	804.9	826.9	853.2	880.3	912.0	941.4	967.8	997.1	1021.5	1053.6	1081.1
12.5°	802.1	828.8	865.3	897.3	935.8	976.3	1015.3	1053.1	1074.7	1128.1	1153.5
15°	795.2	826.9	872.5	921.3	974.3	1022.3	1071.8	1111.2	1175.0	1221.8	1251.6
17.5°	782.0	826.5	880.6	939.4	1003.8	1067.0	1123.1	1183.0	1250.7	1307.3	1367.7
20°	775.9	824.6	884.9	949.9	1016.8	1088.3	1152.2	1224.2	1298.0	1353.7	1431.1
22.5°	764.5	819.6	884.6	957.0	1028.5	1102.6	1177.3	1249.8	1335.1	1411.9	1485.5
25°	745.7	807.6	874.8	955.7	1039.7	1113.9	1203.3	1299.6	1388.6	1487.1	1560.6
27.5°	726.1	792.1	859.6	934.7	1025.0	1113.2	1225.6	1334.3	1443.1	1528.3	1582.7
30°	710.8	775.1	844.8	920.5	1009.9	1114.7	1240.4	1359.1	1465.1	1538.2	1568.7
32.5°	694.5	759.6	821.2	900.7	995.9	1113.8	1249.7	1373.6	1466.3	1515.0	1509.0
35°	668.7	723.3	783.3	859.8	972.0	1106.9	1255.1	1374.9	1431.8	1421.4	1342.5
37.5°	631.6	677.5	736.5	820.3	944.1	1092.7	1244.3	1334.2	1330.5	1245.5	1131.1
40°	608.4	647.4	704.3	792.5	922.4	1083.4	1227.2	1285.7	1236.2	1117.4	980.5
42.5°	578.0	614.0	670.9	761.5	898.7	1064.5	1194.8	1211.6	1114.8	978.2	852.7
45°	531.1	562.8	621.6	715.2	862.9	1023.4	1115.5	1074.1	943.7	802.5	707.0
47.5°	480.5	513.5	570.1	666.2	811.2	961.6	1005.4	917.5	783.6	669.1	581.4
50°	448.7	480.4	535.6	632.8	776.3	910.9	929.1	815.4	692.4	591.8	519.8
52.5°	416.5	446.4	500.7	598.1	735.4	852.0	840.8	725.0	611.9	526.1	469.7
55°	368.6	396.9	448.7	540.0	664.9	757.3	716.7	606.1	512.5	446.0	403.0
57.5°	325.8	352.8	397.5	480.0	588.5	652.1	600.5	507.3	432.8	381.6	349.6
60°	296.7	320.6	363.1	439.8	534.1	582.5	531.4	449.1	386.4	345.4	316.8
62.5°	269.1	290.0	329.4	398.9	480.9	521.5	469.9	400.1	346.8	310.4	286.1
65°	227.4	246.4	281.1	335.4	402.6	429.7	385.3	328.7	287.4	260.3	244.1
67.5°	189.3	205.4	235.5	278.1	327.7	347.4	313.6	269.8	238.6	216.9	204.0
70°	164.0	177.9	201.5	238.2	283.2	298.2	266.5	230.6	207.7	190.3	178.3
72.5°	142.6	152.9	174.3	202.7	240.1	252.1	229.9	198.3	177.0	164.0	154.5
75°	108.7	117.1	131.1	153.9	179.9	186.8	170.2	150.5	136.1	126.8	119.5
77.5°	78.4	84.6	94.7	108.8	126.7	133.0	122.5	109.3	98.9	92.6	88.5
80°	59.2	64.2	72.7	84.3	95.1	98.7	92.4	82.4	75.0	71.6	68.1
82.5°	43.7	46.6	51.7	59.6	67.0	71.1	65.8	59.8	55.8	52.7	51.4
85°	22.0	23.6	26.0	29.0	33.6	35.2	33.2	31.7	29.4	27.5	27.5
87.5°	8.7	9.0	10.4	11.3	12.9	14.2	14.4	14.3	14.4	14.0	13.8
90°	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7
92.5°	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4
95°	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3
97.5°	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5
100°	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9
102.5°	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7
105°	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4
107.5°	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2
110°	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1
115°	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2
117.5°	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9
120°	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2
122.5°	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8
125°	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6
127.5°	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6
130°	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5
132.5°	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6
135°	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3
137.5°	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9
140°	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5
142.5°	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8
145°	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9
147.5°	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3
150°	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7
152.5°	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8
155°	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4
157.5°	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2
160°	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0
162.5°	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4
165°	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6
167.5°	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0
170°	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4
172.5°	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3
175°	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6
177.5°	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.3	798.3	798.3	798.3	798.3	798.3	798.3
2.5°	840.1	840.4	843.7	846.3	845.1	846.6	847.2
5°	917.8	931.7	939.1	944.5	944.9	945.2	948.4
7.5°	1028.0	1043.0	1053.9	1070.5	1075.4	1081.1	1079.4
10°	1108.5	1130.5	1149.5	1159.5	1170.3	1186.2	1173.5
12.5°	1183.7	1222.7	1251.6	1267.2	1277.5	1280.6	1274.3
15°	1307.7	1358.8	1386.2	1385.4	1420.3	1435.3	1411.7
17.5°	1421.4	1468.5	1506.2	1525.6	1554.6	1561.0	1558.1
20°	1491.0	1542.5	1571.9	1605.1	1620.2	1633.8	1636.1
22.5°	1551.1	1597.2	1628.8	1656.5	1669.1	1675.5	1679.4
25°	1612.9	1649.2	1668.2	1677.8	1681.3	1680.5	1675.5
27.5°	1608.6	1611.3	1590.5	1570.0	1551.7	1531.0	1523.9
30°	1566.8	1534.3	1476.3	1443.4	1395.1	1356.8	1372.3
32.5°	1456.9	1392.3	1327.2	1255.3	1195.8	1178.9	1161.8
35°	1243.4	1129.7	1063.3	985.9	954.9	924.0	902.7
37.5°	1006.0	918.1	839.1	788.5	757.5	738.0	727.4
40°	869.9	790.5	725.6	684.6	661.0	638.9	635.8
42.5°	761.2	687.5	638.6	606.0	583.3	574.0	567.1
45°	623.5	572.0	539.2	515.9	500.9	495.0	487.4
47.5°	527.8	491.4	466.7	450.9	439.5	435.2	434.5
50°	474.2	444.0	425.9	413.4	404.6	403.0	396.9
52.5°	433.9	407.8	393.6	382.8	376.4	372.0	370.2
55°	376.7	359.3	346.6	340.3	335.4	331.0	331.0
57.5°	329.6	315.1	306.6	301.3	299.8	296.8	294.9
60°	300.5	288.1	281.6	276.9	273.9	274.2	270.7
62.5°	272.1	264.0	257.7	253.1	249.4	249.4	249.7
65°	231.7	225.5	220.9	219.3	217.0	214.3	215.0
67.5°	196.3	190.6	186.9	184.3	183.5	182.0	184.3
70°	171.0	166.7	164.0	161.7	160.9	161.3	163.2
72.5°	147.7	144.7	143.0	141.9	140.2	140.3	141.6
75°	116.0	113.7	112.2	111.0	110.6	110.6	110.6
77.5°	85.2	84.7	84.0	82.3	82.4	82.8	82.9
80°	67.3	66.1	65.7	64.9	63.8	63.0	64.9
82.5°	50.3	49.1	48.8	48.6	46.8	46.7	48.3
85°	27.1	26.0	26.3	26.0	26.0	25.5	25.5
87.5°	13.7	13.5	13.5	13.7	13.5	13.4	13.8
90°	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1



TEST NUMBER: P331930-840

CATALOG NUMBER: S123DIP-S560D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)