

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331984-840

Luminaire Tested: **S123DIP-S775D1025U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331984-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7043.8 lumens
Efficiency: N/A
Efficacy: 135.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82		67	67	67		53	53	53	47
1	97	93	89	86	89	86	82	80	72	70	67		59	58	56		47	46	45	40
2	89	82	76	71	81	75	70	66	63	59	56		52	50	47		42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48		46	43	40		37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41		41	38	35		34	31	29	25
5	68	57	49	43	62	53	46	40	45	39	35		37	33	30		30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31		34	30	26		28	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27		31	26	23		25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24		28	24	21		23	20	18	15
9	50	38	31	26	46	35	29	24	30	25	21		26	22	19		21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	1.5
10°-20°	344.7	4.9
20°-30°	578.5	8.2
30°-40°	655.0	9.3
40°-50°	587.4	8.3
50°-60°	474.0	6.7
60°-70°	330.3	4.7
70°-80°	173.6	2.5
80°-90°	46.3	0.7
90°-100°	277.1	3.9
100°-110°	784.7	11.1
110°-120°	771.9	11.0
120°-130°	615.7	8.7
130°-140°	485.5	6.9
140°-150°	362.3	5.1
150°-160°	252.5	3.6
160°-170°	148.4	2.1
170°-180°	48.3	0.7
0°-30°	1030.6	14.6
0°-40°	1685.7	23.9
0°-60°	2747.1	39.0
0°-90°	3297.3	46.8
90°-120°	1833.8	26.0
90°-150°	3297.3	46.8
90°-180°	3746.0	53.2
0°-180°	7043.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	42
90°	29	2	29	2	29	17
95°	117	34	117	34	117	211
105°	1282	117	1282	117	1282	1265
115°	1559	207	1559	207	1559	1515
125°	1230	287	1230	287	1230	1115
135°	997	337	997	337	997	773
145°	779	384	779	384	779	496
155°	646	436	646	436	646	301
165°	564	477	564	477	564	161
175°	507	497	507	497	507	49
180°	498	498	498	498	498	



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	18.6	17.9	18.1	18.4	18.1	18.2	18.4	18.6	18.8	19.4	19.3
90°	29.2	30.2	29.2	28.2	29.2	27.3	26.3	25.2	24.2	25.2	22.2
92.5°	48.6	50.4	49.4	52.4	54.2	59.5	67.4	84.8	116.9	155.0	170.6
95°	116.9	121.0	128.1	137.1	156.2	192.6	246.0	362.8	484.8	597.7	532.2
97.5°	318.3	327.0	354.3	399.6	473.9	594.5	724.6	904.6	991.1	926.3	678.2
100°	632.1	631.1	670.3	744.0	845.8	988.9	1106.8	1188.5	1153.2	954.6	645.1
102.5°	927.2	950.4	983.2	1041.5	1120.7	1211.4	1280.2	1282.8	1161.2	902.2	596.7
105°	1282.2	1287.3	1319.5	1357.8	1404.2	1430.4	1411.3	1310.4	1099.7	810.4	537.2
107.5°	1486.6	1495.9	1506.8	1519.7	1518.9	1483.0	1394.7	1231.0	992.1	729.4	499.4
110°	1570.5	1572.6	1574.6	1566.5	1538.2	1467.6	1340.7	1155.2	924.3	683.5	484.8



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1587.4	1587.0	1579.3	1554.4	1502.8	1412.0	1269.7	1080.2	865.5	652.8	476.8
115°	1559.4	1554.4	1534.2	1489.9	1414.2	1304.3	1156.2	980.8	794.4	620.0	473.7
117.5°	1470.3	1463.5	1434.4	1383.6	1304.7	1193.3	1060.3	908.9	751.3	600.6	475.5
120°	1396.1	1390.1	1365.8	1309.4	1229.8	1128.0	1007.0	870.9	728.8	591.7	478.8
122.5°	1326.8	1319.1	1292.5	1241.7	1170.9	1076.4	964.3	841.1	710.2	586.0	484.4
125°	1229.8	1222.7	1197.5	1153.2	1088.6	1008.0	911.3	801.4	686.5	578.7	492.9
127.5°	1149.9	1143.5	1120.7	1082.8	1025.3	952.0	864.6	766.7	665.5	575.0	502.6
130°	1104.8	1096.7	1075.6	1039.3	985.8	917.3	835.7	745.0	654.2	572.6	509.1
132.5°	1060.5	1054.8	1036.0	999.8	949.6	884.2	808.2	724.8	643.7	571.8	513.9
135°	996.9	989.9	971.7	941.5	892.1	834.7	769.1	697.5	630.1	570.6	521.2
137.5°	929.8	925.1	909.9	879.2	837.7	787.9	731.4	672.8	618.1	568.4	525.9
140°	883.0	884.0	867.9	839.7	801.4	758.0	709.6	658.2	610.9	567.5	529.2
142.5°	839.5	840.5	826.0	801.0	768.3	730.6	688.7	644.5	604.4	565.9	531.6
145°	779.2	777.2	769.1	747.9	722.8	693.5	661.3	628.0	595.7	563.5	533.2
147.5°	729.6	728.8	721.1	706.8	687.7	666.9	640.9	614.5	587.2	559.7	533.2
150°	700.5	700.5	694.5	683.5	668.3	649.1	628.0	604.8	581.6	556.4	533.2
152.5°	676.4	676.4	672.8	662.5	650.6	634.7	615.9	595.9	575.2	552.4	530.8
155°	646.1	645.1	643.1	635.1	626.0	613.9	598.7	582.6	565.5	545.3	528.2
157.5°	618.5	618.7	617.1	611.1	603.2	593.7	582.0	568.6	554.6	539.1	524.8
160°	600.8	601.8	601.8	595.7	588.7	581.6	571.6	560.5	547.3	534.2	523.2
162.5°	584.6	585.6	585.6	580.5	575.8	569.6	560.3	550.8	540.1	529.4	520.0
165°	563.5	563.5	564.5	560.5	556.4	551.4	544.3	538.3	530.2	522.2	515.1
167.5°	543.3	543.3	544.3	541.5	539.7	536.0	532.0	527.4	520.8	514.9	510.3
170°	531.2	531.2	532.2	530.2	529.2	527.1	523.2	520.2	515.1	510.1	507.1
172.5°	520.0	520.8	522.6	520.6	520.4	519.2	515.9	513.7	509.5	506.0	504.6
175°	507.1	508.1	509.1	508.1	508.1	508.1	506.0	505.0	503.0	501.0	501.0
177.5°	499.6	499.6	501.2	500.4	501.2	501.2	500.4	499.6	498.8	498.0	498.8
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	19.5	19.3	17.5	15.3	14.0	12.2	11.8	10.6	10.1	10.5	10.7
90°	19.2	16.2	13.1	11.1	9.1	6.1	4.0	2.0	4.0	6.1	9.1
92.5°	128.1	84.6	58.3	43.3	34.8	27.1	18.6	12.5	18.6	27.1	34.8
95°	366.9	216.7	131.1	91.7	65.5	48.4	37.3	34.2	37.3	48.4	65.5
97.5°	402.6	233.3	151.4	108.9	83.0	68.2	59.5	58.5	59.5	68.2	83.0
100°	380.0	230.9	160.3	121.0	96.7	82.7	75.6	74.6	75.6	82.7	96.7
102.5°	360.6	234.1	170.8	134.7	112.9	99.6	93.3	91.5	93.3	99.6	112.9
105°	346.8	243.0	188.5	157.2	138.1	126.0	120.0	116.9	120.0	126.0	138.1
107.5°	345.8	259.4	211.7	182.7	164.7	152.8	146.9	143.9	146.9	152.8	164.7
110°	349.8	273.2	227.8	199.5	182.5	171.4	166.3	163.3	166.3	171.4	182.5



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	357.9	286.9	244.8	217.3	200.2	189.1	184.1	181.1	184.1	189.1	200.2
115°	370.9	309.4	271.1	244.0	226.8	216.7	210.7	206.6	210.7	216.7	226.8
117.5°	388.3	333.5	295.6	270.3	251.2	242.0	236.9	232.3	236.9	242.0	251.2
120°	401.2	348.8	312.5	287.3	268.1	258.0	253.0	249.9	253.0	258.0	268.1
122.5°	413.3	364.9	329.4	302.7	284.3	273.4	268.3	265.3	268.3	273.4	284.3
125°	432.4	388.1	352.8	325.6	306.4	295.4	289.3	287.3	289.3	295.4	306.4
127.5°	448.2	408.3	374.2	347.0	325.8	314.5	307.0	304.1	307.0	314.5	325.8
130°	458.7	420.3	387.1	359.8	338.7	326.6	317.5	314.5	317.5	326.6	338.7
132.5°	468.4	430.8	398.4	371.9	350.8	336.3	326.4	322.6	326.4	336.3	350.8
135°	480.8	446.6	415.3	388.1	366.9	351.8	340.7	336.7	340.7	351.8	366.9
137.5°	490.1	457.5	427.4	402.2	381.2	365.1	354.3	350.0	354.3	365.1	381.2
140°	494.9	464.7	435.5	410.3	390.1	374.0	363.9	358.9	363.9	374.0	390.1
142.5°	499.8	470.4	441.9	418.3	398.2	383.6	372.7	368.5	372.7	383.6	398.2
145°	505.0	477.8	451.6	428.4	411.3	396.2	387.1	384.1	387.1	396.2	411.3
147.5°	508.3	483.8	459.9	440.1	423.5	410.5	401.6	399.8	401.6	410.5	423.5
150°	509.1	487.9	464.7	446.6	432.4	419.3	411.3	410.3	411.3	419.3	432.4
152.5°	510.7	490.3	470.4	453.0	440.5	429.0	420.9	420.7	420.9	429.0	440.5
155°	511.1	494.9	477.8	463.7	452.6	442.5	436.5	436.5	436.5	442.5	452.6
157.5°	512.1	497.6	483.8	472.9	463.5	454.6	449.8	449.0	449.8	454.6	463.5
160°	512.1	500.0	487.9	477.8	470.7	462.7	458.7	458.7	458.7	462.7	470.7
162.5°	511.3	500.8	490.3	481.8	475.5	469.2	466.0	466.0	466.0	469.2	475.5
165°	509.1	502.0	493.9	486.9	482.8	477.8	475.7	476.8	475.7	477.8	482.8
167.5°	507.5	501.8	495.9	491.5	488.7	484.8	483.8	485.0	483.8	484.8	488.7
170°	505.0	501.0	495.9	493.9	491.9	488.9	487.9	489.9	487.9	488.9	491.9
172.5°	504.2	501.0	496.8	495.5	494.3	492.1	491.9	493.1	491.9	492.1	494.3
175°	502.0	500.0	498.0	497.0	497.0	494.9	495.9	497.0	495.9	494.9	497.0
177.5°	500.4	498.8	498.0	498.0	498.0	497.2	498.0	498.8	498.0	497.2	498.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	10.7	11.5	11.7	12.7	12.9	13.9	13.7	13.0	13.2	14.7	13.4
90°	11.1	13.1	16.2	19.2	22.2	25.2	24.2	25.2	26.3	27.3	29.2
92.5°	43.3	58.3	84.6	128.1	170.6	155.0	116.9	84.8	67.4	59.5	54.2
95°	91.7	131.1	216.7	366.9	532.2	597.7	484.8	362.8	246.0	192.6	156.2
97.5°	108.9	151.4	233.3	402.6	678.2	926.3	991.1	904.6	724.6	594.5	473.9
100°	121.0	160.3	230.9	380.0	645.1	954.6	1153.2	1188.5	1106.8	988.9	845.8
102.5°	134.7	170.8	234.1	360.6	596.7	902.2	1161.2	1282.8	1280.2	1211.4	1120.7
105°	157.2	188.5	243.0	346.8	537.2	810.4	1099.7	1310.4	1411.3	1430.4	1404.2
107.5°	182.7	211.7	259.4	345.8	499.4	729.4	992.1	1231.0	1394.7	1483.0	1518.9
110°	199.5	227.8	273.2	349.8	484.8	683.5	924.3	1155.2	1340.7	1467.6	1538.2



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.3	244.8	286.9	357.9	476.8	652.8	865.5	1080.2	1269.7	1412.0	1502.8
115°	244.0	271.1	309.4	370.9	473.7	620.0	794.4	980.8	1156.2	1304.3	1414.2
117.5°	270.3	295.6	333.5	388.3	475.5	600.6	751.3	908.9	1060.3	1193.3	1304.7
120°	287.3	312.5	348.8	401.2	478.8	591.7	728.8	870.9	1007.0	1128.0	1229.8
122.5°	302.7	329.4	364.9	413.3	484.4	586.0	710.2	841.1	964.3	1076.4	1170.9
125°	325.6	352.8	388.1	432.4	492.9	578.7	686.5	801.4	911.3	1008.0	1088.6
127.5°	347.0	374.2	408.3	448.2	502.6	575.0	665.5	766.7	864.6	952.0	1025.3
130°	359.8	387.1	420.3	458.7	509.1	572.6	654.2	745.0	835.7	917.3	985.8
132.5°	371.9	398.4	430.8	468.4	513.9	571.8	643.7	724.8	808.2	884.2	949.6
135°	388.1	415.3	446.6	480.8	521.2	570.6	630.1	697.5	769.1	834.7	892.1
137.5°	402.2	427.4	457.5	490.1	525.9	568.4	618.1	672.8	731.4	787.9	837.7
140°	410.3	435.5	464.7	494.9	529.2	567.5	610.9	658.2	709.6	758.0	801.4
142.5°	418.3	441.9	470.4	499.8	531.6	565.9	604.4	644.5	688.7	730.6	768.3
145°	428.4	451.6	477.8	505.0	533.2	563.5	595.7	628.0	661.3	693.5	722.8
147.5°	440.1	459.9	483.8	508.3	533.2	559.7	587.2	614.5	640.9	666.9	687.7
150°	446.6	464.7	487.9	509.1	533.2	556.4	581.6	604.8	628.0	649.1	668.3
152.5°	453.0	470.4	490.3	510.7	530.8	552.4	575.2	595.9	615.9	634.7	650.6
155°	463.7	477.8	494.9	511.1	528.2	545.3	565.5	582.6	598.7	613.9	626.0
157.5°	472.9	483.8	497.6	512.1	524.8	539.1	554.6	568.6	582.0	593.7	603.2
160°	477.8	487.9	500.0	512.1	523.2	534.2	547.3	560.5	571.6	581.6	588.7
162.5°	481.8	490.3	500.8	511.3	520.0	529.4	540.1	550.8	560.3	569.6	575.8
165°	486.9	493.9	502.0	509.1	515.1	522.2	530.2	538.3	544.3	551.4	556.4
167.5°	491.5	495.9	501.8	507.5	510.3	514.9	520.8	527.4	532.0	536.0	539.7
170°	493.9	495.9	501.0	505.0	507.1	510.1	515.1	520.2	523.2	527.1	529.2
172.5°	495.5	496.8	501.0	504.2	504.6	506.0	509.5	513.7	515.9	519.2	520.4
175°	497.0	498.0	500.0	502.0	501.0	501.0	503.0	505.0	506.0	508.1	508.1
177.5°	498.0	498.0	498.8	500.4	498.8	498.0	498.8	499.6	500.4	501.2	501.2
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	13.2	13.4	13.2	12.6	13.2	13.4	13.2	13.4	14.7	13.2	13.0
90°	28.2	29.2	30.2	29.2	30.2	29.2	28.2	29.2	27.3	26.3	25.2
92.5°	52.4	49.4	50.4	48.6	50.4	49.4	52.4	54.2	59.5	67.4	84.8
95°	137.1	128.1	121.0	116.9	121.0	128.1	137.1	156.2	192.6	246.0	362.8
97.5°	399.6	354.3	327.0	318.3	327.0	354.3	399.6	473.9	594.5	724.6	904.6
100°	744.0	670.3	631.1	632.1	631.1	670.3	744.0	845.8	988.9	1106.8	1188.5
102.5°	1041.5	983.2	950.4	927.2	950.4	983.2	1041.5	1120.7	1211.4	1280.2	1282.8
105°	1357.8	1319.5	1287.3	1282.2	1287.3	1319.5	1357.8	1404.2	1430.4	1411.3	1310.4
107.5°	1519.7	1506.8	1495.9	1486.6	1495.9	1506.8	1519.7	1518.9	1483.0	1394.7	1231.0
110°	1566.5	1574.6	1572.6	1570.5	1572.6	1574.6	1566.5	1538.2	1467.6	1340.7	1155.2



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1554.4	1579.3	1587.0	1587.4	1587.0	1579.3	1554.4	1502.8	1412.0	1269.7	1080.2
115°	1489.9	1534.2	1554.4	1559.4	1554.4	1534.2	1489.9	1414.2	1304.3	1156.2	980.8
117.5°	1383.6	1434.4	1463.5	1470.3	1463.5	1434.4	1383.6	1304.7	1193.3	1060.3	908.9
120°	1309.4	1365.8	1390.1	1396.1	1390.1	1365.8	1309.4	1229.8	1128.0	1007.0	870.9
122.5°	1241.7	1292.5	1319.1	1326.8	1319.1	1292.5	1241.7	1170.9	1076.4	964.3	841.1
125°	1153.2	1197.5	1222.7	1229.8	1222.7	1197.5	1153.2	1088.6	1008.0	911.3	801.4
127.5°	1082.8	1120.7	1143.5	1149.9	1143.5	1120.7	1082.8	1025.3	952.0	864.6	766.7
130°	1039.3	1075.6	1096.7	1104.8	1096.7	1075.6	1039.3	985.8	917.3	835.7	745.0
132.5°	999.8	1036.0	1054.8	1060.5	1054.8	1036.0	999.8	949.6	884.2	808.2	724.8
135°	941.5	971.7	989.9	996.9	989.9	971.7	941.5	892.1	834.7	769.1	697.5
137.5°	879.2	909.9	925.1	929.8	925.1	909.9	879.2	837.7	787.9	731.4	672.8
140°	839.7	867.9	884.0	883.0	884.0	867.9	839.7	801.4	758.0	709.6	658.2
142.5°	801.0	826.0	840.5	839.5	840.5	826.0	801.0	768.3	730.6	688.7	644.5
145°	747.9	769.1	777.2	779.2	777.2	769.1	747.9	722.8	693.5	661.3	628.0
147.5°	706.8	721.1	728.8	729.6	728.8	721.1	706.8	687.7	666.9	640.9	614.5
150°	683.5	694.5	700.5	700.5	700.5	694.5	683.5	668.3	649.1	628.0	604.8
152.5°	662.5	672.8	676.4	676.4	676.4	672.8	662.5	650.6	634.7	615.9	595.9
155°	635.1	643.1	645.1	646.1	645.1	643.1	635.1	626.0	613.9	598.7	582.6
157.5°	611.1	617.1	618.7	618.5	618.7	617.1	611.1	603.2	593.7	582.0	568.6
160°	595.7	601.8	601.8	600.8	601.8	601.8	595.7	588.7	581.6	571.6	560.5
162.5°	580.5	585.6	585.6	584.6	585.6	585.6	580.5	575.8	569.6	560.3	550.8
165°	560.5	564.5	563.5	563.5	563.5	564.5	560.5	556.4	551.4	544.3	538.3
167.5°	541.5	544.3	543.3	543.3	543.3	544.3	541.5	539.7	536.0	532.0	527.4
170°	530.2	532.2	531.2	531.2	531.2	532.2	530.2	529.2	527.1	523.2	520.2
172.5°	520.6	522.6	520.8	520.0	520.8	522.6	520.6	520.4	519.2	515.9	513.7
175°	508.1	509.1	508.1	507.1	508.1	509.1	508.1	508.1	508.1	506.0	505.0
177.5°	500.4	501.2	499.6	499.6	499.6	501.2	500.4	501.2	501.2	500.4	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	13.7	13.9	12.9	12.7	11.7	11.5	10.7	10.7	10.5	10.1	10.6
90°	24.2	25.2	22.2	19.2	16.2	13.1	11.1	9.1	6.1	4.0	2.0
92.5°	116.9	155.0	170.6	128.1	84.6	58.3	43.3	34.8	27.1	18.6	12.5
95°	484.8	597.7	532.2	366.9	216.7	131.1	91.7	65.5	48.4	37.3	34.2
97.5°	991.1	926.3	678.2	402.6	233.3	151.4	108.9	83.0	68.2	59.5	58.5
100°	1153.2	954.6	645.1	380.0	230.9	160.3	121.0	96.7	82.7	75.6	74.6
102.5°	1161.2	902.2	596.7	360.6	234.1	170.8	134.7	112.9	99.6	93.3	91.5
105°	1099.7	810.4	537.2	346.8	243.0	188.5	157.2	138.1	126.0	120.0	116.9
107.5°	992.1	729.4	499.4	345.8	259.4	211.7	182.7	164.7	152.8	146.9	143.9
110°	924.3	683.5	484.8	349.8	273.2	227.8	199.5	182.5	171.4	166.3	163.3



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	865.5	652.8	476.8	357.9	286.9	244.8	217.3	200.2	189.1	184.1	181.1
115°	794.4	620.0	473.7	370.9	309.4	271.1	244.0	226.8	216.7	210.7	206.6
117.5°	751.3	600.6	475.5	388.3	333.5	295.6	270.3	251.2	242.0	236.9	232.3
120°	728.8	591.7	478.8	401.2	348.8	312.5	287.3	268.1	258.0	253.0	249.9
122.5°	710.2	586.0	484.4	413.3	364.9	329.4	302.7	284.3	273.4	268.3	265.3
125°	686.5	578.7	492.9	432.4	388.1	352.8	325.6	306.4	295.4	289.3	287.3
127.5°	665.5	575.0	502.6	448.2	408.3	374.2	347.0	325.8	314.5	307.0	304.1
130°	654.2	572.6	509.1	458.7	420.3	387.1	359.8	338.7	326.6	317.5	314.5
132.5°	643.7	571.8	513.9	468.4	430.8	398.4	371.9	350.8	336.3	326.4	322.6
135°	630.1	570.6	521.2	480.8	446.6	415.3	388.1	366.9	351.8	340.7	336.7
137.5°	618.1	568.4	525.9	490.1	457.5	427.4	402.2	381.2	365.1	354.3	350.0
140°	610.9	567.5	529.2	494.9	464.7	435.5	410.3	390.1	374.0	363.9	358.9
142.5°	604.4	565.9	531.6	499.8	470.4	441.9	418.3	398.2	383.6	372.7	368.5
145°	595.7	563.5	533.2	505.0	477.8	451.6	428.4	411.3	396.2	387.1	384.1
147.5°	587.2	559.7	533.2	508.3	483.8	459.9	440.1	423.5	410.5	401.6	399.8
150°	581.6	556.4	533.2	509.1	487.9	464.7	446.6	432.4	419.3	411.3	410.3
152.5°	575.2	552.4	530.8	510.7	490.3	470.4	453.0	440.5	429.0	420.9	420.7
155°	565.5	545.3	528.2	511.1	494.9	477.8	463.7	452.6	442.5	436.5	436.5
157.5°	554.6	539.1	524.8	512.1	497.6	483.8	472.9	463.5	454.6	449.8	449.0
160°	547.3	534.2	523.2	512.1	500.0	487.9	477.8	470.7	462.7	458.7	458.7
162.5°	540.1	529.4	520.0	511.3	500.8	490.3	481.8	475.5	469.2	466.0	466.0
165°	530.2	522.2	515.1	509.1	502.0	493.9	486.9	482.8	477.8	475.7	476.8
167.5°	520.8	514.9	510.3	507.5	501.8	495.9	491.5	488.7	484.8	483.8	485.0
170°	515.1	510.1	507.1	505.0	501.0	495.9	493.9	491.9	488.9	487.9	489.9
172.5°	509.5	506.0	504.6	504.2	501.0	496.8	495.5	494.3	492.1	491.9	493.1
175°	503.0	501.0	501.0	502.0	500.0	498.0	497.0	497.0	494.9	495.9	497.0
177.5°	498.8	498.0	498.8	500.4	498.8	498.0	498.0	498.0	497.2	498.0	498.8
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.8	12.2	14.0	15.3	17.5	19.3	19.5	19.3	19.4	18.8	18.6
90°	4.0	6.1	9.1	11.1	13.1	16.2	19.2	22.2	25.2	24.2	25.2
92.5°	18.6	27.1	34.8	43.3	58.3	84.6	128.1	170.6	155.0	116.9	84.8
95°	37.3	48.4	65.5	91.7	131.1	216.7	366.9	532.2	597.7	484.8	362.8
97.5°	59.5	68.2	83.0	108.9	151.4	233.3	402.6	678.2	926.3	991.1	904.6
100°	75.6	82.7	96.7	121.0	160.3	230.9	380.0	645.1	954.6	1153.2	1188.5
102.5°	93.3	99.6	112.9	134.7	170.8	234.1	360.6	596.7	902.2	1161.2	1282.8
105°	120.0	126.0	138.1	157.2	188.5	243.0	346.8	537.2	810.4	1099.7	1310.4
107.5°	146.9	152.8	164.7	182.7	211.7	259.4	345.8	499.4	729.4	992.1	1231.0
110°	166.3	171.4	182.5	199.5	227.8	273.2	349.8	484.8	683.5	924.3	1155.2



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	184.1	189.1	200.2	217.3	244.8	286.9	357.9	476.8	652.8	865.5	1080.2
115°	210.7	216.7	226.8	244.0	271.1	309.4	370.9	473.7	620.0	794.4	980.8
117.5°	236.9	242.0	251.2	270.3	295.6	333.5	388.3	475.5	600.6	751.3	908.9
120°	253.0	258.0	268.1	287.3	312.5	348.8	401.2	478.8	591.7	728.8	870.9
122.5°	268.3	273.4	284.3	302.7	329.4	364.9	413.3	484.4	586.0	710.2	841.1
125°	289.3	295.4	306.4	325.6	352.8	388.1	432.4	492.9	578.7	686.5	801.4
127.5°	307.0	314.5	325.8	347.0	374.2	408.3	448.2	502.6	575.0	665.5	766.7
130°	317.5	326.6	338.7	359.8	387.1	420.3	458.7	509.1	572.6	654.2	745.0
132.5°	326.4	336.3	350.8	371.9	398.4	430.8	468.4	513.9	571.8	643.7	724.8
135°	340.7	351.8	366.9	388.1	415.3	446.6	480.8	521.2	570.6	630.1	697.5
137.5°	354.3	365.1	381.2	402.2	427.4	457.5	490.1	525.9	568.4	618.1	672.8
140°	363.9	374.0	390.1	410.3	435.5	464.7	494.9	529.2	567.5	610.9	658.2
142.5°	372.7	383.6	398.2	418.3	441.9	470.4	499.8	531.6	565.9	604.4	644.5
145°	387.1	396.2	411.3	428.4	451.6	477.8	505.0	533.2	563.5	595.7	628.0
147.5°	401.6	410.5	423.5	440.1	459.9	483.8	508.3	533.2	559.7	587.2	614.5
150°	411.3	419.3	432.4	446.6	464.7	487.9	509.1	533.2	556.4	581.6	604.8
152.5°	420.9	429.0	440.5	453.0	470.4	490.3	510.7	530.8	552.4	575.2	595.9
155°	436.5	442.5	452.6	463.7	477.8	494.9	511.1	528.2	545.3	565.5	582.6
157.5°	449.8	454.6	463.5	472.9	483.8	497.6	512.1	524.8	539.1	554.6	568.6
160°	458.7	462.7	470.7	477.8	487.9	500.0	512.1	523.2	534.2	547.3	560.5
162.5°	466.0	469.2	475.5	481.8	490.3	500.8	511.3	520.0	529.4	540.1	550.8
165°	475.7	477.8	482.8	486.9	493.9	502.0	509.1	515.1	522.2	530.2	538.3
167.5°	483.8	484.8	488.7	491.5	495.9	501.8	507.5	510.3	514.9	520.8	527.4
170°	487.9	488.9	491.9	493.9	495.9	501.0	505.0	507.1	510.1	515.1	520.2
172.5°	491.9	492.1	494.3	495.5	496.8	501.0	504.2	504.6	506.0	509.5	513.7
175°	495.9	494.9	497.0	497.0	498.0	500.0	502.0	501.0	501.0	503.0	505.0
177.5°	498.0	497.2	498.0	498.0	498.0	498.8	500.4	498.8	498.0	498.8	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	18.4	18.2	18.1	18.4	18.1	17.9	18.6
90°	26.3	27.3	29.2	28.2	29.2	30.2	29.2
92.5°	67.4	59.5	54.2	52.4	49.4	50.4	48.6
95°	246.0	192.6	156.2	137.1	128.1	121.0	116.9
97.5°	724.6	594.5	473.9	399.6	354.3	327.0	318.3
100°	1106.8	988.9	845.8	744.0	670.3	631.1	632.1
102.5°	1280.2	1211.4	1120.7	1041.5	983.2	950.4	927.2
105°	1411.3	1430.4	1404.2	1357.8	1319.5	1287.3	1282.2
107.5°	1394.7	1483.0	1518.9	1519.7	1506.8	1495.9	1486.6
110°	1340.7	1467.6	1538.2	1566.5	1574.6	1572.6	1570.5



TEST NUMBER: P331984-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1269.7	1412.0	1502.8	1554.4	1579.3	1587.0	1587.4
115°	1156.2	1304.3	1414.2	1489.9	1534.2	1554.4	1559.4
117.5°	1060.3	1193.3	1304.7	1383.6	1434.4	1463.5	1470.3
120°	1007.0	1128.0	1229.8	1309.4	1365.8	1390.1	1396.1
122.5°	964.3	1076.4	1170.9	1241.7	1292.5	1319.1	1326.8
125°	911.3	1008.0	1088.6	1153.2	1197.5	1222.7	1229.8
127.5°	864.6	952.0	1025.3	1082.8	1120.7	1143.5	1149.9
130°	835.7	917.3	985.8	1039.3	1075.6	1096.7	1104.8
132.5°	808.2	884.2	949.6	999.8	1036.0	1054.8	1060.5
135°	769.1	834.7	892.1	941.5	971.7	989.9	996.9
137.5°	731.4	787.9	837.7	879.2	909.9	925.1	929.8
140°	709.6	758.0	801.4	839.7	867.9	884.0	883.0
142.5°	688.7	730.6	768.3	801.0	826.0	840.5	839.5
145°	661.3	693.5	722.8	747.9	769.1	777.2	779.2
147.5°	640.9	666.9	687.7	706.8	721.1	728.8	729.6
150°	628.0	649.1	668.3	683.5	694.5	700.5	700.5
152.5°	615.9	634.7	650.6	662.5	672.8	676.4	676.4
155°	598.7	613.9	626.0	635.1	643.1	645.1	646.1
157.5°	582.0	593.7	603.2	611.1	617.1	618.7	618.5
160°	571.6	581.6	588.7	595.7	601.8	601.8	600.8
162.5°	560.3	569.6	575.8	580.5	585.6	585.6	584.6
165°	544.3	551.4	556.4	560.5	564.5	563.5	563.5
167.5°	532.0	536.0	539.7	541.5	544.3	543.3	543.3
170°	523.2	527.1	529.2	530.2	532.2	531.2	531.2
172.5°	515.9	519.2	520.4	520.6	522.6	520.8	520.0
175°	506.0	508.1	508.1	508.1	509.1	508.1	507.1
177.5°	500.4	501.2	501.2	500.4	501.2	499.6	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0

(END OF REPORT)