

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831870

Luminaire Tested: S123RDIP-S1000D585U950-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831870  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D585U950-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6338.6 lumens  
Efficiency: N/A  
Efficacy: 126.0 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 50.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65				
1	102	98	94	91	96	92	89	86	82	80	77	72	70	69	63	62	61	57				
2	94	87	81	76	88	82	77	73	73	69	66	65	62	59	57	55	53	49				
3	86	78	71	65	81	73	67	62	66	61	57	58	55	52	52	49	46	43				
4	80	70	62	56	75	66	59	54	59	54	50	53	49	45	47	44	41	38				
5	74	63	55	49	69	60	53	47	54	48	44	48	44	40	43	40	37	34				
6	69	57	49	44	65	54	47	42	49	43	39	44	40	36	40	36	33	31				
7	64	52	44	39	60	50	43	38	45	39	35	41	36	33	37	33	30	28				
8	60	48	40	35	56	46	39	34	42	36	32	38	33	30	34	30	28	25				
9	56	44	37	32	53	42	36	31	39	33	29	35	31	27	32	28	25	23				
10	53	41	34	29	50	39	33	28	36	31	27	33	28	25	30	26	23	22				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	33322	33322	33322	33322	33322
5°	39566	38305	33532	27107	25166
10°	35848	38907	33365	21718	18631
15°	24682	33360	33013	17751	14739
20°	17171	25684	32349	14968	12954
25°	13085	19574	31385	13303	11940
30°	11390	15649	30179	12352	11059
35°	10457	13201	28470	11550	10257
40°	9542	11789	26235	10763	9524
45°	8617	10782	23823	10018	8791
50°	7822	9947	20979	9289	7886
55°	7075	9135	18246	8574	6765
60°	6340	8308	15849	7787	6394
65°	5850	7371	13642	6999	6046
70°	4752	6370	11903	6332	4913
75°	4171	5065	10081	5253	4329
80°	3775	4289	8263	4407	4091
85°	3446	3767	6274	4001	3767

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 25137 cd/sqm



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	282.2	4.5
10°-20°	652.9	10.3
20°-30°	749.2	11.8
30°-40°	738.4	11.6
40°-50°	651.2	10.3
50°-60°	501.0	7.9
60°-70°	329.4	5.2
70°-80°	160.0	2.5
80°-90°	41.8	0.7
90°-100°	25.8	0.4
100°-110°	124.8	2.0
110°-120°	306.0	4.8
120°-130°	388.4	6.1
130°-140°	415.0	6.5
140°-150°	388.0	6.1
150°-160°	313.0	4.9
160°-170°	202.0	3.2
170°-180°	69.6	1.1
0°-30°	1684.3	26.6
0°-40°	2422.7	38.2
0°-60°	3574.9	56.4
0°-90°	4106.0	64.8
90°-120°	456.6	7.2
90°-150°	1648.1	26.0
90°-180°	2233.0	35.2
0°-180°	6338.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3096	3096	3096	3096	3096	
5°	3662	3545	3103	2509	2329	335
15°	2215	2994	2962	1593	1323	625
25°	1102	1648	2643	1120	1005	520
35°	796	1005	2167	879	781	496
45°	566	708	1565	658	578	439
55°	377	487	972	457	360	338
65°	230	289	536	275	237	225
75°	100	122	242	126	104	108
85°	28	30	51	32	30	30
90°	16	13	0	13	16	9
95°	21	17	33	17	21	17
105°	24	119	162	119	24	50
115°	320	312	304	312	320	301
125°	438	435	429	435	438	391
135°	539	539	534	539	539	416
145°	622	621	616	621	622	388
155°	677	678	678	678	677	312
165°	714	713	716	713	714	202
175°	730	730	732	730	730	69
180°	732	732	732	732	732	



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	3430.8	3420.0	3409.3	3406.1	3402.9	3392.8	3382.6	3359.8	3336.9	3313.4	3289.9
5°	3661.8	3663.1	3664.4	3661.2	3658.0	3644.7	3631.4	3603.5	3575.5	3545.1	3514.6
7.5°	3590.8	3611.1	3631.4	3635.2	3639.0	3649.2	3659.3	3653.0	3646.6	3635.2	3623.8
10°	3279.8	3278.5	3277.3	3300.1	3322.9	3390.9	3458.8	3493.7	3528.6	3559.7	3590.8
12.5°	2772.1	2774.0	2775.9	2850.8	2925.7	2989.8	3053.9	3142.7	3231.6	3327.4	3423.2
15°	2214.9	2246.0	2277.1	2343.7	2410.3	2506.8	2603.3	2722.6	2841.9	2993.6	3145.3
17.5°	1818.9	1832.2	1845.5	1909.6	1973.7	2065.1	2156.5	2291.7	2426.8	2622.3	2817.8
20°	1499.0	1511.1	1523.1	1569.5	1615.8	1703.4	1790.9	1919.8	2048.6	2242.2	2435.7
22.5°	1251.5	1275.0	1298.5	1329.6	1360.7	1424.1	1487.6	1619.0	1750.3	1926.8	2103.2
25°	1101.7	1112.5	1123.3	1150.0	1176.6	1237.5	1298.5	1385.4	1472.4	1648.1	1823.9
27.5°	1000.2	1003.4	1006.5	1026.2	1045.9	1085.2	1124.6	1205.2	1285.8	1430.5	1575.2
30°	916.4	922.1	927.8	943.1	958.3	986.9	1015.4	1072.5	1129.7	1259.1	1388.6
32.5°	851.7	854.9	858.0	870.7	883.4	904.4	925.3	970.4	1015.4	1114.4	1213.4
35°	795.8	796.5	797.1	806.6	816.1	836.4	856.8	894.2	931.6	1004.6	1077.6
37.5°	732.4	736.8	741.3	748.2	755.2	773.0	790.8	821.2	851.7	912.0	972.3
40°	679.1	682.9	686.7	694.9	703.2	717.1	731.1	759.0	786.9	839.0	891.0
42.5°	625.8	628.3	630.8	639.1	647.3	664.5	681.6	703.8	726.0	769.2	812.3
45°	566.1	572.4	578.8	587.7	596.6	611.2	625.8	648.6	671.4	708.3	745.1
47.5°	516.6	519.8	522.9	530.6	538.2	555.9	573.7	594.0	614.3	648.6	682.9
50°	467.1	468.4	469.6	476.6	483.6	499.5	515.3	538.8	562.3	594.0	625.8
52.5°	420.1	423.3	426.5	433.5	440.4	451.2	462.0	486.1	510.2	541.3	572.4
55°	377.0	378.9	380.8	385.9	390.9	403.6	416.3	437.3	458.2	486.8	515.3
57.5°	336.4	338.9	341.4	345.2	349.0	360.5	371.9	390.3	408.7	437.3	465.8
60°	294.5	297.6	300.8	305.3	309.7	318.6	327.5	344.0	360.5	385.9	411.2
62.5°	264.0	264.6	265.3	269.1	272.9	279.2	285.6	298.9	312.2	337.6	363.0
65°	229.7	231.6	233.5	235.4	237.4	242.4	247.5	258.9	270.4	289.4	308.4
67.5°	194.2	196.1	198.0	201.2	204.4	208.8	213.2	220.9	228.5	246.2	264.0
70°	151.0	151.0	151.0	156.1	161.2	168.8	176.4	182.1	187.9	202.4	217.0
72.5°	123.1	123.8	124.4	125.0	125.7	130.1	134.5	144.1	153.6	162.5	171.4
75°	100.3	100.9	101.5	102.2	102.8	104.1	105.3	108.5	111.7	121.8	132.0
77.5°	80.0	80.6	81.2	81.9	82.5	83.8	85.0	86.3	87.6	91.4	95.2
80°	60.9	61.6	62.2	62.8	63.5	64.1	64.7	66.0	67.3	69.2	71.1
82.5°	44.4	44.4	44.4	44.4	44.4	45.7	47.0	47.0	47.0	48.2	49.5
85°	27.9	27.9	27.9	28.6	29.2	29.2	29.2	29.8	30.5	30.5	30.5
87.5°	12.7	12.1	11.4	12.1	12.7	12.7	12.7	13.3	14.0	14.0	14.0
90°	16.3	16.1	15.8	15.6	15.4	15.0	14.5	14.0	13.5	13.1	11.5
92.5°	18.5	18.4	18.3	18.1	18.0	17.5	16.7	15.8	15.0	14.1	13.1
95°	20.7	20.7	20.7	20.7	20.7	20.3	19.4	18.6	17.7	16.9	15.5
97.5°	22.3	22.2	22.1	21.9	21.8	21.3	20.3	19.3	18.4	17.4	23.6
100°	22.9	22.7	22.6	22.5	22.4	21.8	20.9	19.9	18.9	18.0	36.8
102.5°	23.4	23.2	22.9	22.7	22.4	24.3	28.3	32.3	36.3	40.3	61.3
105°	23.9	23.7	23.5	23.2	23.0	33.6	55.0	76.4	97.8	119.2	130.0
107.5°	56.6	72.4	88.3	104.1	119.9	137.2	155.8	174.4	193.0	211.7	209.8
110°	149.6	166.9	184.2	201.5	218.8	229.4	233.4	237.4	241.4	245.4	244.1



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	283.5	283.7	284.0	284.2	284.5	284.0	282.9	281.9	280.8	279.7	278.3
115°	319.9	319.5	319.0	318.5	318.0	317.2	316.0	314.7	313.5	312.3	311.2
117.5°	349.3	349.2	349.1	349.0	348.8	348.3	347.3	346.4	345.4	344.4	343.8
120°	379.8	379.8	379.8	379.8	379.8	379.3	378.3	377.4	376.4	375.4	375.1
122.5°	409.7	409.6	409.5	409.4	409.2	408.9	408.3	407.7	407.1	406.5	406.0
125°	437.5	437.2	437.0	436.7	436.5	436.3	436.0	435.8	435.5	435.3	434.8
127.5°	464.7	464.9	465.2	465.4	465.6	465.6	465.2	464.9	464.5	464.1	463.5
130°	490.8	491.0	491.3	491.5	491.8	491.6	491.2	490.7	490.2	489.7	489.2
132.5°	514.7	515.1	515.5	515.8	516.2	516.1	515.6	515.2	514.7	514.2	513.8
135°	539.2	539.6	539.9	540.3	540.7	540.7	540.3	539.9	539.6	539.2	538.7
137.5°	562.6	562.9	563.1	563.3	563.6	563.4	562.8	562.2	561.6	561.0	560.7
140°	583.3	583.5	583.8	584.0	584.3	584.1	583.7	583.2	582.7	582.2	581.8
142.5°	602.3	602.7	603.1	603.4	603.8	603.8	603.4	603.1	602.7	602.3	602.0
145°	621.9	621.9	621.9	621.9	621.9	621.8	621.6	621.3	621.1	620.8	620.6
147.5°	636.1	636.7	637.3	637.9	638.5	638.7	638.4	638.2	637.9	637.7	637.5
150°	652.4	652.8	653.1	653.5	653.8	653.9	653.7	653.4	653.2	652.9	652.7
152.5°	665.5	666.1	666.7	667.3	667.9	667.9	667.5	667.0	666.5	666.0	665.9
155°	677.4	678.2	678.9	679.6	680.3	680.4	679.8	679.2	678.6	678.0	677.9
157.5°	687.8	688.7	689.7	690.7	691.6	691.8	691.0	690.3	689.6	688.9	689.0
160°	697.6	698.4	699.3	700.1	700.9	701.0	700.3	699.6	698.8	698.1	698.2
162.5°	706.8	707.5	708.3	709.0	709.7	709.7	708.8	708.0	707.1	706.3	706.4
165°	713.9	714.7	715.6	716.4	717.3	717.2	716.2	715.3	714.3	713.3	713.5
167.5°	719.3	720.3	721.3	722.2	723.2	723.2	722.2	721.3	720.3	719.3	719.3
170°	724.2	725.2	726.2	727.1	728.1	728.1	727.1	726.2	725.2	724.2	724.2
172.5°	726.9	728.0	729.1	730.2	731.3	731.4	730.4	729.4	728.5	727.5	727.4
175°	729.7	730.6	731.6	732.6	733.5	733.6	732.7	731.9	731.1	730.2	730.1
177.5°	730.2	731.4	732.6	733.8	735.0	735.2	734.2	733.2	732.3	731.3	731.2
180°	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	3286.8	3283.6	3253.1	3222.7	3192.8	3163.0	3140.8	3118.6	3081.2	3043.7	3020.2
5°	3490.5	3466.4	3418.1	3369.9	3297.6	3225.2	3164.3	3103.4	3025.9	2948.5	2883.8
7.5°	3604.1	3584.4	3526.0	3467.6	3371.8	3276.0	3180.8	3085.6	2971.4	2857.1	2759.4
10°	3607.3	3623.8	3575.5	3527.3	3419.4	3311.5	3182.1	3052.6	2899.0	2745.4	2619.1
12.5°	3494.3	3565.4	3555.2	3545.1	3435.3	3325.5	3168.1	3010.7	2822.2	2633.7	2475.7
15°	3283.0	3420.7	3461.3	3501.9	3411.2	3320.4	3141.4	2962.5	2741.0	2519.5	2338.0
17.5°	3010.7	3203.6	3310.9	3418.1	3352.1	3286.1	3090.0	2893.9	2644.5	2395.1	2197.7
20°	2688.3	2940.9	3109.1	3277.3	3253.1	3229.0	3026.6	2824.1	2555.0	2286.0	2072.1
22.5°	2369.7	2636.3	2868.6	3100.8	3125.6	3150.3	2946.0	2741.6	2447.2	2152.7	1935.0
25°	2094.9	2365.9	2642.6	2919.3	2975.2	3031.0	2836.8	2642.6	2337.4	2032.1	1815.7
27.5°	1832.8	2090.5	2395.1	2699.7	2801.3	2902.8	2725.1	2547.4	2229.5	1911.5	1695.7
30°	1619.0	1849.3	2160.3	2471.3	2612.8	2754.3	2591.2	2428.1	2112.7	1797.3	1586.0
32.5°	1419.7	1625.9	1938.2	2250.4	2414.8	2579.2	2438.3	2297.4	1994.0	1690.7	1481.9
35°	1262.3	1447.0	1738.3	2029.6	2213.6	2397.7	2282.1	2166.6	1870.3	1573.9	1376.5
37.5°	1127.1	1282.0	1555.5	1829.0	2024.5	2220.0	2123.5	2027.0	1748.4	1469.8	1283.2
40°	1015.4	1139.8	1394.3	1648.8	1840.4	2032.1	1949.6	1867.1	1617.7	1368.3	1193.7
42.5°	919.6	1026.8	1255.3	1483.8	1659.6	1835.4	1780.8	1726.2	1500.3	1274.3	1112.5
45°	835.2	925.3	1126.5	1327.7	1489.5	1651.3	1608.2	1565.0	1370.2	1175.3	1026.8
47.5°	760.3	837.7	1017.3	1196.9	1342.3	1487.6	1447.6	1407.6	1246.4	1085.2	950.0
50°	691.8	757.8	907.5	1057.3	1188.0	1318.8	1285.8	1252.8	1119.5	986.2	869.4
52.5°	627.0	681.6	816.1	950.7	1056.0	1161.4	1136.0	1110.6	1007.8	905.0	799.0
55°	565.5	615.6	729.2	842.8	932.9	1023.0	997.6	972.3	892.3	812.3	719.0
57.5°	509.6	553.4	645.4	737.4	809.2	880.9	868.8	856.8	790.1	723.5	646.7
60°	450.6	489.9	569.3	648.6	706.3	764.1	750.1	736.2	688.6	641.0	575.0
62.5°	397.9	432.8	496.3	559.7	606.7	653.7	643.5	633.4	597.2	561.0	506.4
65°	342.7	377.0	428.4	479.8	516.6	553.4	544.5	535.6	508.3	481.1	437.3
67.5°	292.6	321.1	365.5	410.0	434.7	459.5	454.4	449.3	428.4	407.4	373.2
70°	241.8	266.5	303.4	340.2	357.3	374.4	376.3	378.2	359.2	340.2	314.8
72.5°	191.0	210.7	245.0	279.2	292.6	305.9	305.3	304.6	293.2	281.8	258.9
75°	146.6	161.2	187.9	214.5	225.9	237.4	239.9	242.4	231.6	220.9	208.2
77.5°	105.3	115.5	135.8	156.1	168.8	181.5	182.8	184.0	179.0	173.9	161.8
80°	74.3	77.4	90.1	102.8	116.1	129.5	131.4	133.3	128.2	123.1	115.5
82.5°	51.4	53.3	57.8	62.2	73.0	83.8	86.3	88.8	86.3	83.8	75.5
85°	31.1	31.7	33.6	35.5	40.6	45.7	48.2	50.8	49.5	48.2	43.8
87.5°	14.0	14.0	14.6	15.2	16.5	17.8	20.9	24.1	22.2	20.3	18.4
90°	9.9	8.3	6.8	5.4	4.2	3.0	1.8	0.5	1.8	3.0	4.2
92.5°	12.0	10.9	9.8	9.6	10.3	11.1	11.8	12.5	11.8	11.1	10.3
95°	14.2	12.9	11.5	13.4	18.3	23.3	28.2	33.2	28.2	23.3	18.3
97.5°	29.7	35.9	42.1	46.9	50.2	53.6	57.0	60.4	57.0	53.6	50.2
100°	55.7	74.5	93.4	101.6	99.2	96.8	94.4	92.0	94.4	96.8	99.2
102.5°	82.3	103.4	124.4	134.2	132.6	131.0	129.4	127.9	129.4	131.0	132.6
105°	140.9	151.8	162.7	167.5	166.1	164.8	163.5	162.1	163.5	164.8	166.1
107.5°	208.0	206.2	204.4	203.0	201.9	200.8	199.7	198.6	199.7	200.8	201.9
110°	242.7	241.4	240.1	238.9	238.0	237.0	236.0	235.1	236.0	237.0	238.0





TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.0	275.7	274.4	273.3	272.4	271.6	270.7	269.9	270.7	271.6	272.4
115°	310.1	309.1	308.0	307.1	306.3	305.6	304.9	304.2	304.9	305.6	306.3
117.5°	343.2	342.6	342.0	341.3	340.4	339.6	338.7	337.9	338.7	339.6	340.4
120°	374.7	374.4	374.0	373.3	372.2	371.1	370.0	368.9	370.0	371.1	372.2
122.5°	405.5	405.0	404.5	403.9	403.0	402.2	401.3	400.5	401.3	402.2	403.0
125°	434.3	433.8	433.4	432.6	431.7	430.7	429.7	428.8	429.7	430.7	431.7
127.5°	462.9	462.3	461.7	460.9	460.0	459.0	458.0	457.1	458.0	459.0	460.0
130°	488.7	488.3	487.8	487.0	486.1	485.1	484.1	483.2	484.1	485.1	486.1
132.5°	513.5	513.1	512.7	512.1	511.1	510.1	509.2	508.2	509.2	510.1	511.1
135°	538.3	537.8	537.3	536.7	536.0	535.2	534.5	533.8	534.5	535.2	536.0
137.5°	560.5	560.3	560.0	559.4	558.4	557.5	556.5	555.5	556.5	557.5	558.4
140°	581.5	581.1	580.8	580.2	579.5	578.8	578.0	577.3	578.0	578.8	579.5
142.5°	601.6	601.3	600.9	600.3	599.6	598.9	598.2	597.4	598.2	598.9	599.6
145°	620.4	620.1	619.9	619.3	618.5	617.6	616.8	615.9	616.8	617.6	618.5
147.5°	637.2	637.0	636.7	636.3	635.7	635.1	634.5	633.9	634.5	635.1	635.7
150°	652.5	652.2	652.0	651.7	651.3	650.9	650.6	650.2	650.6	650.9	651.3
152.5°	665.8	665.6	665.5	665.4	665.3	665.2	665.0	664.9	665.0	665.2	665.3
155°	677.7	677.6	677.5	677.5	677.8	678.0	678.3	678.5	678.3	678.0	677.8
157.5°	689.1	689.2	689.3	689.4	689.4	689.4	689.4	689.4	689.4	689.4	689.4
160°	698.3	698.5	698.6	698.7	698.8	699.0	699.1	699.2	699.1	699.0	698.8
162.5°	706.5	706.6	706.8	707.0	707.4	707.7	708.1	708.4	708.1	707.7	707.4
165°	713.6	713.7	713.8	714.1	714.4	714.8	715.2	715.5	715.2	714.8	714.4
167.5°	719.3	719.3	719.3	719.6	720.1	720.5	721.0	721.5	721.0	720.5	720.1
170°	724.2	724.2	724.2	724.5	724.9	725.4	725.9	726.4	725.9	725.4	724.9
172.5°	727.2	727.1	727.0	727.2	727.9	728.5	729.1	729.7	729.1	728.5	727.9
175°	730.0	729.8	729.7	730.0	730.6	731.2	731.8	732.4	731.8	731.2	730.6
177.5°	731.1	730.9	730.8	731.1	731.7	732.3	732.9	733.5	732.9	732.3	731.7
180°	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	2996.7	2960.6	2924.4	2898.4	2872.4	2840.0	2807.6	2806.4	2805.1	2781.0	2756.9
5°	2819.0	2756.2	2693.4	2631.8	2570.3	2508.7	2447.2	2433.2	2419.2	2398.3	2377.3
7.5°	2661.7	2561.4	2461.1	2382.4	2303.7	2242.2	2180.6	2138.7	2096.8	2064.5	2032.1
10°	2492.8	2368.5	2244.1	2148.9	2053.7	1987.0	1920.4	1872.2	1823.9	1801.1	1778.2
12.5°	2317.7	2182.5	2047.3	1954.0	1860.7	1780.8	1700.8	1657.0	1613.2	1581.5	1549.8
15°	2156.5	2011.2	1865.8	1766.8	1667.8	1592.9	1518.0	1474.3	1430.5	1398.7	1367.0
17.5°	2000.4	1853.8	1707.2	1606.9	1506.6	1438.7	1370.8	1328.3	1285.8	1266.1	1246.4
20°	1858.2	1710.3	1562.5	1467.9	1373.4	1306.7	1240.1	1217.2	1194.4	1176.0	1157.6
22.5°	1717.3	1575.2	1433.0	1342.3	1251.5	1203.3	1155.0	1136.6	1118.2	1104.3	1090.3
25°	1599.3	1457.8	1316.2	1236.9	1157.6	1120.1	1082.7	1070.6	1058.6	1044.6	1030.6
27.5°	1480.0	1345.4	1210.9	1147.4	1084.0	1053.5	1023.0	1007.8	992.6	981.1	969.7
30°	1374.6	1250.2	1125.8	1073.2	1020.5	993.8	967.2	950.7	934.2	923.4	912.6
32.5°	1273.1	1162.7	1052.2	1007.2	962.1	936.1	910.1	894.2	878.3	865.6	852.9
35°	1179.2	1083.3	987.5	946.2	905.0	879.0	852.9	837.1	821.2	808.5	795.8
37.5°	1096.6	1009.7	922.8	884.0	845.3	822.5	799.6	783.1	766.6	753.3	740.0
40°	1019.2	942.4	865.6	828.2	790.8	766.0	741.3	726.7	712.1	700.0	687.9
42.5°	950.7	880.2	809.8	773.0	736.2	712.7	689.2	672.1	654.9	648.0	641.0
45°	878.3	816.1	753.9	718.4	682.9	658.1	633.4	618.8	604.2	597.8	591.5
47.5°	814.9	757.1	699.4	664.5	629.6	607.3	585.1	573.7	562.3	553.4	544.5
50°	752.7	696.8	641.0	607.3	573.7	554.7	535.6	521.7	507.7	501.4	495.0
52.5°	693.0	642.3	591.5	557.2	522.9	504.5	486.1	474.1	462.0	448.7	435.4
55°	625.8	581.3	536.9	506.4	476.0	456.9	437.9	423.9	410.0	396.0	382.1
57.5°	569.9	526.1	482.3	455.0	427.7	409.3	390.9	375.7	360.5	349.0	337.6
60°	509.0	470.9	432.8	406.2	379.5	361.7	344.0	329.4	314.8	309.1	303.4
62.5°	451.9	416.3	380.8	357.3	333.8	316.7	299.5	290.0	280.5	276.7	272.9
65°	393.5	363.0	332.5	311.0	289.4	274.8	260.2	255.8	251.3	248.1	245.0
67.5°	338.9	312.9	286.9	267.8	248.8	238.6	228.5	223.4	218.3	214.5	210.7
70°	289.4	266.5	243.7	227.2	210.7	201.2	191.7	187.2	182.8	175.8	168.8
72.5°	236.1	218.3	200.5	187.9	175.2	166.9	158.7	149.8	140.9	134.5	128.2
75°	195.5	177.7	159.9	147.9	135.8	126.3	116.8	113.6	110.4	108.5	106.6
77.5°	149.8	134.5	119.3	109.8	100.3	95.8	91.4	89.5	87.6	86.9	86.3
80°	107.9	95.2	82.5	77.4	72.3	71.1	69.8	68.5	67.3	66.6	66.0
82.5°	67.3	60.9	54.6	53.3	52.0	51.4	50.8	50.1	49.5	48.9	48.2
85°	39.3	36.8	34.3	33.6	33.0	32.4	31.7	31.7	31.7	31.7	31.7
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	15.9	15.2
90°	5.4	6.8	8.3	9.9	11.5	13.1	13.5	14.0	14.5	15.0	15.4
92.5°	9.6	9.8	10.9	12.0	13.1	14.1	15.0	15.8	16.7	17.5	18.0
95°	13.4	11.5	12.9	14.2	15.5	16.9	17.7	18.6	19.4	20.3	20.7
97.5°	46.9	42.1	35.9	29.7	23.6	17.4	18.4	19.3	20.3	21.3	21.8
100°	101.6	93.4	74.5	55.7	36.8	18.0	18.9	19.9	20.9	21.8	22.4
102.5°	134.2	124.4	103.4	82.3	61.3	40.3	36.3	32.3	28.3	24.3	22.4
105°	167.5	162.7	151.8	140.9	130.0	119.2	97.8	76.4	55.0	33.6	23.0
107.5°	203.0	204.4	206.2	208.0	209.8	211.7	193.0	174.4	155.8	137.2	119.9
110°	238.9	240.1	241.4	242.7	244.1	245.4	241.4	237.4	233.4	229.4	218.8



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	273.3	274.4	275.7	277.0	278.3	279.7	280.8	281.9	282.9	284.0	284.5
115°	307.1	308.0	309.1	310.1	311.2	312.3	313.5	314.7	316.0	317.2	318.0
117.5°	341.3	342.0	342.6	343.2	343.8	344.4	345.4	346.4	347.3	348.3	348.8
120°	373.3	374.0	374.4	374.7	375.1	375.4	376.4	377.4	378.3	379.3	379.8
122.5°	403.9	404.5	405.0	405.5	406.0	406.5	407.1	407.7	408.3	408.9	409.2
125°	432.6	433.4	433.8	434.3	434.8	435.3	435.5	435.8	436.0	436.3	436.5
127.5°	460.9	461.7	462.3	462.9	463.5	464.1	464.5	464.9	465.2	465.6	465.6
130°	487.0	487.8	488.3	488.7	489.2	489.7	490.2	490.7	491.2	491.6	491.8
132.5°	512.1	512.7	513.1	513.5	513.8	514.2	514.7	515.2	515.6	516.1	516.2
135°	536.7	537.3	537.8	538.3	538.7	539.2	539.6	539.9	540.3	540.7	540.7
137.5°	559.4	560.0	560.3	560.5	560.7	561.0	561.6	562.2	562.8	563.4	563.6
140°	580.2	580.8	581.1	581.5	581.8	582.2	582.7	583.2	583.7	584.1	584.3
142.5°	600.3	600.9	601.3	601.6	602.0	602.3	602.7	603.1	603.4	603.8	603.8
145°	619.3	619.9	620.1	620.4	620.6	620.8	621.1	621.3	621.6	621.8	621.9
147.5°	636.3	636.7	637.0	637.2	637.5	637.7	637.9	638.2	638.4	638.7	638.5
150°	651.7	652.0	652.2	652.5	652.7	652.9	653.2	653.4	653.7	653.9	653.8
152.5°	665.4	665.5	665.6	665.8	665.9	666.0	666.5	667.0	667.5	667.9	667.9
155°	677.5	677.5	677.6	677.7	677.9	678.0	678.6	679.2	679.8	680.4	680.3
157.5°	689.4	689.3	689.2	689.1	689.0	688.9	689.6	690.3	691.0	691.8	691.6
160°	698.7	698.6	698.5	698.3	698.2	698.1	698.8	699.6	700.3	701.0	700.9
162.5°	707.0	706.8	706.6	706.5	706.4	706.3	707.1	708.0	708.8	709.7	709.7
165°	714.1	713.8	713.7	713.6	713.5	713.3	714.3	715.3	716.2	717.2	717.3
167.5°	719.6	719.3	719.3	719.3	719.3	719.3	720.3	721.3	722.2	723.2	723.2
170°	724.5	724.2	724.2	724.2	724.2	724.2	725.2	726.2	727.1	728.1	728.1
172.5°	727.2	727.0	727.1	727.2	727.4	727.5	728.5	729.4	730.4	731.4	731.3
175°	730.0	729.7	729.8	730.0	730.1	730.2	731.1	731.9	732.7	733.6	733.5
177.5°	731.1	730.8	730.9	731.1	731.2	731.3	732.3	733.2	734.2	735.2	735.0
180°	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4	732.4



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3095.7	3095.7	3095.7	3095.7
2.5°	2750.5	2744.2	2741.6	2739.1
5°	2357.7	2338.0	2333.6	2329.1
7.5°	2023.9	2015.6	1988.3	1961.0
10°	1752.9	1727.5	1716.1	1704.6
12.5°	1526.3	1502.8	1499.0	1495.2
15°	1350.5	1334.0	1328.3	1322.6
17.5°	1235.0	1223.6	1216.6	1209.6
20°	1149.3	1141.1	1136.0	1130.9
22.5°	1084.0	1077.6	1073.8	1070.0
25°	1021.1	1011.6	1008.4	1005.3
27.5°	961.5	953.2	950.0	946.9
30°	905.6	898.6	894.2	889.8
32.5°	844.7	836.4	833.9	831.4
35°	790.8	785.7	783.1	780.6
37.5°	733.6	727.3	723.5	719.7
40°	684.8	681.6	679.7	677.8
42.5°	635.3	629.6	628.9	628.3
45°	585.8	580.1	578.8	577.5
47.5°	539.4	534.4	533.7	533.1
50°	488.0	481.1	476.0	470.9
52.5°	429.0	422.7	418.2	413.8
55°	375.1	368.1	364.3	360.5
57.5°	334.5	331.3	329.4	327.5
60°	301.5	299.5	298.3	297.0
62.5°	271.0	269.1	269.1	269.1
65°	243.1	241.2	239.3	237.4
67.5°	206.9	203.1	202.4	201.8
70°	163.1	157.4	156.8	156.1
72.5°	127.6	126.9	125.7	124.4
75°	105.3	104.1	104.1	104.1
77.5°	85.0	83.8	83.8	83.8
80°	65.4	64.7	65.4	66.0
82.5°	48.2	48.2	47.6	47.0
85°	31.1	30.5	30.5	30.5
87.5°	15.2	15.2	15.2	15.2
90°	15.6	15.8	16.1	16.3
92.5°	18.1	18.3	18.4	18.5
95°	20.7	20.7	20.7	20.7
97.5°	21.9	22.1	22.2	22.3
100°	22.5	22.6	22.7	22.9
102.5°	22.7	22.9	23.2	23.4
105°	23.2	23.5	23.7	23.9
107.5°	104.1	88.3	72.4	56.6
110°	201.5	184.2	166.9	149.6



TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	284.2	284.0	283.7	283.5
115°	318.5	319.0	319.5	319.9
117.5°	349.0	349.1	349.2	349.3
120°	379.8	379.8	379.8	379.8
122.5°	409.4	409.5	409.6	409.7
125°	436.7	437.0	437.2	437.5
127.5°	465.4	465.2	464.9	464.7
130°	491.5	491.3	491.0	490.8
132.5°	515.8	515.5	515.1	514.7
135°	540.3	539.9	539.6	539.2
137.5°	563.3	563.1	562.9	562.6
140°	584.0	583.8	583.5	583.3
142.5°	603.4	603.1	602.7	602.3
145°	621.9	621.9	621.9	621.9
147.5°	637.9	637.3	636.7	636.1
150°	653.5	653.1	652.8	652.4
152.5°	667.3	666.7	666.1	665.5
155°	679.6	678.9	678.2	677.4
157.5°	690.7	689.7	688.7	687.8
160°	700.1	699.3	698.4	697.6
162.5°	709.0	708.3	707.5	706.8
165°	716.4	715.6	714.7	713.9
167.5°	722.2	721.3	720.3	719.3
170°	727.1	726.2	725.2	724.2
172.5°	730.2	729.1	728.0	726.9
175°	732.6	731.6	730.6	729.7
177.5°	733.8	732.6	731.4	730.2
180°	732.4	732.4	732.4	732.4

TEST NUMBER: P831870

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.22	15.15	15.05	16.00	17.05	18.88	19.82	19.71	20.66	21.71
	3H	15.45	16.28	16.29	17.14	18.21	20.39	21.23	21.23	22.08	23.16
	4H	15.83	16.62	16.70	17.48	18.57	20.88	21.67	21.75	22.53	23.62
	6H	16.12	16.85	16.99	17.71	18.81	21.20	21.93	22.07	22.79	23.89
	8H	16.21	16.90	17.09	17.79	18.89	21.28	21.97	22.16	22.86	23.96
	12H	16.27	16.92	17.15	17.80	18.92	21.32	21.97	22.20	22.85	23.98
4H	2H	14.95	15.74	15.82	16.60	17.69	18.89	19.68	19.76	20.54	21.63
	3H	16.33	16.99	17.21	17.88	18.98	20.56	21.21	21.43	22.10	23.21
	4H	16.79	17.39	17.68	18.28	19.41	21.17	21.76	22.06	22.65	23.78
	6H	17.16	17.68	18.07	18.59	19.72	21.61	22.12	22.51	23.04	24.17
	8H	17.29	17.77	18.20	18.68	19.82	21.74	22.22	22.65	23.13	24.27
	12H	17.37	17.80	18.30	18.73	19.88	21.81	22.24	22.73	23.17	24.32
8H	4H	17.11	17.59	18.02	18.50	19.64	21.14	21.62	22.05	22.53	23.67
	6H	17.58	17.97	18.51	18.92	20.07	21.64	22.03	22.57	22.99	24.13
	8H	17.77	18.12	18.71	19.06	20.22	21.83	22.17	22.77	23.12	24.28
	12H	17.92	18.22	18.86	19.16	20.37	21.95	22.25	22.89	23.19	24.40
12H	4H	17.13	17.56	18.05	18.48	19.63	21.10	21.52	22.02	22.45	23.60
	6H	17.64	17.99	18.58	18.93	20.09	21.62	21.96	22.56	22.91	24.07
	8H	17.86	18.17	18.80	19.10	20.31	21.81	22.12	22.76	23.05	24.27