

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331989-840

Luminaire Tested: **S123DIP-S775D1025U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331989-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6759.2 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	47	47	47		
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40	40	40	40	40	40	40		
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33	33	33	33	33	33	33		
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28	28	28	28	28	28	28		
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24	24	24	24		
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21	21	21	21	21	21	21		
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18	18	18	18	18	18	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16	16	16	16	16	16	16		
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15	15	15	15	15	15	15		
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13	13	13	13		
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12	12	12	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	1.7
10°-20°	327.1	4.8
20°-30°	483.2	7.1
30°-40°	564.4	8.4
40°-50°	567.4	8.4
50°-60°	498.4	7.4
60°-70°	371.3	5.5
70°-80°	211.6	3.1
80°-90°	64.5	1.0
90°-100°	83.6	1.2
100°-110°	250.2	3.7
110°-120°	425.6	6.3
120°-130°	559.8	8.3
130°-140°	629.2	9.3
140°-150°	618.5	9.1
150°-160°	520.7	7.7
160°-170°	346.6	5.1
170°-180°	121.4	1.8
0°-30°	926.1	13.7
0°-40°	1490.5	22.1
0°-60°	2556.3	37.8
0°-90°	3203.8	47.4
90°-120°	759.4	11.2
90°-150°	2566.9	38.0
90°-180°	3555.0	52.6
0°-180°	6759.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	11	24	28	30	7
95°	60	67	75	78	79	67
105°	227	229	238	238	240	243
115°	428	431	429	430	429	424
125°	627	630	628	624	620	559
135°	814	819	818	815	812	627
145°	987	989	992	991	987	616
155°	1130	1130	1131	1134	1128	520
165°	1231	1228	1228	1233	1227	347
175°	1280	1276	1276	1282	1275	122
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.2	22.1	21.9	21.8	21.7	21.9	22.2	22.6	23.0	23.4	23.4
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	24.4	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4
95°	59.5	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5
97.5°	105.6	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8
100°	137.1	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9
102.5°	173.4	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3
105°	226.8	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9
107.5°	288.9	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5
110°	327.6	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5



TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	367.9	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6
115°	428.4	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7
117.5°	489.3	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7
120°	527.3	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0
122.5°	566.7	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9
125°	627.0	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1
127.5°	682.7	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6
130°	719.7	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9
132.5°	756.9	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6
135°	813.5	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7
137.5°	866.0	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6
140°	902.2	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.2	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9
145°	986.8	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7
147.5°	1032.1	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5
150°	1063.5	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5
152.5°	1089.3	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7
155°	1130.0	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0
157.5°	1164.7	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3
160°	1186.5	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6
162.5°	1205.9	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0
165°	1230.8	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1
167.5°	1250.8	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0
170°	1262.1	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6
172.5°	1270.9	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3
175°	1280.2	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6
177.5°	1284.0	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	23.4	23.4	23.4	23.4	23.5	23.6	23.7	23.8
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.2	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	76.3	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	118.8	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	149.6	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.0	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.2	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	333.5	334.4	335.3	335.5	335.0	334.6	334.2	333.7



TEST NUMBER: P331989-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	371.7	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.8	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	567.3	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	626.2	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	684.4	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	723.0	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	760.5	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	816.8	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	871.7	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.8	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.7	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.5	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.1	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1132.9	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1166.2	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1186.7	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1206.1	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1230.5	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1269.7	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1278.9	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1283.0	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)