

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832087

Luminaire Tested: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832087  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U950-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5317.8 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 43.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	26				
1	93	89	85	82	83	80	77	74	62	60	58	46	45	44	31	30	30	23				
2	85	78	72	68	76	70	65	61	55	52	49	41	39	37	28	27	26	20				
3	78	69	62	57	69	62	56	52	49	45	42	36	34	32	25	24	23	18				
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20	16				
5	66	55	47	42	58	49	43	38	39	35	31	30	27	24	21	19	18	14				
6	60	49	42	36	54	44	38	33	35	31	27	27	24	21	19	17	16	13				
7	56	44	37	32	50	40	34	29	32	28	24	25	22	19	18	16	14	11				
8	52	40	33	28	46	37	30	26	29	25	22	23	20	17	16	14	13	10				
9	48	37	30	25	43	34	27	23	27	23	19	21	18	16	15	13	12	10				
10	45	34	27	23	40	31	25	21	25	21	18	19	16	14	14	12	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	11408	11408	11408	11408	11408
5°	13545	13113	11479	9280	8616
10°	12272	13319	11423	7436	6379
15°	8450	11420	11302	6077	5046
20°	5879	8793	11074	5125	4435
25°	4480	6701	10745	4555	4087
30°	3899	5358	10332	4228	3786
35°	3581	4519	9746	3954	3511
40°	3267	4036	8982	3684	3260
45°	2950	3691	8156	3430	3009
50°	2678	3406	7182	3180	2699
55°	2423	3126	6247	2935	2316
60°	2170	2844	5425	2665	2189
65°	2004	2524	4671	2397	2071
70°	1627	2181	4076	2168	1681
75°	1426	1734	3452	1797	1481
80°	1296	1469	2827	1506	1401
85°	1186	1284	2149	1371	1284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 8605 cd/sqm



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.6	1.8
10°-20°	223.5	4.2
20°-30°	256.5	4.8
30°-40°	252.8	4.8
40°-50°	222.9	4.2
50°-60°	171.5	3.2
60°-70°	112.8	2.1
70°-80°	54.8	1.0
80°-90°	16.8	0.3
90°-100°	90.8	1.7
100°-110°	274.9	5.2
110°-120°	468.0	8.8
120°-130°	615.7	11.6
130°-140°	692.1	13.0
140°-150°	680.4	12.8
150°-160°	572.8	10.8
160°-170°	381.4	7.2
170°-180°	133.5	2.5
0°-30°	576.6	10.8
0°-40°	829.4	15.6
0°-60°	1223.8	23.0
0°-90°	1408.1	26.5
90°-120°	833.8	15.7
90°-150°	2822.0	53.1
90°-180°	3910.0	73.5
0°-180°	5317.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1060	1060	1060	1060	1060	
5°	1254	1214	1062	859	797	115
15°	758	1025	1014	545	453	214
25°	377	564	905	384	344	178
35°	272	344	742	301	267	170
45°	194	242	536	225	198	150
55°	129	167	333	156	123	116
65°	79	99	183	94	81	77
75°	34	42	83	43	36	37
85°	10	10	17	11	10	10
90°	33	27	1	27	33	16
95°	86	82	65	82	86	87
105°	264	262	249	262	264	280
115°	472	472	471	472	472	468
125°	682	691	689	691	682	610
135°	893	900	894	900	893	687
145°	1085	1091	1085	1091	1085	678
155°	1240	1244	1243	1244	1240	571
165°	1349	1350	1353	1350	1349	381
175°	1402	1403	1408	1403	1402	133
180°	1411	1411	1411	1411	1411	



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1174.5	1170.8	1167.2	1166.1	1165.0	1161.5	1158.0	1150.2	1142.4	1134.3	1126.3
5°	1253.6	1254.1	1254.5	1253.4	1252.3	1247.8	1243.2	1233.6	1224.1	1213.6	1203.2
7.5°	1229.3	1236.2	1243.2	1244.5	1245.8	1249.3	1252.8	1250.6	1248.4	1244.5	1240.6
10°	1122.8	1122.4	1122.0	1129.8	1137.6	1160.9	1184.1	1196.1	1208.0	1218.6	1229.3
12.5°	949.0	949.7	950.3	976.0	1001.6	1023.5	1045.5	1075.9	1106.3	1139.1	1171.9
15°	758.3	768.9	779.6	802.4	825.2	858.2	891.2	932.1	972.9	1024.8	1076.8
17.5°	622.7	627.2	631.8	653.8	675.7	707.0	738.3	784.5	830.8	897.7	964.7
20°	513.2	517.3	521.4	537.3	553.2	583.1	613.1	657.2	701.3	767.6	833.9
22.5°	428.4	436.5	444.5	455.2	465.8	487.5	509.3	554.2	599.2	659.6	720.0
25°	377.2	380.9	384.6	393.7	402.8	423.7	444.5	474.3	504.1	564.2	624.4
27.5°	342.4	343.5	344.6	351.3	358.1	371.5	385.0	412.6	440.2	489.7	539.3
30°	313.7	315.7	317.6	322.9	328.1	337.8	347.6	367.2	386.7	431.1	475.4
32.5°	291.6	292.7	293.7	298.1	302.4	309.6	316.8	332.2	347.6	381.5	415.4
35°	272.5	272.7	272.9	276.1	279.4	286.4	293.3	306.1	318.9	343.9	368.9
37.5°	250.7	252.2	253.8	256.2	258.5	264.6	270.7	281.1	291.6	312.2	332.9
40°	232.5	233.8	235.1	237.9	240.7	245.5	250.3	259.9	269.4	287.2	305.0
42.5°	214.2	215.1	216.0	218.8	221.6	227.5	233.3	240.9	248.6	263.3	278.1
45°	193.8	196.0	198.1	201.2	204.2	209.2	214.2	222.0	229.9	242.5	255.1
47.5°	176.9	177.9	179.0	181.6	184.2	190.3	196.4	203.4	210.3	222.0	233.8
50°	159.9	160.3	160.8	163.2	165.6	171.0	176.4	184.5	192.5	203.4	214.2
52.5°	143.8	144.9	146.0	148.4	150.8	154.5	158.2	166.4	174.7	185.3	196.0
55°	129.1	129.7	130.4	132.1	133.8	138.2	142.5	149.7	156.9	166.6	176.4
57.5°	115.2	116.0	116.9	118.2	119.5	123.4	127.3	133.6	139.9	149.7	159.5
60°	100.8	101.9	103.0	104.5	106.0	109.1	112.1	117.8	123.4	132.1	140.8
62.5°	90.4	90.6	90.8	92.1	93.4	95.6	97.8	102.3	106.9	115.6	124.3
65°	78.7	79.3	80.0	80.6	81.3	83.0	84.7	88.6	92.6	99.1	105.6
67.5°	66.5	67.1	67.8	68.9	70.0	71.5	73.0	75.6	78.2	84.3	90.4
70°	51.7	51.7	51.7	53.4	55.2	57.8	60.4	62.4	64.3	69.3	74.3
72.5°	42.1	42.4	42.6	42.8	43.0	44.5	46.1	49.3	52.6	55.6	58.7
75°	34.3	34.5	34.8	35.0	35.2	35.6	36.1	37.2	38.2	41.7	45.2
77.5°	27.4	27.6	27.8	28.0	28.2	28.7	29.1	29.5	30.0	31.3	32.6
80°	20.9	21.1	21.3	21.5	21.7	21.9	22.2	22.6	23.0	23.7	24.3
82.5°	15.2	15.2	15.2	15.2	15.2	15.6	16.1	16.1	16.1	16.5	16.9
85°	9.6	9.6	9.6	9.8	10.0	10.0	10.0	10.2	10.4	10.4	10.4
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.6	4.8	4.8	4.8
90°	33.3	32.8	32.3	31.8	31.3	30.5	29.6	28.6	27.6	26.6	23.4
92.5°	47.7	48.2	48.6	49.1	49.6	49.5	48.8	48.0	47.3	46.6	45.1
95°	86.5	86.5	86.5	86.5	86.5	86.0	85.0	84.0	83.0	82.0	80.1
97.5°	124.1	124.4	124.6	124.9	125.1	124.6	123.4	122.2	120.9	119.7	118.2
100°	168.5	168.0	167.5	167.0	166.5	165.9	165.2	164.4	163.7	162.9	161.7
102.5°	213.9	214.2	214.4	214.7	214.9	214.7	213.9	213.2	212.5	211.7	210.0
105°	263.8	263.3	262.8	262.3	261.8	261.6	261.6	261.6	261.6	261.6	259.4
107.5°	314.8	315.0	315.3	315.5	315.8	315.5	314.8	314.1	313.3	312.6	311.6
110°	366.9	367.4	367.9	368.4	368.9	368.6	367.6	366.6	365.7	364.7	364.2



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.3	422.3	422.3	422.3	422.3	421.7	420.5	419.2	418.0	416.8	416.8
115°	472.2	472.4	472.7	472.9	473.2	473.2	472.9	472.7	472.4	472.2	472.7
117.5°	523.2	523.9	524.7	525.4	526.1	526.5	526.5	526.5	526.5	526.5	527.0
120°	577.5	578.0	578.5	579.0	579.5	579.8	580.1	580.3	580.6	580.8	582.1
122.5°	629.6	630.3	631.1	631.8	632.5	633.3	634.0	634.8	635.5	636.2	636.7
125°	681.7	682.7	683.7	684.6	685.6	686.6	687.6	688.6	689.6	690.6	691.0
127.5°	733.8	734.8	735.8	736.7	737.7	739.0	740.4	741.9	743.4	744.9	745.4
130°	784.8	786.5	788.2	789.9	791.7	793.0	794.0	795.0	796.0	797.0	797.7
132.5°	838.0	839.2	840.4	841.7	842.9	844.1	845.4	846.6	847.8	849.1	849.6
135°	893.4	893.9	894.4	894.9	895.4	896.1	897.1	898.1	899.1	900.0	900.3
137.5°	942.2	942.9	943.6	944.4	945.1	946.1	947.3	948.6	949.8	951.0	950.3
140°	989.8	991.6	993.3	995.0	996.7	997.7	998.0	998.2	998.5	998.7	998.5
142.5°	1038.6	1039.8	1041.1	1042.3	1043.5	1044.3	1044.5	1044.8	1045.0	1045.3	1044.8
145°	1085.2	1086.1	1087.1	1088.1	1089.1	1089.7	1090.0	1090.2	1090.5	1090.7	1090.0
147.5°	1127.3	1128.8	1130.2	1131.7	1133.2	1133.9	1133.9	1133.9	1133.9	1133.9	1133.2
150°	1167.2	1168.7	1170.1	1171.6	1173.1	1173.8	1173.8	1173.8	1173.8	1173.8	1173.3
152.5°	1206.0	1207.2	1208.4	1209.7	1210.9	1211.3	1210.8	1210.3	1209.8	1209.3	1209.1
155°	1240.3	1242.1	1243.8	1245.5	1247.2	1247.6	1246.6	1245.6	1244.6	1243.7	1243.4
157.5°	1272.5	1274.0	1275.4	1276.9	1278.4	1278.6	1277.7	1276.7	1275.7	1274.7	1274.5
160°	1303.5	1304.5	1305.5	1306.5	1307.5	1307.3	1306.1	1304.9	1303.6	1302.4	1302.4
162.5°	1326.8	1328.5	1330.2	1332.0	1333.7	1333.9	1332.7	1331.5	1330.2	1329.0	1328.8
165°	1349.0	1350.7	1352.4	1354.1	1355.9	1356.0	1354.5	1353.0	1351.6	1350.1	1350.1
167.5°	1368.9	1370.4	1371.9	1373.4	1374.8	1374.8	1373.4	1371.9	1370.4	1368.9	1368.7
170°	1383.3	1385.1	1386.8	1388.5	1390.2	1390.2	1388.5	1386.8	1385.1	1383.3	1383.3
172.5°	1394.4	1396.1	1397.9	1399.6	1401.3	1401.4	1400.0	1398.5	1397.0	1395.5	1395.5
175°	1402.2	1403.9	1405.6	1407.3	1409.1	1409.2	1407.7	1406.2	1404.8	1403.3	1403.3
177.5°	1406.6	1408.3	1410.1	1411.8	1413.5	1413.6	1412.1	1410.7	1409.2	1407.7	1407.7
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1125.2	1124.1	1113.7	1103.3	1093.1	1082.9	1075.3	1067.6	1054.8	1042.0	1034.0
5°	1195.0	1186.7	1170.2	1153.7	1128.9	1104.1	1083.3	1062.4	1035.9	1009.4	987.3
7.5°	1233.9	1227.1	1207.1	1187.1	1154.3	1121.5	1088.9	1056.3	1017.2	978.1	944.7
10°	1234.9	1240.6	1224.1	1207.6	1170.6	1133.7	1089.4	1045.1	992.5	939.9	896.7
12.5°	1196.3	1220.6	1217.1	1213.6	1176.1	1138.5	1084.6	1030.7	966.2	901.7	847.6
15°	1123.9	1171.1	1185.0	1198.9	1167.8	1136.7	1075.5	1014.2	938.4	862.5	800.4
17.5°	1030.7	1096.8	1133.5	1170.2	1147.6	1125.0	1057.9	990.7	905.3	820.0	752.4
20°	920.3	1006.8	1064.4	1122.0	1113.7	1105.5	1036.1	966.8	874.7	782.6	709.4
22.5°	811.3	902.5	982.0	1061.6	1070.0	1078.5	1008.6	938.6	837.8	737.0	662.4
25°	717.2	810.0	904.7	999.4	1018.5	1037.7	971.2	904.7	800.2	695.7	621.6
27.5°	627.5	715.7	820.0	924.3	959.0	993.8	932.9	872.1	763.3	654.4	580.5
30°	554.2	633.1	739.6	846.0	894.5	942.9	887.1	831.3	723.3	615.3	542.9
32.5°	486.0	556.6	663.5	770.4	826.7	883.0	834.7	786.5	682.7	578.8	507.3
35°	432.1	495.4	595.1	694.8	757.8	820.8	781.3	741.7	640.3	538.8	471.3
37.5°	385.9	438.9	532.5	626.2	693.1	760.0	727.0	693.9	598.6	503.2	439.3
40°	347.6	390.2	477.3	564.5	630.1	695.7	667.4	639.2	553.8	468.4	408.7
42.5°	314.8	351.5	429.8	508.0	568.2	628.3	609.6	591.0	513.6	436.3	380.9
45°	285.9	316.8	385.6	454.5	509.9	565.3	550.6	535.8	469.1	402.4	351.5
47.5°	260.3	286.8	348.3	409.8	459.5	509.3	495.6	481.9	426.7	371.5	325.2
50°	236.8	259.4	310.7	362.0	406.7	451.5	440.2	428.9	383.3	337.6	297.7
52.5°	214.7	233.3	279.4	325.5	361.5	397.6	388.9	380.2	345.0	309.8	273.5
55°	193.6	210.7	249.6	288.5	319.4	350.2	341.5	332.9	305.5	278.1	246.2
57.5°	174.5	189.5	221.0	252.5	277.0	301.6	297.4	293.3	270.5	247.7	221.4
60°	154.3	167.7	194.9	222.0	241.8	261.6	256.8	252.0	235.7	219.4	196.8
62.5°	136.2	148.2	169.9	191.6	207.7	223.8	220.3	216.8	204.4	192.1	173.4
65°	117.3	129.1	146.7	164.3	176.9	189.5	186.4	183.4	174.0	164.7	149.7
67.5°	100.2	109.9	125.1	140.4	148.8	157.3	155.6	153.8	146.7	139.5	127.8
70°	82.8	91.3	103.9	116.5	122.3	128.2	128.8	129.5	123.0	116.5	107.8
72.5°	65.4	72.1	83.9	95.6	100.2	104.7	104.5	104.3	100.4	96.5	88.6
75°	50.2	55.2	64.3	73.4	77.3	81.3	82.1	83.0	79.3	75.6	71.3
77.5°	36.1	39.5	46.5	53.4	57.8	62.1	62.6	63.0	61.3	59.5	55.4
80°	25.4	26.5	30.9	35.2	39.8	44.3	45.0	45.6	43.9	42.1	39.5
82.5°	17.6	18.3	19.8	21.3	25.0	28.7	29.5	30.4	29.5	28.7	25.9
85°	10.6	10.9	11.5	12.2	13.9	15.6	16.5	17.4	16.9	16.5	15.0
87.5°	4.8	4.8	5.0	5.2	5.6	6.1	7.2	8.3	7.6	7.0	6.3
90°	20.2	17.0	13.8	11.0	8.5	6.0	3.6	1.1	3.6	6.0	8.5
92.5°	43.6	42.1	40.6	39.2	37.7	36.2	34.7	33.3	34.7	36.2	37.7
95°	78.1	76.1	74.1	72.3	70.6	68.8	67.1	65.4	67.1	68.8	70.6
97.5°	116.8	115.3	113.8	112.4	111.2	110.0	108.7	107.5	108.7	110.0	111.2
100°	160.5	159.2	158.0	156.7	155.2	153.7	152.2	150.7	152.2	153.7	155.2
102.5°	208.3	206.5	204.8	203.6	202.8	202.1	201.4	200.6	201.4	202.1	202.8
105°	257.2	254.9	252.7	251.4	250.9	250.4	249.9	249.4	249.9	250.4	250.9
107.5°	310.6	309.6	308.6	308.0	307.8	307.5	307.3	307.0	307.3	307.5	307.8
110°	363.7	363.2	362.7	362.2	361.7	361.2	360.7	360.2	360.7	361.2	361.7





TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.8	416.8	416.6	416.4	416.2	415.9	415.7	415.9	416.2	416.4
115°	473.2	473.7	474.2	474.0	473.3	472.6	471.8	471.1	471.8	472.6	473.3
117.5°	527.5	528.0	528.5	528.6	528.4	528.1	527.9	527.6	527.9	528.1	528.4
120°	583.3	584.5	585.7	585.6	584.1	582.7	581.2	579.7	581.2	582.7	584.1
122.5°	637.2	637.7	638.2	638.0	637.0	636.0	635.0	634.0	635.0	636.0	637.0
125°	691.5	692.0	692.5	692.4	691.7	690.9	690.2	689.4	690.2	690.9	691.7
127.5°	745.9	746.3	746.8	746.3	744.9	743.4	741.9	740.4	741.9	743.4	744.9
130°	798.4	799.2	799.9	799.3	797.3	795.4	793.4	791.4	793.4	795.4	797.3
132.5°	850.0	850.5	851.0	850.3	848.3	846.4	844.4	842.4	844.4	846.4	848.3
135°	900.5	900.8	901.0	900.4	898.9	897.5	896.0	894.5	896.0	897.5	898.9
137.5°	949.6	948.8	948.1	947.1	945.9	944.6	943.4	942.2	943.4	944.6	945.9
140°	998.2	998.0	997.7	997.0	995.7	994.5	993.3	992.0	993.3	994.5	995.7
142.5°	1044.3	1043.8	1043.3	1042.4	1041.2	1040.0	1038.7	1037.5	1038.7	1040.0	1041.2
145°	1089.2	1088.5	1087.7	1087.1	1086.6	1086.1	1085.7	1085.2	1085.7	1086.1	1086.6
147.5°	1132.5	1131.7	1131.0	1130.1	1129.1	1128.1	1127.2	1126.2	1127.2	1128.1	1129.1
150°	1172.8	1172.4	1171.9	1171.4	1170.9	1170.4	1169.9	1169.4	1169.9	1170.4	1170.9
152.5°	1208.8	1208.6	1208.3	1207.8	1207.1	1206.3	1205.6	1204.9	1205.6	1206.3	1207.1
155°	1243.2	1242.9	1242.7	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6
157.5°	1274.2	1274.0	1273.7	1273.7	1274.0	1274.2	1274.5	1274.7	1274.5	1274.2	1274.0
160°	1302.4	1302.4	1302.4	1302.7	1303.2	1303.6	1304.1	1304.6	1304.1	1303.6	1303.2
162.5°	1328.5	1328.3	1328.0	1328.3	1329.0	1329.8	1330.5	1331.2	1330.5	1329.8	1329.0
165°	1350.1	1350.1	1350.1	1350.4	1351.2	1351.9	1352.7	1353.4	1352.7	1351.9	1351.2
167.5°	1368.4	1368.2	1367.9	1368.3	1369.3	1370.3	1371.3	1372.2	1371.3	1370.3	1369.3
170°	1383.3	1383.3	1383.3	1383.8	1384.8	1385.8	1386.8	1387.8	1386.8	1385.8	1384.8
172.5°	1395.5	1395.5	1395.5	1396.0	1397.0	1398.0	1399.0	1400.0	1399.0	1398.0	1397.0
175°	1403.3	1403.3	1403.3	1403.8	1404.8	1405.7	1406.7	1407.7	1406.7	1405.7	1404.8
177.5°	1407.7	1407.7	1407.7	1408.2	1409.2	1410.2	1411.2	1412.1	1411.2	1410.2	1409.2
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1025.9	1013.5	1001.2	992.3	983.3	972.3	961.2	960.8	960.3	952.1	943.8
5°	965.1	943.6	922.1	901.0	879.9	858.9	837.8	833.0	828.2	821.0	813.9
7.5°	911.2	876.9	842.6	815.6	788.7	767.6	746.5	732.2	717.8	706.8	695.7
10°	853.4	810.8	768.3	735.7	703.1	680.3	657.4	640.9	624.4	616.6	608.8
12.5°	793.5	747.2	700.9	669.0	637.0	609.6	582.3	567.3	552.3	541.4	530.6
15°	738.3	688.5	638.8	604.9	571.0	545.3	519.7	504.7	489.7	478.9	468.0
17.5°	684.8	634.6	584.4	550.1	515.8	492.5	469.3	454.7	440.2	433.4	426.7
20°	636.2	585.5	534.9	502.5	470.2	447.4	424.5	416.7	408.9	402.6	396.3
22.5°	587.9	539.3	490.6	459.5	428.4	411.9	395.4	389.1	382.8	378.0	373.3
25°	547.5	499.1	450.6	423.5	396.3	383.5	370.7	366.5	362.4	357.6	352.8
27.5°	506.7	460.6	414.5	392.8	371.1	360.7	350.2	345.0	339.8	335.9	332.0
30°	470.6	428.0	385.4	367.4	349.4	340.2	331.1	325.5	319.8	316.1	312.4
32.5°	435.8	398.0	360.2	344.8	329.4	320.5	311.6	306.1	300.7	296.4	292.0
35°	403.7	370.9	338.1	323.9	309.8	300.9	292.0	286.6	281.1	276.8	272.5
37.5°	375.4	345.7	315.9	302.7	289.4	281.6	273.8	268.1	262.5	257.9	253.3
40°	348.9	322.6	296.4	283.5	270.7	262.2	253.8	248.8	243.8	239.6	235.5
42.5°	325.5	301.3	277.2	264.6	252.0	244.0	236.0	230.1	224.2	221.8	219.4
45°	300.7	279.4	258.1	245.9	233.8	225.3	216.8	211.8	206.8	204.7	202.5
47.5°	279.0	259.2	239.4	227.5	215.5	207.9	200.3	196.4	192.5	189.5	186.4
50°	257.7	238.6	219.4	207.9	196.4	189.9	183.4	178.6	173.8	171.6	169.5
52.5°	237.3	219.9	202.5	190.8	179.0	172.7	166.4	162.3	158.2	153.6	149.0
55°	214.2	199.0	183.8	173.4	162.9	156.4	149.9	145.1	140.4	135.6	130.8
57.5°	195.1	180.1	165.1	155.8	146.4	140.1	133.8	128.6	123.4	119.5	115.6
60°	174.2	161.2	148.2	139.1	129.9	123.8	117.8	112.8	107.8	105.8	103.9
62.5°	154.7	142.5	130.4	122.3	114.3	108.4	102.5	99.3	96.0	94.7	93.4
65°	134.7	124.3	113.8	106.5	99.1	94.1	89.1	87.6	86.0	85.0	83.9
67.5°	116.0	107.1	98.2	91.7	85.2	81.7	78.2	76.5	74.7	73.4	72.1
70°	99.1	91.3	83.4	77.8	72.1	68.9	65.6	64.1	62.6	60.2	57.8
72.5°	80.8	74.7	68.7	64.3	60.0	57.1	54.3	51.3	48.2	46.1	43.9
75°	66.9	60.8	54.8	50.6	46.5	43.2	40.0	38.9	37.8	37.2	36.5
77.5°	51.3	46.1	40.8	37.6	34.3	32.8	31.3	30.6	30.0	29.8	29.5
80°	36.9	32.6	28.2	26.5	24.8	24.3	23.9	23.5	23.0	22.8	22.6
82.5°	23.0	20.9	18.7	18.3	17.8	17.6	17.4	17.2	16.9	16.7	16.5
85°	13.5	12.6	11.7	11.5	11.3	11.1	10.9	10.9	10.9	10.9	10.9
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	11.0	13.8	17.0	20.2	23.4	26.6	27.6	28.6	29.6	30.5	31.3
92.5°	39.2	40.6	42.1	43.6	45.1	46.6	47.3	48.0	48.8	49.5	49.6
95°	72.3	74.1	76.1	78.1	80.1	82.0	83.0	84.0	85.0	86.0	86.5
97.5°	112.4	113.8	115.3	116.8	118.2	119.7	120.9	122.2	123.4	124.6	125.1
100°	156.7	158.0	159.2	160.5	161.7	162.9	163.7	164.4	165.2	165.9	166.5
102.5°	203.6	204.8	206.5	208.3	210.0	211.7	212.5	213.2	213.9	214.7	214.9
105°	251.4	252.7	254.9	257.2	259.4	261.6	261.6	261.6	261.6	261.6	261.8
107.5°	308.0	308.6	309.6	310.6	311.6	312.6	313.3	314.1	314.8	315.5	315.8
110°	362.2	362.7	363.2	363.7	364.2	364.7	365.7	366.6	367.6	368.6	368.9



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.6	416.8	416.8	416.8	416.8	416.8	418.0	419.2	420.5	421.7	422.3
115°	474.0	474.2	473.7	473.2	472.7	472.2	472.4	472.7	472.9	473.2	473.2
117.5°	528.6	528.5	528.0	527.5	527.0	526.5	526.5	526.5	526.5	526.5	526.1
120°	585.6	585.7	584.5	583.3	582.1	580.8	580.6	580.3	580.1	579.8	579.5
122.5°	638.0	638.2	637.7	637.2	636.7	636.2	635.5	634.8	634.0	633.3	632.5
125°	692.4	692.5	692.0	691.5	691.0	690.6	689.6	688.6	687.6	686.6	685.6
127.5°	746.3	746.8	746.3	745.9	745.4	744.9	743.4	741.9	740.4	739.0	737.7
130°	799.3	799.9	799.2	798.4	797.7	797.0	796.0	795.0	794.0	793.0	791.7
132.5°	850.3	851.0	850.5	850.0	849.6	849.1	847.8	846.6	845.4	844.1	842.9
135°	900.4	901.0	900.8	900.5	900.3	900.0	899.1	898.1	897.1	896.1	895.4
137.5°	947.1	948.1	948.8	949.6	950.3	951.0	949.8	948.6	947.3	946.1	945.1
140°	997.0	997.7	998.0	998.2	998.5	998.7	998.5	998.2	998.0	997.7	996.7
142.5°	1042.4	1043.3	1043.8	1044.3	1044.8	1045.3	1045.0	1044.8	1044.5	1044.3	1043.5
145°	1087.1	1087.7	1088.5	1089.2	1090.0	1090.7	1090.5	1090.2	1090.0	1089.7	1089.1
147.5°	1130.1	1131.0	1131.7	1132.5	1133.2	1133.9	1133.9	1133.9	1133.9	1133.9	1133.2
150°	1171.4	1171.9	1172.4	1172.8	1173.3	1173.8	1173.8	1173.8	1173.8	1173.8	1173.1
152.5°	1207.8	1208.3	1208.6	1208.8	1209.1	1209.3	1209.8	1210.3	1210.8	1211.3	1210.9
155°	1242.6	1242.7	1242.9	1243.2	1243.4	1243.7	1244.6	1245.6	1246.6	1247.6	1247.2
157.5°	1273.7	1273.7	1274.0	1274.2	1274.5	1274.7	1275.7	1276.7	1277.7	1278.6	1278.4
160°	1302.7	1302.4	1302.4	1302.4	1302.4	1302.4	1303.6	1304.9	1306.1	1307.3	1307.5
162.5°	1328.3	1328.0	1328.3	1328.5	1328.8	1329.0	1330.2	1331.5	1332.7	1333.9	1333.7
165°	1350.4	1350.1	1350.1	1350.1	1350.1	1350.1	1351.6	1353.0	1354.5	1356.0	1355.9
167.5°	1368.3	1367.9	1368.2	1368.4	1368.7	1368.9	1370.4	1371.9	1373.4	1374.8	1374.8
170°	1383.8	1383.3	1383.3	1383.3	1383.3	1383.3	1385.1	1386.8	1388.5	1390.2	1390.2
172.5°	1396.0	1395.5	1395.5	1395.5	1395.5	1395.5	1397.0	1398.5	1400.0	1401.4	1401.3
175°	1403.8	1403.3	1403.3	1403.3	1403.3	1403.3	1404.8	1406.2	1407.7	1409.2	1409.1
177.5°	1408.2	1407.7	1407.7	1407.7	1407.7	1407.7	1409.2	1410.7	1412.1	1413.6	1413.5
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1059.8	1059.8	1059.8	1059.8
2.5°	941.6	939.5	938.6	937.7
5°	807.1	800.4	798.9	797.4
7.5°	692.9	690.0	680.7	671.4
10°	600.1	591.4	587.5	583.6
12.5°	522.5	514.5	513.2	511.9
15°	462.3	456.7	454.7	452.8
17.5°	422.8	418.9	416.5	414.1
20°	393.5	390.6	388.9	387.2
22.5°	371.1	368.9	367.6	366.3
25°	349.6	346.3	345.2	344.1
27.5°	329.2	326.3	325.2	324.2
30°	310.0	307.6	306.1	304.6
32.5°	289.2	286.4	285.5	284.6
35°	270.7	269.0	268.1	267.2
37.5°	251.2	249.0	247.7	246.4
40°	234.4	233.3	232.7	232.0
42.5°	217.5	215.5	215.3	215.1
45°	200.5	198.6	198.1	197.7
47.5°	184.7	182.9	182.7	182.5
50°	167.1	164.7	162.9	161.2
52.5°	146.9	144.7	143.2	141.7
55°	128.4	126.0	124.7	123.4
57.5°	114.5	113.4	112.8	112.1
60°	103.2	102.5	102.1	101.7
62.5°	92.8	92.1	92.1	92.1
65°	83.2	82.6	81.9	81.3
67.5°	70.8	69.5	69.3	69.1
70°	55.8	53.9	53.7	53.4
72.5°	43.7	43.5	43.0	42.6
75°	36.1	35.6	35.6	35.6
77.5°	29.1	28.7	28.7	28.7
80°	22.4	22.2	22.4	22.6
82.5°	16.5	16.5	16.3	16.1
85°	10.6	10.4	10.4	10.4
87.5°	5.2	5.2	5.2	5.2
90°	31.8	32.3	32.8	33.3
92.5°	49.1	48.6	48.2	47.7
95°	86.5	86.5	86.5	86.5
97.5°	124.9	124.6	124.4	124.1
100°	167.0	167.5	168.0	168.5
102.5°	214.7	214.4	214.2	213.9
105°	262.3	262.8	263.3	263.8
107.5°	315.5	315.3	315.0	314.8
110°	368.4	367.9	367.4	366.9



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	422.3	422.3	422.3	422.3
115°	472.9	472.7	472.4	472.2
117.5°	525.4	524.7	523.9	523.2
120°	579.0	578.5	578.0	577.5
122.5°	631.8	631.1	630.3	629.6
125°	684.6	683.7	682.7	681.7
127.5°	736.7	735.8	734.8	733.8
130°	789.9	788.2	786.5	784.8
132.5°	841.7	840.4	839.2	838.0
135°	894.9	894.4	893.9	893.4
137.5°	944.4	943.6	942.9	942.2
140°	995.0	993.3	991.6	989.8
142.5°	1042.3	1041.1	1039.8	1038.6
145°	1088.1	1087.1	1086.1	1085.2
147.5°	1131.7	1130.2	1128.8	1127.3
150°	1171.6	1170.1	1168.7	1167.2
152.5°	1209.7	1208.4	1207.2	1206.0
155°	1245.5	1243.8	1242.1	1240.3
157.5°	1276.9	1275.4	1274.0	1272.5
160°	1306.5	1305.5	1304.5	1303.5
162.5°	1332.0	1330.2	1328.5	1326.8
165°	1354.1	1352.4	1350.7	1349.0
167.5°	1373.4	1371.9	1370.4	1368.9
170°	1388.5	1386.8	1385.1	1383.3
172.5°	1399.6	1397.9	1396.1	1394.4
175°	1407.3	1405.6	1403.9	1402.2
177.5°	1411.8	1410.1	1408.3	1406.6
180°	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P832087

CATALOG NUMBER: S123RDIP-S340D1195U950-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.45	7.11	7.59	8.23	9.81	11.11	11.77	12.25	12.90	14.47
	3H	7.65	8.24	8.80	9.38	10.97	12.60	13.19	13.75	14.32	15.91
	4H	8.03	8.59	9.19	9.72	11.32	13.08	13.64	14.24	14.77	16.37
	6H	8.30	8.82	9.47	9.95	11.56	13.38	13.90	14.55	15.03	16.64
	8H	8.38	8.87	9.55	10.03	11.62	13.46	13.94	14.63	15.10	16.70
	12H	8.43	8.89	9.60	10.04	11.66	13.48	13.95	14.66	15.09	16.71
4H	2H	7.15	7.71	8.32	8.84	10.44	11.08	11.64	12.25	12.78	14.38
	3H	8.50	8.97	9.67	10.13	11.74	12.73	13.19	13.90	14.36	15.96
	4H	8.95	9.38	10.13	10.53	12.16	13.33	13.76	14.50	14.91	16.53
	6H	9.31	9.68	10.49	10.85	12.47	13.76	14.12	14.94	15.30	16.91
	8H	9.43	9.78	10.61	10.94	12.57	13.89	14.23	15.06	15.39	17.02
	12H	9.50	9.81	10.70	10.99	12.63	13.94	14.25	15.13	15.42	17.06
8H	4H	9.25	9.60	10.43	10.76	12.39	13.28	13.63	14.46	14.79	16.42
	6H	9.71	9.99	10.91	11.20	12.83	13.77	14.06	14.97	15.26	16.89
	8H	9.91	10.15	11.11	11.34	12.99	13.96	14.20	15.16	15.39	17.04
	12H	10.04	10.26	11.25	11.44	13.12	14.07	14.28	15.27	15.47	17.15
12H	4H	9.26	9.57	10.45	10.74	12.38	13.23	13.54	14.42	14.71	16.35
	6H	9.77	10.02	10.97	11.20	12.85	13.75	13.99	14.95	15.18	16.83
	8H	9.98	10.20	11.19	11.38	13.06	13.93	14.15	15.14	15.33	17.01