

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331992-840

Luminaire Tested: **S123DIP-S775D1195U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331992-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D1195U840-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7436.3 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	88	85	82	79	71	68	66	57	56	55	45	44	43	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32				
3	81	71	64	59	74	66	60	55	55	50	47	45	42	39	36	34	32	27				
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	27	24				
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13				
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.5	1.4
10°-20°	344.7	4.6
20°-30°	578.5	7.8
30°-40°	655.0	8.8
40°-50°	587.4	7.9
50°-60°	474.0	6.4
60°-70°	330.3	4.4
70°-80°	173.6	2.3
80°-90°	46.9	0.6
90°-100°	97.3	1.3
100°-110°	291.2	3.9
110°-120°	495.4	6.7
120°-130°	651.6	8.8
130°-140°	732.3	9.8
140°-150°	719.9	9.7
150°-160°	606.0	8.1
160°-170°	403.4	5.4
170°-180°	141.3	1.9
0°-30°	1030.6	13.9
0°-40°	1685.7	22.7
0°-60°	2747.1	36.9
0°-90°	3297.9	44.3
90°-120°	883.9	11.9
90°-150°	2987.7	40.2
90°-180°	4138.0	55.6
0°-180°	7436.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	42
90°	35	1	35	1	35	19
95°	92	69	92	69	92	94
105°	279	264	279	264	279	296
115°	500	499	500	499	500	495
125°	722	730	722	730	722	645
135°	946	947	946	947	946	727
145°	1149	1149	1149	1149	1149	717
155°	1313	1315	1313	1315	1313	605
165°	1428	1433	1428	1433	1428	403
175°	1484	1490	1484	1490	1484	141
180°	1494	1494	1494	1494	1494	



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	19.7	18.8	19.1	19.4	18.9	19.2	19.4	19.6	19.8	20.0	19.8
90°	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.3	29.2	28.2	24.7
92.5°	47.4	47.7	48.1	48.4	48.7	48.4	47.6	46.8	45.8	45.0	43.1
95°	91.5	91.5	91.5	91.5	91.5	91.0	90.0	88.9	87.9	86.8	84.7
97.5°	140.8	140.9	141.0	141.1	141.2	140.7	139.5	138.3	137.0	135.8	134.3
100°	178.3	177.8	177.3	176.8	176.2	175.6	174.8	174.0	173.3	172.5	171.2
102.5°	216.8	216.9	217.0	217.1	217.2	216.9	216.1	215.3	214.6	213.8	212.1
105°	279.2	278.7	278.2	277.7	277.2	276.9	276.9	276.9	276.9	276.9	274.6
107.5°	344.3	344.6	344.9	345.2	345.5	345.3	344.5	343.6	342.7	341.9	340.9
110°	388.4	388.9	389.4	389.9	390.4	390.2	389.2	388.1	387.1	386.1	385.5



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	435.4	435.5	435.6	435.7	435.8	435.2	433.9	432.6	431.4	430.1	430.0
115°	499.9	500.1	500.4	500.6	500.9	500.9	500.6	500.4	500.1	499.9	500.4
117.5°	565.3	566.0	566.7	567.5	568.3	568.7	568.7	568.8	568.8	568.9	569.6
120°	611.3	611.9	612.4	612.9	613.4	613.8	614.1	614.3	614.6	614.8	616.1
122.5°	655.4	656.1	656.9	657.6	658.3	659.0	659.7	660.5	661.1	661.8	662.5
125°	721.6	722.7	723.7	724.8	725.8	726.8	727.9	728.9	729.9	731.0	731.5
127.5°	787.6	788.7	789.9	791.1	792.3	793.7	795.2	796.6	798.1	799.5	800.1
130°	830.7	832.5	834.4	836.2	838.0	839.5	840.5	841.5	842.6	843.6	844.4
132.5°	875.8	877.2	878.6	880.0	881.4	882.7	884.0	885.2	886.5	887.8	888.3
135°	945.7	946.2	946.7	947.3	947.8	948.6	949.6	950.7	951.7	952.7	953.0
137.5°	1007.4	1008.5	1009.5	1010.4	1011.4	1012.4	1013.5	1014.6	1015.7	1016.8	1016.1
140°	1047.8	1049.7	1051.5	1053.3	1055.1	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9
142.5°	1089.1	1090.6	1091.9	1093.3	1094.7	1095.6	1095.8	1096.1	1096.3	1096.6	1096.1
145°	1148.7	1149.7	1150.7	1151.9	1152.9	1153.6	1153.8	1154.1	1154.3	1154.6	1153.8
147.5°	1201.7	1203.3	1204.9	1206.4	1208.0	1208.8	1208.8	1208.8	1208.8	1208.8	1208.0
150°	1235.6	1237.1	1238.7	1240.2	1241.8	1242.5	1242.5	1242.5	1242.5	1242.5	1242.0
152.5°	1268.4	1269.7	1271.1	1272.4	1273.8	1274.2	1273.8	1273.4	1273.0	1272.6	1272.3
155°	1312.9	1314.8	1316.7	1318.5	1320.3	1320.7	1319.6	1318.6	1317.6	1316.5	1316.3
157.5°	1353.5	1355.0	1356.5	1358.0	1359.4	1359.6	1358.5	1357.4	1356.3	1355.2	1355.0
160°	1379.9	1380.9	1381.9	1383.0	1384.0	1383.9	1382.6	1381.3	1380.0	1378.7	1378.7
162.5°	1399.6	1401.2	1402.9	1404.5	1406.2	1406.4	1405.1	1403.8	1402.5	1401.2	1401.0
165°	1427.9	1429.8	1431.6	1433.4	1435.2	1435.4	1433.8	1432.3	1430.7	1429.2	1429.2
167.5°	1452.1	1453.7	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1	1451.9
170°	1464.3	1466.1	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3	1464.3
172.5°	1473.7	1475.5	1477.3	1479.1	1481.1	1481.2	1479.6	1477.9	1476.3	1474.7	1474.7
175°	1484.3	1486.1	1487.9	1489.8	1491.6	1491.7	1490.2	1488.5	1487.0	1485.4	1485.4
177.5°	1490.0	1491.4	1492.8	1494.3	1495.7	1495.8	1494.6	1493.4	1492.1	1490.9	1490.9
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	19.9	19.7	17.8	15.5	14.0	12.3	11.7	10.4	10.1	10.6	10.7
90°	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2	3.7	6.4	9.0
92.5°	41.2	39.3	37.4	35.4	33.7	31.9	30.2	28.4	30.2	31.9	33.7
95°	82.6	80.6	78.5	76.5	74.7	72.9	71.1	69.3	71.1	72.9	74.7
97.5°	132.9	131.4	129.9	128.4	127.0	125.7	124.3	123.0	124.3	125.7	127.0
100°	169.9	168.5	167.2	165.8	164.3	162.7	161.2	159.6	161.2	162.7	164.3
102.5°	210.4	208.6	206.9	205.6	204.6	203.7	202.8	201.8	202.8	203.7	204.6
105°	272.3	269.8	267.5	266.1	265.6	265.1	264.5	264.0	264.5	265.1	265.6
107.5°	340.0	339.1	338.2	337.5	337.2	336.9	336.6	336.3	336.6	336.9	337.2
110°	385.0	384.5	384.0	383.4	382.9	382.3	381.8	381.3	381.8	382.3	382.9





TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	429.9	429.8	429.7	429.5	429.2	428.9	428.6	428.3	428.6	428.9	429.2
115°	500.9	501.4	501.9	501.8	501.0	500.2	499.5	498.7	499.5	500.2	501.0
117.5°	570.2	570.9	571.6	571.6	571.1	570.6	570.1	569.6	570.1	570.6	571.1
120°	617.4	618.7	620.1	620.0	618.3	616.8	615.2	613.7	615.2	616.8	618.3
122.5°	663.1	663.8	664.5	664.3	663.1	662.0	660.8	659.6	660.8	662.0	663.1
125°	732.1	732.6	733.1	733.0	732.2	731.3	730.6	729.8	730.6	731.3	732.2
127.5°	800.6	801.2	801.8	801.2	799.6	797.9	796.3	794.6	796.3	797.9	799.6
130°	845.2	846.0	846.8	846.1	844.0	841.9	839.8	837.8	839.8	841.9	844.0
132.5°	888.9	889.5	890.1	889.3	887.2	885.1	883.0	880.9	883.0	885.1	887.2
135°	953.3	953.5	953.8	953.1	951.6	950.0	948.5	946.8	948.5	950.0	951.6
137.5°	1015.4	1014.8	1014.1	1013.1	1011.8	1010.5	1009.2	1007.9	1009.2	1010.5	1011.8
140°	1056.6	1056.4	1056.1	1055.3	1054.1	1052.8	1051.5	1050.2	1051.5	1052.8	1054.1
142.5°	1095.7	1095.2	1094.7	1093.9	1092.6	1091.3	1089.9	1088.6	1089.9	1091.3	1092.6
145°	1153.0	1152.3	1151.4	1150.7	1150.2	1149.7	1149.2	1148.7	1149.2	1149.7	1150.2
147.5°	1207.3	1206.6	1205.9	1205.1	1204.1	1203.2	1202.2	1201.2	1202.2	1203.2	1204.1
150°	1241.5	1241.0	1240.5	1240.0	1239.4	1238.9	1238.4	1237.9	1238.4	1238.9	1239.4
152.5°	1272.0	1271.6	1271.3	1270.8	1270.1	1269.4	1268.7	1267.9	1268.7	1269.4	1270.1
155°	1316.0	1315.8	1315.5	1315.3	1315.3	1315.3	1315.3	1315.3	1315.3	1315.3	1315.3
157.5°	1354.8	1354.6	1354.3	1354.4	1354.7	1355.0	1355.3	1355.6	1355.3	1355.0	1354.7
160°	1378.7	1378.7	1378.7	1379.0	1379.5	1380.0	1380.5	1381.0	1380.5	1380.0	1379.5
162.5°	1400.8	1400.6	1400.4	1400.7	1401.4	1402.1	1402.8	1403.5	1402.8	1402.1	1401.4
165°	1429.2	1429.2	1429.2	1429.6	1430.3	1431.1	1431.9	1432.7	1431.9	1431.1	1430.3
167.5°	1451.7	1451.5	1451.3	1451.7	1452.8	1453.8	1454.8	1455.9	1454.8	1453.8	1452.8
170°	1464.3	1464.3	1464.3	1464.8	1465.9	1466.9	1467.9	1469.1	1467.9	1466.9	1465.9
172.5°	1474.7	1474.7	1474.7	1475.2	1476.2	1477.2	1478.3	1479.4	1478.3	1477.2	1476.2
175°	1485.4	1485.4	1485.4	1486.0	1487.0	1488.0	1489.1	1490.2	1489.1	1488.0	1487.0
177.5°	1490.9	1490.9	1490.9	1491.3	1492.1	1493.0	1493.8	1494.6	1493.8	1493.0	1492.1
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	10.8	11.8	12.0	13.1	13.4	14.5	14.7	14.0	14.3	15.8	14.2
90°	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.3	31.3	32.3	33.1
92.5°	35.4	37.4	39.3	41.2	43.1	45.0	45.8	46.8	47.6	48.4	48.7
95°	76.5	78.5	80.6	82.6	84.7	86.8	87.9	88.9	90.0	91.0	91.5
97.5°	128.4	129.9	131.4	132.9	134.3	135.8	137.0	138.3	139.5	140.7	141.2
100°	165.8	167.2	168.5	169.9	171.2	172.5	173.3	174.0	174.8	175.6	176.2
102.5°	205.6	206.9	208.6	210.4	212.1	213.8	214.6	215.3	216.1	216.9	217.2
105°	266.1	267.5	269.8	272.3	274.6	276.9	276.9	276.9	276.9	276.9	277.2
107.5°	337.5	338.2	339.1	340.0	340.9	341.9	342.7	343.6	344.5	345.3	345.5
110°	383.4	384.0	384.5	385.0	385.5	386.1	387.1	388.1	389.2	390.2	390.4



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	429.5	429.7	429.8	429.9	430.0	430.1	431.4	432.6	433.9	435.2	435.8
115°	501.8	501.9	501.4	500.9	500.4	499.9	500.1	500.4	500.6	500.9	500.9
117.5°	571.6	571.6	570.9	570.2	569.6	568.9	568.8	568.8	568.7	568.7	568.3
120°	620.0	620.1	618.7	617.4	616.1	614.8	614.6	614.3	614.1	613.8	613.4
122.5°	664.3	664.5	663.8	663.1	662.5	661.8	661.1	660.5	659.7	659.0	658.3
125°	733.0	733.1	732.6	732.1	731.5	731.0	729.9	728.9	727.9	726.8	725.8
127.5°	801.2	801.8	801.2	800.6	800.1	799.5	798.1	796.6	795.2	793.7	792.3
130°	846.1	846.8	846.0	845.2	844.4	843.6	842.6	841.5	840.5	839.5	838.0
132.5°	889.3	890.1	889.5	888.9	888.3	887.8	886.5	885.2	884.0	882.7	881.4
135°	953.1	953.8	953.5	953.3	953.0	952.7	951.7	950.7	949.6	948.6	947.8
137.5°	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7	1014.6	1013.5	1012.4	1011.4
140°	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9	1056.6	1056.4	1056.1	1055.1
142.5°	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3	1096.1	1095.8	1095.6	1094.7
145°	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3	1154.1	1153.8	1153.6	1152.9
147.5°	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8	1208.8	1208.8	1208.8	1208.0
150°	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5	1242.5	1242.5	1242.5	1241.8
152.5°	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0	1273.4	1273.8	1274.2	1273.8
155°	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6	1318.6	1319.6	1320.7	1320.3
157.5°	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3	1357.4	1358.5	1359.6	1359.4
160°	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0	1381.3	1382.6	1383.9	1384.0
162.5°	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5	1403.8	1405.1	1406.4	1406.2
165°	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7	1432.3	1433.8	1435.4	1435.2
167.5°	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7	1455.3	1456.9	1458.5	1458.5
170°	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1	1467.9	1469.9	1471.7	1471.7
172.5°	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3	1477.9	1479.6	1481.2	1481.1
175°	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0	1488.5	1490.2	1491.7	1491.6
177.5°	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1	1493.4	1494.6	1495.8	1495.7
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	14.3	14.4	14.1	13.8	14.1	14.4	14.3	14.2	15.8	14.3	14.0
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.3
92.5°	48.4	48.1	47.7	47.4	47.7	48.1	48.4	48.7	48.4	47.6	46.8
95°	91.5	91.5	91.5	91.5	91.5	91.5	91.5	91.5	91.0	90.0	88.9
97.5°	141.1	141.0	140.9	140.8	140.9	141.0	141.1	141.2	140.7	139.5	138.3
100°	176.8	177.3	177.8	178.3	177.8	177.3	176.8	176.2	175.6	174.8	174.0
102.5°	217.1	217.0	216.9	216.8	216.9	217.0	217.1	217.2	216.9	216.1	215.3
105°	277.7	278.2	278.7	279.2	278.7	278.2	277.7	277.2	276.9	276.9	276.9
107.5°	345.2	344.9	344.6	344.3	344.6	344.9	345.2	345.5	345.3	344.5	343.6
110°	389.9	389.4	388.9	388.4	388.9	389.4	389.9	390.4	390.2	389.2	388.1



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	435.7	435.6	435.5	435.4	435.5	435.6	435.7	435.8	435.2	433.9	432.6
115°	500.6	500.4	500.1	499.9	500.1	500.4	500.6	500.9	500.9	500.6	500.4
117.5°	567.5	566.7	566.0	565.3	566.0	566.7	567.5	568.3	568.7	568.7	568.8
120°	612.9	612.4	611.9	611.3	611.9	612.4	612.9	613.4	613.8	614.1	614.3
122.5°	657.6	656.9	656.1	655.4	656.1	656.9	657.6	658.3	659.0	659.7	660.5
125°	724.8	723.7	722.7	721.6	722.7	723.7	724.8	725.8	726.8	727.9	728.9
127.5°	791.1	789.9	788.7	787.6	788.7	789.9	791.1	792.3	793.7	795.2	796.6
130°	836.2	834.4	832.5	830.7	832.5	834.4	836.2	838.0	839.5	840.5	841.5
132.5°	880.0	878.6	877.2	875.8	877.2	878.6	880.0	881.4	882.7	884.0	885.2
135°	947.3	946.7	946.2	945.7	946.2	946.7	947.3	947.8	948.6	949.6	950.7
137.5°	1010.4	1009.5	1008.5	1007.4	1008.5	1009.5	1010.4	1011.4	1012.4	1013.5	1014.6
140°	1053.3	1051.5	1049.7	1047.8	1049.7	1051.5	1053.3	1055.1	1056.1	1056.4	1056.6
142.5°	1093.3	1091.9	1090.6	1089.1	1090.6	1091.9	1093.3	1094.7	1095.6	1095.8	1096.1
145°	1151.9	1150.7	1149.7	1148.7	1149.7	1150.7	1151.9	1152.9	1153.6	1153.8	1154.1
147.5°	1206.4	1204.9	1203.3	1201.7	1203.3	1204.9	1206.4	1208.0	1208.8	1208.8	1208.8
150°	1240.2	1238.7	1237.1	1235.6	1237.1	1238.7	1240.2	1241.8	1242.5	1242.5	1242.5
152.5°	1272.4	1271.1	1269.7	1268.4	1269.7	1271.1	1272.4	1273.8	1274.2	1273.8	1273.4
155°	1318.5	1316.7	1314.8	1312.9	1314.8	1316.7	1318.5	1320.3	1320.7	1319.6	1318.6
157.5°	1358.0	1356.5	1355.0	1353.5	1355.0	1356.5	1358.0	1359.4	1359.6	1358.5	1357.4
160°	1383.0	1381.9	1380.9	1379.9	1380.9	1381.9	1383.0	1384.0	1383.9	1382.6	1381.3
162.5°	1404.5	1402.9	1401.2	1399.6	1401.2	1402.9	1404.5	1406.2	1406.4	1405.1	1403.8
165°	1433.4	1431.6	1429.8	1427.9	1429.8	1431.6	1433.4	1435.2	1435.4	1433.8	1432.3
167.5°	1456.9	1455.3	1453.7	1452.1	1453.7	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3
170°	1469.9	1467.9	1466.1	1464.3	1466.1	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9
172.5°	1479.1	1477.3	1475.5	1473.7	1475.5	1477.3	1479.1	1481.1	1481.2	1479.6	1477.9
175°	1489.8	1487.9	1486.1	1484.3	1486.1	1487.9	1489.8	1491.6	1491.7	1490.2	1488.5
177.5°	1494.3	1492.8	1491.4	1490.0	1491.4	1492.8	1494.3	1495.7	1495.8	1494.6	1493.4
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	14.7	14.5	13.4	13.1	12.0	11.8	10.8	10.7	10.6	10.1	10.4
90°	29.2	28.2	24.7	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2
92.5°	45.8	45.0	43.1	41.2	39.3	37.4	35.4	33.7	31.9	30.2	28.4
95°	87.9	86.8	84.7	82.6	80.6	78.5	76.5	74.7	72.9	71.1	69.3
97.5°	137.0	135.8	134.3	132.9	131.4	129.9	128.4	127.0	125.7	124.3	123.0
100°	173.3	172.5	171.2	169.9	168.5	167.2	165.8	164.3	162.7	161.2	159.6
102.5°	214.6	213.8	212.1	210.4	208.6	206.9	205.6	204.6	203.7	202.8	201.8
105°	276.9	276.9	274.6	272.3	269.8	267.5	266.1	265.6	265.1	264.5	264.0
107.5°	342.7	341.9	340.9	340.0	339.1	338.2	337.5	337.2	336.9	336.6	336.3
110°	387.1	386.1	385.5	385.0	384.5	384.0	383.4	382.9	382.3	381.8	381.3



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	431.4	430.1	430.0	429.9	429.8	429.7	429.5	429.2	428.9	428.6	428.3
115°	500.1	499.9	500.4	500.9	501.4	501.9	501.8	501.0	500.2	499.5	498.7
117.5°	568.8	568.9	569.6	570.2	570.9	571.6	571.6	571.1	570.6	570.1	569.6
120°	614.6	614.8	616.1	617.4	618.7	620.1	620.0	618.3	616.8	615.2	613.7
122.5°	661.1	661.8	662.5	663.1	663.8	664.5	664.3	663.1	662.0	660.8	659.6
125°	729.9	731.0	731.5	732.1	732.6	733.1	733.0	732.2	731.3	730.6	729.8
127.5°	798.1	799.5	800.1	800.6	801.2	801.8	801.2	799.6	797.9	796.3	794.6
130°	842.6	843.6	844.4	845.2	846.0	846.8	846.1	844.0	841.9	839.8	837.8
132.5°	886.5	887.8	888.3	888.9	889.5	890.1	889.3	887.2	885.1	883.0	880.9
135°	951.7	952.7	953.0	953.3	953.5	953.8	953.1	951.6	950.0	948.5	946.8
137.5°	1015.7	1016.8	1016.1	1015.4	1014.8	1014.1	1013.1	1011.8	1010.5	1009.2	1007.9
140°	1056.9	1057.2	1056.9	1056.6	1056.4	1056.1	1055.3	1054.1	1052.8	1051.5	1050.2
142.5°	1096.3	1096.6	1096.1	1095.7	1095.2	1094.7	1093.9	1092.6	1091.3	1089.9	1088.6
145°	1154.3	1154.6	1153.8	1153.0	1152.3	1151.4	1150.7	1150.2	1149.7	1149.2	1148.7
147.5°	1208.8	1208.8	1208.0	1207.3	1206.6	1205.9	1205.1	1204.1	1203.2	1202.2	1201.2
150°	1242.5	1242.5	1242.0	1241.5	1241.0	1240.5	1240.0	1239.4	1238.9	1238.4	1237.9
152.5°	1273.0	1272.6	1272.3	1272.0	1271.6	1271.3	1270.8	1270.1	1269.4	1268.7	1267.9
155°	1317.6	1316.5	1316.3	1316.0	1315.8	1315.5	1315.3	1315.3	1315.3	1315.3	1315.3
157.5°	1356.3	1355.2	1355.0	1354.8	1354.6	1354.3	1354.4	1354.7	1355.0	1355.3	1355.6
160°	1380.0	1378.7	1378.7	1378.7	1378.7	1378.7	1379.0	1379.5	1380.0	1380.5	1381.0
162.5°	1402.5	1401.2	1401.0	1400.8	1400.6	1400.4	1400.7	1401.4	1402.1	1402.8	1403.5
165°	1430.7	1429.2	1429.2	1429.2	1429.2	1429.2	1429.6	1430.3	1431.1	1431.9	1432.7
167.5°	1453.7	1452.1	1451.9	1451.7	1451.5	1451.3	1451.7	1452.8	1453.8	1454.8	1455.9
170°	1466.1	1464.3	1464.3	1464.3	1464.3	1464.3	1464.8	1465.9	1466.9	1467.9	1469.1
172.5°	1476.3	1474.7	1474.7	1474.7	1474.7	1474.7	1475.2	1476.2	1477.2	1478.3	1479.4
175°	1487.0	1485.4	1485.4	1485.4	1485.4	1485.4	1486.0	1487.0	1488.0	1489.1	1490.2
177.5°	1492.1	1490.9	1490.9	1490.9	1490.9	1490.9	1491.3	1492.1	1493.0	1493.8	1494.6
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.7	12.3	14.0	15.5	17.8	19.7	19.9	19.8	20.0	19.8	19.6
90°	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.3
92.5°	30.2	31.9	33.7	35.4	37.4	39.3	41.2	43.1	45.0	45.8	46.8
95°	71.1	72.9	74.7	76.5	78.5	80.6	82.6	84.7	86.8	87.9	88.9
97.5°	124.3	125.7	127.0	128.4	129.9	131.4	132.9	134.3	135.8	137.0	138.3
100°	161.2	162.7	164.3	165.8	167.2	168.5	169.9	171.2	172.5	173.3	174.0
102.5°	202.8	203.7	204.6	205.6	206.9	208.6	210.4	212.1	213.8	214.6	215.3
105°	264.5	265.1	265.6	266.1	267.5	269.8	272.3	274.6	276.9	276.9	276.9
107.5°	336.6	336.9	337.2	337.5	338.2	339.1	340.0	340.9	341.9	342.7	343.6
110°	381.8	382.3	382.9	383.4	384.0	384.5	385.0	385.5	386.1	387.1	388.1





TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	428.6	428.9	429.2	429.5	429.7	429.8	429.9	430.0	430.1	431.4	432.6
115°	499.5	500.2	501.0	501.8	501.9	501.4	500.9	500.4	499.9	500.1	500.4
117.5°	570.1	570.6	571.1	571.6	571.6	570.9	570.2	569.6	568.9	568.8	568.8
120°	615.2	616.8	618.3	620.0	620.1	618.7	617.4	616.1	614.8	614.6	614.3
122.5°	660.8	662.0	663.1	664.3	664.5	663.8	663.1	662.5	661.8	661.1	660.5
125°	730.6	731.3	732.2	733.0	733.1	732.6	732.1	731.5	731.0	729.9	728.9
127.5°	796.3	797.9	799.6	801.2	801.8	801.2	800.6	800.1	799.5	798.1	796.6
130°	839.8	841.9	844.0	846.1	846.8	846.0	845.2	844.4	843.6	842.6	841.5
132.5°	883.0	885.1	887.2	889.3	890.1	889.5	888.9	888.3	887.8	886.5	885.2
135°	948.5	950.0	951.6	953.1	953.8	953.5	953.3	953.0	952.7	951.7	950.7
137.5°	1009.2	1010.5	1011.8	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7	1014.6
140°	1051.5	1052.8	1054.1	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9	1056.6
142.5°	1089.9	1091.3	1092.6	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3	1096.1
145°	1149.2	1149.7	1150.2	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3	1154.1
147.5°	1202.2	1203.2	1204.1	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8	1208.8
150°	1238.4	1238.9	1239.4	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5	1242.5
152.5°	1268.7	1269.4	1270.1	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0	1273.4
155°	1315.3	1315.3	1315.3	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6	1318.6
157.5°	1355.3	1355.0	1354.7	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3	1357.4
160°	1380.5	1380.0	1379.5	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0	1381.3
162.5°	1402.8	1402.1	1401.4	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5	1403.8
165°	1431.9	1431.1	1430.3	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7	1432.3
167.5°	1454.8	1453.8	1452.8	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7	1455.3
170°	1467.9	1466.9	1465.9	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1	1467.9
172.5°	1478.3	1477.2	1476.2	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3	1477.9
175°	1489.1	1488.0	1487.0	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0	1488.5
177.5°	1493.8	1493.0	1492.1	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1	1493.4
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	19.4	19.2	18.9	19.4	19.1	18.8	19.7
90°	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	47.6	48.4	48.7	48.4	48.1	47.7	47.4
95°	90.0	91.0	91.5	91.5	91.5	91.5	91.5
97.5°	139.5	140.7	141.2	141.1	141.0	140.9	140.8
100°	174.8	175.6	176.2	176.8	177.3	177.8	178.3
102.5°	216.1	216.9	217.2	217.1	217.0	216.9	216.8
105°	276.9	276.9	277.2	277.7	278.2	278.7	279.2
107.5°	344.5	345.3	345.5	345.2	344.9	344.6	344.3
110°	389.2	390.2	390.4	389.9	389.4	388.9	388.4



TEST NUMBER: P331992-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	433.9	435.2	435.8	435.7	435.6	435.5	435.4
115°	500.6	500.9	500.9	500.6	500.4	500.1	499.9
117.5°	568.7	568.7	568.3	567.5	566.7	566.0	565.3
120°	614.1	613.8	613.4	612.9	612.4	611.9	611.3
122.5°	659.7	659.0	658.3	657.6	656.9	656.1	655.4
125°	727.9	726.8	725.8	724.8	723.7	722.7	721.6
127.5°	795.2	793.7	792.3	791.1	789.9	788.7	787.6
130°	840.5	839.5	838.0	836.2	834.4	832.5	830.7
132.5°	884.0	882.7	881.4	880.0	878.6	877.2	875.8
135°	949.6	948.6	947.8	947.3	946.7	946.2	945.7
137.5°	1013.5	1012.4	1011.4	1010.4	1009.5	1008.5	1007.4
140°	1056.4	1056.1	1055.1	1053.3	1051.5	1049.7	1047.8
142.5°	1095.8	1095.6	1094.7	1093.3	1091.9	1090.6	1089.1
145°	1153.8	1153.6	1152.9	1151.9	1150.7	1149.7	1148.7
147.5°	1208.8	1208.8	1208.0	1206.4	1204.9	1203.3	1201.7
150°	1242.5	1242.5	1241.8	1240.2	1238.7	1237.1	1235.6
152.5°	1273.8	1274.2	1273.8	1272.4	1271.1	1269.7	1268.4
155°	1319.6	1320.7	1320.3	1318.5	1316.7	1314.8	1312.9
157.5°	1358.5	1359.6	1359.4	1358.0	1356.5	1355.0	1353.5
160°	1382.6	1383.9	1384.0	1383.0	1381.9	1380.9	1379.9
162.5°	1405.1	1406.4	1406.2	1404.5	1402.9	1401.2	1399.6
165°	1433.8	1435.4	1435.2	1433.4	1431.6	1429.8	1427.9
167.5°	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3
172.5°	1479.6	1481.2	1481.1	1479.1	1477.3	1475.5	1473.7
175°	1490.2	1491.7	1491.6	1489.8	1487.9	1486.1	1484.3
177.5°	1494.6	1495.8	1495.7	1494.3	1492.8	1491.4	1490.0
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7

(END OF REPORT)