

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832221

Luminaire Tested: S123RDIP-S560D1195U950-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832221
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U950-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6860.9 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	56	50	66	57	51	46	47	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	34	33	30	27	25	23	21	18				
6	62	51	43	38	56	46	40	35	38	33	30	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	36	31	35	30	26	28	24	22	21	19	17	14				
8	53	42	35	30	48	38	32	28	32	27	24	25	22	20	20	17	16	13				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	18755	18755	18755	18755	18755
5°	22269	21558	18872	15257	14164
10°	20176	21898	18779	12223	10486
15°	13892	18775	18580	9990	8295
20°	9664	14455	18207	8424	7291
25°	7365	11017	17664	7487	6720
30°	6411	8809	16986	6953	6224
35°	5886	7430	16023	6501	5773
40°	5370	6635	14765	6058	5361
45°	4850	6068	13408	5638	4947
50°	4402	5598	11807	5228	4438
55°	3982	5142	10269	4827	3808
60°	3567	4676	8919	4383	3599
65°	3293	4149	7679	3940	3403
70°	2675	3585	6700	3563	2766
75°	2346	2853	5673	2957	2437
80°	2126	2411	4649	2479	2300
85°	1939	2112	3532	2248	2112

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 14148 cd/sqm



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.8	2.3
10°-20°	367.5	5.4
20°-30°	421.6	6.1
30°-40°	415.6	6.1
40°-50°	366.5	5.3
50°-60°	282.0	4.1
60°-70°	185.4	2.7
70°-80°	90.0	1.3
80°-90°	25.7	0.4
90°-100°	52.6	0.8
100°-110°	254.3	3.7
110°-120°	623.3	9.1
120°-130°	791.2	11.5
130°-140°	845.3	12.3
140°-150°	790.4	11.5
150°-160°	637.6	9.3
160°-170°	411.4	6.0
170°-180°	141.8	2.1
0°-30°	947.9	13.8
0°-40°	1363.5	19.9
0°-60°	2012.0	29.3
0°-90°	2313.1	33.7
90°-120°	930.1	13.6
90°-150°	3357.1	48.9
90°-180°	4548.0	66.3
0°-180°	6860.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1742	1742	1742	1742	1742	
5°	2061	1995	1747	1412	1311	188
15°	1247	1685	1667	896	744	352
25°	620	928	1487	630	566	293
35°	448	565	1219	495	439	279
45°	319	399	881	370	325	247
55°	212	274	547	257	203	190
65°	129	163	302	155	134	127
75°	56	69	136	71	59	61
85°	16	17	29	18	17	17
90°	33	27	1	27	33	15
95°	42	34	68	34	42	35
105°	49	243	330	243	49	102
115°	652	636	620	636	652	613
125°	891	887	873	887	891	796
135°	1098	1098	1087	1098	1098	847
145°	1267	1265	1255	1265	1267	791
155°	1380	1381	1382	1381	1380	637
165°	1454	1453	1458	1453	1454	411
175°	1486	1487	1492	1487	1486	141
180°	1492	1492	1492	1492	1492	



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4
2.5°	1930.9	1924.9	1918.8	1917.0	1915.2	1909.5	1903.8	1890.9	1878.1	1864.9	1851.7
5°	2061.0	2061.7	2062.4	2060.6	2058.8	2051.3	2043.8	2028.1	2012.4	1995.2	1978.1
7.5°	2021.0	2032.4	2043.8	2046.0	2048.1	2053.8	2059.5	2056.0	2052.4	2046.0	2039.5
10°	1845.9	1845.2	1844.5	1857.4	1870.2	1908.4	1946.7	1966.3	1986.0	2003.5	2021.0
12.5°	1560.2	1561.3	1562.3	1604.5	1646.6	1682.7	1718.8	1768.8	1818.8	1872.7	1926.7
15°	1246.6	1264.1	1281.6	1319.1	1356.6	1410.9	1465.2	1532.3	1599.5	1684.8	1770.2
17.5°	1023.7	1031.2	1038.7	1074.8	1110.8	1162.3	1213.7	1289.8	1365.9	1475.9	1585.9
20°	843.7	850.5	857.2	883.3	909.4	958.7	1008.0	1080.5	1153.0	1261.9	1370.9
22.5°	704.4	717.6	730.8	748.3	765.8	801.5	837.2	911.2	985.1	1084.4	1183.7
25°	620.1	626.1	632.2	647.2	662.2	696.5	730.8	779.7	828.7	927.6	1026.6
27.5°	562.9	564.7	566.5	577.6	588.6	610.8	632.9	678.3	723.7	805.1	886.5
30°	515.8	519.0	522.2	530.8	539.4	555.4	571.5	603.6	635.8	708.7	781.5
32.5°	479.3	481.1	482.9	490.1	497.2	509.0	520.8	546.1	571.5	627.2	682.9
35°	447.9	448.3	448.6	454.0	459.3	470.8	482.2	503.3	524.3	565.4	606.5
37.5°	412.2	414.7	417.2	421.1	425.1	435.1	445.1	462.2	479.3	513.3	547.2
40°	382.2	384.3	386.5	391.1	395.8	403.6	411.5	427.2	442.9	472.2	501.5
42.5°	352.2	353.6	355.0	359.7	364.3	374.0	383.6	396.1	408.6	432.9	457.2
45°	318.6	322.2	325.8	330.8	335.8	344.0	352.2	365.0	377.9	398.6	419.3
47.5°	290.7	292.5	294.3	298.6	302.9	312.9	322.9	334.3	345.8	365.0	384.3
50°	262.9	263.6	264.3	268.2	272.2	281.1	290.0	303.3	316.5	334.3	352.2
52.5°	236.5	238.2	240.0	244.0	247.9	254.0	260.0	273.6	287.2	304.7	322.2
55°	212.2	213.2	214.3	217.2	220.0	227.2	234.3	246.1	257.9	274.0	290.0
57.5°	189.3	190.7	192.2	194.3	196.5	202.9	209.3	219.7	230.0	246.1	262.2
60°	165.7	167.5	169.3	171.8	174.3	179.3	184.3	193.6	202.9	217.2	231.5
62.5°	148.6	148.9	149.3	151.4	153.6	157.2	160.7	168.2	175.7	190.0	204.3
65°	129.3	130.4	131.4	132.5	133.6	136.4	139.3	145.7	152.2	162.9	173.6
67.5°	109.3	110.4	111.4	113.2	115.0	117.5	120.0	124.3	128.6	138.6	148.6
70°	85.0	85.0	85.0	87.9	90.7	95.0	99.3	102.5	105.7	113.9	122.2
72.5°	69.3	69.7	70.0	70.4	70.7	73.2	75.7	81.1	86.4	91.4	96.4
75°	56.4	56.8	57.1	57.5	57.9	58.6	59.3	61.1	62.9	68.6	74.3
77.5°	45.0	45.4	45.7	46.1	46.4	47.1	47.9	48.6	49.3	51.4	53.6
80°	34.3	34.6	35.0	35.4	35.7	36.1	36.4	37.1	37.9	38.9	40.0
82.5°	25.0	25.0	25.0	25.0	25.0	25.7	26.4	26.4	26.4	27.1	27.9
85°	15.7	15.7	15.7	16.1	16.4	16.4	16.4	16.8	17.1	17.1	17.1
87.5°	7.1	6.8	6.4	6.8	7.1	7.1	7.1	7.5	7.9	7.9	7.9
90°	33.3	32.8	32.3	31.8	31.3	30.5	29.6	28.6	27.6	26.6	23.4
92.5°	37.7	37.4	37.2	36.9	36.7	35.7	34.0	32.3	30.5	28.8	26.6
95°	42.1	42.1	42.1	42.1	42.1	41.3	39.5	37.8	36.1	34.4	31.7
97.5°	45.4	45.2	45.0	44.7	44.5	43.3	41.4	39.4	37.4	35.5	48.0
100°	46.6	46.3	46.1	45.8	45.6	44.5	42.5	40.5	38.5	36.6	75.0
102.5°	47.7	47.2	46.7	46.2	45.7	49.5	57.6	65.8	73.9	82.0	124.9
105°	48.8	48.3	47.8	47.3	46.8	68.3	111.9	155.5	199.1	242.7	264.9
107.5°	115.3	147.5	179.8	212.1	244.3	279.4	317.4	355.3	393.2	431.2	427.5
110°	304.8	340.0	375.2	410.5	445.7	467.4	475.5	483.6	491.7	499.9	497.2



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	577.5	578.0	578.4	578.9	579.4	578.6	576.4	574.1	571.9	569.7	567.0
115°	651.7	650.7	649.7	648.8	647.8	646.1	643.6	641.1	638.7	636.2	634.0
117.5°	711.6	711.3	711.1	710.8	710.6	709.5	707.5	705.5	703.6	701.6	700.4
120°	773.6	773.6	773.6	773.6	773.6	772.7	770.7	768.7	766.7	764.8	764.0
122.5°	834.6	834.4	834.1	833.9	833.6	832.9	831.6	830.4	829.2	827.9	827.0
125°	891.1	890.6	890.1	889.6	889.2	888.7	888.2	887.7	887.2	886.7	885.7
127.5°	946.5	947.0	947.5	948.0	948.5	948.4	947.7	946.9	946.2	945.4	944.2
130°	999.7	1000.2	1000.7	1001.2	1001.7	1001.5	1000.5	999.5	998.5	997.5	996.5
132.5°	1048.5	1049.3	1050.0	1050.7	1051.5	1051.3	1050.4	1049.4	1048.4	1047.4	1046.7
135°	1098.4	1099.1	1099.9	1100.6	1101.3	1101.3	1100.6	1099.9	1099.1	1098.4	1097.4
137.5°	1146.1	1146.5	1147.0	1147.5	1148.0	1147.7	1146.4	1145.2	1144.0	1142.7	1142.2
140°	1188.2	1188.7	1189.2	1189.6	1190.1	1189.9	1188.9	1187.9	1186.9	1186.0	1185.2
142.5°	1227.0	1227.7	1228.4	1229.2	1229.9	1229.9	1229.2	1228.4	1227.7	1227.0	1226.2
145°	1266.9	1266.9	1266.9	1266.9	1266.9	1266.6	1266.1	1265.6	1265.1	1264.6	1264.2
147.5°	1295.7	1296.9	1298.1	1299.4	1300.6	1301.0	1300.5	1300.0	1299.5	1299.0	1298.5
150°	1328.9	1329.7	1330.4	1331.1	1331.9	1332.0	1331.5	1331.0	1330.5	1330.0	1329.5
152.5°	1355.5	1356.8	1358.0	1359.2	1360.5	1360.6	1359.6	1358.6	1357.6	1356.6	1356.4
155°	1379.9	1381.4	1382.9	1384.3	1385.8	1386.0	1384.7	1383.5	1382.3	1381.0	1380.8
157.5°	1401.0	1402.9	1404.9	1406.9	1408.9	1409.1	1407.6	1406.1	1404.7	1403.2	1403.4
160°	1420.9	1422.7	1424.4	1426.1	1427.8	1427.9	1426.5	1425.0	1423.5	1422.0	1422.3
162.5°	1439.8	1441.2	1442.7	1444.2	1445.7	1445.6	1443.8	1442.1	1440.4	1438.7	1438.9
165°	1454.2	1455.9	1457.6	1459.3	1461.1	1461.0	1459.0	1457.0	1455.0	1453.1	1453.3
167.5°	1465.3	1467.2	1469.2	1471.2	1473.1	1473.1	1471.2	1469.2	1467.2	1465.3	1465.3
170°	1475.2	1477.2	1479.2	1481.1	1483.1	1483.1	1481.1	1479.2	1477.2	1475.2	1475.2
172.5°	1480.8	1483.0	1485.2	1487.4	1489.6	1489.8	1487.8	1485.8	1483.9	1481.9	1481.6
175°	1486.3	1488.3	1490.3	1492.2	1494.2	1494.3	1492.6	1490.9	1489.2	1487.4	1487.2
177.5°	1487.4	1489.9	1492.4	1494.8	1497.3	1497.5	1495.6	1493.6	1491.6	1489.6	1489.4
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4
2.5°	1849.9	1848.1	1830.9	1813.8	1797.0	1780.2	1767.7	1755.2	1734.1	1713.1	1699.8
5°	1964.5	1950.9	1923.8	1896.7	1855.9	1815.2	1780.9	1746.6	1703.1	1659.5	1623.1
7.5°	2028.5	2017.4	1984.5	1951.7	1897.7	1843.8	1790.2	1736.6	1672.3	1608.1	1553.0
10°	2030.2	2039.5	2012.4	1985.2	1924.5	1863.8	1790.9	1718.1	1631.6	1545.2	1474.1
12.5°	1966.7	2006.7	2001.0	1995.2	1933.4	1871.7	1783.1	1694.5	1588.4	1482.3	1393.4
15°	1847.7	1925.2	1948.1	1971.0	1919.9	1868.8	1768.1	1667.3	1542.7	1418.0	1315.9
17.5°	1694.5	1803.1	1863.4	1923.8	1886.7	1849.5	1739.1	1628.8	1488.4	1348.0	1236.9
20°	1513.0	1655.2	1749.9	1844.5	1830.9	1817.4	1703.4	1589.5	1438.0	1286.6	1166.2
22.5°	1333.7	1483.8	1614.5	1745.2	1759.1	1773.1	1658.1	1543.0	1377.3	1211.6	1089.1
25°	1179.1	1331.6	1487.3	1643.1	1674.5	1705.9	1596.6	1487.3	1315.5	1143.7	1021.9
27.5°	1031.6	1176.6	1348.0	1519.5	1576.6	1633.8	1533.8	1433.7	1254.8	1075.8	954.4
30°	911.2	1040.8	1215.9	1390.9	1470.5	1550.2	1458.4	1366.6	1189.1	1011.6	892.6
32.5°	799.0	915.1	1090.8	1266.6	1359.1	1451.6	1372.3	1293.0	1122.3	951.5	834.0
35°	710.4	814.4	978.3	1142.3	1245.9	1349.4	1284.4	1219.4	1052.6	885.8	774.7
37.5°	634.4	721.5	875.5	1029.4	1139.4	1249.4	1195.1	1140.9	984.0	827.2	722.2
40°	571.5	641.5	784.7	928.0	1035.8	1143.7	1097.3	1050.8	910.5	770.1	671.9
42.5°	517.6	577.9	706.5	835.1	934.0	1033.0	1002.3	971.5	844.4	717.2	626.1
45°	470.1	520.8	634.0	747.2	838.3	929.4	905.1	880.8	771.2	661.5	577.9
47.5°	427.9	471.5	572.6	673.7	755.4	837.2	814.7	792.2	701.5	610.8	534.7
50°	389.3	426.5	510.8	595.1	668.7	742.2	723.7	705.1	630.1	555.1	489.3
52.5°	352.9	383.6	459.3	535.1	594.4	653.7	639.4	625.1	567.2	509.3	449.7
55°	318.3	346.5	410.4	474.3	525.1	575.8	561.5	547.2	502.2	457.2	404.7
57.5°	286.8	311.5	363.3	415.1	455.4	495.8	489.0	482.2	444.7	407.2	364.0
60°	253.6	275.7	320.4	365.0	397.5	430.1	422.2	414.3	387.5	360.8	323.6
62.5°	224.0	243.6	279.3	315.0	341.5	367.9	362.2	356.5	336.1	315.8	285.0
65°	192.9	212.2	241.1	270.0	290.7	311.5	306.5	301.5	286.1	270.7	246.1
67.5°	164.7	180.7	205.7	230.7	244.7	258.6	255.7	252.9	241.1	229.3	210.0
70°	136.1	150.0	170.7	191.5	201.1	210.7	211.8	212.9	202.2	191.5	177.2
72.5°	107.5	118.6	137.9	157.2	164.7	172.2	171.8	171.4	165.0	158.6	145.7
75°	82.5	90.7	105.7	120.7	127.2	133.6	135.0	136.4	130.4	124.3	117.2
77.5°	59.3	65.0	76.4	87.9	95.0	102.2	102.9	103.6	100.7	97.9	91.1
80°	41.8	43.6	50.7	57.9	65.4	72.9	73.9	75.0	72.2	69.3	65.0
82.5°	28.9	30.0	32.5	35.0	41.1	47.1	48.6	50.0	48.6	47.1	42.5
85°	17.5	17.9	18.9	20.0	22.9	25.7	27.1	28.6	27.9	27.1	24.6
87.5°	7.9	7.9	8.2	8.6	9.3	10.0	11.8	13.6	12.5	11.4	10.4
90°	20.2	17.0	13.8	11.0	8.5	6.0	3.6	1.1	3.6	6.0	8.5
92.5°	24.4	22.2	20.0	19.6	21.1	22.5	24.0	25.5	24.0	22.5	21.1
95°	28.9	26.2	23.5	27.2	37.3	47.4	57.5	67.6	57.5	47.4	37.3
97.5°	60.6	73.2	85.7	95.4	102.3	109.2	116.1	123.0	116.1	109.2	102.3
100°	113.4	151.8	190.3	207.0	202.1	197.2	192.2	187.3	192.2	197.2	202.1
102.5°	167.7	210.6	253.4	273.3	270.1	266.9	263.7	260.5	263.7	266.9	270.1
105°	287.1	309.2	331.4	341.1	338.4	335.7	333.0	330.3	333.0	335.7	338.4
107.5°	423.8	420.1	416.4	413.4	411.2	409.0	406.8	404.6	406.8	409.0	411.2
110°	494.5	491.7	489.0	486.7	484.7	482.8	480.8	478.8	480.8	482.8	484.7



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.3	561.6	558.9	556.6	554.9	553.2	551.5	549.7	551.5	553.2	554.9
115°	631.8	629.6	627.3	625.5	624.0	622.5	621.1	619.6	621.1	622.5	624.0
117.5°	699.1	697.9	696.7	695.2	693.5	691.7	690.0	688.3	690.0	691.7	693.5
120°	763.3	762.6	761.8	760.3	758.1	755.9	753.7	751.5	753.7	755.9	758.1
122.5°	826.0	825.0	824.0	822.7	820.9	819.2	817.5	815.8	817.5	819.2	820.9
125°	884.7	883.7	882.8	881.3	879.3	877.3	875.4	873.4	875.4	877.3	879.3
127.5°	943.0	941.7	940.5	938.9	936.9	935.0	933.0	931.0	933.0	935.0	936.9
130°	995.6	994.6	993.6	992.1	990.1	988.2	986.2	984.2	986.2	988.2	990.1
132.5°	1045.9	1045.2	1044.5	1043.1	1041.1	1039.2	1037.2	1035.2	1037.2	1039.2	1041.1
135°	1096.4	1095.4	1094.5	1093.2	1091.7	1090.3	1088.8	1087.3	1088.8	1090.3	1091.7
137.5°	1141.7	1141.2	1140.8	1139.5	1137.6	1135.6	1133.6	1131.6	1133.6	1135.6	1137.6
140°	1184.5	1183.7	1183.0	1181.9	1180.4	1178.9	1177.5	1176.0	1177.5	1178.9	1180.4
142.5°	1225.5	1224.7	1224.0	1222.9	1221.4	1219.9	1218.5	1217.0	1218.5	1219.9	1221.4
145°	1263.7	1263.2	1262.7	1261.6	1259.8	1258.1	1256.4	1254.7	1256.4	1258.1	1259.8
147.5°	1298.0	1297.5	1297.0	1296.2	1294.9	1293.7	1292.5	1291.2	1292.5	1293.7	1294.9
150°	1329.1	1328.6	1328.1	1327.5	1326.7	1326.0	1325.2	1324.5	1325.2	1326.0	1326.7
152.5°	1356.1	1355.9	1355.7	1355.4	1355.2	1354.9	1354.7	1354.4	1354.7	1354.9	1355.2
155°	1380.5	1380.3	1380.0	1380.2	1380.7	1381.1	1381.6	1382.1	1381.6	1381.1	1380.7
157.5°	1403.7	1403.9	1404.2	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3
160°	1422.5	1422.8	1423.0	1423.3	1423.5	1423.8	1424.0	1424.3	1424.0	1423.8	1423.5
162.5°	1439.2	1439.4	1439.6	1440.1	1440.9	1441.6	1442.4	1443.1	1442.4	1441.6	1440.9
165°	1453.6	1453.8	1454.1	1454.5	1455.3	1456.0	1456.8	1457.5	1456.8	1456.0	1455.3
167.5°	1465.3	1465.3	1465.3	1465.8	1466.7	1467.7	1468.7	1469.7	1468.7	1467.7	1466.7
170°	1475.2	1475.2	1475.2	1475.7	1476.7	1477.7	1478.7	1479.7	1478.7	1477.7	1476.7
172.5°	1481.4	1481.1	1480.9	1481.4	1482.6	1483.9	1485.1	1486.3	1485.1	1483.9	1482.6
175°	1486.9	1486.7	1486.4	1486.9	1488.2	1489.4	1490.6	1491.9	1490.6	1489.4	1488.2
177.5°	1489.2	1488.9	1488.7	1489.2	1490.4	1491.6	1492.8	1494.1	1492.8	1491.6	1490.4
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4
2.5°	1686.6	1666.3	1645.9	1631.3	1616.6	1598.4	1580.2	1579.5	1578.8	1565.2	1551.6
5°	1586.6	1551.3	1515.9	1481.2	1446.6	1412.0	1377.3	1369.5	1361.6	1349.8	1338.0
7.5°	1498.0	1441.6	1385.2	1340.9	1296.6	1261.9	1227.3	1203.7	1180.1	1161.9	1143.7
10°	1403.0	1333.0	1263.0	1209.4	1155.9	1118.3	1080.8	1053.7	1026.6	1013.7	1000.8
12.5°	1304.4	1228.4	1152.3	1099.8	1047.3	1002.3	957.3	932.6	908.0	890.1	872.2
15°	1213.7	1131.9	1050.1	994.4	938.7	896.5	854.4	829.7	805.1	787.2	769.4
17.5°	1125.8	1043.3	960.8	904.4	848.0	809.7	771.5	747.6	723.7	712.6	701.5
20°	1045.8	962.6	879.4	826.2	773.0	735.4	697.9	685.1	672.2	661.9	651.5
22.5°	966.5	886.5	806.5	755.4	704.4	677.2	650.1	639.7	629.4	621.5	613.6
25°	900.1	820.5	740.8	696.2	651.5	630.4	609.4	602.6	595.8	587.9	580.1
27.5°	833.0	757.2	681.5	645.8	610.1	592.9	575.8	567.2	558.6	552.2	545.8
30°	773.7	703.7	633.6	604.0	574.4	559.4	544.4	535.1	525.8	519.7	513.6
32.5°	716.5	654.4	592.2	566.9	541.5	526.8	512.2	503.3	494.3	487.2	480.1
35°	663.7	609.7	555.8	532.6	509.3	494.7	480.1	471.1	462.2	455.1	447.9
37.5°	617.2	568.3	519.3	497.6	475.8	462.9	450.1	440.8	431.5	424.0	416.5
40°	573.6	530.4	487.2	466.1	445.1	431.1	417.2	409.0	400.8	394.0	387.2
42.5°	535.1	495.4	455.8	435.1	414.3	401.1	387.9	378.3	368.6	364.7	360.8
45°	494.3	459.3	424.3	404.3	384.3	370.4	356.5	348.3	340.0	336.5	332.9
47.5°	458.6	426.1	393.6	374.0	354.3	341.8	329.3	322.9	316.5	311.5	306.5
50°	423.6	392.2	360.8	341.8	322.9	312.2	301.5	293.6	285.7	282.2	278.6
52.5°	390.0	361.5	332.9	313.6	294.3	284.0	273.6	266.8	260.0	252.5	245.0
55°	352.2	327.2	302.2	285.0	267.9	257.2	246.5	238.6	230.7	222.9	215.0
57.5°	320.8	296.1	271.5	256.1	240.7	230.4	220.0	211.5	202.9	196.5	190.0
60°	286.5	265.0	243.6	228.6	213.6	203.6	193.6	185.4	177.2	173.9	170.7
62.5°	254.3	234.3	214.3	201.1	187.9	178.2	168.6	163.2	157.9	155.7	153.6
65°	221.5	204.3	187.2	175.0	162.9	154.7	146.4	143.9	141.4	139.7	137.9
67.5°	190.7	176.1	161.4	150.7	140.0	134.3	128.6	125.7	122.9	120.7	118.6
70°	162.9	150.0	137.2	127.9	118.6	113.2	107.9	105.4	102.9	98.9	95.0
72.5°	132.9	122.9	112.9	105.7	98.6	93.9	89.3	84.3	79.3	75.7	72.2
75°	110.0	100.0	90.0	83.2	76.4	71.1	65.7	63.9	62.2	61.1	60.0
77.5°	84.3	75.7	67.2	61.8	56.4	53.9	51.4	50.4	49.3	48.9	48.6
80°	60.7	53.6	46.4	43.6	40.7	40.0	39.3	38.6	37.9	37.5	37.1
82.5°	37.9	34.3	30.7	30.0	29.3	28.9	28.6	28.2	27.9	27.5	27.1
85°	22.1	20.7	19.3	18.9	18.6	18.2	17.9	17.9	17.9	17.9	17.9
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.9	8.6
90°	11.0	13.8	17.0	20.2	23.4	26.6	27.6	28.6	29.6	30.5	31.3
92.5°	19.6	20.0	22.2	24.4	26.6	28.8	30.5	32.3	34.0	35.7	36.7
95°	27.2	23.5	26.2	28.9	31.7	34.4	36.1	37.8	39.5	41.3	42.1
97.5°	95.4	85.7	73.2	60.6	48.0	35.5	37.4	39.4	41.4	43.3	44.5
100°	207.0	190.3	151.8	113.4	75.0	36.6	38.5	40.5	42.5	44.5	45.6
102.5°	273.3	253.4	210.6	167.7	124.9	82.0	73.9	65.8	57.6	49.5	45.7
105°	341.1	331.4	309.2	287.1	264.9	242.7	199.1	155.5	111.9	68.3	46.8
107.5°	413.4	416.4	420.1	423.8	427.5	431.2	393.2	355.3	317.4	279.4	244.3
110°	486.7	489.0	491.7	494.5	497.2	499.9	491.7	483.6	475.5	467.4	445.7



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	556.6	558.9	561.6	564.3	567.0	569.7	571.9	574.1	576.4	578.6	579.4
115°	625.5	627.3	629.6	631.8	634.0	636.2	638.7	641.1	643.6	646.1	647.8
117.5°	695.2	696.7	697.9	699.1	700.4	701.6	703.6	705.5	707.5	709.5	710.6
120°	760.3	761.8	762.6	763.3	764.0	764.8	766.7	768.7	770.7	772.7	773.6
122.5°	822.7	824.0	825.0	826.0	827.0	827.9	829.2	830.4	831.6	832.9	833.6
125°	881.3	882.8	883.7	884.7	885.7	886.7	887.2	887.7	888.2	888.7	889.2
127.5°	938.9	940.5	941.7	943.0	944.2	945.4	946.2	946.9	947.7	948.4	948.5
130°	992.1	993.6	994.6	995.6	996.5	997.5	998.5	999.5	1000.5	1001.5	1001.7
132.5°	1043.1	1044.5	1045.2	1045.9	1046.7	1047.4	1048.4	1049.4	1050.4	1051.3	1051.5
135°	1093.2	1094.5	1095.4	1096.4	1097.4	1098.4	1099.1	1099.9	1100.6	1101.3	1101.3
137.5°	1139.5	1140.8	1141.2	1141.7	1142.2	1142.7	1144.0	1145.2	1146.4	1147.7	1148.0
140°	1181.9	1183.0	1183.7	1184.5	1185.2	1186.0	1186.9	1187.9	1188.9	1189.9	1190.1
142.5°	1222.9	1224.0	1224.7	1225.5	1226.2	1227.0	1227.7	1228.4	1229.2	1229.9	1229.9
145°	1261.6	1262.7	1263.2	1263.7	1264.2	1264.6	1265.1	1265.6	1266.1	1266.6	1266.9
147.5°	1296.2	1297.0	1297.5	1298.0	1298.5	1299.0	1299.5	1300.0	1300.5	1301.0	1300.6
150°	1327.5	1328.1	1328.6	1329.1	1329.5	1330.0	1330.5	1331.0	1331.5	1332.0	1331.9
152.5°	1355.4	1355.7	1355.9	1356.1	1356.4	1356.6	1357.6	1358.6	1359.6	1360.6	1360.5
155°	1380.2	1380.0	1380.3	1380.5	1380.8	1381.0	1382.3	1383.5	1384.7	1386.0	1385.8
157.5°	1404.3	1404.2	1403.9	1403.7	1403.4	1403.2	1404.7	1406.1	1407.6	1409.1	1408.9
160°	1423.3	1423.0	1422.8	1422.5	1422.3	1422.0	1423.5	1425.0	1426.5	1427.9	1427.8
162.5°	1440.1	1439.6	1439.4	1439.2	1438.9	1438.7	1440.4	1442.1	1443.8	1445.6	1445.7
165°	1454.5	1454.1	1453.8	1453.6	1453.3	1453.1	1455.0	1457.0	1459.0	1461.0	1461.1
167.5°	1465.8	1465.3	1465.3	1465.3	1465.3	1465.3	1467.2	1469.2	1471.2	1473.1	1473.1
170°	1475.7	1475.2	1475.2	1475.2	1475.2	1475.2	1477.2	1479.2	1481.1	1483.1	1483.1
172.5°	1481.4	1480.9	1481.1	1481.4	1481.6	1481.9	1483.9	1485.8	1487.8	1489.8	1489.6
175°	1486.9	1486.4	1486.7	1486.9	1487.2	1487.4	1489.2	1490.9	1492.6	1494.3	1494.2
177.5°	1489.2	1488.7	1488.9	1489.2	1489.4	1489.6	1491.6	1493.6	1495.6	1497.5	1497.3
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1742.4	1742.4	1742.4	1742.4
2.5°	1548.0	1544.5	1543.0	1541.6
5°	1326.9	1315.9	1313.4	1310.9
7.5°	1139.1	1134.4	1119.1	1103.7
10°	986.5	972.3	965.8	959.4
12.5°	859.0	845.8	843.7	841.5
15°	760.1	750.8	747.6	744.4
17.5°	695.1	688.7	684.7	680.8
20°	646.9	642.2	639.4	636.5
22.5°	610.1	606.5	604.4	602.2
25°	574.7	569.4	567.6	565.8
27.5°	541.1	536.5	534.7	532.9
30°	509.7	505.8	503.3	500.8
32.5°	475.4	470.8	469.3	467.9
35°	445.1	442.2	440.8	439.3
37.5°	412.9	409.3	407.2	405.0
40°	385.4	383.6	382.5	381.5
42.5°	357.5	354.3	354.0	353.6
45°	329.7	326.5	325.8	325.0
47.5°	303.6	300.8	300.4	300.0
50°	274.7	270.7	267.9	265.0
52.5°	241.5	237.9	235.4	232.9
55°	211.1	207.2	205.0	202.9
57.5°	188.2	186.5	185.4	184.3
60°	169.7	168.6	167.9	167.2
62.5°	152.5	151.4	151.4	151.4
65°	136.8	135.7	134.7	133.6
67.5°	116.4	114.3	113.9	113.6
70°	91.8	88.6	88.2	87.9
72.5°	71.8	71.4	70.7	70.0
75°	59.3	58.6	58.6	58.6
77.5°	47.9	47.1	47.1	47.1
80°	36.8	36.4	36.8	37.1
82.5°	27.1	27.1	26.8	26.4
85°	17.5	17.1	17.1	17.1
87.5°	8.6	8.6	8.6	8.6
90°	31.8	32.3	32.8	33.3
92.5°	36.9	37.2	37.4	37.7
95°	42.1	42.1	42.1	42.1
97.5°	44.7	45.0	45.2	45.4
100°	45.8	46.1	46.3	46.6
102.5°	46.2	46.7	47.2	47.7
105°	47.3	47.8	48.3	48.8
107.5°	212.1	179.8	147.5	115.3
110°	410.5	375.2	340.0	304.8



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	578.9	578.4	578.0	577.5
115°	648.8	649.7	650.7	651.7
117.5°	710.8	711.1	711.3	711.6
120°	773.6	773.6	773.6	773.6
122.5°	833.9	834.1	834.4	834.6
125°	889.6	890.1	890.6	891.1
127.5°	948.0	947.5	947.0	946.5
130°	1001.2	1000.7	1000.2	999.7
132.5°	1050.7	1050.0	1049.3	1048.5
135°	1100.6	1099.9	1099.1	1098.4
137.5°	1147.5	1147.0	1146.5	1146.1
140°	1189.6	1189.2	1188.7	1188.2
142.5°	1229.2	1228.4	1227.7	1227.0
145°	1266.9	1266.9	1266.9	1266.9
147.5°	1299.4	1298.1	1296.9	1295.7
150°	1331.1	1330.4	1329.7	1328.9
152.5°	1359.2	1358.0	1356.8	1355.5
155°	1384.3	1382.9	1381.4	1379.9
157.5°	1406.9	1404.9	1402.9	1401.0
160°	1426.1	1424.4	1422.7	1420.9
162.5°	1444.2	1442.7	1441.2	1439.8
165°	1459.3	1457.6	1455.9	1454.2
167.5°	1471.2	1469.2	1467.2	1465.3
170°	1481.1	1479.2	1477.2	1475.2
172.5°	1487.4	1485.2	1483.0	1480.8
175°	1492.2	1490.3	1488.3	1486.3
177.5°	1494.8	1492.4	1489.9	1487.4
180°	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832221

CATALOG NUMBER: S123RDIP-S560D1195U950-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.17	9.87	10.27	10.96	12.45	13.84	14.54	14.93	15.62	17.11
	3H	10.39	11.01	11.49	12.11	13.61	15.33	15.95	16.43	17.05	18.55
	4H	10.76	11.35	11.88	12.45	13.96	15.81	16.40	16.92	17.50	19.01
	6H	11.04	11.58	12.16	12.68	14.20	16.12	16.66	17.24	17.76	19.28
	8H	11.12	11.64	12.25	12.75	14.27	16.19	16.71	17.32	17.82	19.34
	12H	11.17	11.66	12.30	12.77	14.31	16.22	16.71	17.35	17.82	19.36
4H	2H	9.88	10.47	11.00	11.57	13.08	13.82	14.41	14.94	15.51	17.02
	3H	11.24	11.73	12.37	12.85	14.38	15.46	15.96	16.59	17.08	18.60
	4H	11.69	12.14	12.82	13.25	14.80	16.07	16.52	17.20	17.63	19.18
	6H	12.05	12.44	13.19	13.57	15.11	16.50	16.88	17.63	18.02	19.56
	8H	12.17	12.54	13.31	13.66	15.22	16.63	16.99	17.76	18.11	19.67
	12H	12.24	12.57	13.40	13.71	15.27	16.68	17.01	17.83	18.15	19.71
8H	4H	12.00	12.36	13.13	13.48	15.04	16.02	16.39	17.16	17.51	19.07
	6H	12.45	12.75	13.61	13.92	15.47	16.52	16.81	17.67	17.98	19.53
	8H	12.65	12.91	13.81	14.06	15.63	16.70	16.96	17.86	18.11	19.68
	12H	12.78	13.01	13.95	14.16	15.76	16.81	17.04	17.98	18.19	19.79
12H	4H	12.00	12.33	13.15	13.47	15.02	15.97	16.30	17.12	17.43	18.99
	6H	12.51	12.77	13.67	13.92	15.49	16.49	16.75	17.65	17.90	19.47
	8H	12.73	12.95	13.89	14.10	15.70	16.68	16.91	17.84	18.05	19.66