

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331997-840

Luminaire Tested: **S123DIP-S775D1195U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331997-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D1195U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8020.3 lumens  
Efficiency: N/A  
Efficacy: 141.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	68	79	73	67	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.8	1.4
10°-20°	327.1	4.1
20°-30°	483.2	6.0
30°-40°	564.4	7.0
40°-50°	567.4	7.1
50°-60°	498.4	6.2
60°-70°	371.3	4.6
70°-80°	211.6	2.6
80°-90°	65.1	0.8
90°-100°	57.4	0.7
100°-110°	273.6	3.4
110°-120°	657.3	8.2
120°-130°	837.0	10.4
130°-140°	894.3	11.2
140°-150°	836.3	10.4
150°-160°	674.6	8.4
160°-170°	435.4	5.4
170°-180°	150.0	1.9
0°-30°	926.1	11.5
0°-40°	1490.5	18.6
0°-60°	2556.3	31.9
0°-90°	3204.4	40.0
90°-120°	988.3	12.3
90°-150°	3555.9	44.3
90°-180°	4816.0	60.0
0°-180°	8020.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	13	28	33	35	6
95°	72	27	36	44	44	88
105°	350	356	257	61	52	371
115°	656	663	674	685	690	647
125°	924	934	939	941	943	825
135°	1151	1158	1163	1166	1163	886
145°	1328	1336	1339	1341	1341	831
155°	1463	1461	1462	1467	1461	674
165°	1543	1539	1538	1547	1539	436
175°	1579	1574	1574	1582	1573	150
180°	1579	1579	1579	1579	1579	



TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.2	22.2	22.1	22.1	22.0	22.3	22.7	23.2	23.7	24.2	24.2
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	21.8	21.1	20.4	19.6	18.9	19.8	22.4	24.9	27.5	30.0	31.7
95°	71.6	60.9	50.2	39.5	28.8	24.9	27.8	30.6	33.5	36.4	38.2
97.5°	143.8	139.1	134.2	129.5	124.6	112.9	94.1	75.3	56.6	37.8	39.9
100°	198.2	203.5	208.7	213.9	219.1	201.4	160.8	120.1	79.4	38.7	40.8
102.5°	260.2	264.0	267.7	271.5	275.3	254.9	210.5	166.0	121.6	77.2	70.7
105°	349.6	352.5	355.4	358.2	361.1	350.8	327.3	303.9	280.4	256.9	210.8
107.5°	443.9	446.3	448.6	450.8	453.1	456.2	459.9	463.5	467.3	471.0	437.1
110°	506.9	509.0	511.0	513.1	515.2	517.7	520.6	523.4	526.2	529.2	520.6



TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	566.9	568.8	570.7	572.6	574.4	576.8	579.7	582.6	585.4	588.2	588.4
115°	655.9	657.4	658.9	660.6	662.1	664.1	666.4	668.7	671.2	673.5	676.1
117.5°	741.9	743.9	745.8	747.8	749.7	751.2	752.5	753.7	754.9	756.1	758.1
120°	795.5	797.8	800.2	802.5	804.9	806.5	807.2	808.0	808.8	809.5	811.6
122.5°	849.9	851.8	853.7	855.7	857.7	859.1	860.1	861.1	862.0	863.0	864.5
125°	924.5	926.7	928.7	930.8	932.9	934.4	935.4	936.5	937.6	938.6	939.2
127.5°	996.8	998.9	1001.0	1003.1	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7
130°	1041.9	1044.0	1046.0	1048.1	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0
132.5°	1085.0	1087.1	1089.2	1091.3	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2
135°	1150.9	1152.6	1154.1	1155.7	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5
137.5°	1207.3	1209.3	1211.2	1213.3	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0
140°	1244.9	1246.4	1248.0	1249.5	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5
142.5°	1279.6	1281.1	1282.7	1284.2	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0
145°	1328.2	1330.0	1331.8	1333.6	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2
147.5°	1373.9	1375.1	1376.3	1377.5	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2
150°	1402.1	1402.8	1403.6	1404.4	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5
152.5°	1427.4	1427.7	1428.2	1428.5	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4
155°	1463.1	1462.6	1462.0	1461.5	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2
157.5°	1490.8	1490.7	1490.7	1490.6	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0
160°	1507.6	1507.4	1507.1	1506.9	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9
162.5°	1523.6	1523.0	1522.3	1521.6	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2
165°	1542.9	1542.1	1541.3	1540.5	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2
167.5°	1557.9	1556.8	1555.8	1554.8	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3
170°	1566.3	1565.3	1564.3	1563.2	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7
172.5°	1572.0	1570.7	1569.4	1568.2	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3
175°	1579.2	1577.9	1576.6	1575.3	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4
177.5°	1581.1	1580.0	1579.0	1578.0	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	24.2	24.3	24.3	24.3	24.5	24.6	24.7	24.8
90°	30.2	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	33.3	35.0	36.8	37.7	38.0	38.4	38.7	39.0
95°	40.0	41.8	43.6	44.5	44.5	44.5	44.5	44.5
97.5°	41.9	44.0	46.2	47.3	47.6	47.9	48.1	48.4
100°	42.9	44.9	47.1	48.3	48.5	48.8	49.0	49.3
102.5°	64.2	57.8	51.3	48.4	48.8	49.3	49.8	50.2
105°	164.6	118.5	72.3	49.6	50.1	50.6	51.1	51.6
107.5°	403.2	369.4	335.6	301.2	266.5	231.7	196.9	162.2
110°	511.9	503.3	494.7	471.8	434.5	397.2	359.9	322.7





TEST NUMBER: P331997-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	588.5	588.8	589.0	585.0	577.1	569.3	561.4	553.5
115°	678.6	681.3	683.9	685.7	686.7	687.8	688.8	689.8
117.5°	760.2	762.3	764.4	765.6	765.8	766.0	766.2	766.4
120°	813.7	815.8	817.9	818.9	818.9	818.9	818.9	818.9
122.5°	866.0	867.5	868.9	869.7	869.9	870.1	870.4	870.6
125°	939.7	940.2	940.7	941.2	941.7	942.3	942.8	943.3
127.5°	1013.5	1014.3	1015.1	1015.3	1014.8	1014.3	1013.8	1013.2
130°	1058.0	1059.0	1060.2	1060.4	1059.9	1059.3	1058.8	1058.3
132.5°	1100.2	1101.4	1102.4	1102.5	1101.8	1101.1	1100.3	1099.5
135°	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8
137.5°	1221.3	1222.5	1223.8	1224.2	1223.7	1223.1	1222.6	1222.0
140°	1257.5	1258.5	1259.6	1259.8	1259.3	1258.8	1258.3	1257.8
142.5°	1291.8	1292.6	1293.4	1293.5	1292.8	1292.0	1291.3	1290.6
145°	1339.8	1340.3	1340.8	1341.0	1341.0	1341.0	1341.0	1341.0
147.5°	1382.7	1383.2	1383.7	1383.4	1382.2	1381.0	1379.8	1378.6
150°	1409.0	1409.5	1410.0	1409.9	1409.1	1408.4	1407.5	1406.7
152.5°	1432.3	1433.3	1434.2	1434.1	1432.9	1431.7	1430.5	1429.3
155°	1464.5	1465.8	1467.1	1466.9	1465.4	1463.9	1462.3	1460.8
157.5°	1492.5	1494.0	1495.6	1495.4	1493.4	1491.3	1489.2	1487.2
160°	1508.4	1510.0	1511.6	1511.5	1509.6	1507.8	1505.9	1504.1
162.5°	1523.0	1524.7	1526.5	1526.5	1524.9	1523.3	1521.7	1520.0
165°	1542.4	1544.4	1546.5	1546.6	1544.8	1543.0	1541.2	1539.3
167.5°	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2
170°	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7
172.5°	1571.5	1573.5	1575.6	1575.5	1573.2	1570.9	1568.6	1566.3
175°	1578.2	1580.0	1581.9	1581.7	1579.6	1577.5	1575.5	1573.4
177.5°	1580.6	1582.4	1584.0	1583.8	1581.8	1579.6	1577.5	1575.5
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

(END OF REPORT)