

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331998-840

Luminaire Tested: **S123DIP-S775D1195U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331998-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7342.8 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42				37	
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36				31	
3	80	71	63	57	73	65	58	53	54	49	45	44	40	38	35	32	30				26	
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26				22	
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23				19	
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20				17	
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18				15	
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16				13	
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14				12	
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13				11	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	1.6
10°-20°	327.1	4.5
20°-30°	483.2	6.6
30°-40°	564.4	7.7
40°-50°	567.4	7.7
50°-60°	498.4	6.8
60°-70°	371.3	5.1
70°-80°	211.6	2.9
80°-90°	65.1	0.9
90°-100°	97.3	1.3
100°-110°	291.2	4.0
110°-120°	495.4	6.7
120°-130°	651.6	8.9
130°-140°	732.3	10.0
140°-150°	719.9	9.8
150°-160°	606.0	8.3
160°-170°	403.4	5.5
170°-180°	141.3	1.9
0°-30°	926.1	12.6
0°-40°	1490.5	20.3
0°-60°	2556.3	34.8
0°-90°	3204.4	43.6
90°-120°	883.9	12.0
90°-150°	2987.7	40.7
90°-180°	4138.0	56.4
0°-180°	7342.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	13	28	33	35	7
95°	69	78	87	91	92	78
105°	264	267	277	277	279	283
115°	499	502	500	501	500	493
125°	730	733	731	726	722	651
135°	947	953	953	948	946	729
145°	1149	1151	1155	1153	1149	717
155°	1315	1315	1316	1320	1313	605
165°	1433	1429	1429	1435	1428	404
175°	1490	1486	1485	1492	1484	141
180°	1494	1494	1494	1494	1494	



TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.2	22.2	22.1	22.1	22.0	22.3	22.8	23.2	23.7	24.2	24.2
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	28.4	30.2	31.9	33.7	35.4	37.4	39.3	41.2	43.1	45.0	45.8
95°	69.3	71.1	72.9	74.7	76.5	78.5	80.6	82.6	84.7	86.8	87.9
97.5°	123.0	124.3	125.7	127.0	128.4	129.9	131.4	132.9	134.3	135.8	137.0
100°	159.6	161.2	162.7	164.3	165.8	167.2	168.5	169.9	171.2	172.5	173.3
102.5°	201.8	202.8	203.7	204.6	205.6	206.9	208.6	210.4	212.1	213.8	214.6
105°	264.0	264.5	265.1	265.6	266.1	267.5	269.8	272.3	274.6	276.9	276.9
107.5°	336.3	336.6	336.9	337.2	337.5	338.2	339.1	340.0	340.9	341.9	342.7
110°	381.3	381.8	382.3	382.9	383.4	384.0	384.5	385.0	385.5	386.1	387.1



TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.3	428.6	428.9	429.2	429.5	429.7	429.8	429.9	430.0	430.1	431.4
115°	498.7	499.5	500.2	501.0	501.8	501.9	501.4	500.9	500.4	499.9	500.1
117.5°	569.6	570.1	570.6	571.1	571.6	571.6	570.9	570.2	569.6	568.9	568.8
120°	613.7	615.2	616.8	618.3	620.0	620.1	618.7	617.4	616.1	614.8	614.6
122.5°	659.6	660.8	662.0	663.1	664.3	664.5	663.8	663.1	662.5	661.8	661.1
125°	729.8	730.6	731.3	732.2	733.0	733.1	732.6	732.1	731.5	731.0	729.9
127.5°	794.6	796.3	797.9	799.6	801.2	801.8	801.2	800.6	800.1	799.5	798.1
130°	837.8	839.8	841.9	844.0	846.1	846.8	846.0	845.2	844.4	843.6	842.6
132.5°	880.9	883.0	885.1	887.2	889.3	890.1	889.5	888.9	888.3	887.8	886.5
135°	946.8	948.5	950.0	951.6	953.1	953.8	953.5	953.3	953.0	952.7	951.7
137.5°	1007.9	1009.2	1010.5	1011.8	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7
140°	1050.2	1051.5	1052.8	1054.1	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9
142.5°	1088.6	1089.9	1091.3	1092.6	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3
145°	1148.7	1149.2	1149.7	1150.2	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3
147.5°	1201.2	1202.2	1203.2	1204.1	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8
150°	1237.9	1238.4	1238.9	1239.4	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5
152.5°	1267.9	1268.7	1269.4	1270.1	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0
155°	1315.3	1315.3	1315.3	1315.3	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6
157.5°	1355.6	1355.3	1355.0	1354.7	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3
160°	1381.0	1380.5	1380.0	1379.5	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0
162.5°	1403.5	1402.8	1402.1	1401.4	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5
165°	1432.7	1431.9	1431.1	1430.3	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7
167.5°	1455.9	1454.8	1453.8	1452.8	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7
170°	1469.1	1467.9	1466.9	1465.9	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1
172.5°	1479.4	1478.3	1477.2	1476.2	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3
175°	1490.2	1489.1	1488.0	1487.0	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0
177.5°	1494.6	1493.8	1493.0	1492.1	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	24.2	24.3	24.3	24.3	24.5	24.6	24.7	24.8
90°	30.3	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	46.8	47.6	48.4	48.7	48.4	48.1	47.7	47.4
95°	88.9	90.0	91.0	91.5	91.5	91.5	91.5	91.5
97.5°	138.3	139.5	140.7	141.2	141.1	141.0	140.9	140.8
100°	174.0	174.8	175.6	176.2	176.8	177.3	177.8	178.3
102.5°	215.3	216.1	216.9	217.2	217.1	217.0	216.9	216.8
105°	276.9	276.9	276.9	277.2	277.7	278.2	278.7	279.2
107.5°	343.6	344.5	345.3	345.5	345.2	344.9	344.6	344.3
110°	388.1	389.2	390.2	390.4	389.9	389.4	388.9	388.4



TEST NUMBER: P331998-840

CATALOG NUMBER: S123DIP-S775D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.6	433.9	435.2	435.8	435.7	435.6	435.5	435.4
115°	500.4	500.6	500.9	500.9	500.6	500.4	500.1	499.9
117.5°	568.8	568.7	568.7	568.3	567.5	566.7	566.0	565.3
120°	614.3	614.1	613.8	613.4	612.9	612.4	611.9	611.3
122.5°	660.5	659.7	659.0	658.3	657.6	656.9	656.1	655.4
125°	728.9	727.9	726.8	725.8	724.8	723.7	722.7	721.6
127.5°	796.6	795.2	793.7	792.3	791.1	789.9	788.7	787.6
130°	841.5	840.5	839.5	838.0	836.2	834.4	832.5	830.7
132.5°	885.2	884.0	882.7	881.4	880.0	878.6	877.2	875.8
135°	950.7	949.6	948.6	947.8	947.3	946.7	946.2	945.7
137.5°	1014.6	1013.5	1012.4	1011.4	1010.4	1009.5	1008.5	1007.4
140°	1056.6	1056.4	1056.1	1055.1	1053.3	1051.5	1049.7	1047.8
142.5°	1096.1	1095.8	1095.6	1094.7	1093.3	1091.9	1090.6	1089.1
145°	1154.1	1153.8	1153.6	1152.9	1151.9	1150.7	1149.7	1148.7
147.5°	1208.8	1208.8	1208.8	1208.0	1206.4	1204.9	1203.3	1201.7
150°	1242.5	1242.5	1242.5	1241.8	1240.2	1238.7	1237.1	1235.6
152.5°	1273.4	1273.8	1274.2	1273.8	1272.4	1271.1	1269.7	1268.4
155°	1318.6	1319.6	1320.7	1320.3	1318.5	1316.7	1314.8	1312.9
157.5°	1357.4	1358.5	1359.6	1359.4	1358.0	1356.5	1355.0	1353.5
160°	1381.3	1382.6	1383.9	1384.0	1383.0	1381.9	1380.9	1379.9
162.5°	1403.8	1405.1	1406.4	1406.2	1404.5	1402.9	1401.2	1399.6
165°	1432.3	1433.8	1435.4	1435.2	1433.4	1431.6	1429.8	1427.9
167.5°	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3
172.5°	1477.9	1479.6	1481.2	1481.1	1479.1	1477.3	1475.5	1473.7
175°	1488.5	1490.2	1491.7	1491.6	1489.8	1487.9	1486.1	1484.3
177.5°	1493.4	1494.6	1495.8	1495.7	1494.3	1492.8	1491.4	1490.0
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7

(END OF REPORT)