

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832356

Luminaire Tested: S123RDIP-S775D1195U950-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832356
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U950-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7708.5 lumens
Efficiency: N/A
Efficacy: 135.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				
1	96	92	89	86	88	84	81	79	70	67	66	56	54	53	43	42	42	36				
2	88	81	76	71	80	75	70	66	62	58	55	50	48	46	39	37	36	31				
3	81	72	65	60	74	66	60	56	55	51	47	45	42	39	35	33	32	27				
4	75	64	57	51	68	59	53	48	49	45	41	40	37	34	32	30	28	24				
5	69	58	50	45	63	53	47	42	45	40	36	37	33	30	29	27	25	22				
6	64	52	45	39	58	48	41	37	41	36	32	33	30	27	27	24	22	19				
7	59	47	40	35	54	44	37	33	37	32	28	31	27	24	25	22	20	18				
8	55	43	36	31	50	40	34	29	34	29	25	28	25	22	23	20	18	16				
9	51	40	33	28	47	37	31	26	31	27	23	26	23	20	21	19	17	15				
10	48	37	30	25	44	34	28	24	29	24	21	24	21	18	20	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	25635	25635	25635	25635	25635
5°	30439	29469	25797	20854	19360
10°	27578	29932	25668	16709	14334
15°	18989	25664	25397	13657	11339
20°	13210	19759	24888	11515	9966
25°	10067	15060	24145	10234	9185
30°	8763	12040	23218	9503	8508
35°	8046	10156	21904	8885	7891
40°	7340	9070	20183	8280	7326
45°	6629	8295	18328	7707	6763
50°	6017	7653	16139	7145	6067
55°	5442	7028	14037	6596	5204
60°	4876	6389	12193	5991	4919
65°	4500	5670	10496	5384	4651
70°	3657	4900	9158	4872	3780
75°	3206	3897	7756	4042	3331
80°	2907	3298	6354	3391	3149
85°	2655	2890	4829	3075	2890

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 19339 cd/sqm



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.1	2.8
10°-20°	502.3	6.5
20°-30°	576.3	7.5
30°-40°	568.1	7.4
40°-50°	501.0	6.5
50°-60°	385.4	5.0
60°-70°	253.4	3.3
70°-80°	123.1	1.6
80°-90°	34.0	0.4
90°-100°	52.6	0.7
100°-110°	254.3	3.3
110°-120°	623.3	8.1
120°-130°	791.2	10.3
130°-140°	845.3	11.0
140°-150°	790.4	10.3
150°-160°	637.6	8.3
160°-170°	411.4	5.3
170°-180°	141.8	1.8
0°-30°	1295.8	16.8
0°-40°	1863.8	24.2
0°-60°	2750.2	35.7
0°-90°	3160.7	41.0
90°-120°	930.1	12.1
90°-150°	3357.1	43.6
90°-180°	4548.0	59.0
0°-180°	7708.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2382	2382	2382	2382	2382	
5°	2817	2727	2388	1930	1792	257
15°	1704	2303	2279	1226	1018	481
25°	848	1268	2033	862	773	400
35°	612	773	1667	676	600	382
45°	436	545	1204	506	444	338
55°	290	374	748	352	277	260
65°	177	223	412	211	183	173
75°	77	94	186	97	80	83
85°	22	23	39	25	23	23
90°	33	27	1	27	33	16
95°	42	34	68	34	42	35
105°	49	243	330	243	49	102
115°	652	636	620	636	652	613
125°	891	887	873	887	891	796
135°	1098	1098	1087	1098	1098	847
145°	1267	1265	1255	1265	1267	791
155°	1380	1381	1382	1381	1380	637
165°	1454	1453	1458	1453	1454	411
175°	1486	1487	1492	1487	1486	141
180°	1492	1492	1492	1492	1492	



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6
2.5°	2639.4	2631.1	2622.8	2620.4	2617.9	2610.1	2602.3	2584.7	2567.2	2549.1	2531.0
5°	2817.1	2818.1	2819.1	2816.7	2814.2	2804.0	2793.7	2772.2	2750.7	2727.3	2703.9
7.5°	2762.5	2778.1	2793.7	2796.6	2799.6	2807.4	2815.2	2810.3	2805.4	2796.6	2787.9
10°	2523.2	2522.2	2521.3	2538.8	2556.4	2608.7	2660.9	2687.8	2714.6	2738.5	2762.5
12.5°	2132.6	2134.1	2135.6	2193.2	2250.8	2300.1	2349.4	2417.8	2486.1	2559.8	2633.6
15°	1704.0	1727.9	1751.8	1803.1	1854.3	1928.5	2002.8	2094.5	2186.3	2303.0	2419.7
17.5°	1399.3	1409.5	1419.8	1469.1	1518.4	1588.7	1659.0	1763.0	1867.0	2017.4	2167.8
20°	1153.2	1162.5	1171.8	1207.4	1243.1	1310.4	1377.8	1476.9	1576.0	1725.0	1873.9
22.5°	962.8	980.9	998.9	1022.9	1046.8	1095.6	1144.4	1245.5	1346.6	1482.3	1618.0
25°	847.6	855.9	864.2	884.7	905.2	952.1	998.9	1065.8	1132.7	1268.0	1403.2
27.5°	769.5	771.9	774.3	789.5	804.6	834.9	865.2	927.2	989.2	1100.5	1211.8
30°	705.0	709.4	713.8	725.5	737.2	759.2	781.2	825.1	869.1	968.7	1068.3
32.5°	655.2	657.7	660.1	669.9	679.6	695.7	711.9	746.5	781.2	857.3	933.5
35°	612.3	612.7	613.2	620.6	627.9	643.5	659.1	687.9	716.7	772.9	829.0
37.5°	563.4	566.8	570.3	575.6	581.0	594.7	608.3	631.8	655.2	701.6	748.0
40°	522.4	525.3	528.3	534.6	541.0	551.7	562.5	583.9	605.4	645.5	685.5
42.5°	481.4	483.4	485.3	491.7	498.0	511.2	524.4	541.5	558.5	591.7	624.9
45°	435.5	440.4	445.3	452.1	458.9	470.2	481.4	499.0	516.6	544.9	573.2
47.5°	397.4	399.9	402.3	408.2	414.0	427.7	441.4	457.0	472.6	499.0	525.3
50°	359.3	360.3	361.3	366.7	372.0	384.2	396.5	414.5	432.6	457.0	481.4
52.5°	323.2	325.7	328.1	333.5	338.8	347.1	355.4	374.0	392.5	416.5	440.4
55°	290.0	291.5	292.9	296.8	300.8	310.5	320.3	336.4	352.5	374.5	396.5
57.5°	258.8	260.7	262.7	265.6	268.5	277.3	286.1	300.3	314.4	336.4	358.4
60°	226.5	229.0	231.4	234.8	238.3	245.1	251.9	264.6	277.3	296.8	316.4
62.5°	203.1	203.6	204.1	207.0	209.9	214.8	219.7	230.0	240.2	259.7	279.3
65°	176.7	178.2	179.7	181.1	182.6	186.5	190.4	199.2	208.0	222.6	237.3
67.5°	149.4	150.9	152.3	154.8	157.2	160.6	164.0	169.9	175.8	189.4	203.1
70°	116.2	116.2	116.2	120.1	124.0	129.9	135.7	140.1	144.5	155.7	167.0
72.5°	94.7	95.2	95.7	96.2	96.7	100.1	103.5	110.8	118.2	125.0	131.8
75°	77.1	77.6	78.1	78.6	79.1	80.1	81.0	83.5	85.9	93.7	101.6
77.5°	61.5	62.0	62.5	63.0	63.5	64.4	65.4	66.4	67.4	70.3	73.2
80°	46.9	47.4	47.8	48.3	48.8	49.3	49.8	50.8	51.8	53.2	54.7
82.5°	34.2	34.2	34.2	34.2	34.2	35.2	36.1	36.1	36.1	37.1	38.1
85°	21.5	21.5	21.5	22.0	22.5	22.5	22.5	22.9	23.4	23.4	23.4
87.5°	9.8	9.3	8.8	9.3	9.8	9.8	9.8	10.3	10.7	10.7	10.7
90°	33.3	32.8	32.3	31.8	31.3	30.5	29.6	28.6	27.6	26.6	23.4
92.5°	37.7	37.4	37.2	36.9	36.7	35.7	34.0	32.3	30.5	28.8	26.6
95°	42.1	42.1	42.1	42.1	42.1	41.3	39.5	37.8	36.1	34.4	31.7
97.5°	45.4	45.2	45.0	44.7	44.5	43.3	41.4	39.4	37.4	35.5	48.0
100°	46.6	46.3	46.1	45.8	45.6	44.5	42.5	40.5	38.5	36.6	75.0
102.5°	47.7	47.2	46.7	46.2	45.7	49.5	57.6	65.8	73.9	82.0	124.9
105°	48.8	48.3	47.8	47.3	46.8	68.3	111.9	155.5	199.1	242.7	264.9
107.5°	115.3	147.5	179.8	212.1	244.3	279.4	317.4	355.3	393.2	431.2	427.5
110°	304.8	340.0	375.2	410.5	445.7	467.4	475.5	483.6	491.7	499.9	497.2



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	577.5	578.0	578.4	578.9	579.4	578.6	576.4	574.1	571.9	569.7	567.0
115°	651.7	650.7	649.7	648.8	647.8	646.1	643.6	641.1	638.7	636.2	634.0
117.5°	711.6	711.3	711.1	710.8	710.6	709.5	707.5	705.5	703.6	701.6	700.4
120°	773.6	773.6	773.6	773.6	773.6	772.7	770.7	768.7	766.7	764.8	764.0
122.5°	834.6	834.4	834.1	833.9	833.6	832.9	831.6	830.4	829.2	827.9	827.0
125°	891.1	890.6	890.1	889.6	889.2	888.7	888.2	887.7	887.2	886.7	885.7
127.5°	946.5	947.0	947.5	948.0	948.5	948.4	947.7	946.9	946.2	945.4	944.2
130°	999.7	1000.2	1000.7	1001.2	1001.7	1001.5	1000.5	999.5	998.5	997.5	996.5
132.5°	1048.5	1049.3	1050.0	1050.7	1051.5	1051.3	1050.4	1049.4	1048.4	1047.4	1046.7
135°	1098.4	1099.1	1099.9	1100.6	1101.3	1101.3	1100.6	1099.9	1099.1	1098.4	1097.4
137.5°	1146.1	1146.5	1147.0	1147.5	1148.0	1147.7	1146.4	1145.2	1144.0	1142.7	1142.2
140°	1188.2	1188.7	1189.2	1189.6	1190.1	1189.9	1188.9	1187.9	1186.9	1186.0	1185.2
142.5°	1227.0	1227.7	1228.4	1229.2	1229.9	1229.9	1229.2	1228.4	1227.7	1227.0	1226.2
145°	1266.9	1266.9	1266.9	1266.9	1266.9	1266.6	1266.1	1265.6	1265.1	1264.6	1264.2
147.5°	1295.7	1296.9	1298.1	1299.4	1300.6	1301.0	1300.5	1300.0	1299.5	1299.0	1298.5
150°	1328.9	1329.7	1330.4	1331.1	1331.9	1332.0	1331.5	1331.0	1330.5	1330.0	1329.5
152.5°	1355.5	1356.8	1358.0	1359.2	1360.5	1360.6	1359.6	1358.6	1357.6	1356.6	1356.4
155°	1379.9	1381.4	1382.9	1384.3	1385.8	1386.0	1384.7	1383.5	1382.3	1381.0	1380.8
157.5°	1401.0	1402.9	1404.9	1406.9	1408.9	1409.1	1407.6	1406.1	1404.7	1403.2	1403.4
160°	1420.9	1422.7	1424.4	1426.1	1427.8	1427.9	1426.5	1425.0	1423.5	1422.0	1422.3
162.5°	1439.8	1441.2	1442.7	1444.2	1445.7	1445.6	1443.8	1442.1	1440.4	1438.7	1438.9
165°	1454.2	1455.9	1457.6	1459.3	1461.1	1461.0	1459.0	1457.0	1455.0	1453.1	1453.3
167.5°	1465.3	1467.2	1469.2	1471.2	1473.1	1473.1	1471.2	1469.2	1467.2	1465.3	1465.3
170°	1475.2	1477.2	1479.2	1481.1	1483.1	1483.1	1481.1	1479.2	1477.2	1475.2	1475.2
172.5°	1480.8	1483.0	1485.2	1487.4	1489.6	1489.8	1487.8	1485.8	1483.9	1481.9	1481.6
175°	1486.3	1488.3	1490.3	1492.2	1494.2	1494.3	1492.6	1490.9	1489.2	1487.4	1487.2
177.5°	1487.4	1489.9	1492.4	1494.8	1497.3	1497.5	1495.6	1493.6	1491.6	1489.6	1489.4
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6
2.5°	2528.6	2526.2	2502.7	2479.3	2456.3	2433.4	2416.3	2399.2	2370.4	2341.6	2323.5
5°	2685.3	2666.8	2629.7	2592.6	2536.9	2481.2	2434.4	2387.5	2327.9	2268.4	2218.6
7.5°	2772.7	2757.6	2712.7	2667.7	2594.0	2520.3	2447.1	2373.8	2285.9	2198.1	2122.9
10°	2775.2	2787.9	2750.7	2713.6	2630.6	2547.6	2448.0	2348.4	2230.3	2112.1	2015.0
12.5°	2688.2	2742.9	2735.1	2727.3	2642.8	2558.4	2437.3	2316.2	2171.2	2026.2	1904.6
15°	2525.7	2631.6	2662.9	2694.1	2624.3	2554.5	2416.8	2279.1	2108.7	1938.3	1798.7
17.5°	2316.2	2464.6	2547.1	2629.7	2578.9	2528.1	2377.2	2226.4	2034.5	1842.6	1690.8
20°	2068.2	2262.5	2391.9	2521.3	2502.7	2484.2	2328.4	2172.7	1965.7	1758.6	1594.1
22.5°	1823.1	2028.1	2206.8	2385.5	2404.6	2423.6	2266.4	2109.2	1882.7	1656.1	1488.6
25°	1611.7	1820.2	2033.0	2245.9	2288.9	2331.8	2182.4	2033.0	1798.2	1563.3	1396.9
27.5°	1410.0	1608.3	1842.6	2077.0	2155.1	2233.2	2096.5	1959.8	1715.2	1470.6	1304.6
30°	1245.5	1422.7	1662.0	1901.2	2010.1	2119.0	1993.5	1868.0	1625.4	1382.7	1220.1
32.5°	1092.2	1250.9	1491.1	1731.3	1857.8	1984.2	1875.8	1767.4	1534.1	1300.7	1140.0
35°	971.1	1113.2	1337.3	1561.4	1703.0	1844.6	1755.7	1666.9	1438.8	1210.8	1059.0
37.5°	867.1	986.2	1196.7	1407.1	1557.5	1707.9	1633.7	1559.4	1345.1	1130.8	987.2
40°	781.2	876.9	1072.7	1268.4	1415.9	1563.3	1499.9	1436.4	1244.5	1052.6	918.4
42.5°	707.5	790.0	965.7	1141.5	1276.7	1412.0	1370.0	1328.0	1154.2	980.4	855.9
45°	642.5	711.9	866.6	1021.4	1145.9	1270.4	1237.2	1204.0	1054.1	904.2	790.0
47.5°	584.9	644.5	782.6	920.8	1032.6	1144.4	1113.7	1082.9	958.9	834.9	730.9
50°	532.2	583.0	698.2	813.4	914.0	1014.6	989.2	963.8	861.3	758.7	668.9
52.5°	482.4	524.4	627.9	731.4	812.4	893.5	873.9	854.4	775.3	696.2	614.7
55°	435.0	473.6	561.0	648.4	717.7	787.0	767.5	748.0	686.5	624.9	553.2
57.5°	392.1	425.7	496.5	567.3	622.5	677.7	668.4	659.1	607.9	556.6	497.5
60°	346.7	376.9	438.0	499.0	543.4	587.8	577.1	566.4	529.7	493.1	442.3
62.5°	306.1	333.0	381.8	430.6	466.8	502.9	495.1	487.3	459.4	431.6	389.6
65°	263.6	290.0	329.6	369.1	397.4	425.7	418.9	412.1	391.1	370.1	336.4
67.5°	225.1	247.0	281.2	315.4	334.4	353.5	349.6	345.7	329.6	313.5	287.1
70°	186.0	205.1	233.4	261.7	274.9	288.1	289.5	291.0	276.3	261.7	242.2
72.5°	147.0	162.1	188.5	214.8	225.1	235.3	234.8	234.4	225.6	216.8	199.2
75°	112.8	124.0	144.5	165.0	173.8	182.6	184.6	186.5	178.2	169.9	160.1
77.5°	81.0	88.9	104.5	120.1	129.9	139.6	140.6	141.6	137.7	133.8	124.5
80°	57.1	59.6	69.3	79.1	89.3	99.6	101.1	102.5	98.6	94.7	88.9
82.5°	39.5	41.0	44.4	47.8	56.1	64.4	66.4	68.4	66.4	64.4	58.1
85°	23.9	24.4	25.9	27.3	31.2	35.2	37.1	39.1	38.1	37.1	33.7
87.5°	10.7	10.7	11.2	11.7	12.7	13.7	16.1	18.6	17.1	15.6	14.2
90°	20.2	17.0	13.8	11.0	8.5	6.0	3.6	1.1	3.6	6.0	8.5
92.5°	24.4	22.2	20.0	19.6	21.1	22.5	24.0	25.5	24.0	22.5	21.1
95°	28.9	26.2	23.5	27.2	37.3	47.4	57.5	67.6	57.5	47.4	37.3
97.5°	60.6	73.2	85.7	95.4	102.3	109.2	116.1	123.0	116.1	109.2	102.3
100°	113.4	151.8	190.3	207.0	202.1	197.2	192.2	187.3	192.2	197.2	202.1
102.5°	167.7	210.6	253.4	273.3	270.1	266.9	263.7	260.5	263.7	266.9	270.1
105°	287.1	309.2	331.4	341.1	338.4	335.7	333.0	330.3	333.0	335.7	338.4
107.5°	423.8	420.1	416.4	413.4	411.2	409.0	406.8	404.6	406.8	409.0	411.2
110°	494.5	491.7	489.0	486.7	484.7	482.8	480.8	478.8	480.8	482.8	484.7



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.3	561.6	558.9	556.6	554.9	553.2	551.5	549.7	551.5	553.2	554.9
115°	631.8	629.6	627.3	625.5	624.0	622.5	621.1	619.6	621.1	622.5	624.0
117.5°	699.1	697.9	696.7	695.2	693.5	691.7	690.0	688.3	690.0	691.7	693.5
120°	763.3	762.6	761.8	760.3	758.1	755.9	753.7	751.5	753.7	755.9	758.1
122.5°	826.0	825.0	824.0	822.7	820.9	819.2	817.5	815.8	817.5	819.2	820.9
125°	884.7	883.7	882.8	881.3	879.3	877.3	875.4	873.4	875.4	877.3	879.3
127.5°	943.0	941.7	940.5	938.9	936.9	935.0	933.0	931.0	933.0	935.0	936.9
130°	995.6	994.6	993.6	992.1	990.1	988.2	986.2	984.2	986.2	988.2	990.1
132.5°	1045.9	1045.2	1044.5	1043.1	1041.1	1039.2	1037.2	1035.2	1037.2	1039.2	1041.1
135°	1096.4	1095.4	1094.5	1093.2	1091.7	1090.3	1088.8	1087.3	1088.8	1090.3	1091.7
137.5°	1141.7	1141.2	1140.8	1139.5	1137.6	1135.6	1133.6	1131.6	1133.6	1135.6	1137.6
140°	1184.5	1183.7	1183.0	1181.9	1180.4	1178.9	1177.5	1176.0	1177.5	1178.9	1180.4
142.5°	1225.5	1224.7	1224.0	1222.9	1221.4	1219.9	1218.5	1217.0	1218.5	1219.9	1221.4
145°	1263.7	1263.2	1262.7	1261.6	1259.8	1258.1	1256.4	1254.7	1256.4	1258.1	1259.8
147.5°	1298.0	1297.5	1297.0	1296.2	1294.9	1293.7	1292.5	1291.2	1292.5	1293.7	1294.9
150°	1329.1	1328.6	1328.1	1327.5	1326.7	1326.0	1325.2	1324.5	1325.2	1326.0	1326.7
152.5°	1356.1	1355.9	1355.7	1355.4	1355.2	1354.9	1354.7	1354.4	1354.7	1354.9	1355.2
155°	1380.5	1380.3	1380.0	1380.2	1380.7	1381.1	1381.6	1382.1	1381.6	1381.1	1380.7
157.5°	1403.7	1403.9	1404.2	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3	1404.3
160°	1422.5	1422.8	1423.0	1423.3	1423.5	1423.8	1424.0	1424.3	1424.0	1423.8	1423.5
162.5°	1439.2	1439.4	1439.6	1440.1	1440.9	1441.6	1442.4	1443.1	1442.4	1441.6	1440.9
165°	1453.6	1453.8	1454.1	1454.5	1455.3	1456.0	1456.8	1457.5	1456.8	1456.0	1455.3
167.5°	1465.3	1465.3	1465.3	1465.8	1466.7	1467.7	1468.7	1469.7	1468.7	1467.7	1466.7
170°	1475.2	1475.2	1475.2	1475.7	1476.7	1477.7	1478.7	1479.7	1478.7	1477.7	1476.7
172.5°	1481.4	1481.1	1480.9	1481.4	1482.6	1483.9	1485.1	1486.3	1485.1	1483.9	1482.6
175°	1486.9	1486.7	1486.4	1486.9	1488.2	1489.4	1490.6	1491.9	1490.6	1489.4	1488.2
177.5°	1489.2	1488.9	1488.7	1489.2	1490.4	1491.6	1492.8	1494.1	1492.8	1491.6	1490.4
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6	2381.6
2.5°	2305.5	2277.6	2249.8	2229.8	2209.8	2184.9	2160.0	2159.0	2158.0	2139.5	2120.9
5°	2168.8	2120.4	2072.1	2024.7	1977.4	1930.0	1882.7	1871.9	1861.2	1845.1	1828.9
7.5°	2047.7	1970.5	1893.4	1832.9	1772.3	1725.0	1677.6	1645.4	1613.1	1588.2	1563.3
10°	1917.8	1822.1	1726.4	1653.2	1579.9	1528.7	1477.4	1440.3	1403.2	1385.6	1368.0
12.5°	1783.1	1679.1	1575.1	1503.3	1431.5	1370.0	1308.5	1274.8	1241.1	1216.7	1192.3
15°	1659.0	1547.2	1435.4	1359.3	1283.1	1225.5	1167.9	1134.2	1100.5	1076.1	1051.7
17.5°	1538.9	1426.1	1313.4	1236.2	1159.1	1106.8	1054.6	1021.9	989.2	974.0	958.9
20°	1429.6	1315.8	1202.0	1129.3	1056.6	1005.3	954.0	936.4	918.9	904.7	890.5
22.5°	1321.2	1211.8	1102.4	1032.6	962.8	925.7	888.6	874.4	860.3	849.5	838.8
25°	1230.4	1121.5	1012.6	951.6	890.5	861.7	832.9	823.7	814.4	803.6	792.9
27.5°	1138.6	1035.1	931.6	882.7	833.9	810.5	787.0	775.3	763.6	754.8	746.0
30°	1057.5	961.8	866.1	825.6	785.1	764.6	744.1	731.4	718.7	710.4	702.1
32.5°	979.4	894.5	809.5	774.8	740.2	720.2	700.1	687.9	675.7	666.0	656.2
35°	907.1	833.4	759.7	728.0	696.2	676.2	656.2	644.0	631.8	622.0	612.3
37.5°	843.7	776.8	709.9	680.1	650.3	632.8	615.2	602.5	589.8	579.5	569.3
40°	784.1	725.0	666.0	637.2	608.3	589.3	570.3	559.0	547.8	538.5	529.3
42.5°	731.4	677.2	623.0	594.7	566.4	548.3	530.2	517.0	503.9	498.5	493.1
45°	675.7	627.9	580.0	552.7	525.3	506.3	487.3	476.0	464.8	459.9	455.0
47.5°	626.9	582.5	538.0	511.2	484.3	467.2	450.2	441.4	432.6	425.7	418.9
50°	579.1	536.1	493.1	467.2	441.4	426.7	412.1	401.3	390.6	385.7	380.8
52.5°	533.2	494.1	455.0	428.7	402.3	388.2	374.0	364.7	355.4	345.2	334.9
55°	481.4	447.2	413.1	389.6	366.2	351.5	336.9	326.1	315.4	304.7	293.9
57.5°	438.4	404.8	371.1	350.1	329.1	314.9	300.8	289.0	277.3	268.5	259.7
60°	391.6	362.3	333.0	312.5	292.0	278.3	264.6	253.4	242.2	237.8	233.4
62.5°	347.6	320.3	292.9	274.9	256.8	243.6	230.4	223.1	215.8	212.9	209.9
65°	302.7	279.3	255.8	239.2	222.6	211.4	200.2	196.8	193.3	190.9	188.5
67.5°	260.7	240.7	220.7	206.0	191.4	183.6	175.8	171.9	168.0	165.0	162.1
70°	222.6	205.1	187.5	174.8	162.1	154.8	147.4	144.0	140.6	135.2	129.9
72.5°	181.6	168.0	154.3	144.5	134.8	128.4	122.1	115.2	108.4	103.5	98.6
75°	150.4	136.7	123.0	113.8	104.5	97.2	89.8	87.4	85.0	83.5	82.0
77.5°	115.2	103.5	91.8	84.5	77.1	73.7	70.3	68.8	67.4	66.9	66.4
80°	83.0	73.2	63.5	59.6	55.7	54.7	53.7	52.7	51.8	51.3	50.8
82.5°	51.8	46.9	42.0	41.0	40.0	39.5	39.1	38.6	38.1	37.6	37.1
85°	30.3	28.3	26.4	25.9	25.4	24.9	24.4	24.4	24.4	24.4	24.4
87.5°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.2	11.7
90°	11.0	13.8	17.0	20.2	23.4	26.6	27.6	28.6	29.6	30.5	31.3
92.5°	19.6	20.0	22.2	24.4	26.6	28.8	30.5	32.3	34.0	35.7	36.7
95°	27.2	23.5	26.2	28.9	31.7	34.4	36.1	37.8	39.5	41.3	42.1
97.5°	95.4	85.7	73.2	60.6	48.0	35.5	37.4	39.4	41.4	43.3	44.5
100°	207.0	190.3	151.8	113.4	75.0	36.6	38.5	40.5	42.5	44.5	45.6
102.5°	273.3	253.4	210.6	167.7	124.9	82.0	73.9	65.8	57.6	49.5	45.7
105°	341.1	331.4	309.2	287.1	264.9	242.7	199.1	155.5	111.9	68.3	46.8
107.5°	413.4	416.4	420.1	423.8	427.5	431.2	393.2	355.3	317.4	279.4	244.3
110°	486.7	489.0	491.7	494.5	497.2	499.9	491.7	483.6	475.5	467.4	445.7



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	556.6	558.9	561.6	564.3	567.0	569.7	571.9	574.1	576.4	578.6	579.4
115°	625.5	627.3	629.6	631.8	634.0	636.2	638.7	641.1	643.6	646.1	647.8
117.5°	695.2	696.7	697.9	699.1	700.4	701.6	703.6	705.5	707.5	709.5	710.6
120°	760.3	761.8	762.6	763.3	764.0	764.8	766.7	768.7	770.7	772.7	773.6
122.5°	822.7	824.0	825.0	826.0	827.0	827.9	829.2	830.4	831.6	832.9	833.6
125°	881.3	882.8	883.7	884.7	885.7	886.7	887.2	887.7	888.2	888.7	889.2
127.5°	938.9	940.5	941.7	943.0	944.2	945.4	946.2	946.9	947.7	948.4	948.5
130°	992.1	993.6	994.6	995.6	996.5	997.5	998.5	999.5	1000.5	1001.5	1001.7
132.5°	1043.1	1044.5	1045.2	1045.9	1046.7	1047.4	1048.4	1049.4	1050.4	1051.3	1051.5
135°	1093.2	1094.5	1095.4	1096.4	1097.4	1098.4	1099.1	1099.9	1100.6	1101.3	1101.3
137.5°	1139.5	1140.8	1141.2	1141.7	1142.2	1142.7	1144.0	1145.2	1146.4	1147.7	1148.0
140°	1181.9	1183.0	1183.7	1184.5	1185.2	1186.0	1186.9	1187.9	1188.9	1189.9	1190.1
142.5°	1222.9	1224.0	1224.7	1225.5	1226.2	1227.0	1227.7	1228.4	1229.2	1229.9	1229.9
145°	1261.6	1262.7	1263.2	1263.7	1264.2	1264.6	1265.1	1265.6	1266.1	1266.6	1266.9
147.5°	1296.2	1297.0	1297.5	1298.0	1298.5	1299.0	1299.5	1300.0	1300.5	1301.0	1300.6
150°	1327.5	1328.1	1328.6	1329.1	1329.5	1330.0	1330.5	1331.0	1331.5	1332.0	1331.9
152.5°	1355.4	1355.7	1355.9	1356.1	1356.4	1356.6	1357.6	1358.6	1359.6	1360.6	1360.5
155°	1380.2	1380.0	1380.3	1380.5	1380.8	1381.0	1382.3	1383.5	1384.7	1386.0	1385.8
157.5°	1404.3	1404.2	1403.9	1403.7	1403.4	1403.2	1404.7	1406.1	1407.6	1409.1	1408.9
160°	1423.3	1423.0	1422.8	1422.5	1422.3	1422.0	1423.5	1425.0	1426.5	1427.9	1427.8
162.5°	1440.1	1439.6	1439.4	1439.2	1438.9	1438.7	1440.4	1442.1	1443.8	1445.6	1445.7
165°	1454.5	1454.1	1453.8	1453.6	1453.3	1453.1	1455.0	1457.0	1459.0	1461.0	1461.1
167.5°	1465.8	1465.3	1465.3	1465.3	1465.3	1465.3	1467.2	1469.2	1471.2	1473.1	1473.1
170°	1475.7	1475.2	1475.2	1475.2	1475.2	1475.2	1477.2	1479.2	1481.1	1483.1	1483.1
172.5°	1481.4	1480.9	1481.1	1481.4	1481.6	1481.9	1483.9	1485.8	1487.8	1489.8	1489.6
175°	1486.9	1486.4	1486.7	1486.9	1487.2	1487.4	1489.2	1490.9	1492.6	1494.3	1494.2
177.5°	1489.2	1488.7	1488.9	1489.2	1489.4	1489.6	1491.6	1493.6	1495.6	1497.5	1497.3
180°	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9	1491.9



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2381.6	2381.6	2381.6	2381.6
2.5°	2116.0	2111.1	2109.2	2107.2
5°	1813.8	1798.7	1795.3	1791.8
7.5°	1557.0	1550.7	1529.7	1508.7
10°	1348.5	1329.0	1320.2	1311.4
12.5°	1174.2	1156.2	1153.2	1150.3
15°	1039.0	1026.3	1021.9	1017.5
17.5°	950.1	941.3	936.0	930.6
20°	884.2	877.9	873.9	870.0
22.5°	833.9	829.0	826.1	823.2
25°	785.6	778.3	775.8	773.4
27.5°	739.7	733.3	730.9	728.5
30°	696.7	691.3	687.9	684.5
32.5°	649.8	643.5	641.5	639.6
35°	608.3	604.4	602.5	600.5
37.5°	564.4	559.5	556.6	553.7
40°	526.8	524.4	522.9	521.4
42.5°	488.7	484.3	483.8	483.4
45°	450.6	446.3	445.3	444.3
47.5°	415.0	411.1	410.6	410.1
50°	375.5	370.1	366.2	362.3
52.5°	330.1	325.2	321.8	318.3
55°	288.5	283.2	280.2	277.3
57.5°	257.3	254.9	253.4	251.9
60°	231.9	230.4	229.5	228.5
62.5°	208.5	207.0	207.0	207.0
65°	187.0	185.5	184.1	182.6
67.5°	159.2	156.2	155.7	155.3
70°	125.5	121.1	120.6	120.1
72.5°	98.1	97.6	96.7	95.7
75°	81.0	80.1	80.1	80.1
77.5°	65.4	64.4	64.4	64.4
80°	50.3	49.8	50.3	50.8
82.5°	37.1	37.1	36.6	36.1
85°	23.9	23.4	23.4	23.4
87.5°	11.7	11.7	11.7	11.7
90°	31.8	32.3	32.8	33.3
92.5°	36.9	37.2	37.4	37.7
95°	42.1	42.1	42.1	42.1
97.5°	44.7	45.0	45.2	45.4
100°	45.8	46.1	46.3	46.6
102.5°	46.2	46.7	47.2	47.7
105°	47.3	47.8	48.3	48.8
107.5°	212.1	179.8	147.5	115.3
110°	410.5	375.2	340.0	304.8



TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	578.9	578.4	578.0	577.5
115°	648.8	649.7	650.7	651.7
117.5°	710.8	711.1	711.3	711.6
120°	773.6	773.6	773.6	773.6
122.5°	833.9	834.1	834.4	834.6
125°	889.6	890.1	890.6	891.1
127.5°	948.0	947.5	947.0	946.5
130°	1001.2	1000.7	1000.2	999.7
132.5°	1050.7	1050.0	1049.3	1048.5
135°	1100.6	1099.9	1099.1	1098.4
137.5°	1147.5	1147.0	1146.5	1146.1
140°	1189.6	1189.2	1188.7	1188.2
142.5°	1229.2	1228.4	1227.7	1227.0
145°	1266.9	1266.9	1266.9	1266.9
147.5°	1299.4	1298.1	1296.9	1295.7
150°	1331.1	1330.4	1329.7	1328.9
152.5°	1359.2	1358.0	1356.8	1355.5
155°	1384.3	1382.9	1381.4	1379.9
157.5°	1406.9	1404.9	1402.9	1401.0
160°	1426.1	1424.4	1422.7	1420.9
162.5°	1444.2	1442.7	1441.2	1439.8
165°	1459.3	1457.6	1455.9	1454.2
167.5°	1471.2	1469.2	1467.2	1465.3
170°	1481.1	1479.2	1477.2	1475.2
172.5°	1487.4	1485.2	1483.0	1480.8
175°	1492.2	1490.3	1488.3	1486.3
177.5°	1494.8	1492.4	1489.9	1487.4
180°	1491.9	1491.9	1491.9	1491.9

TEST NUMBER: P832356

CATALOG NUMBER: S123RDIP-S775D1195U950-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.11	11.85	12.15	12.89	14.29	15.77	16.52	16.81	17.56	18.95
	3H	12.32	12.99	13.37	14.04	15.45	17.27	17.93	18.32	18.98	20.40
	4H	12.70	13.33	13.76	14.38	15.81	17.75	18.38	18.81	19.43	20.86
	6H	12.98	13.56	14.05	14.61	16.05	18.06	18.64	19.13	19.69	21.13
	8H	13.06	13.61	14.14	14.68	16.11	18.14	18.69	19.21	19.76	21.19
	12H	13.11	13.63	14.19	14.70	16.15	18.16	18.69	19.24	19.75	21.21
4H	2H	11.82	12.45	12.89	13.50	14.93	15.76	16.39	16.83	17.44	18.86
	3H	13.18	13.70	14.26	14.78	16.22	17.41	17.93	18.48	19.01	20.45
	4H	13.63	14.11	14.71	15.18	16.64	18.01	18.49	19.09	19.56	21.02
	6H	14.00	14.41	15.09	15.50	16.95	18.44	18.86	19.53	19.95	21.40
	8H	14.12	14.50	15.21	15.59	17.06	18.57	18.96	19.66	20.04	21.51
	12H	14.19	14.54	15.30	15.64	17.11	18.63	18.98	19.74	20.08	21.55
8H	4H	13.94	14.33	15.03	15.41	16.88	17.97	18.36	19.06	19.44	20.91
	6H	14.40	14.72	15.51	15.85	17.31	18.47	18.78	19.58	19.91	21.37
	8H	14.60	14.87	15.71	15.98	17.47	18.65	18.93	19.77	20.04	21.52
	12H	14.73	14.98	15.85	16.08	17.60	18.76	19.01	19.88	20.11	21.63
12H	4H	13.95	14.30	15.06	15.39	16.87	17.92	18.26	19.03	19.36	20.84
	6H	14.46	14.74	15.58	15.85	17.33	18.44	18.72	19.56	19.83	21.31
	8H	14.68	14.92	15.80	16.02	17.55	18.63	18.87	19.75	19.98	21.50