

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331965-840

Luminaire Tested: **S123DIP-S775D585U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331965-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5327.2 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	59	57	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	2.0
10°-20°	344.7	6.5
20°-30°	578.5	10.9
30°-40°	655.0	12.3
40°-50°	587.4	11.0
50°-60°	474.0	8.9
60°-70°	330.3	6.2
70°-80°	173.6	3.3
80°-90°	44.6	0.8
90°-100°	47.8	0.9
100°-110°	143.0	2.7
110°-120°	243.2	4.6
120°-130°	319.9	6.0
130°-140°	359.5	6.7
140°-150°	353.4	6.6
150°-160°	297.5	5.6
160°-170°	198.0	3.7
170°-180°	69.3	1.3
0°-30°	1030.6	19.3
0°-40°	1685.7	31.6
0°-60°	2747.1	51.6
0°-90°	3295.6	61.9
90°-120°	433.9	8.1
90°-150°	1466.7	27.5
90°-180°	2032.0	38.1
0°-180°	5327.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	42
90°	17	1	17	1	17	10
95°	45	34	45	34	45	46
105°	137	130	137	130	137	145
115°	245	245	245	245	245	243
125°	354	358	354	358	354	317
135°	464	465	464	465	464	357
145°	564	564	564	564	564	352
155°	645	646	645	646	645	297
165°	701	703	701	703	701	198
175°	729	732	729	732	729	69
180°	733	733	733	733	733	



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	16.2	15.2	15.7	16.0	15.6	15.9	16.2	16.5	16.9	17.2	17.3
90°	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8	14.3	13.8	12.1
92.5°	23.2	23.4	23.5	23.7	23.9	23.7	23.3	22.9	22.5	22.1	21.2
95°	44.9	44.9	44.9	44.9	44.9	44.6	44.1	43.6	43.1	42.6	41.6
97.5°	69.1	69.2	69.2	69.3	69.3	69.1	68.5	67.9	67.3	66.8	65.9
100°	87.6	87.3	87.1	86.7	86.5	86.2	85.8	85.4	85.0	84.6	84.0
102.5°	106.4	106.5	106.5	106.6	106.6	106.4	106.1	105.7	105.3	104.9	104.1
105°	137.1	136.8	136.5	136.3	136.0	135.9	135.9	135.9	135.9	135.9	134.8
107.5°	169.1	169.2	169.4	169.5	169.7	169.5	169.1	168.6	168.2	167.8	167.4
110°	190.7	191.0	191.2	191.5	191.7	191.6	191.1	190.6	190.1	189.6	189.2



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.7	213.8	213.8	213.9	213.9	213.6	213.0	212.4	211.8	211.2	211.2
115°	245.4	245.5	245.6	245.8	245.9	245.9	245.8	245.6	245.5	245.4	245.6
117.5°	277.5	277.9	278.2	278.6	278.9	279.1	279.1	279.2	279.2	279.2	279.6
120°	300.1	300.3	300.6	300.8	301.1	301.3	301.4	301.5	301.7	301.8	302.5
122.5°	321.7	322.1	322.4	322.9	323.2	323.6	323.9	324.2	324.6	324.9	325.2
125°	354.3	354.8	355.3	355.8	356.3	356.8	357.3	357.8	358.3	358.9	359.1
127.5°	386.6	387.2	387.8	388.4	389.0	389.6	390.3	391.0	391.8	392.5	392.7
130°	407.8	408.7	409.6	410.5	411.4	412.1	412.6	413.1	413.6	414.1	414.5
132.5°	429.9	430.6	431.3	432.0	432.7	433.3	433.9	434.5	435.2	435.9	436.1
135°	464.2	464.5	464.7	465.0	465.2	465.6	466.2	466.7	467.3	467.8	467.9
137.5°	494.5	495.0	495.5	496.0	496.6	497.1	497.6	498.1	498.7	499.2	498.9
140°	514.4	515.2	516.1	517.1	518.0	518.5	518.6	518.8	518.9	519.0	518.9
142.5°	534.6	535.3	536.0	536.7	537.5	537.9	538.0	538.1	538.3	538.4	538.2
145°	563.9	564.4	564.9	565.4	565.9	566.3	566.4	566.5	566.6	566.8	566.4
147.5°	590.0	590.8	591.5	592.3	593.0	593.4	593.4	593.4	593.4	593.4	593.1
150°	606.5	607.3	608.0	608.8	609.7	610.0	610.0	610.0	610.0	610.0	609.8
152.5°	622.7	623.4	624.0	624.7	625.3	625.6	625.4	625.2	624.9	624.7	624.6
155°	644.6	645.5	646.3	647.2	648.1	648.3	647.8	647.3	646.8	646.3	646.2
157.5°	664.5	665.2	665.9	666.6	667.3	667.4	666.9	666.4	665.8	665.3	665.2
160°	677.4	677.9	678.4	678.9	679.4	679.3	678.7	678.1	677.4	676.8	676.8
162.5°	687.1	687.9	688.7	689.5	690.3	690.4	689.8	689.1	688.5	687.9	687.8
165°	701.0	702.0	702.8	703.7	704.6	704.7	703.9	703.2	702.4	701.6	701.6
167.5°	712.9	713.7	714.5	715.3	716.1	716.1	715.3	714.5	713.7	712.9	712.8
170°	718.8	719.7	720.6	721.5	722.5	722.5	721.5	720.6	719.7	718.8	718.8
172.5°	723.5	724.4	725.3	726.2	727.1	727.1	726.3	725.5	724.8	724.0	724.0
175°	728.6	729.5	730.4	731.3	732.3	732.4	731.5	730.7	730.0	729.2	729.2
177.5°	731.4	732.2	732.9	733.6	734.3	734.4	733.8	733.2	732.5	731.8	731.8
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	17.8	17.9	16.3	14.2	13.1	11.6	11.4	10.3	9.7	9.9	9.8
90°	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	20.2	19.3	18.4	17.5	16.6	15.7	14.8	13.9	14.8	15.7	16.6
95°	40.6	39.6	38.6	37.6	36.7	35.7	34.8	34.0	34.8	35.7	36.7
97.5°	65.2	64.4	63.7	63.0	62.4	61.7	61.0	60.4	61.0	61.7	62.4
100°	83.4	82.7	82.1	81.4	80.7	79.9	79.1	78.4	79.1	79.9	80.7
102.5°	103.3	102.4	101.6	100.9	100.5	100.0	99.6	99.1	99.6	100.0	100.5
105°	133.6	132.5	131.3	130.7	130.4	130.1	129.9	129.6	129.9	130.1	130.4
107.5°	166.9	166.4	166.0	165.7	165.5	165.4	165.2	165.1	165.2	165.4	165.5
110°	189.0	188.7	188.4	188.2	187.9	187.7	187.4	187.2	187.4	187.7	187.9



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	211.1	211.1	211.0	210.9	210.7	210.6	210.4	210.3	210.4	210.6	210.7
115°	245.9	246.1	246.4	246.3	246.0	245.6	245.2	244.8	245.2	245.6	246.0
117.5°	279.9	280.2	280.5	280.6	280.3	280.1	279.8	279.6	279.8	280.1	280.3
120°	303.2	303.8	304.4	304.4	303.6	302.8	302.1	301.2	302.1	302.8	303.6
122.5°	325.6	325.9	326.2	326.1	325.5	325.0	324.4	323.9	324.4	325.0	325.5
125°	359.4	359.6	359.9	359.8	359.4	359.0	358.7	358.3	358.7	359.0	359.4
127.5°	393.0	393.3	393.6	393.3	392.5	391.7	390.9	390.1	390.9	391.7	392.5
130°	415.0	415.4	415.7	415.4	414.3	413.3	412.3	411.3	412.3	413.3	414.3
132.5°	436.4	436.7	437.0	436.6	435.6	434.5	433.5	432.4	433.5	434.5	435.6
135°	468.0	468.1	468.3	467.9	467.2	466.4	465.6	464.8	465.6	466.4	467.2
137.5°	498.5	498.2	497.9	497.4	496.8	496.0	495.4	494.8	495.4	496.0	496.8
140°	518.8	518.6	518.5	518.1	517.5	516.8	516.1	515.5	516.1	516.8	517.5
142.5°	537.9	537.7	537.5	536.9	536.3	535.7	535.0	534.4	535.0	535.7	536.3
145°	566.0	565.6	565.2	564.9	564.7	564.4	564.2	563.9	564.2	564.4	564.7
147.5°	592.7	592.4	592.0	591.6	591.1	590.7	590.2	589.8	590.2	590.7	591.1
150°	609.5	609.3	608.9	608.7	608.4	608.2	607.9	607.7	607.9	608.2	608.4
152.5°	624.4	624.3	624.1	623.9	623.5	623.2	622.8	622.5	622.8	623.2	623.5
155°	646.0	645.9	645.8	645.7	645.7	645.7	645.7	645.7	645.7	645.7	645.7
157.5°	665.1	665.0	664.9	664.9	665.1	665.2	665.4	665.5	665.4	665.2	665.1
160°	676.8	676.8	676.8	676.9	677.2	677.4	677.7	677.9	677.7	677.4	677.2
162.5°	687.7	687.6	687.5	687.6	687.9	688.3	688.6	689.0	688.6	688.3	687.9
165°	701.6	701.6	701.6	701.8	702.2	702.6	703.0	703.3	703.0	702.6	702.2
167.5°	712.7	712.6	712.5	712.7	713.2	713.7	714.2	714.7	714.2	713.7	713.2
170°	718.8	718.8	718.8	719.1	719.6	720.1	720.6	721.1	720.6	720.1	719.6
172.5°	724.0	724.0	724.0	724.2	724.7	725.2	725.7	726.2	725.7	725.2	724.7
175°	729.2	729.2	729.2	729.5	730.0	730.5	731.0	731.5	731.0	730.5	730.0
177.5°	731.8	731.8	731.8	732.1	732.5	733.0	733.4	733.8	733.4	733.0	732.5
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	9.6	10.3	10.2	11.0	10.9	11.6	11.7	11.0	11.1	12.5	10.9
90°	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8	15.3	15.9	16.3
92.5°	17.5	18.4	19.3	20.2	21.2	22.1	22.5	22.9	23.3	23.7	23.9
95°	37.6	38.6	39.6	40.6	41.6	42.6	43.1	43.6	44.1	44.6	44.9
97.5°	63.0	63.7	64.4	65.2	65.9	66.8	67.3	67.9	68.5	69.1	69.3
100°	81.4	82.1	82.7	83.4	84.0	84.6	85.0	85.4	85.8	86.2	86.5
102.5°	100.9	101.6	102.4	103.3	104.1	104.9	105.3	105.7	106.1	106.4	106.6
105°	130.7	131.3	132.5	133.6	134.8	135.9	135.9	135.9	135.9	135.9	136.0
107.5°	165.7	166.0	166.4	166.9	167.4	167.8	168.2	168.6	169.1	169.5	169.7
110°	188.2	188.4	188.7	189.0	189.2	189.6	190.1	190.6	191.1	191.6	191.7



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	210.9	211.0	211.1	211.1	211.2	211.2	211.8	212.4	213.0	213.6	213.9
115°	246.3	246.4	246.1	245.9	245.6	245.4	245.5	245.6	245.8	245.9	245.9
117.5°	280.6	280.5	280.2	279.9	279.6	279.2	279.2	279.2	279.1	279.1	278.9
120°	304.4	304.4	303.8	303.2	302.5	301.8	301.7	301.5	301.4	301.3	301.1
122.5°	326.1	326.2	325.9	325.6	325.2	324.9	324.6	324.2	323.9	323.6	323.2
125°	359.8	359.9	359.6	359.4	359.1	358.9	358.3	357.8	357.3	356.8	356.3
127.5°	393.3	393.6	393.3	393.0	392.7	392.5	391.8	391.0	390.3	389.6	389.0
130°	415.4	415.7	415.4	415.0	414.5	414.1	413.6	413.1	412.6	412.1	411.4
132.5°	436.6	437.0	436.7	436.4	436.1	435.9	435.2	434.5	433.9	433.3	432.7
135°	467.9	468.3	468.1	468.0	467.9	467.8	467.3	466.7	466.2	465.6	465.2
137.5°	497.4	497.9	498.2	498.5	498.9	499.2	498.7	498.1	497.6	497.1	496.6
140°	518.1	518.5	518.6	518.8	518.9	519.0	518.9	518.8	518.6	518.5	518.0
142.5°	536.9	537.5	537.7	537.9	538.2	538.4	538.3	538.1	538.0	537.9	537.5
145°	564.9	565.2	565.6	566.0	566.4	566.8	566.6	566.5	566.4	566.3	565.9
147.5°	591.6	592.0	592.4	592.7	593.1	593.4	593.4	593.4	593.4	593.4	593.0
150°	608.7	608.9	609.3	609.5	609.8	610.0	610.0	610.0	610.0	610.0	609.7
152.5°	623.9	624.1	624.3	624.4	624.6	624.7	624.9	625.2	625.4	625.6	625.3
155°	645.7	645.8	645.9	646.0	646.2	646.3	646.8	647.3	647.8	648.3	648.1
157.5°	664.9	664.9	665.0	665.1	665.2	665.3	665.8	666.4	666.9	667.4	667.3
160°	676.9	676.8	676.8	676.8	676.8	676.8	677.4	678.1	678.7	679.3	679.4
162.5°	687.6	687.5	687.6	687.7	687.8	687.9	688.5	689.1	689.8	690.4	690.3
165°	701.8	701.6	701.6	701.6	701.6	701.6	702.4	703.2	703.9	704.7	704.6
167.5°	712.7	712.5	712.6	712.7	712.8	712.9	713.7	714.5	715.3	716.1	716.1
170°	719.1	718.8	718.8	718.8	718.8	718.8	719.7	720.6	721.5	722.5	722.5
172.5°	724.2	724.0	724.0	724.0	724.0	724.0	724.8	725.5	726.3	727.1	727.1
175°	729.5	729.2	729.2	729.2	729.2	729.2	730.0	730.7	731.5	732.4	732.3
177.5°	732.1	731.8	731.8	731.8	731.8	731.8	732.5	733.2	733.8	734.4	734.3
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	10.9	11.0	10.6	10.2	10.6	11.0	10.9	10.9	12.5	11.1	11.0
90°	16.6	16.8	17.1	17.3	17.1	16.8	16.6	16.3	15.9	15.3	14.8
92.5°	23.7	23.5	23.4	23.2	23.4	23.5	23.7	23.9	23.7	23.3	22.9
95°	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.6	44.1	43.6
97.5°	69.3	69.2	69.2	69.1	69.2	69.2	69.3	69.3	69.1	68.5	67.9
100°	86.7	87.1	87.3	87.6	87.3	87.1	86.7	86.5	86.2	85.8	85.4
102.5°	106.6	106.5	106.5	106.4	106.5	106.5	106.6	106.6	106.4	106.1	105.7
105°	136.3	136.5	136.8	137.1	136.8	136.5	136.3	136.0	135.9	135.9	135.9
107.5°	169.5	169.4	169.2	169.1	169.2	169.4	169.5	169.7	169.5	169.1	168.6
110°	191.5	191.2	191.0	190.7	191.0	191.2	191.5	191.7	191.6	191.1	190.6



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	213.9	213.8	213.8	213.7	213.8	213.8	213.9	213.9	213.6	213.0	212.4
115°	245.8	245.6	245.5	245.4	245.5	245.6	245.8	245.9	245.9	245.8	245.6
117.5°	278.6	278.2	277.9	277.5	277.9	278.2	278.6	278.9	279.1	279.1	279.2
120°	300.8	300.6	300.3	300.1	300.3	300.6	300.8	301.1	301.3	301.4	301.5
122.5°	322.9	322.4	322.1	321.7	322.1	322.4	322.9	323.2	323.6	323.9	324.2
125°	355.8	355.3	354.8	354.3	354.8	355.3	355.8	356.3	356.8	357.3	357.8
127.5°	388.4	387.8	387.2	386.6	387.2	387.8	388.4	389.0	389.6	390.3	391.0
130°	410.5	409.6	408.7	407.8	408.7	409.6	410.5	411.4	412.1	412.6	413.1
132.5°	432.0	431.3	430.6	429.9	430.6	431.3	432.0	432.7	433.3	433.9	434.5
135°	465.0	464.7	464.5	464.2	464.5	464.7	465.0	465.2	465.6	466.2	466.7
137.5°	496.0	495.5	495.0	494.5	495.0	495.5	496.0	496.6	497.1	497.6	498.1
140°	517.1	516.1	515.2	514.4	515.2	516.1	517.1	518.0	518.5	518.6	518.8
142.5°	536.7	536.0	535.3	534.6	535.3	536.0	536.7	537.5	537.9	538.0	538.1
145°	565.4	564.9	564.4	563.9	564.4	564.9	565.4	565.9	566.3	566.4	566.5
147.5°	592.3	591.5	590.8	590.0	590.8	591.5	592.3	593.0	593.4	593.4	593.4
150°	608.8	608.0	607.3	606.5	607.3	608.0	608.8	609.7	610.0	610.0	610.0
152.5°	624.7	624.0	623.4	622.7	623.4	624.0	624.7	625.3	625.6	625.4	625.2
155°	647.2	646.3	645.5	644.6	645.5	646.3	647.2	648.1	648.3	647.8	647.3
157.5°	666.6	665.9	665.2	664.5	665.2	665.9	666.6	667.3	667.4	666.9	666.4
160°	678.9	678.4	677.9	677.4	677.9	678.4	678.9	679.4	679.3	678.7	678.1
162.5°	689.5	688.7	687.9	687.1	687.9	688.7	689.5	690.3	690.4	689.8	689.1
165°	703.7	702.8	702.0	701.0	702.0	702.8	703.7	704.6	704.7	703.9	703.2
167.5°	715.3	714.5	713.7	712.9	713.7	714.5	715.3	716.1	716.1	715.3	714.5
170°	721.5	720.6	719.7	718.8	719.7	720.6	721.5	722.5	722.5	721.5	720.6
172.5°	726.2	725.3	724.4	723.5	724.4	725.3	726.2	727.1	727.1	726.3	725.5
175°	731.3	730.4	729.5	728.6	729.5	730.4	731.3	732.3	732.4	731.5	730.7
177.5°	733.6	732.9	732.2	731.4	732.2	732.9	733.6	734.3	734.4	733.8	733.2
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	11.7	11.6	10.9	11.0	10.2	10.3	9.6	9.8	9.9	9.7	10.3
90°	14.3	13.8	12.1	10.5	8.8	7.2	5.7	4.4	3.1	1.8	0.6
92.5°	22.5	22.1	21.2	20.2	19.3	18.4	17.5	16.6	15.7	14.8	13.9
95°	43.1	42.6	41.6	40.6	39.6	38.6	37.6	36.7	35.7	34.8	34.0
97.5°	67.3	66.8	65.9	65.2	64.4	63.7	63.0	62.4	61.7	61.0	60.4
100°	85.0	84.6	84.0	83.4	82.7	82.1	81.4	80.7	79.9	79.1	78.4
102.5°	105.3	104.9	104.1	103.3	102.4	101.6	100.9	100.5	100.0	99.6	99.1
105°	135.9	135.9	134.8	133.6	132.5	131.3	130.7	130.4	130.1	129.9	129.6
107.5°	168.2	167.8	167.4	166.9	166.4	166.0	165.7	165.5	165.4	165.2	165.1
110°	190.1	189.6	189.2	189.0	188.7	188.4	188.2	187.9	187.7	187.4	187.2



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	211.8	211.2	211.2	211.1	211.1	211.0	210.9	210.7	210.6	210.4	210.3
115°	245.5	245.4	245.6	245.9	246.1	246.4	246.3	246.0	245.6	245.2	244.8
117.5°	279.2	279.2	279.6	279.9	280.2	280.5	280.6	280.3	280.1	279.8	279.6
120°	301.7	301.8	302.5	303.2	303.8	304.4	304.4	303.6	302.8	302.1	301.2
122.5°	324.6	324.9	325.2	325.6	325.9	326.2	326.1	325.5	325.0	324.4	323.9
125°	358.3	358.9	359.1	359.4	359.6	359.9	359.8	359.4	359.0	358.7	358.3
127.5°	391.8	392.5	392.7	393.0	393.3	393.6	393.3	392.5	391.7	390.9	390.1
130°	413.6	414.1	414.5	415.0	415.4	415.7	415.4	414.3	413.3	412.3	411.3
132.5°	435.2	435.9	436.1	436.4	436.7	437.0	436.6	435.6	434.5	433.5	432.4
135°	467.3	467.8	467.9	468.0	468.1	468.3	467.9	467.2	466.4	465.6	464.8
137.5°	498.7	499.2	498.9	498.5	498.2	497.9	497.4	496.8	496.0	495.4	494.8
140°	518.9	519.0	518.9	518.8	518.6	518.5	518.1	517.5	516.8	516.1	515.5
142.5°	538.3	538.4	538.2	537.9	537.7	537.5	536.9	536.3	535.7	535.0	534.4
145°	566.6	566.8	566.4	566.0	565.6	565.2	564.9	564.7	564.4	564.2	563.9
147.5°	593.4	593.4	593.1	592.7	592.4	592.0	591.6	591.1	590.7	590.2	589.8
150°	610.0	610.0	609.8	609.5	609.3	608.9	608.7	608.4	608.2	607.9	607.7
152.5°	624.9	624.7	624.6	624.4	624.3	624.1	623.9	623.5	623.2	622.8	622.5
155°	646.8	646.3	646.2	646.0	645.9	645.8	645.7	645.7	645.7	645.7	645.7
157.5°	665.8	665.3	665.2	665.1	665.0	664.9	664.9	665.1	665.2	665.4	665.5
160°	677.4	676.8	676.8	676.8	676.8	676.8	676.9	677.2	677.4	677.7	677.9
162.5°	688.5	687.9	687.8	687.7	687.6	687.5	687.6	687.9	688.3	688.6	689.0
165°	702.4	701.6	701.6	701.6	701.6	701.6	701.8	702.2	702.6	703.0	703.3
167.5°	713.7	712.9	712.8	712.7	712.6	712.5	712.7	713.2	713.7	714.2	714.7
170°	719.7	718.8	718.8	718.8	718.8	718.8	719.1	719.6	720.1	720.6	721.1
172.5°	724.8	724.0	724.0	724.0	724.0	724.0	724.2	724.7	725.2	725.7	726.2
175°	730.0	729.2	729.2	729.2	729.2	729.2	729.5	730.0	730.5	731.0	731.5
177.5°	732.5	731.8	731.8	731.8	731.8	731.8	732.1	732.5	733.0	733.4	733.8
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.4	11.6	13.1	14.2	16.3	17.9	17.8	17.3	17.2	16.9	16.5
90°	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3	14.8
92.5°	14.8	15.7	16.6	17.5	18.4	19.3	20.2	21.2	22.1	22.5	22.9
95°	34.8	35.7	36.7	37.6	38.6	39.6	40.6	41.6	42.6	43.1	43.6
97.5°	61.0	61.7	62.4	63.0	63.7	64.4	65.2	65.9	66.8	67.3	67.9
100°	79.1	79.9	80.7	81.4	82.1	82.7	83.4	84.0	84.6	85.0	85.4
102.5°	99.6	100.0	100.5	100.9	101.6	102.4	103.3	104.1	104.9	105.3	105.7
105°	129.9	130.1	130.4	130.7	131.3	132.5	133.6	134.8	135.9	135.9	135.9
107.5°	165.2	165.4	165.5	165.7	166.0	166.4	166.9	167.4	167.8	168.2	168.6
110°	187.4	187.7	187.9	188.2	188.4	188.7	189.0	189.2	189.6	190.1	190.6



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	210.4	210.6	210.7	210.9	211.0	211.1	211.1	211.2	211.2	211.8	212.4
115°	245.2	245.6	246.0	246.3	246.4	246.1	245.9	245.6	245.4	245.5	245.6
117.5°	279.8	280.1	280.3	280.6	280.5	280.2	279.9	279.6	279.2	279.2	279.2
120°	302.1	302.8	303.6	304.4	304.4	303.8	303.2	302.5	301.8	301.7	301.5
122.5°	324.4	325.0	325.5	326.1	326.2	325.9	325.6	325.2	324.9	324.6	324.2
125°	358.7	359.0	359.4	359.8	359.9	359.6	359.4	359.1	358.9	358.3	357.8
127.5°	390.9	391.7	392.5	393.3	393.6	393.3	393.0	392.7	392.5	391.8	391.0
130°	412.3	413.3	414.3	415.4	415.7	415.4	415.0	414.5	414.1	413.6	413.1
132.5°	433.5	434.5	435.6	436.6	437.0	436.7	436.4	436.1	435.9	435.2	434.5
135°	465.6	466.4	467.2	467.9	468.3	468.1	468.0	467.9	467.8	467.3	466.7
137.5°	495.4	496.0	496.8	497.4	497.9	498.2	498.5	498.9	499.2	498.7	498.1
140°	516.1	516.8	517.5	518.1	518.5	518.6	518.8	518.9	519.0	518.9	518.8
142.5°	535.0	535.7	536.3	536.9	537.5	537.7	537.9	538.2	538.4	538.3	538.1
145°	564.2	564.4	564.7	564.9	565.2	565.6	566.0	566.4	566.8	566.6	566.5
147.5°	590.2	590.7	591.1	591.6	592.0	592.4	592.7	593.1	593.4	593.4	593.4
150°	607.9	608.2	608.4	608.7	608.9	609.3	609.5	609.8	610.0	610.0	610.0
152.5°	622.8	623.2	623.5	623.9	624.1	624.3	624.4	624.6	624.7	624.9	625.2
155°	645.7	645.7	645.7	645.7	645.8	645.9	646.0	646.2	646.3	646.8	647.3
157.5°	665.4	665.2	665.1	664.9	664.9	665.0	665.1	665.2	665.3	665.8	666.4
160°	677.7	677.4	677.2	676.9	676.8	676.8	676.8	676.8	676.8	677.4	678.1
162.5°	688.6	688.3	687.9	687.6	687.5	687.6	687.7	687.8	687.9	688.5	689.1
165°	703.0	702.6	702.2	701.8	701.6	701.6	701.6	701.6	701.6	702.4	703.2
167.5°	714.2	713.7	713.2	712.7	712.5	712.6	712.7	712.8	712.9	713.7	714.5
170°	720.6	720.1	719.6	719.1	718.8	718.8	718.8	718.8	718.8	719.7	720.6
172.5°	725.7	725.2	724.7	724.2	724.0	724.0	724.0	724.0	724.0	724.8	725.5
175°	731.0	730.5	730.0	729.5	729.2	729.2	729.2	729.2	729.2	730.0	730.7
177.5°	733.4	733.0	732.5	732.1	731.8	731.8	731.8	731.8	731.8	732.5	733.2
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	16.2	15.9	15.6	16.0	15.7	15.2	16.2
90°	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	23.3	23.7	23.9	23.7	23.5	23.4	23.2
95°	44.1	44.6	44.9	44.9	44.9	44.9	44.9
97.5°	68.5	69.1	69.3	69.3	69.2	69.2	69.1
100°	85.8	86.2	86.5	86.7	87.1	87.3	87.6
102.5°	106.1	106.4	106.6	106.6	106.5	106.5	106.4
105°	135.9	135.9	136.0	136.3	136.5	136.8	137.1
107.5°	169.1	169.5	169.7	169.5	169.4	169.2	169.1
110°	191.1	191.6	191.7	191.5	191.2	191.0	190.7



TEST NUMBER: P331965-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	213.0	213.6	213.9	213.9	213.8	213.8	213.7
115°	245.8	245.9	245.9	245.8	245.6	245.5	245.4
117.5°	279.1	279.1	278.9	278.6	278.2	277.9	277.5
120°	301.4	301.3	301.1	300.8	300.6	300.3	300.1
122.5°	323.9	323.6	323.2	322.9	322.4	322.1	321.7
125°	357.3	356.8	356.3	355.8	355.3	354.8	354.3
127.5°	390.3	389.6	389.0	388.4	387.8	387.2	386.6
130°	412.6	412.1	411.4	410.5	409.6	408.7	407.8
132.5°	433.9	433.3	432.7	432.0	431.3	430.6	429.9
135°	466.2	465.6	465.2	465.0	464.7	464.5	464.2
137.5°	497.6	497.1	496.6	496.0	495.5	495.0	494.5
140°	518.6	518.5	518.0	517.1	516.1	515.2	514.4
142.5°	538.0	537.9	537.5	536.7	536.0	535.3	534.6
145°	566.4	566.3	565.9	565.4	564.9	564.4	563.9
147.5°	593.4	593.4	593.0	592.3	591.5	590.8	590.0
150°	610.0	610.0	609.7	608.8	608.0	607.3	606.5
152.5°	625.4	625.6	625.3	624.7	624.0	623.4	622.7
155°	647.8	648.3	648.1	647.2	646.3	645.5	644.6
157.5°	666.9	667.4	667.3	666.6	665.9	665.2	664.5
160°	678.7	679.3	679.4	678.9	678.4	677.9	677.4
162.5°	689.8	690.4	690.3	689.5	688.7	687.9	687.1
165°	703.9	704.7	704.6	703.7	702.8	702.0	701.0
167.5°	715.3	716.1	716.1	715.3	714.5	713.7	712.9
170°	721.5	722.5	722.5	721.5	720.6	719.7	718.8
172.5°	726.3	727.1	727.1	726.2	725.3	724.4	723.5
175°	731.5	732.4	732.3	731.3	730.4	729.5	728.6
177.5°	733.8	734.4	734.3	733.6	732.9	732.2	731.4
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3

(END OF REPORT)