

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331970-840

Luminaire Tested: **S123DIP-S775D585U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331970-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5566.4 lumens  
Efficiency: N/A  
Efficacy: 138.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45	40
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	37	59	48	41	36	42	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.8	2.1
10°-20°	327.1	5.9
20°-30°	483.2	8.7
30°-40°	564.4	10.1
40°-50°	567.4	10.2
50°-60°	498.4	9.0
60°-70°	371.3	6.7
70°-80°	211.6	3.8
80°-90°	62.9	1.1
90°-100°	28.2	0.5
100°-110°	134.3	2.4
110°-120°	322.7	5.8
120°-130°	410.9	7.4
130°-140°	439.0	7.9
140°-150°	410.5	7.4
150°-160°	331.2	5.9
160°-170°	213.7	3.8
170°-180°	73.7	1.3
0°-30°	926.1	16.6
0°-40°	1490.5	26.8
0°-60°	2556.3	45.9
0°-90°	3202.1	57.5
90°-120°	485.2	8.7
90°-150°	1745.7	31.4
90°-180°	2364.0	42.5
0°-180°	5566.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	6	14	16	17	5
95°	35	13	18	22	22	43
105°	172	175	126	30	25	182
115°	322	326	331	336	339	318
125°	454	458	461	462	463	405
135°	565	568	571	572	571	435
145°	652	656	657	658	658	408
155°	718	717	718	720	717	331
165°	757	756	755	759	756	214
175°	775	773	773	777	772	74
180°	775	775	775	775	775	



TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.1	21.8	21.5	21.2	20.9	20.8	20.9	21.1	21.2	21.4	21.3
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	10.7	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6
95°	35.1	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8
97.5°	70.6	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6
100°	97.4	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0
102.5°	127.7	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7
105°	171.7	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5
107.5°	217.9	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6
110°	248.8	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5



TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9
115°	321.9	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9
117.5°	364.3	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2
120°	390.5	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5
122.5°	417.3	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4
125°	453.8	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0
127.5°	489.4	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2
130°	511.5	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9
132.5°	532.7	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7
135°	565.0	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2
137.5°	592.7	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0
140°	611.1	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8
142.5°	628.1	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8
145°	652.0	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4
147.5°	674.5	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5
150°	688.3	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5
152.5°	700.7	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7
155°	718.2	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3
157.5°	731.8	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0
160°	740.1	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7
162.5°	748.0	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8
165°	757.4	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2
167.5°	764.8	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6
170°	768.9	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7
172.5°	771.7	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4
175°	775.3	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9
177.5°	776.2	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	21.2	21.1	21.0	21.0	21.1	21.1	21.2	21.2
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	16.4	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	19.7	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	20.6	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	21.0	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	31.5	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	80.8	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	197.9	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	251.4	247.1	242.9	231.6	213.3	195.0	176.7	158.3





TEST NUMBER: P331970-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.9	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	333.2	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	373.2	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	399.5	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.2	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.3	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	497.6	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.4	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.2	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	599.6	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.3	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.2	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.7	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	678.8	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	691.7	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.2	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	718.9	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	732.7	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	740.5	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	747.6	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	757.2	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	771.4	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	774.8	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.0	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)