

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331972-840

Luminaire Tested: **S123DIP-S775D585U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331972-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5342.9 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	30	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	2.2
10°-20°	327.1	6.1
20°-30°	483.2	9.0
30°-40°	564.4	10.6
40°-50°	567.4	10.6
50°-60°	498.4	9.3
60°-70°	371.3	6.9
70°-80°	211.6	4.0
80°-90°	62.9	1.2
90°-100°	158.3	3.0
100°-110°	448.4	8.4
110°-120°	441.1	8.3
120°-130°	351.8	6.6
130°-140°	277.4	5.2
140°-150°	207.0	3.9
150°-160°	144.3	2.7
160°-170°	84.8	1.6
170°-180°	27.6	0.5
0°-30°	926.1	17.3
0°-40°	1490.5	27.9
0°-60°	2556.3	47.8
0°-90°	3202.2	59.9
90°-120°	1047.8	19.6
90°-150°	1884.1	35.3
90°-180°	2141.0	40.1
0°-180°	5342.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	1	7	14	16	17	4
95°	20	64	342	100	67	21
105°	67	99	463	810	733	71
115°	118	147	354	777	891	117
125°	164	194	331	599	703	146
135°	192	230	326	493	570	149
145°	219	251	322	405	445	138
155°	249	269	312	354	369	115
165°	272	280	298	316	322	77
175°	284	284	286	290	290	27
180°	285	285	285	285	285	



TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.2	21.9	21.5	21.3	21.0	20.9	21.0	21.2	21.3	21.5	21.2
90°	1.1	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8
92.5°	7.2	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9
95°	19.6	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0
97.5°	33.4	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3
100°	42.6	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9
102.5°	52.3	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6
105°	66.9	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4
107.5°	82.2	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9
110°	93.3	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2



TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.4	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5
115°	118.1	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9
117.5°	132.7	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4
120°	142.9	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5
122.5°	151.6	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9
125°	164.2	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2
127.5°	173.7	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3
130°	179.8	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9
132.5°	184.3	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8
135°	192.4	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0
137.5°	200.0	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3
140°	205.1	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0
142.5°	210.6	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4
145°	219.4	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4
147.5°	228.4	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6
150°	234.4	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3
152.5°	240.4	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7
155°	249.4	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2
157.5°	256.5	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9
160°	262.1	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8
162.5°	266.2	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6
165°	272.5	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0
167.5°	277.2	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6
170°	279.9	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4
172.5°	281.8	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1
175°	284.0	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4
177.5°	285.0	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	21.1	21.0	21.0	21.1	21.0	21.1	21.2	21.1
90°	14.4	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	48.5	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	207.3	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	516.9	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	679.1	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	733.1	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	748.8	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	703.4	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	660.0	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P331972-840

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	617.2	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	560.5	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	519.3	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	497.7	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	480.6	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	457.9	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	438.1	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	425.7	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	414.1	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	398.6	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	384.5	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	376.2	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	368.3	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	358.8	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	351.1	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	345.6	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	340.5	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	333.0	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	324.9	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	320.2	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	314.8	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	307.6	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	301.3	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	297.2	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	293.6	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	288.6	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.5	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)