

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831674

Luminaire Tested: S123DIP-S775D585U840-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831674
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U840-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5723.7 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 41.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63				
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54				
2	93	86	80	75	87	81	75	71	71	67	64	62	59	57	54	52	50	46				
3	85	76	69	63	80	72	65	60	63	59	55	56	52	49	49	46	44	40				
4	78	68	60	54	73	64	57	52	57	52	47	50	46	43	44	41	38	35				
5	72	61	53	47	68	58	51	45	52	46	42	46	41	38	40	37	34	31				
6	67	55	47	42	63	52	45	40	47	41	37	42	37	34	37	33	31	28				
7	62	50	43	37	59	48	41	36	43	37	33	38	34	30	34	31	28	25				
8	58	46	39	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23				
9	54	42	35	30	51	40	34	29	37	31	27	33	28	25	30	26	23	21				
10	51	39	32	27	48	37	31	27	34	29	25	31	26	23	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	23983	23983	23983	23983	23983
5°	30331	28627	24198	19500	17919
10°	30626	31552	24037	15545	13584
15°	23066	29294	23873	13164	11487
20°	16071	23704	23568	11512	10434
25°	12256	18229	23049	10592	9786
30°	10602	14482	22219	9940	9266
35°	9837	12227	21262	9469	8899
40°	9312	10968	19918	9022	8775
45°	9003	10152	18211	8672	8719
50°	8847	9505	16188	8354	8674
55°	8518	9032	14202	8053	8711
60°	8213	8525	12243	7767	8570
65°	7715	8046	10560	7465	8400
70°	7125	7437	8982	6965	7906
75°	6450	6667	7698	6471	7224
80°	5318	5833	6087	5641	6087
85°	4211	4730	4471	4792	4854

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 20791 cd/sqm



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.6	3.7
10°-20°	524.0	9.2
20°-30°	620.5	10.8
30°-40°	623.9	10.9
40°-50°	572.4	10.0
50°-60°	472.4	8.3
60°-70°	334.2	5.8
70°-80°	178.4	3.1
80°-90°	46.8	0.8
90°-100°	154.4	2.7
100°-110°	452.1	7.9
110°-120°	441.4	7.7
120°-130°	351.6	6.1
130°-140°	277.4	4.8
140°-150°	206.9	3.6
150°-160°	144.3	2.5
160°-170°	84.8	1.5
170°-180°	27.6	0.5
0°-30°	1355.2	23.7
0°-40°	1979.1	34.6
0°-60°	3023.9	52.8
0°-90°	3583.3	62.6
90°-120°	1047.9	18.3
90°-150°	1883.8	32.9
90°-180°	2140.0	37.4
0°-180°	5723.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2228	2228	2228	2228	2228	
5°	2807	2649	2240	1805	1658	267
15°	2070	2629	2142	1181	1031	572
25°	1032	1535	1941	892	824	487
35°	749	930	1618	721	677	470
45°	591	667	1196	570	573	458
55°	454	481	757	429	464	406
65°	303	316	415	293	330	301
75°	155	160	185	156	174	163
85°	34	38	36	39	39	38
90°	17	14	1	14	17	11
95°	67	342	20	342	67	109
105°	733	463	67	463	733	731
115°	891	354	118	354	891	869
125°	703	331	164	331	703	636
135°	570	326	192	326	570	442
145°	445	322	220	322	445	283
155°	369	312	249	312	369	172
165°	322	298	272	298	322	92
175°	290	286	284	286	290	28
180°	284	284	284	284	284	



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1
2.5°	2511.4	2508.8	2506.2	2493.3	2480.4	2474.2	2468.0	2449.4	2430.8	2410.1	2389.4
5°	2807.1	2814.4	2821.6	2813.3	2805.1	2779.7	2754.4	2720.8	2687.2	2649.4	2611.7
7.5°	2943.6	2947.7	2951.9	2946.7	2941.5	2934.8	2928.1	2898.1	2868.1	2829.4	2790.6
10°	2802.0	2811.3	2820.6	2840.7	2860.9	2883.6	2906.4	2902.2	2898.1	2886.7	2875.4
12.5°	2490.7	2502.1	2513.5	2553.8	2594.1	2645.8	2697.5	2742.0	2786.4	2817.5	2848.5
15°	2069.9	2101.5	2133.0	2169.7	2206.4	2282.4	2358.4	2452.0	2545.5	2628.8	2712.0
17.5°	1705.0	1716.8	1728.7	1768.0	1807.3	1902.9	1998.6	2106.6	2214.7	2352.7	2490.7
20°	1403.0	1413.9	1424.8	1476.5	1528.1	1603.1	1678.1	1799.6	1921.0	2069.4	2217.8
22.5°	1178.7	1195.7	1212.8	1241.8	1270.7	1342.6	1414.4	1522.5	1630.5	1794.4	1958.3
25°	1031.9	1044.3	1056.7	1074.3	1091.8	1149.2	1206.6	1295.5	1384.4	1534.9	1685.3
27.5°	931.6	936.7	941.9	959.5	977.1	1014.3	1051.5	1128.0	1204.5	1332.2	1459.9
30°	853.0	856.6	860.2	875.7	891.2	916.6	941.9	997.2	1052.5	1165.2	1277.9
32.5°	798.2	800.8	803.4	815.3	827.1	845.2	863.3	903.7	944.0	1037.0	1130.1
35°	748.6	750.1	751.7	760.5	769.2	782.7	796.1	826.6	857.1	930.5	1003.9
37.5°	705.1	707.2	709.3	714.4	719.6	731.5	743.4	767.7	792.0	848.3	904.7
40°	662.7	666.4	670.0	673.6	677.2	687.0	696.9	715.5	734.1	780.6	827.1
42.5°	626.6	630.2	633.8	635.4	636.9	642.6	648.3	665.3	682.4	717.0	751.7
45°	591.4	593.0	594.5	596.1	597.6	602.3	606.9	621.9	636.9	666.9	696.9
47.5°	559.4	559.4	559.4	560.4	561.4	565.6	569.7	580.6	591.4	614.7	637.9
50°	528.3	528.3	528.3	526.8	525.2	527.8	530.4	538.7	546.9	567.6	588.3
52.5°	491.1	491.1	491.1	491.6	492.2	492.2	492.2	499.4	506.6	525.2	543.8
55°	453.9	456.0	458.0	456.5	454.9	456.0	457.0	461.6	466.3	481.3	496.3
57.5°	416.7	417.7	418.7	418.2	417.7	418.2	418.7	422.9	427.0	438.4	449.8
60°	381.5	381.5	381.5	380.5	379.5	380.5	381.5	383.6	385.7	396.0	406.3
62.5°	342.2	342.7	343.3	343.8	344.3	343.3	342.2	344.8	347.4	355.2	362.9
65°	302.9	303.5	304.0	305.5	307.1	306.0	305.0	307.6	310.2	315.9	321.6
67.5°	267.8	266.8	265.7	266.2	266.8	268.3	269.9	270.4	270.9	277.1	283.3
70°	226.4	227.5	228.5	228.0	227.5	228.0	228.5	230.0	231.6	236.3	240.9
72.5°	189.2	189.7	190.2	190.2	190.2	191.3	192.3	193.9	195.4	198.0	200.6
75°	155.1	155.1	155.1	156.1	157.2	157.7	158.2	158.2	158.2	160.3	162.3
77.5°	117.9	120.5	123.0	122.5	122.0	123.0	124.1	125.6	127.2	128.2	129.2
80°	85.8	85.8	85.8	86.3	86.9	88.4	90.0	91.0	92.0	94.1	96.2
82.5°	54.8	55.3	55.8	57.4	58.9	60.0	61.0	62.6	64.1	64.1	64.1
85°	34.1	33.1	32.1	33.1	34.1	35.2	36.2	36.7	37.2	38.3	39.3
87.5°	16.5	16.5	16.5	16.5	16.5	17.1	17.6	17.6	17.6	17.6	17.6
90°	16.7	17.3	16.7	16.1	16.7	15.6	15.0	14.4	13.8	14.4	12.7
92.5°	30.5	31.7	31.1	33.4	34.6	38.6	44.4	57.0	80.1	107.1	118.7
95°	66.8	69.1	73.2	78.3	89.3	110.0	140.5	207.4	277.1	341.6	304.1
97.5°	137.1	143.4	157.2	179.1	217.7	283.4	359.4	476.4	543.2	525.3	392.3
100°	361.2	360.6	383.0	425.1	483.3	565.1	632.4	679.1	658.9	545.5	368.6
102.5°	572.0	588.7	606.5	637.6	679.7	724.0	756.3	746.5	664.7	508.0	334.1
105°	732.7	735.6	754.0	775.9	802.4	817.3	806.4	748.8	628.4	463.1	307.0
107.5°	837.5	843.8	851.3	861.7	865.2	849.6	804.7	714.2	576.6	423.4	287.4
110°	897.4	898.6	899.7	895.1	879.0	838.7	766.1	660.1	528.2	390.5	277.1



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	909.5	908.9	903.2	886.5	853.6	798.9	715.4	606.5	486.1	368.6	271.3
115°	891.1	888.2	876.7	851.3	808.1	745.3	660.7	560.4	453.9	354.2	270.7
117.5°	850.8	846.7	829.4	801.2	756.3	691.2	613.4	524.7	432.6	344.4	271.3
120°	797.8	794.3	780.5	748.2	702.7	644.5	575.4	497.7	416.4	338.1	273.6
122.5°	748.2	743.6	728.1	699.8	660.7	607.7	544.9	476.4	403.2	334.1	277.6
125°	702.7	698.7	684.3	658.9	622.1	576.0	520.7	457.9	392.3	330.6	281.7
127.5°	663.6	660.1	646.8	625.0	591.6	548.9	498.2	441.2	381.9	328.9	286.3
130°	631.3	626.7	614.6	593.9	563.3	524.2	477.5	425.7	373.8	327.2	290.9
132.5°	599.6	596.7	586.4	565.6	537.4	500.5	457.9	411.3	366.3	326.6	294.3
135°	569.7	565.6	555.3	538.0	509.8	476.9	439.5	398.6	360.0	326.0	297.8
137.5°	538.0	534.5	525.9	508.0	483.8	454.5	421.1	386.5	354.2	324.9	300.1
140°	504.6	505.2	495.9	479.8	457.9	433.2	405.5	376.1	349.1	324.3	302.4
142.5°	473.5	474.0	466.0	452.2	434.3	413.6	390.5	366.3	344.4	323.1	304.1
145°	445.2	444.1	439.5	427.4	413.0	396.3	377.9	358.8	340.4	322.0	304.7
147.5°	421.1	420.5	415.9	407.2	395.7	383.6	368.1	352.5	336.4	320.3	304.7
150°	400.3	400.3	396.9	390.5	381.9	370.9	358.8	345.6	332.4	318.0	304.7
152.5°	383.0	383.0	381.3	375.6	369.2	360.6	350.2	339.3	327.7	315.1	303.0
155°	369.2	368.6	367.5	362.9	357.7	350.8	342.1	332.9	323.1	311.6	301.8
157.5°	356.0	356.0	354.8	351.4	346.8	341.0	334.1	326.0	318.0	308.7	300.1
160°	343.3	343.9	343.9	340.4	336.4	332.4	326.6	320.3	312.8	305.3	298.9
162.5°	331.8	332.4	332.4	329.5	327.2	323.7	318.5	313.3	307.6	301.8	296.6
165°	322.0	322.0	322.6	320.3	318.0	315.1	311.0	307.6	303.0	298.4	294.3
167.5°	312.2	312.2	312.8	311.0	309.9	307.6	305.3	302.4	298.4	294.9	292.0
170°	303.6	303.6	304.1	303.0	302.4	301.2	298.9	297.2	294.3	291.5	289.7
172.5°	295.5	296.1	297.2	296.1	296.1	295.5	293.8	292.6	290.3	288.6	288.0
175°	289.7	290.3	290.9	290.3	290.3	290.3	289.2	288.6	287.4	286.3	286.3
177.5°	285.7	285.7	286.8	286.3	286.8	286.8	286.3	285.7	285.1	284.5	285.1
180°	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1
2.5°	2383.2	2377.0	2354.3	2331.5	2305.7	2279.8	2260.7	2241.6	2213.1	2184.7	2161.4
5°	2582.8	2553.8	2505.7	2457.7	2392.5	2327.4	2283.4	2239.5	2180.6	2121.6	2074.6
7.5°	2740.9	2691.3	2624.1	2556.9	2471.6	2386.3	2305.7	2225.0	2135.1	2045.1	1971.7
10°	2841.8	2808.2	2730.6	2653.1	2538.8	2424.6	2311.9	2199.2	2083.4	1967.6	1870.4
12.5°	2851.6	2854.7	2783.3	2712.0	2582.8	2453.5	2316.5	2179.5	2033.7	1888.0	1774.7
15°	2765.2	2818.5	2779.2	2739.9	2609.6	2479.4	2310.8	2142.3	1974.3	1806.3	1675.5
17.5°	2605.0	2719.2	2724.9	2730.6	2600.3	2470.1	2283.4	2096.8	1906.6	1716.3	1578.8
20°	2386.3	2554.8	2612.7	2670.6	2564.7	2458.7	2258.1	2057.5	1844.5	1631.5	1487.3
22.5°	2163.0	2367.7	2473.7	2579.7	2501.1	2422.5	2209.0	1995.5	1770.6	1545.7	1399.4
25°	1908.6	2132.0	2294.8	2457.7	2409.6	2361.5	2151.1	1940.7	1701.3	1462.0	1312.6
27.5°	1686.9	1913.8	2110.3	2306.7	2296.4	2286.0	2077.2	1868.3	1623.3	1378.2	1234.0
30°	1489.4	1700.8	1920.5	2140.2	2165.6	2190.9	1989.3	1787.7	1542.1	1296.5	1157.5
32.5°	1314.6	1499.2	1734.9	1970.7	2020.3	2069.9	1888.0	1706.0	1463.0	1220.0	1086.1
35°	1171.4	1338.9	1574.7	1810.4	1872.4	1934.5	1776.3	1618.1	1381.3	1144.6	1016.9
37.5°	1044.8	1184.9	1414.9	1645.0	1721.0	1797.0	1655.3	1513.7	1291.9	1070.1	952.8
40°	939.8	1052.5	1264.0	1475.4	1563.3	1651.2	1534.4	1417.5	1207.1	996.7	888.7
42.5°	852.0	952.2	1144.0	1335.8	1420.1	1504.4	1405.6	1306.9	1119.7	932.6	833.9
45°	777.0	857.1	1031.3	1205.6	1285.7	1365.8	1281.0	1196.3	1031.3	866.4	774.4
47.5°	706.7	775.4	924.3	1073.2	1144.6	1215.9	1149.7	1083.6	944.0	804.4	721.2
50°	643.6	698.9	829.2	959.5	1021.5	1083.6	1025.1	966.7	852.0	737.2	664.8
52.5°	588.8	633.8	742.9	852.0	905.2	958.5	908.3	858.2	767.2	676.2	613.1
55°	534.5	572.8	667.4	762.0	798.2	834.4	795.6	756.8	683.4	610.0	556.8
57.5°	483.9	518.0	595.5	673.1	701.0	728.9	693.8	658.6	603.3	548.0	503.5
60°	434.3	462.2	526.8	591.4	608.5	625.5	597.1	568.7	529.9	491.1	451.3
62.5°	388.2	413.6	461.6	509.7	521.1	532.5	510.8	489.0	459.6	430.1	399.1
65°	340.7	359.8	399.1	438.4	445.6	452.9	433.7	414.6	392.4	370.1	347.4
67.5°	296.7	310.2	342.2	374.3	374.8	375.3	359.8	344.3	331.9	319.5	301.4
70°	253.8	266.8	287.9	309.1	309.7	310.2	297.8	285.4	276.1	266.8	253.3
72.5°	209.9	219.2	235.2	251.2	250.2	249.2	241.4	233.7	226.4	219.2	209.4
75°	170.1	177.8	188.7	199.5	196.4	193.3	189.2	185.1	178.9	172.7	166.5
77.5°	133.9	138.5	144.8	151.0	148.9	146.8	143.2	139.6	134.9	130.3	127.7
80°	98.2	100.3	104.4	108.6	107.5	106.5	102.4	98.2	97.2	96.2	92.5
82.5°	66.7	69.3	70.3	71.3	70.8	70.3	67.2	64.1	63.1	62.0	61.5
85°	39.8	40.3	40.8	41.4	39.8	38.3	37.2	36.2	36.2	36.2	35.7
87.5°	18.1	18.6	18.6	18.6	18.1	17.6	16.5	15.5	16.0	16.5	16.5
90°	10.9	9.2	7.5	6.3	5.2	3.5	2.3	1.2	2.3	3.5	5.2
92.5°	88.7	58.2	39.7	29.4	23.6	18.4	12.7	8.6	12.7	18.4	23.6
95°	209.7	123.8	74.9	52.4	37.4	27.6	21.3	19.6	21.3	27.6	37.4
97.5°	233.3	133.6	85.2	60.5	45.5	36.9	31.7	31.1	31.7	36.9	45.5
100°	217.2	131.9	91.6	69.1	55.3	47.2	43.2	42.6	43.2	47.2	55.3
102.5°	203.3	134.2	99.1	78.9	66.8	59.3	55.9	54.7	55.9	59.3	66.8
105°	198.1	138.8	107.7	89.9	78.9	72.0	68.5	66.8	68.5	72.0	78.9
107.5°	197.0	146.3	118.7	102.0	91.6	84.7	81.2	79.5	81.2	84.7	91.6
110°	199.9	156.1	130.2	114.0	104.3	97.9	95.0	93.3	95.0	97.9	104.3

TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	205.6	165.9	142.3	126.7	116.9	110.6	107.7	106.0	107.7	110.6	116.9
115°	212.0	176.8	154.9	139.4	129.6	123.8	120.4	118.1	120.4	123.8	129.6
117.5°	220.0	188.4	166.5	152.1	141.1	135.9	133.1	130.2	133.1	135.9	141.1
120°	229.2	199.3	178.6	164.2	153.2	147.5	144.6	142.8	144.6	147.5	153.2
122.5°	237.9	210.8	190.7	175.1	164.7	158.4	155.5	153.8	155.5	158.4	164.7
125°	247.1	221.8	201.6	186.0	175.1	168.8	165.3	164.2	165.3	168.8	175.1
127.5°	254.6	231.6	212.0	196.4	184.3	178.0	174.0	172.2	174.0	178.0	184.3
130°	262.1	240.2	221.2	205.6	193.5	186.6	181.4	179.7	181.4	186.6	193.5
132.5°	269.0	247.7	229.2	214.3	202.2	193.5	187.8	185.5	187.8	193.5	202.2
135°	274.8	255.2	237.3	221.8	209.7	201.0	194.7	192.4	194.7	201.0	209.7
137.5°	279.4	260.4	243.1	228.7	216.6	207.4	201.0	198.7	201.0	207.4	216.6
140°	282.8	265.5	248.8	234.4	222.9	213.7	207.9	205.1	207.9	213.7	222.9
142.5°	286.3	269.6	253.4	240.2	228.7	220.6	214.3	212.0	214.3	220.6	228.7
145°	288.6	273.0	258.0	244.8	235.0	226.4	221.2	219.5	221.2	226.4	235.0
147.5°	290.3	275.9	262.1	250.6	240.8	233.3	228.1	226.9	228.1	233.3	240.8
150°	290.9	278.8	265.5	255.2	247.1	239.6	235.0	234.4	235.0	239.6	247.1
152.5°	292.0	280.5	269.6	259.8	252.9	246.5	241.9	241.9	241.9	246.5	252.9
155°	292.0	282.8	273.0	265.0	258.6	252.9	249.4	249.4	249.4	252.9	258.6
157.5°	292.6	284.0	275.9	269.6	263.8	258.6	255.7	255.2	255.7	258.6	263.8
160°	292.6	285.7	278.8	273.0	269.0	264.4	262.1	262.1	262.1	264.4	269.0
162.5°	292.0	286.3	280.5	275.9	272.4	269.0	267.3	267.3	267.3	269.0	272.4
165°	290.9	286.8	282.2	278.2	275.9	273.0	271.9	272.4	271.9	273.0	275.9
167.5°	290.3	286.8	283.4	280.5	278.8	276.5	275.9	276.5	275.9	276.5	278.8
170°	288.6	286.3	283.4	282.2	281.1	279.4	278.8	279.9	278.8	279.4	281.1
172.5°	288.0	286.3	284.0	283.4	282.8	281.7	281.7	282.2	281.7	281.7	282.8
175°	286.8	285.7	284.5	284.0	284.0	282.8	283.4	284.0	283.4	282.8	284.0
177.5°	286.3	285.1	284.5	284.5	284.5	284.0	284.5	285.1	284.5	284.0	284.5
180°	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1	2228.1
2.5°	2138.2	2118.0	2097.8	2082.3	2066.8	2040.5	2014.1	2007.9	2001.7	1992.9	1984.1
5°	2027.5	1977.9	1928.3	1883.8	1839.4	1804.7	1770.1	1747.3	1724.6	1708.1	1691.5
7.5°	1898.3	1823.9	1749.4	1696.7	1643.9	1593.8	1543.7	1527.6	1511.6	1489.9	1468.2
10°	1773.2	1691.0	1608.8	1540.0	1471.3	1422.2	1373.1	1353.4	1333.8	1306.4	1279.0
12.5°	1661.5	1571.6	1481.6	1412.3	1343.1	1295.5	1248.0	1219.5	1191.1	1175.6	1160.1
15°	1544.7	1448.5	1352.4	1288.3	1224.2	1181.3	1138.4	1113.5	1088.7	1073.7	1058.7
17.5°	1441.3	1346.2	1251.1	1189.5	1128.0	1088.7	1049.4	1027.7	1006.0	994.6	983.3
20°	1343.1	1250.0	1157.0	1097.0	1037.0	1005.0	972.9	959.0	945.0	935.7	926.4
22.5°	1253.1	1161.6	1070.1	1018.9	967.8	941.9	916.1	906.2	896.4	888.7	880.9
25°	1163.2	1081.5	999.8	956.4	913.0	891.8	870.6	860.7	850.9	843.2	835.4
27.5°	1089.8	1011.7	933.6	896.4	859.2	842.7	826.1	818.4	810.6	803.4	796.1
30°	1018.4	948.6	878.8	846.8	814.7	799.7	784.8	777.0	769.2	762.5	755.8
32.5°	952.2	892.3	832.3	802.8	773.4	761.0	748.6	739.3	730.0	724.8	719.6
35°	889.2	835.4	781.7	757.4	733.1	720.6	708.2	700.5	692.7	688.6	684.5
37.5°	835.4	787.3	739.3	716.0	692.7	680.8	669.0	662.2	655.5	654.0	652.4
40°	780.6	739.3	697.9	675.2	652.4	642.1	631.7	627.6	623.5	622.4	621.4
42.5°	735.1	694.8	654.5	633.8	613.1	604.3	595.5	593.5	591.4	593.0	594.5
45°	682.4	648.8	615.2	596.1	576.9	569.7	562.5	560.9	559.4	562.5	565.6
47.5°	637.9	606.9	575.9	557.8	539.7	534.5	529.4	528.9	528.3	532.5	536.6
50°	592.4	562.5	532.5	518.0	503.5	498.9	494.2	495.8	497.3	504.0	510.8
52.5°	550.1	522.1	494.2	480.8	467.3	464.2	461.1	464.8	468.4	475.6	482.8
55°	503.5	478.2	452.9	442.5	432.2	429.1	426.0	433.2	440.5	447.2	453.9
57.5°	459.1	436.8	414.6	405.3	396.0	395.5	395.0	401.7	408.4	415.6	422.9
60°	411.5	392.9	374.3	367.0	359.8	360.8	361.9	369.6	377.4	383.1	388.8
62.5°	368.1	352.6	337.1	330.3	323.6	326.2	328.8	336.5	344.3	351.0	357.7
65°	324.7	311.7	298.8	294.2	289.5	293.1	296.7	303.5	310.2	314.8	319.5
67.5°	283.3	272.4	261.6	258.0	254.3	258.0	261.6	268.3	275.0	279.7	284.3
70°	239.9	231.1	222.3	219.7	217.1	221.3	225.4	231.1	236.8	241.4	246.1
72.5°	199.5	192.8	186.1	185.6	185.1	188.7	192.3	198.0	203.7	206.8	209.9
75°	160.3	156.6	153.0	152.5	152.0	155.6	159.2	162.3	165.4	168.0	170.6
77.5°	125.1	122.0	118.9	119.4	119.9	122.5	125.1	128.2	131.3	132.9	134.4
80°	88.9	87.9	86.9	87.9	88.9	91.0	93.1	95.1	97.2	98.2	99.3
82.5°	61.0	60.0	58.9	60.5	62.0	63.6	65.1	66.7	68.2	68.8	69.3
85°	35.2	36.7	38.3	38.3	38.3	38.8	39.3	39.8	40.3	39.8	39.3
87.5°	16.5	17.1	17.6	17.6	17.6	18.1	18.6	18.6	18.6	18.1	17.6
90°	6.3	7.5	9.2	10.9	12.7	14.4	13.8	14.4	15.0	15.6	16.7
92.5°	29.4	39.7	58.2	88.7	118.7	107.1	80.1	57.0	44.4	38.6	34.6
95°	52.4	74.9	123.8	209.7	304.1	341.6	277.1	207.4	140.5	110.0	89.3
97.5°	60.5	85.2	133.6	233.3	392.3	525.3	543.2	476.4	359.4	283.4	217.7
100°	69.1	91.6	131.9	217.2	368.6	545.5	658.9	679.1	632.4	565.1	483.3
102.5°	78.9	99.1	134.2	203.3	334.1	508.0	664.7	746.5	756.3	724.0	679.7
105°	89.9	107.7	138.8	198.1	307.0	463.1	628.4	748.8	806.4	817.3	802.4
107.5°	102.0	118.7	146.3	197.0	287.4	423.4	576.6	714.2	804.7	849.6	865.2
110°	114.0	130.2	156.1	199.9	277.1	390.5	528.2	660.1	766.1	838.7	879.0

TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	142.3	165.9	205.6	271.3	368.6	486.1	606.5	715.4	798.9	853.6
115°	139.4	154.9	176.8	212.0	270.7	354.2	453.9	560.4	660.7	745.3	808.1
117.5°	152.1	166.5	188.4	220.0	271.3	344.4	432.6	524.7	613.4	691.2	756.3
120°	164.2	178.6	199.3	229.2	273.6	338.1	416.4	497.7	575.4	644.5	702.7
122.5°	175.1	190.7	210.8	237.9	277.6	334.1	403.2	476.4	544.9	607.7	660.7
125°	186.0	201.6	221.8	247.1	281.7	330.6	392.3	457.9	520.7	576.0	622.1
127.5°	196.4	212.0	231.6	254.6	286.3	328.9	381.9	441.2	498.2	548.9	591.6
130°	205.6	221.2	240.2	262.1	290.9	327.2	373.8	425.7	477.5	524.2	563.3
132.5°	214.3	229.2	247.7	269.0	294.3	326.6	366.3	411.3	457.9	500.5	537.4
135°	221.8	237.3	255.2	274.8	297.8	326.0	360.0	398.6	439.5	476.9	509.8
137.5°	228.7	243.1	260.4	279.4	300.1	324.9	354.2	386.5	421.1	454.5	483.8
140°	234.4	248.8	265.5	282.8	302.4	324.3	349.1	376.1	405.5	433.2	457.9
142.5°	240.2	253.4	269.6	286.3	304.1	323.1	344.4	366.3	390.5	413.6	434.3
145°	244.8	258.0	273.0	288.6	304.7	322.0	340.4	358.8	377.9	396.3	413.0
147.5°	250.6	262.1	275.9	290.3	304.7	320.3	336.4	352.5	368.1	383.6	395.7
150°	255.2	265.5	278.8	290.9	304.7	318.0	332.4	345.6	358.8	370.9	381.9
152.5°	259.8	269.6	280.5	292.0	303.0	315.1	327.7	339.3	350.2	360.6	369.2
155°	265.0	273.0	282.8	292.0	301.8	311.6	323.1	332.9	342.1	350.8	357.7
157.5°	269.6	275.9	284.0	292.6	300.1	308.7	318.0	326.0	334.1	341.0	346.8
160°	273.0	278.8	285.7	292.6	298.9	305.3	312.8	320.3	326.6	332.4	336.4
162.5°	275.9	280.5	286.3	292.0	296.6	301.8	307.6	313.3	318.5	323.7	327.2
165°	278.2	282.2	286.8	290.9	294.3	298.4	303.0	307.6	311.0	315.1	318.0
167.5°	280.5	283.4	286.8	290.3	292.0	294.9	298.4	302.4	305.3	307.6	309.9
170°	282.2	283.4	286.3	288.6	289.7	291.5	294.3	297.2	298.9	301.2	302.4
172.5°	283.4	284.0	286.3	288.0	288.0	288.6	290.3	292.6	293.8	295.5	296.1
175°	284.0	284.5	285.7	286.8	286.3	286.3	287.4	288.6	289.2	290.3	290.3
177.5°	284.5	284.5	285.1	286.3	285.1	284.5	285.1	285.7	286.3	286.8	286.8
180°	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5	284.5



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2228.1	2228.1	2228.1	2228.1
2.5°	1980.5	1976.9	1962.4	1947.9
5°	1679.1	1666.7	1662.6	1658.4
7.5°	1467.1	1466.1	1444.4	1422.7
10°	1280.5	1282.1	1262.4	1242.8
12.5°	1147.1	1134.2	1132.7	1131.1
15°	1046.9	1035.0	1032.9	1030.8
17.5°	976.0	968.8	966.7	964.7
20°	922.3	918.1	914.5	910.9
22.5°	875.7	870.6	867.5	864.4
25°	830.8	826.1	825.1	824.0
27.5°	790.4	784.8	784.8	784.8
30°	752.2	748.6	747.0	745.5
32.5°	716.5	713.4	713.4	713.4
35°	682.9	681.4	679.3	677.2
37.5°	652.4	652.4	651.4	650.3
40°	622.9	624.5	624.5	624.5
42.5°	596.1	597.6	597.6	597.6
45°	568.1	570.7	571.8	572.8
47.5°	540.7	544.9	545.9	546.9
50°	513.9	517.0	517.5	518.0
52.5°	486.5	490.1	492.7	495.3
55°	457.5	461.1	462.7	464.2
57.5°	426.5	430.1	430.6	431.1
60°	392.4	396.0	397.0	398.1
62.5°	359.8	361.9	362.9	363.9
65°	322.6	325.7	327.8	329.8
67.5°	286.9	289.5	289.5	289.5
70°	247.1	248.1	249.7	251.2
72.5°	210.4	210.9	210.9	210.9
75°	171.6	172.7	173.2	173.7
77.5°	134.9	135.4	135.4	135.4
80°	98.7	98.2	98.2	98.2
82.5°	67.7	66.2	66.2	66.2
85°	38.8	38.3	38.8	39.3
87.5°	17.6	17.6	17.6	17.6
90°	16.1	16.7	17.3	16.7
92.5°	33.4	31.1	31.7	30.5
95°	78.3	73.2	69.1	66.8
97.5°	179.1	157.2	143.4	137.1
100°	425.1	383.0	360.6	361.2
102.5°	637.6	606.5	588.7	572.0
105°	775.9	754.0	735.6	732.7
107.5°	861.7	851.3	843.8	837.5
110°	895.1	899.7	898.6	897.4



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	886.5	903.2	908.9	909.5
115°	851.3	876.7	888.2	891.1
117.5°	801.2	829.4	846.7	850.8
120°	748.2	780.5	794.3	797.8
122.5°	699.8	728.1	743.6	748.2
125°	658.9	684.3	698.7	702.7
127.5°	625.0	646.8	660.1	663.6
130°	593.9	614.6	626.7	631.3
132.5°	565.6	586.4	596.7	599.6
135°	538.0	555.3	565.6	569.7
137.5°	508.0	525.9	534.5	538.0
140°	479.8	495.9	505.2	504.6
142.5°	452.2	466.0	474.0	473.5
145°	427.4	439.5	444.1	445.2
147.5°	407.2	415.9	420.5	421.1
150°	390.5	396.9	400.3	400.3
152.5°	375.6	381.3	383.0	383.0
155°	362.9	367.5	368.6	369.2
157.5°	351.4	354.8	356.0	356.0
160°	340.4	343.9	343.9	343.3
162.5°	329.5	332.4	332.4	331.8
165°	320.3	322.6	322.0	322.0
167.5°	311.0	312.8	312.2	312.2
170°	303.0	304.1	303.6	303.6
172.5°	296.1	297.2	296.1	295.5
175°	290.3	290.9	290.3	289.7
177.5°	286.3	286.8	285.7	285.7
180°	284.5	284.5	284.5	284.5



TEST NUMBER: P831674

CATALOG NUMBER: S123DIP-S775D585U840-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.71	16.65	16.56	17.51	18.60	17.95	18.89	18.80	19.75	20.83
	3H	17.36	18.20	18.23	19.08	20.19	19.38	20.22	20.24	21.09	22.20
	4H	17.94	18.74	18.82	19.62	20.74	19.83	20.63	20.71	21.51	22.63
	6H	18.32	19.05	19.21	19.94	21.07	20.11	20.84	21.00	21.73	22.86
	8H	18.42	19.11	19.32	20.02	21.15	20.18	20.87	21.07	21.78	22.91
	12H	18.47	19.13	19.37	20.03	21.18	20.20	20.86	21.10	21.76	22.92
4H	2H	16.30	17.09	17.18	17.97	19.09	18.12	18.91	19.00	19.79	20.91
	3H	18.13	18.79	19.02	19.70	20.84	19.75	20.41	20.64	21.32	22.45
	4H	18.83	19.43	19.74	20.34	21.50	20.33	20.93	21.24	21.84	23.00
	6H	19.31	19.83	20.23	20.76	21.92	20.74	21.26	21.66	22.19	23.36
	8H	19.45	19.93	20.37	20.86	22.04	20.85	21.34	21.78	22.27	23.44
	12H	19.52	19.95	20.46	20.90	22.08	20.90	21.34	21.84	22.28	23.46
8H	4H	19.10	19.59	20.02	20.51	21.69	20.44	20.93	21.37	21.85	23.03
	6H	19.70	20.09	20.64	21.06	22.24	20.95	21.35	21.90	22.32	23.49
	8H	19.90	20.26	20.86	21.22	22.41	21.13	21.48	22.09	22.44	23.63
	12H	20.03	20.34	20.99	21.29	22.54	21.23	21.54	22.19	22.50	23.74
12H	4H	19.11	19.54	20.05	20.49	21.67	20.42	20.86	21.36	21.80	22.98
	6H	19.75	20.10	20.70	21.06	22.25	20.96	21.32	21.92	22.28	23.47
	8H	19.98	20.29	20.94	21.25	22.49	21.17	21.48	22.13	22.43	23.67