

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832471

Luminaire Tested: S123RDP-S560D927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832471
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S560D927-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1918.2 lumens
 Efficiency: N/A
 Efficacy: 97.9 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 19.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832471
CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832471

CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89			87		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78			76		
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69			67		
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61			59		
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54			53		
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49			47		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45			43		
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41			39		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38			36		
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35			33		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	15573	15573	15573	15573	15573
5°	18492	17902	15672	12669	11761
10°	16753	18183	15593	10151	8708
15°	11535	15591	15428	8296	6888
20°	8025	12003	15119	6995	6054
25°	6115	9149	14668	6217	5580
30°	5323	7315	14105	5773	5168
35°	4887	6169	13306	5398	4794
40°	4460	5510	12261	5030	4451
45°	4028	5039	11134	4682	4109
50°	3656	4649	9805	4340	3686
55°	3307	4269	8527	4008	3162
60°	2962	3881	7408	3640	2988
65°	2735	3443	6375	3270	2825
70°	2222	2977	5564	2958	2297
75°	1951	2366	4712	2454	2021
80°	1767	2002	3862	2058	1909
85°	1618	1754	2927	1865	1754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 11749 cd/sqm

TEST NUMBER: P832471
 CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	6.9
10°-20°	305.2	15.9
20°-30°	350.1	18.3
30°-40°	345.1	18.0
40°-50°	304.3	15.9
50°-60°	234.1	12.2
60°-70°	153.9	8.0
70°-80°	74.8	3.9
80°-90°	18.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.2	41.0
0°-40°	1132.3	59.0
0°-60°	1670.7	87.1
0°-90°	1918.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1918.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1447	1447	1447	1447	1447	
5°	1711	1657	1450	1172	1088	156
15°	1035	1399	1384	744	618	292
25°	515	770	1235	524	470	243
35°	372	470	1013	411	365	232
45°	265	331	731	308	270	205
55°	176	228	454	214	168	158
65°	107	135	250	128	111	105
75°	47	57	113	59	49	50
85°	13	14	24	15	14	15
90°	0	0	0	0	0	

TEST NUMBER: P832471

CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8
2.5°	1603.4	1598.4	1593.3	1591.8	1590.4	1585.6	1580.9	1570.2	1559.5	1548.5	1537.6
5°	1711.4	1712.0	1712.6	1711.1	1709.6	1703.4	1697.1	1684.1	1671.0	1656.8	1642.6
7.5°	1678.2	1687.7	1697.1	1698.9	1700.7	1705.4	1710.2	1707.2	1704.3	1698.9	1693.6
10°	1532.8	1532.2	1531.6	1542.3	1553.0	1584.7	1616.5	1632.8	1649.1	1663.6	1678.2
12.5°	1295.5	1296.4	1297.3	1332.3	1367.3	1397.3	1427.2	1468.8	1510.3	1555.1	1599.9
15°	1035.1	1049.7	1064.2	1095.3	1126.5	1171.6	1216.7	1272.4	1328.2	1399.1	1469.9
17.5°	850.1	856.3	862.5	892.5	922.4	965.1	1007.8	1071.0	1134.2	1225.5	1316.9
20°	700.6	706.2	711.8	733.5	755.1	796.1	837.0	897.2	957.4	1047.9	1138.3
22.5°	584.9	595.9	606.8	621.4	635.9	665.6	695.2	756.6	818.0	900.5	982.9
25°	514.9	519.9	525.0	537.4	549.9	578.4	606.8	647.5	688.1	770.3	852.4
27.5°	467.4	468.9	470.4	479.6	488.8	507.2	525.6	563.2	600.9	668.5	736.2
30°	428.3	431.0	433.6	440.7	447.9	461.2	474.6	501.3	527.9	588.5	649.0
32.5°	398.0	399.5	401.0	406.9	412.9	422.7	432.4	453.5	474.6	520.8	567.1
35°	371.9	372.2	372.5	377.0	381.4	390.9	400.4	417.9	435.4	469.5	503.6
37.5°	342.3	344.4	346.4	349.7	353.0	361.3	369.6	383.8	398.0	426.2	454.4
40°	317.4	319.1	320.9	324.8	328.6	335.2	341.7	354.7	367.8	392.1	416.4
42.5°	292.4	293.6	294.8	298.7	302.5	310.5	318.5	328.9	339.3	359.5	379.6
45°	264.6	267.5	270.5	274.7	278.8	285.6	292.4	303.1	313.8	331.0	348.2
47.5°	241.4	242.9	244.4	248.0	251.5	259.8	268.1	277.6	287.1	303.1	319.1
50°	218.3	218.9	219.5	222.7	226.0	233.4	240.8	251.8	262.8	277.6	292.4
52.5°	196.3	197.8	199.3	202.6	205.8	210.9	215.9	227.2	238.5	253.0	267.5
55°	176.2	177.1	178.0	180.3	182.7	188.6	194.6	204.4	214.1	227.5	240.8
57.5°	157.2	158.4	159.6	161.4	163.1	168.5	173.8	182.4	191.0	204.4	217.7
60°	137.6	139.1	140.6	142.7	144.7	148.9	153.0	160.8	168.5	180.3	192.2
62.5°	123.4	123.7	124.0	125.8	127.5	130.5	133.5	139.7	145.9	157.8	169.7
65°	107.4	108.3	109.1	110.0	110.9	113.3	115.7	121.0	126.4	135.2	144.1
67.5°	90.8	91.6	92.5	94.0	95.5	97.6	99.7	103.2	106.8	115.1	123.4
70°	70.6	70.6	70.6	73.0	75.3	78.9	82.5	85.1	87.8	94.6	101.4
72.5°	57.5	57.8	58.1	58.4	58.7	60.8	62.9	67.3	71.8	75.9	80.1
75°	46.9	47.2	47.5	47.8	48.0	48.6	49.2	50.7	52.2	56.9	61.7
77.5°	37.4	37.7	38.0	38.3	38.6	39.2	39.7	40.3	40.9	42.7	44.5
80°	28.5	28.8	29.1	29.4	29.7	30.0	30.3	30.8	31.4	32.3	33.2
82.5°	20.8	20.8	20.8	20.8	20.8	21.4	21.9	21.9	21.9	22.5	23.1
85°	13.1	13.1	13.1	13.3	13.6	13.6	13.6	13.9	14.2	14.2	14.2
87.5°	5.9	5.6	5.3	5.6	5.9	5.9	5.9	6.2	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832471

CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8
2.5°	1536.1	1534.6	1520.4	1506.1	1492.2	1478.3	1467.9	1457.5	1440.0	1422.5	1411.5
5°	1631.3	1620.0	1597.5	1574.9	1541.1	1507.3	1478.8	1450.4	1414.2	1378.0	1347.7
7.5°	1684.4	1675.2	1647.9	1620.6	1575.8	1531.0	1486.6	1442.1	1388.7	1335.3	1289.6
10°	1685.9	1693.6	1671.0	1648.5	1598.1	1547.7	1487.1	1426.6	1354.9	1283.1	1224.1
12.5°	1633.1	1666.3	1661.6	1656.8	1605.5	1554.2	1480.6	1407.1	1319.0	1230.9	1157.0
15°	1534.3	1598.7	1617.7	1636.6	1594.2	1551.8	1468.2	1384.5	1281.0	1177.5	1092.7
17.5°	1407.1	1497.2	1547.4	1597.5	1566.6	1535.8	1444.1	1352.5	1235.9	1119.4	1027.1
20°	1256.4	1374.4	1453.0	1531.6	1520.4	1509.1	1414.5	1319.9	1194.1	1068.4	968.4
22.5°	1107.5	1232.1	1340.6	1449.2	1460.8	1472.3	1376.8	1281.3	1143.7	1006.1	904.3
25°	979.1	1105.7	1235.0	1364.4	1390.5	1416.6	1325.8	1235.0	1092.4	949.7	848.6
27.5°	856.6	977.0	1119.4	1261.7	1309.2	1356.6	1273.6	1190.6	1042.0	893.4	792.5
30°	756.6	864.3	1009.6	1155.0	1221.1	1287.2	1211.0	1134.8	987.4	840.0	741.2
32.5°	663.5	759.9	905.8	1051.7	1128.6	1205.4	1139.5	1073.7	931.9	790.1	692.6
35°	589.9	676.2	812.4	948.5	1034.5	1120.6	1066.6	1012.6	874.1	735.6	643.3
37.5°	526.8	599.1	727.0	854.8	946.2	1037.5	992.4	947.3	817.1	686.9	599.7
40°	474.6	532.7	651.6	770.6	860.1	949.7	911.2	872.6	756.0	639.5	557.9
42.5°	429.8	479.9	586.7	693.4	775.6	857.8	832.3	806.8	701.2	595.6	519.9
45°	390.3	432.4	526.5	620.5	696.1	771.8	751.6	731.4	640.4	549.3	479.9
47.5°	355.3	391.5	475.4	559.4	627.3	695.2	676.5	657.9	582.5	507.2	444.0
50°	323.3	354.1	424.1	494.1	555.2	616.3	600.9	585.5	523.2	460.9	406.3
52.5°	293.0	318.5	381.4	444.3	493.5	542.8	530.9	519.0	471.0	423.0	373.4
55°	264.3	287.7	340.8	393.9	436.0	478.1	466.3	454.4	417.0	379.6	336.0
57.5°	238.2	258.6	301.6	344.6	378.2	411.7	406.0	400.4	369.3	338.1	302.2
60°	210.6	229.0	266.0	303.1	330.1	357.1	350.6	344.1	321.8	299.6	268.7
62.5°	186.0	202.3	231.9	261.6	283.5	305.5	300.8	296.0	279.1	262.2	236.7
65°	160.2	176.2	200.2	224.2	241.4	258.6	254.5	250.3	237.6	224.8	204.4
67.5°	136.7	150.1	170.8	191.6	203.2	214.7	212.4	210.0	200.2	190.4	174.4
70°	113.0	124.6	141.8	159.0	167.0	175.0	175.9	176.8	167.9	159.0	147.1
72.5°	89.3	98.5	114.5	130.5	136.7	143.0	142.7	142.4	137.0	131.7	121.0
75°	68.5	75.3	87.8	100.3	105.6	110.9	112.1	113.3	108.3	103.2	97.3
77.5°	49.2	54.0	63.5	73.0	78.9	84.8	85.4	86.0	83.6	81.3	75.6
80°	34.7	36.2	42.1	48.0	54.3	60.5	61.4	62.3	59.9	57.5	54.0
82.5°	24.0	24.9	27.0	29.1	34.1	39.2	40.3	41.5	40.3	39.2	35.3
85°	14.5	14.8	15.7	16.6	19.0	21.4	22.5	23.7	23.1	22.5	20.5
87.5°	6.5	6.5	6.8	7.1	7.7	8.3	9.8	11.3	10.4	9.5	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832471

CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8	1446.8
2.5°	1400.5	1383.6	1366.7	1354.6	1342.4	1327.3	1312.2	1311.6	1311.0	1299.7	1288.4
5°	1317.5	1288.1	1258.8	1230.0	1201.2	1172.5	1143.7	1137.2	1130.6	1120.8	1111.1
7.5°	1243.9	1197.1	1150.2	1113.4	1076.7	1047.9	1019.1	999.5	980.0	964.8	949.7
10°	1165.0	1106.9	1048.8	1004.3	959.8	928.7	897.5	875.0	852.4	841.7	831.1
12.5°	1083.2	1020.0	956.8	913.2	869.6	832.3	794.9	774.4	754.0	739.1	724.3
15°	1007.8	939.9	872.0	825.7	779.5	744.5	709.5	689.0	668.5	653.7	638.9
17.5°	934.9	866.4	797.9	751.0	704.1	672.4	640.7	620.8	600.9	591.7	582.5
20°	868.4	799.3	730.2	686.0	641.8	610.7	579.6	568.9	558.2	549.6	541.0
22.5°	802.6	736.2	669.7	627.3	584.9	562.4	539.8	531.2	522.6	516.1	509.6
25°	747.4	681.3	615.1	578.1	541.0	523.5	506.0	500.4	494.7	488.2	481.7
27.5°	691.7	628.8	565.9	536.3	506.6	492.4	478.1	471.0	463.9	458.5	453.2
30°	642.4	584.3	526.2	501.5	476.9	464.5	452.0	444.3	436.6	431.6	426.5
32.5°	595.0	543.4	491.8	470.7	449.6	437.5	425.3	417.9	410.5	404.6	398.6
35°	551.1	506.3	461.5	442.2	423.0	410.8	398.6	391.2	383.8	377.9	371.9
37.5°	512.5	471.9	431.3	413.2	395.1	384.4	373.7	366.0	358.3	352.1	345.8
40°	476.3	440.5	404.6	387.1	369.6	358.0	346.4	339.6	332.8	327.1	321.5
42.5°	444.3	411.4	378.5	361.3	344.1	333.1	322.1	314.1	306.1	302.8	299.6
45°	410.5	381.4	352.4	335.8	319.1	307.6	296.0	289.2	282.4	279.4	276.4
47.5°	380.8	353.8	326.9	310.5	294.2	283.8	273.5	268.1	262.8	258.6	254.5
50°	351.8	325.7	299.6	283.8	268.1	259.2	250.3	243.8	237.3	234.3	231.3
52.5°	323.9	300.2	276.4	260.4	244.4	235.8	227.2	221.6	215.9	209.7	203.5
55°	292.4	271.7	250.9	236.7	222.4	213.6	204.7	198.1	191.6	185.1	178.6
57.5°	266.3	245.9	225.4	212.7	199.9	191.3	182.7	175.6	168.5	163.1	157.8
60°	237.9	220.1	202.3	189.8	177.4	169.1	160.8	153.9	147.1	144.4	141.8
62.5°	211.2	194.6	178.0	167.0	156.0	148.0	140.0	135.5	131.1	129.3	127.5
65°	183.9	169.7	155.4	145.3	135.2	128.4	121.6	119.5	117.5	116.0	114.5
67.5°	158.4	146.2	134.1	125.2	116.3	111.5	106.8	104.4	102.0	100.3	98.5
70°	135.2	124.6	113.9	106.2	98.5	94.0	89.6	87.5	85.4	82.2	78.9
72.5°	110.3	102.0	93.7	87.8	81.9	78.0	74.1	70.0	65.8	62.9	59.9
75°	91.4	83.0	74.7	69.1	63.5	59.0	54.6	53.1	51.6	50.7	49.8
77.5°	70.0	62.9	55.8	51.3	46.9	44.8	42.7	41.8	40.9	40.6	40.3
80°	50.4	44.5	38.6	36.2	33.8	33.2	32.6	32.0	31.4	31.1	30.8
82.5°	31.4	28.5	25.5	24.9	24.3	24.0	23.7	23.4	23.1	22.8	22.5
85°	18.4	17.2	16.0	15.7	15.4	15.1	14.8	14.8	14.8	14.8	14.8
87.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.4	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832471

CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1446.8	1446.8	1446.8	1446.8
2.5°	1285.5	1282.5	1281.3	1280.1
5°	1101.9	1092.7	1090.6	1088.5
7.5°	945.9	942.0	929.2	916.5
10°	819.2	807.3	802.0	796.7
12.5°	713.3	702.3	700.6	698.8
15°	631.2	623.5	620.8	618.1
17.5°	577.2	571.8	568.6	565.3
20°	537.1	533.3	530.9	528.5
22.5°	506.6	503.6	501.8	500.1
25°	477.2	472.8	471.3	469.8
27.5°	449.3	445.5	444.0	442.5
30°	423.2	420.0	417.9	415.8
32.5°	394.8	390.9	389.7	388.5
35°	369.6	367.2	366.0	364.8
37.5°	342.9	339.9	338.1	336.3
40°	320.0	318.5	317.7	316.8
42.5°	296.9	294.2	293.9	293.6
45°	273.8	271.1	270.5	269.9
47.5°	252.1	249.7	249.4	249.1
50°	228.1	224.8	222.4	220.1
52.5°	200.5	197.5	195.5	193.4
55°	175.3	172.0	170.2	168.5
57.5°	156.3	154.8	153.9	153.0
60°	140.9	140.0	139.4	138.8
62.5°	126.6	125.8	125.8	125.8
65°	113.6	112.7	111.8	110.9
67.5°	96.7	94.9	94.6	94.3
70°	76.2	73.6	73.3	73.0
72.5°	59.6	59.3	58.7	58.1
75°	49.2	48.6	48.6	48.6
77.5°	39.7	39.2	39.2	39.2
80°	30.5	30.3	30.5	30.8
82.5°	22.5	22.5	22.2	21.9
85°	14.5	14.2	14.2	14.2
87.5°	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832471

CATALOG NUMBER: S123RDP-S560D927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.24	15.70	14.61	16.01	16.33	18.91	20.36	19.27	20.68	20.99
	3H	15.51	16.81	15.89	17.14	17.50	20.45	21.75	20.83	22.08	22.44
	4H	15.92	17.14	16.32	17.49	17.87	20.97	22.19	21.37	22.54	22.92
	6H	16.23	17.35	16.64	17.72	18.11	21.31	22.43	21.72	22.80	23.19
	8H	16.33	17.40	16.76	17.79	18.19	21.40	22.47	21.83	22.86	23.26
	12H	16.40	17.43	16.83	17.81	18.24	21.45	22.48	21.88	22.86	23.29
4H	2H	15.04	16.26	15.44	16.61	16.99	18.97	20.19	19.37	20.54	20.92
	3H	16.46	17.47	16.87	17.87	18.27	20.68	21.69	21.09	22.09	22.49
	4H	16.93	17.84	17.37	18.26	18.70	21.31	22.22	21.74	22.63	23.07
	6H	17.33	18.12	17.79	18.56	19.03	21.78	22.56	22.24	23.01	23.47
	8H	17.47	18.20	17.93	18.65	19.12	21.92	22.65	22.38	23.10	23.57
	12H	17.57	18.23	18.05	18.71	19.18	22.01	22.66	22.49	23.14	23.61
8H	4H	17.29	18.02	17.75	18.47	18.94	21.32	22.05	21.78	22.50	22.97
	6H	17.77	18.38	18.27	18.87	19.35	21.83	22.44	22.33	22.93	23.41
	8H	17.97	18.51	18.48	19.02	19.51	22.02	22.56	22.54	23.07	23.56
	12H	18.13	18.61	18.64	19.10	19.67	22.16	22.64	22.67	23.13	23.70
12H	4H	17.33	17.98	17.81	18.46	18.93	21.29	21.95	21.78	22.43	22.90
	6H	17.83	18.37	18.35	18.89	19.38	21.81	22.35	22.32	22.86	23.35
	8H	18.08	18.56	18.59	19.05	19.62	22.03	22.51	22.54	23.00	23.57