

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331975-840

Luminaire Tested: **S123DIP-S775D805U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331975-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6230.9 lumens
Efficiency: N/A
Efficacy: 135.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	44	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	1.7
10°-20°	344.7	5.5
20°-30°	578.5	9.3
30°-40°	655.0	10.5
40°-50°	587.4	9.4
50°-60°	474.0	7.6
60°-70°	330.3	5.3
70°-80°	173.6	2.8
80°-90°	45.5	0.7
90°-100°	217.1	3.5
100°-110°	614.6	9.9
110°-120°	604.6	9.7
120°-130°	482.3	7.7
130°-140°	380.2	6.1
140°-150°	283.8	4.6
150°-160°	197.8	3.2
160°-170°	116.2	1.9
170°-180°	37.8	0.6
0°-30°	1030.6	16.5
0°-40°	1685.7	27.1
0°-60°	2747.1	44.1
0°-90°	3296.5	52.9
90°-120°	1436.3	23.1
90°-150°	2582.6	41.4
90°-180°	2934.0	47.1
0°-180°	6230.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	42
90°	23	2	23	2	23	14
95°	92	27	92	27	92	165
105°	1004	92	1004	92	1004	991
115°	1221	162	1221	162	1221	1187
125°	963	225	963	225	963	873
135°	781	264	781	264	781	606
145°	610	301	610	301	610	388
155°	506	342	506	342	506	236
165°	441	373	441	373	441	126
175°	397	389	397	389	397	39
180°	390	390	390	390	390	



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	17.3	16.6	16.9	17.1	16.9	17.0	17.2	17.5	17.8	18.3	18.3
90°	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7	19.0	19.7	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4	91.6	121.4	133.6
95°	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3	379.8	468.2	416.9
97.5°	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5	776.3	725.6	531.2
100°	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9	903.2	747.7	505.3
102.5°	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7	909.6	706.6	467.4
105°	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4	861.4	634.8	420.8
107.5°	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2	777.1	571.3	391.1
110°	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8	724.0	535.3	379.8



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1	677.9	511.3	373.4
115°	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2	622.2	485.5	371.1
117.5°	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9	588.5	470.4	372.5
120°	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2	570.9	463.4	375.1
122.5°	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8	556.3	459.1	379.4
125°	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6	537.7	453.2	386.1
127.5°	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6	521.3	450.4	393.6
130°	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5	512.4	448.5	398.7
132.5°	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6	504.2	447.8	402.5
135°	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3	493.4	446.9	408.2
137.5°	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9	484.1	445.1	412.0
140°	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5	478.5	444.5	414.5
142.5°	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8	473.4	443.2	416.4
145°	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9	466.7	441.3	417.7
147.5°	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3	460.0	438.4	417.7
150°	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7	455.6	435.9	417.7
152.5°	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8	450.5	432.6	415.8
155°	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4	442.9	427.2	413.7
157.5°	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2	434.4	422.2	411.0
160°	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0	428.7	418.5	409.8
162.5°	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4	423.0	414.7	407.3
165°	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6	415.3	409.0	403.4
167.5°	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0	407.9	403.3	399.7
170°	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4	403.4	399.5	397.2
172.5°	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3	399.0	396.4	395.3
175°	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6	393.9	392.4	392.4
177.5°	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	18.7	18.6	16.9	14.8	13.7	11.9	11.6	10.5	9.9	10.3	10.3
90°	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6	3.1	4.7	7.1
92.5°	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8	14.5	21.2	27.4
95°	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9	29.2	37.9	51.3
97.5°	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7	46.6	53.4	65.0
100°	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5	59.2	64.7	75.8
102.5°	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7	73.1	78.0	88.5
105°	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6	93.9	98.7	108.2
107.5°	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7	115.1	119.7	129.0
110°	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9	130.3	134.2	142.9



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8	144.2	148.1	156.8
115°	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9	165.0	169.8	177.6
117.5°	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9	185.5	189.5	196.7
120°	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8	198.1	202.1	210.1
122.5°	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8	210.2	214.1	222.7
125°	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0	226.6	231.4	240.0
127.5°	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1	240.4	246.3	255.2
130°	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3	248.7	255.8	265.3
132.5°	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7	255.7	263.4	274.8
135°	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7	266.9	275.6	287.4
137.5°	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1	277.4	286.0	298.6
140°	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0	285.0	293.0	305.6
142.5°	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6	292.0	300.5	311.8
145°	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8	303.2	310.3	322.1
147.5°	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2	314.6	321.5	331.7
150°	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3	322.1	328.4	338.7
152.5°	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5	329.7	336.0	345.1
155°	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8	341.8	346.6	354.5
157.5°	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6	352.2	356.1	363.0
160°	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2	359.2	362.4	368.7
162.5°	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0	365.0	367.5	372.5
165°	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4	372.6	374.3	378.2
167.5°	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9	379.0	379.8	382.7
170°	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7	382.1	382.9	385.3
172.5°	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3	385.3	385.5	387.2
175°	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2	388.5	387.7	389.2
177.5°	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6	390.0	389.4	390.0
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	10.2	10.9	11.0	11.9	11.9	12.8	12.6	12.0	12.1	13.5	12.2
90°	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7	20.5	21.3	22.9
92.5°	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4	52.7	46.6	42.5
95°	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3	192.7	150.8	122.4
97.5°	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5	567.5	465.6	371.2
100°	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9	866.9	774.6	662.4
102.5°	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7	1002.7	948.9	877.8
105°	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4	1105.3	1120.3	1099.8
107.5°	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2	1092.4	1161.5	1189.6
110°	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8	1050.1	1149.5	1204.9



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1	994.5	1106.0	1177.0
115°	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2	905.5	1021.7	1107.7
117.5°	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9	830.4	934.6	1022.0
120°	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2	788.7	883.5	963.2
122.5°	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8	755.3	843.0	917.2
125°	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6	713.8	789.5	852.7
127.5°	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6	677.2	745.7	803.1
130°	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5	654.5	718.5	772.1
132.5°	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6	633.1	692.6	743.8
135°	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3	602.4	653.7	698.7
137.5°	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9	572.9	617.1	656.1
140°	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5	555.8	593.7	627.6
142.5°	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8	539.4	572.3	601.8
145°	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9	518.0	543.2	566.1
147.5°	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3	502.0	522.4	538.7
150°	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7	491.9	508.5	523.4
152.5°	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8	482.4	497.1	509.6
155°	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4	469.0	480.8	490.3
157.5°	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2	455.9	465.0	472.4
160°	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0	447.7	455.6	461.1
162.5°	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4	438.8	446.1	451.0
165°	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6	426.4	431.9	435.9
167.5°	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0	416.7	419.9	422.7
170°	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4	409.8	412.9	414.5
172.5°	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3	404.0	406.6	407.6
175°	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6	396.4	397.9	397.9
177.5°	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3	391.9	392.5	392.5
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	12.0	12.2	11.9	11.3	11.9	12.2	12.0	12.2	13.5	12.1	12.0
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4
95°	107.3	100.3	94.7	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3
97.5°	313.0	277.4	256.1	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5
100°	582.7	525.0	494.2	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9
102.5°	815.8	770.1	744.4	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7
105°	1063.5	1033.5	1008.2	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4
107.5°	1190.3	1180.2	1171.6	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2
110°	1226.9	1233.2	1231.6	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.5	1237.1	1243.0	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1
115°	1166.9	1201.6	1217.5	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2
117.5°	1083.7	1123.5	1146.2	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9
120°	1025.6	1069.9	1088.7	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2
122.5°	972.5	1012.3	1033.2	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8
125°	903.2	938.0	957.7	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6
127.5°	848.1	877.8	895.6	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6
130°	814.1	842.4	859.0	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5
132.5°	783.0	811.5	826.2	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6
135°	737.4	761.1	775.3	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3
137.5°	688.6	712.7	724.7	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9
140°	657.7	679.7	692.5	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5
142.5°	627.3	646.9	658.3	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8
145°	585.8	602.4	608.7	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9
147.5°	553.6	564.8	570.9	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3
150°	535.3	544.0	548.8	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7
152.5°	518.9	526.9	529.8	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8
155°	497.4	503.7	505.3	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4
157.5°	478.6	483.3	484.6	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2
160°	466.7	471.3	471.3	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0
162.5°	454.6	458.7	458.7	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4
165°	439.0	442.1	441.3	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6
167.5°	424.1	426.4	425.6	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0
170°	415.3	416.9	416.1	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4
172.5°	407.7	409.3	407.9	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3
175°	397.9	398.7	397.9	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6
177.5°	391.9	392.5	391.3	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	12.6	12.8	11.9	11.9	11.0	10.9	10.2	10.3	10.3	9.9	10.5
90°	19.0	19.7	17.4	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6
92.5°	91.6	121.4	133.6	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8
95°	379.8	468.2	416.9	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9
97.5°	776.3	725.6	531.2	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7
100°	903.2	747.7	505.3	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5
102.5°	909.6	706.6	467.4	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7
105°	861.4	634.8	420.8	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6
107.5°	777.1	571.3	391.1	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7
110°	724.0	535.3	379.8	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	677.9	511.3	373.4	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8
115°	622.2	485.5	371.1	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9
117.5°	588.5	470.4	372.5	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9
120°	570.9	463.4	375.1	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8
122.5°	556.3	459.1	379.4	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8
125°	537.7	453.2	386.1	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0
127.5°	521.3	450.4	393.6	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1
130°	512.4	448.5	398.7	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3
132.5°	504.2	447.8	402.5	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7
135°	493.4	446.9	408.2	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7
137.5°	484.1	445.1	412.0	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1
140°	478.5	444.5	414.5	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0
142.5°	473.4	443.2	416.4	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6
145°	466.7	441.3	417.7	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8
147.5°	460.0	438.4	417.7	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2
150°	455.6	435.9	417.7	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3
152.5°	450.5	432.6	415.8	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5
155°	442.9	427.2	413.7	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8
157.5°	434.4	422.2	411.0	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6
160°	428.7	418.5	409.8	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2
162.5°	423.0	414.7	407.3	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0
165°	415.3	409.0	403.4	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4
167.5°	407.9	403.3	399.7	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9
170°	403.4	399.5	397.2	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7
172.5°	399.0	396.4	395.3	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3
175°	393.9	392.4	392.4	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2
177.5°	390.6	390.0	390.6	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.6	11.9	13.7	14.8	16.9	18.6	18.7	18.3	18.3	17.8	17.5
90°	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7
92.5°	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4
95°	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3
97.5°	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5
100°	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9
102.5°	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7
105°	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4
107.5°	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2
110°	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1
115°	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2
117.5°	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9
120°	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2
122.5°	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8
125°	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6
127.5°	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6
130°	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5
132.5°	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6
135°	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3
137.5°	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9
140°	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5
142.5°	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8
145°	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9
147.5°	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3
150°	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7
152.5°	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8
155°	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4
157.5°	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2
160°	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0
162.5°	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4
165°	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6
167.5°	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0
170°	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4
172.5°	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3
175°	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6
177.5°	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	17.2	17.0	16.9	17.1	16.9	16.6	17.3
90°	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1



TEST NUMBER: P331975-840

CATALOG NUMBER: S123DIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)