

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332358-840

Luminaire Tested: **S123RDIP-S1000D1195U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332358-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7971.4 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48				48
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	47	41				41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35				35
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30				30
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30	26				26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23				23
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18				18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16				16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15				15
10	47	35	28	24	44	33	27	22	29	24	20	25	20	18	21	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.0
10°-20°	442.8	5.6
20°-30°	637.6	8.0
30°-40°	718.2	9.0
40°-50°	687.1	8.6
50°-60°	562.6	7.1
60°-70°	379.6	4.8
70°-80°	191.0	2.4
80°-90°	54.9	0.7
90°-100°	97.3	1.2
100°-110°	291.2	3.7
110°-120°	495.4	6.2
120°-130°	651.6	8.2
130°-140°	732.3	9.2
140°-150°	719.9	9.0
150°-160°	606.0	7.6
160°-170°	403.4	5.1
170°-180°	141.3	1.8
0°-30°	1239.5	15.5
0°-40°	1957.7	24.6
0°-60°	3207.4	40.2
0°-90°	3832.9	48.1
90°-120°	883.9	11.1
90°-150°	2987.7	37.5
90°-180°	4138.0	51.9
0°-180°	7971.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	1	13	28	33	35	8
95°	69	78	87	91	92	78
105°	264	267	277	277	279	283
115°	499	502	500	501	500	493
125°	730	733	731	726	722	651
135°	947	953	953	948	946	729
145°	1149	1151	1155	1153	1149	717
155°	1315	1315	1316	1320	1313	605
165°	1433	1429	1429	1435	1428	404
175°	1490	1486	1485	1492	1484	141
180°	1494	1494	1494	1494	1494	



TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.7	24.4	22.3	20.1	18.0	17.2	17.9	18.6	19.3	19.9	19.9
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	28.4	30.2	31.9	33.7	35.4	37.4	39.3	41.2	43.1	45.0	45.8
95°	69.3	71.1	72.9	74.7	76.5	78.5	80.6	82.6	84.7	86.8	87.9
97.5°	123.0	124.3	125.7	127.0	128.4	129.9	131.4	132.9	134.3	135.8	137.0
100°	159.6	161.2	162.7	164.3	165.8	167.2	168.5	169.9	171.2	172.5	173.3
102.5°	201.8	202.8	203.7	204.6	205.6	206.9	208.6	210.4	212.1	213.8	214.6
105°	264.0	264.5	265.1	265.6	266.1	267.5	269.8	272.3	274.6	276.9	276.9
107.5°	336.3	336.6	336.9	337.2	337.5	338.2	339.1	340.0	340.9	341.9	342.7
110°	381.3	381.8	382.3	382.9	383.4	384.0	384.5	385.0	385.5	386.1	387.1



TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.3	428.6	428.9	429.2	429.5	429.7	429.8	429.9	430.0	430.1	431.4
115°	498.7	499.5	500.2	501.0	501.8	501.9	501.4	500.9	500.4	499.9	500.1
117.5°	569.6	570.1	570.6	571.1	571.6	571.6	570.9	570.2	569.6	568.9	568.8
120°	613.7	615.2	616.8	618.3	620.0	620.1	618.7	617.4	616.1	614.8	614.6
122.5°	659.6	660.8	662.0	663.1	664.3	664.5	663.8	663.1	662.5	661.8	661.1
125°	729.8	730.6	731.3	732.2	733.0	733.1	732.6	732.1	731.5	731.0	729.9
127.5°	794.6	796.3	797.9	799.6	801.2	801.8	801.2	800.6	800.1	799.5	798.1
130°	837.8	839.8	841.9	844.0	846.1	846.8	846.0	845.2	844.4	843.6	842.6
132.5°	880.9	883.0	885.1	887.2	889.3	890.1	889.5	888.9	888.3	887.8	886.5
135°	946.8	948.5	950.0	951.6	953.1	953.8	953.5	953.3	953.0	952.7	951.7
137.5°	1007.9	1009.2	1010.5	1011.8	1013.1	1014.1	1014.8	1015.4	1016.1	1016.8	1015.7
140°	1050.2	1051.5	1052.8	1054.1	1055.3	1056.1	1056.4	1056.6	1056.9	1057.2	1056.9
142.5°	1088.6	1089.9	1091.3	1092.6	1093.9	1094.7	1095.2	1095.7	1096.1	1096.6	1096.3
145°	1148.7	1149.2	1149.7	1150.2	1150.7	1151.4	1152.3	1153.0	1153.8	1154.6	1154.3
147.5°	1201.2	1202.2	1203.2	1204.1	1205.1	1205.9	1206.6	1207.3	1208.0	1208.8	1208.8
150°	1237.9	1238.4	1238.9	1239.4	1240.0	1240.5	1241.0	1241.5	1242.0	1242.5	1242.5
152.5°	1267.9	1268.7	1269.4	1270.1	1270.8	1271.3	1271.6	1272.0	1272.3	1272.6	1273.0
155°	1315.3	1315.3	1315.3	1315.3	1315.3	1315.5	1315.8	1316.0	1316.3	1316.5	1317.6
157.5°	1355.6	1355.3	1355.0	1354.7	1354.4	1354.3	1354.6	1354.8	1355.0	1355.2	1356.3
160°	1381.0	1380.5	1380.0	1379.5	1379.0	1378.7	1378.7	1378.7	1378.7	1378.7	1380.0
162.5°	1403.5	1402.8	1402.1	1401.4	1400.7	1400.4	1400.6	1400.8	1401.0	1401.2	1402.5
165°	1432.7	1431.9	1431.1	1430.3	1429.6	1429.2	1429.2	1429.2	1429.2	1429.2	1430.7
167.5°	1455.9	1454.8	1453.8	1452.8	1451.7	1451.3	1451.5	1451.7	1451.9	1452.1	1453.7
170°	1469.1	1467.9	1466.9	1465.9	1464.8	1464.3	1464.3	1464.3	1464.3	1464.3	1466.1
172.5°	1479.4	1478.3	1477.2	1476.2	1475.2	1474.7	1474.7	1474.7	1474.7	1474.7	1476.3
175°	1490.2	1489.1	1488.0	1487.0	1486.0	1485.4	1485.4	1485.4	1485.4	1485.4	1487.0
177.5°	1494.6	1493.8	1493.0	1492.1	1491.3	1490.9	1490.9	1490.9	1490.9	1490.9	1492.1
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7



TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	19.9	19.8	19.8	19.7	19.6	19.4	19.3	19.1
90°	30.3	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	46.8	47.6	48.4	48.7	48.4	48.1	47.7	47.4
95°	88.9	90.0	91.0	91.5	91.5	91.5	91.5	91.5
97.5°	138.3	139.5	140.7	141.2	141.1	141.0	140.9	140.8
100°	174.0	174.8	175.6	176.2	176.8	177.3	177.8	178.3
102.5°	215.3	216.1	216.9	217.2	217.1	217.0	216.9	216.8
105°	276.9	276.9	276.9	277.2	277.7	278.2	278.7	279.2
107.5°	343.6	344.5	345.3	345.5	345.2	344.9	344.6	344.3
110°	388.1	389.2	390.2	390.4	389.9	389.4	388.9	388.4



TEST NUMBER: P332358-840

CATALOG NUMBER: S123RDIP-S1000D1195U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.6	433.9	435.2	435.8	435.7	435.6	435.5	435.4
115°	500.4	500.6	500.9	500.9	500.6	500.4	500.1	499.9
117.5°	568.8	568.7	568.7	568.3	567.5	566.7	566.0	565.3
120°	614.3	614.1	613.8	613.4	612.9	612.4	611.9	611.3
122.5°	660.5	659.7	659.0	658.3	657.6	656.9	656.1	655.4
125°	728.9	727.9	726.8	725.8	724.8	723.7	722.7	721.6
127.5°	796.6	795.2	793.7	792.3	791.1	789.9	788.7	787.6
130°	841.5	840.5	839.5	838.0	836.2	834.4	832.5	830.7
132.5°	885.2	884.0	882.7	881.4	880.0	878.6	877.2	875.8
135°	950.7	949.6	948.6	947.8	947.3	946.7	946.2	945.7
137.5°	1014.6	1013.5	1012.4	1011.4	1010.4	1009.5	1008.5	1007.4
140°	1056.6	1056.4	1056.1	1055.1	1053.3	1051.5	1049.7	1047.8
142.5°	1096.1	1095.8	1095.6	1094.7	1093.3	1091.9	1090.6	1089.1
145°	1154.1	1153.8	1153.6	1152.9	1151.9	1150.7	1149.7	1148.7
147.5°	1208.8	1208.8	1208.8	1208.0	1206.4	1204.9	1203.3	1201.7
150°	1242.5	1242.5	1242.5	1241.8	1240.2	1238.7	1237.1	1235.6
152.5°	1273.4	1273.8	1274.2	1273.8	1272.4	1271.1	1269.7	1268.4
155°	1318.6	1319.6	1320.7	1320.3	1318.5	1316.7	1314.8	1312.9
157.5°	1357.4	1358.5	1359.6	1359.4	1358.0	1356.5	1355.0	1353.5
160°	1381.3	1382.6	1383.9	1384.0	1383.0	1381.9	1380.9	1379.9
162.5°	1403.8	1405.1	1406.4	1406.2	1404.5	1402.9	1401.2	1399.6
165°	1432.3	1433.8	1435.4	1435.2	1433.4	1431.6	1429.8	1427.9
167.5°	1455.3	1456.9	1458.5	1458.5	1456.9	1455.3	1453.7	1452.1
170°	1467.9	1469.9	1471.7	1471.7	1469.9	1467.9	1466.1	1464.3
172.5°	1477.9	1479.6	1481.2	1481.1	1479.1	1477.3	1475.5	1473.7
175°	1488.5	1490.2	1491.7	1491.6	1489.8	1487.9	1486.1	1484.3
177.5°	1493.4	1494.6	1495.8	1495.7	1494.3	1492.8	1491.4	1490.0
180°	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7	1493.7

(END OF REPORT)