

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832458

Luminaire Tested: S123RDP-S340D830-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832458
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S340D830-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1388.3 lumens
 Efficiency: N/A
 Efficacy: 112.0 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 12.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832458
CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832458

CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11271	11271	11271	11271	11271
5°	13383	12956	11342	9168	8512
10°	12125	13160	11285	7346	6302
15°	8349	11283	11166	6004	4985
20°	5808	8687	10942	5063	4381
25°	4425	6621	10615	4500	4038
30°	3853	5294	10208	4179	3740
35°	3537	4465	9629	3907	3469
40°	3228	3988	8873	3641	3222
45°	2915	3647	8057	3389	2973
50°	2646	3364	7095	3141	2668
55°	2393	3089	6172	2901	2288
60°	2144	2809	5360	2635	2164
65°	1979	2493	4615	2366	2045
70°	1608	2156	4025	2140	1662
75°	1410	1713	3410	1776	1464
80°	1277	1450	2796	1488	1382
85°	1161	1272	2124	1346	1272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8502 cd/sqm

TEST NUMBER: P832458
 CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.4	6.9
10°-20°	220.8	15.9
20°-30°	253.4	18.3
30°-40°	249.8	18.0
40°-50°	220.3	15.9
50°-60°	169.5	12.2
60°-70°	111.4	8.0
70°-80°	54.1	3.9
80°-90°	13.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.7	41.0
0°-40°	819.4	59.0
0°-60°	1209.1	87.1
0°-90°	1388.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1388.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1047	1047	1047	1047	1047	
5°	1239	1199	1050	848	788	113
15°	749	1012	1002	539	447	211
25°	373	558	894	379	340	176
35°	269	340	733	297	264	168
45°	192	240	529	223	195	149
55°	128	165	329	155	122	114
65°	78	98	181	93	80	76
75°	34	41	82	43	35	36
85°	9	10	17	11	10	11
90°	0	0	0	0	0	

TEST NUMBER: P832458

CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1
2.5°	1160.4	1156.8	1153.1	1152.1	1151.0	1147.6	1144.1	1136.4	1128.7	1120.7	1112.8
5°	1238.6	1239.0	1239.4	1238.4	1237.3	1232.8	1228.3	1218.8	1209.4	1199.1	1188.8
7.5°	1214.5	1221.4	1228.3	1229.6	1230.8	1234.3	1237.7	1235.6	1233.4	1229.6	1225.7
10°	1109.3	1108.9	1108.5	1116.2	1123.9	1146.9	1169.9	1181.7	1193.5	1204.0	1214.5
12.5°	937.6	938.3	938.9	964.2	989.6	1011.2	1032.9	1063.0	1093.0	1125.4	1157.9
15°	749.2	759.7	770.2	792.7	815.3	847.9	880.5	920.9	961.2	1012.5	1063.8
17.5°	615.2	619.7	624.2	645.9	667.6	698.5	729.4	775.1	820.8	887.0	953.1
20°	507.0	511.1	515.2	530.8	546.5	576.1	605.8	649.3	692.9	758.4	823.9
22.5°	423.3	431.2	439.2	449.7	460.2	481.7	503.2	547.6	592.0	651.7	711.4
25°	372.6	376.3	379.9	389.0	398.0	418.6	439.2	468.6	498.0	557.5	616.9
27.5°	338.3	339.4	340.4	347.1	353.8	367.1	380.4	407.6	434.9	483.8	532.8
30°	310.0	311.9	313.8	319.0	324.1	333.8	343.5	362.8	382.1	425.9	469.7
32.5°	288.1	289.1	290.2	294.5	298.8	305.9	313.0	328.2	343.5	376.9	410.4
35°	269.2	269.4	269.6	272.8	276.0	282.9	289.8	302.5	315.1	339.8	364.5
37.5°	247.7	249.2	250.7	253.1	255.4	261.5	267.5	277.8	288.1	308.5	328.9
40°	229.7	231.0	232.3	235.0	237.8	242.6	247.3	256.7	266.2	283.8	301.4
42.5°	211.7	212.5	213.4	216.2	219.0	224.7	230.5	238.1	245.6	260.2	274.8
45°	191.5	193.6	195.8	198.8	201.8	206.7	211.7	219.4	227.1	239.6	252.0
47.5°	174.7	175.8	176.9	179.5	182.0	188.0	194.0	200.9	207.8	219.4	231.0
50°	158.0	158.4	158.8	161.2	163.6	168.9	174.3	182.2	190.2	200.9	211.7
52.5°	142.1	143.2	144.2	146.6	149.0	152.6	156.3	164.4	172.6	183.1	193.6
55°	127.5	128.2	128.8	130.5	132.2	136.5	140.8	147.9	155.0	164.6	174.3
57.5°	113.8	114.6	115.5	116.8	118.1	121.9	125.8	132.0	138.2	147.9	157.6
60°	99.6	100.7	101.7	103.2	104.8	107.8	110.8	116.3	121.9	130.5	139.1
62.5°	89.3	89.5	89.7	91.0	92.3	94.4	96.6	101.1	105.6	114.2	122.8
65°	77.7	78.3	79.0	79.6	80.3	82.0	83.7	87.6	91.4	97.9	104.3
67.5°	65.7	66.3	67.0	68.0	69.1	70.6	72.1	74.7	77.3	83.3	89.3
70°	51.1	51.1	51.1	52.8	54.5	57.1	59.7	61.6	63.5	68.5	73.4
72.5°	41.6	41.9	42.1	42.3	42.5	44.0	45.5	48.7	51.9	55.0	58.0
75°	33.9	34.1	34.3	34.6	34.8	35.2	35.6	36.7	37.8	41.2	44.6
77.5°	27.0	27.3	27.5	27.7	27.9	28.3	28.8	29.2	29.6	30.9	32.2
80°	20.6	20.8	21.0	21.3	21.5	21.7	21.9	22.3	22.8	23.4	24.0
82.5°	15.0	15.0	15.0	15.0	15.0	15.5	15.9	15.9	15.9	16.3	16.7
85°	9.4	9.4	9.4	9.7	9.9	9.9	9.9	10.1	10.3	10.3	10.3
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.5	4.7	4.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832458

CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1
2.5°	1111.7	1110.6	1100.3	1090.0	1079.9	1069.9	1062.3	1054.8	1042.2	1029.5	1021.6
5°	1180.6	1172.5	1156.1	1139.8	1115.4	1090.9	1070.3	1049.7	1023.5	997.3	975.4
7.5°	1219.0	1212.4	1192.6	1172.9	1140.5	1108.1	1075.9	1043.7	1005.0	966.4	933.3
10°	1220.1	1225.7	1209.4	1193.1	1156.6	1120.1	1076.3	1032.5	980.6	928.6	885.9
12.5°	1181.9	1205.9	1202.5	1199.1	1161.9	1124.8	1071.6	1018.3	954.6	890.8	837.4
15°	1110.4	1157.0	1170.7	1184.5	1153.8	1123.1	1062.6	1002.0	927.1	852.2	790.8
17.5°	1018.3	1083.6	1119.9	1156.1	1133.8	1111.5	1045.2	978.8	894.5	810.1	743.4
20°	909.3	994.7	1051.6	1108.5	1100.3	1092.2	1023.7	955.2	864.2	773.2	700.9
22.5°	801.5	891.7	970.2	1048.8	1057.2	1065.6	996.4	927.3	827.7	728.1	654.5
25°	708.6	800.2	893.8	987.4	1006.3	1025.2	959.5	893.8	790.6	687.3	614.1
27.5°	619.9	707.1	810.1	913.2	947.5	981.8	921.7	861.6	754.1	646.5	573.6
30°	547.6	625.5	730.7	835.9	883.7	931.6	876.4	821.3	714.6	607.9	536.4
32.5°	480.2	550.0	655.6	761.2	816.8	872.4	824.7	777.1	674.5	571.8	501.2
35°	427.0	489.4	587.9	686.5	748.7	811.0	771.9	732.8	632.6	532.3	465.6
37.5°	381.2	433.6	526.1	618.6	684.8	750.9	718.2	685.6	591.4	497.1	434.0
40°	343.5	385.5	471.6	557.7	622.5	687.3	659.4	631.5	547.2	462.8	403.8
42.5°	311.0	347.3	424.6	501.9	561.3	620.8	602.3	583.9	507.4	431.0	376.3
45°	282.5	313.0	381.0	449.1	503.8	558.5	543.9	529.3	463.4	397.5	347.3
47.5°	257.2	283.3	344.1	404.8	454.0	503.2	489.6	476.1	421.6	367.1	321.3
50°	234.0	256.3	307.0	357.6	401.8	446.1	434.9	423.7	378.7	333.6	294.1
52.5°	212.1	230.5	276.0	321.6	357.2	392.8	384.2	375.6	340.9	306.1	270.3
55°	191.3	208.2	246.6	285.1	315.5	346.0	337.4	328.9	301.8	274.8	243.2
57.5°	172.4	187.2	218.3	249.4	273.7	297.9	293.9	289.8	267.2	244.7	218.7
60°	152.4	165.7	192.5	219.4	238.9	258.4	253.7	249.0	232.9	216.8	194.5
62.5°	134.6	146.4	167.9	189.3	205.2	221.1	217.7	214.2	202.0	189.8	171.3
65°	115.9	127.5	144.9	162.3	174.7	187.2	184.2	181.2	171.9	162.7	147.9
67.5°	99.0	108.6	123.6	138.7	147.0	155.4	153.7	152.0	144.9	137.8	126.2
70°	81.8	90.2	102.6	115.1	120.9	126.6	127.3	127.9	121.5	115.1	106.5
72.5°	64.6	71.3	82.9	94.4	99.0	103.5	103.2	103.0	99.2	95.3	87.6
75°	49.6	54.5	63.5	72.6	76.4	80.3	81.1	82.0	78.3	74.7	70.4
77.5°	35.6	39.1	45.9	52.8	57.1	61.4	61.8	62.3	60.5	58.8	54.7
80°	25.1	26.2	30.5	34.8	39.3	43.8	44.4	45.1	43.4	41.6	39.1
82.5°	17.4	18.0	19.5	21.0	24.7	28.3	29.2	30.1	29.2	28.3	25.5
85°	10.5	10.7	11.4	12.0	13.7	15.5	16.3	17.2	16.7	16.3	14.8
87.5°	4.7	4.7	4.9	5.2	5.6	6.0	7.1	8.2	7.5	6.9	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832458

CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1	1047.1
2.5°	1013.6	1001.4	989.1	980.3	971.5	960.6	949.6	949.2	948.8	940.6	932.5
5°	953.5	932.3	911.0	890.2	869.4	848.5	827.7	823.0	818.3	811.2	804.1
7.5°	900.3	866.4	832.4	805.8	779.2	758.4	737.6	723.4	709.2	698.3	687.3
10°	843.2	801.1	759.0	726.8	694.6	672.1	649.6	633.2	616.9	609.2	601.5
12.5°	783.9	738.2	692.5	660.9	629.4	602.3	575.3	560.5	545.7	534.9	524.2
15°	729.4	680.2	631.1	597.6	564.1	538.8	513.5	498.6	483.8	473.1	462.4
17.5°	676.6	627.0	577.4	543.5	509.6	486.6	463.7	449.3	434.9	428.2	421.6
20°	628.5	578.5	528.5	496.5	464.5	442.0	419.4	411.7	404.0	397.8	391.5
22.5°	580.9	532.8	484.7	454.0	423.3	407.0	390.7	384.5	378.2	373.5	368.8
25°	540.9	493.1	445.2	418.4	391.5	378.9	366.2	362.1	358.0	353.3	348.6
27.5°	500.6	455.1	409.6	388.1	366.6	356.3	346.0	340.9	335.7	331.9	328.0
30°	464.9	422.9	380.8	363.0	345.2	336.2	327.1	321.6	316.0	312.3	308.7
32.5°	430.6	393.3	355.9	340.7	325.4	316.6	307.8	302.5	297.1	292.8	288.5
35°	398.8	366.4	334.0	320.1	306.1	297.3	288.5	283.1	277.8	273.5	269.2
37.5°	370.9	341.5	312.1	299.0	285.9	278.2	270.5	264.9	259.3	254.8	250.3
40°	344.7	318.8	292.8	280.1	267.5	259.1	250.7	245.8	240.8	236.8	232.7
42.5°	321.6	297.7	273.9	261.5	249.0	241.1	233.1	227.3	221.5	219.2	216.8
45°	297.1	276.0	255.0	243.0	231.0	222.6	214.2	209.3	204.4	202.2	200.1
47.5°	275.6	256.1	236.6	224.7	212.9	205.4	197.9	194.0	190.2	187.2	184.2
50°	254.6	235.7	216.8	205.4	194.0	187.6	181.2	176.4	171.7	169.6	167.4
52.5°	234.4	217.2	200.1	188.5	176.9	170.7	164.4	160.3	156.3	151.8	147.3
55°	211.7	196.6	181.6	171.3	161.0	154.6	148.1	143.4	138.7	133.9	129.2
57.5°	192.8	178.0	163.1	153.9	144.7	138.5	132.2	127.1	121.9	118.1	114.2
60°	172.2	159.3	146.4	137.4	128.4	122.4	116.3	111.4	106.5	104.5	102.6
62.5°	152.8	140.8	128.8	120.9	112.9	107.1	101.3	98.1	94.9	93.6	92.3
65°	133.1	122.8	112.5	105.2	97.9	92.9	88.0	86.5	85.0	83.9	82.9
67.5°	114.6	105.8	97.0	90.6	84.1	80.7	77.3	75.6	73.8	72.6	71.3
70°	97.9	90.2	82.4	76.8	71.3	68.0	64.8	63.3	61.8	59.5	57.1
72.5°	79.9	73.8	67.8	63.5	59.2	56.5	53.7	50.7	47.7	45.5	43.4
75°	66.1	60.1	54.1	50.0	45.9	42.7	39.5	38.4	37.4	36.7	36.1
77.5°	50.7	45.5	40.4	37.1	33.9	32.4	30.9	30.3	29.6	29.4	29.2
80°	36.5	32.2	27.9	26.2	24.5	24.0	23.6	23.2	22.8	22.5	22.3
82.5°	22.8	20.6	18.5	18.0	17.6	17.4	17.2	17.0	16.7	16.5	16.3
85°	13.3	12.5	11.6	11.4	11.2	10.9	10.7	10.7	10.7	10.7	10.7
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832458

CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1047.1	1047.1	1047.1	1047.1
2.5°	930.3	928.2	927.3	926.5
5°	797.5	790.8	789.3	787.8
7.5°	684.5	681.8	672.5	663.3
10°	592.9	584.3	580.4	576.6
12.5°	516.2	508.3	507.0	505.7
15°	456.8	451.2	449.3	447.3
17.5°	417.7	413.9	411.5	409.1
20°	388.7	386.0	384.2	382.5
22.5°	366.6	364.5	363.2	361.9
25°	345.4	342.2	341.1	340.0
27.5°	325.2	322.4	321.3	320.3
30°	306.3	304.0	302.5	300.9
32.5°	285.7	282.9	282.1	281.2
35°	267.5	265.7	264.9	264.0
37.5°	248.1	246.0	244.7	243.4
40°	231.6	230.5	229.9	229.3
42.5°	214.9	212.9	212.7	212.5
45°	198.1	196.2	195.8	195.3
47.5°	182.5	180.7	180.5	180.3
50°	165.1	162.7	161.0	159.3
52.5°	145.1	143.0	141.5	140.0
55°	126.9	124.5	123.2	121.9
57.5°	113.1	112.1	111.4	110.8
60°	102.0	101.3	100.9	100.5
62.5°	91.7	91.0	91.0	91.0
65°	82.2	81.6	80.9	80.3
67.5°	70.0	68.7	68.5	68.3
70°	55.2	53.2	53.0	52.8
72.5°	43.1	42.9	42.5	42.1
75°	35.6	35.2	35.2	35.2
77.5°	28.8	28.3	28.3	28.3
80°	22.1	21.9	22.1	22.3
82.5°	16.3	16.3	16.1	15.9
85°	10.5	10.3	10.3	10.3
87.5°	5.2	5.2	5.2	5.2
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832458

CATALOG NUMBER: S123RDP-S340D830-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.12	14.58	13.48	14.89	15.20	17.78	19.24	18.15	19.55	19.87
	3H	14.38	15.69	14.76	16.01	16.38	19.33	20.63	19.70	20.96	21.32
	4H	14.79	16.01	15.19	16.36	16.74	19.84	21.06	20.24	21.41	21.79
	6H	15.10	16.23	15.52	16.60	16.99	20.18	21.31	20.60	21.68	22.07
	8H	15.21	16.28	15.63	16.67	17.07	20.28	21.35	20.71	21.74	22.14
	12H	15.28	16.30	15.71	16.68	17.11	20.33	21.35	20.76	21.74	22.16
4H	2H	13.91	15.13	14.31	15.48	15.86	17.85	19.07	18.25	19.42	19.80
	3H	15.33	16.34	15.74	16.74	17.15	19.56	20.57	19.97	20.97	21.37
	4H	15.81	16.72	16.24	17.13	17.57	20.19	21.09	20.62	21.51	21.95
	6H	16.21	17.00	16.67	17.44	17.90	20.65	21.44	21.11	21.89	22.35
	8H	16.34	17.08	16.81	17.52	17.99	20.80	21.53	21.26	21.98	22.44
	12H	16.45	17.10	16.93	17.58	18.05	20.89	21.54	21.37	22.02	22.49
8H	4H	16.16	16.90	16.63	17.34	17.81	20.19	20.93	20.66	21.37	21.84
	6H	16.65	17.25	17.15	17.75	18.23	20.71	21.32	21.21	21.81	22.29
	8H	16.84	17.39	17.36	17.90	18.39	20.90	21.44	21.41	21.95	22.44
	12H	17.01	17.49	17.52	17.98	18.55	21.04	21.52	21.55	22.01	22.58
12H	4H	16.20	16.86	16.69	17.34	17.81	20.17	20.83	20.65	21.31	21.78
	6H	16.71	17.25	17.22	17.76	18.25	20.68	21.23	21.20	21.74	22.23
	8H	16.95	17.43	17.47	17.93	18.49	20.91	21.38	21.42	21.88	22.44